

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332239

Luminaire Tested: **S123DIW-S1165D1535U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332239
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10081.2 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	47	47	47		
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40	40	40	40	40	40	40		
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	42	40	38	33	33	33	33	33	33	33		
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28	28	28	28	28	28	28		
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24	24	24	24		
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21	21	21	21	21	21	21		
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21	18	18	18	18	18	18	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16	16	16	16	16	16	16		
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15	15	15	15	15	15	15		
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13	13	13	13		
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12	12	12	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	1.7
10°-20°	486.2	4.8
20°-30°	718.3	7.1
30°-40°	839.0	8.3
40°-50°	843.5	8.4
50°-60°	740.9	7.3
60°-70°	552.0	5.5
70°-80°	314.5	3.1
80°-90°	96.0	1.0
90°-100°	125.1	1.2
100°-110°	374.3	3.7
110°-120°	636.6	6.3
120°-130°	837.4	8.3
130°-140°	941.2	9.3
140°-150°	925.2	9.2
150°-160°	778.9	7.7
160°-170°	518.5	5.1
170°-180°	181.6	1.8
0°-30°	1376.7	13.7
0°-40°	2215.7	22.0
0°-60°	3800.2	37.7
0°-90°	4762.6	47.2
90°-120°	1136.0	11.3
90°-150°	3839.7	38.1
90°-180°	5319.0	52.8
0°-180°	10081.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	2	17	36	42	45	10
95°	89	100	112	117	118	100
105°	339	343	356	356	359	363
115°	641	645	642	644	642	634
125°	938	942	940	933	927	836
135°	1217	1225	1224	1219	1215	937
145°	1476	1479	1484	1482	1476	922
155°	1690	1690	1692	1697	1687	778
165°	1841	1837	1837	1845	1835	519
175°	1915	1909	1909	1917	1908	182
180°	1920	1920	1920	1920	1920	



TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	33.0	32.8	32.7	32.5	32.3	32.5	33.1	33.7	34.3	34.9	34.9
90°	1.5	4.9	8.2	11.6	14.9	18.8	23.1	27.5	31.8	36.2	37.5
92.5°	36.5	38.8	41.0	43.3	45.6	48.0	50.5	52.9	55.4	57.9	59.0
95°	89.0	91.3	93.7	96.0	98.4	100.9	103.5	106.2	108.9	111.6	112.9
97.5°	158.0	159.8	161.5	163.3	165.0	166.8	168.8	170.7	172.7	174.6	176.2
100°	205.1	207.1	209.1	211.1	213.1	215.0	216.6	218.3	220.0	221.7	222.7
102.5°	259.4	260.6	261.8	263.0	264.2	265.9	268.1	270.3	272.5	274.7	275.8
105°	339.3	340.0	340.6	341.3	342.0	343.8	346.8	349.8	352.9	355.9	355.9
107.5°	432.2	432.6	433.0	433.4	433.8	434.6	435.8	437.0	438.2	439.4	440.5
110°	490.1	490.8	491.4	492.1	492.8	493.4	494.1	494.8	495.4	496.1	497.5



TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	550.4	550.8	551.2	551.6	552.0	552.3	552.4	552.5	552.7	552.8	554.4
115°	640.9	641.9	642.9	643.9	644.9	645.1	644.4	643.7	643.1	642.4	642.7
117.5°	732.0	732.6	733.3	734.0	734.6	734.5	733.7	732.8	731.9	731.1	731.0
120°	788.7	790.7	792.7	794.7	796.7	796.9	795.2	793.5	791.8	790.2	789.8
122.5°	847.8	849.2	850.7	852.2	853.7	854.0	853.1	852.2	851.4	850.5	849.6
125°	937.9	938.9	940.0	941.0	942.0	942.1	941.5	940.8	940.1	939.5	938.1
127.5°	1021.2	1023.3	1025.5	1027.6	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6
130°	1076.7	1079.4	1082.0	1084.7	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9
132.5°	1132.2	1134.8	1137.5	1140.2	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3
135°	1216.9	1218.9	1220.9	1222.9	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1
137.5°	1295.3	1297.0	1298.7	1300.4	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4
140°	1349.6	1351.3	1353.0	1354.6	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3
142.5°	1399.1	1400.7	1402.4	1404.1	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0
145°	1476.3	1477.0	1477.6	1478.3	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5
147.5°	1543.8	1545.0	1546.2	1547.5	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5
150°	1590.9	1591.6	1592.2	1592.9	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9
152.5°	1629.5	1630.4	1631.4	1632.3	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1
155°	1690.4	1690.4	1690.4	1690.4	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3
157.5°	1742.3	1741.9	1741.5	1741.1	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1
160°	1774.9	1774.2	1773.5	1772.8	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5
162.5°	1803.8	1802.9	1801.9	1801.0	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5
165°	1841.2	1840.2	1839.2	1838.2	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7
167.5°	1871.1	1869.7	1868.4	1867.0	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3
170°	1887.9	1886.6	1885.3	1883.9	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3
172.5°	1901.2	1899.9	1898.5	1897.2	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3
175°	1915.1	1913.8	1912.4	1911.1	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1
177.5°	1920.8	1919.8	1918.7	1917.6	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	34.9	34.9	34.9	34.9	35.1	35.2	35.3	35.5
90°	38.9	40.2	41.6	42.6	43.2	43.9	44.6	45.2
92.5°	60.0	61.1	62.2	62.5	62.1	61.7	61.3	60.9
95°	114.3	115.6	116.9	117.6	117.6	117.6	117.6	117.6
97.5°	177.7	179.2	180.8	181.5	181.4	181.2	181.1	181.0
100°	223.7	224.7	225.7	226.5	227.2	227.9	228.5	229.2
102.5°	276.8	277.8	278.8	279.2	279.1	278.9	278.8	278.7
105°	355.9	355.9	355.9	356.2	356.9	357.6	358.2	358.9
107.5°	441.6	442.6	443.7	444.0	443.6	443.2	442.8	442.4
110°	498.8	500.1	501.5	501.8	501.1	500.5	499.8	499.1



TEST NUMBER: P332239

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	556.0	557.6	559.2	560.0	559.9	559.7	559.6	559.4
115°	643.1	643.4	643.7	643.7	643.4	643.1	642.7	642.4
117.5°	730.9	730.9	730.8	730.3	729.3	728.4	727.5	726.5
120°	789.5	789.2	788.8	788.3	787.7	787.0	786.3	785.6
122.5°	848.7	847.9	847.0	846.1	845.2	844.2	843.3	842.3
125°	936.8	935.4	934.1	932.7	931.4	930.1	928.7	927.4
127.5°	1023.8	1021.9	1020.0	1018.3	1016.8	1015.2	1013.7	1012.1
130°	1081.5	1080.2	1078.9	1077.0	1074.7	1072.3	1070.0	1067.6
132.5°	1137.7	1136.1	1134.5	1132.8	1131.0	1129.2	1127.3	1125.5
135°	1221.8	1220.4	1219.1	1218.1	1217.4	1216.7	1216.1	1215.4
137.5°	1304.0	1302.6	1301.2	1299.8	1298.5	1297.3	1296.0	1294.7
140°	1358.0	1357.7	1357.3	1356.0	1353.6	1351.3	1348.9	1346.6
142.5°	1408.7	1408.3	1408.0	1406.9	1405.1	1403.3	1401.5	1399.7
145°	1483.1	1482.8	1482.5	1481.6	1480.3	1479.0	1477.6	1476.3
147.5°	1553.5	1553.5	1553.5	1552.5	1550.5	1548.5	1546.4	1544.4
150°	1596.9	1596.9	1596.9	1595.9	1593.9	1591.9	1589.9	1587.9
152.5°	1636.6	1637.1	1637.7	1637.1	1635.3	1633.6	1631.8	1630.1
155°	1694.6	1695.9	1697.3	1696.8	1694.4	1692.1	1689.7	1687.4
157.5°	1744.5	1745.9	1747.3	1747.1	1745.2	1743.3	1741.4	1739.6
160°	1775.2	1776.9	1778.5	1778.7	1777.4	1776.0	1774.7	1773.3
162.5°	1804.1	1805.8	1807.5	1807.3	1805.1	1803.0	1800.8	1798.7
165°	1840.7	1842.7	1844.7	1844.6	1842.2	1839.9	1837.5	1835.2
167.5°	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2
170°	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9
172.5°	1899.3	1901.4	1903.5	1903.4	1901.0	1898.7	1896.3	1894.0
175°	1913.1	1915.1	1917.1	1916.9	1914.6	1912.2	1909.9	1907.6
177.5°	1919.2	1920.8	1922.4	1922.3	1920.4	1918.5	1916.7	1914.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6

(END OF REPORT)