

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332101

Luminaire Tested: **S123DIW-S340D755U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332101
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4030.8 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	1.3
10°-20°	144.1	3.6
20°-30°	212.9	5.3
30°-40°	248.7	6.2
40°-50°	250.0	6.2
50°-60°	219.6	5.4
60°-70°	163.6	4.1
70°-80°	93.2	2.3
80°-90°	29.6	0.7
90°-100°	61.6	1.5
100°-110°	184.2	4.6
110°-120°	313.4	7.8
120°-130°	412.2	10.2
130°-140°	463.3	11.5
140°-150°	455.4	11.3
150°-160°	383.4	9.5
160°-170°	255.2	6.3
170°-180°	89.4	2.2
0°-30°	408.1	10.1
0°-40°	656.8	16.3
0°-60°	1126.5	27.9
0°-90°	1412.9	35.1
90°-120°	559.2	13.9
90°-150°	1890.0	46.9
90°-180°	2618.0	65.0
0°-180°	4030.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	1	8	18	21	22	4
95°	44	49	55	58	58	49
105°	167	169	175	175	177	179
115°	316	317	316	317	316	312
125°	462	464	462	459	456	412
135°	599	603	603	600	598	461
145°	727	728	730	730	727	454
155°	832	832	833	835	831	383
165°	906	904	904	908	903	255
175°	943	940	940	944	939	89
180°	945	945	945	945	945	



TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.8	9.9	10.0	10.1	10.2	10.4	10.7	11.1	11.4	11.8	11.8
90°	0.7	2.4	4.0	5.7	7.3	9.2	11.4	13.5	15.7	17.8	18.5
92.5°	18.0	19.1	20.2	21.3	22.4	23.6	24.8	26.1	27.3	28.5	29.0
95°	43.8	44.9	46.1	47.3	48.4	49.6	51.0	52.3	53.6	54.9	55.6
97.5°	77.8	78.6	79.5	80.4	81.2	82.1	83.1	84.0	85.0	86.0	86.7
100°	100.9	101.9	102.9	103.9	104.9	105.8	106.6	107.5	108.3	109.1	109.6
102.5°	127.7	128.3	128.9	129.4	130.0	130.9	132.0	133.1	134.1	135.2	135.7
105°	167.0	167.3	167.7	168.0	168.3	169.2	170.7	172.2	173.7	175.2	175.2
107.5°	212.7	212.9	213.1	213.3	213.5	213.9	214.5	215.1	215.7	216.3	216.8
110°	241.2	241.6	241.9	242.2	242.5	242.9	243.2	243.5	243.9	244.2	244.9



TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	270.9	271.1	271.3	271.5	271.7	271.8	271.9	272.0	272.0	272.1	272.9
115°	315.5	315.9	316.4	316.9	317.4	317.5	317.2	316.9	316.5	316.2	316.4
117.5°	360.3	360.6	360.9	361.3	361.6	361.6	361.1	360.7	360.3	359.8	359.8
120°	388.2	389.2	390.2	391.2	392.2	392.2	391.4	390.6	389.8	388.9	388.8
122.5°	417.3	418.0	418.7	419.5	420.2	420.3	419.9	419.5	419.1	418.6	418.2
125°	461.7	462.2	462.7	463.2	463.7	463.7	463.4	463.1	462.7	462.4	461.8
127.5°	502.6	503.7	504.8	505.8	506.9	507.2	506.9	506.5	506.1	505.8	504.8
130°	530.0	531.3	532.6	533.9	535.2	535.7	535.2	534.7	534.2	533.7	533.0
132.5°	557.3	558.6	559.9	561.2	562.6	563.0	562.7	562.3	561.9	561.6	560.8
135°	599.0	600.0	601.0	602.0	602.9	603.4	603.2	603.0	602.9	602.7	602.0
137.5°	637.6	638.4	639.2	640.1	640.9	641.5	641.9	642.4	642.8	643.2	642.5
140°	664.3	665.1	666.0	666.8	667.6	668.1	668.3	668.4	668.6	668.8	668.6
142.5°	688.7	689.5	690.3	691.1	691.9	692.5	692.8	693.1	693.4	693.7	693.5
145°	726.7	727.0	727.3	727.6	728.0	728.4	728.9	729.4	729.9	730.4	730.2
147.5°	759.9	760.5	761.1	761.7	762.3	762.8	763.3	763.7	764.2	764.7	764.7
150°	783.1	783.4	783.7	784.1	784.4	784.7	785.0	785.4	785.7	786.0	786.0
152.5°	802.1	802.5	803.0	803.5	803.9	804.2	804.4	804.6	804.8	805.0	805.3
155°	832.1	832.1	832.1	832.1	832.1	832.1	832.3	832.5	832.6	832.8	833.5
157.5°	857.6	857.4	857.2	857.0	856.8	856.8	856.9	857.0	857.2	857.3	858.0
160°	873.6	873.3	873.0	872.6	872.3	872.1	872.1	872.1	872.1	872.1	873.0
162.5°	887.9	887.4	886.9	886.5	886.0	885.9	886.0	886.1	886.3	886.4	887.2
165°	906.3	905.8	905.3	904.8	904.3	904.0	904.0	904.0	904.0	904.0	905.0
167.5°	921.0	920.3	919.7	919.0	918.3	918.1	918.2	918.3	918.5	918.6	919.6
170°	929.3	928.6	928.0	927.3	926.6	926.3	926.3	926.3	926.3	926.3	927.5
172.5°	935.8	935.2	934.5	933.8	933.2	932.8	932.8	932.8	932.8	932.8	933.9
175°	942.6	942.0	941.3	940.7	940.0	939.7	939.7	939.7	939.7	939.7	940.7
177.5°	945.5	944.9	944.4	943.9	943.4	943.1	943.1	943.1	943.1	943.1	943.9
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	11.9	11.9	12.0	12.0	12.1	12.1	12.2	12.3
90°	19.1	19.8	20.5	20.9	21.3	21.6	21.9	22.3
92.5°	29.6	30.1	30.6	30.8	30.6	30.4	30.2	30.0
95°	56.2	56.9	57.6	57.9	57.9	57.9	57.9	57.9
97.5°	87.5	88.2	89.0	89.3	89.3	89.2	89.1	89.1
100°	110.1	110.6	111.1	111.5	111.8	112.2	112.5	112.8
102.5°	136.2	136.7	137.2	137.4	137.4	137.3	137.2	137.2
105°	175.2	175.2	175.2	175.3	175.7	176.0	176.3	176.7
107.5°	217.3	217.9	218.4	218.6	218.4	218.2	218.0	217.8
110°	245.5	246.2	246.8	247.0	246.7	246.3	246.0	245.7



TEST NUMBER: P332101

CATALOG NUMBER: S123DIW-S340D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	273.7	274.5	275.3	275.6	275.6	275.5	275.4	275.4
115°	316.5	316.7	316.9	316.9	316.7	316.5	316.4	316.2
117.5°	359.8	359.7	359.7	359.5	359.0	358.5	358.1	357.6
120°	388.6	388.4	388.3	388.0	387.7	387.4	387.0	386.7
122.5°	417.8	417.3	416.9	416.5	416.0	415.5	415.1	414.6
125°	461.1	460.4	459.8	459.1	458.5	457.8	457.1	456.5
127.5°	503.9	503.0	502.1	501.2	500.5	499.7	499.0	498.2
130°	532.4	531.7	531.0	530.1	529.0	527.8	526.7	525.5
132.5°	560.0	559.2	558.4	557.6	556.7	555.8	554.9	554.0
135°	601.4	600.7	600.1	599.6	599.2	598.9	598.6	598.2
137.5°	641.8	641.1	640.5	639.8	639.2	638.5	637.9	637.3
140°	668.4	668.3	668.1	667.4	666.3	665.1	664.0	662.8
142.5°	693.4	693.2	693.0	692.5	691.6	690.7	689.8	688.9
145°	730.0	729.9	729.7	729.3	728.6	728.0	727.3	726.7
147.5°	764.7	764.7	764.7	764.2	763.2	762.2	761.2	760.2
150°	786.0	786.0	786.0	785.5	784.5	783.6	782.6	781.6
152.5°	805.6	805.8	806.1	805.8	804.9	804.1	803.2	802.4
155°	834.1	834.8	835.4	835.2	834.0	832.9	831.7	830.6
157.5°	858.7	859.4	860.1	859.9	859.0	858.1	857.2	856.2
160°	873.8	874.6	875.4	875.5	874.9	874.2	873.5	872.9
162.5°	888.0	888.9	889.7	889.6	888.5	887.5	886.4	885.3
165°	906.0	907.0	908.0	907.9	906.8	905.6	904.5	903.3
167.5°	920.6	921.7	922.7	922.7	921.7	920.6	919.6	918.6
170°	928.6	929.8	930.9	930.9	929.8	928.6	927.5	926.3
172.5°	934.9	935.9	936.9	936.9	935.7	934.6	933.4	932.3
175°	941.7	942.6	943.6	943.6	942.4	941.2	940.1	938.9
177.5°	944.7	945.5	946.3	946.2	945.3	944.3	943.4	942.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9

(END OF REPORT)