

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332133

Luminaire Tested: **S123DIW-S560D1030U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332133  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D1030U835-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5963.0 lumens  
Efficiency: N/A  
Efficacy: 131.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																												
1	96	92	88	84	87	84	80	78	68	66	64	55	53	52	42	41	40	34																												
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	35	34	29																												
3	80	71	64	58	72	65	58	54	53	49	45	43	40	37	33	31	29	25																												
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21																												
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19																												
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16																												
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15																												
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	16	13																												
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13	11																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8509	8509	8509	8509
5°	10147	8546	7573	8546
10°	12701	8502	6840	8502
15°	15578	8433	6367	8433
20°	18558	8326	6063	8326
25°	19705	8197	5995	8197
30°	16890	8103	6027	8103
35°	11746	7967	6089	7967
40°	8847	7808	6070	7808
45°	7346	7573	5993	7573
50°	6581	7093	5940	7093
55°	6152	6576	5864	6576
60°	5772	6036	5804	6036
65°	5422	5501	5619	5501
70°	5086	4894	5350	4894
75°	4554	4284	4907	4284
80°	3986	3515	4228	3515
85°	3125	2556	2841	2556



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.9	1.3
10°-20°	249.7	4.2
20°-30°	419.1	7.0
30°-40°	474.5	8.0
40°-50°	425.5	7.1
50°-60°	343.4	5.8
60°-70°	239.3	4.0
70°-80°	125.8	2.1
80°-90°	34.6	0.6
90°-100°	84.0	1.4
100°-110°	251.5	4.2
110°-120°	427.7	7.2
120°-130°	562.6	9.4
130°-140°	632.3	10.6
140°-150°	621.6	10.4
150°-160°	523.3	8.8
160°-170°	348.3	5.8
170°-180°	122.0	2.0
0°-30°	746.6	12.5
0°-40°	1221.1	20.5
0°-60°	1990.1	33.4
0°-90°	2389.7	40.1
90°-120°	763.2	12.8
90°-150°	2579.7	43.3
90°-180°	3573.0	59.9
0°-180°	5963.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	790	790	790	790	790	
5°	939	791	701	791	939	97
15°	1398	757	571	757	1398	404
25°	1659	690	505	690	1659	728
35°	894	606	463	606	894	581
45°	483	498	394	498	483	382
55°	328	350	312	350	328	294
65°	213	216	221	216	213	212
75°	110	103	118	103	110	117
85°	25	21	23	21	25	31
90°	30	1	30	1	30	16
95°	79	60	79	60	79	81
105°	241	228	241	228	241	256
115°	432	431	432	431	432	427
125°	623	630	623	630	623	557
135°	817	818	817	818	817	628
145°	992	992	992	992	992	619
155°	1134	1136	1134	1136	1134	522
165°	1233	1237	1233	1237	1233	348
175°	1282	1287	1282	1287	1282	122
180°	1290	1290	1290	1290	1290	



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	838.9	838.3	836.8	838.0	835.5	832.2	831.9	828.8	819.9	819.3	816.9
5°	939.1	936.0	935.7	935.3	929.9	922.6	908.8	907.7	889.3	880.1	869.0
7.5°	1068.9	1070.5	1064.9	1060.0	1043.6	1032.8	1018.0	999.1	976.5	953.6	938.3
10°	1162.0	1174.6	1158.9	1148.2	1138.3	1119.5	1097.7	1070.5	1043.3	1011.5	987.4
12.5°	1261.9	1268.1	1265.0	1254.8	1239.4	1210.8	1172.1	1142.2	1117.1	1064.2	1042.8
15°	1397.9	1421.3	1406.4	1371.9	1372.7	1345.5	1294.9	1239.4	1209.9	1163.5	1100.3
17.5°	1542.9	1545.8	1539.4	1510.7	1491.5	1454.2	1407.5	1354.3	1294.5	1238.5	1171.4
20°	1620.1	1617.8	1604.4	1589.4	1556.5	1527.4	1476.4	1417.1	1340.5	1285.3	1212.2
22.5°	1663.0	1659.1	1652.8	1640.3	1612.9	1581.6	1535.9	1471.0	1398.1	1322.1	1237.6
25°	1659.1	1664.1	1664.9	1661.4	1651.9	1633.1	1597.1	1545.4	1472.6	1375.0	1286.9
27.5°	1509.0	1516.0	1536.5	1554.7	1575.0	1595.6	1592.9	1567.2	1513.4	1429.0	1321.3
30°	1358.9	1343.5	1381.5	1429.3	1461.9	1519.3	1551.5	1553.4	1523.2	1450.8	1345.8
32.5°	1150.5	1167.4	1184.1	1243.0	1314.2	1378.7	1442.7	1494.3	1500.2	1452.0	1360.2
35°	893.9	915.0	945.6	976.3	1052.9	1118.7	1231.3	1329.4	1407.5	1417.8	1361.5
37.5°	720.3	730.8	750.1	780.8	830.9	909.1	996.2	1120.1	1233.3	1317.5	1321.2
40°	629.6	632.7	654.5	677.9	718.5	782.8	861.4	970.9	1106.5	1224.1	1273.1
42.5°	561.6	568.4	577.6	600.1	632.4	680.8	753.8	844.4	968.6	1103.9	1199.8
45°	482.6	490.2	496.0	510.9	533.9	566.4	617.4	700.1	794.7	934.5	1063.6
47.5°	430.3	430.9	435.2	446.5	462.1	486.6	522.6	575.7	662.6	775.9	908.5
50°	393.0	399.1	400.6	409.4	421.7	439.7	469.6	514.7	586.0	685.6	807.4
52.5°	366.6	368.4	372.7	379.1	389.8	403.8	429.7	465.1	521.0	605.9	717.9
55°	327.8	327.8	332.1	337.0	343.2	355.8	373.0	399.1	441.6	507.5	600.2
57.5°	292.0	293.9	296.9	298.4	303.6	312.0	326.4	346.2	377.9	428.6	502.3
60°	268.1	271.5	271.2	274.2	278.8	285.3	297.6	313.7	342.0	382.6	444.7
62.5°	247.3	247.0	247.0	250.6	255.2	261.4	269.4	283.3	307.4	343.4	396.2
65°	212.9	212.2	214.9	217.2	218.7	223.3	229.4	241.7	257.8	284.6	325.5
67.5°	182.5	180.2	181.7	182.5	185.1	188.7	194.4	202.0	214.8	236.3	267.2
70°	161.6	159.7	159.3	160.1	162.4	165.1	169.3	176.6	188.4	205.7	228.3
72.5°	140.2	138.9	138.8	140.5	141.6	143.3	146.3	153.0	162.4	175.3	196.4
75°	109.5	109.5	109.5	109.9	111.1	112.6	114.9	118.3	125.6	134.8	149.0
77.5°	82.1	82.0	81.6	81.5	83.2	83.9	84.4	87.6	91.7	97.9	108.2
80°	64.3	62.4	63.2	64.3	65.1	65.5	66.6	67.4	70.9	74.3	81.6
82.5°	47.8	46.2	46.3	48.1	48.3	48.6	49.8	50.9	52.2	55.3	59.2
85°	25.3	25.3	25.7	25.7	26.0	25.7	26.8	27.2	27.2	29.1	31.4
87.5°	15.3	14.6	14.8	15.0	14.6	14.8	14.9	15.0	15.2	15.3	15.0
90°	30.4	29.9	29.5	29.0	28.6	27.9	27.0	26.1	25.2	24.3	21.4
92.5°	40.9	41.2	41.5	41.7	42.0	41.8	41.1	40.3	39.6	38.9	37.2
95°	79.0	79.0	79.0	79.0	79.0	78.6	77.7	76.8	75.9	75.0	73.2
97.5°	121.6	121.7	121.8	121.8	121.9	121.5	120.4	119.4	118.4	117.3	116.0
100°	154.0	153.5	153.1	152.6	152.2	151.6	151.0	150.3	149.6	148.9	147.8
102.5°	187.2	187.3	187.4	187.5	187.6	187.3	186.6	185.9	185.3	184.6	183.1
105°	241.1	240.7	240.2	239.8	239.3	239.1	239.1	239.1	239.1	239.1	237.1
107.5°	297.2	297.5	297.8	298.1	298.3	298.1	297.4	296.7	295.9	295.2	294.4
110°	335.3	335.8	336.2	336.7	337.1	336.9	336.0	335.1	334.2	333.3	332.9



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.9	376.0	376.0	376.1	376.2	375.7	374.6	373.6	372.5	371.4	371.3
115°	431.6	431.8	432.0	432.3	432.5	432.5	432.3	432.0	431.8	431.6	432.0
117.5°	488.1	488.7	489.4	490.0	490.6	491.0	491.0	491.1	491.1	491.2	491.7
120°	527.8	528.3	528.7	529.2	529.6	530.0	530.2	530.4	530.6	530.9	532.0
122.5°	565.9	566.6	567.2	567.8	568.4	569.1	569.6	570.2	570.8	571.4	572.0
125°	623.1	624.0	624.9	625.8	626.7	627.6	628.5	629.4	630.3	631.2	631.6
127.5°	680.0	681.0	682.1	683.1	684.1	685.3	686.6	687.8	689.1	690.3	690.8
130°	717.3	718.9	720.4	722.0	723.6	724.8	725.7	726.6	727.5	728.4	729.1
132.5°	756.2	757.4	758.6	759.8	761.1	762.2	763.3	764.4	765.4	766.5	767.0
135°	816.6	817.0	817.5	817.9	818.4	819.0	819.9	820.8	821.7	822.6	822.9
137.5°	869.9	870.7	871.6	872.4	873.3	874.2	875.1	876.1	877.0	878.0	877.4
140°	904.7	906.3	907.9	909.4	911.0	911.9	912.1	912.4	912.6	912.8	912.6
142.5°	940.4	941.6	942.8	944.0	945.2	946.0	946.2	946.4	946.6	946.9	946.5
145°	991.8	992.7	993.6	994.5	995.4	996.0	996.2	996.5	996.7	996.9	996.2
147.5°	1037.6	1039.0	1040.3	1041.7	1043.0	1043.7	1043.7	1043.7	1043.7	1043.7	1043.1
150°	1066.8	1068.2	1069.5	1070.9	1072.2	1072.9	1072.9	1072.9	1072.9	1072.9	1072.4
152.5°	1095.2	1096.3	1097.5	1098.7	1099.9	1100.3	1099.9	1099.5	1099.2	1098.8	1098.6
155°	1133.7	1135.3	1136.8	1138.4	1140.0	1140.3	1139.4	1138.5	1137.6	1136.7	1136.5
157.5°	1168.7	1170.0	1171.3	1172.5	1173.8	1173.9	1173.0	1172.0	1171.1	1170.1	1170.0
160°	1191.4	1192.3	1193.2	1194.1	1195.0	1194.9	1193.8	1192.7	1191.5	1190.4	1190.4
162.5°	1208.4	1209.9	1211.3	1212.8	1214.2	1214.4	1213.2	1212.1	1211.0	1209.9	1209.7
165°	1233.0	1234.5	1236.1	1237.7	1239.3	1239.4	1238.0	1236.7	1235.3	1234.0	1234.0
167.5°	1253.8	1255.2	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8	1253.7
170°	1264.4	1265.9	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4	1264.4
172.5°	1272.5	1274.0	1275.6	1277.2	1278.8	1278.9	1277.5	1276.1	1274.7	1273.3	1273.3
175°	1281.6	1283.2	1284.7	1286.3	1287.9	1288.0	1286.7	1285.3	1284.0	1282.6	1282.6
177.5°	1286.5	1287.7	1289.0	1290.2	1291.5	1291.6	1290.5	1289.4	1288.3	1287.3	1287.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	815.0	812.6	810.1	805.8	802.1	796.9	795.4	793.6	788.1	783.1	779.5
5°	864.8	855.6	842.2	829.9	820.0	806.6	798.9	790.9	779.4	769.1	760.6
7.5°	916.9	898.8	878.0	855.5	834.5	814.2	797.9	783.4	767.3	752.0	740.2
10°	958.3	932.2	903.1	871.7	844.9	818.8	797.0	777.9	757.2	739.2	724.2
12.5°	1005.4	966.8	926.7	888.5	856.8	820.7	794.3	769.9	746.5	724.8	708.0
15°	1061.3	1012.3	964.8	912.3	864.0	818.8	787.4	756.8	729.6	707.4	685.9
17.5°	1112.1	1056.6	994.0	930.2	872.0	818.4	774.4	739.8	705.8	678.6	657.2
20°	1140.9	1077.7	1006.9	940.6	876.3	816.5	768.3	726.9	690.2	661.4	637.3
22.5°	1165.8	1091.8	1018.5	947.7	876.0	811.6	757.0	714.4	674.5	646.4	620.8
25°	1191.5	1103.0	1029.5	946.4	866.3	799.7	738.4	690.2	650.3	617.4	591.0
27.5°	1213.6	1102.3	1015.0	925.6	851.2	784.4	719.0	667.2	624.9	589.1	562.3
30°	1228.3	1103.8	1000.0	911.5	836.5	767.5	703.9	651.9	607.4	571.0	545.8
32.5°	1237.5	1102.9	986.2	891.9	813.2	752.2	687.7	633.8	588.1	552.4	528.0
35°	1242.8	1096.1	962.5	851.4	775.6	716.2	662.2	606.3	558.4	525.1	497.5
37.5°	1232.1	1082.0	934.9	812.3	729.3	670.9	625.4	577.8	532.0	495.3	471.5
40°	1215.2	1072.8	913.4	784.8	697.4	641.1	602.5	555.7	510.5	475.7	453.5
42.5°	1183.1	1054.1	889.9	754.1	664.3	608.0	572.4	533.4	490.6	457.9	435.7
45°	1104.6	1013.4	854.5	708.2	615.5	557.3	525.9	497.5	458.8	427.0	407.9
47.5°	995.6	952.2	803.3	659.7	564.5	508.5	475.8	453.0	424.7	399.1	380.7
50°	920.0	902.0	768.7	626.6	530.4	475.7	444.3	423.6	403.3	377.6	360.8
52.5°	832.6	843.7	728.2	592.3	495.8	442.0	412.4	396.0	377.6	356.5	341.8
55°	709.7	749.9	658.4	534.7	444.3	393.0	365.0	350.4	339.7	324.0	311.4
57.5°	594.6	645.7	582.8	475.3	393.6	349.4	322.6	306.7	299.8	291.6	281.7
60°	526.2	576.8	528.9	435.5	359.6	317.5	293.8	280.4	273.5	267.7	259.3
62.5°	465.3	516.4	476.2	395.0	326.2	287.2	266.5	253.4	248.0	245.0	237.8
65°	381.5	425.5	398.7	332.1	278.4	244.0	225.2	216.0	211.0	209.9	205.3
67.5°	310.5	344.0	324.5	275.4	233.2	203.4	187.5	179.7	175.9	175.5	172.0
70°	263.9	295.3	280.4	235.9	199.5	176.2	162.4	155.5	153.2	152.8	150.9
72.5°	227.7	249.6	237.8	200.7	172.6	151.4	141.2	134.0	131.4	132.0	130.7
75°	168.5	185.0	178.1	152.4	129.8	116.0	107.6	103.0	100.7	101.9	100.3
77.5°	121.3	131.7	125.5	107.7	93.8	83.8	77.6	74.8	72.7	72.6	71.9
80°	91.5	97.7	94.2	83.5	72.0	63.6	58.6	56.7	55.5	55.2	54.8
82.5°	65.2	70.4	66.3	59.0	51.2	46.1	43.3	40.8	39.9	40.1	39.8
85°	32.9	34.9	33.3	28.7	25.7	23.4	21.8	20.7	19.9	20.3	19.5
87.5°	15.0	14.7	13.2	11.5	10.4	9.1	8.6	7.6	7.4	7.8	8.0
90°	18.5	15.5	12.6	10.0	7.8	5.5	3.3	1.0	3.3	5.5	7.8
92.5°	35.6	33.9	32.2	30.6	29.1	27.6	26.0	24.5	26.0	27.6	29.1
95°	71.4	69.6	67.8	66.1	64.5	62.9	61.3	59.8	61.3	62.9	64.5
97.5°	114.7	113.4	112.1	110.9	109.7	108.5	107.3	106.2	107.3	108.5	109.7
100°	146.7	145.6	144.4	143.2	141.8	140.5	139.1	137.8	139.1	140.5	141.8
102.5°	181.6	180.1	178.6	177.5	176.7	175.9	175.1	174.3	175.1	175.9	176.7
105°	235.0	233.0	231.0	229.8	229.3	228.9	228.4	228.0	228.4	228.9	229.3
107.5°	293.6	292.8	292.0	291.4	291.2	290.9	290.6	290.4	290.6	290.9	291.2
110°	332.4	332.0	331.5	331.1	330.6	330.2	329.7	329.3	329.7	330.2	330.6





TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	371.2	371.1	371.0	370.9	370.6	370.3	370.1	369.8	370.1	370.3	370.6
115°	432.5	432.9	433.4	433.3	432.6	431.9	431.2	430.6	431.2	431.9	432.6
117.5°	492.3	492.9	493.5	493.6	493.1	492.7	492.2	491.8	492.2	492.7	493.1
120°	533.1	534.2	535.4	535.3	533.9	532.6	531.2	529.9	531.2	532.6	533.9
122.5°	572.6	573.2	573.7	573.5	572.5	571.6	570.6	569.6	570.6	571.6	572.5
125°	632.1	632.5	633.0	632.9	632.2	631.5	630.8	630.2	630.8	631.5	632.2
127.5°	691.3	691.8	692.3	691.8	690.4	689.0	687.5	686.1	687.5	689.0	690.4
130°	729.8	730.5	731.1	730.6	728.8	727.0	725.2	723.4	725.2	727.0	728.8
132.5°	767.5	768.0	768.5	767.9	766.1	764.2	762.4	760.6	762.4	764.2	766.1
135°	823.1	823.3	823.5	823.0	821.6	820.3	818.9	817.6	818.9	820.3	821.6
137.5°	876.8	876.2	875.6	874.8	873.6	872.5	871.4	870.3	871.4	872.5	873.6
140°	912.4	912.1	911.9	911.2	910.1	909.0	907.9	906.7	907.9	909.0	910.1
142.5°	946.0	945.6	945.2	944.5	943.3	942.2	941.1	940.0	941.1	942.2	943.3
145°	995.6	994.9	994.2	993.6	993.2	992.7	992.3	991.8	992.3	992.7	993.2
147.5°	1042.5	1041.8	1041.2	1040.5	1039.7	1038.8	1038.0	1037.2	1038.0	1038.8	1039.7
150°	1072.0	1071.5	1071.1	1070.6	1070.2	1069.7	1069.3	1068.8	1069.3	1069.7	1070.2
152.5°	1098.3	1098.0	1097.7	1097.3	1096.7	1096.0	1095.4	1094.8	1095.4	1096.0	1096.7
155°	1136.3	1136.0	1135.8	1135.7	1135.7	1135.7	1135.7	1135.7	1135.7	1135.7	1135.7
157.5°	1169.8	1169.6	1169.4	1169.5	1169.7	1170.0	1170.3	1170.6	1170.3	1170.0	1169.7
160°	1190.4	1190.4	1190.4	1190.6	1191.1	1191.5	1192.0	1192.4	1192.0	1191.5	1191.1
162.5°	1209.5	1209.3	1209.1	1209.4	1210.0	1210.6	1211.3	1211.9	1211.3	1210.6	1210.0
165°	1234.0	1234.0	1234.0	1234.3	1235.0	1235.7	1236.3	1237.0	1236.3	1235.7	1235.0
167.5°	1253.5	1253.3	1253.1	1253.5	1254.4	1255.3	1256.2	1257.1	1256.2	1255.3	1254.4
170°	1264.4	1264.4	1264.4	1264.8	1265.7	1266.6	1267.5	1268.4	1267.5	1266.6	1265.7
172.5°	1273.3	1273.3	1273.3	1273.7	1274.6	1275.5	1276.4	1277.3	1276.4	1275.5	1274.6
175°	1282.6	1282.6	1282.6	1283.1	1284.0	1284.9	1285.8	1286.7	1285.8	1284.9	1284.0
177.5°	1287.3	1287.3	1287.3	1287.6	1288.3	1289.1	1289.8	1290.5	1289.8	1289.1	1288.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	777.3	775.2	772.1	767.5	763.8	758.0	758.0	758.9	758.9	758.6	758.0
5°	753.7	748.0	741.1	733.1	724.6	716.2	714.7	711.6	709.3	707.8	705.9
7.5°	728.8	718.7	708.6	697.4	687.1	678.6	672.7	667.8	664.6	661.3	658.8
10°	712.0	699.3	687.5	675.6	662.6	652.2	645.7	641.1	637.7	634.6	633.1
12.5°	692.1	677.6	664.5	653.2	639.0	628.3	622.1	620.0	615.9	609.5	606.1
15°	663.0	649.6	633.9	616.6	609.7	596.7	589.4	586.0	583.7	578.7	577.2
17.5°	638.1	620.5	602.9	590.0	577.2	566.7	562.6	558.3	555.3	551.2	550.0
20°	618.2	602.5	586.4	572.6	559.2	547.7	544.2	541.2	538.1	536.2	534.7
22.5°	597.9	582.2	568.9	556.0	541.7	534.2	530.4	527.1	524.9	523.6	522.1
25°	569.5	555.7	540.8	529.3	517.8	512.8	510.5	508.6	507.1	505.2	504.8
27.5°	544.1	529.1	517.0	506.2	498.0	493.8	491.6	490.7	491.0	491.7	492.1
30°	525.1	511.3	501.3	492.1	484.5	480.7	480.3	480.3	481.8	482.2	483.0
32.5°	507.6	496.3	486.3	477.4	471.6	469.0	470.5	470.5	471.7	472.7	474.1
35°	482.2	472.2	464.6	456.9	451.9	453.1	453.8	454.6	456.5	458.8	460.4
37.5°	457.9	449.3	441.3	435.3	433.0	435.1	436.9	438.5	440.8	442.5	444.0
40°	440.4	433.9	426.3	420.9	421.7	422.8	424.4	426.3	428.2	429.3	430.9
42.5°	424.2	417.4	411.6	407.1	408.2	409.7	410.6	411.6	413.8	415.9	416.8
45°	399.5	394.1	388.7	386.1	386.8	387.6	388.4	389.5	391.4	393.0	393.3
47.5°	371.7	367.9	364.3	361.7	362.9	362.6	363.6	366.1	366.7	367.6	369.7
50°	353.9	350.4	346.2	345.5	345.5	345.5	345.8	348.9	348.9	350.4	352.0
52.5°	334.3	332.1	329.4	328.0	327.4	327.4	329.0	330.5	331.1	333.3	334.8
55°	305.2	302.9	300.7	299.5	298.7	299.5	302.6	303.3	305.2	306.4	307.5
57.5°	275.0	273.2	271.4	270.8	270.6	271.6	273.3	275.6	276.1	279.6	281.3
60°	255.1	252.4	250.9	250.9	250.1	253.5	252.8	256.6	257.4	259.7	262.4
62.5°	234.5	230.9	230.3	230.3	231.4	232.4	233.5	235.2	237.2	240.1	242.1
65°	201.5	199.5	202.2	201.8	201.1	203.4	203.4	205.3	207.6	210.3	214.5
67.5°	170.1	169.1	169.4	169.4	170.5	171.8	172.9	174.6	177.3	180.2	182.9
70°	149.0	150.1	148.2	149.8	150.9	151.3	152.0	154.3	157.4	159.3	162.4
72.5°	128.5	128.4	128.6	129.2	130.4	131.1	131.8	134.4	137.8	139.4	141.9
75°	98.8	98.4	99.6	99.6	101.5	102.3	103.0	104.2	107.2	109.5	111.5
77.5°	72.2	72.6	72.4	73.7	73.2	73.3	75.7	76.8	77.1	81.7	82.7
80°	54.4	55.2	55.5	55.9	56.3	55.5	58.2	59.4	59.4	62.0	64.0
82.5°	39.1	39.5	40.5	40.9	41.0	41.7	42.0	42.8	43.7	44.9	47.4
85°	19.5	20.7	21.1	20.7	21.1	20.3	21.4	21.8	22.2	22.2	22.2
87.5°	8.1	9.0	9.2	10.1	10.4	11.3	11.5	11.0	11.2	12.3	11.2
90°	10.0	12.6	15.5	18.5	21.4	24.3	25.2	26.1	27.0	27.9	28.6
92.5°	30.6	32.2	33.9	35.6	37.2	38.9	39.6	40.3	41.1	41.8	42.0
95°	66.1	67.8	69.6	71.4	73.2	75.0	75.9	76.8	77.7	78.6	79.0
97.5°	110.9	112.1	113.4	114.7	116.0	117.3	118.4	119.4	120.4	121.5	121.9
100°	143.2	144.4	145.6	146.7	147.8	148.9	149.6	150.3	151.0	151.6	152.2
102.5°	177.5	178.6	180.1	181.6	183.1	184.6	185.3	185.9	186.6	187.3	187.6
105°	229.8	231.0	233.0	235.0	237.1	239.1	239.1	239.1	239.1	239.1	239.3
107.5°	291.4	292.0	292.8	293.6	294.4	295.2	295.9	296.7	297.4	298.1	298.3
110°	331.1	331.5	332.0	332.4	332.9	333.3	334.2	335.1	336.0	336.9	337.1



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	370.9	371.0	371.1	371.2	371.3	371.4	372.5	373.6	374.6	375.7	376.2
115°	433.3	433.4	432.9	432.5	432.0	431.6	431.8	432.0	432.3	432.5	432.5
117.5°	493.6	493.5	492.9	492.3	491.7	491.2	491.1	491.1	491.0	491.0	490.6
120°	535.3	535.4	534.2	533.1	532.0	530.9	530.6	530.4	530.2	530.0	529.6
122.5°	573.5	573.7	573.2	572.6	572.0	571.4	570.8	570.2	569.6	569.1	568.4
125°	632.9	633.0	632.5	632.1	631.6	631.2	630.3	629.4	628.5	627.6	626.7
127.5°	691.8	692.3	691.8	691.3	690.8	690.3	689.1	687.8	686.6	685.3	684.1
130°	730.6	731.1	730.5	729.8	729.1	728.4	727.5	726.6	725.7	724.8	723.6
132.5°	767.9	768.5	768.0	767.5	767.0	766.5	765.4	764.4	763.3	762.2	761.1
135°	823.0	823.5	823.3	823.1	822.9	822.6	821.7	820.8	819.9	819.0	818.4
137.5°	874.8	875.6	876.2	876.8	877.4	878.0	877.0	876.1	875.1	874.2	873.3
140°	911.2	911.9	912.1	912.4	912.6	912.8	912.6	912.4	912.1	911.9	911.0
142.5°	944.5	945.2	945.6	946.0	946.5	946.9	946.6	946.4	946.2	946.0	945.2
145°	993.6	994.2	994.9	995.6	996.2	996.9	996.7	996.5	996.2	996.0	995.4
147.5°	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7	1043.7	1043.7	1043.7	1043.0
150°	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9	1072.9	1072.9	1072.9	1072.2
152.5°	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2	1099.5	1099.9	1100.3	1099.9
155°	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6	1138.5	1139.4	1140.3	1140.0
157.5°	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1	1172.0	1173.0	1173.9	1173.8
160°	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5	1192.7	1193.8	1194.9	1195.0
162.5°	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0	1212.1	1213.2	1214.4	1214.2
165°	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3	1236.7	1238.0	1239.4	1239.3
167.5°	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2	1256.6	1258.0	1259.4	1259.4
170°	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9	1267.5	1269.1	1270.7	1270.7
172.5°	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7	1276.1	1277.5	1278.9	1278.8
175°	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0	1285.3	1286.7	1288.0	1287.9
177.5°	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3	1289.4	1290.5	1291.6	1291.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	755.9	755.6	757.7	756.2	757.7	755.6	755.9	758.0	758.6	758.9	758.9
5°	703.6	704.7	700.9	700.9	700.9	704.7	703.6	705.9	707.8	709.3	711.6
7.5°	657.0	655.3	655.5	653.4	655.5	655.3	657.0	658.8	661.3	664.6	667.8
10°	628.5	626.2	625.4	625.8	625.4	626.2	628.5	633.1	634.6	637.7	641.1
12.5°	604.9	604.4	599.4	599.5	599.4	604.4	604.9	606.1	609.5	615.9	620.0
15°	577.2	569.9	569.1	571.4	569.1	569.9	577.2	577.2	578.7	583.7	586.0
17.5°	549.4	545.5	545.8	544.6	545.8	545.5	549.4	550.0	551.2	555.3	558.3
20°	534.7	532.4	532.0	529.3	532.0	532.4	534.7	534.7	536.2	538.1	541.2
22.5°	521.2	520.4	520.6	517.7	520.6	520.4	521.2	522.1	523.6	524.9	527.1
25°	504.4	506.3	504.8	504.8	504.8	506.3	504.4	504.8	505.2	507.1	508.6
27.5°	493.1	493.0	492.2	492.2	492.2	493.0	493.1	492.1	491.7	491.0	490.7
30°	484.5	484.1	484.9	484.9	484.9	484.1	484.5	483.0	482.2	481.8	480.3
32.5°	475.9	476.4	476.6	476.9	476.6	476.4	475.9	474.1	472.7	471.7	470.5
35°	462.7	463.0	464.2	463.4	464.2	463.0	462.7	460.4	458.8	456.5	454.6
37.5°	444.7	446.5	446.1	446.7	446.1	446.5	444.7	444.0	442.5	440.8	438.5
40°	431.3	432.4	432.0	432.0	432.0	432.4	431.3	430.9	429.3	428.2	426.3
42.5°	417.5	418.3	417.3	416.7	417.3	418.3	417.5	416.8	415.9	413.8	411.6
45°	394.9	394.1	395.3	393.7	395.3	394.1	394.9	393.3	393.0	391.4	389.5
47.5°	369.6	370.4	370.7	371.8	370.7	370.4	369.6	369.7	367.6	366.7	366.1
50°	352.7	355.0	355.0	354.7	355.0	355.0	352.7	352.0	350.4	348.9	348.9
52.5°	336.2	337.3	338.8	338.7	338.8	337.3	336.2	334.8	333.3	331.1	330.5
55°	310.6	311.4	312.1	312.5	312.1	311.4	310.6	307.5	306.4	305.2	303.3
57.5°	284.1	283.8	285.6	286.2	285.6	283.8	284.1	281.3	279.6	276.1	275.6
60°	265.4	265.4	268.5	269.6	268.5	265.4	265.4	262.4	259.7	257.4	256.6
62.5°	245.5	246.7	249.8	248.2	249.8	246.7	245.5	242.1	240.1	237.2	235.2
65°	216.4	219.5	219.1	220.6	219.1	219.5	216.4	214.5	210.3	207.6	205.3
67.5°	186.0	187.9	190.7	190.9	190.7	187.9	186.0	182.9	180.2	177.3	174.6
70°	165.5	167.4	168.9	170.0	168.9	167.4	165.5	162.4	159.3	157.4	154.3
72.5°	145.5	146.5	150.2	148.6	150.2	146.5	145.5	141.9	139.4	137.8	134.4
75°	114.1	116.8	119.1	118.0	119.1	116.8	114.1	111.5	109.5	107.2	104.2
77.5°	84.4	87.1	88.2	87.2	88.2	87.1	84.4	82.7	81.7	77.1	76.8
80°	66.6	66.3	68.6	68.2	68.6	66.3	66.6	64.0	62.0	59.4	59.4
82.5°	48.9	48.5	49.6	49.8	49.6	48.5	48.9	47.4	44.9	43.7	42.8
85°	23.7	24.9	23.4	23.0	23.4	24.9	23.7	22.2	22.2	22.2	21.8
87.5°	11.3	11.4	11.2	11.0	11.2	11.4	11.3	11.2	12.3	11.2	11.0
90°	29.0	29.5	29.9	30.4	29.9	29.5	29.0	28.6	27.9	27.0	26.1
92.5°	41.7	41.5	41.2	40.9	41.2	41.5	41.7	42.0	41.8	41.1	40.3
95°	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	78.6	77.7	76.8
97.5°	121.8	121.8	121.7	121.6	121.7	121.8	121.8	121.9	121.5	120.4	119.4
100°	152.6	153.1	153.5	154.0	153.5	153.1	152.6	152.2	151.6	151.0	150.3
102.5°	187.5	187.4	187.3	187.2	187.3	187.4	187.5	187.6	187.3	186.6	185.9
105°	239.8	240.2	240.7	241.1	240.7	240.2	239.8	239.3	239.1	239.1	239.1
107.5°	298.1	297.8	297.5	297.2	297.5	297.8	298.1	298.3	298.1	297.4	296.7
110°	336.7	336.2	335.8	335.3	335.8	336.2	336.7	337.1	336.9	336.0	335.1



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	376.1	376.0	376.0	375.9	376.0	376.0	376.1	376.2	375.7	374.6	373.6
115°	432.3	432.0	431.8	431.6	431.8	432.0	432.3	432.5	432.5	432.3	432.0
117.5°	490.0	489.4	488.7	488.1	488.7	489.4	490.0	490.6	491.0	491.0	491.1
120°	529.2	528.7	528.3	527.8	528.3	528.7	529.2	529.6	530.0	530.2	530.4
122.5°	567.8	567.2	566.6	565.9	566.6	567.2	567.8	568.4	569.1	569.6	570.2
125°	625.8	624.9	624.0	623.1	624.0	624.9	625.8	626.7	627.6	628.5	629.4
127.5°	683.1	682.1	681.0	680.0	681.0	682.1	683.1	684.1	685.3	686.6	687.8
130°	722.0	720.4	718.9	717.3	718.9	720.4	722.0	723.6	724.8	725.7	726.6
132.5°	759.8	758.6	757.4	756.2	757.4	758.6	759.8	761.1	762.2	763.3	764.4
135°	817.9	817.5	817.0	816.6	817.0	817.5	817.9	818.4	819.0	819.9	820.8
137.5°	872.4	871.6	870.7	869.9	870.7	871.6	872.4	873.3	874.2	875.1	876.1
140°	909.4	907.9	906.3	904.7	906.3	907.9	909.4	911.0	911.9	912.1	912.4
142.5°	944.0	942.8	941.6	940.4	941.6	942.8	944.0	945.2	946.0	946.2	946.4
145°	994.5	993.6	992.7	991.8	992.7	993.6	994.5	995.4	996.0	996.2	996.5
147.5°	1041.7	1040.3	1039.0	1037.6	1039.0	1040.3	1041.7	1043.0	1043.7	1043.7	1043.7
150°	1070.9	1069.5	1068.2	1066.8	1068.2	1069.5	1070.9	1072.2	1072.9	1072.9	1072.9
152.5°	1098.7	1097.5	1096.3	1095.2	1096.3	1097.5	1098.7	1099.9	1100.3	1099.9	1099.5
155°	1138.4	1136.8	1135.3	1133.7	1135.3	1136.8	1138.4	1140.0	1140.3	1139.4	1138.5
157.5°	1172.5	1171.3	1170.0	1168.7	1170.0	1171.3	1172.5	1173.8	1173.9	1173.0	1172.0
160°	1194.1	1193.2	1192.3	1191.4	1192.3	1193.2	1194.1	1195.0	1194.9	1193.8	1192.7
162.5°	1212.8	1211.3	1209.9	1208.4	1209.9	1211.3	1212.8	1214.2	1214.4	1213.2	1212.1
165°	1237.7	1236.1	1234.5	1233.0	1234.5	1236.1	1237.7	1239.3	1239.4	1238.0	1236.7
167.5°	1258.0	1256.6	1255.2	1253.8	1255.2	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6
170°	1269.1	1267.5	1265.9	1264.4	1265.9	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5
172.5°	1277.2	1275.6	1274.0	1272.5	1274.0	1275.6	1277.2	1278.8	1278.9	1277.5	1276.1
175°	1286.3	1284.7	1283.2	1281.6	1283.2	1284.7	1286.3	1287.9	1288.0	1286.7	1285.3
177.5°	1290.2	1289.0	1287.7	1286.5	1287.7	1289.0	1290.2	1291.5	1291.6	1290.5	1289.4
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	758.0	758.0	763.8	767.5	772.1	775.2	777.3	779.5	783.1	788.1	793.6
5°	714.7	716.2	724.6	733.1	741.1	748.0	753.7	760.6	769.1	779.4	790.9
7.5°	672.7	678.6	687.1	697.4	708.6	718.7	728.8	740.2	752.0	767.3	783.4
10°	645.7	652.2	662.6	675.6	687.5	699.3	712.0	724.2	739.2	757.2	777.9
12.5°	622.1	628.3	639.0	653.2	664.5	677.6	692.1	708.0	724.8	746.5	769.9
15°	589.4	596.7	609.7	616.6	633.9	649.6	663.0	685.9	707.4	729.6	756.8
17.5°	562.6	566.7	577.2	590.0	602.9	620.5	638.1	657.2	678.6	705.8	739.8
20°	544.2	547.7	559.2	572.6	586.4	602.5	618.2	637.3	661.4	690.2	726.9
22.5°	530.4	534.2	541.7	556.0	568.9	582.2	597.9	620.8	646.4	674.5	714.4
25°	510.5	512.8	517.8	529.3	540.8	555.7	569.5	591.0	617.4	650.3	690.2
27.5°	491.6	493.8	498.0	506.2	517.0	529.1	544.1	562.3	589.1	624.9	667.2
30°	480.3	480.7	484.5	492.1	501.3	511.3	525.1	545.8	571.0	607.4	651.9
32.5°	470.5	469.0	471.6	477.4	486.3	496.3	507.6	528.0	552.4	588.1	633.8
35°	453.8	453.1	451.9	456.9	464.6	472.2	482.2	497.5	525.1	558.4	606.3
37.5°	436.9	435.1	433.0	435.3	441.3	449.3	457.9	471.5	495.3	532.0	577.8
40°	424.4	422.8	421.7	420.9	426.3	433.9	440.4	453.5	475.7	510.5	555.7
42.5°	410.6	409.7	408.2	407.1	411.6	417.4	424.2	435.7	457.9	490.6	533.4
45°	388.4	387.6	386.8	386.1	388.7	394.1	399.5	407.9	427.0	458.8	497.5
47.5°	363.6	362.6	362.9	361.7	364.3	367.9	371.7	380.7	399.1	424.7	453.0
50°	345.8	345.5	345.5	345.5	346.2	350.4	353.9	360.8	377.6	403.3	423.6
52.5°	329.0	327.4	327.4	328.0	329.4	332.1	334.3	341.8	356.5	377.6	396.0
55°	302.6	299.5	298.7	299.5	300.7	302.9	305.2	311.4	324.0	339.7	350.4
57.5°	273.3	271.6	270.6	270.8	271.4	273.2	275.0	281.7	291.6	299.8	306.7
60°	252.8	253.5	250.1	250.9	250.9	252.4	255.1	259.3	267.7	273.5	280.4
62.5°	233.5	232.4	231.4	230.3	230.3	230.9	234.5	237.8	245.0	248.0	253.4
65°	203.4	203.4	201.1	201.8	202.2	199.5	201.5	205.3	209.9	211.0	216.0
67.5°	172.9	171.8	170.5	169.4	169.4	169.1	170.1	172.0	175.5	175.9	179.7
70°	152.0	151.3	150.9	149.8	148.2	150.1	149.0	150.9	152.8	153.2	155.5
72.5°	131.8	131.1	130.4	129.2	128.6	128.4	128.5	130.7	132.0	131.4	134.0
75°	103.0	102.3	101.5	99.6	99.6	98.4	98.8	100.3	101.9	100.7	103.0
77.5°	75.7	73.3	73.2	73.7	72.4	72.6	72.2	71.9	72.6	72.7	74.8
80°	58.2	55.5	56.3	55.9	55.5	55.2	54.4	54.8	55.2	55.5	56.7
82.5°	42.0	41.7	41.0	40.9	40.5	39.5	39.1	39.8	40.1	39.9	40.8
85°	21.4	20.3	21.1	20.7	21.1	20.7	19.5	19.5	20.3	19.9	20.7
87.5°	11.5	11.3	10.4	10.1	9.2	9.0	8.1	8.0	7.8	7.4	7.6
90°	25.2	24.3	21.4	18.5	15.5	12.6	10.0	7.8	5.5	3.3	1.0
92.5°	39.6	38.9	37.2	35.6	33.9	32.2	30.6	29.1	27.6	26.0	24.5
95°	75.9	75.0	73.2	71.4	69.6	67.8	66.1	64.5	62.9	61.3	59.8
97.5°	118.4	117.3	116.0	114.7	113.4	112.1	110.9	109.7	108.5	107.3	106.2
100°	149.6	148.9	147.8	146.7	145.6	144.4	143.2	141.8	140.5	139.1	137.8
102.5°	185.3	184.6	183.1	181.6	180.1	178.6	177.5	176.7	175.9	175.1	174.3
105°	239.1	239.1	237.1	235.0	233.0	231.0	229.8	229.3	228.9	228.4	228.0
107.5°	295.9	295.2	294.4	293.6	292.8	292.0	291.4	291.2	290.9	290.6	290.4
110°	334.2	333.3	332.9	332.4	332.0	331.5	331.1	330.6	330.2	329.7	329.3



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	372.5	371.4	371.3	371.2	371.1	371.0	370.9	370.6	370.3	370.1	369.8
115°	431.8	431.6	432.0	432.5	432.9	433.4	433.3	432.6	431.9	431.2	430.6
117.5°	491.1	491.2	491.7	492.3	492.9	493.5	493.6	493.1	492.7	492.2	491.8
120°	530.6	530.9	532.0	533.1	534.2	535.4	535.3	533.9	532.6	531.2	529.9
122.5°	570.8	571.4	572.0	572.6	573.2	573.7	573.5	572.5	571.6	570.6	569.6
125°	630.3	631.2	631.6	632.1	632.5	633.0	632.9	632.2	631.5	630.8	630.2
127.5°	689.1	690.3	690.8	691.3	691.8	692.3	691.8	690.4	689.0	687.5	686.1
130°	727.5	728.4	729.1	729.8	730.5	731.1	730.6	728.8	727.0	725.2	723.4
132.5°	765.4	766.5	767.0	767.5	768.0	768.5	767.9	766.1	764.2	762.4	760.6
135°	821.7	822.6	822.9	823.1	823.3	823.5	823.0	821.6	820.3	818.9	817.6
137.5°	877.0	878.0	877.4	876.8	876.2	875.6	874.8	873.6	872.5	871.4	870.3
140°	912.6	912.8	912.6	912.4	912.1	911.9	911.2	910.1	909.0	907.9	906.7
142.5°	946.6	946.9	946.5	946.0	945.6	945.2	944.5	943.3	942.2	941.1	940.0
145°	996.7	996.9	996.2	995.6	994.9	994.2	993.6	993.2	992.7	992.3	991.8
147.5°	1043.7	1043.7	1043.1	1042.5	1041.8	1041.2	1040.5	1039.7	1038.8	1038.0	1037.2
150°	1072.9	1072.9	1072.4	1072.0	1071.5	1071.1	1070.6	1070.2	1069.7	1069.3	1068.8
152.5°	1099.2	1098.8	1098.6	1098.3	1098.0	1097.7	1097.3	1096.7	1096.0	1095.4	1094.8
155°	1137.6	1136.7	1136.5	1136.3	1136.0	1135.8	1135.7	1135.7	1135.7	1135.7	1135.7
157.5°	1171.1	1170.1	1170.0	1169.8	1169.6	1169.4	1169.5	1169.7	1170.0	1170.3	1170.6
160°	1191.5	1190.4	1190.4	1190.4	1190.4	1190.4	1190.6	1191.1	1191.5	1192.0	1192.4
162.5°	1211.0	1209.9	1209.7	1209.5	1209.3	1209.1	1209.4	1210.0	1210.6	1211.3	1211.9
165°	1235.3	1234.0	1234.0	1234.0	1234.0	1234.0	1234.3	1235.0	1235.7	1236.3	1237.0
167.5°	1255.2	1253.8	1253.7	1253.5	1253.3	1253.1	1253.5	1254.4	1255.3	1256.2	1257.1
170°	1265.9	1264.4	1264.4	1264.4	1264.4	1264.4	1264.8	1265.7	1266.6	1267.5	1268.4
172.5°	1274.7	1273.3	1273.3	1273.3	1273.3	1273.3	1273.7	1274.6	1275.5	1276.4	1277.3
175°	1284.0	1282.6	1282.6	1282.6	1282.6	1282.6	1283.1	1284.0	1284.9	1285.8	1286.7
177.5°	1288.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.6	1288.3	1289.1	1289.8	1290.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	795.4	796.9	802.1	805.8	810.1	812.6	815.0	816.9	819.3	819.9	828.8
5°	798.9	806.6	820.0	829.9	842.2	855.6	864.8	869.0	880.1	889.3	907.7
7.5°	797.9	814.2	834.5	855.5	878.0	898.8	916.9	938.3	953.6	976.5	999.1
10°	797.0	818.8	844.9	871.7	903.1	932.2	958.3	987.4	1011.5	1043.3	1070.5
12.5°	794.3	820.7	856.8	888.5	926.7	966.8	1005.4	1042.8	1064.2	1117.1	1142.2
15°	787.4	818.8	864.0	912.3	964.8	1012.3	1061.3	1100.3	1163.5	1209.9	1239.4
17.5°	774.4	818.4	872.0	930.2	994.0	1056.6	1112.1	1171.4	1238.5	1294.5	1354.3
20°	768.3	816.5	876.3	940.6	1006.9	1077.7	1140.9	1212.2	1285.3	1340.5	1417.1
22.5°	757.0	811.6	876.0	947.7	1018.5	1091.8	1165.8	1237.6	1322.1	1398.1	1471.0
25°	738.4	799.7	866.3	946.4	1029.5	1103.0	1191.5	1286.9	1375.0	1472.6	1545.4
27.5°	719.0	784.4	851.2	925.6	1015.0	1102.3	1213.6	1321.3	1429.0	1513.4	1567.2
30°	703.9	767.5	836.5	911.5	1000.0	1103.8	1228.3	1345.8	1450.8	1523.2	1553.4
32.5°	687.7	752.2	813.2	891.9	986.2	1102.9	1237.5	1360.2	1452.0	1500.2	1494.3
35°	662.2	716.2	775.6	851.4	962.5	1096.1	1242.8	1361.5	1417.8	1407.5	1329.4
37.5°	625.4	670.9	729.3	812.3	934.9	1082.0	1232.1	1321.2	1317.5	1233.3	1120.1
40°	602.5	641.1	697.4	784.8	913.4	1072.8	1215.2	1273.1	1224.1	1106.5	970.9
42.5°	572.4	608.0	664.3	754.1	889.9	1054.1	1183.1	1199.8	1103.9	968.6	844.4
45°	525.9	557.3	615.5	708.2	854.5	1013.4	1104.6	1063.6	934.5	794.7	700.1
47.5°	475.8	508.5	564.5	659.7	803.3	952.2	995.6	908.5	775.9	662.6	575.7
50°	444.3	475.7	530.4	626.6	768.7	902.0	920.0	807.4	685.6	586.0	514.7
52.5°	412.4	442.0	495.8	592.3	728.2	843.7	832.6	717.9	605.9	521.0	465.1
55°	365.0	393.0	444.3	534.7	658.4	749.9	709.7	600.2	507.5	441.6	399.1
57.5°	322.6	349.4	393.6	475.3	582.8	645.7	594.6	502.3	428.6	377.9	346.2
60°	293.8	317.5	359.6	435.5	528.9	576.8	526.2	444.7	382.6	342.0	313.7
62.5°	266.5	287.2	326.2	395.0	476.2	516.4	465.3	396.2	343.4	307.4	283.3
65°	225.2	244.0	278.4	332.1	398.7	425.5	381.5	325.5	284.6	257.8	241.7
67.5°	187.5	203.4	233.2	275.4	324.5	344.0	310.5	267.2	236.3	214.8	202.0
70°	162.4	176.2	199.5	235.9	280.4	295.3	263.9	228.3	205.7	188.4	176.6
72.5°	141.2	151.4	172.6	200.7	237.8	249.6	227.7	196.4	175.3	162.4	153.0
75°	107.6	116.0	129.8	152.4	178.1	185.0	168.5	149.0	134.8	125.6	118.3
77.5°	77.6	83.8	93.8	107.7	125.5	131.7	121.3	108.2	97.9	91.7	87.6
80°	58.6	63.6	72.0	83.5	94.2	97.7	91.5	81.6	74.3	70.9	67.4
82.5°	43.3	46.1	51.2	59.0	66.3	70.4	65.2	59.2	55.3	52.2	50.9
85°	21.8	23.4	25.7	28.7	33.3	34.9	32.9	31.4	29.1	27.2	27.2
87.5°	8.6	9.1	10.4	11.5	13.2	14.7	15.0	15.0	15.3	15.2	15.0
90°	3.3	5.5	7.8	10.0	12.6	15.5	18.5	21.4	24.3	25.2	26.1
92.5°	26.0	27.6	29.1	30.6	32.2	33.9	35.6	37.2	38.9	39.6	40.3
95°	61.3	62.9	64.5	66.1	67.8	69.6	71.4	73.2	75.0	75.9	76.8
97.5°	107.3	108.5	109.7	110.9	112.1	113.4	114.7	116.0	117.3	118.4	119.4
100°	139.1	140.5	141.8	143.2	144.4	145.6	146.7	147.8	148.9	149.6	150.3
102.5°	175.1	175.9	176.7	177.5	178.6	180.1	181.6	183.1	184.6	185.3	185.9
105°	228.4	228.9	229.3	229.8	231.0	233.0	235.0	237.1	239.1	239.1	239.1
107.5°	290.6	290.9	291.2	291.4	292.0	292.8	293.6	294.4	295.2	295.9	296.7
110°	329.7	330.2	330.6	331.1	331.5	332.0	332.4	332.9	333.3	334.2	335.1





TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	370.1	370.3	370.6	370.9	371.0	371.1	371.2	371.3	371.4	372.5	373.6
115°	431.2	431.9	432.6	433.3	433.4	432.9	432.5	432.0	431.6	431.8	432.0
117.5°	492.2	492.7	493.1	493.6	493.5	492.9	492.3	491.7	491.2	491.1	491.1
120°	531.2	532.6	533.9	535.3	535.4	534.2	533.1	532.0	530.9	530.6	530.4
122.5°	570.6	571.6	572.5	573.5	573.7	573.2	572.6	572.0	571.4	570.8	570.2
125°	630.8	631.5	632.2	632.9	633.0	632.5	632.1	631.6	631.2	630.3	629.4
127.5°	687.5	689.0	690.4	691.8	692.3	691.8	691.3	690.8	690.3	689.1	687.8
130°	725.2	727.0	728.8	730.6	731.1	730.5	729.8	729.1	728.4	727.5	726.6
132.5°	762.4	764.2	766.1	767.9	768.5	768.0	767.5	767.0	766.5	765.4	764.4
135°	818.9	820.3	821.6	823.0	823.5	823.3	823.1	822.9	822.6	821.7	820.8
137.5°	871.4	872.5	873.6	874.8	875.6	876.2	876.8	877.4	878.0	877.0	876.1
140°	907.9	909.0	910.1	911.2	911.9	912.1	912.4	912.6	912.8	912.6	912.4
142.5°	941.1	942.2	943.3	944.5	945.2	945.6	946.0	946.5	946.9	946.6	946.4
145°	992.3	992.7	993.2	993.6	994.2	994.9	995.6	996.2	996.9	996.7	996.5
147.5°	1038.0	1038.8	1039.7	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7	1043.7
150°	1069.3	1069.7	1070.2	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9	1072.9
152.5°	1095.4	1096.0	1096.7	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2	1099.5
155°	1135.7	1135.7	1135.7	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6	1138.5
157.5°	1170.3	1170.0	1169.7	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1	1172.0
160°	1192.0	1191.5	1191.1	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5	1192.7
162.5°	1211.3	1210.6	1210.0	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0	1212.1
165°	1236.3	1235.7	1235.0	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3	1236.7
167.5°	1256.2	1255.3	1254.4	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2	1256.6
170°	1267.5	1266.6	1265.7	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9	1267.5
172.5°	1276.4	1275.5	1274.6	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7	1276.1
175°	1285.8	1284.9	1284.0	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0	1285.3
177.5°	1289.8	1289.1	1288.3	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3	1289.4
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	831.9	832.2	835.5	838.0	836.8	838.3	838.9
5°	908.8	922.6	929.9	935.3	935.7	936.0	939.1
7.5°	1018.0	1032.8	1043.6	1060.0	1064.9	1070.5	1068.9
10°	1097.7	1119.5	1138.3	1148.2	1158.9	1174.6	1162.0
12.5°	1172.1	1210.8	1239.4	1254.8	1265.0	1268.1	1261.9
15°	1294.9	1345.5	1372.7	1371.9	1406.4	1421.3	1397.9
17.5°	1407.5	1454.2	1491.5	1510.7	1539.4	1545.8	1542.9
20°	1476.4	1527.4	1556.5	1589.4	1604.4	1617.8	1620.1
22.5°	1535.9	1581.6	1612.9	1640.3	1652.8	1659.1	1663.0
25°	1597.1	1633.1	1651.9	1661.4	1664.9	1664.1	1659.1
27.5°	1592.9	1595.6	1575.0	1554.7	1536.5	1516.0	1509.0
30°	1551.5	1519.3	1461.9	1429.3	1381.5	1343.5	1358.9
32.5°	1442.7	1378.7	1314.2	1243.0	1184.1	1167.4	1150.5
35°	1231.3	1118.7	1052.9	976.3	945.6	915.0	893.9
37.5°	996.2	909.1	830.9	780.8	750.1	730.8	720.3
40°	861.4	782.8	718.5	677.9	654.5	632.7	629.6
42.5°	753.8	680.8	632.4	600.1	577.6	568.4	561.6
45°	617.4	566.4	533.9	510.9	496.0	490.2	482.6
47.5°	522.6	486.6	462.1	446.5	435.2	430.9	430.3
50°	469.6	439.7	421.7	409.4	400.6	399.1	393.0
52.5°	429.7	403.8	389.8	379.1	372.7	368.4	366.6
55°	373.0	355.8	343.2	337.0	332.1	327.8	327.8
57.5°	326.4	312.0	303.6	298.4	296.9	293.9	292.0
60°	297.6	285.3	278.8	274.2	271.2	271.5	268.1
62.5°	269.4	261.4	255.2	250.6	247.0	247.0	247.3
65°	229.4	223.3	218.7	217.2	214.9	212.2	212.9
67.5°	194.4	188.7	185.1	182.5	181.7	180.2	182.5
70°	169.3	165.1	162.4	160.1	159.3	159.7	161.6
72.5°	146.3	143.3	141.6	140.5	138.8	138.9	140.2
75°	114.9	112.6	111.1	109.9	109.5	109.5	109.5
77.5°	84.4	83.9	83.2	81.5	81.6	82.0	82.1
80°	66.6	65.5	65.1	64.3	63.2	62.4	64.3
82.5°	49.8	48.6	48.3	48.1	46.3	46.2	47.8
85°	26.8	25.7	26.0	25.7	25.7	25.3	25.3
87.5°	14.9	14.8	14.6	15.0	14.8	14.6	15.3
90°	27.0	27.9	28.6	29.0	29.5	29.9	30.4
92.5°	41.1	41.8	42.0	41.7	41.5	41.2	40.9
95°	77.7	78.6	79.0	79.0	79.0	79.0	79.0
97.5°	120.4	121.5	121.9	121.8	121.8	121.7	121.6
100°	151.0	151.6	152.2	152.6	153.1	153.5	154.0
102.5°	186.6	187.3	187.6	187.5	187.4	187.3	187.2
105°	239.1	239.1	239.3	239.8	240.2	240.7	241.1
107.5°	297.4	298.1	298.3	298.1	297.8	297.5	297.2
110°	336.0	336.9	337.1	336.7	336.2	335.8	335.3



TEST NUMBER: P332133

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.6	375.7	376.2	376.1	376.0	376.0	375.9
115°	432.3	432.5	432.5	432.3	432.0	431.8	431.6
117.5°	491.0	491.0	490.6	490.0	489.4	488.7	488.1
120°	530.2	530.0	529.6	529.2	528.7	528.3	527.8
122.5°	569.6	569.1	568.4	567.8	567.2	566.6	565.9
125°	628.5	627.6	626.7	625.8	624.9	624.0	623.1
127.5°	686.6	685.3	684.1	683.1	682.1	681.0	680.0
130°	725.7	724.8	723.6	722.0	720.4	718.9	717.3
132.5°	763.3	762.2	761.1	759.8	758.6	757.4	756.2
135°	819.9	819.0	818.4	817.9	817.5	817.0	816.6
137.5°	875.1	874.2	873.3	872.4	871.6	870.7	869.9
140°	912.1	911.9	911.0	909.4	907.9	906.3	904.7
142.5°	946.2	946.0	945.2	944.0	942.8	941.6	940.4
145°	996.2	996.0	995.4	994.5	993.6	992.7	991.8
147.5°	1043.7	1043.7	1043.0	1041.7	1040.3	1039.0	1037.6
150°	1072.9	1072.9	1072.2	1070.9	1069.5	1068.2	1066.8
152.5°	1099.9	1100.3	1099.9	1098.7	1097.5	1096.3	1095.2
155°	1139.4	1140.3	1140.0	1138.4	1136.8	1135.3	1133.7
157.5°	1173.0	1173.9	1173.8	1172.5	1171.3	1170.0	1168.7
160°	1193.8	1194.9	1195.0	1194.1	1193.2	1192.3	1191.4
162.5°	1213.2	1214.4	1214.2	1212.8	1211.3	1209.9	1208.4
165°	1238.0	1239.4	1239.3	1237.7	1236.1	1234.5	1233.0
167.5°	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8
170°	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4
172.5°	1277.5	1278.9	1278.8	1277.2	1275.6	1274.0	1272.5
175°	1286.7	1288.0	1287.9	1286.3	1284.7	1283.2	1281.6
177.5°	1290.5	1291.6	1291.5	1290.2	1289.0	1287.7	1286.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7

(END OF REPORT)