

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332191-940

Luminaire Tested: **S123DIW-S1000D755U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332191-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6009.7 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	59	57	56
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	51	49	47
3	83	73	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	64	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	27	24
8	55	43	35	29	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	2.2
10°-20°	375.4	6.2
20°-30°	554.6	9.2
30°-40°	647.8	10.8
40°-50°	651.3	10.8
50°-60°	572.1	9.5
60°-70°	426.2	7.1
70°-80°	242.8	4.0
80°-90°	72.2	1.2
90°-100°	54.9	0.9
100°-110°	164.3	2.7
110°-120°	279.4	4.6
120°-130°	367.5	6.1
130°-140°	413.1	6.9
140°-150°	406.1	6.8
150°-160°	341.9	5.7
160°-170°	227.6	3.8
170°-180°	79.7	1.3
0°-30°	1062.9	17.7
0°-40°	1710.7	28.5
0°-60°	2934.1	48.8
0°-90°	3675.3	61.2
90°-120°	498.6	8.3
90°-150°	1685.3	28.0
90°-180°	2334.0	38.8
0°-180°	6009.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	7	16	18	20	6
95°	39	44	49	52	52	44
105°	149	150	156	156	158	159
115°	281	283	282	283	282	278
125°	412	414	412	410	407	367
135°	534	538	537	535	533	411
145°	648	649	651	650	648	405
155°	742	742	743	745	741	341
165°	808	806	806	810	806	228
175°	840	838	838	841	837	80
180°	843	843	843	843	843	



TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	24.7	24.3	24.0	23.9	24.1	24.2	24.3	24.5	24.4
90°	0.6	2.1	3.6	5.1	6.5	8.2	10.2	12.0	14.0	15.9	16.5
92.5°	16.1	17.0	18.0	19.0	20.0	21.0	22.1	23.3	24.3	25.4	25.9
95°	39.1	40.0	41.1	42.2	43.2	44.2	45.5	46.6	47.8	49.0	49.6
97.5°	69.4	70.1	70.9	71.7	72.4	73.2	74.1	74.9	75.8	76.7	77.3
100°	90.0	90.9	91.8	92.6	93.5	94.3	95.1	95.9	96.6	97.3	97.7
102.5°	113.9	114.4	114.9	115.4	115.9	116.7	117.7	118.7	119.6	120.6	121.0
105°	148.9	149.2	149.5	149.8	150.1	150.9	152.2	153.6	154.9	156.2	156.2
107.5°	189.7	189.8	190.0	190.2	190.4	190.7	191.3	191.8	192.3	192.9	193.3
110°	215.1	215.4	215.7	216.0	216.2	216.6	216.9	217.1	217.5	217.8	218.4



TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	241.6	241.7	241.9	242.1	242.3	242.4	242.5	242.5	242.5	242.6	243.3
115°	281.3	281.7	282.1	282.6	283.0	283.1	282.9	282.6	282.2	282.0	282.1
117.5°	321.3	321.6	321.8	322.2	322.4	322.4	322.0	321.6	321.3	320.8	320.8
120°	346.2	347.1	347.9	348.8	349.7	349.7	349.0	348.3	347.6	346.8	346.7
122.5°	372.1	372.7	373.4	374.1	374.7	374.8	374.4	374.1	373.7	373.3	372.9
125°	411.7	412.1	412.6	413.0	413.5	413.5	413.2	413.0	412.6	412.3	411.8
127.5°	448.2	449.2	450.1	451.0	452.0	452.3	452.0	451.7	451.3	451.0	450.1
130°	472.6	473.8	474.9	476.1	477.2	477.7	477.2	476.8	476.4	475.9	475.3
132.5°	497.0	498.1	499.3	500.4	501.7	502.0	501.8	501.4	501.1	500.8	500.1
135°	534.1	535.0	535.9	536.8	537.6	538.1	537.9	537.7	537.6	537.4	536.8
137.5°	568.6	569.3	570.0	570.8	571.5	572.0	572.4	572.8	573.2	573.5	572.9
140°	592.4	593.1	593.9	594.6	595.3	595.8	595.9	596.0	596.2	596.4	596.2
142.5°	614.1	614.8	615.5	616.3	617.0	617.5	617.8	618.0	618.3	618.6	618.4
145°	648.0	648.3	648.5	648.8	649.2	649.5	650.0	650.4	650.9	651.3	651.1
147.5°	677.6	678.1	678.7	679.2	679.8	680.2	680.6	681.0	681.4	681.9	681.9
150°	698.3	698.6	698.8	699.2	699.5	699.7	700.0	700.3	700.6	700.9	700.9
152.5°	715.2	715.6	716.0	716.5	716.8	717.1	717.3	717.5	717.6	717.8	718.1
155°	742.0	742.0	742.0	742.0	742.0	742.0	742.2	742.3	742.4	742.6	743.2
157.5°	764.7	764.6	764.4	764.2	764.0	764.0	764.1	764.2	764.4	764.5	765.1
160°	779.0	778.7	778.5	778.1	777.8	777.7	777.7	777.7	777.7	777.7	778.5
162.5°	791.8	791.3	790.9	790.5	790.1	790.0	790.1	790.1	790.3	790.4	791.1
165°	808.2	807.7	807.3	806.8	806.4	806.1	806.1	806.1	806.1	806.1	807.0
167.5°	821.3	820.6	820.1	819.5	818.9	818.7	818.8	818.9	819.0	819.1	820.0
170°	828.7	828.0	827.5	826.9	826.3	826.0	826.0	826.0	826.0	826.0	827.1
172.5°	834.5	833.9	833.3	832.7	832.1	831.8	831.8	831.8	831.8	831.8	832.8
175°	840.5	840.0	839.4	838.8	838.2	837.9	837.9	837.9	837.9	837.9	838.8
177.5°	843.1	842.6	842.1	841.7	841.2	841.0	841.0	841.0	841.0	841.0	841.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	24.3	24.3	24.2	24.2	24.2	24.3	24.3	24.3
90°	17.0	17.7	18.3	18.6	19.0	19.3	19.5	19.9
92.5°	26.4	26.8	27.3	27.5	27.3	27.1	26.9	26.8
95°	50.1	50.7	51.4	51.6	51.6	51.6	51.6	51.6
97.5°	78.0	78.6	79.4	79.6	79.6	79.5	79.5	79.5
100°	98.2	98.6	99.1	99.4	99.7	100.0	100.3	100.6
102.5°	121.5	121.9	122.3	122.5	122.5	122.4	122.3	122.3
105°	156.2	156.2	156.2	156.3	156.7	156.9	157.2	157.6
107.5°	193.8	194.3	194.7	194.9	194.7	194.6	194.4	194.2
110°	218.9	219.5	220.1	220.3	220.0	219.6	219.4	219.1



TEST NUMBER: P332191-940

CATALOG NUMBER: S123DIW-S1000D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.1	244.8	245.5	245.8	245.8	245.7	245.6	245.6
115°	282.2	282.4	282.6	282.6	282.4	282.2	282.1	282.0
117.5°	320.8	320.7	320.7	320.6	320.1	319.7	319.3	318.9
120°	346.5	346.3	346.3	346.0	345.7	345.4	345.1	344.8
122.5°	372.6	372.1	371.8	371.4	371.0	370.5	370.1	369.7
125°	411.2	410.5	410.0	409.4	408.8	408.2	407.6	407.1
127.5°	449.3	448.5	447.7	446.9	446.3	445.6	445.0	444.3
130°	474.7	474.1	473.5	472.7	471.7	470.6	469.7	468.6
132.5°	499.4	498.6	497.9	497.2	496.4	495.6	494.8	494.0
135°	536.3	535.7	535.1	534.7	534.3	534.0	533.8	533.4
137.5°	572.3	571.7	571.1	570.5	570.0	569.4	568.8	568.3
140°	596.0	595.9	595.8	595.1	594.1	593.1	592.1	591.0
142.5°	618.3	618.1	618.0	617.5	616.7	615.9	615.1	614.3
145°	650.9	650.9	650.7	650.3	649.7	649.2	648.5	648.0
147.5°	681.9	681.9	681.9	681.4	680.6	679.7	678.8	677.9
150°	700.9	700.9	700.9	700.4	699.5	698.7	697.9	697.0
152.5°	718.4	718.5	718.8	718.5	717.7	717.0	716.2	715.5
155°	743.8	744.4	744.9	744.8	743.7	742.7	741.6	740.7
157.5°	765.7	766.3	767.0	766.8	766.0	765.2	764.4	763.5
160°	779.2	779.9	780.6	780.7	780.2	779.5	778.9	778.4
162.5°	791.8	792.6	793.4	793.3	792.3	791.4	790.4	789.4
165°	807.9	808.8	809.7	809.6	808.6	807.5	806.6	805.5
167.5°	820.9	821.9	822.8	822.8	821.9	820.9	820.0	819.1
170°	828.0	829.1	830.1	830.1	829.1	828.0	827.1	826.0
172.5°	833.7	834.6	835.4	835.4	834.4	833.4	832.3	831.3
175°	839.7	840.5	841.4	841.4	840.3	839.3	838.3	837.2
177.5°	842.4	843.1	843.8	843.7	842.9	842.0	841.2	840.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6

(END OF REPORT)