

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332137

Luminaire Tested: **S123DIW-S560D1030U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332137
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1030U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5895.3 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.4
10°-20°	237.0	4.0
20°-30°	350.0	5.9
30°-40°	408.9	6.9
40°-50°	411.1	7.0
50°-60°	361.1	6.1
60°-70°	269.0	4.6
70°-80°	153.3	2.6
80°-90°	47.8	0.8
90°-100°	84.0	1.4
100°-110°	251.5	4.3
110°-120°	427.7	7.3
120°-130°	562.6	9.5
130°-140°	632.3	10.7
140°-150°	621.6	10.5
150°-160°	523.3	8.9
160°-170°	348.3	5.9
170°-180°	122.0	2.1
0°-30°	670.9	11.4
0°-40°	1079.8	18.3
0°-60°	1851.9	31.4
0°-90°	2322.0	39.4
90°-120°	763.2	12.9
90°-150°	2579.7	43.8
90°-180°	3573.0	60.6
0°-180°	5895.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	1	11	24	28	30	6
95°	60	67	75	79	79	67
105°	228	230	239	239	241	244
115°	431	433	432	432	432	426
125°	630	633	631	627	623	562
135°	818	823	823	819	817	630
145°	992	994	997	996	992	619
155°	1136	1136	1137	1140	1134	523
165°	1237	1234	1234	1239	1233	349
175°	1287	1283	1283	1288	1282	122
180°	1290	1290	1290	1290	1290	



TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.1	16.2	16.2	16.3	16.3	16.5	17.0	17.4	17.9	18.3	18.4
90°	1.0	3.3	5.5	7.8	10.0	12.6	15.5	18.5	21.4	24.3	25.2
92.5°	24.5	26.0	27.6	29.1	30.6	32.2	33.9	35.6	37.2	38.9	39.6
95°	59.8	61.3	62.9	64.5	66.1	67.8	69.6	71.4	73.2	75.0	75.9
97.5°	106.2	107.3	108.5	109.7	110.9	112.1	113.4	114.7	116.0	117.3	118.4
100°	137.8	139.1	140.5	141.8	143.2	144.4	145.6	146.7	147.8	148.9	149.6
102.5°	174.3	175.1	175.9	176.7	177.5	178.6	180.1	181.6	183.1	184.6	185.3
105°	228.0	228.4	228.9	229.3	229.8	231.0	233.0	235.0	237.1	239.1	239.1
107.5°	290.4	290.6	290.9	291.2	291.4	292.0	292.8	293.6	294.4	295.2	295.9
110°	329.3	329.7	330.2	330.6	331.1	331.5	332.0	332.4	332.9	333.3	334.2



TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	369.8	370.1	370.3	370.6	370.9	371.0	371.1	371.2	371.3	371.4	372.5
115°	430.6	431.2	431.9	432.6	433.3	433.4	432.9	432.5	432.0	431.6	431.8
117.5°	491.8	492.2	492.7	493.1	493.6	493.5	492.9	492.3	491.7	491.2	491.1
120°	529.9	531.2	532.6	533.9	535.3	535.4	534.2	533.1	532.0	530.9	530.6
122.5°	569.6	570.6	571.6	572.5	573.5	573.7	573.2	572.6	572.0	571.4	570.8
125°	630.2	630.8	631.5	632.2	632.9	633.0	632.5	632.1	631.6	631.2	630.3
127.5°	686.1	687.5	689.0	690.4	691.8	692.3	691.8	691.3	690.8	690.3	689.1
130°	723.4	725.2	727.0	728.8	730.6	731.1	730.5	729.8	729.1	728.4	727.5
132.5°	760.6	762.4	764.2	766.1	767.9	768.5	768.0	767.5	767.0	766.5	765.4
135°	817.6	818.9	820.3	821.6	823.0	823.5	823.3	823.1	822.9	822.6	821.7
137.5°	870.3	871.4	872.5	873.6	874.8	875.6	876.2	876.8	877.4	878.0	877.0
140°	906.7	907.9	909.0	910.1	911.2	911.9	912.1	912.4	912.6	912.8	912.6
142.5°	940.0	941.1	942.2	943.3	944.5	945.2	945.6	946.0	946.5	946.9	946.6
145°	991.8	992.3	992.7	993.2	993.6	994.2	994.9	995.6	996.2	996.9	996.7
147.5°	1037.2	1038.0	1038.8	1039.7	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7
150°	1068.8	1069.3	1069.7	1070.2	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9
152.5°	1094.8	1095.4	1096.0	1096.7	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2
155°	1135.7	1135.7	1135.7	1135.7	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6
157.5°	1170.6	1170.3	1170.0	1169.7	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1
160°	1192.4	1192.0	1191.5	1191.1	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5
162.5°	1211.9	1211.3	1210.6	1210.0	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0
165°	1237.0	1236.3	1235.7	1235.0	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3
167.5°	1257.1	1256.2	1255.3	1254.4	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2
170°	1268.4	1267.5	1266.6	1265.7	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9
172.5°	1277.3	1276.4	1275.5	1274.6	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7
175°	1286.7	1285.8	1284.9	1284.0	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0
177.5°	1290.5	1289.8	1289.1	1288.3	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	18.4	18.5	18.5	18.6	18.7	18.8	18.9	18.9
90°	26.1	27.0	27.9	28.6	29.0	29.5	29.9	30.4
92.5°	40.3	41.1	41.8	42.0	41.7	41.5	41.2	40.9
95°	76.8	77.7	78.6	79.0	79.0	79.0	79.0	79.0
97.5°	119.4	120.4	121.5	121.9	121.8	121.8	121.7	121.6
100°	150.3	151.0	151.6	152.2	152.6	153.1	153.5	154.0
102.5°	185.9	186.6	187.3	187.6	187.5	187.4	187.3	187.2
105°	239.1	239.1	239.1	239.3	239.8	240.2	240.7	241.1
107.5°	296.7	297.4	298.1	298.3	298.1	297.8	297.5	297.2
110°	335.1	336.0	336.9	337.1	336.7	336.2	335.8	335.3



TEST NUMBER: P332137

CATALOG NUMBER: S123DIW-S560D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	373.6	374.6	375.7	376.2	376.1	376.0	376.0	375.9
115°	432.0	432.3	432.5	432.5	432.3	432.0	431.8	431.6
117.5°	491.1	491.0	491.0	490.6	490.0	489.4	488.7	488.1
120°	530.4	530.2	530.0	529.6	529.2	528.7	528.3	527.8
122.5°	570.2	569.6	569.1	568.4	567.8	567.2	566.6	565.9
125°	629.4	628.5	627.6	626.7	625.8	624.9	624.0	623.1
127.5°	687.8	686.6	685.3	684.1	683.1	682.1	681.0	680.0
130°	726.6	725.7	724.8	723.6	722.0	720.4	718.9	717.3
132.5°	764.4	763.3	762.2	761.1	759.8	758.6	757.4	756.2
135°	820.8	819.9	819.0	818.4	817.9	817.5	817.0	816.6
137.5°	876.1	875.1	874.2	873.3	872.4	871.6	870.7	869.9
140°	912.4	912.1	911.9	911.0	909.4	907.9	906.3	904.7
142.5°	946.4	946.2	946.0	945.2	944.0	942.8	941.6	940.4
145°	996.5	996.2	996.0	995.4	994.5	993.6	992.7	991.8
147.5°	1043.7	1043.7	1043.7	1043.0	1041.7	1040.3	1039.0	1037.6
150°	1072.9	1072.9	1072.9	1072.2	1070.9	1069.5	1068.2	1066.8
152.5°	1099.5	1099.9	1100.3	1099.9	1098.7	1097.5	1096.3	1095.2
155°	1138.5	1139.4	1140.3	1140.0	1138.4	1136.8	1135.3	1133.7
157.5°	1172.0	1173.0	1173.9	1173.8	1172.5	1171.3	1170.0	1168.7
160°	1192.7	1193.8	1194.9	1195.0	1194.1	1193.2	1192.3	1191.4
162.5°	1212.1	1213.2	1214.4	1214.2	1212.8	1211.3	1209.9	1208.4
165°	1236.7	1238.0	1239.4	1239.3	1237.7	1236.1	1234.5	1233.0
167.5°	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8
170°	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4
172.5°	1276.1	1277.5	1278.9	1278.8	1277.2	1275.6	1274.0	1272.5
175°	1285.3	1286.7	1288.0	1287.9	1286.3	1284.7	1283.2	1281.6
177.5°	1289.4	1290.5	1291.6	1291.5	1290.2	1289.0	1287.7	1286.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7

(END OF REPORT)