

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332149

Luminaire Tested: **S123DIW-S560D1535U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332149  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D1535U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7642.4 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	34	33	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27	21
3	77	68	61	56	69	62	55	51	49	45	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.9	1.1
10°-20°	237.0	3.1
20°-30°	350.0	4.6
30°-40°	408.9	5.3
40°-50°	411.1	5.4
50°-60°	361.1	4.7
60°-70°	269.0	3.5
70°-80°	153.3	2.0
80°-90°	49.7	0.6
90°-100°	125.1	1.6
100°-110°	374.3	4.9
110°-120°	636.6	8.3
120°-130°	837.4	11.0
130°-140°	941.2	12.3
140°-150°	925.2	12.1
150°-160°	778.9	10.2
160°-170°	518.5	6.8
170°-180°	181.6	2.4
0°-30°	670.9	8.8
0°-40°	1079.8	14.1
0°-60°	1851.9	24.2
0°-90°	2323.8	30.4
90°-120°	1136.0	14.9
90°-150°	3839.7	50.2
90°-180°	5319.0	69.6
0°-180°	7642.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	2	17	36	42	45	8
95°	89	100	112	117	118	100
105°	339	343	356	356	359	363
115°	641	645	642	644	642	634
125°	938	942	940	933	927	836
135°	1217	1225	1224	1219	1215	937
145°	1476	1479	1484	1482	1476	922
155°	1690	1690	1692	1697	1687	778
165°	1841	1837	1837	1845	1835	519
175°	1915	1909	1909	1917	1908	182
180°	1920	1920	1920	1920	1920	



TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.2	16.5	16.8	17.0	17.3	17.8	18.5	19.2	20.0	20.7	20.9
90°	1.5	4.9	8.2	11.6	14.9	18.8	23.1	27.5	31.8	36.2	37.5
92.5°	36.5	38.8	41.0	43.3	45.6	48.0	50.5	52.9	55.4	57.9	59.0
95°	89.0	91.3	93.7	96.0	98.4	100.9	103.5	106.2	108.9	111.6	112.9
97.5°	158.0	159.8	161.5	163.3	165.0	166.8	168.8	170.7	172.7	174.6	176.2
100°	205.1	207.1	209.1	211.1	213.1	215.0	216.6	218.3	220.0	221.7	222.7
102.5°	259.4	260.6	261.8	263.0	264.2	265.9	268.1	270.3	272.5	274.7	275.8
105°	339.3	340.0	340.6	341.3	342.0	343.8	346.8	349.8	352.9	355.9	355.9
107.5°	432.2	432.6	433.0	433.4	433.8	434.6	435.8	437.0	438.2	439.4	440.5
110°	490.1	490.8	491.4	492.1	492.8	493.4	494.1	494.8	495.4	496.1	497.5



TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	550.4	550.8	551.2	551.6	552.0	552.3	552.4	552.5	552.7	552.8	554.4
115°	640.9	641.9	642.9	643.9	644.9	645.1	644.4	643.7	643.1	642.4	642.7
117.5°	732.0	732.6	733.3	734.0	734.6	734.5	733.7	732.8	731.9	731.1	731.0
120°	788.7	790.7	792.7	794.7	796.7	796.9	795.2	793.5	791.8	790.2	789.8
122.5°	847.8	849.2	850.7	852.2	853.7	854.0	853.1	852.2	851.4	850.5	849.6
125°	937.9	938.9	940.0	941.0	942.0	942.1	941.5	940.8	940.1	939.5	938.1
127.5°	1021.2	1023.3	1025.5	1027.6	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6
130°	1076.7	1079.4	1082.0	1084.7	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9
132.5°	1132.2	1134.8	1137.5	1140.2	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3
135°	1216.9	1218.9	1220.9	1222.9	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1
137.5°	1295.3	1297.0	1298.7	1300.4	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4
140°	1349.6	1351.3	1353.0	1354.6	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3
142.5°	1399.1	1400.7	1402.4	1404.1	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0
145°	1476.3	1477.0	1477.6	1478.3	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5
147.5°	1543.8	1545.0	1546.2	1547.5	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5
150°	1590.9	1591.6	1592.2	1592.9	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9
152.5°	1629.5	1630.4	1631.4	1632.3	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1
155°	1690.4	1690.4	1690.4	1690.4	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3
157.5°	1742.3	1741.9	1741.5	1741.1	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1
160°	1774.9	1774.2	1773.5	1772.8	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5
162.5°	1803.8	1802.9	1801.9	1801.0	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5
165°	1841.2	1840.2	1839.2	1838.2	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7
167.5°	1871.1	1869.7	1868.4	1867.0	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3
170°	1887.9	1886.6	1885.3	1883.9	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3
172.5°	1901.2	1899.9	1898.5	1897.2	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3
175°	1915.1	1913.8	1912.4	1911.1	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1
177.5°	1920.8	1919.8	1918.7	1917.6	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	21.0	21.1	21.2	21.4	21.5	21.6	21.8	21.9
90°	38.9	40.2	41.6	42.6	43.2	43.9	44.6	45.2
92.5°	60.0	61.1	62.2	62.5	62.1	61.7	61.3	60.9
95°	114.3	115.6	116.9	117.6	117.6	117.6	117.6	117.6
97.5°	177.7	179.2	180.8	181.5	181.4	181.2	181.1	181.0
100°	223.7	224.7	225.7	226.5	227.2	227.9	228.5	229.2
102.5°	276.8	277.8	278.8	279.2	279.1	278.9	278.8	278.7
105°	355.9	355.9	355.9	356.2	356.9	357.6	358.2	358.9
107.5°	441.6	442.6	443.7	444.0	443.6	443.2	442.8	442.4
110°	498.8	500.1	501.5	501.8	501.1	500.5	499.8	499.1





TEST NUMBER: P332149

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	556.0	557.6	559.2	560.0	559.9	559.7	559.6	559.4
115°	643.1	643.4	643.7	643.7	643.4	643.1	642.7	642.4
117.5°	730.9	730.9	730.8	730.3	729.3	728.4	727.5	726.5
120°	789.5	789.2	788.8	788.3	787.7	787.0	786.3	785.6
122.5°	848.7	847.9	847.0	846.1	845.2	844.2	843.3	842.3
125°	936.8	935.4	934.1	932.7	931.4	930.1	928.7	927.4
127.5°	1023.8	1021.9	1020.0	1018.3	1016.8	1015.2	1013.7	1012.1
130°	1081.5	1080.2	1078.9	1077.0	1074.7	1072.3	1070.0	1067.6
132.5°	1137.7	1136.1	1134.5	1132.8	1131.0	1129.2	1127.3	1125.5
135°	1221.8	1220.4	1219.1	1218.1	1217.4	1216.7	1216.1	1215.4
137.5°	1304.0	1302.6	1301.2	1299.8	1298.5	1297.3	1296.0	1294.7
140°	1358.0	1357.7	1357.3	1356.0	1353.6	1351.3	1348.9	1346.6
142.5°	1408.7	1408.3	1408.0	1406.9	1405.1	1403.3	1401.5	1399.7
145°	1483.1	1482.8	1482.5	1481.6	1480.3	1479.0	1477.6	1476.3
147.5°	1553.5	1553.5	1553.5	1552.5	1550.5	1548.5	1546.4	1544.4
150°	1596.9	1596.9	1596.9	1595.9	1593.9	1591.9	1589.9	1587.9
152.5°	1636.6	1637.1	1637.7	1637.1	1635.3	1633.6	1631.8	1630.1
155°	1694.6	1695.9	1697.3	1696.8	1694.4	1692.1	1689.7	1687.4
157.5°	1744.5	1745.9	1747.3	1747.1	1745.2	1743.3	1741.4	1739.6
160°	1775.2	1776.9	1778.5	1778.7	1777.4	1776.0	1774.7	1773.3
162.5°	1804.1	1805.8	1807.5	1807.3	1805.1	1803.0	1800.8	1798.7
165°	1840.7	1842.7	1844.7	1844.6	1842.2	1839.9	1837.5	1835.2
167.5°	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2
170°	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9
172.5°	1899.3	1901.4	1903.5	1903.4	1901.0	1898.7	1896.3	1894.0
175°	1913.1	1915.1	1917.1	1916.9	1914.6	1912.2	1909.9	1907.6
177.5°	1919.2	1920.8	1922.4	1922.3	1920.4	1918.5	1916.7	1914.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6

(END OF REPORT)