

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332220-940

Luminaire Tested: **S123DIW-S1165D755U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332220-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D755U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6937.7 lumens  
Efficiency: N/A  
Efficacy: 116.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	59	57	56
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	52	49	47
3	83	73	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	64	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	27	24
8	55	43	35	29	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17546	17546	17546
5°	17629	17386	17507
10°	17511	17235	17343
15°	17307	17041	17072
20°	17068	16763	16778
25°	16747	16431	16397
30°	16394	16063	15940
35°	16025	15674	15471
40°	15638	15244	15008
45°	15213	14850	14487
50°	14788	14364	13966
55°	14230	13863	13440
60°	13670	13276	12854
65°	13173	12638	12246
70°	12441	11909	11383
75°	11366	10959	10493
80°	10253	9819	9732
85°	9003	8657	8312



TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.6	2.2
10°-20°	433.6	6.2
20°-30°	640.5	9.2
30°-40°	748.2	10.8
40°-50°	752.2	10.8
50°-60°	660.7	9.5
60°-70°	492.2	7.1
70°-80°	280.4	4.0
80°-90°	83.0	1.2
90°-100°	32.1	0.5
100°-110°	153.0	2.2
110°-120°	367.6	5.3
120°-130°	468.1	6.7
130°-140°	500.2	7.2
140°-150°	467.7	6.7
150°-160°	377.3	5.4
160°-170°	243.5	3.5
170°-180°	83.9	1.2
0°-30°	1227.6	17.7
0°-40°	1975.8	28.5
0°-60°	3388.7	48.8
0°-90°	4244.3	61.2
90°-120°	552.8	8.0
90°-150°	1988.7	28.7
90°-180°	2693.0	38.8
0°-180°	6937.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1630	1630	1630	1630	1630	
5°	1632	1624	1609	1622	1620	155
15°	1553	1547	1529	1539	1532	438
25°	1410	1401	1384	1385	1381	649
35°	1220	1211	1193	1185	1177	763
45°	999	993	976	959	952	771
55°	758	756	739	724	716	679
65°	517	510	496	485	481	510
75°	273	268	264	257	252	292
85°	73	70	70	67	67	80
90°	1	7	16	18	20	6
95°	40	15	20	25	25	49
105°	196	199	144	34	29	207
115°	367	371	377	383	386	362
125°	517	522	525	526	528	462
135°	644	648	650	652	650	495
145°	743	747	749	750	750	465
155°	818	817	818	821	817	377
165°	863	861	860	865	861	244
175°	883	880	881	885	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1635.8	1634.8	1633.8	1632.8	1631.7	1629.9	1627.2	1624.4	1621.7	1618.9	1621.4
5°	1631.6	1630.0	1628.4	1626.9	1625.3	1622.8	1619.4	1616.0	1612.6	1609.1	1612.2
7.5°	1615.6	1614.0	1612.5	1610.9	1609.4	1606.8	1603.2	1599.7	1596.2	1592.6	1595.4
10°	1602.1	1600.5	1599.0	1597.4	1595.9	1593.1	1589.0	1585.0	1580.9	1576.9	1579.7
12.5°	1584.2	1582.9	1581.5	1580.3	1579.0	1576.4	1572.6	1568.8	1565.0	1561.2	1563.3
15°	1553.1	1551.8	1550.6	1549.3	1548.1	1545.4	1541.4	1537.3	1533.3	1529.2	1531.7
17.5°	1516.9	1515.3	1513.7	1512.1	1510.4	1507.6	1503.5	1499.5	1495.4	1491.4	1493.2
20°	1490.0	1488.1	1486.2	1484.3	1482.6	1479.5	1475.5	1471.5	1467.4	1463.4	1464.6
22.5°	1459.7	1457.9	1456.0	1454.1	1452.2	1449.3	1445.2	1441.2	1437.2	1433.1	1434.0
25°	1410.1	1408.2	1406.3	1404.4	1402.7	1399.6	1395.6	1391.6	1387.5	1383.5	1383.8
27.5°	1357.1	1355.3	1353.5	1351.7	1349.9	1346.8	1342.5	1338.1	1333.7	1329.4	1329.6
30°	1319.0	1317.4	1315.9	1314.3	1312.8	1309.8	1305.5	1301.1	1296.7	1292.4	1292.4
32.5°	1280.9	1278.8	1276.8	1274.7	1272.6	1269.9	1266.6	1263.2	1259.8	1256.5	1254.7
35°	1219.5	1217.6	1215.8	1213.9	1212.0	1209.1	1205.0	1201.0	1196.9	1192.8	1191.0
37.5°	1156.6	1154.3	1151.9	1149.6	1147.2	1144.0	1139.9	1135.8	1131.7	1127.5	1125.2
40°	1112.9	1111.1	1109.2	1107.3	1105.5	1102.3	1098.0	1093.6	1089.2	1084.9	1082.4
42.5°	1069.2	1067.1	1065.0	1062.8	1060.7	1057.5	1053.1	1048.7	1044.4	1040.1	1037.6
45°	999.4	998.2	996.9	995.7	994.4	991.8	987.7	983.6	979.6	975.5	971.9
47.5°	930.1	928.4	926.6	924.7	922.9	920.2	916.3	912.5	908.7	904.9	901.3
50°	883.1	881.5	879.9	878.4	876.8	874.1	870.0	865.9	861.8	857.8	854.4
52.5°	833.7	832.7	831.6	830.5	829.5	826.8	822.5	818.2	814.0	809.6	806.6
55°	758.3	758.0	757.7	757.4	757.1	754.9	750.8	746.8	742.7	738.7	735.3
57.5°	686.5	685.5	684.4	683.4	682.3	680.2	676.9	673.7	670.5	667.2	664.1
60°	635.0	634.6	634.4	634.0	633.7	631.7	627.9	624.2	620.5	616.7	613.9
62.5°	589.0	588.2	587.4	586.6	585.8	583.4	579.7	576.0	572.3	568.6	565.7
65°	517.2	515.7	514.1	512.6	511.0	508.6	505.5	502.4	499.3	496.2	493.7
67.5°	441.2	439.9	438.5	437.1	435.8	433.9	431.5	429.2	426.8	424.5	422.2
70°	395.3	393.4	391.6	389.7	387.8	385.9	384.1	382.2	380.3	378.4	376.3
72.5°	347.1	345.7	344.3	343.0	341.6	339.8	337.7	335.6	333.5	331.4	329.4
75°	273.3	272.1	270.8	269.6	268.3	267.2	266.4	265.4	264.5	263.5	262.0
77.5°	208.0	207.3	206.6	206.0	205.3	204.4	203.2	202.2	201.0	199.9	198.9
80°	165.4	164.4	163.5	162.6	161.7	160.9	160.2	159.6	159.0	158.4	158.1
82.5°	123.9	123.7	123.5	123.3	123.1	123.0	122.9	122.8	122.6	122.5	122.0
85°	72.9	72.2	71.6	71.0	70.4	70.1	70.1	70.1	70.1	70.1	69.5
87.5°	29.2	28.8	28.4	27.9	27.5	27.3	27.5	27.6	27.7	27.8	27.6
90°	0.6	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3
92.5°	12.2	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7
95°	40.0	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4
97.5°	80.4	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3
100°	110.9	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8
102.5°	145.5	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6
105°	195.6	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9
107.5°	248.3	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4
110°	283.5	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1



TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.1	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1
115°	366.8	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1
117.5°	415.0	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0
120°	444.9	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0
122.5°	475.4	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5
125°	517.1	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2
127.5°	557.5	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3
130°	582.6	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1
132.5°	606.8	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7
135°	643.7	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7
137.5°	675.2	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3
140°	696.2	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7
142.5°	715.6	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0
145°	742.8	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9
147.5°	768.4	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0
150°	784.2	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7
152.5°	798.3	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5
155°	818.2	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3
157.5°	833.7	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8
160°	843.2	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8
162.5°	852.1	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8
165°	862.9	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4
167.5°	871.3	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8
170°	876.0	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5
172.5°	879.1	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7
175°	883.2	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6
177.5°	884.2	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1623.9	1626.4	1628.9	1630.0	1629.8	1629.5	1629.2	1629.1
5°	1615.3	1618.5	1621.6	1622.8	1622.2	1621.6	1621.0	1620.3
7.5°	1598.2	1601.0	1603.8	1605.0	1604.6	1604.3	1603.9	1603.6
10°	1582.5	1585.3	1588.1	1589.2	1588.6	1588.0	1587.3	1586.7
12.5°	1565.3	1567.4	1569.4	1570.3	1569.9	1569.5	1569.1	1568.8
15°	1534.2	1536.7	1539.2	1539.5	1537.7	1535.8	1533.9	1532.0
17.5°	1494.9	1496.6	1498.3	1498.9	1498.3	1497.5	1496.8	1496.2
20°	1465.9	1467.1	1468.4	1468.5	1467.6	1466.6	1465.7	1464.7
22.5°	1435.1	1436.1	1437.1	1437.0	1435.8	1434.6	1433.4	1432.3
25°	1384.1	1384.4	1384.7	1384.4	1383.5	1382.5	1381.6	1380.6
27.5°	1329.9	1330.1	1330.3	1329.9	1328.7	1327.5	1326.3	1325.2
30°	1292.4	1292.4	1292.4	1291.3	1289.1	1286.9	1284.7	1282.5
32.5°	1252.9	1251.2	1249.5	1248.0	1246.9	1245.6	1244.5	1243.3
35°	1189.1	1187.2	1185.4	1183.7	1182.1	1180.5	1178.9	1177.4
37.5°	1123.0	1120.8	1118.6	1117.0	1115.9	1114.9	1113.9	1112.9
40°	1080.0	1077.5	1075.0	1073.1	1071.8	1070.6	1069.3	1068.1
42.5°	1035.1	1032.6	1030.1	1028.2	1027.0	1025.7	1024.5	1023.2
45°	968.1	964.4	960.6	958.0	956.4	954.8	953.3	951.7
47.5°	897.6	893.9	890.2	887.7	886.4	884.9	883.6	882.3
50°	851.0	847.6	844.1	841.5	839.6	837.8	835.9	834.0
52.5°	803.8	800.8	797.9	795.5	793.6	791.8	789.9	788.0
55°	731.8	728.4	725.0	722.5	720.9	719.3	717.8	716.2
57.5°	661.1	658.1	655.0	652.6	650.8	649.0	647.1	645.3
60°	611.2	608.3	605.6	603.3	601.8	600.2	598.7	597.1
62.5°	562.9	560.1	557.3	555.4	554.3	553.2	552.2	551.2
65°	491.2	488.7	486.2	484.6	483.6	482.7	481.7	480.8
67.5°	420.1	417.9	415.7	413.9	412.7	411.3	410.0	408.8
70°	374.1	371.9	369.7	367.8	366.3	364.7	363.2	361.7
72.5°	327.5	325.6	323.6	322.3	321.5	320.7	319.9	319.1
75°	260.4	258.9	257.3	256.0	255.1	254.1	253.2	252.3
77.5°	197.8	196.7	195.6	195.1	195.1	195.1	195.1	195.1
80°	157.7	157.5	157.1	157.0	157.0	157.0	157.0	157.0
82.5°	121.4	120.8	120.3	119.8	119.6	119.4	119.1	118.9
85°	68.8	68.2	67.6	67.3	67.3	67.3	67.3	67.3
87.5°	27.6	27.5	27.3	27.3	27.3	27.4	27.5	27.5
90°	16.9	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	18.6	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	22.4	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	23.5	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	24.0	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	35.9	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	92.1	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	225.5	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	286.3	281.5	276.7	263.9	243.0	222.1	201.3	180.5





TEST NUMBER: P332220-940

CATALOG NUMBER: S123DIW-S1165D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.2	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	379.6	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	425.2	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	455.1	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	484.3	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.5	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	566.9	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	591.7	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.4	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.1	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.3	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.5	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.3	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.3	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.0	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.0	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.0	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	834.7	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	843.6	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	851.8	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	862.6	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	878.9	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	882.6	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.0	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)