

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332130

Luminaire Tested: **S123DIW-S560D755U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332130
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D755U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5341.4 lumens
Efficiency: N/A
Efficacy: 142.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	44	39	37	35	31
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	54	48	66	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.6
10°-20°	237.0	4.4
20°-30°	350.0	6.6
30°-40°	408.9	7.7
40°-50°	411.1	7.7
50°-60°	361.1	6.8
60°-70°	269.0	5.0
70°-80°	153.3	2.9
80°-90°	46.8	0.9
90°-100°	36.0	0.7
100°-110°	171.6	3.2
110°-120°	412.3	7.7
120°-130°	525.0	9.8
130°-140°	560.9	10.5
140°-150°	524.5	9.8
150°-160°	423.1	7.9
160°-170°	273.1	5.1
170°-180°	94.1	1.8
0°-30°	670.9	12.6
0°-40°	1079.8	20.2
0°-60°	1851.9	34.7
0°-90°	2320.9	43.5
90°-120°	619.9	11.6
90°-150°	2230.2	41.8
90°-180°	3020.0	56.5
0°-180°	5341.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	1	8	18	21	22	4
95°	45	17	23	28	28	55
105°	219	223	161	38	32	232
115°	411	416	422	430	433	406
125°	580	586	589	590	592	518
135°	722	726	729	731	729	555
145°	833	838	840	841	841	521
155°	918	916	917	920	916	423
165°	968	966	965	970	965	273
175°	990	987	988	992	987	94
180°	990	990	990	990	990	



TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.1	16.0	15.9	15.8	15.8	15.9	16.1	16.4	16.7	17.0	17.0
90°	0.7	2.4	4.0	5.6	7.3	9.2	11.3	13.4	15.5	17.7	18.3
92.5°	13.7	13.2	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.8	19.9
95°	44.9	38.2	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.2	87.2	84.2	81.2	78.2	70.8	59.0	47.2	35.5	23.7	25.0
100°	124.4	127.6	130.9	134.2	137.4	126.3	100.8	75.3	49.8	24.3	25.6
102.5°	163.2	165.6	167.9	170.3	172.6	159.9	132.0	104.1	76.3	48.4	44.4
105°	219.3	221.1	222.9	224.7	226.5	220.0	205.3	190.6	175.9	161.2	132.2
107.5°	278.4	279.9	281.3	282.8	284.2	286.1	288.4	290.7	293.1	295.4	274.1
110°	317.9	319.2	320.5	321.8	323.1	324.7	326.5	328.3	330.1	331.9	326.5



TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.6	356.7	357.9	359.1	360.3	361.8	363.6	365.4	367.2	369.0	369.1
115°	411.3	412.3	413.3	414.3	415.3	416.5	418.0	419.4	420.9	422.4	424.0
117.5°	465.4	466.6	467.8	469.0	470.2	471.2	471.9	472.7	473.4	474.2	475.5
120°	498.9	500.4	501.9	503.3	504.8	505.8	506.3	506.8	507.3	507.7	509.1
122.5°	533.1	534.3	535.5	536.7	537.9	538.8	539.4	540.1	540.7	541.3	542.2
125°	579.9	581.2	582.5	583.8	585.1	586.1	586.7	587.4	588.0	588.7	589.0
127.5°	625.2	626.5	627.8	629.1	630.4	631.5	632.3	633.0	633.8	634.6	635.1
130°	653.4	654.8	656.1	657.4	658.7	659.7	660.3	661.0	661.6	662.3	662.9
132.5°	680.5	681.8	683.1	684.4	685.8	686.7	687.2	687.7	688.2	688.8	689.4
135°	721.9	722.9	723.8	724.8	725.8	726.6	727.3	727.9	728.6	729.2	729.7
137.5°	757.2	758.4	759.7	760.9	762.2	763.0	763.3	763.7	764.1	764.4	765.2
140°	780.7	781.7	782.7	783.7	784.7	785.4	785.9	786.4	786.9	787.4	788.0
142.5°	802.5	803.5	804.5	805.5	806.5	807.2	807.7	808.2	808.7	809.2	809.7
145°	833.0	834.1	835.3	836.4	837.6	838.3	838.6	839.0	839.3	839.6	839.9
147.5°	861.7	862.4	863.2	863.9	864.7	865.2	865.6	865.9	866.2	866.5	866.9
150°	879.4	879.8	880.3	880.8	881.3	881.7	882.1	882.4	882.7	883.0	883.4
152.5°	895.2	895.5	895.7	895.9	896.2	896.4	896.6	896.8	897.0	897.2	897.7
155°	917.6	917.3	917.0	916.6	916.3	916.2	916.4	916.6	916.7	916.9	917.7
157.5°	935.0	935.0	934.9	934.9	934.9	934.8	934.6	934.4	934.3	934.1	935.1
160°	945.6	945.4	945.3	945.1	944.9	944.8	944.6	944.4	944.3	944.1	945.1
162.5°	955.6	955.2	954.7	954.3	953.9	953.6	953.4	953.3	953.1	952.9	954.1
165°	967.7	967.2	966.7	966.2	965.7	965.4	965.2	965.0	964.9	964.7	966.0
167.5°	977.1	976.4	975.8	975.1	974.5	974.1	974.1	974.1	974.1	974.1	975.4
170°	982.4	981.7	981.1	980.4	979.8	979.4	979.4	979.4	979.4	979.4	980.7
172.5°	985.9	985.1	984.3	983.6	982.8	982.4	982.6	982.7	982.8	983.0	984.3
175°	990.5	989.6	988.8	988.0	987.2	986.9	987.0	987.2	987.4	987.5	988.7
177.5°	991.6	991.0	990.3	989.7	989.0	988.8	988.9	989.0	989.2	989.3	990.3
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	17.0	17.0	17.0	17.0	17.1	17.2	17.2	17.3
90°	19.0	19.6	20.3	20.8	21.1	21.4	21.7	22.1
92.5°	20.9	22.0	23.0	23.6	23.8	24.0	24.2	24.4
95°	25.1	26.2	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.3	27.6	28.9	29.7	29.8	30.0	30.2	30.3
100°	26.9	28.2	29.5	30.3	30.4	30.6	30.7	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.5
105°	103.3	74.3	45.4	31.1	31.4	31.7	32.1	32.4
107.5°	252.9	231.7	210.5	189.0	167.1	145.3	123.5	101.7
110°	321.1	315.7	310.3	295.9	272.5	249.1	225.7	202.4



TEST NUMBER: P332130

CATALOG NUMBER: S123DIW-S560D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.2	369.3	369.4	366.9	362.0	357.1	352.1	347.2
115°	425.7	427.3	428.9	430.1	430.7	431.4	432.0	432.7
117.5°	476.8	478.1	479.4	480.1	480.3	480.4	480.5	480.7
120°	510.4	511.7	513.0	513.6	513.6	513.6	513.6	513.6
122.5°	543.1	544.0	545.0	545.5	545.6	545.7	545.9	546.0
125°	589.3	589.7	590.0	590.3	590.7	591.0	591.3	591.6
127.5°	635.7	636.2	636.7	636.8	636.5	636.1	635.8	635.5
130°	663.6	664.2	664.9	665.1	664.7	664.4	664.1	663.7
132.5°	690.1	690.7	691.4	691.5	691.0	690.6	690.1	689.6
135°	730.2	730.7	731.2	731.2	730.7	730.2	729.7	729.2
137.5°	766.0	766.8	767.6	767.8	767.5	767.1	766.8	766.5
140°	788.7	789.3	790.0	790.2	789.8	789.5	789.2	788.8
142.5°	810.2	810.7	811.2	811.3	810.8	810.4	809.9	809.4
145°	840.3	840.6	840.9	841.1	841.1	841.1	841.1	841.1
147.5°	867.2	867.5	867.9	867.6	866.9	866.1	865.4	864.6
150°	883.7	884.0	884.3	884.3	883.8	883.3	882.8	882.3
152.5°	898.3	898.9	899.5	899.4	898.7	897.9	897.2	896.4
155°	918.5	919.3	920.2	920.1	919.1	918.1	917.1	916.1
157.5°	936.1	937.0	938.0	937.9	936.6	935.3	934.1	932.8
160°	946.1	947.1	948.0	948.0	946.8	945.7	944.5	943.4
162.5°	955.2	956.3	957.4	957.4	956.4	955.4	954.4	953.4
165°	967.3	968.6	969.9	970.0	968.9	967.7	966.6	965.4
167.5°	976.7	978.1	979.4	979.4	978.1	976.7	975.4	974.1
170°	982.0	983.4	984.7	984.7	983.4	982.0	980.7	979.4
172.5°	985.6	986.9	988.2	988.1	986.7	985.3	983.8	982.4
175°	989.8	991.0	992.1	992.0	990.7	989.4	988.1	986.8
177.5°	991.4	992.4	993.5	993.3	992.0	990.7	989.4	988.1
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5

(END OF REPORT)