

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332154

Luminaire Tested: **S123DIW-S775D460U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332154  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D460U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5014.5 lumens  
Efficiency: N/A  
Efficacy: 133.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	91	91	91		79	79	79		68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74		69	68	66		60	59	58	53
2	92	84	78	72	86	79	73	69	70	65	62		61	58	55		53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52		54	50	46		47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44		48	43	40		42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38		43	38	34		38	34	31	28
6	65	52	44	38	61	50	42	36	44	38	33		39	34	30		34	30	27	25
7	60	47	39	33	56	45	37	32	40	34	29		36	31	27		31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24		30	25	22		27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21		28	23	20		25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.7	2.3
10°-20°	323.9	6.5
20°-30°	478.4	9.5
30°-40°	558.9	11.1
40°-50°	561.9	11.2
50°-60°	493.6	9.8
60°-70°	367.7	7.3
70°-80°	209.5	4.2
80°-90°	61.8	1.2
90°-100°	22.0	0.4
100°-110°	104.8	2.1
110°-120°	251.7	5.0
120°-130°	320.5	6.4
130°-140°	342.4	6.8
140°-150°	320.2	6.4
150°-160°	258.3	5.2
160°-170°	166.7	3.3
170°-180°	57.5	1.1
0°-30°	917.1	18.3
0°-40°	1475.9	29.4
0°-60°	2531.4	50.5
0°-90°	3170.4	63.2
90°-120°	378.5	7.5
90°-150°	1361.6	27.2
90°-180°	1844.0	36.8
0°-180°	5014.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	0	5	11	13	14	4
95°	27	10	14	17	17	34
105°	134	136	98	23	20	142
115°	251	254	258	262	264	248
125°	354	358	359	360	361	316
135°	441	443	445	446	445	339
145°	509	512	513	513	514	318
155°	560	559	560	562	559	258
165°	591	590	589	592	590	167
175°	605	603	603	606	602	58
180°	605	605	605	605	605	



TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	21.9	21.5	21.2	20.8	20.4	20.3	20.4	20.4	20.5	20.6	20.5
90°	0.4	1.4	2.4	3.4	4.4	5.6	6.9	8.2	9.5	10.8	11.2
92.5°	8.4	8.1	7.8	7.5	7.2	7.6	8.6	9.5	10.5	11.5	12.1
95°	27.4	23.3	19.2	15.1	11.0	9.5	10.6	11.7	12.8	13.9	14.6
97.5°	55.1	53.2	51.4	49.6	47.7	43.2	36.0	28.8	21.7	14.5	15.3
100°	75.9	77.9	79.9	81.9	83.9	77.1	61.6	46.0	30.4	14.8	15.6
102.5°	99.6	101.1	102.5	104.0	105.4	97.6	80.6	63.6	46.6	29.6	27.1
105°	133.9	135.0	136.1	137.2	138.3	134.3	125.3	116.4	107.4	98.4	80.7
107.5°	170.0	170.9	171.8	172.6	173.5	174.7	176.1	177.5	178.9	180.3	167.4
110°	194.1	194.9	195.7	196.5	197.3	198.2	199.3	200.4	201.5	202.6	199.3



TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.1	217.8	218.5	219.2	220.0	220.9	222.0	223.1	224.2	225.3	225.3
115°	251.1	251.7	252.3	252.9	253.5	254.3	255.2	256.1	257.0	257.9	258.9
117.5°	284.1	284.9	285.6	286.3	287.1	287.7	288.1	288.6	289.1	289.5	290.3
120°	304.6	305.5	306.4	307.3	308.2	308.8	309.1	309.4	309.7	310.0	310.8
122.5°	325.5	326.2	326.9	327.7	328.4	329.0	329.4	329.7	330.1	330.5	331.0
125°	354.0	354.8	355.6	356.4	357.2	357.8	358.2	358.6	359.0	359.4	359.6
127.5°	381.7	382.5	383.3	384.1	384.9	385.5	386.0	386.5	387.0	387.5	387.8
130°	399.0	399.8	400.6	401.4	402.2	402.8	403.2	403.6	404.0	404.3	404.7
132.5°	415.5	416.3	417.1	417.9	418.7	419.2	419.6	419.9	420.2	420.5	420.9
135°	440.7	441.3	441.9	442.5	443.1	443.6	444.0	444.4	444.8	445.2	445.5
137.5°	462.3	463.1	463.8	464.6	465.3	465.8	466.1	466.3	466.5	466.7	467.2
140°	476.7	477.3	477.9	478.5	479.1	479.5	479.8	480.1	480.4	480.7	481.1
142.5°	490.0	490.6	491.2	491.8	492.4	492.8	493.1	493.4	493.7	494.0	494.3
145°	508.6	509.3	510.0	510.7	511.4	511.8	512.0	512.2	512.4	512.6	512.8
147.5°	526.1	526.6	527.0	527.5	527.9	528.3	528.5	528.7	528.9	529.1	529.3
150°	536.9	537.2	537.5	537.8	538.1	538.3	538.5	538.7	538.9	539.1	539.3
152.5°	546.6	546.7	546.9	547.0	547.2	547.3	547.4	547.5	547.6	547.8	548.1
155°	560.2	560.0	559.8	559.7	559.5	559.4	559.5	559.6	559.7	559.8	560.3
157.5°	570.9	570.8	570.8	570.8	570.8	570.7	570.6	570.5	570.4	570.3	570.9
160°	577.3	577.2	577.1	577.0	576.9	576.8	576.7	576.6	576.5	576.4	577.0
162.5°	583.4	583.2	582.9	582.7	582.4	582.2	582.1	582.0	581.9	581.8	582.5
165°	590.8	590.5	590.2	589.9	589.6	589.4	589.3	589.2	589.1	589.0	589.8
167.5°	596.6	596.2	595.8	595.4	595.0	594.8	594.8	594.8	594.8	594.8	595.6
170°	599.8	599.4	599.0	598.6	598.2	598.0	598.0	598.0	598.0	598.0	598.8
172.5°	601.9	601.5	601.0	600.5	600.0	599.8	599.9	600.0	600.1	600.1	600.9
175°	604.7	604.2	603.7	603.2	602.7	602.5	602.6	602.7	602.8	602.9	603.6
177.5°	605.4	605.0	604.6	604.2	603.8	603.7	603.8	603.8	603.9	604.0	604.6
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7



TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	20.4	20.3	20.2	20.1	20.2	20.2	20.2	20.3
90°	11.6	12.0	12.4	12.7	12.9	13.1	13.3	13.5
92.5°	12.8	13.4	14.1	14.4	14.6	14.7	14.8	14.9
95°	15.3	16.0	16.7	17.1	17.1	17.1	17.1	17.1
97.5°	16.1	16.9	17.7	18.1	18.2	18.3	18.4	18.5
100°	16.4	17.2	18.0	18.5	18.6	18.7	18.8	18.9
102.5°	24.6	22.1	19.7	18.5	18.7	18.9	19.0	19.2
105°	63.0	45.4	27.7	19.0	19.2	19.4	19.6	19.8
107.5°	154.4	141.5	128.5	115.4	102.0	88.7	75.4	62.1
110°	196.0	192.7	189.4	180.7	166.4	152.1	137.8	123.6





TEST NUMBER: P332154

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.4	225.4	225.5	224.0	221.0	218.0	215.0	212.0
115°	259.9	260.9	261.9	262.6	263.0	263.4	263.8	264.2
117.5°	291.1	291.9	292.7	293.1	293.2	293.3	293.4	293.5
120°	311.6	312.4	313.2	313.6	313.6	313.6	313.6	313.6
122.5°	331.6	332.2	332.7	333.0	333.1	333.2	333.3	333.4
125°	359.8	360.0	360.2	360.4	360.6	360.8	361.0	361.2
127.5°	388.1	388.4	388.7	388.8	388.6	388.4	388.2	388.0
130°	405.1	405.5	405.9	406.0	405.8	405.6	405.4	405.2
132.5°	421.3	421.7	422.1	422.2	421.9	421.6	421.3	421.1
135°	445.8	446.1	446.4	446.4	446.1	445.8	445.5	445.2
137.5°	467.7	468.1	468.6	468.8	468.6	468.4	468.2	468.0
140°	481.5	481.9	482.3	482.4	482.2	482.0	481.8	481.6
142.5°	494.7	495.0	495.3	495.3	495.0	494.8	494.5	494.2
145°	513.0	513.2	513.4	513.5	513.5	513.5	513.5	513.5
147.5°	529.5	529.7	529.9	529.7	529.3	528.8	528.4	527.9
150°	539.5	539.7	539.9	539.9	539.6	539.3	539.0	538.7
152.5°	548.5	548.8	549.2	549.1	548.7	548.2	547.8	547.3
155°	560.8	561.3	561.8	561.7	561.1	560.5	559.9	559.4
157.5°	571.5	572.1	572.7	572.6	571.8	571.1	570.3	569.5
160°	577.6	578.2	578.8	578.8	578.1	577.4	576.7	576.0
162.5°	583.2	583.9	584.5	584.6	583.9	583.3	582.7	582.1
165°	590.6	591.4	592.2	592.2	591.5	590.9	590.2	589.5
167.5°	596.4	597.1	597.9	597.9	597.1	596.4	595.6	594.8
170°	599.6	600.4	601.2	601.2	600.4	599.6	598.8	598.0
172.5°	601.7	602.5	603.3	603.3	602.4	601.5	600.7	599.8
175°	604.3	605.0	605.7	605.7	604.9	604.1	603.3	602.5
177.5°	605.3	605.9	606.6	606.5	605.7	604.9	604.1	603.3
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7

(END OF REPORT)