

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332157

Luminaire Tested: **S123DIW-S775D755U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332157  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D755U835-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5882.0 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	74	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	25	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11630	11630	11630	11630
5°	13870	11681	10351	11681
10°	17361	11622	9349	11622
15°	21293	11528	8704	11528
20°	25366	11381	8287	11381
25°	26935	11204	8195	11204
30°	23086	11074	8238	11074
35°	16056	10889	8324	10889
40°	12094	10673	8297	10673
45°	10041	10353	8193	10353
50°	8994	9696	8118	9696
55°	8409	8989	8017	8989
60°	7890	8249	7935	8249
65°	7414	7521	7679	7521
70°	6952	6688	7314	6688
75°	6226	5856	6704	5856
80°	5455	4804	5777	4804
85°	4273	3495	3878	3495



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.4	1.8
10°-20°	341.3	5.8
20°-30°	572.8	9.7
30°-40°	648.6	11.0
40°-50°	581.7	9.9
50°-60°	469.4	8.0
60°-70°	327.1	5.6
70°-80°	171.9	2.9
80°-90°	44.8	0.8
90°-100°	61.6	1.0
100°-110°	184.2	3.1
110°-120°	313.4	5.3
120°-130°	412.2	7.0
130°-140°	463.3	7.9
140°-150°	455.4	7.7
150°-160°	383.4	6.5
160°-170°	255.2	4.3
170°-180°	89.4	1.5
0°-30°	1020.6	17.4
0°-40°	1669.2	28.4
0°-60°	2720.2	46.2
0°-90°	3264.1	55.5
90°-120°	559.2	9.5
90°-150°	1890.0	32.1
90°-180°	2618.0	44.5
0°-180°	5882.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1284	1081	958	1081	1284	133
15°	1911	1034	781	1034	1911	552
25°	2268	943	690	943	2268	995
35°	1222	829	634	829	1222	794
45°	660	680	538	680	660	522
55°	448	479	427	479	448	402
65°	291	295	302	295	291	290
75°	150	141	161	141	150	160
85°	35	28	31	28	35	41
90°	22	1	22	1	22	13
95°	58	44	58	44	58	59
105°	177	167	177	167	177	187
115°	316	316	316	316	316	313
125°	456	462	456	462	456	408
135°	598	599	598	599	598	460
145°	727	727	727	727	727	454
155°	831	832	831	832	831	382
165°	903	906	903	906	903	255
175°	939	943	939	943	939	89
180°	945	945	945	945	945	



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1146.7	1145.9	1143.8	1145.5	1142.1	1137.5	1137.1	1132.9	1120.7	1119.9	1116.6
5°	1283.7	1279.5	1279.0	1278.4	1271.1	1261.2	1242.3	1240.7	1215.6	1203.0	1187.9
7.5°	1461.0	1463.2	1455.6	1448.9	1426.5	1411.7	1391.5	1365.6	1334.8	1303.5	1282.6
10°	1588.4	1605.6	1584.2	1569.5	1555.9	1530.2	1500.4	1463.2	1426.1	1382.6	1349.6
12.5°	1724.9	1733.4	1729.1	1715.3	1694.1	1655.1	1602.2	1561.2	1527.0	1454.6	1425.4
15°	1910.8	1942.8	1922.4	1875.2	1876.3	1839.1	1770.0	1694.1	1653.8	1590.4	1504.1
17.5°	2108.9	2112.9	2104.2	2065.0	2038.8	1987.7	1923.9	1851.2	1769.5	1692.8	1601.2
20°	2214.5	2211.3	2193.0	2172.6	2127.6	2087.8	2018.2	1937.0	1832.3	1756.9	1656.9
22.5°	2273.1	2267.9	2259.2	2242.1	2204.6	2161.9	2099.4	2010.7	1911.1	1807.2	1691.7
25°	2267.9	2274.7	2275.7	2271.0	2257.9	2232.3	2183.1	2112.4	2012.9	1879.4	1759.0
27.5°	2062.7	2072.3	2100.3	2125.1	2152.8	2181.1	2177.3	2142.2	2068.6	1953.4	1806.1
30°	1857.4	1836.5	1888.3	1953.8	1998.3	2076.8	2120.8	2123.4	2082.0	1983.1	1839.6
32.5°	1572.6	1595.7	1618.6	1699.1	1796.4	1884.6	1972.1	2042.6	2050.6	1984.8	1859.3
35°	1221.9	1250.7	1292.6	1334.4	1439.2	1529.2	1683.1	1817.1	1923.9	1938.1	1861.1
37.5°	984.6	998.9	1025.4	1067.3	1135.8	1242.6	1361.7	1531.1	1685.8	1800.9	1805.9
40°	860.7	864.9	894.7	926.6	982.1	1070.1	1177.4	1327.1	1512.4	1673.2	1740.2
42.5°	767.7	776.9	789.6	820.2	864.4	930.6	1030.4	1154.1	1324.0	1509.0	1640.1
45°	659.6	670.1	678.0	698.4	729.8	774.3	843.9	957.0	1086.3	1277.4	1453.8
47.5°	588.2	589.1	594.9	610.3	631.7	665.1	714.3	787.0	905.7	1060.6	1241.8
50°	537.1	545.5	547.6	559.6	576.4	601.0	641.8	703.6	801.0	937.1	1103.6
52.5°	501.1	503.6	509.5	518.2	532.8	552.0	587.4	635.8	712.2	828.2	981.3
55°	448.1	448.1	453.9	460.7	469.1	486.3	509.9	545.5	603.6	693.7	820.4
57.5°	399.1	401.7	405.8	407.9	415.0	426.5	446.1	473.2	516.5	585.8	686.5
60°	366.5	371.2	370.7	374.8	381.1	390.0	406.8	428.8	467.5	523.0	607.8
62.5°	338.0	337.7	337.6	342.6	348.9	357.4	368.2	387.3	420.2	469.4	541.6
65°	291.1	290.0	293.7	296.8	298.9	305.2	313.6	330.3	352.3	389.0	445.0
67.5°	249.4	246.4	248.4	249.4	253.0	257.9	265.7	276.1	293.6	323.0	365.2
70°	220.9	218.3	217.8	218.8	222.0	225.6	231.4	241.3	257.6	281.1	312.0
72.5°	191.6	189.8	189.7	192.0	193.5	195.9	200.0	209.1	222.0	239.7	268.5
75°	149.7	149.7	149.7	150.2	151.8	153.9	157.1	161.8	171.7	184.3	203.6
77.5°	112.2	112.1	111.5	111.4	113.7	114.7	115.4	119.8	125.3	133.8	147.9
80°	88.0	85.3	86.4	88.0	89.0	89.5	91.1	92.1	96.9	101.6	111.5
82.5°	65.3	63.1	63.3	65.8	66.0	66.5	68.1	69.5	71.3	75.6	80.9
85°	34.6	34.6	35.1	35.1	35.6	35.1	36.6	37.2	37.2	39.8	42.9
87.5°	17.0	16.1	16.5	16.8	16.3	16.7	16.9	17.2	17.5	17.8	17.8
90°	22.3	21.9	21.6	21.3	20.9	20.5	19.8	19.1	18.5	17.8	15.7
92.5°	30.0	30.2	30.4	30.6	30.8	30.6	30.1	29.6	29.0	28.5	27.3
95°	57.9	57.9	57.9	57.9	57.9	57.6	56.9	56.2	55.6	54.9	53.6
97.5°	89.1	89.1	89.2	89.3	89.3	89.0	88.2	87.5	86.7	86.0	85.0
100°	112.8	112.5	112.2	111.8	111.5	111.1	110.6	110.1	109.6	109.1	108.3
102.5°	137.2	137.2	137.3	137.4	137.4	137.2	136.7	136.2	135.7	135.2	134.1
105°	176.7	176.3	176.0	175.7	175.3	175.2	175.2	175.2	175.2	175.2	173.7
107.5°	217.8	218.0	218.2	218.4	218.6	218.4	217.9	217.3	216.8	216.3	215.7
110°	245.7	246.0	246.3	246.7	247.0	246.8	246.2	245.5	244.9	244.2	243.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.4	275.4	275.5	275.6	275.6	275.3	274.5	273.7	272.9	272.1	272.0
115°	316.2	316.4	316.5	316.7	316.9	316.9	316.7	316.5	316.4	316.2	316.5
117.5°	357.6	358.1	358.5	359.0	359.5	359.7	359.7	359.8	359.8	359.8	360.3
120°	386.7	387.0	387.4	387.7	388.0	388.3	388.4	388.6	388.8	388.9	389.8
122.5°	414.6	415.1	415.5	416.0	416.5	416.9	417.3	417.8	418.2	418.6	419.1
125°	456.5	457.1	457.8	458.5	459.1	459.8	460.4	461.1	461.8	462.4	462.7
127.5°	498.2	499.0	499.7	500.5	501.2	502.1	503.0	503.9	504.8	505.8	506.1
130°	525.5	526.7	527.8	529.0	530.1	531.0	531.7	532.4	533.0	533.7	534.2
132.5°	554.0	554.9	555.8	556.7	557.6	558.4	559.2	560.0	560.8	561.6	561.9
135°	598.2	598.6	598.9	599.2	599.6	600.1	600.7	601.4	602.0	602.7	602.9
137.5°	637.3	637.9	638.5	639.2	639.8	640.5	641.1	641.8	642.5	643.2	642.8
140°	662.8	664.0	665.1	666.3	667.4	668.1	668.3	668.4	668.6	668.8	668.6
142.5°	688.9	689.8	690.7	691.6	692.5	693.0	693.2	693.4	693.5	693.7	693.4
145°	726.7	727.3	728.0	728.6	729.3	729.7	729.9	730.0	730.2	730.4	729.9
147.5°	760.2	761.2	762.2	763.2	764.2	764.7	764.7	764.7	764.7	764.7	764.2
150°	781.6	782.6	783.6	784.5	785.5	786.0	786.0	786.0	786.0	786.0	785.7
152.5°	802.4	803.2	804.1	804.9	805.8	806.1	805.8	805.6	805.3	805.0	804.8
155°	830.6	831.7	832.9	834.0	835.2	835.4	834.8	834.1	833.5	832.8	832.6
157.5°	856.2	857.2	858.1	859.0	859.9	860.1	859.4	858.7	858.0	857.3	857.2
160°	872.9	873.5	874.2	874.9	875.5	875.4	874.6	873.8	873.0	872.1	872.1
162.5°	885.3	886.4	887.5	888.5	889.6	889.7	888.9	888.0	887.2	886.4	886.3
165°	903.3	904.5	905.6	906.8	907.9	908.0	907.0	906.0	905.0	904.0	904.0
167.5°	918.6	919.6	920.6	921.7	922.7	922.7	921.7	920.6	919.6	918.6	918.5
170°	926.3	927.5	928.6	929.8	930.9	930.9	929.8	928.6	927.5	926.3	926.3
172.5°	932.3	933.4	934.6	935.7	936.9	936.9	935.9	934.9	933.9	932.8	932.8
175°	938.9	940.1	941.2	942.4	943.6	943.6	942.6	941.7	940.7	939.7	939.7
177.5°	942.5	943.4	944.3	945.3	946.2	946.3	945.5	944.7	943.9	943.1	943.1
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1114.0	1110.7	1107.3	1101.5	1096.5	1089.3	1087.2	1084.7	1077.2	1070.5	1065.5
5°	1182.1	1169.5	1151.2	1134.5	1120.9	1102.5	1092.1	1081.1	1065.4	1051.2	1039.7
7.5°	1253.3	1228.6	1200.1	1169.3	1140.6	1113.0	1090.7	1070.8	1048.8	1028.0	1011.8
10°	1309.8	1274.2	1234.5	1191.5	1154.9	1119.3	1089.4	1063.3	1035.0	1010.4	990.0
12.5°	1374.3	1321.6	1266.7	1214.6	1171.2	1121.8	1085.7	1052.4	1020.3	990.7	967.8
15°	1450.7	1383.7	1318.7	1247.0	1181.1	1119.3	1076.4	1034.5	997.3	966.9	937.6
17.5°	1520.2	1444.3	1358.7	1271.5	1191.9	1118.7	1058.6	1011.2	964.7	927.6	898.4
20°	1559.6	1473.2	1376.3	1285.8	1197.8	1116.1	1050.2	993.6	943.4	904.1	871.1
22.5°	1593.5	1492.4	1392.2	1295.4	1197.4	1109.4	1034.7	976.5	922.0	883.6	848.5
25°	1628.7	1507.7	1407.2	1293.6	1184.2	1093.1	1009.3	943.4	888.9	843.9	807.8
27.5°	1658.8	1506.7	1387.4	1265.2	1163.5	1072.2	982.7	912.0	854.2	805.3	768.6
30°	1678.9	1508.8	1366.9	1246.0	1143.4	1049.1	962.2	891.0	830.3	780.6	746.0
32.5°	1691.5	1507.5	1348.1	1219.2	1111.5	1028.2	940.0	866.3	803.9	755.0	721.7
35°	1698.8	1498.3	1315.6	1163.8	1060.1	979.0	905.2	828.7	763.3	717.7	680.1
37.5°	1684.2	1478.9	1277.9	1110.4	996.9	917.0	854.9	789.8	727.2	677.0	644.6
40°	1661.1	1466.4	1248.6	1072.7	953.3	876.4	823.5	759.6	697.8	650.2	619.8
42.5°	1617.1	1440.8	1216.3	1030.8	908.1	831.1	782.5	729.1	670.6	625.9	595.6
45°	1509.8	1385.2	1168.0	968.0	841.3	761.7	718.8	680.1	627.2	583.7	557.5
47.5°	1360.9	1301.6	1098.0	901.7	771.6	695.0	650.4	619.2	580.6	545.5	520.4
50°	1257.5	1232.9	1050.7	856.5	725.1	650.2	607.3	579.0	551.3	516.2	493.2
52.5°	1138.1	1153.3	995.4	809.6	677.7	604.1	563.7	541.3	516.1	487.3	467.2
55°	970.1	1025.0	899.9	730.8	607.3	537.1	498.9	479.0	464.4	442.9	425.6
57.5°	812.7	882.7	796.7	649.7	538.1	477.6	440.9	419.2	409.8	398.6	385.0
60°	719.3	788.4	723.0	595.2	491.6	434.0	401.5	383.2	373.8	365.9	354.4
62.5°	636.0	705.9	650.9	540.0	445.9	392.5	364.3	346.4	339.0	334.9	325.1
65°	521.4	581.6	545.0	453.9	380.6	333.5	307.8	295.3	288.5	286.9	280.6
67.5°	424.4	470.2	443.5	376.5	318.8	278.1	256.3	245.6	240.4	239.9	235.2
70°	360.7	403.6	383.2	322.5	272.8	240.8	222.0	212.5	209.4	208.9	206.3
72.5°	311.3	341.2	325.0	274.3	235.9	206.9	193.1	183.2	179.7	180.4	178.6
75°	230.3	252.9	243.4	208.4	177.5	158.6	147.1	140.8	137.7	139.3	137.2
77.5°	165.7	180.0	171.5	147.2	128.2	114.5	106.1	102.2	99.4	99.3	98.3
80°	125.1	133.5	128.8	114.1	98.4	86.9	80.1	77.5	75.9	75.4	74.9
82.5°	89.1	96.2	90.7	80.6	69.9	63.0	59.2	55.7	54.6	54.9	54.3
85°	45.0	47.6	45.5	39.3	35.1	31.9	29.8	28.3	27.2	27.7	26.7
87.5°	18.2	18.2	16.5	14.5	13.3	11.7	11.4	10.2	9.7	10.0	9.9
90°	13.5	11.4	9.2	7.3	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	26.1	24.8	23.6	22.4	21.3	20.2	19.1	18.0	19.1	20.2	21.3
95°	52.3	51.0	49.6	48.4	47.3	46.1	44.9	43.8	44.9	46.1	47.3
97.5°	84.0	83.1	82.1	81.2	80.4	79.5	78.6	77.8	78.6	79.5	80.4
100°	107.5	106.6	105.8	104.9	103.9	102.9	101.9	100.9	101.9	102.9	103.9
102.5°	133.1	132.0	130.9	130.0	129.4	128.9	128.3	127.7	128.3	128.9	129.4
105°	172.2	170.7	169.2	168.3	168.0	167.7	167.3	167.0	167.3	167.7	168.0
107.5°	215.1	214.5	213.9	213.5	213.3	213.1	212.9	212.7	212.9	213.1	213.3
110°	243.5	243.2	242.9	242.5	242.2	241.9	241.6	241.2	241.6	241.9	242.2





TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	271.9	271.8	271.7	271.5	271.3	271.1	270.9	271.1	271.3	271.5
115°	316.9	317.2	317.5	317.4	316.9	316.4	315.9	315.5	315.9	316.4	316.9
117.5°	360.7	361.1	361.6	361.6	361.3	360.9	360.6	360.3	360.6	360.9	361.3
120°	390.6	391.4	392.2	392.2	391.2	390.2	389.2	388.2	389.2	390.2	391.2
122.5°	419.5	419.9	420.3	420.2	419.5	418.7	418.0	417.3	418.0	418.7	419.5
125°	463.1	463.4	463.7	463.7	463.2	462.7	462.2	461.7	462.2	462.7	463.2
127.5°	506.5	506.9	507.2	506.9	505.8	504.8	503.7	502.6	503.7	504.8	505.8
130°	534.7	535.2	535.7	535.2	533.9	532.6	531.3	530.0	531.3	532.6	533.9
132.5°	562.3	562.7	563.0	562.6	561.2	559.9	558.6	557.3	558.6	559.9	561.2
135°	603.0	603.2	603.4	602.9	602.0	601.0	600.0	599.0	600.0	601.0	602.0
137.5°	642.4	641.9	641.5	640.9	640.1	639.2	638.4	637.6	638.4	639.2	640.1
140°	668.4	668.3	668.1	667.6	666.8	666.0	665.1	664.3	665.1	666.0	666.8
142.5°	693.1	692.8	692.5	691.9	691.1	690.3	689.5	688.7	689.5	690.3	691.1
145°	729.4	728.9	728.4	728.0	727.6	727.3	727.0	726.7	727.0	727.3	727.6
147.5°	763.7	763.3	762.8	762.3	761.7	761.1	760.5	759.9	760.5	761.1	761.7
150°	785.4	785.0	784.7	784.4	784.1	783.7	783.4	783.1	783.4	783.7	784.1
152.5°	804.6	804.4	804.2	803.9	803.5	803.0	802.5	802.1	802.5	803.0	803.5
155°	832.5	832.3	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
157.5°	857.0	856.9	856.8	856.8	857.0	857.2	857.4	857.6	857.4	857.2	857.0
160°	872.1	872.1	872.1	872.3	872.6	873.0	873.3	873.6	873.3	873.0	872.6
162.5°	886.1	886.0	885.9	886.0	886.5	886.9	887.4	887.9	887.4	886.9	886.5
165°	904.0	904.0	904.0	904.3	904.8	905.3	905.8	906.3	905.8	905.3	904.8
167.5°	918.3	918.2	918.1	918.3	919.0	919.7	920.3	921.0	920.3	919.7	919.0
170°	926.3	926.3	926.3	926.6	927.3	928.0	928.6	929.3	928.6	928.0	927.3
172.5°	932.8	932.8	932.8	933.2	933.8	934.5	935.2	935.8	935.2	934.5	933.8
175°	939.7	939.7	939.7	940.0	940.7	941.3	942.0	942.6	942.0	941.3	940.7
177.5°	943.1	943.1	943.1	943.4	943.9	944.4	944.9	945.5	944.9	944.4	943.9
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1062.5	1059.6	1055.4	1049.1	1044.1	1036.1	1036.1	1037.4	1037.4	1037.0	1036.1
5°	1030.3	1022.4	1013.0	1002.0	990.5	979.0	976.9	972.7	969.6	967.5	964.8
7.5°	996.3	982.3	968.6	953.2	939.2	927.6	919.5	912.8	908.5	903.9	900.6
10°	973.2	955.9	939.7	923.5	905.7	891.6	882.7	876.4	871.7	867.5	865.4
12.5°	946.0	926.2	908.3	892.9	873.4	858.9	850.4	847.5	841.9	833.1	828.5
15°	906.2	887.9	866.4	842.9	833.4	815.6	805.7	801.0	797.8	791.0	788.9
17.5°	872.2	848.2	824.1	806.5	789.0	774.6	769.0	763.2	759.0	753.4	751.8
20°	845.0	823.5	801.5	782.7	764.3	748.6	743.9	739.7	735.5	732.9	730.8
22.5°	817.3	795.9	777.6	760.0	740.5	730.2	725.1	720.5	717.5	715.8	713.7
25°	778.5	759.6	739.2	723.5	707.8	701.0	697.8	695.2	693.1	690.5	690.0
27.5°	743.7	723.2	706.6	692.0	680.7	675.0	672.0	670.7	671.2	672.1	672.7
30°	717.7	698.9	685.3	672.7	662.3	657.0	656.5	656.5	658.6	659.1	660.2
32.5°	693.9	678.4	664.8	652.6	644.7	641.1	643.1	643.1	644.8	646.1	648.0
35°	659.1	645.5	635.0	624.6	617.8	619.3	620.4	621.4	624.0	627.2	629.3
37.5°	625.9	614.1	603.2	595.0	591.9	594.7	597.2	599.4	602.5	604.9	607.0
40°	602.0	593.1	582.7	575.3	576.4	578.0	580.1	582.7	585.3	586.9	589.0
42.5°	579.8	570.5	562.6	556.5	558.0	560.0	561.2	562.6	565.6	568.4	569.7
45°	546.0	538.7	531.4	527.7	528.8	529.8	530.8	532.4	535.0	537.1	537.7
47.5°	508.0	502.9	498.0	494.4	496.1	495.7	497.0	500.4	501.2	502.5	505.4
50°	483.7	479.0	473.3	472.2	472.2	472.2	472.7	476.9	476.9	479.0	481.1
52.5°	456.9	453.9	450.2	448.3	447.5	447.5	449.7	451.8	452.6	455.6	457.7
55°	417.2	414.1	411.0	409.4	408.3	409.4	413.6	414.6	417.2	418.8	420.4
57.5°	375.9	373.5	371.0	370.1	369.9	371.3	373.6	376.7	377.4	382.2	384.6
60°	348.7	345.0	342.9	342.9	341.9	346.6	345.5	350.8	351.8	354.9	358.6
62.5°	320.6	315.7	314.8	314.8	316.3	317.7	319.1	321.4	324.2	328.1	331.0
65°	275.4	272.8	276.4	275.9	274.8	278.0	278.0	280.6	283.7	287.4	293.2
67.5°	232.5	231.2	231.5	231.5	233.1	234.9	236.3	238.6	242.4	246.3	250.0
70°	203.6	205.2	202.6	204.7	206.3	206.8	207.8	211.0	215.2	217.8	222.0
72.5°	175.6	175.5	175.8	176.6	178.2	179.1	180.2	183.8	188.4	190.6	193.9
75°	135.1	134.5	136.1	136.1	138.7	139.8	140.8	142.4	146.6	149.7	152.3
77.5°	98.6	99.3	98.9	100.7	100.0	100.2	103.4	105.0	105.4	111.6	113.0
80°	74.3	75.4	75.9	76.4	77.0	75.9	79.6	81.1	81.1	84.8	87.4
82.5°	53.4	54.0	55.4	55.9	56.0	57.1	57.4	58.5	59.8	61.4	64.8
85°	26.7	28.3	28.8	28.3	28.8	27.7	29.3	29.8	30.4	30.4	30.4
87.5°	9.8	10.6	10.7	11.5	11.5	12.4	12.5	11.8	11.9	13.3	11.7
90°	7.3	9.2	11.4	13.5	15.7	17.8	18.5	19.1	19.8	20.5	20.9
92.5°	22.4	23.6	24.8	26.1	27.3	28.5	29.0	29.6	30.1	30.6	30.8
95°	48.4	49.6	51.0	52.3	53.6	54.9	55.6	56.2	56.9	57.6	57.9
97.5°	81.2	82.1	83.1	84.0	85.0	86.0	86.7	87.5	88.2	89.0	89.3
100°	104.9	105.8	106.6	107.5	108.3	109.1	109.6	110.1	110.6	111.1	111.5
102.5°	130.0	130.9	132.0	133.1	134.1	135.2	135.7	136.2	136.7	137.2	137.4
105°	168.3	169.2	170.7	172.2	173.7	175.2	175.2	175.2	175.2	175.2	175.3
107.5°	213.5	213.9	214.5	215.1	215.7	216.3	216.8	217.3	217.9	218.4	218.6
110°	242.5	242.9	243.2	243.5	243.9	244.2	244.9	245.5	246.2	246.8	247.0



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	271.7	271.8	271.9	272.0	272.0	272.1	272.9	273.7	274.5	275.3	275.6
115°	317.4	317.5	317.2	316.9	316.5	316.2	316.4	316.5	316.7	316.9	316.9
117.5°	361.6	361.6	361.1	360.7	360.3	359.8	359.8	359.8	359.7	359.7	359.5
120°	392.2	392.2	391.4	390.6	389.8	388.9	388.8	388.6	388.4	388.3	388.0
122.5°	420.2	420.3	419.9	419.5	419.1	418.6	418.2	417.8	417.3	416.9	416.5
125°	463.7	463.7	463.4	463.1	462.7	462.4	461.8	461.1	460.4	459.8	459.1
127.5°	506.9	507.2	506.9	506.5	506.1	505.8	504.8	503.9	503.0	502.1	501.2
130°	535.2	535.7	535.2	534.7	534.2	533.7	533.0	532.4	531.7	531.0	530.1
132.5°	562.6	563.0	562.7	562.3	561.9	561.6	560.8	560.0	559.2	558.4	557.6
135°	602.9	603.4	603.2	603.0	602.9	602.7	602.0	601.4	600.7	600.1	599.6
137.5°	640.9	641.5	641.9	642.4	642.8	643.2	642.5	641.8	641.1	640.5	639.8
140°	667.6	668.1	668.3	668.4	668.6	668.8	668.6	668.4	668.3	668.1	667.4
142.5°	691.9	692.5	692.8	693.1	693.4	693.7	693.5	693.4	693.2	693.0	692.5
145°	728.0	728.4	728.9	729.4	729.9	730.4	730.2	730.0	729.9	729.7	729.3
147.5°	762.3	762.8	763.3	763.7	764.2	764.7	764.7	764.7	764.7	764.7	764.2
150°	784.4	784.7	785.0	785.4	785.7	786.0	786.0	786.0	786.0	786.0	785.5
152.5°	803.9	804.2	804.4	804.6	804.8	805.0	805.3	805.6	805.8	806.1	805.8
155°	832.1	832.1	832.3	832.5	832.6	832.8	833.5	834.1	834.8	835.4	835.2
157.5°	856.8	856.8	856.9	857.0	857.2	857.3	858.0	858.7	859.4	860.1	859.9
160°	872.3	872.1	872.1	872.1	872.1	872.1	873.0	873.8	874.6	875.4	875.5
162.5°	886.0	885.9	886.0	886.1	886.3	886.4	887.2	888.0	888.9	889.7	889.6
165°	904.3	904.0	904.0	904.0	904.0	904.0	905.0	906.0	907.0	908.0	907.9
167.5°	918.3	918.1	918.2	918.3	918.5	918.6	919.6	920.6	921.7	922.7	922.7
170°	926.6	926.3	926.3	926.3	926.3	926.3	927.5	928.6	929.8	930.9	930.9
172.5°	933.2	932.8	932.8	932.8	932.8	932.8	933.9	934.9	935.9	936.9	936.9
175°	940.0	939.7	939.7	939.7	939.7	939.7	940.7	941.7	942.6	943.6	943.6
177.5°	943.4	943.1	943.1	943.1	943.1	943.1	943.9	944.7	945.5	946.3	946.2
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1033.2	1032.8	1035.7	1033.6	1035.7	1032.8	1033.2	1036.1	1037.0	1037.4	1037.4
5°	961.7	963.3	958.0	958.0	958.0	963.3	961.7	964.8	967.5	969.6	972.7
7.5°	898.0	895.7	895.9	893.1	895.9	895.7	898.0	900.6	903.9	908.5	912.8
10°	859.1	856.0	854.9	855.4	854.9	856.0	859.1	865.4	867.5	871.7	876.4
12.5°	826.8	826.2	819.3	819.4	819.3	826.2	826.8	828.5	833.1	841.9	847.5
15°	788.9	779.0	777.9	781.1	777.9	779.0	788.9	788.9	791.0	797.8	801.0
17.5°	750.9	745.7	746.0	744.4	746.0	745.7	750.9	751.8	753.4	759.0	763.2
20°	730.8	727.7	727.2	723.5	727.2	727.7	730.8	730.8	732.9	735.5	739.7
22.5°	712.4	711.4	711.7	707.6	711.7	711.4	712.4	713.7	715.8	717.5	720.5
25°	689.5	692.1	690.0	690.0	690.0	692.1	689.5	690.0	690.5	693.1	695.2
27.5°	674.0	673.9	672.8	672.8	672.8	673.9	674.0	672.7	672.1	671.2	670.7
30°	662.3	661.7	662.8	662.8	662.8	661.7	662.3	660.2	659.1	658.6	656.5
32.5°	650.5	651.3	651.5	651.9	651.5	651.3	650.5	648.0	646.1	644.8	643.1
35°	632.4	632.9	634.5	633.5	634.5	632.9	632.4	629.3	627.2	624.0	621.4
37.5°	607.9	610.3	609.8	610.6	609.8	610.3	607.9	607.0	604.9	602.5	599.4
40°	589.5	591.1	590.5	590.5	590.5	591.1	589.5	589.0	586.9	585.3	582.7
42.5°	570.6	571.8	570.4	569.6	570.4	571.8	570.6	569.7	568.4	565.6	562.6
45°	539.7	538.7	540.3	538.2	540.3	538.7	539.7	537.7	537.1	535.0	532.4
47.5°	505.2	506.2	506.7	508.2	506.7	506.2	505.2	505.4	502.5	501.2	500.4
50°	482.2	485.3	485.3	484.8	485.3	485.3	482.2	481.1	479.0	476.9	476.9
52.5°	459.5	461.0	463.1	463.0	463.1	461.0	459.5	457.7	455.6	452.6	451.8
55°	424.6	425.6	426.7	427.2	426.7	425.6	424.6	420.4	418.8	417.2	414.6
57.5°	388.3	387.9	390.4	391.2	390.4	387.9	388.3	384.6	382.2	377.4	376.7
60°	362.8	362.8	367.0	368.6	367.0	362.8	362.8	358.6	354.9	351.8	350.8
62.5°	335.6	337.3	341.4	339.2	341.4	337.3	335.6	331.0	328.1	324.2	321.4
65°	295.8	300.0	299.5	301.5	299.5	300.0	295.8	293.2	287.4	283.7	280.6
67.5°	254.2	256.8	260.6	260.9	260.6	256.8	254.2	250.0	246.3	242.4	238.6
70°	226.2	228.8	230.9	232.4	230.9	228.8	226.2	222.0	217.8	215.2	211.0
72.5°	198.9	200.3	205.3	203.1	205.3	200.3	198.9	193.9	190.6	188.4	183.8
75°	156.0	159.7	162.8	161.2	162.8	159.7	156.0	152.3	149.7	146.6	142.4
77.5°	115.4	119.0	120.5	119.2	120.5	119.0	115.4	113.0	111.6	105.4	105.0
80°	91.1	90.6	93.7	93.2	93.7	90.6	91.1	87.4	84.8	81.1	81.1
82.5°	66.8	66.3	67.7	68.1	67.7	66.3	66.8	64.8	61.4	59.8	58.5
85°	32.5	34.0	31.9	31.4	31.9	34.0	32.5	30.4	30.4	30.4	29.8
87.5°	11.8	11.9	11.5	11.2	11.5	11.9	11.8	11.7	13.3	11.9	11.8
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.5	19.8	19.1
92.5°	30.6	30.4	30.2	30.0	30.2	30.4	30.6	30.8	30.6	30.1	29.6
95°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.6	56.9	56.2
97.5°	89.3	89.2	89.1	89.1	89.1	89.2	89.3	89.3	89.0	88.2	87.5
100°	111.8	112.2	112.5	112.8	112.5	112.2	111.8	111.5	111.1	110.6	110.1
102.5°	137.4	137.3	137.2	137.2	137.2	137.3	137.4	137.4	137.2	136.7	136.2
105°	175.7	176.0	176.3	176.7	176.3	176.0	175.7	175.3	175.2	175.2	175.2
107.5°	218.4	218.2	218.0	217.8	218.0	218.2	218.4	218.6	218.4	217.9	217.3
110°	246.7	246.3	246.0	245.7	246.0	246.3	246.7	247.0	246.8	246.2	245.5



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	275.6	275.5	275.4	275.4	275.4	275.5	275.6	275.6	275.3	274.5	273.7
115°	316.7	316.5	316.4	316.2	316.4	316.5	316.7	316.9	316.9	316.7	316.5
117.5°	359.0	358.5	358.1	357.6	358.1	358.5	359.0	359.5	359.7	359.7	359.8
120°	387.7	387.4	387.0	386.7	387.0	387.4	387.7	388.0	388.3	388.4	388.6
122.5°	416.0	415.5	415.1	414.6	415.1	415.5	416.0	416.5	416.9	417.3	417.8
125°	458.5	457.8	457.1	456.5	457.1	457.8	458.5	459.1	459.8	460.4	461.1
127.5°	500.5	499.7	499.0	498.2	499.0	499.7	500.5	501.2	502.1	503.0	503.9
130°	529.0	527.8	526.7	525.5	526.7	527.8	529.0	530.1	531.0	531.7	532.4
132.5°	556.7	555.8	554.9	554.0	554.9	555.8	556.7	557.6	558.4	559.2	560.0
135°	599.2	598.9	598.6	598.2	598.6	598.9	599.2	599.6	600.1	600.7	601.4
137.5°	639.2	638.5	637.9	637.3	637.9	638.5	639.2	639.8	640.5	641.1	641.8
140°	666.3	665.1	664.0	662.8	664.0	665.1	666.3	667.4	668.1	668.3	668.4
142.5°	691.6	690.7	689.8	688.9	689.8	690.7	691.6	692.5	693.0	693.2	693.4
145°	728.6	728.0	727.3	726.7	727.3	728.0	728.6	729.3	729.7	729.9	730.0
147.5°	763.2	762.2	761.2	760.2	761.2	762.2	763.2	764.2	764.7	764.7	764.7
150°	784.5	783.6	782.6	781.6	782.6	783.6	784.5	785.5	786.0	786.0	786.0
152.5°	804.9	804.1	803.2	802.4	803.2	804.1	804.9	805.8	806.1	805.8	805.6
155°	834.0	832.9	831.7	830.6	831.7	832.9	834.0	835.2	835.4	834.8	834.1
157.5°	859.0	858.1	857.2	856.2	857.2	858.1	859.0	859.9	860.1	859.4	858.7
160°	874.9	874.2	873.5	872.9	873.5	874.2	874.9	875.5	875.4	874.6	873.8
162.5°	888.5	887.5	886.4	885.3	886.4	887.5	888.5	889.6	889.7	888.9	888.0
165°	906.8	905.6	904.5	903.3	904.5	905.6	906.8	907.9	908.0	907.0	906.0
167.5°	921.7	920.6	919.6	918.6	919.6	920.6	921.7	922.7	922.7	921.7	920.6
170°	929.8	928.6	927.5	926.3	927.5	928.6	929.8	930.9	930.9	929.8	928.6
172.5°	935.7	934.6	933.4	932.3	933.4	934.6	935.7	936.9	936.9	935.9	934.9
175°	942.4	941.2	940.1	938.9	940.1	941.2	942.4	943.6	943.6	942.6	941.7
177.5°	945.3	944.3	943.4	942.5	943.4	944.3	945.3	946.2	946.3	945.5	944.7
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1036.1	1036.1	1044.1	1049.1	1055.4	1059.6	1062.5	1065.5	1070.5	1077.2	1084.7
5°	976.9	979.0	990.5	1002.0	1013.0	1022.4	1030.3	1039.7	1051.2	1065.4	1081.1
7.5°	919.5	927.6	939.2	953.2	968.6	982.3	996.3	1011.8	1028.0	1048.8	1070.8
10°	882.7	891.6	905.7	923.5	939.7	955.9	973.2	990.0	1010.4	1035.0	1063.3
12.5°	850.4	858.9	873.4	892.9	908.3	926.2	946.0	967.8	990.7	1020.3	1052.4
15°	805.7	815.6	833.4	842.9	866.4	887.9	906.2	937.6	966.9	997.3	1034.5
17.5°	769.0	774.6	789.0	806.5	824.1	848.2	872.2	898.4	927.6	964.7	1011.2
20°	743.9	748.6	764.3	782.7	801.5	823.5	845.0	871.1	904.1	943.4	993.6
22.5°	725.1	730.2	740.5	760.0	777.6	795.9	817.3	848.5	883.6	922.0	976.5
25°	697.8	701.0	707.8	723.5	739.2	759.6	778.5	807.8	843.9	888.9	943.4
27.5°	672.0	675.0	680.7	692.0	706.6	723.2	743.7	768.6	805.3	854.2	912.0
30°	656.5	657.0	662.3	672.7	685.3	698.9	717.7	746.0	780.6	830.3	891.0
32.5°	643.1	641.1	644.7	652.6	664.8	678.4	693.9	721.7	755.0	803.9	866.3
35°	620.4	619.3	617.8	624.6	635.0	645.5	659.1	680.1	717.7	763.3	828.7
37.5°	597.2	594.7	591.9	595.0	603.2	614.1	625.9	644.6	677.0	727.2	789.8
40°	580.1	578.0	576.4	575.3	582.7	593.1	602.0	619.8	650.2	697.8	759.6
42.5°	561.2	560.0	558.0	556.5	562.6	570.5	579.8	595.6	625.9	670.6	729.1
45°	530.8	529.8	528.8	527.7	531.4	538.7	546.0	557.5	583.7	627.2	680.1
47.5°	497.0	495.7	496.1	494.4	498.0	502.9	508.0	520.4	545.5	580.6	619.2
50°	472.7	472.2	472.2	472.2	473.3	479.0	483.7	493.2	516.2	551.3	579.0
52.5°	449.7	447.5	447.5	448.3	450.2	453.9	456.9	467.2	487.3	516.1	541.3
55°	413.6	409.4	408.3	409.4	411.0	414.1	417.2	425.6	442.9	464.4	479.0
57.5°	373.6	371.3	369.9	370.1	371.0	373.5	375.9	385.0	398.6	409.8	419.2
60°	345.5	346.6	341.9	342.9	342.9	345.0	348.7	354.4	365.9	373.8	383.2
62.5°	319.1	317.7	316.3	314.8	314.8	315.7	320.6	325.1	334.9	339.0	346.4
65°	278.0	278.0	274.8	275.9	276.4	272.8	275.4	280.6	286.9	288.5	295.3
67.5°	236.3	234.9	233.1	231.5	231.5	231.2	232.5	235.2	239.9	240.4	245.6
70°	207.8	206.8	206.3	204.7	202.6	205.2	203.6	206.3	208.9	209.4	212.5
72.5°	180.2	179.1	178.2	176.6	175.8	175.5	175.6	178.6	180.4	179.7	183.2
75°	140.8	139.8	138.7	136.1	136.1	134.5	135.1	137.2	139.3	137.7	140.8
77.5°	103.4	100.2	100.0	100.7	98.9	99.3	98.6	98.3	99.3	99.4	102.2
80°	79.6	75.9	77.0	76.4	75.9	75.4	74.3	74.9	75.4	75.9	77.5
82.5°	57.4	57.1	56.0	55.9	55.4	54.0	53.4	54.3	54.9	54.6	55.7
85°	29.3	27.7	28.8	28.3	28.8	28.3	26.7	26.7	27.7	27.2	28.3
87.5°	12.5	12.4	11.5	11.5	10.7	10.6	9.8	9.9	10.0	9.7	10.2
90°	18.5	17.8	15.7	13.5	11.4	9.2	7.3	5.7	4.0	2.4	0.7
92.5°	29.0	28.5	27.3	26.1	24.8	23.6	22.4	21.3	20.2	19.1	18.0
95°	55.6	54.9	53.6	52.3	51.0	49.6	48.4	47.3	46.1	44.9	43.8
97.5°	86.7	86.0	85.0	84.0	83.1	82.1	81.2	80.4	79.5	78.6	77.8
100°	109.6	109.1	108.3	107.5	106.6	105.8	104.9	103.9	102.9	101.9	100.9
102.5°	135.7	135.2	134.1	133.1	132.0	130.9	130.0	129.4	128.9	128.3	127.7
105°	175.2	175.2	173.7	172.2	170.7	169.2	168.3	168.0	167.7	167.3	167.0
107.5°	216.8	216.3	215.7	215.1	214.5	213.9	213.5	213.3	213.1	212.9	212.7
110°	244.9	244.2	243.9	243.5	243.2	242.9	242.5	242.2	241.9	241.6	241.2



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.9	272.1	272.0	272.0	271.9	271.8	271.7	271.5	271.3	271.1	270.9
115°	316.4	316.2	316.5	316.9	317.2	317.5	317.4	316.9	316.4	315.9	315.5
117.5°	359.8	359.8	360.3	360.7	361.1	361.6	361.6	361.3	360.9	360.6	360.3
120°	388.8	388.9	389.8	390.6	391.4	392.2	392.2	391.2	390.2	389.2	388.2
122.5°	418.2	418.6	419.1	419.5	419.9	420.3	420.2	419.5	418.7	418.0	417.3
125°	461.8	462.4	462.7	463.1	463.4	463.7	463.7	463.2	462.7	462.2	461.7
127.5°	504.8	505.8	506.1	506.5	506.9	507.2	506.9	505.8	504.8	503.7	502.6
130°	533.0	533.7	534.2	534.7	535.2	535.7	535.2	533.9	532.6	531.3	530.0
132.5°	560.8	561.6	561.9	562.3	562.7	563.0	562.6	561.2	559.9	558.6	557.3
135°	602.0	602.7	602.9	603.0	603.2	603.4	602.9	602.0	601.0	600.0	599.0
137.5°	642.5	643.2	642.8	642.4	641.9	641.5	640.9	640.1	639.2	638.4	637.6
140°	668.6	668.8	668.6	668.4	668.3	668.1	667.6	666.8	666.0	665.1	664.3
142.5°	693.5	693.7	693.4	693.1	692.8	692.5	691.9	691.1	690.3	689.5	688.7
145°	730.2	730.4	729.9	729.4	728.9	728.4	728.0	727.6	727.3	727.0	726.7
147.5°	764.7	764.7	764.2	763.7	763.3	762.8	762.3	761.7	761.1	760.5	759.9
150°	786.0	786.0	785.7	785.4	785.0	784.7	784.4	784.1	783.7	783.4	783.1
152.5°	805.3	805.0	804.8	804.6	804.4	804.2	803.9	803.5	803.0	802.5	802.1
155°	833.5	832.8	832.6	832.5	832.3	832.1	832.1	832.1	832.1	832.1	832.1
157.5°	858.0	857.3	857.2	857.0	856.9	856.8	856.8	857.0	857.2	857.4	857.6
160°	873.0	872.1	872.1	872.1	872.1	872.1	872.3	872.6	873.0	873.3	873.6
162.5°	887.2	886.4	886.3	886.1	886.0	885.9	886.0	886.5	886.9	887.4	887.9
165°	905.0	904.0	904.0	904.0	904.0	904.0	904.3	904.8	905.3	905.8	906.3
167.5°	919.6	918.6	918.5	918.3	918.2	918.1	918.3	919.0	919.7	920.3	921.0
170°	927.5	926.3	926.3	926.3	926.3	926.3	926.6	927.3	928.0	928.6	929.3
172.5°	933.9	932.8	932.8	932.8	932.8	932.8	933.2	933.8	934.5	935.2	935.8
175°	940.7	939.7	939.7	939.7	939.7	939.7	940.0	940.7	941.3	942.0	942.6
177.5°	943.9	943.1	943.1	943.1	943.1	943.1	943.4	943.9	944.4	944.9	945.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1087.2	1089.3	1096.5	1101.5	1107.3	1110.7	1114.0	1116.6	1119.9	1120.7	1132.9
5°	1092.1	1102.5	1120.9	1134.5	1151.2	1169.5	1182.1	1187.9	1203.0	1215.6	1240.7
7.5°	1090.7	1113.0	1140.6	1169.3	1200.1	1228.6	1253.3	1282.6	1303.5	1334.8	1365.6
10°	1089.4	1119.3	1154.9	1191.5	1234.5	1274.2	1309.8	1349.6	1382.6	1426.1	1463.2
12.5°	1085.7	1121.8	1171.2	1214.6	1266.7	1321.6	1374.3	1425.4	1454.6	1527.0	1561.2
15°	1076.4	1119.3	1181.1	1247.0	1318.7	1383.7	1450.7	1504.1	1590.4	1653.8	1694.1
17.5°	1058.6	1118.7	1191.9	1271.5	1358.7	1444.3	1520.2	1601.2	1692.8	1769.5	1851.2
20°	1050.2	1116.1	1197.8	1285.8	1376.3	1473.2	1559.6	1656.9	1756.9	1832.3	1937.0
22.5°	1034.7	1109.4	1197.4	1295.4	1392.2	1492.4	1593.5	1691.7	1807.2	1911.1	2010.7
25°	1009.3	1093.1	1184.2	1293.6	1407.2	1507.7	1628.7	1759.0	1879.4	2012.9	2112.4
27.5°	982.7	1072.2	1163.5	1265.2	1387.4	1506.7	1658.8	1806.1	1953.4	2068.6	2142.2
30°	962.2	1049.1	1143.4	1246.0	1366.9	1508.8	1678.9	1839.6	1983.1	2082.0	2123.4
32.5°	940.0	1028.2	1111.5	1219.2	1348.1	1507.5	1691.5	1859.3	1984.8	2050.6	2042.6
35°	905.2	979.0	1060.1	1163.8	1315.6	1498.3	1698.8	1861.1	1938.1	1923.9	1817.1
37.5°	854.9	917.0	996.9	1110.4	1277.9	1478.9	1684.2	1805.9	1800.9	1685.8	1531.1
40°	823.5	876.4	953.3	1072.7	1248.6	1466.4	1661.1	1740.2	1673.2	1512.4	1327.1
42.5°	782.5	831.1	908.1	1030.8	1216.3	1440.8	1617.1	1640.1	1509.0	1324.0	1154.1
45°	718.8	761.7	841.3	968.0	1168.0	1385.2	1509.8	1453.8	1277.4	1086.3	957.0
47.5°	650.4	695.0	771.6	901.7	1098.0	1301.6	1360.9	1241.8	1060.6	905.7	787.0
50°	607.3	650.2	725.1	856.5	1050.7	1232.9	1257.5	1103.6	937.1	801.0	703.6
52.5°	563.7	604.1	677.7	809.6	995.4	1153.3	1138.1	981.3	828.2	712.2	635.8
55°	498.9	537.1	607.3	730.8	899.9	1025.0	970.1	820.4	693.7	603.6	545.5
57.5°	440.9	477.6	538.1	649.7	796.7	882.7	812.7	686.5	585.8	516.5	473.2
60°	401.5	434.0	491.6	595.2	723.0	788.4	719.3	607.8	523.0	467.5	428.8
62.5°	364.3	392.5	445.9	540.0	650.9	705.9	636.0	541.6	469.4	420.2	387.3
65°	307.8	333.5	380.6	453.9	545.0	581.6	521.4	445.0	389.0	352.3	330.3
67.5°	256.3	278.1	318.8	376.5	443.5	470.2	424.4	365.2	323.0	293.6	276.1
70°	222.0	240.8	272.8	322.5	383.2	403.6	360.7	312.0	281.1	257.6	241.3
72.5°	193.1	206.9	235.9	274.3	325.0	341.2	311.3	268.5	239.7	222.0	209.1
75°	147.1	158.6	177.5	208.4	243.4	252.9	230.3	203.6	184.3	171.7	161.8
77.5°	106.1	114.5	128.2	147.2	171.5	180.0	165.7	147.9	133.8	125.3	119.8
80°	80.1	86.9	98.4	114.1	128.8	133.5	125.1	111.5	101.6	96.9	92.1
82.5°	59.2	63.0	69.9	80.6	90.7	96.2	89.1	80.9	75.6	71.3	69.5
85°	29.8	31.9	35.1	39.3	45.5	47.6	45.0	42.9	39.8	37.2	37.2
87.5°	11.4	11.7	13.3	14.5	16.5	18.2	18.2	17.8	17.8	17.5	17.2
90°	2.4	4.0	5.7	7.3	9.2	11.4	13.5	15.7	17.8	18.5	19.1
92.5°	19.1	20.2	21.3	22.4	23.6	24.8	26.1	27.3	28.5	29.0	29.6
95°	44.9	46.1	47.3	48.4	49.6	51.0	52.3	53.6	54.9	55.6	56.2
97.5°	78.6	79.5	80.4	81.2	82.1	83.1	84.0	85.0	86.0	86.7	87.5
100°	101.9	102.9	103.9	104.9	105.8	106.6	107.5	108.3	109.1	109.6	110.1
102.5°	128.3	128.9	129.4	130.0	130.9	132.0	133.1	134.1	135.2	135.7	136.2
105°	167.3	167.7	168.0	168.3	169.2	170.7	172.2	173.7	175.2	175.2	175.2
107.5°	212.9	213.1	213.3	213.5	213.9	214.5	215.1	215.7	216.3	216.8	217.3
110°	241.6	241.9	242.2	242.5	242.9	243.2	243.5	243.9	244.2	244.9	245.5





TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	271.1	271.3	271.5	271.7	271.8	271.9	272.0	272.0	272.1	272.9	273.7
115°	315.9	316.4	316.9	317.4	317.5	317.2	316.9	316.5	316.2	316.4	316.5
117.5°	360.6	360.9	361.3	361.6	361.6	361.1	360.7	360.3	359.8	359.8	359.8
120°	389.2	390.2	391.2	392.2	392.2	391.4	390.6	389.8	388.9	388.8	388.6
122.5°	418.0	418.7	419.5	420.2	420.3	419.9	419.5	419.1	418.6	418.2	417.8
125°	462.2	462.7	463.2	463.7	463.7	463.4	463.1	462.7	462.4	461.8	461.1
127.5°	503.7	504.8	505.8	506.9	507.2	506.9	506.5	506.1	505.8	504.8	503.9
130°	531.3	532.6	533.9	535.2	535.7	535.2	534.7	534.2	533.7	533.0	532.4
132.5°	558.6	559.9	561.2	562.6	563.0	562.7	562.3	561.9	561.6	560.8	560.0
135°	600.0	601.0	602.0	602.9	603.4	603.2	603.0	602.9	602.7	602.0	601.4
137.5°	638.4	639.2	640.1	640.9	641.5	641.9	642.4	642.8	643.2	642.5	641.8
140°	665.1	666.0	666.8	667.6	668.1	668.3	668.4	668.6	668.8	668.6	668.4
142.5°	689.5	690.3	691.1	691.9	692.5	692.8	693.1	693.4	693.7	693.5	693.4
145°	727.0	727.3	727.6	728.0	728.4	728.9	729.4	729.9	730.4	730.2	730.0
147.5°	760.5	761.1	761.7	762.3	762.8	763.3	763.7	764.2	764.7	764.7	764.7
150°	783.4	783.7	784.1	784.4	784.7	785.0	785.4	785.7	786.0	786.0	786.0
152.5°	802.5	803.0	803.5	803.9	804.2	804.4	804.6	804.8	805.0	805.3	805.6
155°	832.1	832.1	832.1	832.1	832.1	832.3	832.5	832.6	832.8	833.5	834.1
157.5°	857.4	857.2	857.0	856.8	856.8	856.9	857.0	857.2	857.3	858.0	858.7
160°	873.3	873.0	872.6	872.3	872.1	872.1	872.1	872.1	872.1	873.0	873.8
162.5°	887.4	886.9	886.5	886.0	885.9	886.0	886.1	886.3	886.4	887.2	888.0
165°	905.8	905.3	904.8	904.3	904.0	904.0	904.0	904.0	904.0	905.0	906.0
167.5°	920.3	919.7	919.0	918.3	918.1	918.2	918.3	918.5	918.6	919.6	920.6
170°	928.6	928.0	927.3	926.6	926.3	926.3	926.3	926.3	926.3	927.5	928.6
172.5°	935.2	934.5	933.8	933.2	932.8	932.8	932.8	932.8	932.8	933.9	934.9
175°	942.0	941.3	940.7	940.0	939.7	939.7	939.7	939.7	939.7	940.7	941.7
177.5°	944.9	944.4	943.9	943.4	943.1	943.1	943.1	943.1	943.1	943.9	944.7
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
2.5°	1137.1	1137.5	1142.1	1145.5	1143.8	1145.9	1146.7
5°	1242.3	1261.2	1271.1	1278.4	1279.0	1279.5	1283.7
7.5°	1391.5	1411.7	1426.5	1448.9	1455.6	1463.2	1461.0
10°	1500.4	1530.2	1555.9	1569.5	1584.2	1605.6	1588.4
12.5°	1602.2	1655.1	1694.1	1715.3	1729.1	1733.4	1724.9
15°	1770.0	1839.1	1876.3	1875.2	1922.4	1942.8	1910.8
17.5°	1923.9	1987.7	2038.8	2065.0	2104.2	2112.9	2108.9
20°	2018.2	2087.8	2127.6	2172.6	2193.0	2211.3	2214.5
22.5°	2099.4	2161.9	2204.6	2242.1	2259.2	2267.9	2273.1
25°	2183.1	2232.3	2257.9	2271.0	2275.7	2274.7	2267.9
27.5°	2177.3	2181.1	2152.8	2125.1	2100.3	2072.3	2062.7
30°	2120.8	2076.8	1998.3	1953.8	1888.3	1836.5	1857.4
32.5°	1972.1	1884.6	1796.4	1699.1	1618.6	1595.7	1572.6
35°	1683.1	1529.2	1439.2	1334.4	1292.6	1250.7	1221.9
37.5°	1361.7	1242.6	1135.8	1067.3	1025.4	998.9	984.6
40°	1177.4	1070.1	982.1	926.6	894.7	864.9	860.7
42.5°	1030.4	930.6	864.4	820.2	789.6	776.9	767.7
45°	843.9	774.3	729.8	698.4	678.0	670.1	659.6
47.5°	714.3	665.1	631.7	610.3	594.9	589.1	588.2
50°	641.8	601.0	576.4	559.6	547.6	545.5	537.1
52.5°	587.4	552.0	532.8	518.2	509.5	503.6	501.1
55°	509.9	486.3	469.1	460.7	453.9	448.1	448.1
57.5°	446.1	426.5	415.0	407.9	405.8	401.7	399.1
60°	406.8	390.0	381.1	374.8	370.7	371.2	366.5
62.5°	368.2	357.4	348.9	342.6	337.6	337.7	338.0
65°	313.6	305.2	298.9	296.8	293.7	290.0	291.1
67.5°	265.7	257.9	253.0	249.4	248.4	246.4	249.4
70°	231.4	225.6	222.0	218.8	217.8	218.3	220.9
72.5°	200.0	195.9	193.5	192.0	189.7	189.8	191.6
75°	157.1	153.9	151.8	150.2	149.7	149.7	149.7
77.5°	115.4	114.7	113.7	111.4	111.5	112.1	112.2
80°	91.1	89.5	89.0	88.0	86.4	85.3	88.0
82.5°	68.1	66.5	66.0	65.8	63.3	63.1	65.3
85°	36.6	35.1	35.6	35.1	35.1	34.6	34.6
87.5°	16.9	16.7	16.3	16.8	16.5	16.1	17.0
90°	19.8	20.5	20.9	21.3	21.6	21.9	22.3
92.5°	30.1	30.6	30.8	30.6	30.4	30.2	30.0
95°	56.9	57.6	57.9	57.9	57.9	57.9	57.9
97.5°	88.2	89.0	89.3	89.3	89.2	89.1	89.1
100°	110.6	111.1	111.5	111.8	112.2	112.5	112.8
102.5°	136.7	137.2	137.4	137.4	137.3	137.2	137.2
105°	175.2	175.2	175.3	175.7	176.0	176.3	176.7
107.5°	217.9	218.4	218.6	218.4	218.2	218.0	217.8
110°	246.2	246.8	247.0	246.7	246.3	246.0	245.7



TEST NUMBER: P332157

CATALOG NUMBER: S123DIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.5	275.3	275.6	275.6	275.5	275.4	275.4
115°	316.7	316.9	316.9	316.7	316.5	316.4	316.2
117.5°	359.7	359.7	359.5	359.0	358.5	358.1	357.6
120°	388.4	388.3	388.0	387.7	387.4	387.0	386.7
122.5°	417.3	416.9	416.5	416.0	415.5	415.1	414.6
125°	460.4	459.8	459.1	458.5	457.8	457.1	456.5
127.5°	503.0	502.1	501.2	500.5	499.7	499.0	498.2
130°	531.7	531.0	530.1	529.0	527.8	526.7	525.5
132.5°	559.2	558.4	557.6	556.7	555.8	554.9	554.0
135°	600.7	600.1	599.6	599.2	598.9	598.6	598.2
137.5°	641.1	640.5	639.8	639.2	638.5	637.9	637.3
140°	668.3	668.1	667.4	666.3	665.1	664.0	662.8
142.5°	693.2	693.0	692.5	691.6	690.7	689.8	688.9
145°	729.9	729.7	729.3	728.6	728.0	727.3	726.7
147.5°	764.7	764.7	764.2	763.2	762.2	761.2	760.2
150°	786.0	786.0	785.5	784.5	783.6	782.6	781.6
152.5°	805.8	806.1	805.8	804.9	804.1	803.2	802.4
155°	834.8	835.4	835.2	834.0	832.9	831.7	830.6
157.5°	859.4	860.1	859.9	859.0	858.1	857.2	856.2
160°	874.6	875.4	875.5	874.9	874.2	873.5	872.9
162.5°	888.9	889.7	889.6	888.5	887.5	886.4	885.3
165°	907.0	908.0	907.9	906.8	905.6	904.5	903.3
167.5°	921.7	922.7	922.7	921.7	920.6	919.6	918.6
170°	929.8	930.9	930.9	929.8	928.6	927.5	926.3
172.5°	935.9	936.9	936.9	935.7	934.6	933.4	932.3
175°	942.6	943.6	943.6	942.4	941.2	940.1	938.9
177.5°	945.5	946.3	946.2	945.3	944.3	943.4	942.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9

(END OF REPORT)