

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332126-940

Luminaire Tested: **S123DIW-S560D755U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332126-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D755U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4823.4 lumens  
Efficiency: N/A  
Efficacy: 128.3 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32				
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27				
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13				
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7587	7587	7587	7587
5°	9048	7621	6753	7621
10°	11326	7582	6099	7582
15°	13891	7520	5678	7520
20°	16549	7425	5407	7425
25°	17570	7310	5346	7310
30°	15060	7225	5374	7225
35°	10474	7104	5430	7104
40°	7888	6962	5413	6962
45°	6550	6753	5345	6753
50°	5868	6325	5297	6325
55°	5485	5864	5230	5864
60°	5147	5382	5175	5382
65°	4834	4905	5010	4905
70°	4535	4365	4771	4365
75°	4059	3818	4375	3818
80°	3552	3137	3769	3137
85°	2791	2285	2532	2285



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.4	1.4
10°-20°	222.7	4.6
20°-30°	373.7	7.7
30°-40°	423.1	8.8
40°-50°	379.5	7.9
50°-60°	306.2	6.3
60°-70°	213.4	4.4
70°-80°	112.2	2.3
80°-90°	29.9	0.6
90°-100°	32.1	0.7
100°-110°	153.0	3.2
110°-120°	367.6	7.6
120°-130°	468.1	9.7
130°-140°	500.2	10.4
140°-150°	467.7	9.7
150°-160°	377.3	7.8
160°-170°	243.5	5.0
170°-180°	83.9	1.7
0°-30°	665.8	13.8
0°-40°	1088.9	22.6
0°-60°	1774.6	36.8
0°-90°	2130.0	44.2
90°-120°	552.8	11.5
90°-150°	1988.7	41.2
90°-180°	2693.0	55.8
0°-180°	4823.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	705	705	705	705	705	
5°	837	705	625	705	837	87
15°	1246	675	510	675	1246	360
25°	1479	616	450	616	1479	649
35°	797	541	413	541	797	518
45°	430	444	351	444	430	340
55°	292	312	279	312	292	262
65°	190	193	197	193	190	189
75°	98	92	105	92	98	105
85°	23	18	20	18	23	27
90°	20	1	20	1	20	10
95°	25	40	25	40	25	21
105°	29	196	29	196	29	66
115°	386	367	386	367	386	357
125°	528	517	528	517	528	471
135°	650	644	650	644	650	501
145°	750	743	750	743	750	468
155°	817	818	817	818	817	377
165°	861	863	861	863	861	243
175°	880	883	880	883	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	748.1	747.5	746.2	747.3	745.0	742.1	741.8	739.0	731.1	730.6	728.4
5°	837.4	834.6	834.4	834.0	829.2	822.7	810.4	809.4	793.0	784.8	774.9
7.5°	953.1	954.6	949.6	945.2	930.6	921.0	907.8	890.9	870.8	850.3	836.7
10°	1036.2	1047.4	1033.4	1023.9	1015.0	998.3	978.8	954.6	930.3	902.0	880.5
12.5°	1125.2	1130.8	1128.0	1118.9	1105.2	1079.7	1045.2	1018.5	996.1	949.0	929.9
15°	1246.5	1267.4	1254.1	1223.3	1224.1	1199.8	1154.7	1105.2	1078.9	1037.5	981.1
17.5°	1375.8	1378.4	1372.7	1347.1	1330.0	1296.7	1255.1	1207.6	1154.3	1104.4	1044.6
20°	1444.7	1442.6	1430.7	1417.3	1387.9	1362.0	1316.5	1263.6	1195.3	1146.1	1080.9
22.5°	1482.9	1479.4	1473.8	1462.7	1438.2	1410.3	1369.6	1311.7	1246.7	1178.9	1103.6
25°	1479.4	1483.9	1484.6	1481.5	1473.0	1456.3	1424.2	1378.0	1313.1	1226.1	1147.5
27.5°	1345.6	1351.8	1370.1	1386.3	1404.4	1422.8	1420.4	1397.5	1349.5	1274.3	1178.2
30°	1211.7	1198.0	1231.9	1274.5	1303.6	1354.8	1383.5	1385.2	1358.3	1293.7	1200.1
32.5°	1025.9	1041.0	1055.9	1108.4	1171.9	1229.4	1286.5	1332.5	1337.7	1294.8	1212.9
35°	797.1	815.9	843.2	870.6	938.9	997.6	1098.0	1185.4	1255.1	1264.3	1214.1
37.5°	642.3	651.7	668.9	696.2	740.9	810.7	888.3	998.8	1099.7	1174.8	1178.1
40°	561.4	564.2	583.6	604.5	640.7	698.0	768.1	865.8	986.7	1091.5	1135.2
42.5°	500.8	506.8	515.1	535.1	563.9	607.1	672.2	753.0	863.7	984.4	1069.9
45°	430.3	437.1	442.3	455.6	476.1	505.1	550.5	624.3	708.6	833.3	948.4
47.5°	383.7	384.2	388.1	398.1	412.1	433.9	466.0	513.4	590.8	691.9	810.1
50°	350.4	355.9	357.2	365.1	376.0	392.1	418.7	459.0	522.5	611.4	720.0
52.5°	326.9	328.5	332.3	338.0	347.6	360.1	383.2	414.7	464.6	540.3	640.2
55°	292.3	292.3	296.1	300.5	306.0	317.3	332.6	355.9	393.8	452.5	535.2
57.5°	260.4	262.1	264.7	266.1	270.7	278.2	291.1	308.7	337.0	382.2	447.9
60°	239.1	242.1	241.8	244.5	248.6	254.4	265.4	279.7	305.0	341.2	396.5
62.5°	220.5	220.3	220.3	223.5	227.6	233.1	240.2	252.6	274.1	306.2	353.3
65°	189.8	189.2	191.6	193.7	195.0	199.1	204.6	215.5	229.9	253.8	290.3
67.5°	162.7	160.7	162.0	162.7	165.1	168.3	173.3	180.1	191.5	210.7	238.3
70°	144.1	142.4	142.0	142.8	144.8	147.2	151.0	157.5	168.0	183.4	203.6
72.5°	125.0	123.9	123.8	125.3	126.3	127.8	130.5	136.4	144.8	156.3	175.1
75°	97.6	97.6	97.6	98.0	99.1	100.4	102.5	105.5	112.0	120.2	132.9
77.5°	73.2	73.1	72.8	72.7	74.2	74.8	75.3	78.1	81.8	87.3	96.5
80°	57.3	55.6	56.4	57.3	58.1	58.4	59.4	60.1	63.2	66.3	72.8
82.5°	42.6	41.2	41.3	42.9	43.1	43.3	44.4	45.4	46.5	49.3	52.8
85°	22.6	22.6	22.9	22.9	23.2	22.9	23.9	24.3	24.3	25.9	28.0
87.5°	12.1	11.5	11.8	11.9	11.6	11.8	11.9	12.1	12.3	12.4	12.3
90°	19.7	19.4	19.1	18.8	18.5	18.1	17.5	16.9	16.3	15.8	13.8
92.5°	21.8	21.6	21.4	21.2	21.0	20.5	19.6	18.6	17.7	16.8	15.3
95°	25.0	25.0	25.0	25.0	25.0	24.4	23.4	22.4	21.4	20.3	18.7
97.5°	27.0	26.9	26.8	26.6	26.5	25.8	24.6	23.5	22.3	21.1	31.7
100°	27.6	27.4	27.3	27.1	27.0	26.3	25.1	24.0	22.8	21.7	44.4
102.5°	28.1	27.8	27.6	27.3	27.0	28.7	32.4	35.9	39.6	43.2	68.0
105°	28.9	28.6	28.3	28.0	27.7	40.5	66.3	92.1	117.9	143.7	156.9
107.5°	90.7	110.1	129.6	149.0	168.5	187.7	206.6	225.5	244.4	263.4	261.4
110°	180.5	201.3	222.1	243.0	263.9	276.7	281.5	286.3	291.1	296.0	294.4



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	309.6	314.0	318.4	322.8	327.2	329.4	329.3	329.2	329.1	329.0	327.4
115°	385.8	385.2	384.7	384.1	383.5	382.5	381.0	379.6	378.1	376.7	375.3
117.5°	428.6	428.5	428.4	428.3	428.1	427.5	426.3	425.2	424.0	422.8	422.1
120°	458.0	458.0	458.0	458.0	458.0	457.4	456.3	455.1	454.0	452.7	452.4
122.5°	486.9	486.8	486.6	486.5	486.4	486.0	485.1	484.3	483.5	482.7	482.1
125°	527.5	527.3	527.0	526.7	526.4	526.1	525.8	525.5	525.2	525.0	524.3
127.5°	566.7	566.9	567.2	567.6	567.8	567.8	567.3	566.9	566.3	565.9	565.2
130°	591.8	592.2	592.5	592.7	593.1	592.9	592.3	591.7	591.1	590.6	590.0
132.5°	614.9	615.4	615.8	616.2	616.6	616.5	615.9	615.4	614.7	614.2	613.7
135°	650.2	650.7	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2	649.7
137.5°	683.5	683.8	684.0	684.4	684.7	684.5	683.8	683.1	682.3	681.6	681.4
140°	703.4	703.7	704.0	704.3	704.6	704.5	703.8	703.3	702.7	702.1	701.7
142.5°	721.8	722.2	722.6	723.0	723.4	723.4	722.9	722.5	722.0	721.6	721.1
145°	750.0	750.0	750.0	750.0	750.0	749.8	749.6	749.3	748.9	748.7	748.4
147.5°	771.0	771.7	772.3	773.0	773.6	773.9	773.6	773.3	773.0	772.7	772.4
150°	786.8	787.2	787.6	788.1	788.5	788.5	788.3	788.0	787.7	787.4	787.1
152.5°	799.3	800.0	800.7	801.4	802.0	802.1	801.6	801.0	800.5	800.0	799.9
155°	816.9	817.8	818.7	819.6	820.5	820.6	819.7	819.0	818.3	817.6	817.4
157.5°	831.8	832.9	834.0	835.2	836.3	836.4	835.5	834.7	833.8	832.9	833.1
160°	841.2	842.2	843.3	844.3	845.3	845.3	844.5	843.6	842.8	841.9	842.0
162.5°	850.2	851.0	851.9	852.8	853.7	853.7	852.7	851.8	850.8	849.7	849.9
165°	860.9	861.9	862.9	864.0	865.0	864.9	863.7	862.6	861.4	860.2	860.4
167.5°	868.6	869.8	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6	868.6
170°	873.3	874.5	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3	873.3
172.5°	876.0	877.3	878.6	879.9	881.1	881.2	880.0	878.9	877.7	876.6	876.4
175°	879.9	881.1	882.3	883.4	884.6	884.7	883.7	882.6	881.6	880.6	880.5
177.5°	881.1	882.3	883.4	884.6	885.7	885.9	884.9	884.0	883.1	882.2	882.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	726.7	724.6	722.4	718.5	715.2	710.6	709.3	707.7	702.8	698.3	695.1
5°	771.2	762.9	751.0	740.0	731.2	719.3	712.4	705.3	695.0	685.8	678.2
7.5°	817.6	801.5	782.9	762.9	744.1	726.0	711.5	698.6	684.2	670.6	660.0
10°	854.5	831.3	805.3	777.3	753.4	730.1	710.7	693.7	675.2	659.2	645.8
12.5°	896.5	862.1	826.3	792.3	764.0	731.8	708.3	686.5	665.7	646.3	631.3
15°	946.4	902.7	860.3	813.5	770.4	730.1	702.1	674.8	650.6	630.8	611.6
17.5°	991.7	942.2	886.4	829.5	777.6	729.8	690.5	659.7	629.4	605.1	586.0
20°	1017.4	961.0	897.9	838.7	781.4	728.1	685.1	648.2	615.5	589.8	568.3
22.5°	1039.6	973.6	908.2	845.1	781.1	723.7	675.0	637.0	601.5	576.4	553.6
25°	1062.5	983.6	918.0	843.9	772.5	713.1	658.4	615.5	579.9	550.5	527.0
27.5°	1082.2	982.9	905.1	825.4	759.0	699.5	641.1	594.9	557.2	525.3	501.4
30°	1095.3	984.3	891.7	812.8	745.9	684.4	627.7	581.3	541.6	509.2	486.7
32.5°	1103.5	983.5	879.4	795.3	725.1	670.7	613.2	565.2	524.4	492.6	470.8
35°	1108.2	977.4	858.3	759.2	691.6	638.6	590.5	540.6	497.9	468.2	443.6
37.5°	1098.7	964.8	833.7	724.3	650.3	598.2	557.7	515.2	474.4	441.7	420.4
40°	1083.6	956.6	814.5	699.8	621.9	571.7	537.3	495.5	455.2	424.2	404.4
42.5°	1055.0	940.0	793.5	672.4	592.4	542.2	510.4	475.6	437.5	408.3	388.5
45°	985.0	903.7	762.0	631.5	548.8	497.0	469.0	443.6	409.1	380.8	363.7
47.5°	887.8	849.1	716.3	588.3	503.4	453.4	424.3	403.9	378.7	355.9	339.5
50°	820.4	804.3	685.5	558.7	473.0	424.2	396.2	377.7	359.6	336.7	321.7
52.5°	742.4	752.3	649.3	528.2	442.1	394.1	367.7	353.1	336.7	317.9	304.8
55°	632.8	668.7	587.1	476.8	396.2	350.4	325.5	312.5	302.9	288.9	277.7
57.5°	530.2	575.8	519.7	423.8	351.0	311.6	287.7	273.5	267.3	260.0	251.2
60°	469.2	514.3	471.6	388.3	320.7	283.1	262.0	250.0	243.9	238.7	231.2
62.5°	414.9	460.5	424.6	352.2	290.9	256.1	237.6	226.0	221.1	218.5	212.0
65°	340.2	379.4	355.5	296.1	248.3	217.6	200.8	192.6	188.2	187.2	183.1
67.5°	276.9	306.7	289.4	245.6	207.9	181.4	167.2	160.2	156.9	156.5	153.4
70°	235.3	263.3	250.0	210.4	177.9	157.1	144.8	138.7	136.6	136.3	134.6
72.5°	203.0	222.6	212.0	179.0	153.9	135.0	125.9	119.5	117.2	117.7	116.5
75°	150.3	165.0	158.8	135.9	115.7	103.4	95.9	91.8	89.8	90.9	89.4
77.5°	108.2	117.4	111.9	96.0	83.6	74.7	69.2	66.7	64.8	64.7	64.1
80°	81.6	87.1	84.0	74.5	64.2	56.7	52.3	50.6	49.5	49.2	48.9
82.5°	58.1	62.8	59.1	52.6	45.7	41.1	38.6	36.4	35.6	35.8	35.5
85°	29.3	31.1	29.7	25.6	22.9	20.9	19.4	18.5	17.7	18.1	17.4
87.5°	12.5	12.4	11.2	9.8	8.9	7.8	7.5	6.7	6.4	6.7	6.8
90°	11.9	10.1	8.2	6.5	5.0	3.6	2.1	0.6	2.1	3.6	5.0
92.5°	13.9	12.5	11.1	10.6	11.0	11.4	11.8	12.2	11.8	11.4	11.0
95°	17.1	15.5	13.9	16.1	22.1	28.1	34.1	40.0	34.1	28.1	22.1
97.5°	42.1	52.6	63.1	69.7	72.4	75.1	77.8	80.4	77.8	75.1	72.4
100°	67.1	89.9	112.6	122.5	119.7	116.7	113.8	110.9	113.8	116.7	119.7
102.5°	92.8	117.7	142.6	153.9	151.9	149.7	147.7	145.5	147.7	149.7	151.9
105°	170.0	183.1	196.2	202.0	200.4	198.8	197.2	195.6	197.2	198.8	200.4
107.5°	259.2	257.2	255.1	253.4	252.2	250.8	249.6	248.3	249.6	250.8	252.2
110°	292.7	291.1	289.5	288.1	287.0	285.8	284.6	283.5	284.6	285.8	287.0





TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.8	324.2	322.6	321.3	320.2	319.1	318.1	317.1	318.1	319.1	320.2
115°	374.0	372.7	371.4	370.3	369.4	368.5	367.7	366.8	367.7	368.5	369.4
117.5°	421.5	420.8	420.2	419.3	418.2	417.1	416.1	415.0	416.1	417.1	418.2
120°	451.9	451.5	451.0	450.1	448.8	447.5	446.2	444.9	446.2	447.5	448.8
122.5°	481.6	481.0	480.5	479.7	478.6	477.5	476.4	475.4	476.4	477.5	478.6
125°	523.8	523.2	522.6	521.7	520.6	519.4	518.3	517.1	518.3	519.4	520.6
127.5°	564.5	563.8	563.1	562.1	561.0	559.8	558.7	557.5	558.7	559.8	561.0
130°	589.4	588.8	588.3	587.4	586.2	585.1	583.9	582.6	583.9	585.1	586.2
132.5°	613.2	612.8	612.3	611.5	610.3	609.1	608.0	606.8	608.0	609.1	610.3
135°	649.1	648.5	647.9	647.2	646.3	645.4	644.6	643.7	644.6	645.4	646.3
137.5°	681.0	680.6	680.4	679.7	678.5	677.4	676.3	675.2	676.3	677.4	678.5
140°	701.2	700.8	700.3	699.7	698.8	697.9	697.1	696.2	697.1	697.9	698.8
142.5°	720.7	720.2	719.8	719.2	718.3	717.4	716.5	715.6	716.5	717.4	718.3
145°	748.1	747.8	747.5	746.9	745.8	744.8	743.8	742.8	743.8	744.8	745.8
147.5°	772.1	771.9	771.5	771.1	770.3	769.7	769.0	768.4	769.0	769.7	770.3
150°	786.8	786.6	786.2	785.9	785.4	785.0	784.5	784.2	784.5	785.0	785.4
152.5°	799.7	799.5	799.3	799.2	798.9	798.7	798.5	798.3	798.5	798.7	798.9
155°	817.3	817.2	817.0	817.1	817.3	817.7	818.0	818.2	818.0	817.7	817.3
157.5°	833.2	833.4	833.6	833.7	833.7	833.7	833.7	833.7	833.7	833.7	833.7
160°	842.1	842.3	842.5	842.6	842.8	842.9	843.0	843.2	843.0	842.9	842.8
162.5°	850.1	850.2	850.3	850.6	851.0	851.3	851.8	852.1	851.8	851.3	851.0
165°	860.5	860.7	860.9	861.1	861.6	862.0	862.5	862.9	862.5	862.0	861.6
167.5°	868.6	868.6	868.6	869.0	869.5	870.1	870.7	871.3	870.7	870.1	869.5
170°	873.3	873.3	873.3	873.7	874.2	874.9	875.4	876.0	875.4	874.9	874.2
172.5°	876.3	876.2	876.0	876.4	877.1	877.7	878.4	879.1	878.4	877.7	877.1
175°	880.3	880.1	880.0	880.3	881.0	881.7	882.4	883.2	882.4	881.7	881.0
177.5°	881.9	881.8	881.7	881.9	882.5	883.1	883.7	884.2	883.7	883.1	882.5
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	693.1	691.3	688.5	684.4	681.1	675.9	675.9	676.7	676.7	676.5	675.9
5°	672.1	667.0	660.8	653.7	646.1	638.6	637.3	634.5	632.5	631.2	629.5
7.5°	649.9	640.9	631.9	621.9	612.7	605.1	599.9	595.5	592.6	589.7	587.5
10°	634.9	623.6	613.1	602.4	590.8	581.6	575.8	571.7	568.6	565.9	564.5
12.5°	617.2	604.2	592.5	582.5	569.8	560.3	554.7	552.9	549.2	543.5	540.5
15°	591.2	579.3	565.3	549.8	543.7	532.1	525.6	522.5	520.5	516.0	514.7
17.5°	569.0	553.3	537.6	526.1	514.7	505.3	501.7	497.8	495.2	491.5	490.4
20°	551.3	537.3	522.9	510.6	498.6	488.4	485.3	482.6	479.8	478.1	476.8
22.5°	533.2	519.2	507.3	495.8	483.0	476.4	473.0	470.0	468.1	466.9	465.6
25°	507.8	495.5	482.2	472.0	461.7	457.3	455.2	453.5	452.2	450.5	450.1
27.5°	485.2	471.8	461.0	451.4	444.1	440.3	438.4	437.6	437.8	438.5	438.8
30°	468.2	455.9	447.0	438.8	432.0	428.6	428.3	428.3	429.6	430.0	430.7
32.5°	452.6	442.6	433.6	425.7	420.5	418.2	419.5	419.5	420.6	421.5	422.8
35°	430.0	421.1	414.3	407.4	403.0	404.0	404.7	405.4	407.1	409.1	410.5
37.5°	408.3	400.6	393.5	388.2	386.1	388.0	389.6	391.0	393.1	394.6	395.9
40°	392.7	386.9	380.1	375.3	376.0	377.0	378.4	380.1	381.8	382.8	384.2
42.5°	378.3	372.2	367.0	363.0	364.0	365.3	366.1	367.0	369.0	370.9	371.7
45°	356.2	351.4	346.6	344.3	344.9	345.6	346.3	347.3	349.0	350.4	350.7
47.5°	331.4	328.1	324.9	322.5	323.6	323.3	324.2	326.5	327.0	327.8	329.7
50°	315.6	312.5	308.7	308.1	308.1	308.1	308.4	311.1	311.1	312.5	313.9
52.5°	298.1	296.1	293.7	292.5	291.9	291.9	293.4	294.7	295.2	297.2	298.5
55°	272.2	270.1	268.1	267.1	266.4	267.1	269.8	270.5	272.2	273.2	274.2
57.5°	245.2	243.6	242.0	241.5	241.3	242.2	243.7	245.8	246.2	249.3	250.8
60°	227.5	225.1	223.7	223.7	223.0	226.0	225.4	228.8	229.5	231.6	234.0
62.5°	209.1	205.9	205.4	205.4	206.3	207.2	208.2	209.7	211.5	214.1	215.9
65°	179.7	177.9	180.3	179.9	179.3	181.4	181.4	183.1	185.1	187.5	191.3
67.5°	151.7	150.8	151.1	151.1	152.0	153.2	154.2	155.7	158.1	160.7	163.1
70°	132.9	133.8	132.2	133.6	134.6	134.9	135.5	137.6	140.4	142.0	144.8
72.5°	114.6	114.5	114.7	115.2	116.3	116.9	117.5	119.8	122.9	124.3	126.5
75°	88.1	87.7	88.8	88.8	90.5	91.2	91.8	92.9	95.6	97.6	99.4
77.5°	64.4	64.7	64.6	65.7	65.3	65.4	67.5	68.5	68.8	72.9	73.7
80°	48.5	49.2	49.5	49.8	50.2	49.5	51.9	53.0	53.0	55.3	57.1
82.5°	34.9	35.2	36.1	36.5	36.6	37.2	37.5	38.2	39.0	40.0	42.3
85°	17.4	18.5	18.8	18.5	18.8	18.1	19.1	19.4	19.8	19.8	19.8
87.5°	6.8	7.4	7.5	8.1	8.2	8.9	9.0	8.6	8.6	9.6	8.6
90°	6.5	8.2	10.1	11.9	13.8	15.8	16.3	16.9	17.5	18.1	18.5
92.5°	10.6	11.1	12.5	13.9	15.3	16.8	17.7	18.6	19.6	20.5	21.0
95°	16.1	13.9	15.5	17.1	18.7	20.3	21.4	22.4	23.4	24.4	25.0
97.5°	69.7	63.1	52.6	42.1	31.7	21.1	22.3	23.5	24.6	25.8	26.5
100°	122.5	112.6	89.9	67.1	44.4	21.7	22.8	24.0	25.1	26.3	27.0
102.5°	153.9	142.6	117.7	92.8	68.0	43.2	39.6	35.9	32.4	28.7	27.0
105°	202.0	196.2	183.1	170.0	156.9	143.7	117.9	92.1	66.3	40.5	27.7
107.5°	253.4	255.1	257.2	259.2	261.4	263.4	244.4	225.5	206.6	187.7	168.5
110°	288.1	289.5	291.1	292.7	294.4	296.0	291.1	286.3	281.5	276.7	263.9



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	321.3	322.6	324.2	325.8	327.4	329.0	329.1	329.2	329.3	329.4	327.2
115°	370.3	371.4	372.7	374.0	375.3	376.7	378.1	379.6	381.0	382.5	383.5
117.5°	419.3	420.2	420.8	421.5	422.1	422.8	424.0	425.2	426.3	427.5	428.1
120°	450.1	451.0	451.5	451.9	452.4	452.7	454.0	455.1	456.3	457.4	458.0
122.5°	479.7	480.5	481.0	481.6	482.1	482.7	483.5	484.3	485.1	486.0	486.4
125°	521.7	522.6	523.2	523.8	524.3	525.0	525.2	525.5	525.8	526.1	526.4
127.5°	562.1	563.1	563.8	564.5	565.2	565.9	566.3	566.9	567.3	567.8	567.8
130°	587.4	588.3	588.8	589.4	590.0	590.6	591.1	591.7	592.3	592.9	593.1
132.5°	611.5	612.3	612.8	613.2	613.7	614.2	614.7	615.4	615.9	616.5	616.6
135°	647.2	647.9	648.5	649.1	649.7	650.2	650.7	651.1	651.6	652.0	652.0
137.5°	679.7	680.4	680.6	681.0	681.4	681.6	682.3	683.1	683.8	684.5	684.7
140°	699.7	700.3	700.8	701.2	701.7	702.1	702.7	703.3	703.8	704.5	704.6
142.5°	719.2	719.8	720.2	720.7	721.1	721.6	722.0	722.5	722.9	723.4	723.4
145°	746.9	747.5	747.8	748.1	748.4	748.7	748.9	749.3	749.6	749.8	750.0
147.5°	771.1	771.5	771.9	772.1	772.4	772.7	773.0	773.3	773.6	773.9	773.6
150°	785.9	786.2	786.6	786.8	787.1	787.4	787.7	788.0	788.3	788.5	788.5
152.5°	799.2	799.3	799.5	799.7	799.9	800.0	800.5	801.0	801.6	802.1	802.0
155°	817.1	817.0	817.2	817.3	817.4	817.6	818.3	819.0	819.7	820.6	820.5
157.5°	833.7	833.6	833.4	833.2	833.1	832.9	833.8	834.7	835.5	836.4	836.3
160°	842.6	842.5	842.3	842.1	842.0	841.9	842.8	843.6	844.5	845.3	845.3
162.5°	850.6	850.3	850.2	850.1	849.9	849.7	850.8	851.8	852.7	853.7	853.7
165°	861.1	860.9	860.7	860.5	860.4	860.2	861.4	862.6	863.7	864.9	865.0
167.5°	869.0	868.6	868.6	868.6	868.6	868.6	869.8	870.9	872.2	873.3	873.3
170°	873.7	873.3	873.3	873.3	873.3	873.3	874.5	875.7	876.9	878.1	878.1
172.5°	876.4	876.0	876.2	876.3	876.4	876.6	877.7	878.9	880.0	881.2	881.1
175°	880.3	880.0	880.1	880.3	880.5	880.6	881.6	882.6	883.7	884.7	884.6
177.5°	881.9	881.7	881.8	881.9	882.1	882.2	883.1	884.0	884.9	885.9	885.7
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	674.0	673.8	675.6	674.3	675.6	673.8	674.0	675.9	676.5	676.7	676.7
5°	627.4	628.4	625.0	625.0	625.0	628.4	627.4	629.5	631.2	632.5	634.5
7.5°	585.9	584.3	584.5	582.6	584.5	584.3	585.9	587.5	589.7	592.6	595.5
10°	560.4	558.4	557.7	558.0	557.7	558.4	560.4	564.5	565.9	568.6	571.7
12.5°	539.4	539.0	534.5	534.6	534.5	539.0	539.4	540.5	543.5	549.2	552.9
15°	514.7	508.2	507.5	509.5	507.5	508.2	514.7	514.7	516.0	520.5	522.5
17.5°	489.9	486.4	486.7	485.6	486.7	486.4	489.9	490.4	491.5	495.2	497.8
20°	476.8	474.7	474.4	472.0	474.4	474.7	476.8	476.8	478.1	479.8	482.6
22.5°	464.8	464.0	464.2	461.6	464.2	464.0	464.8	465.6	466.9	468.1	470.0
25°	449.8	451.5	450.1	450.1	450.1	451.5	449.8	450.1	450.5	452.2	453.5
27.5°	439.7	439.6	438.9	438.9	438.9	439.6	439.7	438.8	438.5	437.8	437.6
30°	432.0	431.7	432.4	432.4	432.4	431.7	432.0	430.7	430.0	429.6	428.3
32.5°	424.4	424.8	425.0	425.3	425.0	424.8	424.4	422.8	421.5	420.6	419.5
35°	412.6	412.9	413.9	413.2	413.9	412.9	412.6	410.5	409.1	407.1	405.4
37.5°	396.5	398.1	397.8	398.3	397.8	398.1	396.5	395.9	394.6	393.1	391.0
40°	384.6	385.6	385.2	385.2	385.2	385.6	384.6	384.2	382.8	381.8	380.1
42.5°	372.3	373.0	372.1	371.6	372.1	373.0	372.3	371.7	370.9	369.0	367.0
45°	352.1	351.4	352.5	351.1	352.5	351.4	352.1	350.7	350.4	349.0	347.3
47.5°	329.6	330.3	330.6	331.5	330.6	330.3	329.6	329.7	327.8	327.0	326.5
50°	314.5	316.6	316.6	316.3	316.6	316.6	314.5	313.9	312.5	311.1	311.1
52.5°	299.8	300.8	302.1	302.0	302.1	300.8	299.8	298.5	297.2	295.2	294.7
55°	277.0	277.7	278.3	278.7	278.3	277.7	277.0	274.2	273.2	272.2	270.5
57.5°	253.3	253.1	254.7	255.2	254.7	253.1	253.3	250.8	249.3	246.2	245.8
60°	236.7	236.7	239.4	240.4	239.4	236.7	236.7	234.0	231.6	229.5	228.8
62.5°	218.9	220.0	222.7	221.3	222.7	220.0	218.9	215.9	214.1	211.5	209.7
65°	193.0	195.7	195.4	196.7	195.4	195.7	193.0	191.3	187.5	185.1	183.1
67.5°	165.9	167.6	170.0	170.2	170.0	167.6	165.9	163.1	160.7	158.1	155.7
70°	147.6	149.3	150.6	151.6	150.6	149.3	147.6	144.8	142.0	140.4	137.6
72.5°	129.7	130.6	133.9	132.5	133.9	130.6	129.7	126.5	124.3	122.9	119.8
75°	101.7	104.2	106.2	105.2	106.2	104.2	101.7	99.4	97.6	95.6	92.9
77.5°	75.3	77.7	78.6	77.8	78.6	77.7	75.3	73.7	72.9	68.8	68.5
80°	59.4	59.1	61.2	60.8	61.2	59.1	59.4	57.1	55.3	53.0	53.0
82.5°	43.6	43.2	44.2	44.4	44.2	43.2	43.6	42.3	40.0	39.0	38.2
85°	21.1	22.2	20.9	20.5	20.9	22.2	21.1	19.8	19.8	19.8	19.4
87.5°	8.6	8.7	8.6	8.3	8.6	8.7	8.6	8.6	9.6	8.6	8.6
90°	18.8	19.1	19.4	19.7	19.4	19.1	18.8	18.5	18.1	17.5	16.9
92.5°	21.2	21.4	21.6	21.8	21.6	21.4	21.2	21.0	20.5	19.6	18.6
95°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	24.4	23.4	22.4
97.5°	26.6	26.8	26.9	27.0	26.9	26.8	26.6	26.5	25.8	24.6	23.5
100°	27.1	27.3	27.4	27.6	27.4	27.3	27.1	27.0	26.3	25.1	24.0
102.5°	27.3	27.6	27.8	28.1	27.8	27.6	27.3	27.0	28.7	32.4	35.9
105°	28.0	28.3	28.6	28.9	28.6	28.3	28.0	27.7	40.5	66.3	92.1
107.5°	149.0	129.6	110.1	90.7	110.1	129.6	149.0	168.5	187.7	206.6	225.5
110°	243.0	222.1	201.3	180.5	201.3	222.1	243.0	263.9	276.7	281.5	286.3



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	322.8	318.4	314.0	309.6	314.0	318.4	322.8	327.2	329.4	329.3	329.2
115°	384.1	384.7	385.2	385.8	385.2	384.7	384.1	383.5	382.5	381.0	379.6
117.5°	428.3	428.4	428.5	428.6	428.5	428.4	428.3	428.1	427.5	426.3	425.2
120°	458.0	458.0	458.0	458.0	458.0	458.0	458.0	458.0	457.4	456.3	455.1
122.5°	486.5	486.6	486.8	486.9	486.8	486.6	486.5	486.4	486.0	485.1	484.3
125°	526.7	527.0	527.3	527.5	527.3	527.0	526.7	526.4	526.1	525.8	525.5
127.5°	567.6	567.2	566.9	566.7	566.9	567.2	567.6	567.8	567.8	567.3	566.9
130°	592.7	592.5	592.2	591.8	592.2	592.5	592.7	593.1	592.9	592.3	591.7
132.5°	616.2	615.8	615.4	614.9	615.4	615.8	616.2	616.6	616.5	615.9	615.4
135°	651.6	651.1	650.7	650.2	650.7	651.1	651.6	652.0	652.0	651.6	651.1
137.5°	684.4	684.0	683.8	683.5	683.8	684.0	684.4	684.7	684.5	683.8	683.1
140°	704.3	704.0	703.7	703.4	703.7	704.0	704.3	704.6	704.5	703.8	703.3
142.5°	723.0	722.6	722.2	721.8	722.2	722.6	723.0	723.4	723.4	722.9	722.5
145°	750.0	750.0	750.0	750.0	750.0	750.0	750.0	750.0	749.8	749.6	749.3
147.5°	773.0	772.3	771.7	771.0	771.7	772.3	773.0	773.6	773.9	773.6	773.3
150°	788.1	787.6	787.2	786.8	787.2	787.6	788.1	788.5	788.5	788.3	788.0
152.5°	801.4	800.7	800.0	799.3	800.0	800.7	801.4	802.0	802.1	801.6	801.0
155°	819.6	818.7	817.8	816.9	817.8	818.7	819.6	820.5	820.6	819.7	819.0
157.5°	835.2	834.0	832.9	831.8	832.9	834.0	835.2	836.3	836.4	835.5	834.7
160°	844.3	843.3	842.2	841.2	842.2	843.3	844.3	845.3	845.3	844.5	843.6
162.5°	852.8	851.9	851.0	850.2	851.0	851.9	852.8	853.7	853.7	852.7	851.8
165°	864.0	862.9	861.9	860.9	861.9	862.9	864.0	865.0	864.9	863.7	862.6
167.5°	872.2	870.9	869.8	868.6	869.8	870.9	872.2	873.3	873.3	872.2	870.9
170°	876.9	875.7	874.5	873.3	874.5	875.7	876.9	878.1	878.1	876.9	875.7
172.5°	879.9	878.6	877.3	876.0	877.3	878.6	879.9	881.1	881.2	880.0	878.9
175°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	884.7	883.7	882.6
177.5°	884.6	883.4	882.3	881.1	882.3	883.4	884.6	885.7	885.9	884.9	884.0
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	675.9	675.9	681.1	684.4	688.5	691.3	693.1	695.1	698.3	702.8	707.7
5°	637.3	638.6	646.1	653.7	660.8	667.0	672.1	678.2	685.8	695.0	705.3
7.5°	599.9	605.1	612.7	621.9	631.9	640.9	649.9	660.0	670.6	684.2	698.6
10°	575.8	581.6	590.8	602.4	613.1	623.6	634.9	645.8	659.2	675.2	693.7
12.5°	554.7	560.3	569.8	582.5	592.5	604.2	617.2	631.3	646.3	665.7	686.5
15°	525.6	532.1	543.7	549.8	565.3	579.3	591.2	611.6	630.8	650.6	674.8
17.5°	501.7	505.3	514.7	526.1	537.6	553.3	569.0	586.0	605.1	629.4	659.7
20°	485.3	488.4	498.6	510.6	522.9	537.3	551.3	568.3	589.8	615.5	648.2
22.5°	473.0	476.4	483.0	495.8	507.3	519.2	533.2	553.6	576.4	601.5	637.0
25°	455.2	457.3	461.7	472.0	482.2	495.5	507.8	527.0	550.5	579.9	615.5
27.5°	438.4	440.3	444.1	451.4	461.0	471.8	485.2	501.4	525.3	557.2	594.9
30°	428.3	428.6	432.0	438.8	447.0	455.9	468.2	486.7	509.2	541.6	581.3
32.5°	419.5	418.2	420.5	425.7	433.6	442.6	452.6	470.8	492.6	524.4	565.2
35°	404.7	404.0	403.0	407.4	414.3	421.1	430.0	443.6	468.2	497.9	540.6
37.5°	389.6	388.0	386.1	388.2	393.5	400.6	408.3	420.4	441.7	474.4	515.2
40°	378.4	377.0	376.0	375.3	380.1	386.9	392.7	404.4	424.2	455.2	495.5
42.5°	366.1	365.3	364.0	363.0	367.0	372.2	378.3	388.5	408.3	437.5	475.6
45°	346.3	345.6	344.9	344.3	346.6	351.4	356.2	363.7	380.8	409.1	443.6
47.5°	324.2	323.3	323.6	322.5	324.9	328.1	331.4	339.5	355.9	378.7	403.9
50°	308.4	308.1	308.1	308.1	308.7	312.5	315.6	321.7	336.7	359.6	377.7
52.5°	293.4	291.9	291.9	292.5	293.7	296.1	298.1	304.8	317.9	336.7	353.1
55°	269.8	267.1	266.4	267.1	268.1	270.1	272.2	277.7	288.9	302.9	312.5
57.5°	243.7	242.2	241.3	241.5	242.0	243.6	245.2	251.2	260.0	267.3	273.5
60°	225.4	226.0	223.0	223.7	223.7	225.1	227.5	231.2	238.7	243.9	250.0
62.5°	208.2	207.2	206.3	205.4	205.4	205.9	209.1	212.0	218.5	221.1	226.0
65°	181.4	181.4	179.3	179.9	180.3	177.9	179.7	183.1	187.2	188.2	192.6
67.5°	154.2	153.2	152.0	151.1	151.1	150.8	151.7	153.4	156.5	156.9	160.2
70°	135.5	134.9	134.6	133.6	132.2	133.8	132.9	134.6	136.3	136.6	138.7
72.5°	117.5	116.9	116.3	115.2	114.7	114.5	114.6	116.5	117.7	117.2	119.5
75°	91.8	91.2	90.5	88.8	88.8	87.7	88.1	89.4	90.9	89.8	91.8
77.5°	67.5	65.4	65.3	65.7	64.6	64.7	64.4	64.1	64.7	64.8	66.7
80°	51.9	49.5	50.2	49.8	49.5	49.2	48.5	48.9	49.2	49.5	50.6
82.5°	37.5	37.2	36.6	36.5	36.1	35.2	34.9	35.5	35.8	35.6	36.4
85°	19.1	18.1	18.8	18.5	18.8	18.5	17.4	17.4	18.1	17.7	18.5
87.5°	9.0	8.9	8.2	8.1	7.5	7.4	6.8	6.8	6.7	6.4	6.7
90°	16.3	15.8	13.8	11.9	10.1	8.2	6.5	5.0	3.6	2.1	0.6
92.5°	17.7	16.8	15.3	13.9	12.5	11.1	10.6	11.0	11.4	11.8	12.2
95°	21.4	20.3	18.7	17.1	15.5	13.9	16.1	22.1	28.1	34.1	40.0
97.5°	22.3	21.1	31.7	42.1	52.6	63.1	69.7	72.4	75.1	77.8	80.4
100°	22.8	21.7	44.4	67.1	89.9	112.6	122.5	119.7	116.7	113.8	110.9
102.5°	39.6	43.2	68.0	92.8	117.7	142.6	153.9	151.9	149.7	147.7	145.5
105°	117.9	143.7	156.9	170.0	183.1	196.2	202.0	200.4	198.8	197.2	195.6
107.5°	244.4	263.4	261.4	259.2	257.2	255.1	253.4	252.2	250.8	249.6	248.3
110°	291.1	296.0	294.4	292.7	291.1	289.5	288.1	287.0	285.8	284.6	283.5



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	329.0	327.4	325.8	324.2	322.6	321.3	320.2	319.1	318.1	317.1
115°	378.1	376.7	375.3	374.0	372.7	371.4	370.3	369.4	368.5	367.7	366.8
117.5°	424.0	422.8	422.1	421.5	420.8	420.2	419.3	418.2	417.1	416.1	415.0
120°	454.0	452.7	452.4	451.9	451.5	451.0	450.1	448.8	447.5	446.2	444.9
122.5°	483.5	482.7	482.1	481.6	481.0	480.5	479.7	478.6	477.5	476.4	475.4
125°	525.2	525.0	524.3	523.8	523.2	522.6	521.7	520.6	519.4	518.3	517.1
127.5°	566.3	565.9	565.2	564.5	563.8	563.1	562.1	561.0	559.8	558.7	557.5
130°	591.1	590.6	590.0	589.4	588.8	588.3	587.4	586.2	585.1	583.9	582.6
132.5°	614.7	614.2	613.7	613.2	612.8	612.3	611.5	610.3	609.1	608.0	606.8
135°	650.7	650.2	649.7	649.1	648.5	647.9	647.2	646.3	645.4	644.6	643.7
137.5°	682.3	681.6	681.4	681.0	680.6	680.4	679.7	678.5	677.4	676.3	675.2
140°	702.7	702.1	701.7	701.2	700.8	700.3	699.7	698.8	697.9	697.1	696.2
142.5°	722.0	721.6	721.1	720.7	720.2	719.8	719.2	718.3	717.4	716.5	715.6
145°	748.9	748.7	748.4	748.1	747.8	747.5	746.9	745.8	744.8	743.8	742.8
147.5°	773.0	772.7	772.4	772.1	771.9	771.5	771.1	770.3	769.7	769.0	768.4
150°	787.7	787.4	787.1	786.8	786.6	786.2	785.9	785.4	785.0	784.5	784.2
152.5°	800.5	800.0	799.9	799.7	799.5	799.3	799.2	798.9	798.7	798.5	798.3
155°	818.3	817.6	817.4	817.3	817.2	817.0	817.1	817.3	817.7	818.0	818.2
157.5°	833.8	832.9	833.1	833.2	833.4	833.6	833.7	833.7	833.7	833.7	833.7
160°	842.8	841.9	842.0	842.1	842.3	842.5	842.6	842.8	842.9	843.0	843.2
162.5°	850.8	849.7	849.9	850.1	850.2	850.3	850.6	851.0	851.3	851.8	852.1
165°	861.4	860.2	860.4	860.5	860.7	860.9	861.1	861.6	862.0	862.5	862.9
167.5°	869.8	868.6	868.6	868.6	868.6	868.6	869.0	869.5	870.1	870.7	871.3
170°	874.5	873.3	873.3	873.3	873.3	873.3	873.7	874.2	874.9	875.4	876.0
172.5°	877.7	876.6	876.4	876.3	876.2	876.0	876.4	877.1	877.7	878.4	879.1
175°	881.6	880.6	880.5	880.3	880.1	880.0	880.3	881.0	881.7	882.4	883.2
177.5°	883.1	882.2	882.1	881.9	881.8	881.7	881.9	882.5	883.1	883.7	884.2
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	709.3	710.6	715.2	718.5	722.4	724.6	726.7	728.4	730.6	731.1	739.0
5°	712.4	719.3	731.2	740.0	751.0	762.9	771.2	774.9	784.8	793.0	809.4
7.5°	711.5	726.0	744.1	762.9	782.9	801.5	817.6	836.7	850.3	870.8	890.9
10°	710.7	730.1	753.4	777.3	805.3	831.3	854.5	880.5	902.0	930.3	954.6
12.5°	708.3	731.8	764.0	792.3	826.3	862.1	896.5	929.9	949.0	996.1	1018.5
15°	702.1	730.1	770.4	813.5	860.3	902.7	946.4	981.1	1037.5	1078.9	1105.2
17.5°	690.5	729.8	777.6	829.5	886.4	942.2	991.7	1044.6	1104.4	1154.3	1207.6
20°	685.1	728.1	781.4	838.7	897.9	961.0	1017.4	1080.9	1146.1	1195.3	1263.6
22.5°	675.0	723.7	781.1	845.1	908.2	973.6	1039.6	1103.6	1178.9	1246.7	1311.7
25°	658.4	713.1	772.5	843.9	918.0	983.6	1062.5	1147.5	1226.1	1313.1	1378.0
27.5°	641.1	699.5	759.0	825.4	905.1	982.9	1082.2	1178.2	1274.3	1349.5	1397.5
30°	627.7	684.4	745.9	812.8	891.7	984.3	1095.3	1200.1	1293.7	1358.3	1385.2
32.5°	613.2	670.7	725.1	795.3	879.4	983.5	1103.5	1212.9	1294.8	1337.7	1332.5
35°	590.5	638.6	691.6	759.2	858.3	977.4	1108.2	1214.1	1264.3	1255.1	1185.4
37.5°	557.7	598.2	650.3	724.3	833.7	964.8	1098.7	1178.1	1174.8	1099.7	998.8
40°	537.3	571.7	621.9	699.8	814.5	956.6	1083.6	1135.2	1091.5	986.7	865.8
42.5°	510.4	542.2	592.4	672.4	793.5	940.0	1055.0	1069.9	984.4	863.7	753.0
45°	469.0	497.0	548.8	631.5	762.0	903.7	985.0	948.4	833.3	708.6	624.3
47.5°	424.3	453.4	503.4	588.3	716.3	849.1	887.8	810.1	691.9	590.8	513.4
50°	396.2	424.2	473.0	558.7	685.5	804.3	820.4	720.0	611.4	522.5	459.0
52.5°	367.7	394.1	442.1	528.2	649.3	752.3	742.4	640.2	540.3	464.6	414.7
55°	325.5	350.4	396.2	476.8	587.1	668.7	632.8	535.2	452.5	393.8	355.9
57.5°	287.7	311.6	351.0	423.8	519.7	575.8	530.2	447.9	382.2	337.0	308.7
60°	262.0	283.1	320.7	388.3	471.6	514.3	469.2	396.5	341.2	305.0	279.7
62.5°	237.6	256.1	290.9	352.2	424.6	460.5	414.9	353.3	306.2	274.1	252.6
65°	200.8	217.6	248.3	296.1	355.5	379.4	340.2	290.3	253.8	229.9	215.5
67.5°	167.2	181.4	207.9	245.6	289.4	306.7	276.9	238.3	210.7	191.5	180.1
70°	144.8	157.1	177.9	210.4	250.0	263.3	235.3	203.6	183.4	168.0	157.5
72.5°	125.9	135.0	153.9	179.0	212.0	222.6	203.0	175.1	156.3	144.8	136.4
75°	95.9	103.4	115.7	135.9	158.8	165.0	150.3	132.9	120.2	112.0	105.5
77.5°	69.2	74.7	83.6	96.0	111.9	117.4	108.2	96.5	87.3	81.8	78.1
80°	52.3	56.7	64.2	74.5	84.0	87.1	81.6	72.8	66.3	63.2	60.1
82.5°	38.6	41.1	45.7	52.6	59.1	62.8	58.1	52.8	49.3	46.5	45.4
85°	19.4	20.9	22.9	25.6	29.7	31.1	29.3	28.0	25.9	24.3	24.3
87.5°	7.5	7.8	8.9	9.8	11.2	12.4	12.5	12.3	12.4	12.3	12.1
90°	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3	16.9
92.5°	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7	18.6
95°	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4	22.4
97.5°	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3	23.5
100°	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8	24.0
102.5°	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6	35.9
105°	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9	92.1
107.5°	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4	225.5
110°	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1	286.3





TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1	329.2
115°	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1	379.6
117.5°	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0	425.2
120°	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0	455.1
122.5°	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5	484.3
125°	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2	525.5
127.5°	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3	566.9
130°	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1	591.7
132.5°	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7	615.4
135°	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7	651.1
137.5°	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3	683.1
140°	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7	703.3
142.5°	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0	722.5
145°	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9	749.3
147.5°	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0	773.3
150°	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7	788.0
152.5°	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5	801.0
155°	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3	819.0
157.5°	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8	834.7
160°	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8	843.6
162.5°	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8	851.8
165°	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4	862.6
167.5°	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8	870.9
170°	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5	875.7
172.5°	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7	878.9
175°	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6	882.6
177.5°	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1	884.0
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	741.8	742.1	745.0	747.3	746.2	747.5	748.1
5°	810.4	822.7	829.2	834.0	834.4	834.6	837.4
7.5°	907.8	921.0	930.6	945.2	949.6	954.6	953.1
10°	978.8	998.3	1015.0	1023.9	1033.4	1047.4	1036.2
12.5°	1045.2	1079.7	1105.2	1118.9	1128.0	1130.8	1125.2
15°	1154.7	1199.8	1224.1	1223.3	1254.1	1267.4	1246.5
17.5°	1255.1	1296.7	1330.0	1347.1	1372.7	1378.4	1375.8
20°	1316.5	1362.0	1387.9	1417.3	1430.7	1442.6	1444.7
22.5°	1369.6	1410.3	1438.2	1462.7	1473.8	1479.4	1482.9
25°	1424.2	1456.3	1473.0	1481.5	1484.6	1483.9	1479.4
27.5°	1420.4	1422.8	1404.4	1386.3	1370.1	1351.8	1345.6
30°	1383.5	1354.8	1303.6	1274.5	1231.9	1198.0	1211.7
32.5°	1286.5	1229.4	1171.9	1108.4	1055.9	1041.0	1025.9
35°	1098.0	997.6	938.9	870.6	843.2	815.9	797.1
37.5°	888.3	810.7	740.9	696.2	668.9	651.7	642.3
40°	768.1	698.0	640.7	604.5	583.6	564.2	561.4
42.5°	672.2	607.1	563.9	535.1	515.1	506.8	500.8
45°	550.5	505.1	476.1	455.6	442.3	437.1	430.3
47.5°	466.0	433.9	412.1	398.1	388.1	384.2	383.7
50°	418.7	392.1	376.0	365.1	357.2	355.9	350.4
52.5°	383.2	360.1	347.6	338.0	332.3	328.5	326.9
55°	332.6	317.3	306.0	300.5	296.1	292.3	292.3
57.5°	291.1	278.2	270.7	266.1	264.7	262.1	260.4
60°	265.4	254.4	248.6	244.5	241.8	242.1	239.1
62.5°	240.2	233.1	227.6	223.5	220.3	220.3	220.5
65°	204.6	199.1	195.0	193.7	191.6	189.2	189.8
67.5°	173.3	168.3	165.1	162.7	162.0	160.7	162.7
70°	151.0	147.2	144.8	142.8	142.0	142.4	144.1
72.5°	130.5	127.8	126.3	125.3	123.8	123.9	125.0
75°	102.5	100.4	99.1	98.0	97.6	97.6	97.6
77.5°	75.3	74.8	74.2	72.7	72.8	73.1	73.2
80°	59.4	58.4	58.1	57.3	56.4	55.6	57.3
82.5°	44.4	43.3	43.1	42.9	41.3	41.2	42.6
85°	23.9	22.9	23.2	22.9	22.9	22.6	22.6
87.5°	11.9	11.8	11.6	11.9	11.8	11.5	12.1
90°	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	281.5	276.7	263.9	243.0	222.1	201.3	180.5



TEST NUMBER: P332126-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)