

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332130-940

Luminaire Tested: **S123DIW-S560D755U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332130-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D755U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4763.0 lumens  
Efficiency: N/A  
Efficacy: 126.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	44	39	37	35	31
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	54	48	66	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.8	1.6
10°-20°	211.3	4.4
20°-30°	312.1	6.6
30°-40°	364.6	7.7
40°-50°	366.5	7.7
50°-60°	322.0	6.8
60°-70°	239.9	5.0
70°-80°	136.7	2.9
80°-90°	41.7	0.9
90°-100°	32.1	0.7
100°-110°	153.0	3.2
110°-120°	367.6	7.7
120°-130°	468.1	9.8
130°-140°	500.2	10.5
140°-150°	467.7	9.8
150°-160°	377.3	7.9
160°-170°	243.5	5.1
170°-180°	83.9	1.8
0°-30°	598.2	12.6
0°-40°	962.8	20.2
0°-60°	1651.3	34.7
0°-90°	2069.6	43.5
90°-120°	552.8	11.6
90°-150°	1988.7	41.8
90°-180°	2693.0	56.5
0°-180°	4763.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	7	16	18	20	4
95°	40	15	20	25	25	49
105°	196	199	144	34	29	207
115°	367	371	377	383	386	362
125°	517	522	525	526	528	462
135°	644	648	650	652	650	495
145°	743	747	749	750	750	465
155°	818	817	818	821	817	377
165°	863	861	860	865	861	244
175°	883	880	881	885	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.3	14.2	14.1	14.1	14.2	14.4	14.6	14.9	15.2	15.2
90°	0.6	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3
92.5°	12.2	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7
95°	40.0	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4
97.5°	80.4	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3
100°	110.9	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8
102.5°	145.5	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6
105°	195.6	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9
107.5°	248.3	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4
110°	283.5	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1



TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.1	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1
115°	366.8	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1
117.5°	415.0	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0
120°	444.9	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0
122.5°	475.4	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5
125°	517.1	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2
127.5°	557.5	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3
130°	582.6	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1
132.5°	606.8	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7
135°	643.7	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7
137.5°	675.2	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3
140°	696.2	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7
142.5°	715.6	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0
145°	742.8	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9
147.5°	768.4	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0
150°	784.2	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7
152.5°	798.3	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5
155°	818.2	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3
157.5°	833.7	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8
160°	843.2	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8
162.5°	852.1	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8
165°	862.9	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4
167.5°	871.3	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8
170°	876.0	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5
172.5°	879.1	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7
175°	883.2	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6
177.5°	884.2	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	15.2	15.2	15.2	15.2	15.2	15.3	15.3	15.4
90°	16.9	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	18.6	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	22.4	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	23.5	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	24.0	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	35.9	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	92.1	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	225.5	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	286.3	281.5	276.7	263.9	243.0	222.1	201.3	180.5





TEST NUMBER: P332130-940

CATALOG NUMBER: S123DIW-S560D755U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.2	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	379.6	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	425.2	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	455.1	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	484.3	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.5	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	566.9	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	591.7	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.4	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.1	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.3	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.5	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.3	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.3	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.0	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.0	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.0	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	834.7	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	843.6	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	851.8	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	862.6	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	878.9	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	882.6	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.0	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)