

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332463

Luminaire Tested: **S123RDIW-S1000D1320U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332463
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8537.5 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17111	17111	17111	17111
5°	20398	17184	15132	17184
10°	25468	17086	13671	17086
15°	29895	16912	12467	16912
20°	33364	16651	11443	16651
25°	32831	16376	10815	16376
30°	23599	16122	10167	16122
35°	15757	15792	9747	15792
40°	11609	15396	9313	15396
45°	9738	14700	8888	14700
50°	8592	13788	8296	13788
55°	7535	12746	7484	12746
60°	6710	11750	6857	11750
65°	5894	10677	6378	10677
70°	4626	9725	5825	9725
75°	4076	8492	5319	8492
80°	3546	7215	5232	7215
85°	2853	5805	5545	5805



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	1.8
10°-20°	488.4	5.7
20°-30°	767.3	9.0
30°-40°	800.5	9.4
40°-50°	685.1	8.0
50°-60°	522.2	6.1
60°-70°	334.7	3.9
70°-80°	161.0	1.9
80°-90°	47.5	0.6
90°-100°	107.6	1.3
100°-110°	321.9	3.8
110°-120°	547.5	6.4
120°-130°	720.2	8.4
130°-140°	809.5	9.5
140°-150°	795.7	9.3
150°-160°	669.9	7.8
160°-170°	445.9	5.2
170°-180°	156.2	1.8
0°-30°	1412.0	16.5
0°-40°	2212.6	25.9
0°-60°	3419.8	40.1
0°-90°	3963.0	46.4
90°-120°	977.1	11.4
90°-150°	3302.5	38.7
90°-180°	4574.0	53.6
0°-180°	8537.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1888	1590	1400	1590	1888	195
15°	2683	1518	1119	1518	2683	761
25°	2764	1379	911	1379	2764	1188
35°	1199	1202	742	1202	1199	786
45°	640	966	584	966	640	503
55°	402	679	399	679	402	363
65°	231	419	250	419	231	228
75°	98	204	128	204	98	105
85°	23	47	45	47	23	28
90°	39	1	39	1	39	20
95°	101	76	101	76	101	104
105°	309	292	309	292	309	328
115°	552	551	552	551	552	547
125°	798	807	798	807	798	713
135°	1045	1047	1045	1047	1045	804
145°	1270	1270	1270	1270	1270	793
155°	1451	1454	1451	1454	1451	668
165°	1578	1584	1578	1584	1578	445
175°	1641	1647	1641	1647	1641	156
180°	1651	1651	1651	1651	1651	



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1693.2	1695.3	1688.3	1687.2	1679.0	1676.8	1676.8	1665.4	1658.3	1649.1	1643.6
5°	1887.8	1898.7	1893.2	1881.0	1860.6	1855.8	1842.9	1822.5	1799.3	1770.7	1757.1
7.5°	2130.9	2145.7	2140.0	2121.1	2099.7	2082.4	2046.0	2012.1	1964.6	1922.9	1887.3
10°	2330.1	2314.5	2302.2	2283.9	2264.1	2232.1	2194.0	2141.6	2081.1	2033.4	1980.4
12.5°	2479.3	2476.7	2461.2	2442.3	2414.4	2384.0	2337.2	2273.4	2203.0	2134.2	2073.4
15°	2682.7	2686.7	2676.5	2656.8	2617.3	2563.6	2492.8	2466.3	2365.5	2290.7	2215.8
17.5°	2823.4	2822.6	2821.2	2793.9	2753.6	2715.3	2649.7	2579.9	2488.7	2383.2	2282.4
20°	2912.7	2905.9	2907.2	2876.6	2846.7	2802.4	2738.5	2637.1	2562.2	2440.4	2336.3
22.5°	2910.5	2909.1	2914.3	2903.8	2882.1	2848.2	2797.8	2712.2	2616.6	2493.7	2376.6
25°	2764.3	2758.9	2790.9	2799.7	2834.4	2840.5	2825.6	2778.6	2688.1	2561.5	2416.6
27.5°	2313.5	2310.5	2369.9	2444.2	2538.4	2611.6	2682.4	2716.6	2688.1	2597.5	2452.2
30°	1898.7	1962.7	1992.6	2100.1	2219.9	2362.8	2488.0	2607.1	2636.4	2596.9	2477.8
32.5°	1576.4	1632.2	1657.2	1749.5	1861.1	2028.5	2216.4	2385.0	2504.1	2534.3	2462.6
35°	1199.1	1199.8	1256.9	1297.8	1401.2	1573.4	1755.8	1981.7	2206.3	2376.4	2394.1
37.5°	956.8	960.2	994.8	1035.5	1113.1	1204.1	1364.7	1552.6	1812.0	2073.2	2226.3
40°	826.2	832.3	858.2	898.3	954.1	1022.8	1148.1	1325.0	1541.4	1832.0	2069.5
42.5°	742.3	752.3	765.6	796.5	831.1	895.4	996.7	1133.4	1330.2	1605.0	1879.0
45°	639.7	645.1	655.4	669.6	700.9	745.9	813.9	905.8	1069.1	1290.3	1564.5
47.5°	564.3	561.4	572.2	583.8	604.6	635.2	680.8	755.8	872.3	1049.8	1282.4
50°	513.1	512.4	519.9	528.8	548.5	571.0	608.4	664.9	757.4	904.4	1117.4
52.5°	465.2	467.8	473.1	484.1	498.4	516.5	550.1	590.8	670.3	797.2	974.8
55°	401.5	403.6	411.0	417.2	427.4	445.7	466.8	500.9	555.3	643.8	790.1
57.5°	347.6	346.7	353.9	355.4	366.9	381.9	398.2	424.7	464.1	529.9	628.4
60°	311.7	309.6	315.8	320.5	326.7	338.9	352.5	378.4	409.7	458.0	542.4
62.5°	279.0	278.1	282.6	287.3	292.4	303.5	315.0	334.8	359.6	400.3	467.3
65°	231.4	233.4	235.5	237.5	240.2	247.0	257.9	271.5	288.5	317.1	365.4
67.5°	181.8	183.9	184.6	188.8	194.6	198.9	205.5	217.6	229.5	253.6	281.1
70°	147.0	146.3	147.0	149.0	156.5	164.0	172.9	181.7	189.2	206.2	229.3
72.5°	126.3	125.1	126.9	127.3	130.9	133.0	138.6	146.9	156.5	168.1	184.7
75°	98.0	98.0	98.0	98.0	100.7	102.1	104.1	106.2	109.6	115.0	127.3
77.5°	72.4	72.5	73.5	74.2	74.7	75.5	76.8	78.8	80.0	82.9	88.2
80°	57.2	57.8	57.2	57.8	57.8	59.2	59.9	61.9	62.6	66.0	68.1
82.5°	43.0	42.6	43.0	43.7	43.7	45.1	45.2	46.7	46.8	48.6	50.6
85°	23.1	21.8	23.1	22.5	23.8	22.5	23.1	24.5	24.5	25.2	27.9
87.5°	13.2	14.2	13.0	13.4	13.3	13.7	13.5	13.2	14.1	13.3	13.1
90°	38.9	38.3	37.8	37.2	36.6	35.7	34.6	33.4	32.3	31.1	27.4
92.5°	52.4	52.7	53.1	53.4	53.8	53.5	52.6	51.6	50.7	49.8	47.7
95°	101.2	101.2	101.2	101.2	101.2	100.6	99.4	98.3	97.1	96.0	93.7
97.5°	155.6	155.8	155.9	156.0	156.1	155.5	154.2	152.8	151.5	150.2	148.5
100°	197.1	196.6	196.0	195.4	194.8	194.1	193.2	192.4	191.5	190.7	189.2
102.5°	239.7	239.8	239.9	240.0	240.1	239.8	238.9	238.0	237.2	236.3	234.4
105°	308.7	308.1	307.5	307.0	306.4	306.1	306.1	306.1	306.1	306.1	303.5
107.5°	380.5	380.9	381.2	381.6	381.9	381.6	380.7	379.8	378.9	377.9	376.9
110°	429.3	429.9	430.5	431.0	431.6	431.3	430.2	429.0	427.9	426.7	426.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.2	481.3	481.4	481.5	481.6	481.0	479.6	478.2	476.9	475.5	475.4
115°	552.5	552.8	553.1	553.4	553.7	553.7	553.4	553.1	552.8	552.5	553.1
117.5°	624.9	625.7	626.5	627.3	628.1	628.5	628.6	628.7	628.7	628.8	629.5
120°	675.7	676.3	676.9	677.5	678.0	678.5	678.8	679.0	679.3	679.6	681.1
122.5°	724.5	725.3	726.1	726.9	727.7	728.5	729.2	730.0	730.7	731.5	732.2
125°	797.6	798.8	799.9	801.1	802.3	803.4	804.6	805.7	806.9	808.0	808.6
127.5°	870.5	871.9	873.2	874.5	875.8	877.3	878.9	880.5	882.1	883.8	884.4
130°	918.3	920.3	922.3	924.3	926.3	927.9	929.1	930.2	931.4	932.5	933.4
132.5°	968.1	969.6	971.2	972.7	974.3	975.8	977.1	978.5	979.9	981.3	981.9
135°	1045.4	1045.9	1046.5	1047.1	1047.7	1048.5	1049.7	1050.8	1052.0	1053.1	1053.4
137.5°	1113.6	1114.7	1115.8	1116.9	1118.0	1119.1	1120.3	1121.5	1122.7	1124.0	1123.2
140°	1158.2	1160.2	1162.2	1164.3	1166.3	1167.4	1167.7	1168.0	1168.3	1168.6	1168.3
142.5°	1203.9	1205.4	1207.0	1208.5	1210.1	1211.0	1211.3	1211.6	1211.9	1212.2	1211.6
145°	1269.7	1270.9	1272.0	1273.2	1274.4	1275.1	1275.4	1275.6	1275.9	1276.2	1275.4
147.5°	1328.4	1330.1	1331.8	1333.6	1335.3	1336.1	1336.1	1336.1	1336.1	1336.1	1335.3
150°	1365.7	1367.4	1369.2	1370.9	1372.6	1373.5	1373.5	1373.5	1373.5	1373.5	1372.9
152.5°	1402.0	1403.5	1405.0	1406.5	1408.0	1408.5	1408.1	1407.6	1407.2	1406.7	1406.4
155°	1451.3	1453.3	1455.4	1457.4	1459.4	1459.8	1458.7	1457.5	1456.4	1455.2	1454.9
157.5°	1496.2	1497.8	1499.4	1501.0	1502.6	1502.9	1501.6	1500.4	1499.2	1498.0	1497.8
160°	1525.2	1526.4	1527.6	1528.7	1529.9	1529.7	1528.3	1526.8	1525.4	1523.9	1523.9
162.5°	1547.0	1548.9	1550.7	1552.6	1554.4	1554.6	1553.2	1551.7	1550.3	1548.8	1548.6
165°	1578.4	1580.4	1582.5	1584.5	1586.5	1586.6	1584.9	1583.2	1581.4	1579.7	1579.7
167.5°	1605.1	1606.9	1608.7	1610.5	1612.3	1612.3	1610.5	1608.7	1606.9	1605.1	1604.9
170°	1618.6	1620.6	1622.7	1624.7	1626.7	1626.7	1624.7	1622.7	1620.6	1618.6	1618.6
172.5°	1629.0	1631.0	1633.0	1635.1	1637.1	1637.2	1635.4	1633.6	1631.8	1630.0	1630.0
175°	1640.7	1642.7	1644.7	1646.7	1648.7	1648.9	1647.2	1645.4	1643.7	1642.0	1642.0
177.5°	1646.9	1648.5	1650.1	1651.7	1653.4	1653.5	1652.1	1650.7	1649.3	1647.9	1647.9
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1641.4	1639.8	1632.2	1623.5	1612.0	1604.4	1598.4	1595.2	1585.4	1573.4	1565.2
5°	1742.8	1722.4	1700.7	1674.1	1649.6	1624.4	1608.8	1590.4	1567.9	1542.8	1525.1
7.5°	1851.5	1811.4	1768.3	1723.8	1679.8	1640.4	1605.5	1575.7	1539.9	1503.8	1478.5
10°	1934.8	1876.2	1815.7	1753.7	1697.2	1644.2	1603.3	1563.2	1520.3	1478.8	1447.5
12.5°	2010.4	1933.4	1863.6	1787.5	1715.2	1651.8	1593.0	1545.8	1494.2	1449.9	1414.3
15°	2106.2	2027.3	1942.9	1827.2	1731.3	1651.0	1579.5	1517.6	1455.0	1400.5	1365.8
17.5°	2195.8	2077.0	1963.6	1867.1	1742.4	1642.1	1554.9	1480.8	1412.1	1354.4	1311.7
20°	2232.8	2117.8	1994.6	1871.5	1749.0	1636.7	1535.3	1453.6	1382.2	1316.8	1277.4
22.5°	2255.1	2124.9	1995.2	1862.8	1732.6	1616.0	1515.7	1425.9	1348.4	1286.3	1237.6
25°	2281.1	2126.0	1983.1	1852.4	1719.7	1593.1	1474.0	1378.8	1295.1	1229.0	1177.3
27.5°	2298.3	2115.8	1946.9	1801.6	1667.0	1541.0	1431.8	1330.8	1245.9	1176.1	1120.6
30°	2301.6	2107.6	1919.1	1761.9	1625.1	1509.4	1393.7	1297.1	1207.3	1133.1	1081.4
32.5°	2305.9	2087.5	1881.5	1714.5	1574.5	1459.9	1355.1	1262.8	1170.8	1097.7	1044.9
35°	2288.0	2076.3	1824.5	1632.6	1492.4	1381.5	1286.9	1201.8	1111.3	1040.5	986.8
37.5°	2210.6	2032.1	1765.4	1540.3	1393.7	1291.0	1213.9	1139.8	1056.7	980.4	929.7
40°	2132.8	1988.5	1719.7	1484.2	1331.1	1225.6	1156.2	1095.7	1015.4	943.9	889.5
42.5°	2016.8	1929.2	1676.2	1425.4	1260.3	1158.7	1100.1	1043.4	972.9	900.3	849.2
45°	1804.1	1815.7	1587.0	1331.8	1162.3	1060.3	1005.1	965.7	903.1	843.2	790.8
47.5°	1537.3	1645.5	1482.3	1232.0	1059.0	963.2	915.0	880.6	838.4	779.6	731.8
50°	1363.1	1517.6	1398.5	1165.1	994.3	899.0	851.3	823.4	786.7	740.4	694.8
52.5°	1202.5	1368.4	1297.2	1090.5	924.0	836.9	790.4	767.4	738.2	694.7	653.4
55°	980.6	1148.7	1132.4	977.9	818.7	740.4	705.0	679.2	659.4	626.8	594.1
57.5°	793.2	952.6	961.0	852.7	725.9	648.5	618.1	598.6	585.7	561.0	530.8
60°	675.1	821.4	850.0	768.3	659.4	591.4	561.4	545.8	535.6	515.8	492.7
62.5°	577.1	701.6	734.0	675.2	595.7	532.0	508.6	493.5	486.6	469.6	449.2
65°	441.7	545.1	576.4	543.7	502.2	451.2	432.1	419.2	413.1	403.6	388.6
67.5°	332.1	407.5	441.8	418.8	403.8	371.6	359.5	352.5	347.1	340.5	328.0
70°	266.8	322.6	358.0	351.8	339.6	322.6	313.7	309.0	303.5	298.1	287.2
72.5°	214.5	252.9	286.1	289.2	279.2	275.8	268.0	266.0	262.7	256.2	250.2
75°	142.2	168.8	191.9	200.8	204.8	208.2	204.8	204.2	203.5	198.0	194.6
77.5°	93.2	107.5	122.1	137.2	143.6	148.2	149.3	151.8	150.0	147.1	145.5
80°	71.5	74.9	85.1	98.0	108.2	112.3	115.0	116.4	115.7	115.0	112.3
82.5°	51.9	54.7	59.5	68.6	77.2	84.0	85.6	85.3	86.8	87.2	85.1
85°	27.9	28.6	29.9	31.3	36.1	43.6	45.6	47.0	48.3	48.3	44.2
87.5°	13.4	12.1	12.5	11.8	12.9	12.8	15.5	17.7	18.8	17.2	17.8
90°	23.6	19.9	16.1	12.8	9.9	7.1	4.2	1.3	4.2	7.1	9.9
92.5°	45.5	43.4	41.3	39.2	37.3	35.3	33.3	31.4	33.3	35.3	37.3
95°	91.4	89.1	86.8	84.6	82.6	80.6	78.5	76.5	78.5	80.6	82.6
97.5°	146.8	145.2	143.5	141.9	140.4	138.9	137.4	135.9	137.4	138.9	140.4
100°	187.8	186.3	184.9	183.3	181.6	179.8	178.1	176.4	178.1	179.8	181.6
102.5°	232.5	230.6	228.7	227.2	226.2	225.2	224.1	223.1	224.1	225.2	226.2
105°	300.9	298.3	295.7	294.1	293.5	293.0	292.4	291.8	292.4	293.0	293.5
107.5°	375.9	374.8	373.8	373.1	372.8	372.4	372.1	371.7	372.1	372.4	372.8
110°	425.6	425.0	424.4	423.8	423.2	422.7	422.1	421.5	422.1	422.7	423.2



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	475.2	475.1	475.0	474.8	474.4	474.1	473.7	473.4	473.7	474.1	474.4
115°	553.7	554.2	554.8	554.7	553.8	552.9	552.1	551.2	552.1	552.9	553.8
117.5°	630.3	631.0	631.8	631.9	631.3	630.7	630.1	629.6	630.1	630.7	631.3
120°	682.5	683.9	685.4	685.2	683.5	681.8	680.0	678.3	680.0	681.8	683.5
122.5°	733.0	733.7	734.5	734.2	733.0	731.7	730.4	729.2	730.4	731.7	733.0
125°	809.2	809.7	810.3	810.2	809.3	808.4	807.6	806.7	807.6	808.4	809.3
127.5°	885.0	885.7	886.3	885.7	883.8	882.0	880.2	878.3	880.2	882.0	883.8
130°	934.3	935.1	936.0	935.3	933.0	930.7	928.3	926.0	928.3	930.7	933.0
132.5°	982.6	983.2	983.8	983.0	980.7	978.4	976.1	973.8	976.1	978.4	980.7
135°	1053.7	1054.0	1054.3	1053.6	1051.8	1050.1	1048.4	1046.7	1048.4	1050.1	1051.8
137.5°	1122.5	1121.7	1121.0	1119.9	1118.4	1117.0	1115.5	1114.1	1115.5	1117.0	1118.4
140°	1168.0	1167.7	1167.4	1166.6	1165.1	1163.7	1162.2	1160.8	1162.2	1163.7	1165.1
142.5°	1211.1	1210.6	1210.1	1209.1	1207.7	1206.2	1204.8	1203.3	1204.8	1206.2	1207.7
145°	1274.5	1273.6	1272.8	1272.0	1271.5	1270.9	1270.3	1269.7	1270.3	1270.9	1271.5
147.5°	1334.5	1333.7	1332.9	1332.0	1331.0	1329.9	1328.9	1327.8	1328.9	1329.9	1331.0
150°	1372.3	1371.8	1371.2	1370.6	1370.0	1369.5	1368.9	1368.3	1368.9	1369.5	1370.0
152.5°	1406.0	1405.7	1405.3	1404.7	1403.9	1403.1	1402.3	1401.5	1402.3	1403.1	1403.9
155°	1454.6	1454.3	1454.1	1453.9	1453.9	1453.9	1453.9	1453.9	1453.9	1453.9	1453.9
157.5°	1497.5	1497.3	1497.1	1497.1	1497.5	1497.8	1498.2	1498.5	1498.2	1497.8	1497.5
160°	1523.9	1523.9	1523.9	1524.2	1524.8	1525.4	1526.0	1526.5	1526.0	1525.4	1524.8
162.5°	1548.4	1548.2	1547.9	1548.2	1549.0	1549.8	1550.6	1551.4	1550.6	1549.8	1549.0
165°	1579.7	1579.7	1579.7	1580.2	1581.0	1581.9	1582.7	1583.6	1582.7	1581.9	1581.0
167.5°	1604.7	1604.4	1604.2	1604.7	1605.8	1607.0	1608.1	1609.3	1608.1	1607.0	1605.8
170°	1618.6	1618.6	1618.6	1619.2	1620.4	1621.5	1622.7	1623.8	1622.7	1621.5	1620.4
172.5°	1630.0	1630.0	1630.0	1630.6	1631.8	1632.9	1634.1	1635.2	1634.1	1632.9	1631.8
175°	1642.0	1642.0	1642.0	1642.5	1643.7	1644.9	1646.0	1647.2	1646.0	1644.9	1643.7
177.5°	1647.9	1647.9	1647.9	1648.4	1649.3	1650.2	1651.2	1652.1	1651.2	1650.2	1649.3
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1562.5	1555.4	1550.5	1539.6	1532.6	1524.9	1517.3	1522.2	1521.7	1521.1	1521.1
5°	1510.1	1494.4	1480.2	1461.8	1450.2	1435.9	1425.0	1423.7	1426.4	1416.9	1411.4
7.5°	1458.1	1436.7	1416.5	1396.2	1374.7	1357.5	1346.8	1341.7	1334.8	1328.9	1322.8
10°	1421.6	1396.5	1376.7	1351.5	1328.4	1308.0	1295.1	1286.2	1281.4	1276.7	1267.8
12.5°	1384.1	1359.4	1334.3	1305.8	1283.8	1260.1	1250.4	1240.5	1231.4	1226.0	1213.9
15°	1329.1	1297.1	1270.6	1240.6	1216.1	1193.0	1179.4	1159.6	1156.9	1150.1	1137.9
17.5°	1274.0	1239.2	1202.6	1180.5	1152.8	1128.7	1108.0	1101.4	1081.9	1074.6	1063.9
20°	1230.4	1198.4	1170.5	1141.3	1101.1	1078.6	1062.3	1053.5	1037.8	1028.3	1021.5
22.5°	1192.8	1160.3	1128.1	1093.9	1060.8	1035.6	1023.7	1009.9	1001.3	988.0	980.6
25°	1139.2	1103.8	1065.0	1028.3	1004.5	985.4	966.4	954.1	941.9	935.7	922.1
27.5°	1076.9	1039.9	1003.6	975.7	946.5	927.7	910.4	899.5	884.8	874.5	867.0
30°	1042.6	999.0	967.7	942.5	905.1	887.4	874.5	860.9	850.0	839.1	831.6
32.5°	1002.8	963.1	933.4	902.3	873.5	854.2	837.5	825.5	816.2	805.9	798.4
35°	940.5	907.2	876.5	845.2	824.1	804.4	784.7	774.4	765.6	756.1	749.3
37.5°	884.1	853.0	823.9	794.2	768.0	752.0	736.1	728.3	716.3	709.9	703.0
40°	849.3	818.7	787.4	758.8	731.6	719.3	705.0	693.5	682.6	677.8	670.3
42.5°	811.2	780.6	754.2	723.4	701.1	684.5	671.3	658.6	650.5	643.5	639.3
45°	754.7	727.5	701.6	671.0	649.9	635.6	620.6	609.1	601.6	596.8	589.3
47.5°	699.9	672.6	646.4	619.7	599.3	582.9	568.0	559.9	550.0	544.2	539.1
50°	660.1	635.6	607.7	583.2	562.8	546.5	534.2	524.0	515.2	507.7	504.3
52.5°	623.6	597.5	573.4	550.6	529.0	510.5	499.4	488.6	482.0	473.4	469.4
55°	563.5	538.3	517.9	495.4	474.3	458.7	445.1	435.5	428.7	419.2	413.8
57.5°	507.0	484.4	460.0	440.6	418.8	405.6	394.3	381.4	373.1	365.6	360.3
60°	468.9	443.0	421.9	403.6	384.5	367.5	357.3	347.1	338.2	330.7	326.0
62.5°	429.1	406.6	386.5	366.5	349.1	334.3	322.4	313.9	306.1	301.3	296.6
65°	368.2	350.5	330.1	313.7	297.4	286.5	277.0	269.5	264.0	260.6	256.6
67.5°	312.1	294.9	277.1	261.1	250.2	241.9	235.6	229.2	226.5	222.1	219.4
70°	275.6	257.9	242.3	230.0	219.1	213.0	208.9	204.2	201.4	196.0	193.3
72.5°	235.9	223.1	211.8	201.7	193.0	187.4	182.2	176.4	172.0	166.0	163.3
75°	185.8	174.2	165.4	158.6	153.1	145.6	138.1	132.0	130.0	127.9	127.3
77.5°	137.6	130.3	123.9	118.1	111.3	105.9	104.3	102.9	102.5	101.4	101.4
80°	108.2	101.4	96.6	89.8	85.7	85.7	85.7	84.4	85.1	85.1	85.1
82.5°	80.4	74.2	71.6	69.1	68.3	68.9	68.9	69.1	68.7	69.8	69.3
85°	41.5	42.2	43.6	42.9	43.6	43.6	44.9	44.2	44.9	43.6	44.9
87.5°	17.8	20.1	21.4	22.7	24.0	24.2	25.0	25.2	26.0	26.2	26.4
90°	12.8	16.1	19.9	23.6	27.4	31.1	32.3	33.4	34.6	35.7	36.6
92.5°	39.2	41.3	43.4	45.5	47.7	49.8	50.7	51.6	52.6	53.5	53.8
95°	84.6	86.8	89.1	91.4	93.7	96.0	97.1	98.3	99.4	100.6	101.2
97.5°	141.9	143.5	145.2	146.8	148.5	150.2	151.5	152.8	154.2	155.5	156.1
100°	183.3	184.9	186.3	187.8	189.2	190.7	191.5	192.4	193.2	194.1	194.8
102.5°	227.2	228.7	230.6	232.5	234.4	236.3	237.2	238.0	238.9	239.8	240.1
105°	294.1	295.7	298.3	300.9	303.5	306.1	306.1	306.1	306.1	306.1	306.4
107.5°	373.1	373.8	374.8	375.9	376.9	377.9	378.9	379.8	380.7	381.6	381.9
110°	423.8	424.4	425.0	425.6	426.1	426.7	427.9	429.0	430.2	431.3	431.6



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	474.8	475.0	475.1	475.2	475.4	475.5	476.9	478.2	479.6	481.0	481.6
115°	554.7	554.8	554.2	553.7	553.1	552.5	552.8	553.1	553.4	553.7	553.7
117.5°	631.9	631.8	631.0	630.3	629.5	628.8	628.7	628.7	628.6	628.5	628.1
120°	685.2	685.4	683.9	682.5	681.1	679.6	679.3	679.0	678.8	678.5	678.0
122.5°	734.2	734.5	733.7	733.0	732.2	731.5	730.7	730.0	729.2	728.5	727.7
125°	810.2	810.3	809.7	809.2	808.6	808.0	806.9	805.7	804.6	803.4	802.3
127.5°	885.7	886.3	885.7	885.0	884.4	883.8	882.1	880.5	878.9	877.3	875.8
130°	935.3	936.0	935.1	934.3	933.4	932.5	931.4	930.2	929.1	927.9	926.3
132.5°	983.0	983.8	983.2	982.6	981.9	981.3	979.9	978.5	977.1	975.8	974.3
135°	1053.6	1054.3	1054.0	1053.7	1053.4	1053.1	1052.0	1050.8	1049.7	1048.5	1047.7
137.5°	1119.9	1121.0	1121.7	1122.5	1123.2	1124.0	1122.7	1121.5	1120.3	1119.1	1118.0
140°	1166.6	1167.4	1167.7	1168.0	1168.3	1168.6	1168.3	1168.0	1167.7	1167.4	1166.3
142.5°	1209.1	1210.1	1210.6	1211.1	1211.6	1212.2	1211.9	1211.6	1211.3	1211.0	1210.1
145°	1272.0	1272.8	1273.6	1274.5	1275.4	1276.2	1275.9	1275.6	1275.4	1275.1	1274.4
147.5°	1332.0	1332.9	1333.7	1334.5	1335.3	1336.1	1336.1	1336.1	1336.1	1336.1	1335.3
150°	1370.6	1371.2	1371.8	1372.3	1372.9	1373.5	1373.5	1373.5	1373.5	1373.5	1372.6
152.5°	1404.7	1405.3	1405.7	1406.0	1406.4	1406.7	1407.2	1407.6	1408.1	1408.5	1408.0
155°	1453.9	1454.1	1454.3	1454.6	1454.9	1455.2	1456.4	1457.5	1458.7	1459.8	1459.4
157.5°	1497.1	1497.1	1497.3	1497.5	1497.8	1498.0	1499.2	1500.4	1501.6	1502.9	1502.6
160°	1524.2	1523.9	1523.9	1523.9	1523.9	1523.9	1525.4	1526.8	1528.3	1529.7	1529.9
162.5°	1548.2	1547.9	1548.2	1548.4	1548.6	1548.8	1550.3	1551.7	1553.2	1554.6	1554.4
165°	1580.2	1579.7	1579.7	1579.7	1579.7	1579.7	1581.4	1583.2	1584.9	1586.6	1586.5
167.5°	1604.7	1604.2	1604.4	1604.7	1604.9	1605.1	1606.9	1608.7	1610.5	1612.3	1612.3
170°	1619.2	1618.6	1618.6	1618.6	1618.6	1618.6	1620.6	1622.7	1624.7	1626.7	1626.7
172.5°	1630.6	1630.0	1630.0	1630.0	1630.0	1630.0	1631.8	1633.6	1635.4	1637.2	1637.1
175°	1642.5	1642.0	1642.0	1642.0	1642.0	1642.0	1643.7	1645.4	1647.2	1648.9	1648.7
177.5°	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.3	1650.7	1652.1	1653.5	1653.4
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1514.6	1514.0	1514.6	1512.4	1514.6	1514.0	1514.6	1521.1	1521.1	1521.7	1522.2
5°	1409.4	1408.7	1406.7	1400.5	1406.7	1408.7	1409.4	1411.4	1416.9	1426.4	1423.7
7.5°	1317.5	1316.6	1310.6	1310.7	1310.6	1316.6	1317.5	1322.8	1328.9	1334.8	1341.7
10°	1263.1	1263.7	1255.6	1250.8	1255.6	1263.7	1263.1	1267.8	1276.7	1281.4	1286.2
12.5°	1210.3	1207.1	1200.6	1195.3	1200.6	1207.1	1210.3	1213.9	1226.0	1231.4	1240.5
15°	1140.6	1133.8	1117.4	1118.8	1117.4	1133.8	1140.6	1137.9	1150.1	1156.9	1159.6
17.5°	1058.5	1053.5	1053.2	1043.7	1053.2	1053.5	1058.5	1063.9	1074.6	1081.9	1101.4
20°	1010.6	1007.2	1008.5	999.0	1008.5	1007.2	1010.6	1021.5	1028.3	1037.8	1053.5
22.5°	973.0	969.6	963.9	960.9	963.9	969.6	973.0	980.6	988.0	1001.3	1009.9
25°	918.0	912.6	907.2	910.6	907.2	912.6	918.0	922.1	935.7	941.9	954.1
27.5°	863.1	859.0	853.5	852.8	853.5	859.0	863.1	867.0	874.5	884.8	899.5
30°	828.2	824.1	821.4	818.0	821.4	824.1	828.2	831.6	839.1	850.0	860.9
32.5°	792.8	792.0	787.1	786.4	787.1	792.0	792.8	798.4	805.9	816.2	825.5
35°	746.5	742.5	741.1	741.8	741.1	742.5	746.5	749.3	756.1	765.6	774.4
37.5°	702.6	697.1	694.7	692.2	694.7	697.1	702.6	703.0	709.9	716.3	728.3
40°	671.0	665.6	664.2	662.8	664.2	665.6	671.0	670.3	677.8	682.6	693.5
42.5°	635.6	633.4	632.6	630.2	632.6	633.4	635.6	639.3	643.5	650.5	658.6
45°	587.3	586.6	582.5	583.9	582.5	586.6	587.3	589.3	596.8	601.6	609.1
47.5°	536.4	533.4	530.5	532.4	530.5	533.4	536.4	539.1	544.2	550.0	559.9
50°	501.6	500.2	494.1	495.4	494.1	500.2	501.6	504.3	507.7	515.2	524.0
52.5°	466.7	461.5	459.2	458.4	459.2	461.5	466.7	469.4	473.4	482.0	488.6
55°	409.0	402.9	400.2	398.8	400.2	402.9	409.0	413.8	419.2	428.7	435.5
57.5°	352.4	350.7	348.6	350.1	348.6	350.7	352.4	360.3	365.6	373.1	381.4
60°	319.2	319.2	319.2	318.5	319.2	319.2	319.2	326.0	330.7	338.2	347.1
62.5°	293.6	291.9	291.4	292.4	291.4	291.9	293.6	296.6	301.3	306.1	313.9
65°	254.5	253.8	251.1	250.4	251.1	253.8	254.5	256.6	260.6	264.0	269.5
67.5°	217.6	215.2	214.4	213.4	214.4	215.2	217.6	219.4	222.1	226.5	229.2
70°	189.9	188.5	184.4	185.1	184.4	188.5	189.9	193.3	196.0	201.4	204.2
72.5°	159.9	158.6	157.7	156.8	157.7	158.6	159.9	163.3	166.0	172.0	176.4
75°	126.6	125.9	125.2	127.9	125.2	125.9	126.6	127.3	127.9	130.0	132.0
77.5°	101.4	101.4	101.8	100.7	101.8	101.4	101.4	101.4	101.4	102.5	102.9
80°	85.1	85.1	84.4	84.4	84.4	85.1	85.1	85.1	85.1	85.1	84.4
82.5°	68.2	68.7	69.1	68.1	69.1	68.7	68.2	69.3	69.8	68.7	69.1
85°	44.9	44.2	45.6	44.9	45.6	44.2	44.9	44.9	43.6	44.9	44.2
87.5°	27.6	26.6	26.7	27.4	26.7	26.6	27.6	26.4	26.2	26.0	25.2
90°	37.2	37.8	38.3	38.9	38.3	37.8	37.2	36.6	35.7	34.6	33.4
92.5°	53.4	53.1	52.7	52.4	52.7	53.1	53.4	53.8	53.5	52.6	51.6
95°	101.2	101.2	101.2	101.2	101.2	101.2	101.2	101.2	100.6	99.4	98.3
97.5°	156.0	155.9	155.8	155.6	155.8	155.9	156.0	156.1	155.5	154.2	152.8
100°	195.4	196.0	196.6	197.1	196.6	196.0	195.4	194.8	194.1	193.2	192.4
102.5°	240.0	239.9	239.8	239.7	239.8	239.9	240.0	240.1	239.8	238.9	238.0
105°	307.0	307.5	308.1	308.7	308.1	307.5	307.0	306.4	306.1	306.1	306.1
107.5°	381.6	381.2	380.9	380.5	380.9	381.2	381.6	381.9	381.6	380.7	379.8
110°	431.0	430.5	429.9	429.3	429.9	430.5	431.0	431.6	431.3	430.2	429.0



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	481.5	481.4	481.3	481.2	481.3	481.4	481.5	481.6	481.0	479.6	478.2
115°	553.4	553.1	552.8	552.5	552.8	553.1	553.4	553.7	553.7	553.4	553.1
117.5°	627.3	626.5	625.7	624.9	625.7	626.5	627.3	628.1	628.5	628.6	628.7
120°	677.5	676.9	676.3	675.7	676.3	676.9	677.5	678.0	678.5	678.8	679.0
122.5°	726.9	726.1	725.3	724.5	725.3	726.1	726.9	727.7	728.5	729.2	730.0
125°	801.1	799.9	798.8	797.6	798.8	799.9	801.1	802.3	803.4	804.6	805.7
127.5°	874.5	873.2	871.9	870.5	871.9	873.2	874.5	875.8	877.3	878.9	880.5
130°	924.3	922.3	920.3	918.3	920.3	922.3	924.3	926.3	927.9	929.1	930.2
132.5°	972.7	971.2	969.6	968.1	969.6	971.2	972.7	974.3	975.8	977.1	978.5
135°	1047.1	1046.5	1045.9	1045.4	1045.9	1046.5	1047.1	1047.7	1048.5	1049.7	1050.8
137.5°	1116.9	1115.8	1114.7	1113.6	1114.7	1115.8	1116.9	1118.0	1119.1	1120.3	1121.5
140°	1164.3	1162.2	1160.2	1158.2	1160.2	1162.2	1164.3	1166.3	1167.4	1167.7	1168.0
142.5°	1208.5	1207.0	1205.4	1203.9	1205.4	1207.0	1208.5	1210.1	1211.0	1211.3	1211.6
145°	1273.2	1272.0	1270.9	1269.7	1270.9	1272.0	1273.2	1274.4	1275.1	1275.4	1275.6
147.5°	1333.6	1331.8	1330.1	1328.4	1330.1	1331.8	1333.6	1335.3	1336.1	1336.1	1336.1
150°	1370.9	1369.2	1367.4	1365.7	1367.4	1369.2	1370.9	1372.6	1373.5	1373.5	1373.5
152.5°	1406.5	1405.0	1403.5	1402.0	1403.5	1405.0	1406.5	1408.0	1408.5	1408.1	1407.6
155°	1457.4	1455.4	1453.3	1451.3	1453.3	1455.4	1457.4	1459.4	1459.8	1458.7	1457.5
157.5°	1501.0	1499.4	1497.8	1496.2	1497.8	1499.4	1501.0	1502.6	1502.9	1501.6	1500.4
160°	1528.7	1527.6	1526.4	1525.2	1526.4	1527.6	1528.7	1529.9	1529.7	1528.3	1526.8
162.5°	1552.6	1550.7	1548.9	1547.0	1548.9	1550.7	1552.6	1554.4	1554.6	1553.2	1551.7
165°	1584.5	1582.5	1580.4	1578.4	1580.4	1582.5	1584.5	1586.5	1586.6	1584.9	1583.2
167.5°	1610.5	1608.7	1606.9	1605.1	1606.9	1608.7	1610.5	1612.3	1612.3	1610.5	1608.7
170°	1624.7	1622.7	1620.6	1618.6	1620.6	1622.7	1624.7	1626.7	1626.7	1624.7	1622.7
172.5°	1635.1	1633.0	1631.0	1629.0	1631.0	1633.0	1635.1	1637.1	1637.2	1635.4	1633.6
175°	1646.7	1644.7	1642.7	1640.7	1642.7	1644.7	1646.7	1648.7	1648.9	1647.2	1645.4
177.5°	1651.7	1650.1	1648.5	1646.9	1648.5	1650.1	1651.7	1653.4	1653.5	1652.1	1650.7
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1517.3	1524.9	1532.6	1539.6	1550.5	1555.4	1562.5	1565.2	1573.4	1585.4	1595.2
5°	1425.0	1435.9	1450.2	1461.8	1480.2	1494.4	1510.1	1525.1	1542.8	1567.9	1590.4
7.5°	1346.8	1357.5	1374.7	1396.2	1416.5	1436.7	1458.1	1478.5	1503.8	1539.9	1575.7
10°	1295.1	1308.0	1328.4	1351.5	1376.7	1396.5	1421.6	1447.5	1478.8	1520.3	1563.2
12.5°	1250.4	1260.1	1283.8	1305.8	1334.3	1359.4	1384.1	1414.3	1449.9	1494.2	1545.8
15°	1179.4	1193.0	1216.1	1240.6	1270.6	1297.1	1329.1	1365.8	1400.5	1455.0	1517.6
17.5°	1108.0	1128.7	1152.8	1180.5	1202.6	1239.2	1274.0	1311.7	1354.4	1412.1	1480.8
20°	1062.3	1078.6	1101.1	1141.3	1170.5	1198.4	1230.4	1277.4	1316.8	1382.2	1453.6
22.5°	1023.7	1035.6	1060.8	1093.9	1128.1	1160.3	1192.8	1237.6	1286.3	1348.4	1425.9
25°	966.4	985.4	1004.5	1028.3	1065.0	1103.8	1139.2	1177.3	1229.0	1295.1	1378.8
27.5°	910.4	927.7	946.5	975.7	1003.6	1039.9	1076.9	1120.6	1176.1	1245.9	1330.8
30°	874.5	887.4	905.1	942.5	967.7	999.0	1042.6	1081.4	1133.1	1207.3	1297.1
32.5°	837.5	854.2	873.5	902.3	933.4	963.1	1002.8	1044.9	1097.7	1170.8	1262.8
35°	784.7	804.4	824.1	845.2	876.5	907.2	940.5	986.8	1040.5	1111.3	1201.8
37.5°	736.1	752.0	768.0	794.2	823.9	853.0	884.1	929.7	980.4	1056.7	1139.8
40°	705.0	719.3	731.6	758.8	787.4	818.7	849.3	889.5	943.9	1015.4	1095.7
42.5°	671.3	684.5	701.1	723.4	754.2	780.6	811.2	849.2	900.3	972.9	1043.4
45°	620.6	635.6	649.9	671.0	701.6	727.5	754.7	790.8	843.2	903.1	965.7
47.5°	568.0	582.9	599.3	619.7	646.4	672.6	699.9	731.8	779.6	838.4	880.6
50°	534.2	546.5	562.8	583.2	607.7	635.6	660.1	694.8	740.4	786.7	823.4
52.5°	499.4	510.5	529.0	550.6	573.4	597.5	623.6	653.4	694.7	738.2	767.4
55°	445.1	458.7	474.3	495.4	517.9	538.3	563.5	594.1	626.8	659.4	679.2
57.5°	394.3	405.6	418.8	440.6	460.0	484.4	507.0	530.8	561.0	585.7	598.6
60°	357.3	367.5	384.5	403.6	421.9	443.0	468.9	492.7	515.8	535.6	545.8
62.5°	322.4	334.3	349.1	366.5	386.5	406.6	429.1	449.2	469.6	486.6	493.5
65°	277.0	286.5	297.4	313.7	330.1	350.5	368.2	388.6	403.6	413.1	419.2
67.5°	235.6	241.9	250.2	261.1	277.1	294.9	312.1	328.0	340.5	347.1	352.5
70°	208.9	213.0	219.1	230.0	242.3	257.9	275.6	287.2	298.1	303.5	309.0
72.5°	182.2	187.4	193.0	201.7	211.8	223.1	235.9	250.2	256.2	262.7	266.0
75°	138.1	145.6	153.1	158.6	165.4	174.2	185.8	194.6	198.0	203.5	204.2
77.5°	104.3	105.9	111.3	118.1	123.9	130.3	137.6	145.5	147.1	150.0	151.8
80°	85.7	85.7	85.7	89.8	96.6	101.4	108.2	112.3	115.0	115.7	116.4
82.5°	68.9	68.9	68.3	69.1	71.6	74.2	80.4	85.1	87.2	86.8	85.3
85°	44.9	43.6	43.6	42.9	43.6	42.2	41.5	44.2	48.3	48.3	47.0
87.5°	25.0	24.2	24.0	22.7	21.4	20.1	17.8	17.8	17.2	18.8	17.7
90°	32.3	31.1	27.4	23.6	19.9	16.1	12.8	9.9	7.1	4.2	1.3
92.5°	50.7	49.8	47.7	45.5	43.4	41.3	39.2	37.3	35.3	33.3	31.4
95°	97.1	96.0	93.7	91.4	89.1	86.8	84.6	82.6	80.6	78.5	76.5
97.5°	151.5	150.2	148.5	146.8	145.2	143.5	141.9	140.4	138.9	137.4	135.9
100°	191.5	190.7	189.2	187.8	186.3	184.9	183.3	181.6	179.8	178.1	176.4
102.5°	237.2	236.3	234.4	232.5	230.6	228.7	227.2	226.2	225.2	224.1	223.1
105°	306.1	306.1	303.5	300.9	298.3	295.7	294.1	293.5	293.0	292.4	291.8
107.5°	378.9	377.9	376.9	375.9	374.8	373.8	373.1	372.8	372.4	372.1	371.7
110°	427.9	426.7	426.1	425.6	425.0	424.4	423.8	423.2	422.7	422.1	421.5



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	476.9	475.5	475.4	475.2	475.1	475.0	474.8	474.4	474.1	473.7	473.4
115°	552.8	552.5	553.1	553.7	554.2	554.8	554.7	553.8	552.9	552.1	551.2
117.5°	628.7	628.8	629.5	630.3	631.0	631.8	631.9	631.3	630.7	630.1	629.6
120°	679.3	679.6	681.1	682.5	683.9	685.4	685.2	683.5	681.8	680.0	678.3
122.5°	730.7	731.5	732.2	733.0	733.7	734.5	734.2	733.0	731.7	730.4	729.2
125°	806.9	808.0	808.6	809.2	809.7	810.3	810.2	809.3	808.4	807.6	806.7
127.5°	882.1	883.8	884.4	885.0	885.7	886.3	885.7	883.8	882.0	880.2	878.3
130°	931.4	932.5	933.4	934.3	935.1	936.0	935.3	933.0	930.7	928.3	926.0
132.5°	979.9	981.3	981.9	982.6	983.2	983.8	983.0	980.7	978.4	976.1	973.8
135°	1052.0	1053.1	1053.4	1053.7	1054.0	1054.3	1053.6	1051.8	1050.1	1048.4	1046.7
137.5°	1122.7	1124.0	1123.2	1122.5	1121.7	1121.0	1119.9	1118.4	1117.0	1115.5	1114.1
140°	1168.3	1168.6	1168.3	1168.0	1167.7	1167.4	1166.6	1165.1	1163.7	1162.2	1160.8
142.5°	1211.9	1212.2	1211.6	1211.1	1210.6	1210.1	1209.1	1207.7	1206.2	1204.8	1203.3
145°	1275.9	1276.2	1275.4	1274.5	1273.6	1272.8	1272.0	1271.5	1270.9	1270.3	1269.7
147.5°	1336.1	1336.1	1335.3	1334.5	1333.7	1332.9	1332.0	1331.0	1329.9	1328.9	1327.8
150°	1373.5	1373.5	1372.9	1372.3	1371.8	1371.2	1370.6	1370.0	1369.5	1368.9	1368.3
152.5°	1407.2	1406.7	1406.4	1406.0	1405.7	1405.3	1404.7	1403.9	1403.1	1402.3	1401.5
155°	1456.4	1455.2	1454.9	1454.6	1454.3	1454.1	1453.9	1453.9	1453.9	1453.9	1453.9
157.5°	1499.2	1498.0	1497.8	1497.5	1497.3	1497.1	1497.1	1497.5	1497.8	1498.2	1498.5
160°	1525.4	1523.9	1523.9	1523.9	1523.9	1523.9	1524.2	1524.8	1525.4	1526.0	1526.5
162.5°	1550.3	1548.8	1548.6	1548.4	1548.2	1547.9	1548.2	1549.0	1549.8	1550.6	1551.4
165°	1581.4	1579.7	1579.7	1579.7	1579.7	1579.7	1580.2	1581.0	1581.9	1582.7	1583.6
167.5°	1606.9	1605.1	1604.9	1604.7	1604.4	1604.2	1604.7	1605.8	1607.0	1608.1	1609.3
170°	1620.6	1618.6	1618.6	1618.6	1618.6	1618.6	1619.2	1620.4	1621.5	1622.7	1623.8
172.5°	1631.8	1630.0	1630.0	1630.0	1630.0	1630.0	1630.6	1631.8	1632.9	1634.1	1635.2
175°	1643.7	1642.0	1642.0	1642.0	1642.0	1642.0	1642.5	1643.7	1644.9	1646.0	1647.2
177.5°	1649.3	1647.9	1647.9	1647.9	1647.9	1647.9	1648.4	1649.3	1650.2	1651.2	1652.1
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1598.4	1604.4	1612.0	1623.5	1632.2	1639.8	1641.4	1643.6	1649.1	1658.3	1665.4
5°	1608.8	1624.4	1649.6	1674.1	1700.7	1722.4	1742.8	1757.1	1770.7	1799.3	1822.5
7.5°	1605.5	1640.4	1679.8	1723.8	1768.3	1811.4	1851.5	1887.3	1922.9	1964.6	2012.1
10°	1603.3	1644.2	1697.2	1753.7	1815.7	1876.2	1934.8	1980.4	2033.4	2081.1	2141.6
12.5°	1593.0	1651.8	1715.2	1787.5	1863.6	1933.4	2010.4	2073.4	2134.2	2203.0	2273.4
15°	1579.5	1651.0	1731.3	1827.2	1942.9	2027.3	2106.2	2215.8	2290.7	2365.5	2466.3
17.5°	1554.9	1642.1	1742.4	1867.1	1963.6	2077.0	2195.8	2282.4	2383.2	2488.7	2579.9
20°	1535.3	1636.7	1749.0	1871.5	1994.6	2117.8	2232.8	2336.3	2440.4	2562.2	2637.1
22.5°	1515.7	1616.0	1732.6	1862.8	1995.2	2124.9	2255.1	2376.6	2493.7	2616.6	2712.2
25°	1474.0	1593.1	1719.7	1852.4	1983.1	2126.0	2281.1	2416.6	2561.5	2688.1	2778.6
27.5°	1431.8	1541.0	1667.0	1801.6	1946.9	2115.8	2298.3	2452.2	2597.5	2688.1	2716.6
30°	1393.7	1509.4	1625.1	1761.9	1919.1	2107.6	2301.6	2477.8	2596.9	2636.4	2607.1
32.5°	1355.1	1459.9	1574.5	1714.5	1881.5	2087.5	2305.9	2462.6	2534.3	2504.1	2385.0
35°	1286.9	1381.5	1492.4	1632.6	1824.5	2076.3	2288.0	2394.1	2376.4	2206.3	1981.7
37.5°	1213.9	1291.0	1393.7	1540.3	1765.4	2032.1	2210.6	2226.3	2073.2	1812.0	1552.6
40°	1156.2	1225.6	1331.1	1484.2	1719.7	1988.5	2132.8	2069.5	1832.0	1541.4	1325.0
42.5°	1100.1	1158.7	1260.3	1425.4	1676.2	1929.2	2016.8	1879.0	1605.0	1330.2	1133.4
45°	1005.1	1060.3	1162.3	1331.8	1587.0	1815.7	1804.1	1564.5	1290.3	1069.1	905.8
47.5°	915.0	963.2	1059.0	1232.0	1482.3	1645.5	1537.3	1282.4	1049.8	872.3	755.8
50°	851.3	899.0	994.3	1165.1	1398.5	1517.6	1363.1	1117.4	904.4	757.4	664.9
52.5°	790.4	836.9	924.0	1090.5	1297.2	1368.4	1202.5	974.8	797.2	670.3	590.8
55°	705.0	740.4	818.7	977.9	1132.4	1148.7	980.6	790.1	643.8	555.3	500.9
57.5°	618.1	648.5	725.9	852.7	961.0	952.6	793.2	628.4	529.9	464.1	424.7
60°	561.4	591.4	659.4	768.3	850.0	821.4	675.1	542.4	458.0	409.7	378.4
62.5°	508.6	532.0	595.7	675.2	734.0	701.6	577.1	467.3	400.3	359.6	334.8
65°	432.1	451.2	502.2	543.7	576.4	545.1	441.7	365.4	317.1	288.5	271.5
67.5°	359.5	371.6	403.8	418.8	441.8	407.5	332.1	281.1	253.6	229.5	217.6
70°	313.7	322.6	339.6	351.8	358.0	322.6	266.8	229.3	206.2	189.2	181.7
72.5°	268.0	275.8	279.2	289.2	286.1	252.9	214.5	184.7	168.1	156.5	146.9
75°	204.8	208.2	204.8	200.8	191.9	168.8	142.2	127.3	115.0	109.6	106.2
77.5°	149.3	148.2	143.6	137.2	122.1	107.5	93.2	88.2	82.9	80.0	78.8
80°	115.0	112.3	108.2	98.0	85.1	74.9	71.5	68.1	66.0	62.6	61.9
82.5°	85.6	84.0	77.2	68.6	59.5	54.7	51.9	50.6	48.6	46.8	46.7
85°	45.6	43.6	36.1	31.3	29.9	28.6	27.9	27.9	25.2	24.5	24.5
87.5°	15.5	12.8	12.9	11.8	12.5	12.1	13.4	13.1	13.3	14.1	13.2
90°	4.2	7.1	9.9	12.8	16.1	19.9	23.6	27.4	31.1	32.3	33.4
92.5°	33.3	35.3	37.3	39.2	41.3	43.4	45.5	47.7	49.8	50.7	51.6
95°	78.5	80.6	82.6	84.6	86.8	89.1	91.4	93.7	96.0	97.1	98.3
97.5°	137.4	138.9	140.4	141.9	143.5	145.2	146.8	148.5	150.2	151.5	152.8
100°	178.1	179.8	181.6	183.3	184.9	186.3	187.8	189.2	190.7	191.5	192.4
102.5°	224.1	225.2	226.2	227.2	228.7	230.6	232.5	234.4	236.3	237.2	238.0
105°	292.4	293.0	293.5	294.1	295.7	298.3	300.9	303.5	306.1	306.1	306.1
107.5°	372.1	372.4	372.8	373.1	373.8	374.8	375.9	376.9	377.9	378.9	379.8
110°	422.1	422.7	423.2	423.8	424.4	425.0	425.6	426.1	426.7	427.9	429.0



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	473.7	474.1	474.4	474.8	475.0	475.1	475.2	475.4	475.5	476.9	478.2
115°	552.1	552.9	553.8	554.7	554.8	554.2	553.7	553.1	552.5	552.8	553.1
117.5°	630.1	630.7	631.3	631.9	631.8	631.0	630.3	629.5	628.8	628.7	628.7
120°	680.0	681.8	683.5	685.2	685.4	683.9	682.5	681.1	679.6	679.3	679.0
122.5°	730.4	731.7	733.0	734.2	734.5	733.7	733.0	732.2	731.5	730.7	730.0
125°	807.6	808.4	809.3	810.2	810.3	809.7	809.2	808.6	808.0	806.9	805.7
127.5°	880.2	882.0	883.8	885.7	886.3	885.7	885.0	884.4	883.8	882.1	880.5
130°	928.3	930.7	933.0	935.3	936.0	935.1	934.3	933.4	932.5	931.4	930.2
132.5°	976.1	978.4	980.7	983.0	983.8	983.2	982.6	981.9	981.3	979.9	978.5
135°	1048.4	1050.1	1051.8	1053.6	1054.3	1054.0	1053.7	1053.4	1053.1	1052.0	1050.8
137.5°	1115.5	1117.0	1118.4	1119.9	1121.0	1121.7	1122.5	1123.2	1124.0	1122.7	1121.5
140°	1162.2	1163.7	1165.1	1166.6	1167.4	1167.7	1168.0	1168.3	1168.6	1168.3	1168.0
142.5°	1204.8	1206.2	1207.7	1209.1	1210.1	1210.6	1211.1	1211.6	1212.2	1211.9	1211.6
145°	1270.3	1270.9	1271.5	1272.0	1272.8	1273.6	1274.5	1275.4	1276.2	1275.9	1275.6
147.5°	1328.9	1329.9	1331.0	1332.0	1332.9	1333.7	1334.5	1335.3	1336.1	1336.1	1336.1
150°	1368.9	1369.5	1370.0	1370.6	1371.2	1371.8	1372.3	1372.9	1373.5	1373.5	1373.5
152.5°	1402.3	1403.1	1403.9	1404.7	1405.3	1405.7	1406.0	1406.4	1406.7	1407.2	1407.6
155°	1453.9	1453.9	1453.9	1453.9	1454.1	1454.3	1454.6	1454.9	1455.2	1456.4	1457.5
157.5°	1498.2	1497.8	1497.5	1497.1	1497.1	1497.3	1497.5	1497.8	1498.0	1499.2	1500.4
160°	1526.0	1525.4	1524.8	1524.2	1523.9	1523.9	1523.9	1523.9	1523.9	1525.4	1526.8
162.5°	1550.6	1549.8	1549.0	1548.2	1547.9	1548.2	1548.4	1548.6	1548.8	1550.3	1551.7
165°	1582.7	1581.9	1581.0	1580.2	1579.7	1579.7	1579.7	1579.7	1579.7	1581.4	1583.2
167.5°	1608.1	1607.0	1605.8	1604.7	1604.2	1604.4	1604.7	1604.9	1605.1	1606.9	1608.7
170°	1622.7	1621.5	1620.4	1619.2	1618.6	1618.6	1618.6	1618.6	1618.6	1620.6	1622.7
172.5°	1634.1	1632.9	1631.8	1630.6	1630.0	1630.0	1630.0	1630.0	1630.0	1631.8	1633.6
175°	1646.0	1644.9	1643.7	1642.5	1642.0	1642.0	1642.0	1642.0	1642.0	1643.7	1645.4
177.5°	1651.2	1650.2	1649.3	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.3	1650.7
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1676.8	1676.8	1679.0	1687.2	1688.3	1695.3	1693.2
5°	1842.9	1855.8	1860.6	1881.0	1893.2	1898.7	1887.8
7.5°	2046.0	2082.4	2099.7	2121.1	2140.0	2145.7	2130.9
10°	2194.0	2232.1	2264.1	2283.9	2302.2	2314.5	2330.1
12.5°	2337.2	2384.0	2414.4	2442.3	2461.2	2476.7	2479.3
15°	2492.8	2563.6	2617.3	2656.8	2676.5	2686.7	2682.7
17.5°	2649.7	2715.3	2753.6	2793.9	2821.2	2822.6	2823.4
20°	2738.5	2802.4	2846.7	2876.6	2907.2	2905.9	2912.7
22.5°	2797.8	2848.2	2882.1	2903.8	2914.3	2909.1	2910.5
25°	2825.6	2840.5	2834.4	2799.7	2790.9	2758.9	2764.3
27.5°	2682.4	2611.6	2538.4	2444.2	2369.9	2310.5	2313.5
30°	2488.0	2362.8	2219.9	2100.1	1992.6	1962.7	1898.7
32.5°	2216.4	2028.5	1861.1	1749.5	1657.2	1632.2	1576.4
35°	1755.8	1573.4	1401.2	1297.8	1256.9	1199.8	1199.1
37.5°	1364.7	1204.1	1113.1	1035.5	994.8	960.2	956.8
40°	1148.1	1022.8	954.1	898.3	858.2	832.3	826.2
42.5°	996.7	895.4	831.1	796.5	765.6	752.3	742.3
45°	813.9	745.9	700.9	669.6	655.4	645.1	639.7
47.5°	680.8	635.2	604.6	583.8	572.2	561.4	564.3
50°	608.4	571.0	548.5	528.8	519.9	512.4	513.1
52.5°	550.1	516.5	498.4	484.1	473.1	467.8	465.2
55°	466.8	445.7	427.4	417.2	411.0	403.6	401.5
57.5°	398.2	381.9	366.9	355.4	353.9	346.7	347.6
60°	352.5	338.9	326.7	320.5	315.8	309.6	311.7
62.5°	315.0	303.5	292.4	287.3	282.6	278.1	279.0
65°	257.9	247.0	240.2	237.5	235.5	233.4	231.4
67.5°	205.5	198.9	194.6	188.8	184.6	183.9	181.8
70°	172.9	164.0	156.5	149.0	147.0	146.3	147.0
72.5°	138.6	133.0	130.9	127.3	126.9	125.1	126.3
75°	104.1	102.1	100.7	98.0	98.0	98.0	98.0
77.5°	76.8	75.5	74.7	74.2	73.5	72.5	72.4
80°	59.9	59.2	57.8	57.8	57.2	57.8	57.2
82.5°	45.2	45.1	43.7	43.7	43.0	42.6	43.0
85°	23.1	22.5	23.8	22.5	23.1	21.8	23.1
87.5°	13.5	13.7	13.3	13.4	13.0	14.2	13.2
90°	34.6	35.7	36.6	37.2	37.8	38.3	38.9
92.5°	52.6	53.5	53.8	53.4	53.1	52.7	52.4
95°	99.4	100.6	101.2	101.2	101.2	101.2	101.2
97.5°	154.2	155.5	156.1	156.0	155.9	155.8	155.6
100°	193.2	194.1	194.8	195.4	196.0	196.6	197.1
102.5°	238.9	239.8	240.1	240.0	239.9	239.8	239.7
105°	306.1	306.1	306.4	307.0	307.5	308.1	308.7
107.5°	380.7	381.6	381.9	381.6	381.2	380.9	380.5
110°	430.2	431.3	431.6	431.0	430.5	429.9	429.3



TEST NUMBER: P332463

CATALOG NUMBER: S123RDIW-S1000D1320U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	479.6	481.0	481.6	481.5	481.4	481.3	481.2
115°	553.4	553.7	553.7	553.4	553.1	552.8	552.5
117.5°	628.6	628.5	628.1	627.3	626.5	625.7	624.9
120°	678.8	678.5	678.0	677.5	676.9	676.3	675.7
122.5°	729.2	728.5	727.7	726.9	726.1	725.3	724.5
125°	804.6	803.4	802.3	801.1	799.9	798.8	797.6
127.5°	878.9	877.3	875.8	874.5	873.2	871.9	870.5
130°	929.1	927.9	926.3	924.3	922.3	920.3	918.3
132.5°	977.1	975.8	974.3	972.7	971.2	969.6	968.1
135°	1049.7	1048.5	1047.7	1047.1	1046.5	1045.9	1045.4
137.5°	1120.3	1119.1	1118.0	1116.9	1115.8	1114.7	1113.6
140°	1167.7	1167.4	1166.3	1164.3	1162.2	1160.2	1158.2
142.5°	1211.3	1211.0	1210.1	1208.5	1207.0	1205.4	1203.9
145°	1275.4	1275.1	1274.4	1273.2	1272.0	1270.9	1269.7
147.5°	1336.1	1336.1	1335.3	1333.6	1331.8	1330.1	1328.4
150°	1373.5	1373.5	1372.6	1370.9	1369.2	1367.4	1365.7
152.5°	1408.1	1408.5	1408.0	1406.5	1405.0	1403.5	1402.0
155°	1458.7	1459.8	1459.4	1457.4	1455.4	1453.3	1451.3
157.5°	1501.6	1502.9	1502.6	1501.0	1499.4	1497.8	1496.2
160°	1528.3	1529.7	1529.9	1528.7	1527.6	1526.4	1525.2
162.5°	1553.2	1554.6	1554.4	1552.6	1550.7	1548.9	1547.0
165°	1584.9	1586.6	1586.5	1584.5	1582.5	1580.4	1578.4
167.5°	1610.5	1612.3	1612.3	1610.5	1608.7	1606.9	1605.1
170°	1624.7	1626.7	1626.7	1624.7	1622.7	1620.6	1618.6
172.5°	1635.4	1637.2	1637.1	1635.1	1633.0	1631.0	1629.0
175°	1647.2	1648.9	1648.7	1646.7	1644.7	1642.7	1640.7
177.5°	1652.1	1653.5	1653.4	1651.7	1650.1	1648.5	1646.9
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1

(END OF REPORT)