

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332178-940

Luminaire Tested: **S123DIW-S775D1535U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332178-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1535U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8302.5 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	78	72	67	77	71	66	62	57	53	50	44	42	40	32	31	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	27	25	20
4	71	61	53	47	64	55	49	43	45	40	36	35	31	29	25	23	21	17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	21	19	15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	16	15	12
8	51	39	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	9
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.3	1.2
10°-20°	288.8	3.5
20°-30°	426.6	5.1
30°-40°	498.4	6.0
40°-50°	501.0	6.0
50°-60°	440.1	5.3
60°-70°	327.9	3.9
70°-80°	186.8	2.3
80°-90°	58.6	0.7
90°-100°	65.2	0.8
100°-110°	310.9	3.7
110°-120°	746.8	9.0
120°-130°	951.0	11.5
130°-140°	1016.1	12.2
140°-150°	950.2	11.4
150°-160°	766.5	9.2
160°-170°	494.7	6.0
170°-180°	170.5	2.1
0°-30°	817.7	9.8
0°-40°	1316.1	15.9
0°-60°	2257.3	27.2
0°-90°	2830.6	34.1
90°-120°	1123.0	13.5
90°-150°	4040.3	48.7
90°-180°	5472.0	65.9
0°-180°	8302.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	15	32	37	40	6
95°	81	30	41	50	51	101
105°	397	404	292	69	59	421
115°	745	753	765	778	784	735
125°	1050	1061	1066	1069	1072	938
135°	1308	1316	1321	1325	1321	1006
145°	1509	1518	1521	1524	1524	944
155°	1662	1660	1661	1667	1660	766
165°	1753	1749	1748	1757	1749	495
175°	1794	1788	1789	1797	1788	171
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.7	19.8	19.9	20.0	20.1	20.4	21.0	21.6	22.2	22.8	22.9
90°	1.3	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2
92.5°	24.8	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0
95°	81.3	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4
97.5°	163.5	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3
100°	225.3	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4
102.5°	295.7	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3
105°	397.3	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5
107.5°	504.4	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7
110°	575.9	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5



TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	644.2	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6
115°	745.2	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1
117.5°	843.0	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4
120°	903.8	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2
122.5°	965.7	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3
125°	1050.4	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1
127.5°	1132.6	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6
130°	1183.7	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0
132.5°	1232.9	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9
135°	1307.8	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0
137.5°	1371.7	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3
140°	1414.4	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6
142.5°	1453.8	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8
145°	1509.0	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6
147.5°	1561.0	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5
150°	1593.0	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3
152.5°	1621.8	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4
155°	1662.3	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5
157.5°	1693.8	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0
160°	1713.1	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2
162.5°	1731.2	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4
165°	1753.0	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1
167.5°	1770.0	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1
170°	1779.7	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7
172.5°	1786.1	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2
175°	1794.3	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1
177.5°	1796.4	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	23.0	23.0	23.1	23.2	23.4	23.5	23.5	23.7
90°	34.3	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	37.9	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	45.5	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	47.7	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	48.7	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	73.0	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	187.1	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	458.2	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	581.7	571.9	562.1	536.0	493.7	451.3	408.9	366.6





TEST NUMBER: P332178-940

CATALOG NUMBER: S123DIW-S775D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	668.8	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	771.2	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	863.8	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	924.6	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	983.9	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1067.6	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1151.6	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1202.1	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1250.2	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1387.7	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1428.8	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1467.8	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.2	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.0	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1600.9	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1627.5	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1664.0	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1695.8	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1714.0	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1730.4	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1752.4	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1785.5	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1793.1	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1796.0	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)