

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332156-940

Luminaire Tested: **S123DIW-S775D755U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332156-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D755U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5604.0 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58	52
1	99	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49	44
2	90	83	77	72	83	77	71	67	66	62	58	55	52	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	42	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12369	10416	9231	10416
10°	15481	10364	8337	10364
15°	18988	10280	7762	10280
20°	22620	10149	7391	10149
25°	24018	9991	7308	9991
30°	20586	9875	7346	9875
35°	14318	9711	7423	9711
40°	10784	9517	7399	9517
45°	8954	9232	7305	9232
50°	8020	8646	7239	8646
55°	7499	8015	7148	8015
60°	7035	7356	7076	7356
65°	6612	6706	6849	6706
70°	6200	5964	6521	5964
75°	5552	5224	5976	5224
80°	4866	4283	5151	4283
85°	3816	3112	3458	3112



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.9	1.7
10°-20°	304.3	5.4
20°-30°	510.8	9.1
30°-40°	578.4	10.3
40°-50°	518.7	9.3
50°-60°	418.6	7.5
60°-70°	291.7	5.2
70°-80°	153.3	2.7
80°-90°	40.0	0.7
90°-100°	32.1	0.6
100°-110°	153.0	2.7
110°-120°	367.6	6.6
120°-130°	468.1	8.4
130°-140°	500.2	8.9
140°-150°	467.7	8.3
150°-160°	377.3	6.7
160°-170°	243.5	4.3
170°-180°	83.9	1.5
0°-30°	910.1	16.2
0°-40°	1488.4	26.6
0°-60°	2425.7	43.3
0°-90°	2910.6	51.9
90°-120°	552.8	9.9
90°-150°	1988.7	35.5
90°-180°	2693.0	48.1
0°-180°	5604.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	964	964	964	964	964	
5°	1145	964	854	964	1145	119
15°	1704	922	696	922	1704	492
25°	2022	841	615	841	2022	887
35°	1090	739	565	739	1090	708
45°	588	606	480	606	588	465
55°	400	427	381	427	400	359
65°	260	263	269	263	260	259
75°	134	126	144	126	134	143
85°	31	25	28	25	31	37
90°	20	1	20	1	20	10
95°	25	40	25	40	25	21
105°	29	196	29	196	29	66
115°	386	367	386	367	386	357
125°	528	517	528	517	528	471
135°	650	644	650	644	650	501
145°	750	743	750	743	750	468
155°	817	818	817	818	817	377
165°	861	863	861	863	861	243
175°	880	883	880	883	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1022.5	1021.8	1019.9	1021.5	1018.4	1014.3	1014.0	1010.2	999.3	998.6	995.7
5°	1144.7	1140.9	1140.5	1140.0	1133.5	1124.6	1107.8	1106.3	1084.0	1072.7	1059.3
7.5°	1302.8	1304.8	1298.0	1292.0	1272.0	1258.8	1240.8	1217.7	1190.3	1162.3	1143.7
10°	1416.4	1431.7	1412.6	1399.5	1387.4	1364.5	1337.9	1304.8	1271.7	1232.9	1203.5
12.5°	1538.1	1545.7	1541.9	1529.6	1510.6	1475.9	1428.7	1392.1	1361.6	1297.1	1271.0
15°	1703.9	1732.4	1714.2	1672.1	1673.1	1639.9	1578.3	1510.6	1474.7	1418.2	1341.2
17.5°	1880.5	1884.1	1876.3	1841.4	1818.0	1772.5	1715.6	1650.7	1577.9	1509.5	1427.8
20°	1974.7	1971.8	1955.5	1937.3	1897.2	1861.7	1799.7	1727.2	1633.9	1566.6	1477.5
22.5°	2026.9	2022.3	2014.6	1999.3	1965.9	1927.8	1872.1	1793.0	1704.1	1611.5	1508.5
25°	2022.3	2028.4	2029.3	2025.1	2013.4	1990.6	1946.7	1883.6	1794.9	1675.9	1568.5
27.5°	1839.3	1847.9	1872.9	1895.0	1919.7	1944.9	1941.5	1910.2	1844.6	1741.9	1610.5
30°	1656.3	1637.6	1683.8	1742.2	1781.9	1851.9	1891.1	1893.5	1856.5	1768.4	1640.4
32.5°	1402.3	1422.9	1443.3	1515.1	1601.9	1680.5	1758.5	1821.4	1828.5	1769.9	1658.0
35°	1089.6	1115.3	1152.6	1189.9	1283.4	1363.6	1500.8	1620.3	1715.6	1728.2	1659.6
37.5°	878.0	890.7	914.4	951.7	1012.8	1108.0	1214.2	1365.3	1503.2	1605.9	1610.3
40°	767.5	771.2	797.8	826.3	875.7	954.2	1049.9	1183.4	1348.6	1492.0	1551.8
42.5°	684.6	692.8	704.1	731.4	770.8	829.8	918.8	1029.1	1180.6	1345.6	1462.5
45°	588.2	597.5	604.6	622.8	650.8	690.5	752.5	853.4	968.7	1139.1	1296.4
47.5°	524.5	525.3	530.5	544.2	563.3	593.1	636.9	701.8	807.6	945.7	1107.3
50°	478.9	486.4	488.3	499.0	514.0	535.9	572.3	627.4	714.3	835.6	984.1
52.5°	446.8	449.1	454.3	462.1	475.1	492.2	523.8	566.9	635.1	738.5	875.0
55°	399.6	399.6	404.7	410.8	418.3	433.6	454.7	486.4	538.2	618.6	731.6
57.5°	355.9	358.2	361.9	363.7	370.1	380.3	397.8	422.0	460.6	522.4	612.2
60°	326.8	331.0	330.6	334.2	339.8	347.8	362.7	382.4	416.9	466.4	542.0
62.5°	301.4	301.1	301.0	305.5	311.1	318.7	328.3	345.4	374.7	418.6	483.0
65°	259.6	258.6	261.9	264.7	266.5	272.2	279.6	294.5	314.1	346.9	396.8
67.5°	222.4	219.7	221.5	222.4	225.6	230.0	236.9	246.2	261.8	288.0	325.7
70°	197.0	194.7	194.2	195.1	198.0	201.2	206.3	215.2	229.7	250.7	278.2
72.5°	170.9	169.2	169.2	171.2	172.5	174.7	178.3	186.5	198.0	213.7	239.4
75°	133.5	133.5	133.5	133.9	135.4	137.2	140.1	144.3	153.1	164.3	181.6
77.5°	100.0	100.0	99.4	99.3	101.4	102.3	102.9	106.8	111.7	119.3	131.9
80°	78.5	76.1	77.0	78.5	79.4	79.8	81.2	82.1	86.4	90.6	99.4
82.5°	58.2	56.3	56.4	58.7	58.9	59.3	60.7	62.0	63.6	67.4	72.1
85°	30.9	30.9	31.3	31.3	31.7	31.3	32.6	33.2	33.2	35.5	38.3
87.5°	15.2	14.4	14.6	15.0	14.5	14.8	15.1	15.3	15.6	15.9	15.9
90°	19.7	19.4	19.1	18.8	18.5	18.1	17.5	16.9	16.3	15.8	13.8
92.5°	21.8	21.6	21.4	21.2	21.0	20.5	19.6	18.6	17.7	16.8	15.3
95°	25.0	25.0	25.0	25.0	25.0	24.4	23.4	22.4	21.4	20.3	18.7
97.5°	27.0	26.9	26.8	26.6	26.5	25.8	24.6	23.5	22.3	21.1	31.7
100°	27.6	27.4	27.3	27.1	27.0	26.3	25.1	24.0	22.8	21.7	44.4
102.5°	28.1	27.8	27.6	27.3	27.0	28.7	32.4	35.9	39.6	43.2	68.0
105°	28.9	28.6	28.3	28.0	27.7	40.5	66.3	92.1	117.9	143.7	156.9
107.5°	90.7	110.1	129.6	149.0	168.5	187.7	206.6	225.5	244.4	263.4	261.4
110°	180.5	201.3	222.1	243.0	263.9	276.7	281.5	286.3	291.1	296.0	294.4



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	309.6	314.0	318.4	322.8	327.2	329.4	329.3	329.2	329.1	329.0	327.4
115°	385.8	385.2	384.7	384.1	383.5	382.5	381.0	379.6	378.1	376.7	375.3
117.5°	428.6	428.5	428.4	428.3	428.1	427.5	426.3	425.2	424.0	422.8	422.1
120°	458.0	458.0	458.0	458.0	458.0	457.4	456.3	455.1	454.0	452.7	452.4
122.5°	486.9	486.8	486.6	486.5	486.4	486.0	485.1	484.3	483.5	482.7	482.1
125°	527.5	527.3	527.0	526.7	526.4	526.1	525.8	525.5	525.2	525.0	524.3
127.5°	566.7	566.9	567.2	567.6	567.8	567.8	567.3	566.9	566.3	565.9	565.2
130°	591.8	592.2	592.5	592.7	593.1	592.9	592.3	591.7	591.1	590.6	590.0
132.5°	614.9	615.4	615.8	616.2	616.6	616.5	615.9	615.4	614.7	614.2	613.7
135°	650.2	650.7	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2	649.7
137.5°	683.5	683.8	684.0	684.4	684.7	684.5	683.8	683.1	682.3	681.6	681.4
140°	703.4	703.7	704.0	704.3	704.6	704.5	703.8	703.3	702.7	702.1	701.7
142.5°	721.8	722.2	722.6	723.0	723.4	723.4	722.9	722.5	722.0	721.6	721.1
145°	750.0	750.0	750.0	750.0	750.0	749.8	749.6	749.3	748.9	748.7	748.4
147.5°	771.0	771.7	772.3	773.0	773.6	773.9	773.6	773.3	773.0	772.7	772.4
150°	786.8	787.2	787.6	788.1	788.5	788.5	788.3	788.0	787.7	787.4	787.1
152.5°	799.3	800.0	800.7	801.4	802.0	802.1	801.6	801.0	800.5	800.0	799.9
155°	816.9	817.8	818.7	819.6	820.5	820.6	819.7	819.0	818.3	817.6	817.4
157.5°	831.8	832.9	834.0	835.2	836.3	836.4	835.5	834.7	833.8	832.9	833.1
160°	841.2	842.2	843.3	844.3	845.3	845.3	844.5	843.6	842.8	841.9	842.0
162.5°	850.2	851.0	851.9	852.8	853.7	853.7	852.7	851.8	850.8	849.7	849.9
165°	860.9	861.9	862.9	864.0	865.0	864.9	863.7	862.6	861.4	860.2	860.4
167.5°	868.6	869.8	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6	868.6
170°	873.3	874.5	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3	873.3
172.5°	876.0	877.3	878.6	879.9	881.1	881.2	880.0	878.9	877.7	876.6	876.4
175°	879.9	881.1	882.3	883.4	884.6	884.7	883.7	882.6	881.6	880.6	880.5
177.5°	881.1	882.3	883.4	884.6	885.7	885.9	884.9	884.0	883.1	882.2	882.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	993.4	990.4	987.4	982.2	977.8	971.3	969.5	967.2	960.6	954.6	950.1
5°	1054.1	1042.9	1026.5	1011.6	999.5	983.1	973.8	964.0	950.0	937.4	927.1
7.5°	1117.6	1095.6	1070.1	1042.7	1017.1	992.5	972.6	954.8	935.2	916.7	902.2
10°	1168.0	1136.2	1100.8	1062.5	1029.8	998.1	971.4	948.2	922.9	901.0	882.8
12.5°	1225.5	1178.5	1129.5	1083.1	1044.4	1000.3	968.1	938.4	909.8	883.4	863.0
15°	1293.6	1233.9	1175.9	1112.0	1053.2	998.1	959.8	922.5	889.3	862.2	836.1
17.5°	1355.6	1287.9	1211.6	1133.8	1062.8	997.6	944.0	901.7	860.2	827.2	801.1
20°	1390.7	1313.7	1227.3	1146.6	1068.1	995.2	936.5	886.0	841.2	806.2	776.8
22.5°	1420.9	1330.8	1241.4	1155.1	1067.7	989.3	922.7	870.8	822.2	787.9	756.6
25°	1452.3	1344.4	1254.8	1153.5	1056.0	974.7	900.0	841.2	792.6	752.5	720.3
27.5°	1479.2	1343.5	1237.2	1128.2	1037.5	956.1	876.3	813.2	761.7	718.1	685.4
30°	1497.1	1345.4	1218.9	1111.1	1019.6	935.5	858.0	794.5	740.4	696.1	665.2
32.5°	1508.3	1344.3	1202.1	1087.2	991.1	916.9	838.2	772.5	716.8	673.2	643.5
35°	1514.8	1336.1	1173.1	1037.8	945.3	873.0	807.2	739.0	680.6	640.0	606.5
37.5°	1501.8	1318.8	1139.5	990.2	888.9	817.7	762.3	704.3	648.5	603.7	574.8
40°	1481.2	1307.6	1113.4	956.5	850.1	781.5	734.3	677.3	622.2	579.8	552.7
42.5°	1442.0	1284.8	1084.6	919.2	809.8	741.1	697.8	650.1	598.0	558.1	531.1
45°	1346.3	1235.2	1041.5	863.2	750.2	679.2	641.0	606.5	559.3	520.5	497.1
47.5°	1213.5	1160.7	979.1	804.1	688.0	619.7	580.0	552.1	517.7	486.4	464.0
50°	1121.3	1099.4	936.9	763.8	646.6	579.8	541.5	516.3	491.6	460.3	439.8
52.5°	1014.9	1028.4	887.6	721.9	604.3	538.7	502.7	482.7	460.2	434.5	416.6
55°	865.0	914.0	802.5	651.7	541.5	478.9	444.9	427.1	414.1	394.9	379.5
57.5°	724.7	787.1	710.4	579.3	479.8	425.9	393.2	373.8	365.4	355.4	343.3
60°	641.4	703.0	644.7	530.7	438.4	387.0	358.0	341.7	333.3	326.3	316.0
62.5°	567.1	629.5	580.4	481.5	397.6	350.0	324.9	308.9	302.3	298.6	289.9
65°	464.9	518.6	486.0	404.7	339.4	297.4	274.5	263.3	257.3	255.8	250.2
67.5°	378.4	419.3	395.5	335.7	284.3	248.0	228.5	219.0	214.4	213.9	209.7
70°	321.6	359.9	341.7	287.6	243.3	214.7	198.0	189.5	186.7	186.3	184.0
72.5°	277.6	304.3	289.8	244.6	210.4	184.5	172.2	163.4	160.2	160.9	159.3
75°	205.4	225.5	217.0	185.8	158.3	141.4	131.2	125.6	122.8	124.2	122.3
77.5°	147.8	160.5	152.9	131.3	114.3	102.1	94.6	91.1	88.6	88.5	87.7
80°	111.6	119.0	114.9	101.7	87.7	77.5	71.4	69.1	67.7	67.2	66.8
82.5°	79.5	85.8	80.9	71.9	62.3	56.2	52.8	49.7	48.7	49.0	48.4
85°	40.1	42.4	40.6	35.0	31.3	28.4	26.6	25.2	24.3	24.7	23.8
87.5°	16.2	16.2	14.7	12.8	11.9	10.4	10.2	9.1	8.6	8.9	8.8
90°	11.9	10.1	8.2	6.5	5.0	3.6	2.1	0.6	2.1	3.6	5.0
92.5°	13.9	12.5	11.1	10.6	11.0	11.4	11.8	12.2	11.8	11.4	11.0
95°	17.1	15.5	13.9	16.1	22.1	28.1	34.1	40.0	34.1	28.1	22.1
97.5°	42.1	52.6	63.1	69.7	72.4	75.1	77.8	80.4	77.8	75.1	72.4
100°	67.1	89.9	112.6	122.5	119.7	116.7	113.8	110.9	113.8	116.7	119.7
102.5°	92.8	117.7	142.6	153.9	151.9	149.7	147.7	145.5	147.7	149.7	151.9
105°	170.0	183.1	196.2	202.0	200.4	198.8	197.2	195.6	197.2	198.8	200.4
107.5°	259.2	257.2	255.1	253.4	252.2	250.8	249.6	248.3	249.6	250.8	252.2
110°	292.7	291.1	289.5	288.1	287.0	285.8	284.6	283.5	284.6	285.8	287.0





TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.8	324.2	322.6	321.3	320.2	319.1	318.1	317.1	318.1	319.1	320.2
115°	374.0	372.7	371.4	370.3	369.4	368.5	367.7	366.8	367.7	368.5	369.4
117.5°	421.5	420.8	420.2	419.3	418.2	417.1	416.1	415.0	416.1	417.1	418.2
120°	451.9	451.5	451.0	450.1	448.8	447.5	446.2	444.9	446.2	447.5	448.8
122.5°	481.6	481.0	480.5	479.7	478.6	477.5	476.4	475.4	476.4	477.5	478.6
125°	523.8	523.2	522.6	521.7	520.6	519.4	518.3	517.1	518.3	519.4	520.6
127.5°	564.5	563.8	563.1	562.1	561.0	559.8	558.7	557.5	558.7	559.8	561.0
130°	589.4	588.8	588.3	587.4	586.2	585.1	583.9	582.6	583.9	585.1	586.2
132.5°	613.2	612.8	612.3	611.5	610.3	609.1	608.0	606.8	608.0	609.1	610.3
135°	649.1	648.5	647.9	647.2	646.3	645.4	644.6	643.7	644.6	645.4	646.3
137.5°	681.0	680.6	680.4	679.7	678.5	677.4	676.3	675.2	676.3	677.4	678.5
140°	701.2	700.8	700.3	699.7	698.8	697.9	697.1	696.2	697.1	697.9	698.8
142.5°	720.7	720.2	719.8	719.2	718.3	717.4	716.5	715.6	716.5	717.4	718.3
145°	748.1	747.8	747.5	746.9	745.8	744.8	743.8	742.8	743.8	744.8	745.8
147.5°	772.1	771.9	771.5	771.1	770.3	769.7	769.0	768.4	769.0	769.7	770.3
150°	786.8	786.6	786.2	785.9	785.4	785.0	784.5	784.2	784.5	785.0	785.4
152.5°	799.7	799.5	799.3	799.2	798.9	798.7	798.5	798.3	798.5	798.7	798.9
155°	817.3	817.2	817.0	817.1	817.3	817.7	818.0	818.2	818.0	817.7	817.3
157.5°	833.2	833.4	833.6	833.7	833.7	833.7	833.7	833.7	833.7	833.7	833.7
160°	842.1	842.3	842.5	842.6	842.8	842.9	843.0	843.2	843.0	842.9	842.8
162.5°	850.1	850.2	850.3	850.6	851.0	851.3	851.8	852.1	851.8	851.3	851.0
165°	860.5	860.7	860.9	861.1	861.6	862.0	862.5	862.9	862.5	862.0	861.6
167.5°	868.6	868.6	868.6	869.0	869.5	870.1	870.7	871.3	870.7	870.1	869.5
170°	873.3	873.3	873.3	873.7	874.2	874.9	875.4	876.0	875.4	874.9	874.2
172.5°	876.3	876.2	876.0	876.4	877.1	877.7	878.4	879.1	878.4	877.7	877.1
175°	880.3	880.1	880.0	880.3	881.0	881.7	882.4	883.2	882.4	881.7	881.0
177.5°	881.9	881.8	881.7	881.9	882.5	883.1	883.7	884.2	883.7	883.1	882.5
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	947.4	944.9	941.1	935.5	931.0	923.9	923.9	925.1	925.1	924.7	923.9
5°	918.7	911.7	903.3	893.5	883.2	873.0	871.1	867.4	864.6	862.7	860.3
7.5°	888.4	875.9	863.7	850.0	837.5	827.2	819.9	814.0	810.1	806.0	803.1
10°	867.8	852.4	837.9	823.5	807.6	795.0	787.1	781.5	777.3	773.6	771.7
12.5°	843.6	825.9	809.9	796.2	778.8	765.9	758.3	755.7	750.7	742.9	738.8
15°	808.1	791.8	772.6	751.6	743.2	727.3	718.5	714.3	711.4	705.3	703.5
17.5°	777.8	756.3	734.9	719.2	703.6	690.7	685.7	680.6	676.8	671.8	670.4
20°	753.5	734.3	714.7	697.9	681.5	667.5	663.3	659.6	655.9	653.5	651.7
22.5°	728.8	709.7	693.4	677.7	660.3	651.1	646.6	642.5	639.8	638.3	636.4
25°	694.2	677.3	659.2	645.2	631.2	625.1	622.2	619.9	618.0	615.7	615.3
27.5°	663.2	644.9	630.1	617.1	607.0	601.9	599.2	598.1	598.5	599.3	599.9
30°	640.0	623.2	611.1	599.9	590.6	585.9	585.4	585.4	587.3	587.7	588.7
32.5°	618.8	604.9	592.8	581.9	574.9	571.7	573.5	573.5	575.0	576.1	577.8
35°	587.7	575.6	566.2	557.0	550.9	552.2	553.2	554.1	556.4	559.3	561.2
37.5°	558.1	547.6	537.9	530.6	527.8	530.3	532.5	534.5	537.3	539.4	541.3
40°	536.8	528.9	519.6	513.0	514.0	515.4	517.3	519.6	521.9	523.3	525.2
42.5°	517.0	508.7	501.7	496.2	497.6	499.4	500.4	501.7	504.4	506.8	508.0
45°	486.9	480.4	473.9	470.6	471.5	472.4	473.3	474.7	477.1	478.9	479.5
47.5°	453.0	448.4	444.1	440.9	442.4	442.0	443.2	446.2	446.9	448.1	450.7
50°	431.3	427.1	422.0	421.1	421.1	421.1	421.5	425.3	425.3	427.1	429.0
52.5°	407.4	404.7	401.4	399.8	399.0	399.0	401.0	402.9	403.6	406.3	408.1
55°	372.0	369.3	366.5	365.1	364.1	365.1	368.8	369.7	372.0	373.4	374.9
57.5°	335.2	333.1	330.8	330.0	329.8	331.1	333.1	335.9	336.5	340.8	343.0
60°	310.9	307.6	305.8	305.8	304.9	309.1	308.1	312.8	313.7	316.5	319.8
62.5°	285.9	281.5	280.7	280.7	282.0	283.3	284.5	286.6	289.1	292.6	295.2
65°	245.6	243.3	246.5	246.0	245.0	247.9	247.9	250.2	253.0	256.3	261.4
67.5°	207.3	206.2	206.4	206.4	207.9	209.5	210.7	212.8	216.2	219.6	222.9
70°	181.6	183.0	180.7	182.5	184.0	184.4	185.3	188.2	191.9	194.2	198.0
72.5°	156.6	156.5	156.8	157.5	158.9	159.7	160.7	163.9	168.0	170.0	172.9
75°	120.5	119.9	121.4	121.4	123.7	124.7	125.6	127.0	130.7	133.5	135.8
77.5°	87.9	88.5	88.2	89.8	89.2	89.3	92.2	93.6	94.0	99.5	100.8
80°	66.3	67.2	67.7	68.1	68.7	67.7	71.0	72.3	72.3	75.6	77.9
82.5°	47.6	48.2	49.4	49.8	49.9	50.9	51.2	52.2	53.3	54.8	57.8
85°	23.8	25.2	25.7	25.2	25.7	24.7	26.1	26.6	27.1	27.1	27.1
87.5°	8.7	9.5	9.5	10.3	10.3	11.0	11.1	10.5	10.6	11.9	10.4
90°	6.5	8.2	10.1	11.9	13.8	15.8	16.3	16.9	17.5	18.1	18.5
92.5°	10.6	11.1	12.5	13.9	15.3	16.8	17.7	18.6	19.6	20.5	21.0
95°	16.1	13.9	15.5	17.1	18.7	20.3	21.4	22.4	23.4	24.4	25.0
97.5°	69.7	63.1	52.6	42.1	31.7	21.1	22.3	23.5	24.6	25.8	26.5
100°	122.5	112.6	89.9	67.1	44.4	21.7	22.8	24.0	25.1	26.3	27.0
102.5°	153.9	142.6	117.7	92.8	68.0	43.2	39.6	35.9	32.4	28.7	27.0
105°	202.0	196.2	183.1	170.0	156.9	143.7	117.9	92.1	66.3	40.5	27.7
107.5°	253.4	255.1	257.2	259.2	261.4	263.4	244.4	225.5	206.6	187.7	168.5
110°	288.1	289.5	291.1	292.7	294.4	296.0	291.1	286.3	281.5	276.7	263.9



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	321.3	322.6	324.2	325.8	327.4	329.0	329.1	329.2	329.3	329.4	327.2
115°	370.3	371.4	372.7	374.0	375.3	376.7	378.1	379.6	381.0	382.5	383.5
117.5°	419.3	420.2	420.8	421.5	422.1	422.8	424.0	425.2	426.3	427.5	428.1
120°	450.1	451.0	451.5	451.9	452.4	452.7	454.0	455.1	456.3	457.4	458.0
122.5°	479.7	480.5	481.0	481.6	482.1	482.7	483.5	484.3	485.1	486.0	486.4
125°	521.7	522.6	523.2	523.8	524.3	525.0	525.2	525.5	525.8	526.1	526.4
127.5°	562.1	563.1	563.8	564.5	565.2	565.9	566.3	566.9	567.3	567.8	567.8
130°	587.4	588.3	588.8	589.4	590.0	590.6	591.1	591.7	592.3	592.9	593.1
132.5°	611.5	612.3	612.8	613.2	613.7	614.2	614.7	615.4	615.9	616.5	616.6
135°	647.2	647.9	648.5	649.1	649.7	650.2	650.7	651.1	651.6	652.0	652.0
137.5°	679.7	680.4	680.6	681.0	681.4	681.6	682.3	683.1	683.8	684.5	684.7
140°	699.7	700.3	700.8	701.2	701.7	702.1	702.7	703.3	703.8	704.5	704.6
142.5°	719.2	719.8	720.2	720.7	721.1	721.6	722.0	722.5	722.9	723.4	723.4
145°	746.9	747.5	747.8	748.1	748.4	748.7	748.9	749.3	749.6	749.8	750.0
147.5°	771.1	771.5	771.9	772.1	772.4	772.7	773.0	773.3	773.6	773.9	773.6
150°	785.9	786.2	786.6	786.8	787.1	787.4	787.7	788.0	788.3	788.5	788.5
152.5°	799.2	799.3	799.5	799.7	799.9	800.0	800.5	801.0	801.6	802.1	802.0
155°	817.1	817.0	817.2	817.3	817.4	817.6	818.3	819.0	819.7	820.6	820.5
157.5°	833.7	833.6	833.4	833.2	833.1	832.9	833.8	834.7	835.5	836.4	836.3
160°	842.6	842.5	842.3	842.1	842.0	841.9	842.8	843.6	844.5	845.3	845.3
162.5°	850.6	850.3	850.2	850.1	849.9	849.7	850.8	851.8	852.7	853.7	853.7
165°	861.1	860.9	860.7	860.5	860.4	860.2	861.4	862.6	863.7	864.9	865.0
167.5°	869.0	868.6	868.6	868.6	868.6	868.6	869.8	870.9	872.2	873.3	873.3
170°	873.7	873.3	873.3	873.3	873.3	873.3	874.5	875.7	876.9	878.1	878.1
172.5°	876.4	876.0	876.2	876.3	876.4	876.6	877.7	878.9	880.0	881.2	881.1
175°	880.3	880.0	880.1	880.3	880.5	880.6	881.6	882.6	883.7	884.7	884.6
177.5°	881.9	881.7	881.8	881.9	882.1	882.2	883.1	884.0	884.9	885.9	885.7
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	921.3	921.0	923.5	921.7	923.5	921.0	921.3	923.9	924.7	925.1	925.1
5°	857.6	859.0	854.3	854.3	854.3	859.0	857.6	860.3	862.7	864.6	867.4
7.5°	800.8	798.7	798.9	796.4	798.9	798.7	800.8	803.1	806.0	810.1	814.0
10°	766.1	763.3	762.3	762.8	762.3	763.3	766.1	771.7	773.6	777.3	781.5
12.5°	737.3	736.7	730.6	730.7	730.6	736.7	737.3	738.8	742.9	750.7	755.7
15°	703.5	694.6	693.7	696.5	693.7	694.6	703.5	703.5	705.3	711.4	714.3
17.5°	669.6	664.9	665.2	663.8	665.2	664.9	669.6	670.4	671.8	676.8	680.6
20°	651.7	648.9	648.5	645.2	648.5	648.9	651.7	651.7	653.5	655.9	659.6
22.5°	635.3	634.4	634.6	631.0	634.6	634.4	635.3	636.4	638.3	639.8	642.5
25°	614.8	617.2	615.3	615.3	615.3	617.2	614.8	615.3	615.7	618.0	619.9
27.5°	601.0	600.9	599.9	599.9	599.9	600.9	601.0	599.9	599.3	598.5	598.1
30°	590.6	590.0	591.0	591.0	591.0	590.0	590.6	588.7	587.7	587.3	585.4
32.5°	580.1	580.8	580.9	581.3	580.9	580.8	580.1	577.8	576.1	575.0	573.5
35°	563.9	564.4	565.8	564.9	565.8	564.4	563.9	561.2	559.3	556.4	554.1
37.5°	542.1	544.2	543.8	544.5	543.8	544.2	542.1	541.3	539.4	537.3	534.5
40°	525.7	527.1	526.6	526.6	526.6	527.1	525.7	525.2	523.3	521.9	519.6
42.5°	508.8	509.9	508.6	507.9	508.6	509.9	508.8	508.0	506.8	504.4	501.7
45°	481.3	480.4	481.8	479.9	481.8	480.4	481.3	479.5	478.9	477.1	474.7
47.5°	450.5	451.4	451.8	453.2	451.8	451.4	450.5	450.7	448.1	446.9	446.2
50°	430.0	432.7	432.7	432.3	432.7	432.7	430.0	429.0	427.1	425.3	425.3
52.5°	409.7	411.1	413.0	412.9	413.0	411.1	409.7	408.1	406.3	403.6	402.9
55°	378.6	379.5	380.5	380.9	380.5	379.5	378.6	374.9	373.4	372.0	369.7
57.5°	346.3	345.9	348.1	348.8	348.1	345.9	346.3	343.0	340.8	336.5	335.9
60°	323.5	323.5	327.3	328.7	327.3	323.5	323.5	319.8	316.5	313.7	312.8
62.5°	299.3	300.8	304.4	302.5	304.4	300.8	299.3	295.2	292.6	289.1	286.6
65°	263.8	267.5	267.1	268.9	267.1	267.5	263.8	261.4	256.3	253.0	250.2
67.5°	226.7	229.0	232.4	232.6	232.4	229.0	226.7	222.9	219.6	216.2	212.8
70°	201.7	204.0	205.9	207.2	205.9	204.0	201.7	198.0	194.2	191.9	188.2
72.5°	177.4	178.6	183.1	181.1	183.1	178.6	177.4	172.9	170.0	168.0	163.9
75°	139.1	142.4	145.2	143.7	145.2	142.4	139.1	135.8	133.5	130.7	127.0
77.5°	102.9	106.1	107.5	106.3	107.5	106.1	102.9	100.8	99.5	94.0	93.6
80°	81.2	80.8	83.6	83.1	83.6	80.8	81.2	77.9	75.6	72.3	72.3
82.5°	59.6	59.1	60.4	60.7	60.4	59.1	59.6	57.8	54.8	53.3	52.2
85°	29.0	30.3	28.4	28.0	28.4	30.3	29.0	27.1	27.1	27.1	26.6
87.5°	10.5	10.5	10.3	9.9	10.3	10.5	10.5	10.4	11.9	10.6	10.5
90°	18.8	19.1	19.4	19.7	19.4	19.1	18.8	18.5	18.1	17.5	16.9
92.5°	21.2	21.4	21.6	21.8	21.6	21.4	21.2	21.0	20.5	19.6	18.6
95°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	24.4	23.4	22.4
97.5°	26.6	26.8	26.9	27.0	26.9	26.8	26.6	26.5	25.8	24.6	23.5
100°	27.1	27.3	27.4	27.6	27.4	27.3	27.1	27.0	26.3	25.1	24.0
102.5°	27.3	27.6	27.8	28.1	27.8	27.6	27.3	27.0	28.7	32.4	35.9
105°	28.0	28.3	28.6	28.9	28.6	28.3	28.0	27.7	40.5	66.3	92.1
107.5°	149.0	129.6	110.1	90.7	110.1	129.6	149.0	168.5	187.7	206.6	225.5
110°	243.0	222.1	201.3	180.5	201.3	222.1	243.0	263.9	276.7	281.5	286.3



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	322.8	318.4	314.0	309.6	314.0	318.4	322.8	327.2	329.4	329.3	329.2
115°	384.1	384.7	385.2	385.8	385.2	384.7	384.1	383.5	382.5	381.0	379.6
117.5°	428.3	428.4	428.5	428.6	428.5	428.4	428.3	428.1	427.5	426.3	425.2
120°	458.0	458.0	458.0	458.0	458.0	458.0	458.0	458.0	457.4	456.3	455.1
122.5°	486.5	486.6	486.8	486.9	486.8	486.6	486.5	486.4	486.0	485.1	484.3
125°	526.7	527.0	527.3	527.5	527.3	527.0	526.7	526.4	526.1	525.8	525.5
127.5°	567.6	567.2	566.9	566.7	566.9	567.2	567.6	567.8	567.8	567.3	566.9
130°	592.7	592.5	592.2	591.8	592.2	592.5	592.7	593.1	592.9	592.3	591.7
132.5°	616.2	615.8	615.4	614.9	615.4	615.8	616.2	616.6	616.5	615.9	615.4
135°	651.6	651.1	650.7	650.2	650.7	651.1	651.6	652.0	652.0	651.6	651.1
137.5°	684.4	684.0	683.8	683.5	683.8	684.0	684.4	684.7	684.5	683.8	683.1
140°	704.3	704.0	703.7	703.4	703.7	704.0	704.3	704.6	704.5	703.8	703.3
142.5°	723.0	722.6	722.2	721.8	722.2	722.6	723.0	723.4	723.4	722.9	722.5
145°	750.0	750.0	750.0	750.0	750.0	750.0	750.0	750.0	749.8	749.6	749.3
147.5°	773.0	772.3	771.7	771.0	771.7	772.3	773.0	773.6	773.9	773.6	773.3
150°	788.1	787.6	787.2	786.8	787.2	787.6	788.1	788.5	788.5	788.3	788.0
152.5°	801.4	800.7	800.0	799.3	800.0	800.7	801.4	802.0	802.1	801.6	801.0
155°	819.6	818.7	817.8	816.9	817.8	818.7	819.6	820.5	820.6	819.7	819.0
157.5°	835.2	834.0	832.9	831.8	832.9	834.0	835.2	836.3	836.4	835.5	834.7
160°	844.3	843.3	842.2	841.2	842.2	843.3	844.3	845.3	845.3	844.5	843.6
162.5°	852.8	851.9	851.0	850.2	851.0	851.9	852.8	853.7	853.7	852.7	851.8
165°	864.0	862.9	861.9	860.9	861.9	862.9	864.0	865.0	864.9	863.7	862.6
167.5°	872.2	870.9	869.8	868.6	869.8	870.9	872.2	873.3	873.3	872.2	870.9
170°	876.9	875.7	874.5	873.3	874.5	875.7	876.9	878.1	878.1	876.9	875.7
172.5°	879.9	878.6	877.3	876.0	877.3	878.6	879.9	881.1	881.2	880.0	878.9
175°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	884.7	883.7	882.6
177.5°	884.6	883.4	882.3	881.1	882.3	883.4	884.6	885.7	885.9	884.9	884.0
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	923.9	923.9	931.0	935.5	941.1	944.9	947.4	950.1	954.6	960.6	967.2
5°	871.1	873.0	883.2	893.5	903.3	911.7	918.7	927.1	937.4	950.0	964.0
7.5°	819.9	827.2	837.5	850.0	863.7	875.9	888.4	902.2	916.7	935.2	954.8
10°	787.1	795.0	807.6	823.5	837.9	852.4	867.8	882.8	901.0	922.9	948.2
12.5°	758.3	765.9	778.8	796.2	809.9	825.9	843.6	863.0	883.4	909.8	938.4
15°	718.5	727.3	743.2	751.6	772.6	791.8	808.1	836.1	862.2	889.3	922.5
17.5°	685.7	690.7	703.6	719.2	734.9	756.3	777.8	801.1	827.2	860.2	901.7
20°	663.3	667.5	681.5	697.9	714.7	734.3	753.5	776.8	806.2	841.2	886.0
22.5°	646.6	651.1	660.3	677.7	693.4	709.7	728.8	756.6	787.9	822.2	870.8
25°	622.2	625.1	631.2	645.2	659.2	677.3	694.2	720.3	752.5	792.6	841.2
27.5°	599.2	601.9	607.0	617.1	630.1	644.9	663.2	685.4	718.1	761.7	813.2
30°	585.4	585.9	590.6	599.9	611.1	623.2	640.0	665.2	696.1	740.4	794.5
32.5°	573.5	571.7	574.9	581.9	592.8	604.9	618.8	643.5	673.2	716.8	772.5
35°	553.2	552.2	550.9	557.0	566.2	575.6	587.7	606.5	640.0	680.6	739.0
37.5°	532.5	530.3	527.8	530.6	537.9	547.6	558.1	574.8	603.7	648.5	704.3
40°	517.3	515.4	514.0	513.0	519.6	528.9	536.8	552.7	579.8	622.2	677.3
42.5°	500.4	499.4	497.6	496.2	501.7	508.7	517.0	531.1	558.1	598.0	650.1
45°	473.3	472.4	471.5	470.6	473.9	480.4	486.9	497.1	520.5	559.3	606.5
47.5°	443.2	442.0	442.4	440.9	444.1	448.4	453.0	464.0	486.4	517.7	552.1
50°	421.5	421.1	421.1	421.1	422.0	427.1	431.3	439.8	460.3	491.6	516.3
52.5°	401.0	399.0	399.0	399.8	401.4	404.7	407.4	416.6	434.5	460.2	482.7
55°	368.8	365.1	364.1	365.1	366.5	369.3	372.0	379.5	394.9	414.1	427.1
57.5°	333.1	331.1	329.8	330.0	330.8	333.1	335.2	343.3	355.4	365.4	373.8
60°	308.1	309.1	304.9	305.8	305.8	307.6	310.9	316.0	326.3	333.3	341.7
62.5°	284.5	283.3	282.0	280.7	280.7	281.5	285.9	289.9	298.6	302.3	308.9
65°	247.9	247.9	245.0	246.0	246.5	243.3	245.6	250.2	255.8	257.3	263.3
67.5°	210.7	209.5	207.9	206.4	206.4	206.2	207.3	209.7	213.9	214.4	219.0
70°	185.3	184.4	184.0	182.5	180.7	183.0	181.6	184.0	186.3	186.7	189.5
72.5°	160.7	159.7	158.9	157.5	156.8	156.5	156.6	159.3	160.9	160.2	163.4
75°	125.6	124.7	123.7	121.4	121.4	119.9	120.5	122.3	124.2	122.8	125.6
77.5°	92.2	89.3	89.2	89.8	88.2	88.5	87.9	87.7	88.5	88.6	91.1
80°	71.0	67.7	68.7	68.1	67.7	67.2	66.3	66.8	67.2	67.7	69.1
82.5°	51.2	50.9	49.9	49.8	49.4	48.2	47.6	48.4	49.0	48.7	49.7
85°	26.1	24.7	25.7	25.2	25.7	25.2	23.8	23.8	24.7	24.3	25.2
87.5°	11.1	11.0	10.3	10.3	9.5	9.5	8.7	8.8	8.9	8.6	9.1
90°	16.3	15.8	13.8	11.9	10.1	8.2	6.5	5.0	3.6	2.1	0.6
92.5°	17.7	16.8	15.3	13.9	12.5	11.1	10.6	11.0	11.4	11.8	12.2
95°	21.4	20.3	18.7	17.1	15.5	13.9	16.1	22.1	28.1	34.1	40.0
97.5°	22.3	21.1	31.7	42.1	52.6	63.1	69.7	72.4	75.1	77.8	80.4
100°	22.8	21.7	44.4	67.1	89.9	112.6	122.5	119.7	116.7	113.8	110.9
102.5°	39.6	43.2	68.0	92.8	117.7	142.6	153.9	151.9	149.7	147.7	145.5
105°	117.9	143.7	156.9	170.0	183.1	196.2	202.0	200.4	198.8	197.2	195.6
107.5°	244.4	263.4	261.4	259.2	257.2	255.1	253.4	252.2	250.8	249.6	248.3
110°	291.1	296.0	294.4	292.7	291.1	289.5	288.1	287.0	285.8	284.6	283.5



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	329.0	327.4	325.8	324.2	322.6	321.3	320.2	319.1	318.1	317.1
115°	378.1	376.7	375.3	374.0	372.7	371.4	370.3	369.4	368.5	367.7	366.8
117.5°	424.0	422.8	422.1	421.5	420.8	420.2	419.3	418.2	417.1	416.1	415.0
120°	454.0	452.7	452.4	451.9	451.5	451.0	450.1	448.8	447.5	446.2	444.9
122.5°	483.5	482.7	482.1	481.6	481.0	480.5	479.7	478.6	477.5	476.4	475.4
125°	525.2	525.0	524.3	523.8	523.2	522.6	521.7	520.6	519.4	518.3	517.1
127.5°	566.3	565.9	565.2	564.5	563.8	563.1	562.1	561.0	559.8	558.7	557.5
130°	591.1	590.6	590.0	589.4	588.8	588.3	587.4	586.2	585.1	583.9	582.6
132.5°	614.7	614.2	613.7	613.2	612.8	612.3	611.5	610.3	609.1	608.0	606.8
135°	650.7	650.2	649.7	649.1	648.5	647.9	647.2	646.3	645.4	644.6	643.7
137.5°	682.3	681.6	681.4	681.0	680.6	680.4	679.7	678.5	677.4	676.3	675.2
140°	702.7	702.1	701.7	701.2	700.8	700.3	699.7	698.8	697.9	697.1	696.2
142.5°	722.0	721.6	721.1	720.7	720.2	719.8	719.2	718.3	717.4	716.5	715.6
145°	748.9	748.7	748.4	748.1	747.8	747.5	746.9	745.8	744.8	743.8	742.8
147.5°	773.0	772.7	772.4	772.1	771.9	771.5	771.1	770.3	769.7	769.0	768.4
150°	787.7	787.4	787.1	786.8	786.6	786.2	785.9	785.4	785.0	784.5	784.2
152.5°	800.5	800.0	799.9	799.7	799.5	799.3	799.2	798.9	798.7	798.5	798.3
155°	818.3	817.6	817.4	817.3	817.2	817.0	817.1	817.3	817.7	818.0	818.2
157.5°	833.8	832.9	833.1	833.2	833.4	833.6	833.7	833.7	833.7	833.7	833.7
160°	842.8	841.9	842.0	842.1	842.3	842.5	842.6	842.8	842.9	843.0	843.2
162.5°	850.8	849.7	849.9	850.1	850.2	850.3	850.6	851.0	851.3	851.8	852.1
165°	861.4	860.2	860.4	860.5	860.7	860.9	861.1	861.6	862.0	862.5	862.9
167.5°	869.8	868.6	868.6	868.6	868.6	868.6	869.0	869.5	870.1	870.7	871.3
170°	874.5	873.3	873.3	873.3	873.3	873.3	873.7	874.2	874.9	875.4	876.0
172.5°	877.7	876.6	876.4	876.3	876.2	876.0	876.4	877.1	877.7	878.4	879.1
175°	881.6	880.6	880.5	880.3	880.1	880.0	880.3	881.0	881.7	882.4	883.2
177.5°	883.1	882.2	882.1	881.9	881.8	881.7	881.9	882.5	883.1	883.7	884.2
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	969.5	971.3	977.8	982.2	987.4	990.4	993.4	995.7	998.6	999.3	1010.2
5°	973.8	983.1	999.5	1011.6	1026.5	1042.9	1054.1	1059.3	1072.7	1084.0	1106.3
7.5°	972.6	992.5	1017.1	1042.7	1070.1	1095.6	1117.6	1143.7	1162.3	1190.3	1217.7
10°	971.4	998.1	1029.8	1062.5	1100.8	1136.2	1168.0	1203.5	1232.9	1271.7	1304.8
12.5°	968.1	1000.3	1044.4	1083.1	1129.5	1178.5	1225.5	1271.0	1297.1	1361.6	1392.1
15°	959.8	998.1	1053.2	1112.0	1175.9	1233.9	1293.6	1341.2	1418.2	1474.7	1510.6
17.5°	944.0	997.6	1062.8	1133.8	1211.6	1287.9	1355.6	1427.8	1509.5	1577.9	1650.7
20°	936.5	995.2	1068.1	1146.6	1227.3	1313.7	1390.7	1477.5	1566.6	1633.9	1727.2
22.5°	922.7	989.3	1067.7	1155.1	1241.4	1330.8	1420.9	1508.5	1611.5	1704.1	1793.0
25°	900.0	974.7	1056.0	1153.5	1254.8	1344.4	1452.3	1568.5	1675.9	1794.9	1883.6
27.5°	876.3	956.1	1037.5	1128.2	1237.2	1343.5	1479.2	1610.5	1741.9	1844.6	1910.2
30°	858.0	935.5	1019.6	1111.1	1218.9	1345.4	1497.1	1640.4	1768.4	1856.5	1893.5
32.5°	838.2	916.9	991.1	1087.2	1202.1	1344.3	1508.3	1658.0	1769.9	1828.5	1821.4
35°	807.2	873.0	945.3	1037.8	1173.1	1336.1	1514.8	1659.6	1728.2	1715.6	1620.3
37.5°	762.3	817.7	888.9	990.2	1139.5	1318.8	1501.8	1610.3	1605.9	1503.2	1365.3
40°	734.3	781.5	850.1	956.5	1113.4	1307.6	1481.2	1551.8	1492.0	1348.6	1183.4
42.5°	697.8	741.1	809.8	919.2	1084.6	1284.8	1442.0	1462.5	1345.6	1180.6	1029.1
45°	641.0	679.2	750.2	863.2	1041.5	1235.2	1346.3	1296.4	1139.1	968.7	853.4
47.5°	580.0	619.7	688.0	804.1	979.1	1160.7	1213.5	1107.3	945.7	807.6	701.8
50°	541.5	579.8	646.6	763.8	936.9	1099.4	1121.3	984.1	835.6	714.3	627.4
52.5°	502.7	538.7	604.3	721.9	887.6	1028.4	1014.9	875.0	738.5	635.1	566.9
55°	444.9	478.9	541.5	651.7	802.5	914.0	865.0	731.6	618.6	538.2	486.4
57.5°	393.2	425.9	479.8	579.3	710.4	787.1	724.7	612.2	522.4	460.6	422.0
60°	358.0	387.0	438.4	530.7	644.7	703.0	641.4	542.0	466.4	416.9	382.4
62.5°	324.9	350.0	397.6	481.5	580.4	629.5	567.1	483.0	418.6	374.7	345.4
65°	274.5	297.4	339.4	404.7	486.0	518.6	464.9	396.8	346.9	314.1	294.5
67.5°	228.5	248.0	284.3	335.7	395.5	419.3	378.4	325.7	288.0	261.8	246.2
70°	198.0	214.7	243.3	287.6	341.7	359.9	321.6	278.2	250.7	229.7	215.2
72.5°	172.2	184.5	210.4	244.6	289.8	304.3	277.6	239.4	213.7	198.0	186.5
75°	131.2	141.4	158.3	185.8	217.0	225.5	205.4	181.6	164.3	153.1	144.3
77.5°	94.6	102.1	114.3	131.3	152.9	160.5	147.8	131.9	119.3	111.7	106.8
80°	71.4	77.5	87.7	101.7	114.9	119.0	111.6	99.4	90.6	86.4	82.1
82.5°	52.8	56.2	62.3	71.9	80.9	85.8	79.5	72.1	67.4	63.6	62.0
85°	26.6	28.4	31.3	35.0	40.6	42.4	40.1	38.3	35.5	33.2	33.2
87.5°	10.2	10.4	11.9	12.8	14.7	16.2	16.2	15.9	15.9	15.6	15.3
90°	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3	16.9
92.5°	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7	18.6
95°	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4	22.4
97.5°	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3	23.5
100°	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8	24.0
102.5°	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6	35.9
105°	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9	92.1
107.5°	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4	225.5
110°	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1	286.3





TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1	329.2
115°	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1	379.6
117.5°	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0	425.2
120°	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0	455.1
122.5°	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5	484.3
125°	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2	525.5
127.5°	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3	566.9
130°	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1	591.7
132.5°	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7	615.4
135°	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7	651.1
137.5°	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3	683.1
140°	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7	703.3
142.5°	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0	722.5
145°	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9	749.3
147.5°	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0	773.3
150°	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7	788.0
152.5°	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5	801.0
155°	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3	819.0
157.5°	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8	834.7
160°	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8	843.6
162.5°	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8	851.8
165°	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4	862.6
167.5°	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8	870.9
170°	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5	875.7
172.5°	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7	878.9
175°	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6	882.6
177.5°	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1	884.0
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1014.0	1014.3	1018.4	1021.5	1019.9	1021.8	1022.5
5°	1107.8	1124.6	1133.5	1140.0	1140.5	1140.9	1144.7
7.5°	1240.8	1258.8	1272.0	1292.0	1298.0	1304.8	1302.8
10°	1337.9	1364.5	1387.4	1399.5	1412.6	1431.7	1416.4
12.5°	1428.7	1475.9	1510.6	1529.6	1541.9	1545.7	1538.1
15°	1578.3	1639.9	1673.1	1672.1	1714.2	1732.4	1703.9
17.5°	1715.6	1772.5	1818.0	1841.4	1876.3	1884.1	1880.5
20°	1799.7	1861.7	1897.2	1937.3	1955.5	1971.8	1974.7
22.5°	1872.1	1927.8	1965.9	1999.3	2014.6	2022.3	2026.9
25°	1946.7	1990.6	2013.4	2025.1	2029.3	2028.4	2022.3
27.5°	1941.5	1944.9	1919.7	1895.0	1872.9	1847.9	1839.3
30°	1891.1	1851.9	1781.9	1742.2	1683.8	1637.6	1656.3
32.5°	1758.5	1680.5	1601.9	1515.1	1443.3	1422.9	1402.3
35°	1500.8	1363.6	1283.4	1189.9	1152.6	1115.3	1089.6
37.5°	1214.2	1108.0	1012.8	951.7	914.4	890.7	878.0
40°	1049.9	954.2	875.7	826.3	797.8	771.2	767.5
42.5°	918.8	829.8	770.8	731.4	704.1	692.8	684.6
45°	752.5	690.5	650.8	622.8	604.6	597.5	588.2
47.5°	636.9	593.1	563.3	544.2	530.5	525.3	524.5
50°	572.3	535.9	514.0	499.0	488.3	486.4	478.9
52.5°	523.8	492.2	475.1	462.1	454.3	449.1	446.8
55°	454.7	433.6	418.3	410.8	404.7	399.6	399.6
57.5°	397.8	380.3	370.1	363.7	361.9	358.2	355.9
60°	362.7	347.8	339.8	334.2	330.6	331.0	326.8
62.5°	328.3	318.7	311.1	305.5	301.0	301.1	301.4
65°	279.6	272.2	266.5	264.7	261.9	258.6	259.6
67.5°	236.9	230.0	225.6	222.4	221.5	219.7	222.4
70°	206.3	201.2	198.0	195.1	194.2	194.7	197.0
72.5°	178.3	174.7	172.5	171.2	169.2	169.2	170.9
75°	140.1	137.2	135.4	133.9	133.5	133.5	133.5
77.5°	102.9	102.3	101.4	99.3	99.4	100.0	100.0
80°	81.2	79.8	79.4	78.5	77.0	76.1	78.5
82.5°	60.7	59.3	58.9	58.7	56.4	56.3	58.2
85°	32.6	31.3	31.7	31.3	31.3	30.9	30.9
87.5°	15.1	14.8	14.5	15.0	14.6	14.4	15.2
90°	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	281.5	276.7	263.9	243.0	222.1	201.3	180.5



TEST NUMBER: P332156-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)