

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332459-940

Luminaire Tested: **S123RDIW-S1000D1030U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332459-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6719.2 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	95	91	88	92	88	85	82	75	73	71	63	62	60	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	2.1
10°-20°	435.5	6.5
20°-30°	684.2	10.2
30°-40°	713.8	10.6
40°-50°	610.9	9.1
50°-60°	465.6	6.9
60°-70°	298.4	4.4
70°-80°	143.6	2.1
80°-90°	41.4	0.6
90°-100°	74.9	1.1
100°-110°	224.2	3.3
110°-120°	381.4	5.7
120°-130°	501.7	7.5
130°-140°	563.9	8.4
140°-150°	554.3	8.2
150°-160°	466.6	6.9
160°-170°	310.6	4.6
170°-180°	108.8	1.6
0°-30°	1259.1	18.7
0°-40°	1973.0	29.4
0°-60°	3049.5	45.4
0°-90°	3532.9	52.6
90°-120°	680.6	10.1
90°-150°	2300.3	34.2
90°-180°	3186.0	47.4
0°-180°	6719.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	27	1	27	1	27	14
95°	70	53	70	53	70	72
105°	215	203	215	203	215	228
115°	385	384	385	384	385	381
125°	556	562	556	562	556	497
135°	728	729	728	729	728	560
145°	884	884	884	884	884	552
155°	1011	1013	1011	1013	1011	465
165°	1100	1103	1100	1103	1100	310
175°	1143	1147	1143	1147	1143	109
180°	1150	1150	1150	1150	1150	



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	10.3	11.1	10.1	10.5	10.4	10.8	10.6	10.5	11.3	10.6	10.6
90°	27.1	26.7	26.3	25.9	25.5	24.9	24.1	23.3	22.5	21.7	19.1
92.5°	36.5	36.7	37.0	37.2	37.5	37.3	36.6	35.9	35.3	34.7	33.2
95°	70.4	70.4	70.4	70.4	70.4	70.1	69.3	68.5	67.7	66.9	65.3
97.5°	108.4	108.5	108.6	108.6	108.7	108.3	107.4	106.5	105.6	104.6	103.4
100°	137.3	136.9	136.5	136.1	135.7	135.2	134.6	134.0	133.4	132.8	131.8
102.5°	166.9	167.0	167.1	167.2	167.3	167.0	166.4	165.8	165.2	164.6	163.3
105°	215.0	214.6	214.2	213.8	213.4	213.2	213.2	213.2	213.2	213.2	211.4
107.5°	265.0	265.3	265.6	265.8	266.0	265.8	265.2	264.6	263.9	263.2	262.5
110°	299.0	299.4	299.8	300.2	300.6	300.4	299.6	298.8	298.0	297.2	296.9



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	335.2	335.3	335.3	335.4	335.5	335.0	334.0	333.1	332.2	331.2	331.1
115°	384.9	385.0	385.2	385.5	385.7	385.7	385.5	385.2	385.0	384.9	385.2
117.5°	435.2	435.8	436.4	436.9	437.5	437.8	437.8	437.9	437.9	438.0	438.5
120°	470.6	471.1	471.4	471.9	472.3	472.6	472.8	473.0	473.1	473.4	474.4
122.5°	504.6	505.2	505.8	506.3	506.8	507.5	507.9	508.5	509.0	509.5	510.1
125°	555.6	556.4	557.2	558.0	558.8	559.6	560.4	561.2	562.0	562.8	563.2
127.5°	606.4	607.3	608.2	609.1	610.0	611.1	612.2	613.3	614.5	615.5	616.0
130°	639.6	641.1	642.4	643.8	645.2	646.3	647.1	647.9	648.7	649.5	650.1
132.5°	674.3	675.4	676.5	677.5	678.7	679.7	680.6	681.6	682.5	683.5	683.9
135°	728.2	728.5	729.0	729.3	729.8	730.3	731.1	731.9	732.7	733.5	733.8
137.5°	775.7	776.4	777.2	777.9	778.7	779.5	780.3	781.2	782.0	782.9	782.4
140°	806.7	808.2	809.6	810.9	812.3	813.2	813.3	813.6	813.8	814.0	813.8
142.5°	838.6	839.6	840.7	841.8	842.8	843.6	843.7	843.9	844.1	844.4	844.0
145°	884.4	885.2	886.0	886.8	887.6	888.1	888.3	888.6	888.8	888.9	888.3
147.5°	925.2	926.5	927.6	928.9	930.1	930.7	930.7	930.7	930.7	930.7	930.1
150°	951.3	952.5	953.7	954.9	956.1	956.7	956.7	956.7	956.7	956.7	956.3
152.5°	976.6	977.6	978.7	979.7	980.8	981.1	980.8	980.4	980.2	979.8	979.6
155°	1010.9	1012.4	1013.7	1015.1	1016.6	1016.8	1016.0	1015.2	1014.4	1013.6	1013.4
157.5°	1042.1	1043.3	1044.5	1045.5	1046.7	1046.8	1046.0	1045.1	1044.3	1043.4	1043.3
160°	1062.4	1063.2	1064.0	1064.8	1065.6	1065.5	1064.5	1063.5	1062.5	1061.5	1061.5
162.5°	1077.5	1078.9	1080.1	1081.5	1082.7	1082.9	1081.8	1080.8	1079.9	1078.9	1078.7
165°	1099.5	1100.8	1102.2	1103.7	1105.1	1105.2	1103.9	1102.8	1101.5	1100.4	1100.4
167.5°	1118.0	1119.3	1120.5	1121.8	1123.0	1123.0	1121.8	1120.5	1119.3	1118.0	1117.9
170°	1127.5	1128.8	1130.2	1131.7	1133.1	1133.1	1131.7	1130.2	1128.8	1127.5	1127.5
172.5°	1134.7	1136.0	1137.5	1138.9	1140.3	1140.4	1139.2	1137.9	1136.7	1135.4	1135.4
175°	1142.8	1144.2	1145.6	1147.0	1148.4	1148.5	1147.4	1146.1	1145.0	1143.7	1143.7
177.5°	1147.2	1148.3	1149.4	1150.5	1151.6	1151.7	1150.8	1149.8	1148.8	1147.9	1147.9
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	11.1	10.1	10.5	10.1	11.1	11.1	13.7	15.7	16.6	15.1	15.4
90°	16.5	13.8	11.2	8.9	7.0	4.9	2.9	0.9	2.9	4.9	7.0
92.5°	31.7	30.2	28.7	27.3	25.9	24.6	23.2	21.8	23.2	24.6	25.9
95°	63.7	62.1	60.5	58.9	57.5	56.1	54.7	53.3	54.7	56.1	57.5
97.5°	102.3	101.1	100.0	98.9	97.8	96.8	95.7	94.7	95.7	96.8	97.8
100°	130.8	129.8	128.8	127.7	126.4	125.3	124.0	122.9	124.0	125.3	126.4
102.5°	161.9	160.6	159.3	158.3	157.6	156.9	156.1	155.4	156.1	156.9	157.6
105°	209.6	207.8	206.0	204.9	204.5	204.1	203.7	203.3	203.7	204.1	204.5
107.5°	261.8	261.1	260.4	259.8	259.7	259.4	259.1	259.0	259.1	259.4	259.7
110°	296.4	296.0	295.6	295.2	294.8	294.4	294.0	293.6	294.0	294.4	294.8



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	331.0	330.9	330.8	330.7	330.5	330.2	330.0	329.8	330.0	330.2	330.5
115°	385.7	386.0	386.5	386.4	385.8	385.1	384.5	384.0	384.5	385.1	385.8
117.5°	439.0	439.5	440.1	440.1	439.7	439.3	438.9	438.5	438.9	439.3	439.7
120°	475.4	476.4	477.4	477.3	476.1	474.9	473.7	472.5	473.7	474.9	476.1
122.5°	510.6	511.1	511.6	511.4	510.5	509.7	508.8	507.9	508.8	509.7	510.5
125°	563.7	564.0	564.5	564.4	563.7	563.1	562.5	562.0	562.5	563.1	563.7
127.5°	616.4	616.9	617.3	616.9	615.6	614.4	613.1	611.8	613.1	614.4	615.6
130°	650.8	651.4	651.9	651.5	649.9	648.3	646.7	645.1	646.7	648.3	649.9
132.5°	684.4	684.8	685.3	684.7	683.1	681.4	679.8	678.2	679.8	681.4	683.1
135°	734.0	734.1	734.3	733.9	732.6	731.5	730.2	729.1	730.2	731.5	732.6
137.5°	781.9	781.3	780.8	780.1	779.0	778.0	777.0	776.1	777.0	778.0	779.0
140°	813.6	813.3	813.2	812.5	811.5	810.6	809.6	808.5	809.6	810.6	811.5
142.5°	843.6	843.2	842.8	842.2	841.2	840.2	839.2	838.2	839.2	840.2	841.2
145°	887.8	887.2	886.5	886.0	885.6	885.2	884.8	884.4	884.8	885.2	885.6
147.5°	929.6	929.0	928.4	927.8	927.1	926.3	925.6	924.9	925.6	926.3	927.1
150°	955.9	955.5	955.1	954.7	954.3	953.9	953.5	953.1	953.5	953.9	954.3
152.5°	979.4	979.1	978.8	978.5	977.9	977.3	976.8	976.2	976.8	977.3	977.9
155°	1013.3	1013.0	1012.8	1012.7	1012.7	1012.7	1012.7	1012.7	1012.7	1012.7	1012.7
157.5°	1043.1	1042.9	1042.8	1042.9	1043.0	1043.3	1043.6	1043.8	1043.6	1043.3	1043.0
160°	1061.5	1061.5	1061.5	1061.7	1062.1	1062.5	1062.9	1063.3	1062.9	1062.5	1062.1
162.5°	1078.5	1078.3	1078.2	1078.4	1079.0	1079.5	1080.1	1080.7	1080.1	1079.5	1079.0
165°	1100.4	1100.4	1100.4	1100.6	1101.3	1101.9	1102.4	1103.0	1102.4	1101.9	1101.3
167.5°	1117.8	1117.6	1117.4	1117.8	1118.6	1119.4	1120.2	1121.0	1120.2	1119.4	1118.6
170°	1127.5	1127.5	1127.5	1127.8	1128.6	1129.4	1130.2	1131.0	1130.2	1129.4	1128.6
172.5°	1135.4	1135.4	1135.4	1135.8	1136.6	1137.4	1138.2	1139.0	1138.2	1137.4	1136.6
175°	1143.7	1143.7	1143.7	1144.2	1145.0	1145.8	1146.6	1147.4	1146.6	1145.8	1145.0
177.5°	1147.9	1147.9	1147.9	1148.2	1148.8	1149.5	1150.1	1150.8	1150.1	1149.5	1148.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.3	17.3	18.3	19.4	20.3	20.3	21.0	21.1	21.8	21.9	22.1
90°	8.9	11.2	13.8	16.5	19.1	21.7	22.5	23.3	24.1	24.9	25.5
92.5°	27.3	28.7	30.2	31.7	33.2	34.7	35.3	35.9	36.6	37.3	37.5
95°	58.9	60.5	62.1	63.7	65.3	66.9	67.7	68.5	69.3	70.1	70.4
97.5°	98.9	100.0	101.1	102.3	103.4	104.6	105.6	106.5	107.4	108.3	108.7
100°	127.7	128.8	129.8	130.8	131.8	132.8	133.4	134.0	134.6	135.2	135.7
102.5°	158.3	159.3	160.6	161.9	163.3	164.6	165.2	165.8	166.4	167.0	167.3
105°	204.9	206.0	207.8	209.6	211.4	213.2	213.2	213.2	213.2	213.2	213.4
107.5°	259.8	260.4	261.1	261.8	262.5	263.2	263.9	264.6	265.2	265.8	266.0
110°	295.2	295.6	296.0	296.4	296.9	297.2	298.0	298.8	299.6	300.4	300.6



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	330.7	330.8	330.9	331.0	331.1	331.2	332.2	333.1	334.0	335.0	335.5
115°	386.4	386.5	386.0	385.7	385.2	384.9	385.0	385.2	385.5	385.7	385.7
117.5°	440.1	440.1	439.5	439.0	438.5	438.0	437.9	437.9	437.8	437.8	437.5
120°	477.3	477.4	476.4	475.4	474.4	473.4	473.1	473.0	472.8	472.6	472.3
122.5°	511.4	511.6	511.1	510.6	510.1	509.5	509.0	508.5	507.9	507.5	506.8
125°	564.4	564.5	564.0	563.7	563.2	562.8	562.0	561.2	560.4	559.6	558.8
127.5°	616.9	617.3	616.9	616.4	616.0	615.5	614.5	613.3	612.2	611.1	610.0
130°	651.5	651.9	651.4	650.8	650.1	649.5	648.7	647.9	647.1	646.3	645.2
132.5°	684.7	685.3	684.8	684.4	683.9	683.5	682.5	681.6	680.6	679.7	678.7
135°	733.9	734.3	734.1	734.0	733.8	733.5	732.7	731.9	731.1	730.3	729.8
137.5°	780.1	780.8	781.3	781.9	782.4	782.9	782.0	781.2	780.3	779.5	778.7
140°	812.5	813.2	813.3	813.6	813.8	814.0	813.8	813.6	813.3	813.2	812.3
142.5°	842.2	842.8	843.2	843.6	844.0	844.4	844.1	843.9	843.7	843.6	842.8
145°	886.0	886.5	887.2	887.8	888.3	888.9	888.8	888.6	888.3	888.1	887.6
147.5°	927.8	928.4	929.0	929.6	930.1	930.7	930.7	930.7	930.7	930.7	930.1
150°	954.7	955.1	955.5	955.9	956.3	956.7	956.7	956.7	956.7	956.7	956.1
152.5°	978.5	978.8	979.1	979.4	979.6	979.8	980.2	980.4	980.8	981.1	980.8
155°	1012.7	1012.8	1013.0	1013.3	1013.4	1013.6	1014.4	1015.2	1016.0	1016.8	1016.6
157.5°	1042.9	1042.8	1042.9	1043.1	1043.3	1043.4	1044.3	1045.1	1046.0	1046.8	1046.7
160°	1061.7	1061.5	1061.5	1061.5	1061.5	1061.5	1062.5	1063.5	1064.5	1065.5	1065.6
162.5°	1078.4	1078.2	1078.3	1078.5	1078.7	1078.9	1079.9	1080.8	1081.8	1082.9	1082.7
165°	1100.6	1100.4	1100.4	1100.4	1100.4	1100.4	1101.5	1102.8	1103.9	1105.2	1105.1
167.5°	1117.8	1117.4	1117.6	1117.8	1117.9	1118.0	1119.3	1120.5	1121.8	1123.0	1123.0
170°	1127.8	1127.5	1127.5	1127.5	1127.5	1127.5	1128.8	1130.2	1131.7	1133.1	1133.1
172.5°	1135.8	1135.4	1135.4	1135.4	1135.4	1135.4	1136.7	1137.9	1139.2	1140.4	1140.3
175°	1144.2	1143.7	1143.7	1143.7	1143.7	1143.7	1145.0	1146.1	1147.4	1148.5	1148.4
177.5°	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1148.8	1149.8	1150.8	1151.7	1151.6
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	23.2	22.3	22.3	22.9	22.3	22.3	23.2	22.1	21.9	21.8	21.1
90°	25.9	26.3	26.7	27.1	26.7	26.3	25.9	25.5	24.9	24.1	23.3
92.5°	37.2	37.0	36.7	36.5	36.7	37.0	37.2	37.5	37.3	36.6	35.9
95°	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.4	70.1	69.3	68.5
97.5°	108.6	108.6	108.5	108.4	108.5	108.6	108.6	108.7	108.3	107.4	106.5
100°	136.1	136.5	136.9	137.3	136.9	136.5	136.1	135.7	135.2	134.6	134.0
102.5°	167.2	167.1	167.0	166.9	167.0	167.1	167.2	167.3	167.0	166.4	165.8
105°	213.8	214.2	214.6	215.0	214.6	214.2	213.8	213.4	213.2	213.2	213.2
107.5°	265.8	265.6	265.3	265.0	265.3	265.6	265.8	266.0	265.8	265.2	264.6
110°	300.2	299.8	299.4	299.0	299.4	299.8	300.2	300.6	300.4	299.6	298.8



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	335.4	335.3	335.3	335.2	335.3	335.3	335.4	335.5	335.0	334.0	333.1
115°	385.5	385.2	385.0	384.9	385.0	385.2	385.5	385.7	385.7	385.5	385.2
117.5°	436.9	436.4	435.8	435.2	435.8	436.4	436.9	437.5	437.8	437.8	437.9
120°	471.9	471.4	471.1	470.6	471.1	471.4	471.9	472.3	472.6	472.8	473.0
122.5°	506.3	505.8	505.2	504.6	505.2	505.8	506.3	506.8	507.5	507.9	508.5
125°	558.0	557.2	556.4	555.6	556.4	557.2	558.0	558.8	559.6	560.4	561.2
127.5°	609.1	608.2	607.3	606.4	607.3	608.2	609.1	610.0	611.1	612.2	613.3
130°	643.8	642.4	641.1	639.6	641.1	642.4	643.8	645.2	646.3	647.1	647.9
132.5°	677.5	676.5	675.4	674.3	675.4	676.5	677.5	678.7	679.7	680.6	681.6
135°	729.3	729.0	728.5	728.2	728.5	729.0	729.3	729.8	730.3	731.1	731.9
137.5°	777.9	777.2	776.4	775.7	776.4	777.2	777.9	778.7	779.5	780.3	781.2
140°	810.9	809.6	808.2	806.7	808.2	809.6	810.9	812.3	813.2	813.3	813.6
142.5°	841.8	840.7	839.6	838.6	839.6	840.7	841.8	842.8	843.6	843.7	843.9
145°	886.8	886.0	885.2	884.4	885.2	886.0	886.8	887.6	888.1	888.3	888.6
147.5°	928.9	927.6	926.5	925.2	926.5	927.6	928.9	930.1	930.7	930.7	930.7
150°	954.9	953.7	952.5	951.3	952.5	953.7	954.9	956.1	956.7	956.7	956.7
152.5°	979.7	978.7	977.6	976.6	977.6	978.7	979.7	980.8	981.1	980.8	980.4
155°	1015.1	1013.7	1012.4	1010.9	1012.4	1013.7	1015.1	1016.6	1016.8	1016.0	1015.2
157.5°	1045.5	1044.5	1043.3	1042.1	1043.3	1044.5	1045.5	1046.7	1046.8	1046.0	1045.1
160°	1064.8	1064.0	1063.2	1062.4	1063.2	1064.0	1064.8	1065.6	1065.5	1064.5	1063.5
162.5°	1081.5	1080.1	1078.9	1077.5	1078.9	1080.1	1081.5	1082.7	1082.9	1081.8	1080.8
165°	1103.7	1102.2	1100.8	1099.5	1100.8	1102.2	1103.7	1105.1	1105.2	1103.9	1102.8
167.5°	1121.8	1120.5	1119.3	1118.0	1119.3	1120.5	1121.8	1123.0	1123.0	1121.8	1120.5
170°	1131.7	1130.2	1128.8	1127.5	1128.8	1130.2	1131.7	1133.1	1133.1	1131.7	1130.2
172.5°	1138.9	1137.5	1136.0	1134.7	1136.0	1137.5	1138.9	1140.3	1140.4	1139.2	1137.9
175°	1147.0	1145.6	1144.2	1142.8	1144.2	1145.6	1147.0	1148.4	1148.5	1147.4	1146.1
177.5°	1150.5	1149.4	1148.3	1147.2	1148.3	1149.4	1150.5	1151.6	1151.7	1150.8	1149.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	21.0	20.3	20.3	19.4	18.3	17.3	15.3	15.4	15.1	16.6	15.7
90°	22.5	21.7	19.1	16.5	13.8	11.2	8.9	7.0	4.9	2.9	0.9
92.5°	35.3	34.7	33.2	31.7	30.2	28.7	27.3	25.9	24.6	23.2	21.8
95°	67.7	66.9	65.3	63.7	62.1	60.5	58.9	57.5	56.1	54.7	53.3
97.5°	105.6	104.6	103.4	102.3	101.1	100.0	98.9	97.8	96.8	95.7	94.7
100°	133.4	132.8	131.8	130.8	129.8	128.8	127.7	126.4	125.3	124.0	122.9
102.5°	165.2	164.6	163.3	161.9	160.6	159.3	158.3	157.6	156.9	156.1	155.4
105°	213.2	213.2	211.4	209.6	207.8	206.0	204.9	204.5	204.1	203.7	203.3
107.5°	263.9	263.2	262.5	261.8	261.1	260.4	259.8	259.7	259.4	259.1	259.0
110°	298.0	297.2	296.9	296.4	296.0	295.6	295.2	294.8	294.4	294.0	293.6



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.2	331.2	331.1	331.0	330.9	330.8	330.7	330.5	330.2	330.0	329.8
115°	385.0	384.9	385.2	385.7	386.0	386.5	386.4	385.8	385.1	384.5	384.0
117.5°	437.9	438.0	438.5	439.0	439.5	440.1	440.1	439.7	439.3	438.9	438.5
120°	473.1	473.4	474.4	475.4	476.4	477.4	477.3	476.1	474.9	473.7	472.5
122.5°	509.0	509.5	510.1	510.6	511.1	511.6	511.4	510.5	509.7	508.8	507.9
125°	562.0	562.8	563.2	563.7	564.0	564.5	564.4	563.7	563.1	562.5	562.0
127.5°	614.5	615.5	616.0	616.4	616.9	617.3	616.9	615.6	614.4	613.1	611.8
130°	648.7	649.5	650.1	650.8	651.4	651.9	651.5	649.9	648.3	646.7	645.1
132.5°	682.5	683.5	683.9	684.4	684.8	685.3	684.7	683.1	681.4	679.8	678.2
135°	732.7	733.5	733.8	734.0	734.1	734.3	733.9	732.6	731.5	730.2	729.1
137.5°	782.0	782.9	782.4	781.9	781.3	780.8	780.1	779.0	778.0	777.0	776.1
140°	813.8	814.0	813.8	813.6	813.3	813.2	812.5	811.5	810.6	809.6	808.5
142.5°	844.1	844.4	844.0	843.6	843.2	842.8	842.2	841.2	840.2	839.2	838.2
145°	888.8	888.9	888.3	887.8	887.2	886.5	886.0	885.6	885.2	884.8	884.4
147.5°	930.7	930.7	930.1	929.6	929.0	928.4	927.8	927.1	926.3	925.6	924.9
150°	956.7	956.7	956.3	955.9	955.5	955.1	954.7	954.3	953.9	953.5	953.1
152.5°	980.2	979.8	979.6	979.4	979.1	978.8	978.5	977.9	977.3	976.8	976.2
155°	1014.4	1013.6	1013.4	1013.3	1013.0	1012.8	1012.7	1012.7	1012.7	1012.7	1012.7
157.5°	1044.3	1043.4	1043.3	1043.1	1042.9	1042.8	1042.9	1043.0	1043.3	1043.6	1043.8
160°	1062.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.7	1062.1	1062.5	1062.9	1063.3
162.5°	1079.9	1078.9	1078.7	1078.5	1078.3	1078.2	1078.4	1079.0	1079.5	1080.1	1080.7
165°	1101.5	1100.4	1100.4	1100.4	1100.4	1100.4	1100.6	1101.3	1101.9	1102.4	1103.0
167.5°	1119.3	1118.0	1117.9	1117.8	1117.6	1117.4	1117.8	1118.6	1119.4	1120.2	1121.0
170°	1128.8	1127.5	1127.5	1127.5	1127.5	1127.5	1127.8	1128.6	1129.4	1130.2	1131.0
172.5°	1136.7	1135.4	1135.4	1135.4	1135.4	1135.4	1135.8	1136.6	1137.4	1138.2	1139.0
175°	1145.0	1143.7	1143.7	1143.7	1143.7	1143.7	1144.2	1145.0	1145.8	1146.6	1147.4
177.5°	1148.8	1147.9	1147.9	1147.9	1147.9	1147.9	1148.2	1148.8	1149.5	1150.1	1150.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.7	11.1	11.1	10.1	10.5	10.1	11.1	10.6	10.6	11.3	10.5
90°	2.9	4.9	7.0	8.9	11.2	13.8	16.5	19.1	21.7	22.5	23.3
92.5°	23.2	24.6	25.9	27.3	28.7	30.2	31.7	33.2	34.7	35.3	35.9
95°	54.7	56.1	57.5	58.9	60.5	62.1	63.7	65.3	66.9	67.7	68.5
97.5°	95.7	96.8	97.8	98.9	100.0	101.1	102.3	103.4	104.6	105.6	106.5
100°	124.0	125.3	126.4	127.7	128.8	129.8	130.8	131.8	132.8	133.4	134.0
102.5°	156.1	156.9	157.6	158.3	159.3	160.6	161.9	163.3	164.6	165.2	165.8
105°	203.7	204.1	204.5	204.9	206.0	207.8	209.6	211.4	213.2	213.2	213.2
107.5°	259.1	259.4	259.7	259.8	260.4	261.1	261.8	262.5	263.2	263.9	264.6
110°	294.0	294.4	294.8	295.2	295.6	296.0	296.4	296.9	297.2	298.0	298.8



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	330.0	330.2	330.5	330.7	330.8	330.9	331.0	331.1	331.2	332.2	333.1
115°	384.5	385.1	385.8	386.4	386.5	386.0	385.7	385.2	384.9	385.0	385.2
117.5°	438.9	439.3	439.7	440.1	440.1	439.5	439.0	438.5	438.0	437.9	437.9
120°	473.7	474.9	476.1	477.3	477.4	476.4	475.4	474.4	473.4	473.1	473.0
122.5°	508.8	509.7	510.5	511.4	511.6	511.1	510.6	510.1	509.5	509.0	508.5
125°	562.5	563.1	563.7	564.4	564.5	564.0	563.7	563.2	562.8	562.0	561.2
127.5°	613.1	614.4	615.6	616.9	617.3	616.9	616.4	616.0	615.5	614.5	613.3
130°	646.7	648.3	649.9	651.5	651.9	651.4	650.8	650.1	649.5	648.7	647.9
132.5°	679.8	681.4	683.1	684.7	685.3	684.8	684.4	683.9	683.5	682.5	681.6
135°	730.2	731.5	732.6	733.9	734.3	734.1	734.0	733.8	733.5	732.7	731.9
137.5°	777.0	778.0	779.0	780.1	780.8	781.3	781.9	782.4	782.9	782.0	781.2
140°	809.6	810.6	811.5	812.5	813.2	813.3	813.6	813.8	814.0	813.8	813.6
142.5°	839.2	840.2	841.2	842.2	842.8	843.2	843.6	844.0	844.4	844.1	843.9
145°	884.8	885.2	885.6	886.0	886.5	887.2	887.8	888.3	888.9	888.8	888.6
147.5°	925.6	926.3	927.1	927.8	928.4	929.0	929.6	930.1	930.7	930.7	930.7
150°	953.5	953.9	954.3	954.7	955.1	955.5	955.9	956.3	956.7	956.7	956.7
152.5°	976.8	977.3	977.9	978.5	978.8	979.1	979.4	979.6	979.8	980.2	980.4
155°	1012.7	1012.7	1012.7	1012.7	1012.8	1013.0	1013.3	1013.4	1013.6	1014.4	1015.2
157.5°	1043.6	1043.3	1043.0	1042.9	1042.8	1042.9	1043.1	1043.3	1043.4	1044.3	1045.1
160°	1062.9	1062.5	1062.1	1061.7	1061.5	1061.5	1061.5	1061.5	1061.5	1062.5	1063.5
162.5°	1080.1	1079.5	1079.0	1078.4	1078.2	1078.3	1078.5	1078.7	1078.9	1079.9	1080.8
165°	1102.4	1101.9	1101.3	1100.6	1100.4	1100.4	1100.4	1100.4	1100.4	1101.5	1102.8
167.5°	1120.2	1119.4	1118.6	1117.8	1117.4	1117.6	1117.8	1117.9	1118.0	1119.3	1120.5
170°	1130.2	1129.4	1128.6	1127.8	1127.5	1127.5	1127.5	1127.5	1127.5	1128.8	1130.2
172.5°	1138.2	1137.4	1136.6	1135.8	1135.4	1135.4	1135.4	1135.4	1135.4	1136.7	1137.9
175°	1146.6	1145.8	1145.0	1144.2	1143.7	1143.7	1143.7	1143.7	1143.7	1145.0	1146.1
177.5°	1150.1	1149.5	1148.8	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1148.8	1149.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	10.6	10.8	10.4	10.5	10.1	11.1	10.3
90°	24.1	24.9	25.5	25.9	26.3	26.7	27.1
92.5°	36.6	37.3	37.5	37.2	37.0	36.7	36.5
95°	69.3	70.1	70.4	70.4	70.4	70.4	70.4
97.5°	107.4	108.3	108.7	108.6	108.6	108.5	108.4
100°	134.6	135.2	135.7	136.1	136.5	136.9	137.3
102.5°	166.4	167.0	167.3	167.2	167.1	167.0	166.9
105°	213.2	213.2	213.4	213.8	214.2	214.6	215.0
107.5°	265.2	265.8	266.0	265.8	265.6	265.3	265.0
110°	299.6	300.4	300.6	300.2	299.8	299.4	299.0



TEST NUMBER: P332459-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	334.0	335.0	335.5	335.4	335.3	335.3	335.2
115°	385.5	385.7	385.7	385.5	385.2	385.0	384.9
117.5°	437.8	437.8	437.5	436.9	436.4	435.8	435.2
120°	472.8	472.6	472.3	471.9	471.4	471.1	470.6
122.5°	507.9	507.5	506.8	506.3	505.8	505.2	504.6
125°	560.4	559.6	558.8	558.0	557.2	556.4	555.6
127.5°	612.2	611.1	610.0	609.1	608.2	607.3	606.4
130°	647.1	646.3	645.2	643.8	642.4	641.1	639.6
132.5°	680.6	679.7	678.7	677.5	676.5	675.4	674.3
135°	731.1	730.3	729.8	729.3	729.0	728.5	728.2
137.5°	780.3	779.5	778.7	777.9	777.2	776.4	775.7
140°	813.3	813.2	812.3	810.9	809.6	808.2	806.7
142.5°	843.7	843.6	842.8	841.8	840.7	839.6	838.6
145°	888.3	888.1	887.6	886.8	886.0	885.2	884.4
147.5°	930.7	930.7	930.1	928.9	927.6	926.5	925.2
150°	956.7	956.7	956.1	954.9	953.7	952.5	951.3
152.5°	980.8	981.1	980.8	979.7	978.7	977.6	976.6
155°	1016.0	1016.8	1016.6	1015.1	1013.7	1012.4	1010.9
157.5°	1046.0	1046.8	1046.7	1045.5	1044.5	1043.3	1042.1
160°	1064.5	1065.5	1065.6	1064.8	1064.0	1063.2	1062.4
162.5°	1081.8	1082.9	1082.7	1081.5	1080.1	1078.9	1077.5
165°	1103.9	1105.2	1105.1	1103.7	1102.2	1100.8	1099.5
167.5°	1121.8	1123.0	1123.0	1121.8	1120.5	1119.3	1118.0
170°	1131.7	1133.1	1133.1	1131.7	1130.2	1128.8	1127.5
172.5°	1139.2	1140.4	1140.3	1138.9	1137.5	1136.0	1134.7
175°	1147.4	1148.5	1148.4	1147.0	1145.6	1144.2	1142.8
177.5°	1150.8	1151.7	1151.6	1150.5	1149.4	1148.3	1147.2
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0

(END OF REPORT)