

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332455

Luminaire Tested: **S123RDIW-S1000D755U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332455
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D755U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6578.9 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332455
CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	39	35	33	30
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	36	32	29	26
7	62	49	42	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17111	17111	17111	17111
5°	20398	17184	15132	17184
10°	25468	17086	13671	17086
15°	29895	16912	12467	16912
20°	33364	16651	11443	16651
25°	32831	16376	10815	16376
30°	23599	16122	10167	16122
35°	15757	15792	9747	15792
40°	11609	15396	9313	15396
45°	9738	14700	8888	14700
50°	8592	13788	8296	13788
55°	7535	12746	7484	12746
60°	6710	11750	6857	11750
65°	5894	10677	6378	10677
70°	4626	9725	5825	9725
75°	4076	8492	5319	8492
80°	3546	7215	5232	7215
85°	2853	5805	5545	5805



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	2.4
10°-20°	488.4	7.4
20°-30°	767.3	11.7
30°-40°	800.5	12.2
40°-50°	685.1	10.4
50°-60°	522.2	7.9
60°-70°	334.7	5.1
70°-80°	161.0	2.4
80°-90°	45.4	0.7
90°-100°	61.6	0.9
100°-110°	184.2	2.8
110°-120°	313.4	4.8
120°-130°	412.2	6.3
130°-140°	463.3	7.0
140°-150°	455.4	6.9
150°-160°	383.4	5.8
160°-170°	255.2	3.9
170°-180°	89.4	1.4
0°-30°	1412.0	21.5
0°-40°	2212.6	33.6
0°-60°	3419.8	52.0
0°-90°	3960.9	60.2
90°-120°	559.2	8.5
90°-150°	1890.0	28.7
90°-180°	2618.0	39.8
0°-180°	6578.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1888	1590	1400	1590	1888	195
15°	2683	1518	1119	1518	2683	761
25°	2764	1379	911	1379	2764	1188
35°	1199	1202	742	1202	1199	786
45°	640	966	584	966	640	503
55°	402	679	399	679	402	363
65°	231	419	250	419	231	228
75°	98	204	128	204	98	105
85°	23	47	45	47	23	27
90°	22	1	22	1	22	12
95°	58	44	58	44	58	59
105°	177	167	177	167	177	187
115°	316	316	316	316	316	313
125°	456	462	456	462	456	408
135°	598	599	598	599	598	460
145°	727	727	727	727	727	454
155°	831	832	831	832	831	382
165°	903	906	903	906	903	255
175°	939	943	939	943	939	89
180°	945	945	945	945	945	



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1693.2	1695.3	1688.3	1687.2	1679.0	1676.8	1676.8	1665.4	1658.3	1649.1	1643.6
5°	1887.8	1898.7	1893.2	1881.0	1860.6	1855.8	1842.9	1822.5	1799.3	1770.7	1757.1
7.5°	2130.9	2145.7	2140.0	2121.1	2099.7	2082.4	2046.0	2012.1	1964.6	1922.9	1887.3
10°	2330.1	2314.5	2302.2	2283.9	2264.1	2232.1	2194.0	2141.6	2081.1	2033.4	1980.4
12.5°	2479.3	2476.7	2461.2	2442.3	2414.4	2384.0	2337.2	2273.4	2203.0	2134.2	2073.4
15°	2682.7	2686.7	2676.5	2656.8	2617.3	2563.6	2492.8	2466.3	2365.5	2290.7	2215.8
17.5°	2823.4	2822.6	2821.2	2793.9	2753.6	2715.3	2649.7	2579.9	2488.7	2383.2	2282.4
20°	2912.7	2905.9	2907.2	2876.6	2846.7	2802.4	2738.5	2637.1	2562.2	2440.4	2336.3
22.5°	2910.5	2909.1	2914.3	2903.8	2882.1	2848.2	2797.8	2712.2	2616.6	2493.7	2376.6
25°	2764.3	2758.9	2790.9	2799.7	2834.4	2840.5	2825.6	2778.6	2688.1	2561.5	2416.6
27.5°	2313.5	2310.5	2369.9	2444.2	2538.4	2611.6	2682.4	2716.6	2688.1	2597.5	2452.2
30°	1898.7	1962.7	1992.6	2100.1	2219.9	2362.8	2488.0	2607.1	2636.4	2596.9	2477.8
32.5°	1576.4	1632.2	1657.2	1749.5	1861.1	2028.5	2216.4	2385.0	2504.1	2534.3	2462.6
35°	1199.1	1199.8	1256.9	1297.8	1401.2	1573.4	1755.8	1981.7	2206.3	2376.4	2394.1
37.5°	956.8	960.2	994.8	1035.5	1113.1	1204.1	1364.7	1552.6	1812.0	2073.2	2226.3
40°	826.2	832.3	858.2	898.3	954.1	1022.8	1148.1	1325.0	1541.4	1832.0	2069.5
42.5°	742.3	752.3	765.6	796.5	831.1	895.4	996.7	1133.4	1330.2	1605.0	1879.0
45°	639.7	645.1	655.4	669.6	700.9	745.9	813.9	905.8	1069.1	1290.3	1564.5
47.5°	564.3	561.4	572.2	583.8	604.6	635.2	680.8	755.8	872.3	1049.8	1282.4
50°	513.1	512.4	519.9	528.8	548.5	571.0	608.4	664.9	757.4	904.4	1117.4
52.5°	465.2	467.8	473.1	484.1	498.4	516.5	550.1	590.8	670.3	797.2	974.8
55°	401.5	403.6	411.0	417.2	427.4	445.7	466.8	500.9	555.3	643.8	790.1
57.5°	347.6	346.7	353.9	355.4	366.9	381.9	398.2	424.7	464.1	529.9	628.4
60°	311.7	309.6	315.8	320.5	326.7	338.9	352.5	378.4	409.7	458.0	542.4
62.5°	279.0	278.1	282.6	287.3	292.4	303.5	315.0	334.8	359.6	400.3	467.3
65°	231.4	233.4	235.5	237.5	240.2	247.0	257.9	271.5	288.5	317.1	365.4
67.5°	181.8	183.9	184.6	188.8	194.6	198.9	205.5	217.6	229.5	253.6	281.1
70°	147.0	146.3	147.0	149.0	156.5	164.0	172.9	181.7	189.2	206.2	229.3
72.5°	126.3	125.1	126.9	127.3	130.9	133.0	138.6	146.9	156.5	168.1	184.7
75°	98.0	98.0	98.0	98.0	100.7	102.1	104.1	106.2	109.6	115.0	127.3
77.5°	72.4	72.5	73.5	74.2	74.7	75.5	76.8	78.8	80.0	82.9	88.2
80°	57.2	57.8	57.2	57.8	57.8	59.2	59.9	61.9	62.6	66.0	68.1
82.5°	43.0	42.6	43.0	43.7	43.7	45.1	45.2	46.7	46.8	48.6	50.6
85°	23.1	21.8	23.1	22.5	23.8	22.5	23.1	24.5	24.5	25.2	27.9
87.5°	9.9	10.9	9.8	10.2	10.2	10.6	10.5	10.4	11.3	10.6	10.8
90°	22.3	21.9	21.6	21.3	20.9	20.5	19.8	19.1	18.5	17.8	15.7
92.5°	30.0	30.2	30.4	30.6	30.8	30.6	30.1	29.6	29.0	28.5	27.3
95°	57.9	57.9	57.9	57.9	57.9	57.6	56.9	56.2	55.6	54.9	53.6
97.5°	89.1	89.1	89.2	89.3	89.3	89.0	88.2	87.5	86.7	86.0	85.0
100°	112.8	112.5	112.2	111.8	111.5	111.1	110.6	110.1	109.6	109.1	108.3
102.5°	137.2	137.2	137.3	137.4	137.4	137.2	136.7	136.2	135.7	135.2	134.1
105°	176.7	176.3	176.0	175.7	175.3	175.2	175.2	175.2	175.2	175.2	173.7
107.5°	217.8	218.0	218.2	218.4	218.6	218.4	217.9	217.3	216.8	216.3	215.7
110°	245.7	246.0	246.3	246.7	247.0	246.8	246.2	245.5	244.9	244.2	243.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.4	275.4	275.5	275.6	275.6	275.3	274.5	273.7	272.9	272.1	272.0
115°	316.2	316.4	316.5	316.7	316.9	316.9	316.7	316.5	316.4	316.2	316.5
117.5°	357.6	358.1	358.5	359.0	359.5	359.7	359.7	359.8	359.8	359.8	360.3
120°	386.7	387.0	387.4	387.7	388.0	388.3	388.4	388.6	388.8	388.9	389.8
122.5°	414.6	415.1	415.5	416.0	416.5	416.9	417.3	417.8	418.2	418.6	419.1
125°	456.5	457.1	457.8	458.5	459.1	459.8	460.4	461.1	461.8	462.4	462.7
127.5°	498.2	499.0	499.7	500.5	501.2	502.1	503.0	503.9	504.8	505.8	506.1
130°	525.5	526.7	527.8	529.0	530.1	531.0	531.7	532.4	533.0	533.7	534.2
132.5°	554.0	554.9	555.8	556.7	557.6	558.4	559.2	560.0	560.8	561.6	561.9
135°	598.2	598.6	598.9	599.2	599.6	600.1	600.7	601.4	602.0	602.7	602.9
137.5°	637.3	637.9	638.5	639.2	639.8	640.5	641.1	641.8	642.5	643.2	642.8
140°	662.8	664.0	665.1	666.3	667.4	668.1	668.3	668.4	668.6	668.8	668.6
142.5°	688.9	689.8	690.7	691.6	692.5	693.0	693.2	693.4	693.5	693.7	693.4
145°	726.7	727.3	728.0	728.6	729.3	729.7	729.9	730.0	730.2	730.4	729.9
147.5°	760.2	761.2	762.2	763.2	764.2	764.7	764.7	764.7	764.7	764.7	764.2
150°	781.6	782.6	783.6	784.5	785.5	786.0	786.0	786.0	786.0	786.0	785.7
152.5°	802.4	803.2	804.1	804.9	805.8	806.1	805.8	805.6	805.3	805.0	804.8
155°	830.6	831.7	832.9	834.0	835.2	835.4	834.8	834.1	833.5	832.8	832.6
157.5°	856.2	857.2	858.1	859.0	859.9	860.1	859.4	858.7	858.0	857.3	857.2
160°	872.9	873.5	874.2	874.9	875.5	875.4	874.6	873.8	873.0	872.1	872.1
162.5°	885.3	886.4	887.5	888.5	889.6	889.7	888.9	888.0	887.2	886.4	886.3
165°	903.3	904.5	905.6	906.8	907.9	908.0	907.0	906.0	905.0	904.0	904.0
167.5°	918.6	919.6	920.6	921.7	922.7	922.7	921.7	920.6	919.6	918.6	918.5
170°	926.3	927.5	928.6	929.8	930.9	930.9	929.8	928.6	927.5	926.3	926.3
172.5°	932.3	933.4	934.6	935.7	936.9	936.9	935.9	934.9	933.9	932.8	932.8
175°	938.9	940.1	941.2	942.4	943.6	943.6	942.6	941.7	940.7	939.7	939.7
177.5°	942.5	943.4	944.3	945.3	946.2	946.3	945.5	944.7	943.9	943.1	943.1
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1641.4	1639.8	1632.2	1623.5	1612.0	1604.4	1598.4	1595.2	1585.4	1573.4	1565.2
5°	1742.8	1722.4	1700.7	1674.1	1649.6	1624.4	1608.8	1590.4	1567.9	1542.8	1525.1
7.5°	1851.5	1811.4	1768.3	1723.8	1679.8	1640.4	1605.5	1575.7	1539.9	1503.8	1478.5
10°	1934.8	1876.2	1815.7	1753.7	1697.2	1644.2	1603.3	1563.2	1520.3	1478.8	1447.5
12.5°	2010.4	1933.4	1863.6	1787.5	1715.2	1651.8	1593.0	1545.8	1494.2	1449.9	1414.3
15°	2106.2	2027.3	1942.9	1827.2	1731.3	1651.0	1579.5	1517.6	1455.0	1400.5	1365.8
17.5°	2195.8	2077.0	1963.6	1867.1	1742.4	1642.1	1554.9	1480.8	1412.1	1354.4	1311.7
20°	2232.8	2117.8	1994.6	1871.5	1749.0	1636.7	1535.3	1453.6	1382.2	1316.8	1277.4
22.5°	2255.1	2124.9	1995.2	1862.8	1732.6	1616.0	1515.7	1425.9	1348.4	1286.3	1237.6
25°	2281.1	2126.0	1983.1	1852.4	1719.7	1593.1	1474.0	1378.8	1295.1	1229.0	1177.3
27.5°	2298.3	2115.8	1946.9	1801.6	1667.0	1541.0	1431.8	1330.8	1245.9	1176.1	1120.6
30°	2301.6	2107.6	1919.1	1761.9	1625.1	1509.4	1393.7	1297.1	1207.3	1133.1	1081.4
32.5°	2305.9	2087.5	1881.5	1714.5	1574.5	1459.9	1355.1	1262.8	1170.8	1097.7	1044.9
35°	2288.0	2076.3	1824.5	1632.6	1492.4	1381.5	1286.9	1201.8	1111.3	1040.5	986.8
37.5°	2210.6	2032.1	1765.4	1540.3	1393.7	1291.0	1213.9	1139.8	1056.7	980.4	929.7
40°	2132.8	1988.5	1719.7	1484.2	1331.1	1225.6	1156.2	1095.7	1015.4	943.9	889.5
42.5°	2016.8	1929.2	1676.2	1425.4	1260.3	1158.7	1100.1	1043.4	972.9	900.3	849.2
45°	1804.1	1815.7	1587.0	1331.8	1162.3	1060.3	1005.1	965.7	903.1	843.2	790.8
47.5°	1537.3	1645.5	1482.3	1232.0	1059.0	963.2	915.0	880.6	838.4	779.6	731.8
50°	1363.1	1517.6	1398.5	1165.1	994.3	899.0	851.3	823.4	786.7	740.4	694.8
52.5°	1202.5	1368.4	1297.2	1090.5	924.0	836.9	790.4	767.4	738.2	694.7	653.4
55°	980.6	1148.7	1132.4	977.9	818.7	740.4	705.0	679.2	659.4	626.8	594.1
57.5°	793.2	952.6	961.0	852.7	725.9	648.5	618.1	598.6	585.7	561.0	530.8
60°	675.1	821.4	850.0	768.3	659.4	591.4	561.4	545.8	535.6	515.8	492.7
62.5°	577.1	701.6	734.0	675.2	595.7	532.0	508.6	493.5	486.6	469.6	449.2
65°	441.7	545.1	576.4	543.7	502.2	451.2	432.1	419.2	413.1	403.6	388.6
67.5°	332.1	407.5	441.8	418.8	403.8	371.6	359.5	352.5	347.1	340.5	328.0
70°	266.8	322.6	358.0	351.8	339.6	322.6	313.7	309.0	303.5	298.1	287.2
72.5°	214.5	252.9	286.1	289.2	279.2	275.8	268.0	266.0	262.7	256.2	250.2
75°	142.2	168.8	191.9	200.8	204.8	208.2	204.8	204.2	203.5	198.0	194.6
77.5°	93.2	107.5	122.1	137.2	143.6	148.2	149.3	151.8	150.0	147.1	145.5
80°	71.5	74.9	85.1	98.0	108.2	112.3	115.0	116.4	115.7	115.0	112.3
82.5°	51.9	54.7	59.5	68.6	77.2	84.0	85.6	85.3	86.8	87.2	85.1
85°	27.9	28.6	29.9	31.3	36.1	43.6	45.6	47.0	48.3	48.3	44.2
87.5°	11.4	10.4	11.1	10.7	12.0	12.2	15.2	17.6	18.4	16.6	16.9
90°	13.5	11.4	9.2	7.3	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	26.1	24.8	23.6	22.4	21.3	20.2	19.1	18.0	19.1	20.2	21.3
95°	52.3	51.0	49.6	48.4	47.3	46.1	44.9	43.8	44.9	46.1	47.3
97.5°	84.0	83.1	82.1	81.2	80.4	79.5	78.6	77.8	78.6	79.5	80.4
100°	107.5	106.6	105.8	104.9	103.9	102.9	101.9	100.9	101.9	102.9	103.9
102.5°	133.1	132.0	130.9	130.0	129.4	128.9	128.3	127.7	128.3	128.9	129.4
105°	172.2	170.7	169.2	168.3	168.0	167.7	167.3	167.0	167.3	167.7	168.0
107.5°	215.1	214.5	213.9	213.5	213.3	213.1	212.9	212.7	212.9	213.1	213.3
110°	243.5	243.2	242.9	242.5	242.2	241.9	241.6	241.2	241.6	241.9	242.2



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	271.9	271.8	271.7	271.5	271.3	271.1	270.9	271.1	271.3	271.5
115°	316.9	317.2	317.5	317.4	316.9	316.4	315.9	315.5	315.9	316.4	316.9
117.5°	360.7	361.1	361.6	361.6	361.3	360.9	360.6	360.3	360.6	360.9	361.3
120°	390.6	391.4	392.2	392.2	391.2	390.2	389.2	388.2	389.2	390.2	391.2
122.5°	419.5	419.9	420.3	420.2	419.5	418.7	418.0	417.3	418.0	418.7	419.5
125°	463.1	463.4	463.7	463.7	463.2	462.7	462.2	461.7	462.2	462.7	463.2
127.5°	506.5	506.9	507.2	506.9	505.8	504.8	503.7	502.6	503.7	504.8	505.8
130°	534.7	535.2	535.7	535.2	533.9	532.6	531.3	530.0	531.3	532.6	533.9
132.5°	562.3	562.7	563.0	562.6	561.2	559.9	558.6	557.3	558.6	559.9	561.2
135°	603.0	603.2	603.4	602.9	602.0	601.0	600.0	599.0	600.0	601.0	602.0
137.5°	642.4	641.9	641.5	640.9	640.1	639.2	638.4	637.6	638.4	639.2	640.1
140°	668.4	668.3	668.1	667.6	666.8	666.0	665.1	664.3	665.1	666.0	666.8
142.5°	693.1	692.8	692.5	691.9	691.1	690.3	689.5	688.7	689.5	690.3	691.1
145°	729.4	728.9	728.4	728.0	727.6	727.3	727.0	726.7	727.0	727.3	727.6
147.5°	763.7	763.3	762.8	762.3	761.7	761.1	760.5	759.9	760.5	761.1	761.7
150°	785.4	785.0	784.7	784.4	784.1	783.7	783.4	783.1	783.4	783.7	784.1
152.5°	804.6	804.4	804.2	803.9	803.5	803.0	802.5	802.1	802.5	803.0	803.5
155°	832.5	832.3	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
157.5°	857.0	856.9	856.8	856.8	857.0	857.2	857.4	857.6	857.4	857.2	857.0
160°	872.1	872.1	872.1	872.3	872.6	873.0	873.3	873.6	873.3	873.0	872.6
162.5°	886.1	886.0	885.9	886.0	886.5	886.9	887.4	887.9	887.4	886.9	886.5
165°	904.0	904.0	904.0	904.3	904.8	905.3	905.8	906.3	905.8	905.3	904.8
167.5°	918.3	918.2	918.1	918.3	919.0	919.7	920.3	921.0	920.3	919.7	919.0
170°	926.3	926.3	926.3	926.6	927.3	928.0	928.6	929.3	928.6	928.0	927.3
172.5°	932.8	932.8	932.8	933.2	933.8	934.5	935.2	935.8	935.2	934.5	933.8
175°	939.7	939.7	939.7	940.0	940.7	941.3	942.0	942.6	942.0	941.3	940.7
177.5°	943.1	943.1	943.1	943.4	943.9	944.4	944.9	945.5	944.9	944.4	943.9
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1562.5	1555.4	1550.5	1539.6	1532.6	1524.9	1517.3	1522.2	1521.7	1521.1	1521.1
5°	1510.1	1494.4	1480.2	1461.8	1450.2	1435.9	1425.0	1423.7	1426.4	1416.9	1411.4
7.5°	1458.1	1436.7	1416.5	1396.2	1374.7	1357.5	1346.8	1341.7	1334.8	1328.9	1322.8
10°	1421.6	1396.5	1376.7	1351.5	1328.4	1308.0	1295.1	1286.2	1281.4	1276.7	1267.8
12.5°	1384.1	1359.4	1334.3	1305.8	1283.8	1260.1	1250.4	1240.5	1231.4	1226.0	1213.9
15°	1329.1	1297.1	1270.6	1240.6	1216.1	1193.0	1179.4	1159.6	1156.9	1150.1	1137.9
17.5°	1274.0	1239.2	1202.6	1180.5	1152.8	1128.7	1108.0	1101.4	1081.9	1074.6	1063.9
20°	1230.4	1198.4	1170.5	1141.3	1101.1	1078.6	1062.3	1053.5	1037.8	1028.3	1021.5
22.5°	1192.8	1160.3	1128.1	1093.9	1060.8	1035.6	1023.7	1009.9	1001.3	988.0	980.6
25°	1139.2	1103.8	1065.0	1028.3	1004.5	985.4	966.4	954.1	941.9	935.7	922.1
27.5°	1076.9	1039.9	1003.6	975.7	946.5	927.7	910.4	899.5	884.8	874.5	867.0
30°	1042.6	999.0	967.7	942.5	905.1	887.4	874.5	860.9	850.0	839.1	831.6
32.5°	1002.8	963.1	933.4	902.3	873.5	854.2	837.5	825.5	816.2	805.9	798.4
35°	940.5	907.2	876.5	845.2	824.1	804.4	784.7	774.4	765.6	756.1	749.3
37.5°	884.1	853.0	823.9	794.2	768.0	752.0	736.1	728.3	716.3	709.9	703.0
40°	849.3	818.7	787.4	758.8	731.6	719.3	705.0	693.5	682.6	677.8	670.3
42.5°	811.2	780.6	754.2	723.4	701.1	684.5	671.3	658.6	650.5	643.5	639.3
45°	754.7	727.5	701.6	671.0	649.9	635.6	620.6	609.1	601.6	596.8	589.3
47.5°	699.9	672.6	646.4	619.7	599.3	582.9	568.0	559.9	550.0	544.2	539.1
50°	660.1	635.6	607.7	583.2	562.8	546.5	534.2	524.0	515.2	507.7	504.3
52.5°	623.6	597.5	573.4	550.6	529.0	510.5	499.4	488.6	482.0	473.4	469.4
55°	563.5	538.3	517.9	495.4	474.3	458.7	445.1	435.5	428.7	419.2	413.8
57.5°	507.0	484.4	460.0	440.6	418.8	405.6	394.3	381.4	373.1	365.6	360.3
60°	468.9	443.0	421.9	403.6	384.5	367.5	357.3	347.1	338.2	330.7	326.0
62.5°	429.1	406.6	386.5	366.5	349.1	334.3	322.4	313.9	306.1	301.3	296.6
65°	368.2	350.5	330.1	313.7	297.4	286.5	277.0	269.5	264.0	260.6	256.6
67.5°	312.1	294.9	277.1	261.1	250.2	241.9	235.6	229.2	226.5	222.1	219.4
70°	275.6	257.9	242.3	230.0	219.1	213.0	208.9	204.2	201.4	196.0	193.3
72.5°	235.9	223.1	211.8	201.7	193.0	187.4	182.2	176.4	172.0	166.0	163.3
75°	185.8	174.2	165.4	158.6	153.1	145.6	138.1	132.0	130.0	127.9	127.3
77.5°	137.6	130.3	123.9	118.1	111.3	105.9	104.3	102.9	102.5	101.4	101.4
80°	108.2	101.4	96.6	89.8	85.7	85.7	85.7	84.4	85.1	85.1	85.1
82.5°	80.4	74.2	71.6	69.1	68.3	68.9	68.9	69.1	68.7	69.8	69.3
85°	41.5	42.2	43.6	42.9	43.6	43.6	44.9	44.2	44.9	43.6	44.9
87.5°	16.7	18.7	19.7	20.7	21.6	21.5	22.2	22.3	23.0	23.1	23.2
90°	7.3	9.2	11.4	13.5	15.7	17.8	18.5	19.1	19.8	20.5	20.9
92.5°	22.4	23.6	24.8	26.1	27.3	28.5	29.0	29.6	30.1	30.6	30.8
95°	48.4	49.6	51.0	52.3	53.6	54.9	55.6	56.2	56.9	57.6	57.9
97.5°	81.2	82.1	83.1	84.0	85.0	86.0	86.7	87.5	88.2	89.0	89.3
100°	104.9	105.8	106.6	107.5	108.3	109.1	109.6	110.1	110.6	111.1	111.5
102.5°	130.0	130.9	132.0	133.1	134.1	135.2	135.7	136.2	136.7	137.2	137.4
105°	168.3	169.2	170.7	172.2	173.7	175.2	175.2	175.2	175.2	175.2	175.3
107.5°	213.5	213.9	214.5	215.1	215.7	216.3	216.8	217.3	217.9	218.4	218.6
110°	242.5	242.9	243.2	243.5	243.9	244.2	244.9	245.5	246.2	246.8	247.0



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	271.7	271.8	271.9	272.0	272.0	272.1	272.9	273.7	274.5	275.3	275.6
115°	317.4	317.5	317.2	316.9	316.5	316.2	316.4	316.5	316.7	316.9	316.9
117.5°	361.6	361.6	361.1	360.7	360.3	359.8	359.8	359.8	359.7	359.7	359.5
120°	392.2	392.2	391.4	390.6	389.8	388.9	388.8	388.6	388.4	388.3	388.0
122.5°	420.2	420.3	419.9	419.5	419.1	418.6	418.2	417.8	417.3	416.9	416.5
125°	463.7	463.7	463.4	463.1	462.7	462.4	461.8	461.1	460.4	459.8	459.1
127.5°	506.9	507.2	506.9	506.5	506.1	505.8	504.8	503.9	503.0	502.1	501.2
130°	535.2	535.7	535.2	534.7	534.2	533.7	533.0	532.4	531.7	531.0	530.1
132.5°	562.6	563.0	562.7	562.3	561.9	561.6	560.8	560.0	559.2	558.4	557.6
135°	602.9	603.4	603.2	603.0	602.9	602.7	602.0	601.4	600.7	600.1	599.6
137.5°	640.9	641.5	641.9	642.4	642.8	643.2	642.5	641.8	641.1	640.5	639.8
140°	667.6	668.1	668.3	668.4	668.6	668.8	668.6	668.4	668.3	668.1	667.4
142.5°	691.9	692.5	692.8	693.1	693.4	693.7	693.5	693.4	693.2	693.0	692.5
145°	728.0	728.4	728.9	729.4	729.9	730.4	730.2	730.0	729.9	729.7	729.3
147.5°	762.3	762.8	763.3	763.7	764.2	764.7	764.7	764.7	764.7	764.7	764.2
150°	784.4	784.7	785.0	785.4	785.7	786.0	786.0	786.0	786.0	786.0	785.5
152.5°	803.9	804.2	804.4	804.6	804.8	805.0	805.3	805.6	805.8	806.1	805.8
155°	832.1	832.1	832.3	832.5	832.6	832.8	833.5	834.1	834.8	835.4	835.2
157.5°	856.8	856.8	856.9	857.0	857.2	857.3	858.0	858.7	859.4	860.1	859.9
160°	872.3	872.1	872.1	872.1	872.1	872.1	873.0	873.8	874.6	875.4	875.5
162.5°	886.0	885.9	886.0	886.1	886.3	886.4	887.2	888.0	888.9	889.7	889.6
165°	904.3	904.0	904.0	904.0	904.0	904.0	905.0	906.0	907.0	908.0	907.9
167.5°	918.3	918.1	918.2	918.3	918.5	918.6	919.6	920.6	921.7	922.7	922.7
170°	926.6	926.3	926.3	926.3	926.3	926.3	927.5	928.6	929.8	930.9	930.9
172.5°	933.2	932.8	932.8	932.8	932.8	932.8	933.9	934.9	935.9	936.9	936.9
175°	940.0	939.7	939.7	939.7	939.7	939.7	940.7	941.7	942.6	943.6	943.6
177.5°	943.4	943.1	943.1	943.1	943.1	943.1	943.9	944.7	945.5	946.3	946.2
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1514.6	1514.0	1514.6	1512.4	1514.6	1514.0	1514.6	1521.1	1521.1	1521.7	1522.2
5°	1409.4	1408.7	1406.7	1400.5	1406.7	1408.7	1409.4	1411.4	1416.9	1426.4	1423.7
7.5°	1317.5	1316.6	1310.6	1310.7	1310.6	1316.6	1317.5	1322.8	1328.9	1334.8	1341.7
10°	1263.1	1263.7	1255.6	1250.8	1255.6	1263.7	1263.1	1267.8	1276.7	1281.4	1286.2
12.5°	1210.3	1207.1	1200.6	1195.3	1200.6	1207.1	1210.3	1213.9	1226.0	1231.4	1240.5
15°	1140.6	1133.8	1117.4	1118.8	1117.4	1133.8	1140.6	1137.9	1150.1	1156.9	1159.6
17.5°	1058.5	1053.5	1053.2	1043.7	1053.2	1053.5	1058.5	1063.9	1074.6	1081.9	1101.4
20°	1010.6	1007.2	1008.5	999.0	1008.5	1007.2	1010.6	1021.5	1028.3	1037.8	1053.5
22.5°	973.0	969.6	963.9	960.9	963.9	969.6	973.0	980.6	988.0	1001.3	1009.9
25°	918.0	912.6	907.2	910.6	907.2	912.6	918.0	922.1	935.7	941.9	954.1
27.5°	863.1	859.0	853.5	852.8	853.5	859.0	863.1	867.0	874.5	884.8	899.5
30°	828.2	824.1	821.4	818.0	821.4	824.1	828.2	831.6	839.1	850.0	860.9
32.5°	792.8	792.0	787.1	786.4	787.1	792.0	792.8	798.4	805.9	816.2	825.5
35°	746.5	742.5	741.1	741.8	741.1	742.5	746.5	749.3	756.1	765.6	774.4
37.5°	702.6	697.1	694.7	692.2	694.7	697.1	702.6	703.0	709.9	716.3	728.3
40°	671.0	665.6	664.2	662.8	664.2	665.6	671.0	670.3	677.8	682.6	693.5
42.5°	635.6	633.4	632.6	630.2	632.6	633.4	635.6	639.3	643.5	650.5	658.6
45°	587.3	586.6	582.5	583.9	582.5	586.6	587.3	589.3	596.8	601.6	609.1
47.5°	536.4	533.4	530.5	532.4	530.5	533.4	536.4	539.1	544.2	550.0	559.9
50°	501.6	500.2	494.1	495.4	494.1	500.2	501.6	504.3	507.7	515.2	524.0
52.5°	466.7	461.5	459.2	458.4	459.2	461.5	466.7	469.4	473.4	482.0	488.6
55°	409.0	402.9	400.2	398.8	400.2	402.9	409.0	413.8	419.2	428.7	435.5
57.5°	352.4	350.7	348.6	350.1	348.6	350.7	352.4	360.3	365.6	373.1	381.4
60°	319.2	319.2	319.2	318.5	319.2	319.2	319.2	326.0	330.7	338.2	347.1
62.5°	293.6	291.9	291.4	292.4	291.4	291.9	293.6	296.6	301.3	306.1	313.9
65°	254.5	253.8	251.1	250.4	251.1	253.8	254.5	256.6	260.6	264.0	269.5
67.5°	217.6	215.2	214.4	213.4	214.4	215.2	217.6	219.4	222.1	226.5	229.2
70°	189.9	188.5	184.4	185.1	184.4	188.5	189.9	193.3	196.0	201.4	204.2
72.5°	159.9	158.6	157.7	156.8	157.7	158.6	159.9	163.3	166.0	172.0	176.4
75°	126.6	125.9	125.2	127.9	125.2	125.9	126.6	127.3	127.9	130.0	132.0
77.5°	101.4	101.4	101.8	100.7	101.8	101.4	101.4	101.4	101.4	102.5	102.9
80°	85.1	85.1	84.4	84.4	84.4	85.1	85.1	85.1	85.1	85.1	84.4
82.5°	68.2	68.7	69.1	68.1	69.1	68.7	68.2	69.3	69.8	68.7	69.1
85°	44.9	44.2	45.6	44.9	45.6	44.2	44.9	44.9	43.6	44.9	44.2
87.5°	24.4	23.4	23.4	24.1	23.4	23.4	24.4	23.2	23.1	23.0	22.3
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.5	19.8	19.1
92.5°	30.6	30.4	30.2	30.0	30.2	30.4	30.6	30.8	30.6	30.1	29.6
95°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.6	56.9	56.2
97.5°	89.3	89.2	89.1	89.1	89.1	89.2	89.3	89.3	89.0	88.2	87.5
100°	111.8	112.2	112.5	112.8	112.5	112.2	111.8	111.5	111.1	110.6	110.1
102.5°	137.4	137.3	137.2	137.2	137.2	137.3	137.4	137.4	137.2	136.7	136.2
105°	175.7	176.0	176.3	176.7	176.3	176.0	175.7	175.3	175.2	175.2	175.2
107.5°	218.4	218.2	218.0	217.8	218.0	218.2	218.4	218.6	218.4	217.9	217.3
110°	246.7	246.3	246.0	245.7	246.0	246.3	246.7	247.0	246.8	246.2	245.5



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	275.6	275.5	275.4	275.4	275.4	275.5	275.6	275.6	275.3	274.5	273.7
115°	316.7	316.5	316.4	316.2	316.4	316.5	316.7	316.9	316.9	316.7	316.5
117.5°	359.0	358.5	358.1	357.6	358.1	358.5	359.0	359.5	359.7	359.7	359.8
120°	387.7	387.4	387.0	386.7	387.0	387.4	387.7	388.0	388.3	388.4	388.6
122.5°	416.0	415.5	415.1	414.6	415.1	415.5	416.0	416.5	416.9	417.3	417.8
125°	458.5	457.8	457.1	456.5	457.1	457.8	458.5	459.1	459.8	460.4	461.1
127.5°	500.5	499.7	499.0	498.2	499.0	499.7	500.5	501.2	502.1	503.0	503.9
130°	529.0	527.8	526.7	525.5	526.7	527.8	529.0	530.1	531.0	531.7	532.4
132.5°	556.7	555.8	554.9	554.0	554.9	555.8	556.7	557.6	558.4	559.2	560.0
135°	599.2	598.9	598.6	598.2	598.6	598.9	599.2	599.6	600.1	600.7	601.4
137.5°	639.2	638.5	637.9	637.3	637.9	638.5	639.2	639.8	640.5	641.1	641.8
140°	666.3	665.1	664.0	662.8	664.0	665.1	666.3	667.4	668.1	668.3	668.4
142.5°	691.6	690.7	689.8	688.9	689.8	690.7	691.6	692.5	693.0	693.2	693.4
145°	728.6	728.0	727.3	726.7	727.3	728.0	728.6	729.3	729.7	729.9	730.0
147.5°	763.2	762.2	761.2	760.2	761.2	762.2	763.2	764.2	764.7	764.7	764.7
150°	784.5	783.6	782.6	781.6	782.6	783.6	784.5	785.5	786.0	786.0	786.0
152.5°	804.9	804.1	803.2	802.4	803.2	804.1	804.9	805.8	806.1	805.8	805.6
155°	834.0	832.9	831.7	830.6	831.7	832.9	834.0	835.2	835.4	834.8	834.1
157.5°	859.0	858.1	857.2	856.2	857.2	858.1	859.0	859.9	860.1	859.4	858.7
160°	874.9	874.2	873.5	872.9	873.5	874.2	874.9	875.5	875.4	874.6	873.8
162.5°	888.5	887.5	886.4	885.3	886.4	887.5	888.5	889.6	889.7	888.9	888.0
165°	906.8	905.6	904.5	903.3	904.5	905.6	906.8	907.9	908.0	907.0	906.0
167.5°	921.7	920.6	919.6	918.6	919.6	920.6	921.7	922.7	922.7	921.7	920.6
170°	929.8	928.6	927.5	926.3	927.5	928.6	929.8	930.9	930.9	929.8	928.6
172.5°	935.7	934.6	933.4	932.3	933.4	934.6	935.7	936.9	936.9	935.9	934.9
175°	942.4	941.2	940.1	938.9	940.1	941.2	942.4	943.6	943.6	942.6	941.7
177.5°	945.3	944.3	943.4	942.5	943.4	944.3	945.3	946.2	946.3	945.5	944.7
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1517.3	1524.9	1532.6	1539.6	1550.5	1555.4	1562.5	1565.2	1573.4	1585.4	1595.2
5°	1425.0	1435.9	1450.2	1461.8	1480.2	1494.4	1510.1	1525.1	1542.8	1567.9	1590.4
7.5°	1346.8	1357.5	1374.7	1396.2	1416.5	1436.7	1458.1	1478.5	1503.8	1539.9	1575.7
10°	1295.1	1308.0	1328.4	1351.5	1376.7	1396.5	1421.6	1447.5	1478.8	1520.3	1563.2
12.5°	1250.4	1260.1	1283.8	1305.8	1334.3	1359.4	1384.1	1414.3	1449.9	1494.2	1545.8
15°	1179.4	1193.0	1216.1	1240.6	1270.6	1297.1	1329.1	1365.8	1400.5	1455.0	1517.6
17.5°	1108.0	1128.7	1152.8	1180.5	1202.6	1239.2	1274.0	1311.7	1354.4	1412.1	1480.8
20°	1062.3	1078.6	1101.1	1141.3	1170.5	1198.4	1230.4	1277.4	1316.8	1382.2	1453.6
22.5°	1023.7	1035.6	1060.8	1093.9	1128.1	1160.3	1192.8	1237.6	1286.3	1348.4	1425.9
25°	966.4	985.4	1004.5	1028.3	1065.0	1103.8	1139.2	1177.3	1229.0	1295.1	1378.8
27.5°	910.4	927.7	946.5	975.7	1003.6	1039.9	1076.9	1120.6	1176.1	1245.9	1330.8
30°	874.5	887.4	905.1	942.5	967.7	999.0	1042.6	1081.4	1133.1	1207.3	1297.1
32.5°	837.5	854.2	873.5	902.3	933.4	963.1	1002.8	1044.9	1097.7	1170.8	1262.8
35°	784.7	804.4	824.1	845.2	876.5	907.2	940.5	986.8	1040.5	1111.3	1201.8
37.5°	736.1	752.0	768.0	794.2	823.9	853.0	884.1	929.7	980.4	1056.7	1139.8
40°	705.0	719.3	731.6	758.8	787.4	818.7	849.3	889.5	943.9	1015.4	1095.7
42.5°	671.3	684.5	701.1	723.4	754.2	780.6	811.2	849.2	900.3	972.9	1043.4
45°	620.6	635.6	649.9	671.0	701.6	727.5	754.7	790.8	843.2	903.1	965.7
47.5°	568.0	582.9	599.3	619.7	646.4	672.6	699.9	731.8	779.6	838.4	880.6
50°	534.2	546.5	562.8	583.2	607.7	635.6	660.1	694.8	740.4	786.7	823.4
52.5°	499.4	510.5	529.0	550.6	573.4	597.5	623.6	653.4	694.7	738.2	767.4
55°	445.1	458.7	474.3	495.4	517.9	538.3	563.5	594.1	626.8	659.4	679.2
57.5°	394.3	405.6	418.8	440.6	460.0	484.4	507.0	530.8	561.0	585.7	598.6
60°	357.3	367.5	384.5	403.6	421.9	443.0	468.9	492.7	515.8	535.6	545.8
62.5°	322.4	334.3	349.1	366.5	386.5	406.6	429.1	449.2	469.6	486.6	493.5
65°	277.0	286.5	297.4	313.7	330.1	350.5	368.2	388.6	403.6	413.1	419.2
67.5°	235.6	241.9	250.2	261.1	277.1	294.9	312.1	328.0	340.5	347.1	352.5
70°	208.9	213.0	219.1	230.0	242.3	257.9	275.6	287.2	298.1	303.5	309.0
72.5°	182.2	187.4	193.0	201.7	211.8	223.1	235.9	250.2	256.2	262.7	266.0
75°	138.1	145.6	153.1	158.6	165.4	174.2	185.8	194.6	198.0	203.5	204.2
77.5°	104.3	105.9	111.3	118.1	123.9	130.3	137.6	145.5	147.1	150.0	151.8
80°	85.7	85.7	85.7	89.8	96.6	101.4	108.2	112.3	115.0	115.7	116.4
82.5°	68.9	68.9	68.3	69.1	71.6	74.2	80.4	85.1	87.2	86.8	85.3
85°	44.9	43.6	43.6	42.9	43.6	42.2	41.5	44.2	48.3	48.3	47.0
87.5°	22.2	21.5	21.6	20.7	19.7	18.7	16.7	16.9	16.6	18.4	17.6
90°	18.5	17.8	15.7	13.5	11.4	9.2	7.3	5.7	4.0	2.4	0.7
92.5°	29.0	28.5	27.3	26.1	24.8	23.6	22.4	21.3	20.2	19.1	18.0
95°	55.6	54.9	53.6	52.3	51.0	49.6	48.4	47.3	46.1	44.9	43.8
97.5°	86.7	86.0	85.0	84.0	83.1	82.1	81.2	80.4	79.5	78.6	77.8
100°	109.6	109.1	108.3	107.5	106.6	105.8	104.9	103.9	102.9	101.9	100.9
102.5°	135.7	135.2	134.1	133.1	132.0	130.9	130.0	129.4	128.9	128.3	127.7
105°	175.2	175.2	173.7	172.2	170.7	169.2	168.3	168.0	167.7	167.3	167.0
107.5°	216.8	216.3	215.7	215.1	214.5	213.9	213.5	213.3	213.1	212.9	212.7
110°	244.9	244.2	243.9	243.5	243.2	242.9	242.5	242.2	241.9	241.6	241.2



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.9	272.1	272.0	272.0	271.9	271.8	271.7	271.5	271.3	271.1	270.9
115°	316.4	316.2	316.5	316.9	317.2	317.5	317.4	316.9	316.4	315.9	315.5
117.5°	359.8	359.8	360.3	360.7	361.1	361.6	361.6	361.3	360.9	360.6	360.3
120°	388.8	388.9	389.8	390.6	391.4	392.2	392.2	391.2	390.2	389.2	388.2
122.5°	418.2	418.6	419.1	419.5	419.9	420.3	420.2	419.5	418.7	418.0	417.3
125°	461.8	462.4	462.7	463.1	463.4	463.7	463.7	463.2	462.7	462.2	461.7
127.5°	504.8	505.8	506.1	506.5	506.9	507.2	506.9	505.8	504.8	503.7	502.6
130°	533.0	533.7	534.2	534.7	535.2	535.7	535.2	533.9	532.6	531.3	530.0
132.5°	560.8	561.6	561.9	562.3	562.7	563.0	562.6	561.2	559.9	558.6	557.3
135°	602.0	602.7	602.9	603.0	603.2	603.4	602.9	602.0	601.0	600.0	599.0
137.5°	642.5	643.2	642.8	642.4	641.9	641.5	640.9	640.1	639.2	638.4	637.6
140°	668.6	668.8	668.6	668.4	668.3	668.1	667.6	666.8	666.0	665.1	664.3
142.5°	693.5	693.7	693.4	693.1	692.8	692.5	691.9	691.1	690.3	689.5	688.7
145°	730.2	730.4	729.9	729.4	728.9	728.4	728.0	727.6	727.3	727.0	726.7
147.5°	764.7	764.7	764.2	763.7	763.3	762.8	762.3	761.7	761.1	760.5	759.9
150°	786.0	786.0	785.7	785.4	785.0	784.7	784.4	784.1	783.7	783.4	783.1
152.5°	805.3	805.0	804.8	804.6	804.4	804.2	803.9	803.5	803.0	802.5	802.1
155°	833.5	832.8	832.6	832.5	832.3	832.1	832.1	832.1	832.1	832.1	832.1
157.5°	858.0	857.3	857.2	857.0	856.9	856.8	856.8	857.0	857.2	857.4	857.6
160°	873.0	872.1	872.1	872.1	872.1	872.1	872.3	872.6	873.0	873.3	873.6
162.5°	887.2	886.4	886.3	886.1	886.0	885.9	886.0	886.5	886.9	887.4	887.9
165°	905.0	904.0	904.0	904.0	904.0	904.0	904.3	904.8	905.3	905.8	906.3
167.5°	919.6	918.6	918.5	918.3	918.2	918.1	918.3	919.0	919.7	920.3	921.0
170°	927.5	926.3	926.3	926.3	926.3	926.3	926.6	927.3	928.0	928.6	929.3
172.5°	933.9	932.8	932.8	932.8	932.8	932.8	933.2	933.8	934.5	935.2	935.8
175°	940.7	939.7	939.7	939.7	939.7	939.7	940.0	940.7	941.3	942.0	942.6
177.5°	943.9	943.1	943.1	943.1	943.1	943.1	943.4	943.9	944.4	944.9	945.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1598.4	1604.4	1612.0	1623.5	1632.2	1639.8	1641.4	1643.6	1649.1	1658.3	1665.4
5°	1608.8	1624.4	1649.6	1674.1	1700.7	1722.4	1742.8	1757.1	1770.7	1799.3	1822.5
7.5°	1605.5	1640.4	1679.8	1723.8	1768.3	1811.4	1851.5	1887.3	1922.9	1964.6	2012.1
10°	1603.3	1644.2	1697.2	1753.7	1815.7	1876.2	1934.8	1980.4	2033.4	2081.1	2141.6
12.5°	1593.0	1651.8	1715.2	1787.5	1863.6	1933.4	2010.4	2073.4	2134.2	2203.0	2273.4
15°	1579.5	1651.0	1731.3	1827.2	1942.9	2027.3	2106.2	2215.8	2290.7	2365.5	2466.3
17.5°	1554.9	1642.1	1742.4	1867.1	1963.6	2077.0	2195.8	2282.4	2383.2	2488.7	2579.9
20°	1535.3	1636.7	1749.0	1871.5	1994.6	2117.8	2232.8	2336.3	2440.4	2562.2	2637.1
22.5°	1515.7	1616.0	1732.6	1862.8	1995.2	2124.9	2255.1	2376.6	2493.7	2616.6	2712.2
25°	1474.0	1593.1	1719.7	1852.4	1983.1	2126.0	2281.1	2416.6	2561.5	2688.1	2778.6
27.5°	1431.8	1541.0	1667.0	1801.6	1946.9	2115.8	2298.3	2452.2	2597.5	2688.1	2716.6
30°	1393.7	1509.4	1625.1	1761.9	1919.1	2107.6	2301.6	2477.8	2596.9	2636.4	2607.1
32.5°	1355.1	1459.9	1574.5	1714.5	1881.5	2087.5	2305.9	2462.6	2534.3	2504.1	2385.0
35°	1286.9	1381.5	1492.4	1632.6	1824.5	2076.3	2288.0	2394.1	2376.4	2206.3	1981.7
37.5°	1213.9	1291.0	1393.7	1540.3	1765.4	2032.1	2210.6	2226.3	2073.2	1812.0	1552.6
40°	1156.2	1225.6	1331.1	1484.2	1719.7	1988.5	2132.8	2069.5	1832.0	1541.4	1325.0
42.5°	1100.1	1158.7	1260.3	1425.4	1676.2	1929.2	2016.8	1879.0	1605.0	1330.2	1133.4
45°	1005.1	1060.3	1162.3	1331.8	1587.0	1815.7	1804.1	1564.5	1290.3	1069.1	905.8
47.5°	915.0	963.2	1059.0	1232.0	1482.3	1645.5	1537.3	1282.4	1049.8	872.3	755.8
50°	851.3	899.0	994.3	1165.1	1398.5	1517.6	1363.1	1117.4	904.4	757.4	664.9
52.5°	790.4	836.9	924.0	1090.5	1297.2	1368.4	1202.5	974.8	797.2	670.3	590.8
55°	705.0	740.4	818.7	977.9	1132.4	1148.7	980.6	790.1	643.8	555.3	500.9
57.5°	618.1	648.5	725.9	852.7	961.0	952.6	793.2	628.4	529.9	464.1	424.7
60°	561.4	591.4	659.4	768.3	850.0	821.4	675.1	542.4	458.0	409.7	378.4
62.5°	508.6	532.0	595.7	675.2	734.0	701.6	577.1	467.3	400.3	359.6	334.8
65°	432.1	451.2	502.2	543.7	576.4	545.1	441.7	365.4	317.1	288.5	271.5
67.5°	359.5	371.6	403.8	418.8	441.8	407.5	332.1	281.1	253.6	229.5	217.6
70°	313.7	322.6	339.6	351.8	358.0	322.6	266.8	229.3	206.2	189.2	181.7
72.5°	268.0	275.8	279.2	289.2	286.1	252.9	214.5	184.7	168.1	156.5	146.9
75°	204.8	208.2	204.8	200.8	191.9	168.8	142.2	127.3	115.0	109.6	106.2
77.5°	149.3	148.2	143.6	137.2	122.1	107.5	93.2	88.2	82.9	80.0	78.8
80°	115.0	112.3	108.2	98.0	85.1	74.9	71.5	68.1	66.0	62.6	61.9
82.5°	85.6	84.0	77.2	68.6	59.5	54.7	51.9	50.6	48.6	46.8	46.7
85°	45.6	43.6	36.1	31.3	29.9	28.6	27.9	27.9	25.2	24.5	24.5
87.5°	15.2	12.2	12.0	10.7	11.1	10.4	11.4	10.8	10.6	11.3	10.4
90°	2.4	4.0	5.7	7.3	9.2	11.4	13.5	15.7	17.8	18.5	19.1
92.5°	19.1	20.2	21.3	22.4	23.6	24.8	26.1	27.3	28.5	29.0	29.6
95°	44.9	46.1	47.3	48.4	49.6	51.0	52.3	53.6	54.9	55.6	56.2
97.5°	78.6	79.5	80.4	81.2	82.1	83.1	84.0	85.0	86.0	86.7	87.5
100°	101.9	102.9	103.9	104.9	105.8	106.6	107.5	108.3	109.1	109.6	110.1
102.5°	128.3	128.9	129.4	130.0	130.9	132.0	133.1	134.1	135.2	135.7	136.2
105°	167.3	167.7	168.0	168.3	169.2	170.7	172.2	173.7	175.2	175.2	175.2
107.5°	212.9	213.1	213.3	213.5	213.9	214.5	215.1	215.7	216.3	216.8	217.3
110°	241.6	241.9	242.2	242.5	242.9	243.2	243.5	243.9	244.2	244.9	245.5



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	271.1	271.3	271.5	271.7	271.8	271.9	272.0	272.0	272.1	272.9	273.7
115°	315.9	316.4	316.9	317.4	317.5	317.2	316.9	316.5	316.2	316.4	316.5
117.5°	360.6	360.9	361.3	361.6	361.6	361.1	360.7	360.3	359.8	359.8	359.8
120°	389.2	390.2	391.2	392.2	392.2	391.4	390.6	389.8	388.9	388.8	388.6
122.5°	418.0	418.7	419.5	420.2	420.3	419.9	419.5	419.1	418.6	418.2	417.8
125°	462.2	462.7	463.2	463.7	463.7	463.4	463.1	462.7	462.4	461.8	461.1
127.5°	503.7	504.8	505.8	506.9	507.2	506.9	506.5	506.1	505.8	504.8	503.9
130°	531.3	532.6	533.9	535.2	535.7	535.2	534.7	534.2	533.7	533.0	532.4
132.5°	558.6	559.9	561.2	562.6	563.0	562.7	562.3	561.9	561.6	560.8	560.0
135°	600.0	601.0	602.0	602.9	603.4	603.2	603.0	602.9	602.7	602.0	601.4
137.5°	638.4	639.2	640.1	640.9	641.5	641.9	642.4	642.8	643.2	642.5	641.8
140°	665.1	666.0	666.8	667.6	668.1	668.3	668.4	668.6	668.8	668.6	668.4
142.5°	689.5	690.3	691.1	691.9	692.5	692.8	693.1	693.4	693.7	693.5	693.4
145°	727.0	727.3	727.6	728.0	728.4	728.9	729.4	729.9	730.4	730.2	730.0
147.5°	760.5	761.1	761.7	762.3	762.8	763.3	763.7	764.2	764.7	764.7	764.7
150°	783.4	783.7	784.1	784.4	784.7	785.0	785.4	785.7	786.0	786.0	786.0
152.5°	802.5	803.0	803.5	803.9	804.2	804.4	804.6	804.8	805.0	805.3	805.6
155°	832.1	832.1	832.1	832.1	832.1	832.3	832.5	832.6	832.8	833.5	834.1
157.5°	857.4	857.2	857.0	856.8	856.8	856.9	857.0	857.2	857.3	858.0	858.7
160°	873.3	873.0	872.6	872.3	872.1	872.1	872.1	872.1	872.1	873.0	873.8
162.5°	887.4	886.9	886.5	886.0	885.9	886.0	886.1	886.3	886.4	887.2	888.0
165°	905.8	905.3	904.8	904.3	904.0	904.0	904.0	904.0	904.0	905.0	906.0
167.5°	920.3	919.7	919.0	918.3	918.1	918.2	918.3	918.5	918.6	919.6	920.6
170°	928.6	928.0	927.3	926.6	926.3	926.3	926.3	926.3	926.3	927.5	928.6
172.5°	935.2	934.5	933.8	933.2	932.8	932.8	932.8	932.8	932.8	933.9	934.9
175°	942.0	941.3	940.7	940.0	939.7	939.7	939.7	939.7	939.7	940.7	941.7
177.5°	944.9	944.4	943.9	943.4	943.1	943.1	943.1	943.1	943.1	943.9	944.7
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1676.8	1676.8	1679.0	1687.2	1688.3	1695.3	1693.2
5°	1842.9	1855.8	1860.6	1881.0	1893.2	1898.7	1887.8
7.5°	2046.0	2082.4	2099.7	2121.1	2140.0	2145.7	2130.9
10°	2194.0	2232.1	2264.1	2283.9	2302.2	2314.5	2330.1
12.5°	2337.2	2384.0	2414.4	2442.3	2461.2	2476.7	2479.3
15°	2492.8	2563.6	2617.3	2656.8	2676.5	2686.7	2682.7
17.5°	2649.7	2715.3	2753.6	2793.9	2821.2	2822.6	2823.4
20°	2738.5	2802.4	2846.7	2876.6	2907.2	2905.9	2912.7
22.5°	2797.8	2848.2	2882.1	2903.8	2914.3	2909.1	2910.5
25°	2825.6	2840.5	2834.4	2799.7	2790.9	2758.9	2764.3
27.5°	2682.4	2611.6	2538.4	2444.2	2369.9	2310.5	2313.5
30°	2488.0	2362.8	2219.9	2100.1	1992.6	1962.7	1898.7
32.5°	2216.4	2028.5	1861.1	1749.5	1657.2	1632.2	1576.4
35°	1755.8	1573.4	1401.2	1297.8	1256.9	1199.8	1199.1
37.5°	1364.7	1204.1	1113.1	1035.5	994.8	960.2	956.8
40°	1148.1	1022.8	954.1	898.3	858.2	832.3	826.2
42.5°	996.7	895.4	831.1	796.5	765.6	752.3	742.3
45°	813.9	745.9	700.9	669.6	655.4	645.1	639.7
47.5°	680.8	635.2	604.6	583.8	572.2	561.4	564.3
50°	608.4	571.0	548.5	528.8	519.9	512.4	513.1
52.5°	550.1	516.5	498.4	484.1	473.1	467.8	465.2
55°	466.8	445.7	427.4	417.2	411.0	403.6	401.5
57.5°	398.2	381.9	366.9	355.4	353.9	346.7	347.6
60°	352.5	338.9	326.7	320.5	315.8	309.6	311.7
62.5°	315.0	303.5	292.4	287.3	282.6	278.1	279.0
65°	257.9	247.0	240.2	237.5	235.5	233.4	231.4
67.5°	205.5	198.9	194.6	188.8	184.6	183.9	181.8
70°	172.9	164.0	156.5	149.0	147.0	146.3	147.0
72.5°	138.6	133.0	130.9	127.3	126.9	125.1	126.3
75°	104.1	102.1	100.7	98.0	98.0	98.0	98.0
77.5°	76.8	75.5	74.7	74.2	73.5	72.5	72.4
80°	59.9	59.2	57.8	57.8	57.2	57.8	57.2
82.5°	45.2	45.1	43.7	43.7	43.0	42.6	43.0
85°	23.1	22.5	23.8	22.5	23.1	21.8	23.1
87.5°	10.5	10.6	10.2	10.2	9.8	10.9	9.9
90°	19.8	20.5	20.9	21.3	21.6	21.9	22.3
92.5°	30.1	30.6	30.8	30.6	30.4	30.2	30.0
95°	56.9	57.6	57.9	57.9	57.9	57.9	57.9
97.5°	88.2	89.0	89.3	89.3	89.2	89.1	89.1
100°	110.6	111.1	111.5	111.8	112.2	112.5	112.8
102.5°	136.7	137.2	137.4	137.4	137.3	137.2	137.2
105°	175.2	175.2	175.3	175.7	176.0	176.3	176.7
107.5°	217.9	218.4	218.6	218.4	218.2	218.0	217.8
110°	246.2	246.8	247.0	246.7	246.3	246.0	245.7



TEST NUMBER: P332455

CATALOG NUMBER: S123RDIW-S1000D755U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.5	275.3	275.6	275.6	275.5	275.4	275.4
115°	316.7	316.9	316.9	316.7	316.5	316.4	316.2
117.5°	359.7	359.7	359.5	359.0	358.5	358.1	357.6
120°	388.4	388.3	388.0	387.7	387.4	387.0	386.7
122.5°	417.3	416.9	416.5	416.0	415.5	415.1	414.6
125°	460.4	459.8	459.1	458.5	457.8	457.1	456.5
127.5°	503.0	502.1	501.2	500.5	499.7	499.0	498.2
130°	531.7	531.0	530.1	529.0	527.8	526.7	525.5
132.5°	559.2	558.4	557.6	556.7	555.8	554.9	554.0
135°	600.7	600.1	599.6	599.2	598.9	598.6	598.2
137.5°	641.1	640.5	639.8	639.2	638.5	637.9	637.3
140°	668.3	668.1	667.4	666.3	665.1	664.0	662.8
142.5°	693.2	693.0	692.5	691.6	690.7	689.8	688.9
145°	729.9	729.7	729.3	728.6	728.0	727.3	726.7
147.5°	764.7	764.7	764.2	763.2	762.2	761.2	760.2
150°	786.0	786.0	785.5	784.5	783.6	782.6	781.6
152.5°	805.8	806.1	805.8	804.9	804.1	803.2	802.4
155°	834.8	835.4	835.2	834.0	832.9	831.7	830.6
157.5°	859.4	860.1	859.9	859.0	858.1	857.2	856.2
160°	874.6	875.4	875.5	874.9	874.2	873.5	872.9
162.5°	888.9	889.7	889.6	888.5	887.5	886.4	885.3
165°	907.0	908.0	907.9	906.8	905.6	904.5	903.3
167.5°	921.7	922.7	922.7	921.7	920.6	919.6	918.6
170°	929.8	930.9	930.9	929.8	928.6	927.5	926.3
172.5°	935.9	936.9	936.9	935.7	934.6	933.4	932.3
175°	942.6	943.6	943.6	942.4	941.2	940.1	938.9
177.5°	945.5	946.3	946.2	945.3	944.3	943.4	942.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9

(END OF REPORT)