

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332489

Luminaire Tested: **S123RDIW-S1165D1535U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332489
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9702.8 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33				
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	1.9
10°-20°	506.4	5.2
20°-30°	729.2	7.5
30°-40°	821.3	8.5
40°-50°	785.8	8.1
50°-60°	643.5	6.6
60°-70°	434.1	4.5
70°-80°	218.4	2.3
80°-90°	63.5	0.7
90°-100°	125.1	1.3
100°-110°	374.3	3.9
110°-120°	636.6	6.6
120°-130°	837.4	8.6
130°-140°	941.2	9.7
140°-150°	925.2	9.5
150°-160°	778.9	8.0
160°-170°	518.5	5.3
170°-180°	181.6	1.9
0°-30°	1417.6	14.6
0°-40°	2238.9	23.1
0°-60°	3668.1	37.8
0°-90°	4384.2	45.2
90°-120°	1136.0	11.7
90°-150°	3839.7	39.6
90°-180°	5319.0	54.8
0°-180°	9702.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	2	17	36	42	45	10
95°	89	100	112	117	118	100
105°	339	343	356	356	359	363
115°	641	645	642	644	642	634
125°	938	942	940	933	927	836
135°	1217	1225	1224	1219	1215	937
145°	1476	1479	1484	1482	1476	922
155°	1690	1690	1692	1697	1687	778
165°	1841	1837	1837	1845	1835	519
175°	1915	1909	1909	1917	1908	182
180°	1920	1920	1920	1920	1920	



TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.5	28.1	25.7	23.3	20.9	20.1	21.0	21.8	22.7	23.6	23.6
90°	1.5	4.9	8.2	11.6	14.9	18.8	23.1	27.5	31.8	36.2	37.5
92.5°	36.5	38.8	41.0	43.3	45.6	48.0	50.5	52.9	55.4	57.9	59.0
95°	89.0	91.3	93.7	96.0	98.4	100.9	103.5	106.2	108.9	111.6	112.9
97.5°	158.0	159.8	161.5	163.3	165.0	166.8	168.8	170.7	172.7	174.6	176.2
100°	205.1	207.1	209.1	211.1	213.1	215.0	216.6	218.3	220.0	221.7	222.7
102.5°	259.4	260.6	261.8	263.0	264.2	265.9	268.1	270.3	272.5	274.7	275.8
105°	339.3	340.0	340.6	341.3	342.0	343.8	346.8	349.8	352.9	355.9	355.9
107.5°	432.2	432.6	433.0	433.4	433.8	434.6	435.8	437.0	438.2	439.4	440.5
110°	490.1	490.8	491.4	492.1	492.8	493.4	494.1	494.8	495.4	496.1	497.5



TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	550.4	550.8	551.2	551.6	552.0	552.3	552.4	552.5	552.7	552.8	554.4
115°	640.9	641.9	642.9	643.9	644.9	645.1	644.4	643.7	643.1	642.4	642.7
117.5°	732.0	732.6	733.3	734.0	734.6	734.5	733.7	732.8	731.9	731.1	731.0
120°	788.7	790.7	792.7	794.7	796.7	796.9	795.2	793.5	791.8	790.2	789.8
122.5°	847.8	849.2	850.7	852.2	853.7	854.0	853.1	852.2	851.4	850.5	849.6
125°	937.9	938.9	940.0	941.0	942.0	942.1	941.5	940.8	940.1	939.5	938.1
127.5°	1021.2	1023.3	1025.5	1027.6	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6
130°	1076.7	1079.4	1082.0	1084.7	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9
132.5°	1132.2	1134.8	1137.5	1140.2	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3
135°	1216.9	1218.9	1220.9	1222.9	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1
137.5°	1295.3	1297.0	1298.7	1300.4	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4
140°	1349.6	1351.3	1353.0	1354.6	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3
142.5°	1399.1	1400.7	1402.4	1404.1	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0
145°	1476.3	1477.0	1477.6	1478.3	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5
147.5°	1543.8	1545.0	1546.2	1547.5	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5
150°	1590.9	1591.6	1592.2	1592.9	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9
152.5°	1629.5	1630.4	1631.4	1632.3	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1
155°	1690.4	1690.4	1690.4	1690.4	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3
157.5°	1742.3	1741.9	1741.5	1741.1	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1
160°	1774.9	1774.2	1773.5	1772.8	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5
162.5°	1803.8	1802.9	1801.9	1801.0	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5
165°	1841.2	1840.2	1839.2	1838.2	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7
167.5°	1871.1	1869.7	1868.4	1867.0	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3
170°	1887.9	1886.6	1885.3	1883.9	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3
172.5°	1901.2	1899.9	1898.5	1897.2	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3
175°	1915.1	1913.8	1912.4	1911.1	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1
177.5°	1920.8	1919.8	1918.7	1917.6	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	23.6	23.6	23.5	23.5	23.3	23.2	23.0	22.9
90°	38.9	40.2	41.6	42.6	43.2	43.9	44.6	45.2
92.5°	60.0	61.1	62.2	62.5	62.1	61.7	61.3	60.9
95°	114.3	115.6	116.9	117.6	117.6	117.6	117.6	117.6
97.5°	177.7	179.2	180.8	181.5	181.4	181.2	181.1	181.0
100°	223.7	224.7	225.7	226.5	227.2	227.9	228.5	229.2
102.5°	276.8	277.8	278.8	279.2	279.1	278.9	278.8	278.7
105°	355.9	355.9	355.9	356.2	356.9	357.6	358.2	358.9
107.5°	441.6	442.6	443.7	444.0	443.6	443.2	442.8	442.4
110°	498.8	500.1	501.5	501.8	501.1	500.5	499.8	499.1



TEST NUMBER: P332489

CATALOG NUMBER: S123RDIW-S1165D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	556.0	557.6	559.2	560.0	559.9	559.7	559.6	559.4
115°	643.1	643.4	643.7	643.7	643.4	643.1	642.7	642.4
117.5°	730.9	730.9	730.8	730.3	729.3	728.4	727.5	726.5
120°	789.5	789.2	788.8	788.3	787.7	787.0	786.3	785.6
122.5°	848.7	847.9	847.0	846.1	845.2	844.2	843.3	842.3
125°	936.8	935.4	934.1	932.7	931.4	930.1	928.7	927.4
127.5°	1023.8	1021.9	1020.0	1018.3	1016.8	1015.2	1013.7	1012.1
130°	1081.5	1080.2	1078.9	1077.0	1074.7	1072.3	1070.0	1067.6
132.5°	1137.7	1136.1	1134.5	1132.8	1131.0	1129.2	1127.3	1125.5
135°	1221.8	1220.4	1219.1	1218.1	1217.4	1216.7	1216.1	1215.4
137.5°	1304.0	1302.6	1301.2	1299.8	1298.5	1297.3	1296.0	1294.7
140°	1358.0	1357.7	1357.3	1356.0	1353.6	1351.3	1348.9	1346.6
142.5°	1408.7	1408.3	1408.0	1406.9	1405.1	1403.3	1401.5	1399.7
145°	1483.1	1482.8	1482.5	1481.6	1480.3	1479.0	1477.6	1476.3
147.5°	1553.5	1553.5	1553.5	1552.5	1550.5	1548.5	1546.4	1544.4
150°	1596.9	1596.9	1596.9	1595.9	1593.9	1591.9	1589.9	1587.9
152.5°	1636.6	1637.1	1637.7	1637.1	1635.3	1633.6	1631.8	1630.1
155°	1694.6	1695.9	1697.3	1696.8	1694.4	1692.1	1689.7	1687.4
157.5°	1744.5	1745.9	1747.3	1747.1	1745.2	1743.3	1741.4	1739.6
160°	1775.2	1776.9	1778.5	1778.7	1777.4	1776.0	1774.7	1773.3
162.5°	1804.1	1805.8	1807.5	1807.3	1805.1	1803.0	1800.8	1798.7
165°	1840.7	1842.7	1844.7	1844.6	1842.2	1839.9	1837.5	1835.2
167.5°	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2
170°	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9
172.5°	1899.3	1901.4	1903.5	1903.4	1901.0	1898.7	1896.3	1894.0
175°	1913.1	1915.1	1917.1	1916.9	1914.6	1912.2	1909.9	1907.6
177.5°	1919.2	1920.8	1922.4	1922.3	1920.4	1918.5	1916.7	1914.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6

(END OF REPORT)