

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332465-940

Luminaire Tested: **S123RDIW-S1000D1320U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332465-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7464.1 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.5	1.9
10°-20°	391.0	5.2
20°-30°	563.0	7.5
30°-40°	634.1	8.5
40°-50°	606.7	8.1
50°-60°	496.8	6.7
60°-70°	335.2	4.5
70°-80°	168.6	2.3
80°-90°	49.0	0.7
90°-100°	95.9	1.3
100°-110°	287.1	3.8
110°-120°	488.2	6.5
120°-130°	642.2	8.6
130°-140°	721.9	9.7
140°-150°	709.6	9.5
150°-160°	597.3	8.0
160°-170°	397.6	5.3
170°-180°	139.2	1.9
0°-30°	1094.5	14.7
0°-40°	1728.6	23.2
0°-60°	2832.1	37.9
0°-90°	3384.9	45.3
90°-120°	871.3	11.7
90°-150°	2944.9	39.5
90°-180°	4079.0	54.6
0°-180°	7464.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	13	28	32	35	7
95°	68	76	86	90	90	77
105°	260	263	273	273	275	279
115°	492	495	493	494	493	486
125°	719	723	720	716	711	641
135°	933	940	939	935	932	719
145°	1132	1135	1138	1137	1132	707
155°	1296	1297	1298	1302	1294	597
165°	1412	1409	1409	1415	1408	398
175°	1469	1464	1464	1470	1463	139
180°	1472	1472	1472	1472	1472	



TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.7	19.8	17.9	16.1	15.5	16.1	16.9	17.5	18.2	18.2
90°	1.2	3.7	6.3	8.8	11.4	14.4	17.7	21.0	24.4	27.7	28.8
92.5°	28.0	29.7	31.5	33.3	35.0	36.8	38.7	40.6	42.5	44.4	45.2
95°	68.2	70.0	71.9	73.7	75.4	77.4	79.5	81.5	83.6	85.6	86.6
97.5°	121.2	122.5	123.9	125.2	126.5	128.0	129.5	130.9	132.4	133.9	135.1
100°	157.3	158.8	160.3	161.9	163.5	164.9	166.1	167.5	168.7	170.0	170.8
102.5°	198.9	199.8	200.8	201.7	202.6	203.9	205.6	207.3	209.0	210.7	211.5
105°	260.2	260.7	261.3	261.7	262.3	263.7	266.0	268.3	270.6	273.0	273.0
107.5°	331.4	331.8	332.1	332.4	332.7	333.3	334.2	335.2	336.1	337.0	337.9
110°	375.9	376.4	376.9	377.4	377.9	378.4	379.0	379.5	380.0	380.5	381.6



TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.1	422.4	422.8	423.0	423.4	423.6	423.7	423.7	423.9	424.0	425.3
115°	491.5	492.3	493.0	493.8	494.6	494.7	494.2	493.7	493.2	492.7	492.9
117.5°	561.4	561.9	562.4	562.9	563.5	563.4	562.7	562.0	561.3	560.7	560.6
120°	604.8	606.4	608.0	609.5	611.0	611.2	609.8	608.6	607.3	606.0	605.7
122.5°	650.2	651.3	652.5	653.6	654.7	655.0	654.2	653.6	652.9	652.3	651.6
125°	719.3	720.1	720.9	721.7	722.5	722.6	722.0	721.6	721.0	720.5	719.5
127.5°	783.2	784.9	786.5	788.1	789.8	790.3	789.8	789.2	788.6	788.1	786.6
130°	825.7	827.8	829.9	832.0	834.0	834.6	833.8	833.1	832.3	831.5	830.5
132.5°	868.3	870.4	872.4	874.5	876.6	877.3	876.7	876.2	875.6	875.0	873.8
135°	933.4	934.9	936.4	937.9	939.5	940.1	939.9	939.6	939.3	939.1	938.1
137.5°	993.5	994.7	996.0	997.3	998.6	999.6	1000.2	1000.9	1001.6	1002.3	1001.1
140°	1035.1	1036.3	1037.7	1038.9	1040.3	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8
142.5°	1073.0	1074.3	1075.6	1076.9	1078.2	1079.1	1079.5	1080.0	1080.4	1080.9	1080.7
145°	1132.2	1132.7	1133.3	1133.8	1134.3	1135.0	1135.7	1136.5	1137.3	1138.0	1137.7
147.5°	1184.0	1185.0	1185.9	1186.9	1187.8	1188.6	1189.3	1190.0	1190.7	1191.4	1191.4
150°	1220.1	1220.7	1221.2	1221.6	1222.2	1222.7	1223.2	1223.7	1224.2	1224.8	1224.8
152.5°	1249.7	1250.4	1251.2	1251.9	1252.6	1253.1	1253.5	1253.7	1254.1	1254.4	1254.8
155°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.6	1296.8	1297.1	1297.4	1297.6	1298.7
157.5°	1336.2	1336.0	1335.6	1335.3	1335.0	1335.0	1335.2	1335.3	1335.6	1335.8	1336.9
160°	1361.2	1360.8	1360.2	1359.7	1359.1	1358.9	1358.9	1358.9	1358.9	1358.9	1360.2
162.5°	1383.4	1382.7	1382.0	1381.3	1380.5	1380.3	1380.5	1380.7	1380.9	1381.1	1382.4
165°	1412.1	1411.3	1410.6	1409.8	1409.1	1408.6	1408.6	1408.6	1408.6	1408.6	1410.2
167.5°	1435.0	1434.0	1433.0	1431.9	1430.9	1430.5	1430.7	1430.9	1431.1	1431.3	1432.9
170°	1448.0	1447.0	1445.9	1444.9	1443.9	1443.3	1443.3	1443.3	1443.3	1443.3	1445.1
172.5°	1458.1	1457.1	1456.1	1455.1	1454.0	1453.5	1453.5	1453.5	1453.5	1453.5	1455.1
175°	1468.8	1467.8	1466.8	1465.7	1464.6	1464.2	1464.2	1464.2	1464.2	1464.2	1465.7
177.5°	1473.2	1472.4	1471.5	1470.7	1469.9	1469.5	1469.5	1469.5	1469.5	1469.5	1470.7
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	18.2	18.1	18.1	18.1	17.9	17.8	17.7	17.7
90°	29.8	30.9	31.8	32.6	33.2	33.7	34.2	34.7
92.5°	46.0	46.9	47.7	48.0	47.6	47.3	47.0	46.7
95°	87.7	88.6	89.7	90.2	90.2	90.2	90.2	90.2
97.5°	136.3	137.5	138.7	139.2	139.1	139.0	138.9	138.8
100°	171.6	172.3	173.1	173.7	174.2	174.8	175.3	175.8
102.5°	212.2	213.0	213.8	214.1	214.0	213.9	213.8	213.7
105°	273.0	273.0	273.0	273.2	273.8	274.2	274.7	275.3
107.5°	338.7	339.5	340.3	340.5	340.3	339.9	339.7	339.3
110°	382.5	383.6	384.6	384.9	384.3	383.9	383.3	382.8





TEST NUMBER: P332465-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	426.4	427.7	428.9	429.4	429.4	429.3	429.2	429.1
115°	493.2	493.5	493.7	493.7	493.5	493.2	492.9	492.7
117.5°	560.6	560.5	560.4	560.1	559.4	558.7	557.9	557.2
120°	605.5	605.3	605.0	604.6	604.1	603.6	603.1	602.5
122.5°	650.9	650.2	649.6	648.9	648.2	647.5	646.8	646.0
125°	718.5	717.5	716.4	715.4	714.3	713.3	712.3	711.2
127.5°	785.2	783.7	782.3	781.0	779.8	778.6	777.5	776.2
130°	829.5	828.5	827.4	826.0	824.2	822.4	820.6	818.9
132.5°	872.5	871.3	870.1	868.8	867.4	866.0	864.6	863.3
135°	937.0	936.0	935.0	934.2	933.7	933.2	932.6	932.2
137.5°	1000.1	999.0	997.9	996.9	996.0	995.0	994.0	993.0
140°	1041.5	1041.3	1041.0	1040.0	1038.2	1036.3	1034.6	1032.8
142.5°	1080.4	1080.1	1079.9	1079.1	1077.6	1076.3	1074.9	1073.5
145°	1137.5	1137.3	1137.0	1136.4	1135.3	1134.3	1133.3	1132.2
147.5°	1191.4	1191.4	1191.4	1190.7	1189.2	1187.6	1186.1	1184.5
150°	1224.8	1224.8	1224.8	1224.0	1222.4	1220.9	1219.3	1217.8
152.5°	1255.2	1255.6	1256.0	1255.5	1254.2	1252.9	1251.5	1250.2
155°	1299.7	1300.7	1301.7	1301.4	1299.6	1297.8	1295.9	1294.1
157.5°	1337.9	1339.0	1340.2	1339.9	1338.5	1337.0	1335.6	1334.2
160°	1361.5	1362.8	1364.1	1364.2	1363.2	1362.2	1361.1	1360.0
162.5°	1383.7	1385.0	1386.3	1386.1	1384.5	1382.8	1381.2	1379.5
165°	1411.8	1413.3	1414.8	1414.7	1412.9	1411.1	1409.3	1407.5
167.5°	1434.5	1436.1	1437.7	1437.7	1436.1	1434.5	1432.9	1431.3
170°	1447.0	1448.8	1450.5	1450.5	1448.8	1447.0	1445.1	1443.3
172.5°	1456.7	1458.3	1459.9	1459.8	1458.0	1456.2	1454.4	1452.6
175°	1467.2	1468.8	1470.3	1470.2	1468.4	1466.6	1464.8	1463.0
177.5°	1471.9	1473.2	1474.4	1474.4	1472.8	1471.4	1470.0	1468.6
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3

(END OF REPORT)