

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332466-940

Luminaire Tested: **S123RDIW-S1000D1535U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332466-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1535U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9006.5 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	81	78	68	66	64	54	53	52	42	41	40	34
2	88	81	75	70	80	74	69	65	60	57	54	48	46	44	37	36	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	68	57	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	36	31	35	30	26	29	25	22	23	20	18	15
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	47	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	1.5
10°-20°	435.5	4.8
20°-30°	684.2	7.6
30°-40°	713.8	7.9
40°-50°	610.9	6.8
50°-60°	465.6	5.2
60°-70°	298.4	3.3
70°-80°	143.6	1.6
80°-90°	43.0	0.5
90°-100°	65.2	0.7
100°-110°	310.9	3.5
110°-120°	746.8	8.3
120°-130°	951.0	10.6
130°-140°	1016.1	11.3
140°-150°	950.2	10.6
150°-160°	766.5	8.5
160°-170°	494.7	5.5
170°-180°	170.5	1.9
0°-30°	1259.1	14.0
0°-40°	1973.0	21.9
0°-60°	3049.5	33.9
0°-90°	3534.5	39.2
90°-120°	1123.0	12.5
90°-150°	4040.3	44.9
90°-180°	5472.0	60.8
0°-180°	9006.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	25
90°	40	1	40	1	40	19
95°	51	81	51	81	51	42
105°	59	397	59	397	59	134
115°	784	745	784	745	784	724
125°	1072	1050	1072	1050	1072	957
135°	1321	1308	1321	1308	1321	1019
145°	1524	1509	1524	1509	1524	951
155°	1660	1662	1660	1662	1660	765
165°	1749	1753	1749	1753	1749	494
175°	1788	1794	1788	1794	1788	170
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	12.8	13.7	12.6	13.0	12.8	13.2	12.9	12.7	13.5	12.8	12.4
90°	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3	33.2	32.0	28.2
92.5°	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9	36.0	34.2	31.2
95°	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5	43.4	41.3	38.1
97.5°	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7	45.3	42.9	64.3
100°	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7	46.4	44.0	90.2
102.5°	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0	80.3	87.7	138.2
105°	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1	239.5	291.9	318.6
107.5°	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2	496.7	535.1	530.9
110°	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7	591.5	601.2	598.0



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8	668.6	668.4	665.1
115°	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2	768.1	765.2	762.5
117.5°	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8	861.4	859.1	857.6
120°	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6	922.2	919.8	918.9
122.5°	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9	982.3	980.6	979.5
125°	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6	1067.1	1066.5	1065.3
127.5°	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6	1150.6	1149.7	1148.3
130°	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1	1201.0	1199.8	1198.6
132.5°	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2	1248.9	1247.8	1246.8
135°	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1	1319.9
137.5°	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7	1386.3	1384.8	1384.2
140°	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8	1427.6	1426.4	1425.5
142.5°	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8	1466.8	1465.9	1465.0
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2	1521.6	1521.1	1520.5
147.5°	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0	1570.5	1569.9	1569.2
150°	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9	1600.3	1599.7	1599.1
152.5°	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5	1626.4	1625.3	1625.0
155°	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0	1662.5	1661.0	1660.7
157.5°	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8	1694.0	1692.2	1692.6
160°	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0	1712.2	1710.4	1710.7
162.5°	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4	1728.4	1726.4	1726.6
165°	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4	1750.1	1747.7	1748.0
167.5°	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8	1764.8
170°	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3	1774.3
172.5°	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5	1783.2	1780.7	1780.5
175°	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1	1791.1	1789.0	1788.7
177.5°	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0	1794.1	1792.2	1792.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	12.7	11.4	11.6	10.9	11.8	11.7	14.0	15.8	16.9	15.5	16.1
90°	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3	4.3	7.2	10.3
92.5°	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8	24.0	23.1	22.3
95°	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3	69.2	57.1	44.9
97.5°	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5	158.0	152.6	147.0
100°	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3	231.2	237.1	243.1
102.5°	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7	300.0	304.3	308.4
105°	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3	400.6	403.8	407.1
107.5°	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4	507.0	509.6	512.3
110°	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9	578.3	580.6	583.0



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2	646.3	648.5	650.6
115°	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2	747.0	748.8	750.6
117.5°	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0	845.3	847.4	849.6
120°	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8	906.5	909.2	911.9
122.5°	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7	967.9	970.1	972.2
125°	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4	1052.8	1055.3	1057.6
127.5°	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6	1135.0	1137.4	1139.7
130°	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7	1186.2	1188.6	1190.9
132.5°	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9	1235.2	1237.6	1239.9
135°	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8	1309.6	1311.3	1313.1
137.5°	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7	1374.0	1376.3	1378.5
140°	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4	1416.2	1418.0	1419.8
142.5°	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8	1455.6	1457.4	1459.2
145°	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0	1511.1	1513.2	1515.3
147.5°	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0	1562.5	1563.8	1565.1
150°	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0	1593.9	1594.8	1595.7
152.5°	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8	1622.3	1622.6	1623.1
155°	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3	1661.8	1661.2	1660.6
157.5°	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8	1693.8	1693.7	1693.6
160°	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1	1712.7	1712.4	1712.2
162.5°	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2	1730.4	1729.7	1728.8
165°	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0	1752.1	1751.2	1750.3
167.5°	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0	1768.9	1767.7	1766.6
170°	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7	1778.5	1777.3	1776.1
172.5°	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1	1784.7	1783.2	1781.8
175°	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3	1792.9	1791.4	1789.9
177.5°	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4	1795.3	1794.1	1793.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	16.2	18.4	19.6	20.9	22.1	22.4	23.2	23.4	24.1	24.3	24.5
90°	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3	35.6	36.7	37.6
92.5°	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9	39.9	41.7	42.8
95°	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5	47.5	49.6	50.6
97.5°	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7	50.0	52.4	53.8
100°	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7	51.1	53.5	54.8
102.5°	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0	65.7	58.3	54.9
105°	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1	134.6	82.2	56.3
107.5°	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2	419.7	381.3	342.3
110°	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7	571.9	562.1	536.0



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8	669.0	669.1	664.8
115°	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2	774.1	777.0	779.1
117.5°	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8	866.1	868.5	869.9
120°	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6	926.9	929.3	930.5
122.5°	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9	985.6	987.3	988.2
125°	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6	1068.3	1068.8	1069.4
127.5°	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6	1152.5	1153.4	1153.6
130°	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1	1203.4	1204.5	1204.8
132.5°	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2	1251.3	1252.5	1252.7
135°	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6
137.5°	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7	1389.1	1390.5	1390.9
140°	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8	1429.9	1431.1	1431.5
142.5°	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8	1468.7	1469.6	1469.7
145°	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2	1522.9	1523.4	1523.8
147.5°	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0	1571.6	1572.3	1571.8
150°	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9	1601.5	1602.0	1602.0
152.5°	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5	1628.5	1629.6	1629.4
155°	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0	1665.4	1667.0	1666.8
157.5°	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8	1697.5	1699.3	1699.1
160°	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0	1715.7	1717.4	1717.3
162.5°	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4	1732.4	1734.4	1734.5
165°	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4	1754.8	1757.2	1757.3
167.5°	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2
170°	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9
172.5°	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5	1787.9	1790.2	1790.1
175°	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1	1795.2	1797.3	1797.2
177.5°	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0	1797.9	1799.8	1799.6
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	25.6	24.8	24.9	25.5	24.9	24.8	25.6	24.5	24.3	24.1	23.4
90°	38.3	38.8	39.4	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3
92.5°	43.2	43.5	43.9	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9
95°	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5
97.5°	54.0	54.3	54.7	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7
100°	55.1	55.4	55.7	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7
102.5°	55.5	56.0	56.5	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0
105°	56.9	57.5	58.1	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1
107.5°	302.8	263.2	223.7	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2
110°	493.7	451.3	408.9	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	655.8	646.8	637.9	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8
115°	780.3	781.5	782.7	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2
117.5°	870.0	870.3	870.6	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8
120°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6
122.5°	988.5	988.6	988.9	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9
125°	1070.1	1070.6	1071.2	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6
127.5°	1153.1	1152.4	1151.8	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6
130°	1204.3	1203.6	1203.0	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1
132.5°	1251.9	1251.1	1250.2	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2
135°	1323.7	1322.9	1322.0	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9
137.5°	1390.4	1389.7	1389.1	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7
140°	1430.8	1430.3	1429.7	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8
142.5°	1468.9	1468.0	1467.2	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2
147.5°	1570.5	1569.1	1567.7	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0
150°	1601.1	1600.2	1599.3	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9
152.5°	1628.1	1626.7	1625.3	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5
155°	1665.0	1663.2	1661.4	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0
157.5°	1696.7	1694.4	1692.1	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8
160°	1715.2	1713.2	1711.1	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0
162.5°	1732.7	1730.8	1729.0	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4
165°	1755.2	1753.2	1751.1	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4
167.5°	1771.8	1769.5	1767.1	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5
170°	1781.5	1779.1	1776.7	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1
172.5°	1787.5	1784.9	1782.3	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5
175°	1794.7	1792.4	1790.0	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1
177.5°	1797.2	1794.8	1792.4	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	23.2	22.4	22.1	20.9	19.6	18.4	16.2	16.1	15.5	16.9	15.8
90°	33.2	32.0	28.2	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3
92.5°	36.0	34.2	31.2	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8
95°	43.4	41.3	38.1	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3
97.5°	45.3	42.9	64.3	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5
100°	46.4	44.0	90.2	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3
102.5°	80.3	87.7	138.2	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7
105°	239.5	291.9	318.6	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3
107.5°	496.7	535.1	530.9	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4
110°	591.5	601.2	598.0	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	668.6	668.4	665.1	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2
115°	768.1	765.2	762.5	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2
117.5°	861.4	859.1	857.6	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0
120°	922.2	919.8	918.9	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8
122.5°	982.3	980.6	979.5	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7
125°	1067.1	1066.5	1065.3	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4
127.5°	1150.6	1149.7	1148.3	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6
130°	1201.0	1199.8	1198.6	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7
132.5°	1248.9	1247.8	1246.8	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9
135°	1322.0	1321.1	1319.9	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8
137.5°	1386.3	1384.8	1384.2	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7
140°	1427.6	1426.4	1425.5	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4
142.5°	1466.8	1465.9	1465.0	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8
145°	1521.6	1521.1	1520.5	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0
147.5°	1570.5	1569.9	1569.2	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0
150°	1600.3	1599.7	1599.1	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0
152.5°	1626.4	1625.3	1625.0	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8
155°	1662.5	1661.0	1660.7	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3
157.5°	1694.0	1692.2	1692.6	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8
160°	1712.2	1710.4	1710.7	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1
162.5°	1728.4	1726.4	1726.6	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2
165°	1750.1	1747.7	1748.0	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0
167.5°	1767.1	1764.8	1764.8	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0
170°	1776.7	1774.3	1774.3	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7
172.5°	1783.2	1780.7	1780.5	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1
175°	1791.1	1789.0	1788.7	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3
177.5°	1794.1	1792.2	1792.0	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	14.0	11.7	11.8	10.9	11.6	11.4	12.7	12.4	12.8	13.5	12.7
90°	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3
92.5°	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9
95°	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5
97.5°	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7
100°	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7
102.5°	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0
105°	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1
107.5°	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2
110°	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8
115°	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2
117.5°	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8
120°	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6
122.5°	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9
125°	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6
127.5°	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6
130°	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1
132.5°	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2
135°	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9
137.5°	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7
140°	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8
142.5°	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8
145°	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2
147.5°	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0
150°	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9
152.5°	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5
155°	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0
157.5°	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8
160°	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0
162.5°	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4
165°	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4
167.5°	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5
170°	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1
172.5°	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5
175°	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1
177.5°	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	12.9	13.2	12.8	13.0	12.6	13.7	12.8
90°	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	571.9	562.1	536.0	493.7	451.3	408.9	366.6



TEST NUMBER: P332466-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)