

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332472

Luminaire Tested: **S123RDIW-S1165D460U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332472  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D460U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6224.3 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70																												
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60																												
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51																												
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44																												
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38																												
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33																												
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29																												
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26																												
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24																												
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21																												
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.0	2.9
10°-20°	506.4	8.1
20°-30°	729.2	11.7
30°-40°	821.3	13.2
40°-50°	785.8	12.6
50°-60°	643.5	10.3
60°-70°	434.1	7.0
70°-80°	218.4	3.5
80°-90°	59.5	1.0
90°-100°	22.0	0.4
100°-110°	104.8	1.7
110°-120°	251.7	4.0
120°-130°	320.5	5.1
130°-140°	342.4	5.5
140°-150°	320.2	5.1
150°-160°	258.3	4.1
160°-170°	166.7	2.7
170°-180°	57.5	0.9
0°-30°	1417.6	22.8
0°-40°	2238.9	36.0
0°-60°	3668.1	58.9
0°-90°	4380.2	70.4
90°-120°	378.5	6.1
90°-150°	1361.6	21.9
90°-180°	1844.0	29.6
0°-180°	6224.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	0	5	11	13	14	5
95°	27	10	14	17	17	34
105°	134	136	98	23	20	142
115°	251	254	258	262	264	248
125°	354	358	359	360	361	316
135°	441	443	445	446	445	339
145°	509	512	513	513	514	318
155°	560	559	560	562	559	258
165°	591	590	589	592	590	167
175°	605	603	603	606	602	58
180°	605	605	605	605	605	



TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.3	27.4	24.5	21.6	18.8	17.5	17.7	18.0	18.2	18.5	18.3
90°	0.4	1.4	2.4	3.4	4.4	5.6	6.9	8.2	9.5	10.8	11.2
92.5°	8.4	8.1	7.8	7.5	7.2	7.6	8.6	9.5	10.5	11.5	12.1
95°	27.4	23.3	19.2	15.1	11.0	9.5	10.6	11.7	12.8	13.9	14.6
97.5°	55.1	53.2	51.4	49.6	47.7	43.2	36.0	28.8	21.7	14.5	15.3
100°	75.9	77.9	79.9	81.9	83.9	77.1	61.6	46.0	30.4	14.8	15.6
102.5°	99.6	101.1	102.5	104.0	105.4	97.6	80.6	63.6	46.6	29.6	27.1
105°	133.9	135.0	136.1	137.2	138.3	134.3	125.3	116.4	107.4	98.4	80.7
107.5°	170.0	170.9	171.8	172.6	173.5	174.7	176.1	177.5	178.9	180.3	167.4
110°	194.1	194.9	195.7	196.5	197.3	198.2	199.3	200.4	201.5	202.6	199.3



TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.1	217.8	218.5	219.2	220.0	220.9	222.0	223.1	224.2	225.3	225.3
115°	251.1	251.7	252.3	252.9	253.5	254.3	255.2	256.1	257.0	257.9	258.9
117.5°	284.1	284.9	285.6	286.3	287.1	287.7	288.1	288.6	289.1	289.5	290.3
120°	304.6	305.5	306.4	307.3	308.2	308.8	309.1	309.4	309.7	310.0	310.8
122.5°	325.5	326.2	326.9	327.7	328.4	329.0	329.4	329.7	330.1	330.5	331.0
125°	354.0	354.8	355.6	356.4	357.2	357.8	358.2	358.6	359.0	359.4	359.6
127.5°	381.7	382.5	383.3	384.1	384.9	385.5	386.0	386.5	387.0	387.5	387.8
130°	399.0	399.8	400.6	401.4	402.2	402.8	403.2	403.6	404.0	404.3	404.7
132.5°	415.5	416.3	417.1	417.9	418.7	419.2	419.6	419.9	420.2	420.5	420.9
135°	440.7	441.3	441.9	442.5	443.1	443.6	444.0	444.4	444.8	445.2	445.5
137.5°	462.3	463.1	463.8	464.6	465.3	465.8	466.1	466.3	466.5	466.7	467.2
140°	476.7	477.3	477.9	478.5	479.1	479.5	479.8	480.1	480.4	480.7	481.1
142.5°	490.0	490.6	491.2	491.8	492.4	492.8	493.1	493.4	493.7	494.0	494.3
145°	508.6	509.3	510.0	510.7	511.4	511.8	512.0	512.2	512.4	512.6	512.8
147.5°	526.1	526.6	527.0	527.5	527.9	528.3	528.5	528.7	528.9	529.1	529.3
150°	536.9	537.2	537.5	537.8	538.1	538.3	538.5	538.7	538.9	539.1	539.3
152.5°	546.6	546.7	546.9	547.0	547.2	547.3	547.4	547.5	547.6	547.8	548.1
155°	560.2	560.0	559.8	559.7	559.5	559.4	559.5	559.6	559.7	559.8	560.3
157.5°	570.9	570.8	570.8	570.8	570.8	570.7	570.6	570.5	570.4	570.3	570.9
160°	577.3	577.2	577.1	577.0	576.9	576.8	576.7	576.6	576.5	576.4	577.0
162.5°	583.4	583.2	582.9	582.7	582.4	582.2	582.1	582.0	581.9	581.8	582.5
165°	590.8	590.5	590.2	589.9	589.6	589.4	589.3	589.2	589.1	589.0	589.8
167.5°	596.6	596.2	595.8	595.4	595.0	594.8	594.8	594.8	594.8	594.8	595.6
170°	599.8	599.4	599.0	598.6	598.2	598.0	598.0	598.0	598.0	598.0	598.8
172.5°	601.9	601.5	601.0	600.5	600.0	599.8	599.9	600.0	600.1	600.1	600.9
175°	604.7	604.2	603.7	603.2	602.7	602.5	602.6	602.7	602.8	602.9	603.6
177.5°	605.4	605.0	604.6	604.2	603.8	603.7	603.8	603.8	603.9	604.0	604.6
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7



TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	18.1	17.9	17.7	17.5	17.2	17.0	16.8	16.5
90°	11.6	12.0	12.4	12.7	12.9	13.1	13.3	13.5
92.5°	12.8	13.4	14.1	14.4	14.6	14.7	14.8	14.9
95°	15.3	16.0	16.7	17.1	17.1	17.1	17.1	17.1
97.5°	16.1	16.9	17.7	18.1	18.2	18.3	18.4	18.5
100°	16.4	17.2	18.0	18.5	18.6	18.7	18.8	18.9
102.5°	24.6	22.1	19.7	18.5	18.7	18.9	19.0	19.2
105°	63.0	45.4	27.7	19.0	19.2	19.4	19.6	19.8
107.5°	154.4	141.5	128.5	115.4	102.0	88.7	75.4	62.1
110°	196.0	192.7	189.4	180.7	166.4	152.1	137.8	123.6





TEST NUMBER: P332472

CATALOG NUMBER: S123RDIW-S1165D460U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.4	225.4	225.5	224.0	221.0	218.0	215.0	212.0
115°	259.9	260.9	261.9	262.6	263.0	263.4	263.8	264.2
117.5°	291.1	291.9	292.7	293.1	293.2	293.3	293.4	293.5
120°	311.6	312.4	313.2	313.6	313.6	313.6	313.6	313.6
122.5°	331.6	332.2	332.7	333.0	333.1	333.2	333.3	333.4
125°	359.8	360.0	360.2	360.4	360.6	360.8	361.0	361.2
127.5°	388.1	388.4	388.7	388.8	388.6	388.4	388.2	388.0
130°	405.1	405.5	405.9	406.0	405.8	405.6	405.4	405.2
132.5°	421.3	421.7	422.1	422.2	421.9	421.6	421.3	421.1
135°	445.8	446.1	446.4	446.4	446.1	445.8	445.5	445.2
137.5°	467.7	468.1	468.6	468.8	468.6	468.4	468.2	468.0
140°	481.5	481.9	482.3	482.4	482.2	482.0	481.8	481.6
142.5°	494.7	495.0	495.3	495.3	495.0	494.8	494.5	494.2
145°	513.0	513.2	513.4	513.5	513.5	513.5	513.5	513.5
147.5°	529.5	529.7	529.9	529.7	529.3	528.8	528.4	527.9
150°	539.5	539.7	539.9	539.9	539.6	539.3	539.0	538.7
152.5°	548.5	548.8	549.2	549.1	548.7	548.2	547.8	547.3
155°	560.8	561.3	561.8	561.7	561.1	560.5	559.9	559.4
157.5°	571.5	572.1	572.7	572.6	571.8	571.1	570.3	569.5
160°	577.6	578.2	578.8	578.8	578.1	577.4	576.7	576.0
162.5°	583.2	583.9	584.5	584.6	583.9	583.3	582.7	582.1
165°	590.6	591.4	592.2	592.2	591.5	590.9	590.2	589.5
167.5°	596.4	597.1	597.9	597.9	597.1	596.4	595.6	594.8
170°	599.6	600.4	601.2	601.2	600.4	599.6	598.8	598.0
172.5°	601.7	602.5	603.3	603.3	602.4	601.5	600.7	599.8
175°	604.3	605.0	605.7	605.7	604.9	604.1	603.3	602.5
177.5°	605.3	605.9	606.6	606.5	605.7	604.9	604.1	603.3
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7

(END OF REPORT)