

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332402

Luminaire Tested: **S123RDIW-S340D1320U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332402
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6637.8 lumens
Efficiency: N/A
Efficacy: 142.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	20				
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	25	25	18				
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15				
3	76	67	61	55	67	60	54	50	46	42	39	33	30	28	21	19	18	13				
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16	11				
5	64	53	45	40	56	47	41	36	36	32	29	26	23	21	17	15	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	15	14	12	9				
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8				
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7				
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5858	5858	5858	5858
5°	6983	5883	5181	5883
10°	8719	5850	4680	5850
15°	10234	5789	4268	5789
20°	11423	5700	3918	5700
25°	11240	5606	3702	5606
30°	8079	5520	3480	5520
35°	5394	5406	3336	5406
40°	3974	5271	3188	5271
45°	3334	5033	3043	5033
50°	2942	4721	2840	4721
55°	2580	4363	2562	4363
60°	2297	4021	2347	4021
65°	2017	3655	2183	3655
70°	1583	3330	1995	3330
75°	1393	2907	1822	2907
80°	1215	2467	1791	2467
85°	976	1988	1902	1988



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	0.8
10°-20°	167.2	2.5
20°-30°	262.7	4.0
30°-40°	274.1	4.1
40°-50°	234.5	3.5
50°-60°	178.8	2.7
60°-70°	114.6	1.7
70°-80°	55.1	0.8
80°-90°	19.4	0.3
90°-100°	62.9	0.9
100°-110°	299.9	4.5
110°-120°	720.3	10.9
120°-130°	917.3	13.8
130°-140°	980.1	14.8
140°-150°	916.5	13.8
150°-160°	739.3	11.1
160°-170°	477.1	7.2
170°-180°	164.4	2.5
0°-30°	483.4	7.3
0°-40°	757.5	11.4
0°-60°	1170.8	17.6
0°-90°	1359.9	20.5
90°-120°	1083.2	16.3
90°-150°	3897.1	58.7
90°-180°	5278.0	79.5
0°-180°	6637.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	544	544	544	544	544	
5°	646	544	480	544	646	67
15°	918	520	383	520	918	260
25°	946	472	312	472	946	407
35°	410	411	254	411	410	269
45°	219	331	200	331	219	172
55°	138	232	136	232	138	124
65°	79	144	86	144	79	78
75°	34	70	44	70	34	36
85°	8	16	15	16	8	10
90°	39	1	39	1	39	18
95°	49	78	49	78	49	41
105°	57	383	57	383	57	129
115°	756	719	756	719	756	699
125°	1034	1013	1034	1013	1034	923
135°	1274	1261	1274	1261	1274	983
145°	1470	1456	1470	1456	1470	917
155°	1601	1603	1601	1603	1601	738
165°	1687	1691	1687	1691	1687	476
175°	1724	1731	1724	1731	1724	164
180°	1731	1731	1731	1731	1731	



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	579.7	580.4	578.0	577.6	574.8	574.1	574.1	570.1	567.7	564.6	562.7
5°	646.3	650.0	648.1	644.0	637.0	635.3	630.9	623.9	616.0	606.2	601.6
7.5°	729.5	734.6	732.6	726.2	718.8	712.9	700.4	688.8	672.6	658.3	646.1
10°	797.7	792.4	788.2	781.9	775.1	764.2	751.1	733.2	712.5	696.1	678.0
12.5°	848.8	847.9	842.6	836.1	826.6	816.2	800.1	778.3	754.2	730.6	709.8
15°	918.4	919.8	916.3	909.6	896.0	877.6	853.4	844.3	809.8	784.2	758.6
17.5°	966.6	966.3	965.8	956.5	942.7	929.6	907.1	883.2	852.0	815.9	781.4
20°	997.2	994.8	995.3	984.8	974.6	959.4	937.5	902.8	877.2	835.5	799.8
22.5°	996.4	995.9	997.7	994.1	986.7	975.1	957.8	928.5	895.8	853.7	813.6
25°	946.4	944.5	955.4	958.5	970.4	972.5	967.3	951.3	920.3	876.9	827.3
27.5°	792.0	791.0	811.3	836.8	869.0	894.1	918.3	930.0	920.3	889.2	839.5
30°	650.0	671.9	682.2	719.0	760.0	808.9	851.8	892.5	902.6	889.0	848.3
32.5°	539.7	558.8	567.4	598.9	637.2	694.5	758.8	816.5	857.3	867.6	843.1
35°	410.5	410.7	430.3	444.3	479.7	538.6	601.1	678.4	755.3	813.6	819.6
37.5°	327.6	328.7	340.6	354.5	381.1	412.2	467.2	531.5	620.3	709.7	762.2
40°	282.8	284.9	293.8	307.5	326.6	350.2	393.0	453.6	527.7	627.2	708.5
42.5°	254.1	257.5	262.1	272.7	284.5	306.6	341.2	388.0	455.4	549.5	643.3
45°	219.0	220.9	224.4	229.3	240.0	255.3	278.6	310.1	366.0	441.7	535.6
47.5°	193.2	192.2	195.9	199.8	207.0	217.5	233.1	258.7	298.6	359.4	439.0
50°	175.7	175.4	178.0	181.0	187.8	195.5	208.3	227.6	259.3	309.6	382.6
52.5°	159.3	160.1	162.0	165.7	170.6	176.8	188.3	202.3	229.5	272.9	333.7
55°	137.5	138.2	140.7	142.8	146.3	152.6	159.8	171.5	190.1	220.4	270.5
57.5°	119.0	118.7	121.1	121.7	125.6	130.7	136.3	145.4	158.9	181.4	215.1
60°	106.7	106.0	108.1	109.7	111.8	116.0	120.7	129.5	140.3	156.8	185.7
62.5°	95.5	95.2	96.7	98.4	100.1	103.9	107.8	114.6	123.1	137.0	160.0
65°	79.2	79.9	80.6	81.3	82.2	84.6	88.3	93.0	98.8	108.6	125.1
67.5°	62.3	63.0	63.2	64.6	66.6	68.1	70.4	74.5	78.6	86.8	96.2
70°	50.3	50.1	50.3	51.0	53.6	56.1	59.2	62.2	64.8	70.6	78.5
72.5°	43.2	42.8	43.4	43.6	44.8	45.5	47.4	50.3	53.6	57.5	63.2
75°	33.5	33.5	33.5	33.5	34.5	34.9	35.6	36.3	37.5	39.4	43.6
77.5°	24.8	24.8	25.2	25.4	25.6	25.9	26.3	27.0	27.4	28.4	30.2
80°	19.6	19.8	19.6	19.8	19.8	20.3	20.5	21.2	21.4	22.6	23.3
82.5°	14.7	14.6	14.7	15.0	15.0	15.4	15.5	16.0	16.0	16.6	17.3
85°	7.9	7.5	7.9	7.7	8.2	7.7	7.9	8.4	8.4	8.6	9.6
87.5°	9.6	9.8	9.4	9.4	9.3	9.3	9.1	8.9	9.0	8.6	8.0
90°	38.6	38.0	37.4	36.9	36.3	35.4	34.3	33.1	32.0	30.9	27.1
92.5°	42.7	42.3	42.0	41.7	41.3	40.2	38.4	36.6	34.7	32.9	30.1
95°	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9	41.9	39.9	36.7
97.5°	53.0	52.7	52.4	52.1	51.8	50.5	48.3	46.0	43.7	41.4	38.0
100°	54.0	53.7	53.4	53.1	52.9	51.6	49.3	47.0	44.7	42.4	39.0
102.5°	55.0	54.5	54.0	53.5	53.0	52.3	50.4	48.4	46.4	44.4	42.4
105°	56.6	56.0	55.4	54.9	54.3	53.6	51.9	50.4	48.9	47.4	45.9
107.5°	177.7	215.8	253.9	292.1	330.2	367.8	404.9	442.0	479.0	516.1	553.2
110°	353.6	394.5	435.3	476.2	517.0	542.2	551.6	561.0	570.5	579.9	576.8



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	606.7	615.3	623.9	632.5	641.2	645.4	645.2	645.1	644.9	644.7	641.6
115°	756.1	754.9	753.8	752.6	751.5	749.5	746.6	743.8	740.9	738.1	735.5
117.5°	839.9	839.7	839.4	839.2	839.0	837.7	835.4	833.2	830.9	828.6	827.3
120°	897.5	897.5	897.5	897.5	897.5	896.4	894.1	891.8	889.5	887.2	886.4
122.5°	954.1	953.9	953.6	953.4	953.2	952.3	950.7	949.1	947.5	945.9	944.8
125°	1033.8	1033.2	1032.7	1032.1	1031.5	1030.9	1030.4	1029.8	1029.2	1028.7	1027.5
127.5°	1110.4	1111.0	1111.6	1112.2	1112.7	1112.6	1111.6	1110.7	1109.8	1108.9	1107.5
130°	1159.8	1160.4	1161.0	1161.5	1162.1	1161.8	1160.7	1159.5	1158.4	1157.2	1156.1
132.5°	1205.1	1205.9	1206.7	1207.5	1208.3	1208.1	1207.0	1205.8	1204.7	1203.5	1202.6
135°	1274.3	1275.1	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3	1273.1
137.5°	1339.3	1339.9	1340.5	1341.0	1341.6	1341.2	1339.8	1338.5	1337.1	1335.7	1335.1
140°	1378.4	1379.0	1379.5	1380.1	1380.7	1380.4	1379.3	1378.1	1377.0	1375.8	1375.0
142.5°	1414.4	1415.2	1416.0	1416.8	1417.6	1417.6	1416.6	1415.7	1414.8	1413.9	1413.0
145°	1469.7	1469.7	1469.7	1469.7	1469.7	1469.4	1468.8	1468.3	1467.7	1467.1	1466.6
147.5°	1510.8	1512.2	1513.5	1514.8	1516.1	1516.5	1515.9	1515.3	1514.8	1514.2	1513.6
150°	1541.7	1542.6	1543.4	1544.3	1545.1	1545.3	1544.7	1544.1	1543.6	1543.0	1542.4
152.5°	1566.4	1567.7	1569.0	1570.3	1571.7	1571.8	1570.8	1569.7	1568.7	1567.7	1567.3
155°	1600.9	1602.6	1604.3	1606.0	1607.7	1607.9	1606.4	1605.0	1603.6	1602.1	1601.9
157.5°	1629.9	1632.1	1634.4	1636.6	1638.8	1639.1	1637.4	1635.7	1633.9	1632.2	1632.5
160°	1648.4	1650.4	1652.4	1654.4	1656.4	1656.6	1654.9	1653.1	1651.4	1649.7	1650.0
162.5°	1665.9	1667.7	1669.5	1671.2	1673.0	1672.9	1671.0	1669.0	1667.1	1665.1	1665.4
165°	1687.0	1689.0	1691.0	1693.0	1695.0	1694.9	1692.6	1690.3	1688.0	1685.7	1686.0
167.5°	1702.2	1704.5	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2	1702.2
170°	1711.4	1713.7	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4	1711.4
172.5°	1716.6	1719.1	1721.6	1724.1	1726.6	1726.8	1724.5	1722.2	1719.9	1717.6	1717.4
175°	1724.3	1726.6	1728.9	1731.2	1733.4	1733.6	1731.6	1729.6	1727.6	1725.6	1725.3
177.5°	1726.6	1728.9	1731.2	1733.5	1735.8	1736.0	1734.2	1732.3	1730.5	1728.7	1728.4
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	561.9	561.4	558.8	555.8	551.9	549.3	547.2	546.1	542.7	538.6	535.9
5°	596.7	589.7	582.2	573.1	564.7	556.1	550.8	544.5	536.8	528.2	522.1
7.5°	633.8	620.1	605.4	590.1	575.1	561.6	549.6	539.4	527.2	514.8	506.2
10°	662.4	642.3	621.6	600.4	581.1	562.9	548.9	535.2	520.5	506.3	495.5
12.5°	688.3	661.9	638.0	611.9	587.2	565.5	545.4	529.2	511.5	496.4	484.2
15°	721.1	694.0	665.2	625.5	592.7	565.2	540.7	519.5	498.1	479.5	467.6
17.5°	751.7	711.1	672.2	639.2	596.5	562.2	532.3	507.0	483.4	463.7	449.0
20°	764.4	725.0	682.9	640.7	598.8	560.3	525.6	497.6	473.2	450.8	437.3
22.5°	772.0	727.5	683.0	637.7	593.2	553.2	518.9	488.1	461.6	440.4	423.7
25°	780.9	727.8	678.9	634.2	588.7	545.4	504.6	472.0	443.4	420.8	403.1
27.5°	786.8	724.3	666.5	616.8	570.7	527.6	490.2	455.6	426.5	402.6	383.6
30°	787.9	721.5	657.0	603.2	556.4	516.7	477.1	444.1	413.3	387.9	370.2
32.5°	789.4	714.6	644.1	587.0	539.0	499.8	463.9	432.3	400.8	375.8	357.7
35°	783.3	710.8	624.6	558.9	510.9	472.9	440.6	411.4	380.5	356.2	337.8
37.5°	756.8	695.7	604.4	527.3	477.1	442.0	415.6	390.2	361.8	335.6	318.3
40°	730.2	680.8	588.7	508.1	455.7	419.6	395.8	375.1	347.6	323.1	304.5
42.5°	690.5	660.4	573.8	488.0	431.5	396.7	376.6	357.2	333.1	308.2	290.7
45°	617.6	621.6	543.3	455.9	397.9	363.0	344.1	330.6	309.2	288.7	270.7
47.5°	526.3	563.3	507.5	421.8	362.6	329.8	313.3	301.5	287.0	266.9	250.5
50°	466.7	519.5	478.8	398.9	340.4	307.8	291.5	281.9	269.3	253.5	237.9
52.5°	411.7	468.5	444.1	373.3	316.3	286.5	270.6	262.7	252.7	237.8	223.7
55°	335.7	393.3	387.7	334.8	280.3	253.5	241.4	232.5	225.8	214.6	203.4
57.5°	271.6	326.1	329.0	291.9	248.5	222.0	211.6	204.9	200.5	192.1	181.7
60°	231.1	281.2	291.0	263.0	225.8	202.5	192.2	186.8	183.4	176.6	168.7
62.5°	197.6	240.2	251.3	231.2	204.0	182.1	174.1	169.0	166.6	160.8	153.8
65°	151.2	186.6	197.3	186.2	171.9	154.5	147.9	143.5	141.4	138.2	133.0
67.5°	113.7	139.5	151.3	143.4	138.2	127.2	123.1	120.7	118.8	116.6	112.3
70°	91.3	110.4	122.5	120.5	116.3	110.4	107.4	105.8	103.9	102.0	98.3
72.5°	73.4	86.6	97.9	99.0	95.6	94.4	91.7	91.0	89.9	87.7	85.6
75°	48.7	57.8	65.7	68.7	70.1	71.3	70.1	69.9	69.7	67.8	66.6
77.5°	31.9	36.8	41.8	47.0	49.2	50.7	51.1	52.0	51.3	50.4	49.8
80°	24.5	25.6	29.1	33.5	37.0	38.4	39.4	39.8	39.6	39.4	38.4
82.5°	17.8	18.7	20.4	23.5	26.4	28.7	29.3	29.2	29.7	29.9	29.1
85°	9.6	9.8	10.3	10.7	12.3	14.9	15.6	16.1	16.5	16.5	15.1
87.5°	7.7	6.7	6.4	5.7	5.7	5.3	5.9	6.2	7.0	6.8	7.4
90°	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3	4.1	7.0	9.9
92.5°	27.3	24.5	21.7	20.7	21.5	22.3	23.1	23.9	23.1	22.3	21.5
95°	33.6	30.4	27.3	31.6	43.3	55.0	66.7	78.4	66.7	55.0	43.3
97.5°	82.6	103.1	123.7	136.6	141.9	147.1	152.4	157.6	152.4	147.1	141.9
100°	131.6	176.2	220.7	240.2	234.4	228.7	223.0	217.3	223.0	228.7	234.4
102.5°	182.0	230.7	279.4	301.7	297.5	293.4	289.3	285.2	289.3	293.4	297.5
105°	333.0	358.7	384.5	395.7	392.6	389.5	386.3	383.2	386.3	389.5	392.6
107.5°	508.0	504.0	499.9	496.6	494.1	491.6	489.1	486.6	489.1	491.6	494.1
110°	573.6	570.5	567.3	564.6	562.3	560.0	557.8	555.5	557.8	560.0	562.3



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	638.4	635.3	632.1	629.5	627.5	625.4	623.4	621.3	623.4	625.4	627.5
115°	732.9	730.3	727.8	725.6	723.9	722.2	720.5	718.8	720.5	722.2	723.9
117.5°	826.0	824.6	823.3	821.6	819.5	817.4	815.3	813.2	815.3	817.4	819.5
120°	885.5	884.6	883.8	882.1	879.5	876.9	874.4	871.8	874.4	876.9	879.5
122.5°	943.7	942.6	941.5	939.9	937.8	935.7	933.6	931.5	933.6	935.7	937.8
125°	1026.4	1025.2	1024.1	1022.4	1020.1	1017.8	1015.5	1013.2	1015.5	1017.8	1020.1
127.5°	1106.2	1104.8	1103.4	1101.6	1099.3	1097.0	1094.7	1092.4	1094.7	1097.0	1099.3
130°	1155.0	1153.8	1152.7	1151.0	1148.7	1146.4	1144.1	1141.8	1144.1	1146.4	1148.7
132.5°	1201.7	1200.8	1199.9	1198.3	1196.0	1193.7	1191.4	1189.1	1191.4	1193.7	1196.0
135°	1272.0	1270.8	1269.7	1268.3	1266.5	1264.8	1263.1	1261.4	1263.1	1264.8	1266.5
137.5°	1334.5	1333.8	1333.2	1331.8	1329.6	1327.5	1325.3	1323.1	1325.3	1327.5	1329.6
140°	1374.1	1373.3	1372.4	1371.1	1369.4	1367.7	1366.0	1364.3	1366.0	1367.7	1369.4
142.5°	1412.2	1411.3	1410.5	1409.2	1407.5	1405.8	1404.0	1402.3	1404.0	1405.8	1407.5
145°	1466.0	1465.4	1464.8	1463.6	1461.6	1459.6	1457.6	1455.6	1457.6	1459.6	1461.6
147.5°	1513.0	1512.5	1511.9	1511.0	1509.6	1508.3	1507.0	1505.7	1507.0	1508.3	1509.6
150°	1541.8	1541.3	1540.7	1540.0	1539.1	1538.3	1537.4	1536.6	1537.4	1538.3	1539.1
152.5°	1567.0	1566.7	1566.3	1565.9	1565.5	1565.1	1564.7	1564.3	1564.7	1565.1	1565.5
155°	1601.6	1601.3	1601.0	1601.1	1601.7	1602.3	1602.9	1603.4	1602.9	1602.3	1601.7
157.5°	1632.8	1633.1	1633.4	1633.5	1633.6	1633.7	1633.7	1633.8	1633.7	1633.7	1633.6
160°	1650.3	1650.6	1650.9	1651.1	1651.4	1651.7	1652.0	1652.3	1652.0	1651.7	1651.4
162.5°	1665.7	1666.0	1666.3	1666.8	1667.5	1668.3	1669.0	1669.8	1669.0	1668.3	1667.5
165°	1686.3	1686.6	1686.9	1687.4	1688.3	1689.1	1690.0	1690.9	1690.0	1689.1	1688.3
167.5°	1702.2	1702.2	1702.2	1702.7	1703.9	1705.0	1706.2	1707.3	1706.2	1705.0	1703.9
170°	1711.4	1711.4	1711.4	1712.0	1713.2	1714.3	1715.4	1716.6	1715.4	1714.3	1713.2
172.5°	1717.2	1716.9	1716.7	1717.3	1718.6	1720.0	1721.4	1722.8	1721.4	1720.0	1718.6
175°	1725.0	1724.7	1724.4	1725.0	1726.4	1727.9	1729.3	1730.7	1729.3	1727.9	1726.4
177.5°	1728.2	1728.0	1727.8	1728.2	1729.4	1730.5	1731.6	1732.8	1731.6	1730.5	1729.4
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	534.9	532.5	530.8	527.1	524.7	522.1	519.5	521.1	520.9	520.8	520.8
5°	517.0	511.6	506.7	500.4	496.5	491.6	487.9	487.4	488.3	485.1	483.2
7.5°	499.2	491.9	484.9	478.0	470.6	464.7	461.1	459.3	457.0	455.0	452.9
10°	486.7	478.1	471.3	462.7	454.8	447.8	443.4	440.3	438.7	437.1	434.0
12.5°	473.8	465.4	456.8	447.0	439.5	431.4	428.1	424.7	421.6	419.7	415.6
15°	455.0	444.1	435.0	424.7	416.3	408.4	403.8	397.0	396.1	393.7	389.5
17.5°	436.1	424.3	411.7	404.1	394.7	386.4	379.3	377.1	370.4	367.9	364.2
20°	421.2	410.3	400.7	390.7	377.0	369.3	363.7	360.7	355.3	352.0	349.7
22.5°	408.4	397.2	386.2	374.5	363.2	354.5	350.4	345.7	342.8	338.2	335.7
25°	390.0	377.9	364.6	352.0	343.9	337.4	330.8	326.6	322.4	320.3	315.7
27.5°	368.7	356.0	343.6	334.0	324.0	317.6	311.7	308.0	302.9	299.4	296.8
30°	356.9	342.0	331.3	322.7	309.9	303.8	299.4	294.7	291.0	287.3	284.7
32.5°	343.3	329.7	319.6	308.9	299.1	292.4	286.7	282.6	279.4	275.9	273.3
35°	322.0	310.6	300.1	289.4	282.1	275.4	268.6	265.1	262.1	258.8	256.5
37.5°	302.7	292.0	282.0	271.9	262.9	257.4	252.0	249.3	245.2	243.0	240.7
40°	290.8	280.3	269.6	259.8	250.5	246.3	241.4	237.4	233.7	232.0	229.5
42.5°	277.7	267.2	258.2	247.7	240.0	234.3	229.8	225.5	222.7	220.3	218.9
45°	258.4	249.1	240.2	229.7	222.5	217.6	212.5	208.5	206.0	204.3	201.8
47.5°	239.6	230.3	221.3	212.2	205.2	199.6	194.4	191.7	188.3	186.3	184.6
50°	226.0	217.6	208.1	199.7	192.7	187.1	182.9	179.4	176.4	173.8	172.6
52.5°	213.5	204.6	196.3	188.5	181.1	174.8	171.0	167.3	165.0	162.1	160.7
55°	192.9	184.3	177.3	169.6	162.4	157.0	152.4	149.1	146.8	143.5	141.7
57.5°	173.6	165.8	157.5	150.8	143.4	138.9	135.0	130.6	127.7	125.2	123.3
60°	160.5	151.7	144.4	138.2	131.6	125.8	122.3	118.8	115.8	113.2	111.6
62.5°	146.9	139.2	132.3	125.5	119.5	114.4	110.4	107.5	104.8	103.2	101.5
65°	126.0	120.0	113.0	107.4	101.8	98.1	94.8	92.3	90.4	89.2	87.8
67.5°	106.8	101.0	94.9	89.4	85.6	82.8	80.7	78.5	77.5	76.0	75.1
70°	94.4	88.3	82.9	78.7	75.0	72.9	71.5	69.9	69.0	67.1	66.2
72.5°	80.8	76.4	72.5	69.1	66.1	64.2	62.4	60.4	58.9	56.8	55.9
75°	63.6	59.6	56.6	54.3	52.4	49.9	47.3	45.2	44.5	43.8	43.6
77.5°	47.1	44.6	42.4	40.4	38.1	36.3	35.7	35.2	35.1	34.7	34.7
80°	37.0	34.7	33.1	30.8	29.4	29.4	29.4	28.9	29.1	29.1	29.1
82.5°	27.5	25.4	24.5	23.7	23.4	23.6	23.6	23.7	23.5	23.9	23.7
85°	14.2	14.4	14.9	14.7	14.9	14.9	15.4	15.1	15.4	14.9	15.4
87.5°	7.8	9.0	9.9	10.8	11.8	12.3	12.7	13.0	13.4	13.6	13.8
90°	12.7	16.0	19.7	23.4	27.1	30.9	32.0	33.1	34.3	35.4	36.3
92.5°	20.7	21.7	24.5	27.3	30.1	32.9	34.7	36.6	38.4	40.2	41.3
95°	31.6	27.3	30.4	33.6	36.7	39.9	41.9	43.9	45.9	47.9	48.9
97.5°	136.6	123.7	103.1	82.6	62.0	41.4	43.7	46.0	48.3	50.5	51.8
100°	240.2	220.7	176.2	131.6	87.0	42.4	44.7	47.0	49.3	51.6	52.9
102.5°	301.7	279.4	230.7	182.0	133.3	84.6	77.5	70.4	63.3	56.3	53.0
105°	395.7	384.5	358.7	333.0	307.3	281.6	231.0	180.4	129.9	79.3	54.3
107.5°	496.6	499.9	504.0	508.0	512.1	516.1	479.0	442.0	404.9	367.8	330.2
110°	564.6	567.3	570.5	573.6	576.8	579.9	570.5	561.0	551.6	542.2	517.0



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	629.5	632.1	635.3	638.4	641.6	644.7	644.9	645.1	645.2	645.4	641.2
115°	725.6	727.8	730.3	732.9	735.5	738.1	740.9	743.8	746.6	749.5	751.5
117.5°	821.6	823.3	824.6	826.0	827.3	828.6	830.9	833.2	835.4	837.7	839.0
120°	882.1	883.8	884.6	885.5	886.4	887.2	889.5	891.8	894.1	896.4	897.5
122.5°	939.9	941.5	942.6	943.7	944.8	945.9	947.5	949.1	950.7	952.3	953.2
125°	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2	1029.8	1030.4	1030.9	1031.5
127.5°	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8	1110.7	1111.6	1112.6	1112.7
130°	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4	1159.5	1160.7	1161.8	1162.1
132.5°	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7	1205.8	1207.0	1208.1	1208.3
135°	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1	1276.0	1276.8	1277.7	1277.7
137.5°	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1	1338.5	1339.8	1341.2	1341.6
140°	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0	1378.1	1379.3	1380.4	1380.7
142.5°	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8	1415.7	1416.6	1417.6	1417.6
145°	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7	1468.3	1468.8	1469.4	1469.7
147.5°	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.3	1515.9	1516.5	1516.1
150°	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6	1544.1	1544.7	1545.3	1545.1
152.5°	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7	1569.7	1570.8	1571.8	1571.7
155°	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6	1605.0	1606.4	1607.9	1607.7
157.5°	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9	1635.7	1637.4	1639.1	1638.8
160°	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4	1653.1	1654.9	1656.6	1656.4
162.5°	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1	1669.0	1671.0	1672.9	1673.0
165°	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0	1690.3	1692.6	1694.9	1695.0
167.5°	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5	1706.8	1709.0	1711.3	1711.3
170°	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7	1716.0	1718.3	1720.6	1720.6
172.5°	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9	1722.2	1724.5	1726.8	1726.6
175°	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6	1729.6	1731.6	1733.6	1733.4
177.5°	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5	1732.3	1734.2	1736.0	1735.8
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	518.5	518.3	518.5	517.8	518.5	518.3	518.5	520.8	520.8	520.9	521.1
5°	482.5	482.3	481.6	479.5	481.6	482.3	482.5	483.2	485.1	488.3	487.4
7.5°	451.0	450.7	448.7	448.7	448.7	450.7	451.0	452.9	455.0	457.0	459.3
10°	432.4	432.6	429.8	428.2	429.8	432.6	432.4	434.0	437.1	438.7	440.3
12.5°	414.3	413.3	411.0	409.2	411.0	413.3	414.3	415.6	419.7	421.6	424.7
15°	390.5	388.1	382.6	383.0	382.6	388.1	390.5	389.5	393.7	396.1	397.0
17.5°	362.4	360.7	360.6	357.3	360.6	360.7	362.4	364.2	367.9	370.4	377.1
20°	346.0	344.8	345.3	342.0	345.3	344.8	346.0	349.7	352.0	355.3	360.7
22.5°	333.1	331.9	330.0	329.0	330.0	331.9	333.1	335.7	338.2	342.8	345.7
25°	314.3	312.4	310.6	311.7	310.6	312.4	314.3	315.7	320.3	322.4	326.6
27.5°	295.5	294.1	292.2	292.0	292.2	294.1	295.5	296.8	299.4	302.9	308.0
30°	283.5	282.1	281.2	280.0	281.2	282.1	283.5	284.7	287.3	291.0	294.7
32.5°	271.4	271.1	269.5	269.2	269.5	271.1	271.4	273.3	275.9	279.4	282.6
35°	255.6	254.2	253.7	253.9	253.7	254.2	255.6	256.5	258.8	262.1	265.1
37.5°	240.5	238.7	237.8	237.0	237.8	238.7	240.5	240.7	243.0	245.2	249.3
40°	229.7	227.9	227.4	226.9	227.4	227.9	229.7	229.5	232.0	233.7	237.4
42.5°	217.6	216.9	216.6	215.7	216.6	216.9	217.6	218.9	220.3	222.7	225.5
45°	201.1	200.8	199.4	199.9	199.4	200.8	201.1	201.8	204.3	206.0	208.5
47.5°	183.6	182.6	181.6	182.3	181.6	182.6	183.6	184.6	186.3	188.3	191.7
50°	171.7	171.2	169.1	169.6	169.1	171.2	171.7	172.6	173.8	176.4	179.4
52.5°	159.8	158.0	157.2	156.9	157.2	158.0	159.8	160.7	162.1	165.0	167.3
55°	140.0	137.9	137.0	136.5	137.0	137.9	140.0	141.7	143.5	146.8	149.1
57.5°	120.6	120.1	119.3	119.8	119.3	120.1	120.6	123.3	125.2	127.7	130.6
60°	109.3	109.3	109.3	109.0	109.3	109.3	109.3	111.6	113.2	115.8	118.8
62.5°	100.5	99.9	99.8	100.1	99.8	99.9	100.5	101.5	103.2	104.8	107.5
65°	87.1	86.9	86.0	85.7	86.0	86.9	87.1	87.8	89.2	90.4	92.3
67.5°	74.5	73.7	73.4	73.1	73.4	73.7	74.5	75.1	76.0	77.5	78.5
70°	65.0	64.5	63.1	63.4	63.1	64.5	65.0	66.2	67.1	69.0	69.9
72.5°	54.8	54.3	54.0	53.7	54.0	54.3	54.8	55.9	56.8	58.9	60.4
75°	43.3	43.1	42.9	43.8	42.9	43.1	43.3	43.6	43.8	44.5	45.2
77.5°	34.7	34.7	34.9	34.5	34.9	34.7	34.7	34.7	34.7	35.1	35.2
80°	29.1	29.1	28.9	28.9	28.9	29.1	29.1	29.1	29.1	29.1	28.9
82.5°	23.3	23.5	23.7	23.3	23.7	23.5	23.3	23.7	23.9	23.5	23.7
85°	15.4	15.1	15.6	15.4	15.6	15.1	15.4	15.4	14.9	15.4	15.1
87.5°	14.3	14.0	14.1	14.4	14.1	14.0	14.3	13.8	13.6	13.4	13.0
90°	36.9	37.4	38.0	38.6	38.0	37.4	36.9	36.3	35.4	34.3	33.1
92.5°	41.7	42.0	42.3	42.7	42.3	42.0	41.7	41.3	40.2	38.4	36.6
95°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9
97.5°	52.1	52.4	52.7	53.0	52.7	52.4	52.1	51.8	50.5	48.3	46.0
100°	53.1	53.4	53.7	54.0	53.7	53.4	53.1	52.9	51.6	49.3	47.0
102.5°	53.5	54.0	54.5	55.0	54.5	54.0	53.5	53.0	56.3	63.3	70.4
105°	54.9	55.4	56.0	56.6	56.0	55.4	54.9	54.3	79.3	129.9	180.4
107.5°	292.1	253.9	215.8	177.7	215.8	253.9	292.1	330.2	367.8	404.9	442.0
110°	476.2	435.3	394.5	353.6	394.5	435.3	476.2	517.0	542.2	551.6	561.0



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	632.5	623.9	615.3	606.7	615.3	623.9	632.5	641.2	645.4	645.2	645.1
115°	752.6	753.8	754.9	756.1	754.9	753.8	752.6	751.5	749.5	746.6	743.8
117.5°	839.2	839.4	839.7	839.9	839.7	839.4	839.2	839.0	837.7	835.4	833.2
120°	897.5	897.5	897.5	897.5	897.5	897.5	897.5	897.5	896.4	894.1	891.8
122.5°	953.4	953.6	953.9	954.1	953.9	953.6	953.4	953.2	952.3	950.7	949.1
125°	1032.1	1032.7	1033.2	1033.8	1033.2	1032.7	1032.1	1031.5	1030.9	1030.4	1029.8
127.5°	1112.2	1111.6	1111.0	1110.4	1111.0	1111.6	1112.2	1112.7	1112.6	1111.6	1110.7
130°	1161.5	1161.0	1160.4	1159.8	1160.4	1161.0	1161.5	1162.1	1161.8	1160.7	1159.5
132.5°	1207.5	1206.7	1205.9	1205.1	1205.9	1206.7	1207.5	1208.3	1208.1	1207.0	1205.8
135°	1276.8	1276.0	1275.1	1274.3	1275.1	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0
137.5°	1341.0	1340.5	1339.9	1339.3	1339.9	1340.5	1341.0	1341.6	1341.2	1339.8	1338.5
140°	1380.1	1379.5	1379.0	1378.4	1379.0	1379.5	1380.1	1380.7	1380.4	1379.3	1378.1
142.5°	1416.8	1416.0	1415.2	1414.4	1415.2	1416.0	1416.8	1417.6	1417.6	1416.6	1415.7
145°	1469.7	1469.7	1469.7	1469.7	1469.7	1469.7	1469.7	1469.7	1469.4	1468.8	1468.3
147.5°	1514.8	1513.5	1512.2	1510.8	1512.2	1513.5	1514.8	1516.1	1516.5	1515.9	1515.3
150°	1544.3	1543.4	1542.6	1541.7	1542.6	1543.4	1544.3	1545.1	1545.3	1544.7	1544.1
152.5°	1570.3	1569.0	1567.7	1566.4	1567.7	1569.0	1570.3	1571.7	1571.8	1570.8	1569.7
155°	1606.0	1604.3	1602.6	1600.9	1602.6	1604.3	1606.0	1607.7	1607.9	1606.4	1605.0
157.5°	1636.6	1634.4	1632.1	1629.9	1632.1	1634.4	1636.6	1638.8	1639.1	1637.4	1635.7
160°	1654.4	1652.4	1650.4	1648.4	1650.4	1652.4	1654.4	1656.4	1656.6	1654.9	1653.1
162.5°	1671.2	1669.5	1667.7	1665.9	1667.7	1669.5	1671.2	1673.0	1672.9	1671.0	1669.0
165°	1693.0	1691.0	1689.0	1687.0	1689.0	1691.0	1693.0	1695.0	1694.9	1692.6	1690.3
167.5°	1709.0	1706.8	1704.5	1702.2	1704.5	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8
170°	1718.3	1716.0	1713.7	1711.4	1713.7	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0
172.5°	1724.1	1721.6	1719.1	1716.6	1719.1	1721.6	1724.1	1726.6	1726.8	1724.5	1722.2
175°	1731.2	1728.9	1726.6	1724.3	1726.6	1728.9	1731.2	1733.4	1733.6	1731.6	1729.6
177.5°	1733.5	1731.2	1728.9	1726.6	1728.9	1731.2	1733.5	1735.8	1736.0	1734.2	1732.3
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	519.5	522.1	524.7	527.1	530.8	532.5	534.9	535.9	538.6	542.7	546.1
5°	487.9	491.6	496.5	500.4	506.7	511.6	517.0	522.1	528.2	536.8	544.5
7.5°	461.1	464.7	470.6	478.0	484.9	491.9	499.2	506.2	514.8	527.2	539.4
10°	443.4	447.8	454.8	462.7	471.3	478.1	486.7	495.5	506.3	520.5	535.2
12.5°	428.1	431.4	439.5	447.0	456.8	465.4	473.8	484.2	496.4	511.5	529.2
15°	403.8	408.4	416.3	424.7	435.0	444.1	455.0	467.6	479.5	498.1	519.5
17.5°	379.3	386.4	394.7	404.1	411.7	424.3	436.1	449.0	463.7	483.4	507.0
20°	363.7	369.3	377.0	390.7	400.7	410.3	421.2	437.3	450.8	473.2	497.6
22.5°	350.4	354.5	363.2	374.5	386.2	397.2	408.4	423.7	440.4	461.6	488.1
25°	330.8	337.4	343.9	352.0	364.6	377.9	390.0	403.1	420.8	443.4	472.0
27.5°	311.7	317.6	324.0	334.0	343.6	356.0	368.7	383.6	402.6	426.5	455.6
30°	299.4	303.8	309.9	322.7	331.3	342.0	356.9	370.2	387.9	413.3	444.1
32.5°	286.7	292.4	299.1	308.9	319.6	329.7	343.3	357.7	375.8	400.8	432.3
35°	268.6	275.4	282.1	289.4	300.1	310.6	322.0	337.8	356.2	380.5	411.4
37.5°	252.0	257.4	262.9	271.9	282.0	292.0	302.7	318.3	335.6	361.8	390.2
40°	241.4	246.3	250.5	259.8	269.6	280.3	290.8	304.5	323.1	347.6	375.1
42.5°	229.8	234.3	240.0	247.7	258.2	267.2	277.7	290.7	308.2	333.1	357.2
45°	212.5	217.6	222.5	229.7	240.2	249.1	258.4	270.7	288.7	309.2	330.6
47.5°	194.4	199.6	205.2	212.2	221.3	230.3	239.6	250.5	266.9	287.0	301.5
50°	182.9	187.1	192.7	199.7	208.1	217.6	226.0	237.9	253.5	269.3	281.9
52.5°	171.0	174.8	181.1	188.5	196.3	204.6	213.5	223.7	237.8	252.7	262.7
55°	152.4	157.0	162.4	169.6	177.3	184.3	192.9	203.4	214.6	225.8	232.5
57.5°	135.0	138.9	143.4	150.8	157.5	165.8	173.6	181.7	192.1	200.5	204.9
60°	122.3	125.8	131.6	138.2	144.4	151.7	160.5	168.7	176.6	183.4	186.8
62.5°	110.4	114.4	119.5	125.5	132.3	139.2	146.9	153.8	160.8	166.6	169.0
65°	94.8	98.1	101.8	107.4	113.0	120.0	126.0	133.0	138.2	141.4	143.5
67.5°	80.7	82.8	85.6	89.4	94.9	101.0	106.8	112.3	116.6	118.8	120.7
70°	71.5	72.9	75.0	78.7	82.9	88.3	94.4	98.3	102.0	103.9	105.8
72.5°	62.4	64.2	66.1	69.1	72.5	76.4	80.8	85.6	87.7	89.9	91.0
75°	47.3	49.9	52.4	54.3	56.6	59.6	63.6	66.6	67.8	69.7	69.9
77.5°	35.7	36.3	38.1	40.4	42.4	44.6	47.1	49.8	50.4	51.3	52.0
80°	29.4	29.4	29.4	30.8	33.1	34.7	37.0	38.4	39.4	39.6	39.8
82.5°	23.6	23.6	23.4	23.7	24.5	25.4	27.5	29.1	29.9	29.7	29.2
85°	15.4	14.9	14.9	14.7	14.9	14.4	14.2	15.1	16.5	16.5	16.1
87.5°	12.7	12.3	11.8	10.8	9.9	9.0	7.8	7.4	6.8	7.0	6.2
90°	32.0	30.9	27.1	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3
92.5°	34.7	32.9	30.1	27.3	24.5	21.7	20.7	21.5	22.3	23.1	23.9
95°	41.9	39.9	36.7	33.6	30.4	27.3	31.6	43.3	55.0	66.7	78.4
97.5°	43.7	41.4	62.0	82.6	103.1	123.7	136.6	141.9	147.1	152.4	157.6
100°	44.7	42.4	87.0	131.6	176.2	220.7	240.2	234.4	228.7	223.0	217.3
102.5°	77.5	84.6	133.3	182.0	230.7	279.4	301.7	297.5	293.4	289.3	285.2
105°	231.0	281.6	307.3	333.0	358.7	384.5	395.7	392.6	389.5	386.3	383.2
107.5°	479.0	516.1	512.1	508.0	504.0	499.9	496.6	494.1	491.6	489.1	486.6
110°	570.5	579.9	576.8	573.6	570.5	567.3	564.6	562.3	560.0	557.8	555.5



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	644.9	644.7	641.6	638.4	635.3	632.1	629.5	627.5	625.4	623.4	621.3
115°	740.9	738.1	735.5	732.9	730.3	727.8	725.6	723.9	722.2	720.5	718.8
117.5°	830.9	828.6	827.3	826.0	824.6	823.3	821.6	819.5	817.4	815.3	813.2
120°	889.5	887.2	886.4	885.5	884.6	883.8	882.1	879.5	876.9	874.4	871.8
122.5°	947.5	945.9	944.8	943.7	942.6	941.5	939.9	937.8	935.7	933.6	931.5
125°	1029.2	1028.7	1027.5	1026.4	1025.2	1024.1	1022.4	1020.1	1017.8	1015.5	1013.2
127.5°	1109.8	1108.9	1107.5	1106.2	1104.8	1103.4	1101.6	1099.3	1097.0	1094.7	1092.4
130°	1158.4	1157.2	1156.1	1155.0	1153.8	1152.7	1151.0	1148.7	1146.4	1144.1	1141.8
132.5°	1204.7	1203.5	1202.6	1201.7	1200.8	1199.9	1198.3	1196.0	1193.7	1191.4	1189.1
135°	1275.1	1274.3	1273.1	1272.0	1270.8	1269.7	1268.3	1266.5	1264.8	1263.1	1261.4
137.5°	1337.1	1335.7	1335.1	1334.5	1333.8	1333.2	1331.8	1329.6	1327.5	1325.3	1323.1
140°	1377.0	1375.8	1375.0	1374.1	1373.3	1372.4	1371.1	1369.4	1367.7	1366.0	1364.3
142.5°	1414.8	1413.9	1413.0	1412.2	1411.3	1410.5	1409.2	1407.5	1405.8	1404.0	1402.3
145°	1467.7	1467.1	1466.6	1466.0	1465.4	1464.8	1463.6	1461.6	1459.6	1457.6	1455.6
147.5°	1514.8	1514.2	1513.6	1513.0	1512.5	1511.9	1511.0	1509.6	1508.3	1507.0	1505.7
150°	1543.6	1543.0	1542.4	1541.8	1541.3	1540.7	1540.0	1539.1	1538.3	1537.4	1536.6
152.5°	1568.7	1567.7	1567.3	1567.0	1566.7	1566.3	1565.9	1565.5	1565.1	1564.7	1564.3
155°	1603.6	1602.1	1601.9	1601.6	1601.3	1601.0	1601.1	1601.7	1602.3	1602.9	1603.4
157.5°	1633.9	1632.2	1632.5	1632.8	1633.1	1633.4	1633.5	1633.6	1633.7	1633.7	1633.8
160°	1651.4	1649.7	1650.0	1650.3	1650.6	1650.9	1651.1	1651.4	1651.7	1652.0	1652.3
162.5°	1667.1	1665.1	1665.4	1665.7	1666.0	1666.3	1666.8	1667.5	1668.3	1669.0	1669.8
165°	1688.0	1685.7	1686.0	1686.3	1686.6	1686.9	1687.4	1688.3	1689.1	1690.0	1690.9
167.5°	1704.5	1702.2	1702.2	1702.2	1702.2	1702.2	1702.7	1703.9	1705.0	1706.2	1707.3
170°	1713.7	1711.4	1711.4	1711.4	1711.4	1711.4	1712.0	1713.2	1714.3	1715.4	1716.6
172.5°	1719.9	1717.6	1717.4	1717.2	1716.9	1716.7	1717.3	1718.6	1720.0	1721.4	1722.8
175°	1727.6	1725.6	1725.3	1725.0	1724.7	1724.4	1725.0	1726.4	1727.9	1729.3	1730.7
177.5°	1730.5	1728.7	1728.4	1728.2	1728.0	1727.8	1728.2	1729.4	1730.5	1731.6	1732.8
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	547.2	549.3	551.9	555.8	558.8	561.4	561.9	562.7	564.6	567.7	570.1
5°	550.8	556.1	564.7	573.1	582.2	589.7	596.7	601.6	606.2	616.0	623.9
7.5°	549.6	561.6	575.1	590.1	605.4	620.1	633.8	646.1	658.3	672.6	688.8
10°	548.9	562.9	581.1	600.4	621.6	642.3	662.4	678.0	696.1	712.5	733.2
12.5°	545.4	565.5	587.2	611.9	638.0	661.9	688.3	709.8	730.6	754.2	778.3
15°	540.7	565.2	592.7	625.5	665.2	694.0	721.1	758.6	784.2	809.8	844.3
17.5°	532.3	562.2	596.5	639.2	672.2	711.1	751.7	781.4	815.9	852.0	883.2
20°	525.6	560.3	598.8	640.7	682.9	725.0	764.4	799.8	835.5	877.2	902.8
22.5°	518.9	553.2	593.2	637.7	683.0	727.5	772.0	813.6	853.7	895.8	928.5
25°	504.6	545.4	588.7	634.2	678.9	727.8	780.9	827.3	876.9	920.3	951.3
27.5°	490.2	527.6	570.7	616.8	666.5	724.3	786.8	839.5	889.2	920.3	930.0
30°	477.1	516.7	556.4	603.2	657.0	721.5	787.9	848.3	889.0	902.6	892.5
32.5°	463.9	499.8	539.0	587.0	644.1	714.6	789.4	843.1	867.6	857.3	816.5
35°	440.6	472.9	510.9	558.9	624.6	710.8	783.3	819.6	813.6	755.3	678.4
37.5°	415.6	442.0	477.1	527.3	604.4	695.7	756.8	762.2	709.7	620.3	531.5
40°	395.8	419.6	455.7	508.1	588.7	680.8	730.2	708.5	627.2	527.7	453.6
42.5°	376.6	396.7	431.5	488.0	573.8	660.4	690.5	643.3	549.5	455.4	388.0
45°	344.1	363.0	397.9	455.9	543.3	621.6	617.6	535.6	441.7	366.0	310.1
47.5°	313.3	329.8	362.6	421.8	507.5	563.3	526.3	439.0	359.4	298.6	258.7
50°	291.5	307.8	340.4	398.9	478.8	519.5	466.7	382.6	309.6	259.3	227.6
52.5°	270.6	286.5	316.3	373.3	444.1	468.5	411.7	333.7	272.9	229.5	202.3
55°	241.4	253.5	280.3	334.8	387.7	393.3	335.7	270.5	220.4	190.1	171.5
57.5°	211.6	222.0	248.5	291.9	329.0	326.1	271.6	215.1	181.4	158.9	145.4
60°	192.2	202.5	225.8	263.0	291.0	281.2	231.1	185.7	156.8	140.3	129.5
62.5°	174.1	182.1	204.0	231.2	251.3	240.2	197.6	160.0	137.0	123.1	114.6
65°	147.9	154.5	171.9	186.2	197.3	186.6	151.2	125.1	108.6	98.8	93.0
67.5°	123.1	127.2	138.2	143.4	151.3	139.5	113.7	96.2	86.8	78.6	74.5
70°	107.4	110.4	116.3	120.5	122.5	110.4	91.3	78.5	70.6	64.8	62.2
72.5°	91.7	94.4	95.6	99.0	97.9	86.6	73.4	63.2	57.5	53.6	50.3
75°	70.1	71.3	70.1	68.7	65.7	57.8	48.7	43.6	39.4	37.5	36.3
77.5°	51.1	50.7	49.2	47.0	41.8	36.8	31.9	30.2	28.4	27.4	27.0
80°	39.4	38.4	37.0	33.5	29.1	25.6	24.5	23.3	22.6	21.4	21.2
82.5°	29.3	28.7	26.4	23.5	20.4	18.7	17.8	17.3	16.6	16.0	16.0
85°	15.6	14.9	12.3	10.7	10.3	9.8	9.6	9.6	8.6	8.4	8.4
87.5°	5.9	5.3	5.7	5.7	6.4	6.7	7.7	8.0	8.6	9.0	8.9
90°	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.1	30.9	32.0	33.1
92.5°	23.1	22.3	21.5	20.7	21.7	24.5	27.3	30.1	32.9	34.7	36.6
95°	66.7	55.0	43.3	31.6	27.3	30.4	33.6	36.7	39.9	41.9	43.9
97.5°	152.4	147.1	141.9	136.6	123.7	103.1	82.6	62.0	41.4	43.7	46.0
100°	223.0	228.7	234.4	240.2	220.7	176.2	131.6	87.0	42.4	44.7	47.0
102.5°	289.3	293.4	297.5	301.7	279.4	230.7	182.0	133.3	84.6	77.5	70.4
105°	386.3	389.5	392.6	395.7	384.5	358.7	333.0	307.3	281.6	231.0	180.4
107.5°	489.1	491.6	494.1	496.6	499.9	504.0	508.0	512.1	516.1	479.0	442.0
110°	557.8	560.0	562.3	564.6	567.3	570.5	573.6	576.8	579.9	570.5	561.0



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	623.4	625.4	627.5	629.5	632.1	635.3	638.4	641.6	644.7	644.9	645.1
115°	720.5	722.2	723.9	725.6	727.8	730.3	732.9	735.5	738.1	740.9	743.8
117.5°	815.3	817.4	819.5	821.6	823.3	824.6	826.0	827.3	828.6	830.9	833.2
120°	874.4	876.9	879.5	882.1	883.8	884.6	885.5	886.4	887.2	889.5	891.8
122.5°	933.6	935.7	937.8	939.9	941.5	942.6	943.7	944.8	945.9	947.5	949.1
125°	1015.5	1017.8	1020.1	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2	1029.8
127.5°	1094.7	1097.0	1099.3	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8	1110.7
130°	1144.1	1146.4	1148.7	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4	1159.5
132.5°	1191.4	1193.7	1196.0	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7	1205.8
135°	1263.1	1264.8	1266.5	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1	1276.0
137.5°	1325.3	1327.5	1329.6	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1	1338.5
140°	1366.0	1367.7	1369.4	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0	1378.1
142.5°	1404.0	1405.8	1407.5	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8	1415.7
145°	1457.6	1459.6	1461.6	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7	1468.3
147.5°	1507.0	1508.3	1509.6	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.3
150°	1537.4	1538.3	1539.1	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6	1544.1
152.5°	1564.7	1565.1	1565.5	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7	1569.7
155°	1602.9	1602.3	1601.7	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6	1605.0
157.5°	1633.7	1633.7	1633.6	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9	1635.7
160°	1652.0	1651.7	1651.4	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4	1653.1
162.5°	1669.0	1668.3	1667.5	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1	1669.0
165°	1690.0	1689.1	1688.3	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0	1690.3
167.5°	1706.2	1705.0	1703.9	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5	1706.8
170°	1715.4	1714.3	1713.2	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7	1716.0
172.5°	1721.4	1720.0	1718.6	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9	1722.2
175°	1729.3	1727.9	1726.4	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6	1729.6
177.5°	1731.6	1730.5	1729.4	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5	1732.3
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	544.2	544.2	544.2	544.2	544.2	544.2	544.2
2.5°	574.1	574.1	574.8	577.6	578.0	580.4	579.7
5°	630.9	635.3	637.0	644.0	648.1	650.0	646.3
7.5°	700.4	712.9	718.8	726.2	732.6	734.6	729.5
10°	751.1	764.2	775.1	781.9	788.2	792.4	797.7
12.5°	800.1	816.2	826.6	836.1	842.6	847.9	848.8
15°	853.4	877.6	896.0	909.6	916.3	919.8	918.4
17.5°	907.1	929.6	942.7	956.5	965.8	966.3	966.6
20°	937.5	959.4	974.6	984.8	995.3	994.8	997.2
22.5°	957.8	975.1	986.7	994.1	997.7	995.9	996.4
25°	967.3	972.5	970.4	958.5	955.4	944.5	946.4
27.5°	918.3	894.1	869.0	836.8	811.3	791.0	792.0
30°	851.8	808.9	760.0	719.0	682.2	671.9	650.0
32.5°	758.8	694.5	637.2	598.9	567.4	558.8	539.7
35°	601.1	538.6	479.7	444.3	430.3	410.7	410.5
37.5°	467.2	412.2	381.1	354.5	340.6	328.7	327.6
40°	393.0	350.2	326.6	307.5	293.8	284.9	282.8
42.5°	341.2	306.6	284.5	272.7	262.1	257.5	254.1
45°	278.6	255.3	240.0	229.3	224.4	220.9	219.0
47.5°	233.1	217.5	207.0	199.8	195.9	192.2	193.2
50°	208.3	195.5	187.8	181.0	178.0	175.4	175.7
52.5°	188.3	176.8	170.6	165.7	162.0	160.1	159.3
55°	159.8	152.6	146.3	142.8	140.7	138.2	137.5
57.5°	136.3	130.7	125.6	121.7	121.1	118.7	119.0
60°	120.7	116.0	111.8	109.7	108.1	106.0	106.7
62.5°	107.8	103.9	100.1	98.4	96.7	95.2	95.5
65°	88.3	84.6	82.2	81.3	80.6	79.9	79.2
67.5°	70.4	68.1	66.6	64.6	63.2	63.0	62.3
70°	59.2	56.1	53.6	51.0	50.3	50.1	50.3
72.5°	47.4	45.5	44.8	43.6	43.4	42.8	43.2
75°	35.6	34.9	34.5	33.5	33.5	33.5	33.5
77.5°	26.3	25.9	25.6	25.4	25.2	24.8	24.8
80°	20.5	20.3	19.8	19.8	19.6	19.8	19.6
82.5°	15.5	15.4	15.0	15.0	14.7	14.6	14.7
85°	7.9	7.7	8.2	7.7	7.9	7.5	7.9
87.5°	9.1	9.3	9.3	9.4	9.4	9.8	9.6
90°	34.3	35.4	36.3	36.9	37.4	38.0	38.6
92.5°	38.4	40.2	41.3	41.7	42.0	42.3	42.7
95°	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	48.3	50.5	51.8	52.1	52.4	52.7	53.0
100°	49.3	51.6	52.9	53.1	53.4	53.7	54.0
102.5°	63.3	56.3	53.0	53.5	54.0	54.5	55.0
105°	129.9	79.3	54.3	54.9	55.4	56.0	56.6
107.5°	404.9	367.8	330.2	292.1	253.9	215.8	177.7
110°	551.6	542.2	517.0	476.2	435.3	394.5	353.6



TEST NUMBER: P332402

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	645.2	645.4	641.2	632.5	623.9	615.3	606.7
115°	746.6	749.5	751.5	752.6	753.8	754.9	756.1
117.5°	835.4	837.7	839.0	839.2	839.4	839.7	839.9
120°	894.1	896.4	897.5	897.5	897.5	897.5	897.5
122.5°	950.7	952.3	953.2	953.4	953.6	953.9	954.1
125°	1030.4	1030.9	1031.5	1032.1	1032.7	1033.2	1033.8
127.5°	1111.6	1112.6	1112.7	1112.2	1111.6	1111.0	1110.4
130°	1160.7	1161.8	1162.1	1161.5	1161.0	1160.4	1159.8
132.5°	1207.0	1208.1	1208.3	1207.5	1206.7	1205.9	1205.1
135°	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3
137.5°	1339.8	1341.2	1341.6	1341.0	1340.5	1339.9	1339.3
140°	1379.3	1380.4	1380.7	1380.1	1379.5	1379.0	1378.4
142.5°	1416.6	1417.6	1417.6	1416.8	1416.0	1415.2	1414.4
145°	1468.8	1469.4	1469.7	1469.7	1469.7	1469.7	1469.7
147.5°	1515.9	1516.5	1516.1	1514.8	1513.5	1512.2	1510.8
150°	1544.7	1545.3	1545.1	1544.3	1543.4	1542.6	1541.7
152.5°	1570.8	1571.8	1571.7	1570.3	1569.0	1567.7	1566.4
155°	1606.4	1607.9	1607.7	1606.0	1604.3	1602.6	1600.9
157.5°	1637.4	1639.1	1638.8	1636.6	1634.4	1632.1	1629.9
160°	1654.9	1656.6	1656.4	1654.4	1652.4	1650.4	1648.4
162.5°	1671.0	1672.9	1673.0	1671.2	1669.5	1667.7	1665.9
165°	1692.6	1694.9	1695.0	1693.0	1691.0	1689.0	1687.0
167.5°	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2
170°	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4
172.5°	1724.5	1726.8	1726.6	1724.1	1721.6	1719.1	1716.6
175°	1731.6	1733.6	1733.4	1731.2	1728.9	1726.6	1724.3
177.5°	1734.2	1736.0	1735.8	1733.5	1731.2	1728.9	1726.6
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7

(END OF REPORT)