

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332451-940

Luminaire Tested: **S123RDIW-S1000D460U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332451-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4956.3 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	99	96	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62
2	95	88	82	77	90	83	78	74	75	71	68	68	65	62	61	59	57	53
3	87	78	71	65	82	74	68	63	67	62	58	61	57	53	55	52	49	46
4	80	70	62	56	76	66	59	54	60	55	50	55	50	47	50	46	43	40
5	74	62	54	49	70	60	52	47	54	48	44	50	45	41	45	41	38	35
6	68	56	48	43	65	54	47	41	49	43	39	45	40	36	41	37	34	31
7	64	51	43	38	60	49	42	37	45	39	35	41	36	32	38	34	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27	25
9	55	43	36	30	53	41	34	30	38	32	28	35	30	26	32	28	25	23
10	52	40	32	28	49	38	31	27	35	30	26	33	28	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	2.8
10°-20°	435.5	8.8
20°-30°	684.2	13.8
30°-40°	713.8	14.4
40°-50°	610.9	12.3
50°-60°	465.6	9.4
60°-70°	298.4	6.0
70°-80°	143.6	2.9
80°-90°	39.5	0.8
90°-100°	33.5	0.7
100°-110°	100.3	2.0
110°-120°	170.6	3.4
120°-130°	224.4	4.5
130°-140°	252.2	5.1
140°-150°	247.9	5.0
150°-160°	208.7	4.2
160°-170°	138.9	2.8
170°-180°	48.7	1.0
0°-30°	1259.1	25.4
0°-40°	1973.0	39.8
0°-60°	3049.5	61.5
0°-90°	3531.0	71.2
90°-120°	304.4	6.1
90°-150°	1029.0	20.8
90°-180°	1425.0	28.8
0°-180°	4956.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	12	0	12	0	12	7
95°	32	24	32	24	32	32
105°	96	91	96	91	96	102
115°	172	172	172	172	172	170
125°	248	251	248	251	248	222
135°	326	326	326	326	326	250
145°	396	396	396	396	396	247
155°	452	453	452	453	452	208
165°	492	493	492	493	492	139
175°	511	513	511	513	511	49
180°	514	514	514	514	514	



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	7.3	8.2	7.2	7.7	7.6	8.0	8.0	7.9	8.8	8.3	8.5
90°	12.1	11.9	11.8	11.6	11.4	11.1	10.8	10.4	10.1	9.7	8.6
92.5°	16.3	16.4	16.5	16.7	16.8	16.7	16.4	16.1	15.8	15.5	14.9
95°	31.5	31.5	31.5	31.5	31.5	31.3	30.9	30.6	30.2	29.9	29.2
97.5°	48.5	48.5	48.6	48.6	48.6	48.4	48.1	47.6	47.2	46.8	46.3
100°	61.4	61.3	61.1	60.9	60.7	60.5	60.2	59.9	59.7	59.4	58.9
102.5°	74.6	74.7	74.7	74.8	74.8	74.7	74.5	74.2	73.9	73.7	73.0
105°	96.2	96.0	95.9	95.7	95.4	95.3	95.3	95.3	95.3	95.3	94.5
107.5°	118.6	118.7	118.8	118.9	119.0	118.9	118.6	118.3	118.1	117.8	117.4
110°	133.8	133.9	134.1	134.3	134.5	134.4	134.0	133.7	133.3	133.0	132.8



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.9	150.0	150.0	150.0	150.1	149.9	149.5	149.0	148.6	148.1	148.1
115°	172.2	172.3	172.4	172.5	172.5	172.5	172.5	172.4	172.3	172.2	172.4
117.5°	194.7	194.9	195.2	195.5	195.7	195.8	195.8	195.9	195.9	195.9	196.2
120°	210.5	210.7	210.9	211.1	211.2	211.4	211.5	211.6	211.7	211.8	212.2
122.5°	225.7	226.0	226.2	226.5	226.8	226.9	227.2	227.5	227.7	227.9	228.2
125°	248.5	248.9	249.2	249.6	249.9	250.3	250.7	251.0	251.4	251.7	251.9
127.5°	271.3	271.6	272.1	272.5	272.9	273.3	273.8	274.4	274.8	275.4	275.5
130°	286.1	286.8	287.4	288.0	288.6	289.1	289.4	289.8	290.2	290.5	290.8
132.5°	301.6	302.1	302.6	303.1	303.5	304.0	304.4	304.9	305.3	305.8	305.9
135°	325.7	325.9	326.1	326.3	326.5	326.7	327.1	327.4	327.8	328.1	328.2
137.5°	347.0	347.3	347.7	347.9	348.3	348.7	349.1	349.5	349.8	350.2	350.0
140°	360.9	361.5	362.1	362.7	363.4	363.7	363.8	363.9	364.0	364.1	364.0
142.5°	375.1	375.6	376.0	376.6	377.0	377.3	377.4	377.5	377.6	377.6	377.6
145°	395.7	396.0	396.4	396.7	397.1	397.3	397.3	397.4	397.5	397.6	397.3
147.5°	413.8	414.4	414.9	415.5	416.1	416.3	416.3	416.3	416.3	416.3	416.1
150°	425.5	426.1	426.6	427.1	427.7	427.9	427.9	427.9	427.9	427.9	427.8
152.5°	436.8	437.3	437.7	438.3	438.7	438.9	438.7	438.5	438.5	438.3	438.2
155°	452.2	452.8	453.4	454.1	454.7	454.9	454.5	454.1	453.8	453.4	453.3
157.5°	466.2	466.6	467.2	467.7	468.1	468.2	467.9	467.5	467.1	466.7	466.6
160°	475.2	475.5	475.9	476.3	476.6	476.6	476.2	475.7	475.3	474.8	474.8
162.5°	482.0	482.6	483.1	483.8	484.3	484.4	483.9	483.5	483.0	482.6	482.5
165°	491.8	492.4	493.0	493.7	494.3	494.4	493.8	493.3	492.8	492.2	492.2
167.5°	500.1	500.7	501.2	501.8	502.3	502.3	501.8	501.2	500.7	500.1	500.1
170°	504.4	505.0	505.6	506.2	506.8	506.8	506.2	505.6	505.0	504.4	504.4
172.5°	507.6	508.2	508.8	509.4	510.1	510.1	509.5	509.0	508.5	507.8	507.8
175°	511.2	511.8	512.5	513.1	513.7	513.7	513.2	512.6	512.1	511.6	511.6
177.5°	513.1	513.6	514.2	514.6	515.1	515.1	514.8	514.3	513.9	513.4	513.4
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	9.3	8.6	9.3	9.1	10.3	10.6	13.4	15.6	16.3	14.5	14.7
90°	7.4	6.2	5.0	4.0	3.1	2.2	1.3	0.4	1.3	2.2	3.1
92.5°	14.2	13.6	12.8	12.2	11.6	11.0	10.4	9.8	10.4	11.0	11.6
95°	28.4	27.7	27.0	26.4	25.8	25.1	24.4	23.8	24.4	25.1	25.8
97.5°	45.7	45.2	44.7	44.2	43.8	43.2	42.8	42.4	42.8	43.2	43.8
100°	58.5	58.1	57.6	57.1	56.5	56.0	55.5	54.9	55.5	56.0	56.5
102.5°	72.4	71.9	71.2	70.8	70.4	70.2	69.8	69.5	69.8	70.2	70.4
105°	93.7	92.9	92.1	91.7	91.5	91.3	91.1	91.0	91.1	91.3	91.5
107.5°	117.1	116.8	116.5	116.3	116.1	116.0	115.9	115.8	115.9	116.0	116.1
110°	132.6	132.4	132.2	132.1	131.9	131.7	131.5	131.3	131.5	131.7	131.9



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	148.1	148.0	148.0	147.9	147.8	147.8	147.6	147.5	147.6	147.8	147.8
115°	172.5	172.7	172.9	172.8	172.5	172.3	172.0	171.7	172.0	172.3	172.5
117.5°	196.4	196.6	196.8	196.9	196.7	196.5	196.4	196.2	196.4	196.5	196.7
120°	212.7	213.1	213.6	213.5	212.9	212.4	211.9	211.3	211.9	212.4	212.9
122.5°	228.4	228.6	228.8	228.7	228.4	228.0	227.6	227.2	227.6	228.0	228.4
125°	252.1	252.3	252.4	252.4	252.2	251.9	251.6	251.4	251.6	251.9	252.2
127.5°	275.7	276.0	276.2	276.0	275.4	274.8	274.2	273.7	274.2	274.8	275.4
130°	291.1	291.3	291.6	291.4	290.7	290.0	289.3	288.6	289.3	290.0	290.7
132.5°	306.1	306.3	306.6	306.3	305.6	304.9	304.1	303.4	304.1	304.9	305.6
135°	328.3	328.4	328.5	328.2	327.7	327.2	326.6	326.1	326.6	327.2	327.7
137.5°	349.7	349.5	349.3	348.9	348.5	348.0	347.6	347.1	347.6	348.0	348.5
140°	363.9	363.8	363.7	363.5	363.0	362.6	362.1	361.7	362.1	362.6	363.0
142.5°	377.4	377.2	377.0	376.7	376.3	375.9	375.4	375.0	375.4	375.9	376.3
145°	397.1	396.8	396.5	396.4	396.2	396.0	395.8	395.7	395.8	396.0	396.2
147.5°	415.8	415.5	415.3	415.0	414.6	414.4	414.0	413.8	414.0	414.4	414.6
150°	427.6	427.4	427.2	427.0	426.9	426.7	426.5	426.3	426.5	426.7	426.9
152.5°	438.1	437.9	437.8	437.7	437.4	437.2	436.9	436.7	436.9	437.2	437.4
155°	453.3	453.2	453.1	453.0	453.0	453.0	453.0	453.0	453.0	453.0	453.0
157.5°	466.6	466.5	466.5	466.5	466.5	466.7	466.8	466.9	466.8	466.7	466.5
160°	474.8	474.8	474.8	474.9	475.1	475.3	475.5	475.6	475.5	475.3	475.1
162.5°	482.4	482.3	482.3	482.4	482.6	482.9	483.1	483.4	483.1	482.9	482.6
165°	492.2	492.2	492.2	492.3	492.6	492.8	493.1	493.4	493.1	492.8	492.6
167.5°	500.0	499.9	499.8	500.0	500.3	500.7	501.1	501.4	501.1	500.7	500.3
170°	504.4	504.4	504.4	504.5	504.9	505.2	505.6	506.0	505.6	505.2	504.9
172.5°	507.8	507.8	507.8	508.0	508.5	508.8	509.2	509.5	509.2	508.8	508.5
175°	511.6	511.6	511.6	511.8	512.1	512.5	512.8	513.2	512.8	512.5	512.1
177.5°	513.4	513.4	513.4	513.6	513.9	514.2	514.4	514.8	514.4	514.2	513.9
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	14.4	16.1	16.8	17.5	18.2	17.9	18.5	18.5	19.2	19.3	19.3
90°	4.0	5.0	6.2	7.4	8.6	9.7	10.1	10.4	10.8	11.1	11.4
92.5°	12.2	12.8	13.6	14.2	14.9	15.5	15.8	16.1	16.4	16.7	16.8
95°	26.4	27.0	27.7	28.4	29.2	29.9	30.2	30.6	30.9	31.3	31.5
97.5°	44.2	44.7	45.2	45.7	46.3	46.8	47.2	47.6	48.1	48.4	48.6
100°	57.1	57.6	58.1	58.5	58.9	59.4	59.7	59.9	60.2	60.5	60.7
102.5°	70.8	71.2	71.9	72.4	73.0	73.7	73.9	74.2	74.5	74.7	74.8
105°	91.7	92.1	92.9	93.7	94.5	95.3	95.3	95.3	95.3	95.3	95.4
107.5°	116.3	116.5	116.8	117.1	117.4	117.8	118.1	118.3	118.6	118.9	119.0
110°	132.1	132.2	132.4	132.6	132.8	133.0	133.3	133.7	134.0	134.4	134.5



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.9	148.0	148.0	148.1	148.1	148.1	148.6	149.0	149.5	149.9	150.1
115°	172.8	172.9	172.7	172.5	172.4	172.2	172.3	172.4	172.5	172.5	172.5
117.5°	196.9	196.8	196.6	196.4	196.2	195.9	195.9	195.9	195.8	195.8	195.7
120°	213.5	213.6	213.1	212.7	212.2	211.8	211.7	211.6	211.5	211.4	211.2
122.5°	228.7	228.8	228.6	228.4	228.2	227.9	227.7	227.5	227.2	226.9	226.8
125°	252.4	252.4	252.3	252.1	251.9	251.7	251.4	251.0	250.7	250.3	249.9
127.5°	276.0	276.2	276.0	275.7	275.5	275.4	274.8	274.4	273.8	273.3	272.9
130°	291.4	291.6	291.3	291.1	290.8	290.5	290.2	289.8	289.4	289.1	288.6
132.5°	306.3	306.6	306.3	306.1	305.9	305.8	305.3	304.9	304.4	304.0	303.5
135°	328.2	328.5	328.4	328.3	328.2	328.1	327.8	327.4	327.1	326.7	326.5
137.5°	348.9	349.3	349.5	349.7	350.0	350.2	349.8	349.5	349.1	348.7	348.3
140°	363.5	363.7	363.8	363.9	364.0	364.1	364.0	363.9	363.8	363.7	363.4
142.5°	376.7	377.0	377.2	377.4	377.6	377.6	377.6	377.5	377.4	377.3	377.0
145°	396.4	396.5	396.8	397.1	397.3	397.6	397.5	397.4	397.3	397.3	397.1
147.5°	415.0	415.3	415.5	415.8	416.1	416.3	416.3	416.3	416.3	416.3	416.1
150°	427.0	427.2	427.4	427.6	427.8	427.9	427.9	427.9	427.9	427.9	427.7
152.5°	437.7	437.8	437.9	438.1	438.2	438.3	438.5	438.5	438.7	438.9	438.7
155°	453.0	453.1	453.2	453.3	453.3	453.4	453.8	454.1	454.5	454.9	454.7
157.5°	466.5	466.5	466.5	466.6	466.6	466.7	467.1	467.5	467.9	468.2	468.1
160°	474.9	474.8	474.8	474.8	474.8	474.8	475.3	475.7	476.2	476.6	476.6
162.5°	482.4	482.3	482.3	482.4	482.5	482.6	483.0	483.5	483.9	484.4	484.3
165°	492.3	492.2	492.2	492.2	492.2	492.2	492.8	493.3	493.8	494.4	494.3
167.5°	500.0	499.8	499.9	500.0	500.1	500.1	500.7	501.2	501.8	502.3	502.3
170°	504.5	504.4	504.4	504.4	504.4	504.4	505.0	505.6	506.2	506.8	506.8
172.5°	508.0	507.8	507.8	507.8	507.8	507.8	508.5	509.0	509.5	510.1	510.1
175°	511.8	511.6	511.6	511.6	511.6	511.6	512.1	512.6	513.2	513.7	513.7
177.5°	513.6	513.4	513.4	513.4	513.4	513.4	513.9	514.3	514.8	515.1	515.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	20.2	19.4	19.4	19.9	19.4	19.4	20.2	19.3	19.3	19.2	18.5
90°	11.6	11.8	11.9	12.1	11.9	11.8	11.6	11.4	11.1	10.8	10.4
92.5°	16.7	16.5	16.4	16.3	16.4	16.5	16.7	16.8	16.7	16.4	16.1
95°	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.3	30.9	30.6
97.5°	48.6	48.6	48.5	48.5	48.5	48.6	48.6	48.6	48.4	48.1	47.6
100°	60.9	61.1	61.3	61.4	61.3	61.1	60.9	60.7	60.5	60.2	59.9
102.5°	74.8	74.7	74.7	74.6	74.7	74.7	74.8	74.8	74.7	74.5	74.2
105°	95.7	95.9	96.0	96.2	96.0	95.9	95.7	95.4	95.3	95.3	95.3
107.5°	118.9	118.8	118.7	118.6	118.7	118.8	118.9	119.0	118.9	118.6	118.3
110°	134.3	134.1	133.9	133.8	133.9	134.1	134.3	134.5	134.4	134.0	133.7



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	150.0	150.0	150.0	149.9	150.0	150.0	150.0	150.1	149.9	149.5	149.0
115°	172.5	172.4	172.3	172.2	172.3	172.4	172.5	172.5	172.5	172.5	172.4
117.5°	195.5	195.2	194.9	194.7	194.9	195.2	195.5	195.7	195.8	195.8	195.9
120°	211.1	210.9	210.7	210.5	210.7	210.9	211.1	211.2	211.4	211.5	211.6
122.5°	226.5	226.2	226.0	225.7	226.0	226.2	226.5	226.8	226.9	227.2	227.5
125°	249.6	249.2	248.9	248.5	248.9	249.2	249.6	249.9	250.3	250.7	251.0
127.5°	272.5	272.1	271.6	271.3	271.6	272.1	272.5	272.9	273.3	273.8	274.4
130°	288.0	287.4	286.8	286.1	286.8	287.4	288.0	288.6	289.1	289.4	289.8
132.5°	303.1	302.6	302.1	301.6	302.1	302.6	303.1	303.5	304.0	304.4	304.9
135°	326.3	326.1	325.9	325.7	325.9	326.1	326.3	326.5	326.7	327.1	327.4
137.5°	347.9	347.7	347.3	347.0	347.3	347.7	347.9	348.3	348.7	349.1	349.5
140°	362.7	362.1	361.5	360.9	361.5	362.1	362.7	363.4	363.7	363.8	363.9
142.5°	376.6	376.0	375.6	375.1	375.6	376.0	376.6	377.0	377.3	377.4	377.5
145°	396.7	396.4	396.0	395.7	396.0	396.4	396.7	397.1	397.3	397.3	397.4
147.5°	415.5	414.9	414.4	413.8	414.4	414.9	415.5	416.1	416.3	416.3	416.3
150°	427.1	426.6	426.1	425.5	426.1	426.6	427.1	427.7	427.9	427.9	427.9
152.5°	438.3	437.7	437.3	436.8	437.3	437.7	438.3	438.7	438.9	438.7	438.5
155°	454.1	453.4	452.8	452.2	452.8	453.4	454.1	454.7	454.9	454.5	454.1
157.5°	467.7	467.2	466.6	466.2	466.6	467.2	467.7	468.1	468.2	467.9	467.5
160°	476.3	475.9	475.5	475.2	475.5	475.9	476.3	476.6	476.6	476.2	475.7
162.5°	483.8	483.1	482.6	482.0	482.6	483.1	483.8	484.3	484.4	483.9	483.5
165°	493.7	493.0	492.4	491.8	492.4	493.0	493.7	494.3	494.4	493.8	493.3
167.5°	501.8	501.2	500.7	500.1	500.7	501.2	501.8	502.3	502.3	501.8	501.2
170°	506.2	505.6	505.0	504.4	505.0	505.6	506.2	506.8	506.8	506.2	505.6
172.5°	509.4	508.8	508.2	507.6	508.2	508.8	509.4	510.1	510.1	509.5	509.0
175°	513.1	512.5	511.8	511.2	511.8	512.5	513.1	513.7	513.7	513.2	512.6
177.5°	514.6	514.2	513.6	513.1	513.6	514.2	514.6	515.1	515.1	514.8	514.3
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	18.5	17.9	18.2	17.5	16.8	16.1	14.4	14.7	14.5	16.3	15.6
90°	10.1	9.7	8.6	7.4	6.2	5.0	4.0	3.1	2.2	1.3	0.4
92.5°	15.8	15.5	14.9	14.2	13.6	12.8	12.2	11.6	11.0	10.4	9.8
95°	30.2	29.9	29.2	28.4	27.7	27.0	26.4	25.8	25.1	24.4	23.8
97.5°	47.2	46.8	46.3	45.7	45.2	44.7	44.2	43.8	43.2	42.8	42.4
100°	59.7	59.4	58.9	58.5	58.1	57.6	57.1	56.5	56.0	55.5	54.9
102.5°	73.9	73.7	73.0	72.4	71.9	71.2	70.8	70.4	70.2	69.8	69.5
105°	95.3	95.3	94.5	93.7	92.9	92.1	91.7	91.5	91.3	91.1	91.0
107.5°	118.1	117.8	117.4	117.1	116.8	116.5	116.3	116.1	116.0	115.9	115.8
110°	133.3	133.0	132.8	132.6	132.4	132.2	132.1	131.9	131.7	131.5	131.3



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	148.6	148.1	148.1	148.1	148.0	148.0	147.9	147.8	147.8	147.6	147.5
115°	172.3	172.2	172.4	172.5	172.7	172.9	172.8	172.5	172.3	172.0	171.7
117.5°	195.9	195.9	196.2	196.4	196.6	196.8	196.9	196.7	196.5	196.4	196.2
120°	211.7	211.8	212.2	212.7	213.1	213.6	213.5	212.9	212.4	211.9	211.3
122.5°	227.7	227.9	228.2	228.4	228.6	228.8	228.7	228.4	228.0	227.6	227.2
125°	251.4	251.7	251.9	252.1	252.3	252.4	252.4	252.2	251.9	251.6	251.4
127.5°	274.8	275.4	275.5	275.7	276.0	276.2	276.0	275.4	274.8	274.2	273.7
130°	290.2	290.5	290.8	291.1	291.3	291.6	291.4	290.7	290.0	289.3	288.6
132.5°	305.3	305.8	305.9	306.1	306.3	306.6	306.3	305.6	304.9	304.1	303.4
135°	327.8	328.1	328.2	328.3	328.4	328.5	328.2	327.7	327.2	326.6	326.1
137.5°	349.8	350.2	350.0	349.7	349.5	349.3	348.9	348.5	348.0	347.6	347.1
140°	364.0	364.1	364.0	363.9	363.8	363.7	363.5	363.0	362.6	362.1	361.7
142.5°	377.6	377.6	377.6	377.4	377.2	377.0	376.7	376.3	375.9	375.4	375.0
145°	397.5	397.6	397.3	397.1	396.8	396.5	396.4	396.2	396.0	395.8	395.7
147.5°	416.3	416.3	416.1	415.8	415.5	415.3	415.0	414.6	414.4	414.0	413.8
150°	427.9	427.9	427.8	427.6	427.4	427.2	427.0	426.9	426.7	426.5	426.3
152.5°	438.5	438.3	438.2	438.1	437.9	437.8	437.7	437.4	437.2	436.9	436.7
155°	453.8	453.4	453.3	453.3	453.2	453.1	453.0	453.0	453.0	453.0	453.0
157.5°	467.1	466.7	466.6	466.6	466.5	466.5	466.5	466.5	466.7	466.8	466.9
160°	475.3	474.8	474.8	474.8	474.8	474.8	474.9	475.1	475.3	475.5	475.6
162.5°	483.0	482.6	482.5	482.4	482.3	482.3	482.4	482.6	482.9	483.1	483.4
165°	492.8	492.2	492.2	492.2	492.2	492.2	492.3	492.6	492.8	493.1	493.4
167.5°	500.7	500.1	500.1	500.0	499.9	499.8	500.0	500.3	500.7	501.1	501.4
170°	505.0	504.4	504.4	504.4	504.4	504.4	504.5	504.9	505.2	505.6	506.0
172.5°	508.5	507.8	507.8	507.8	507.8	507.8	508.0	508.5	508.8	509.2	509.5
175°	512.1	511.6	511.6	511.6	511.6	511.6	511.8	512.1	512.5	512.8	513.2
177.5°	513.9	513.4	513.4	513.4	513.4	513.4	513.6	513.9	514.2	514.4	514.8
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.4	10.6	10.3	9.1	9.3	8.6	9.3	8.5	8.3	8.8	7.9
90°	1.3	2.2	3.1	4.0	5.0	6.2	7.4	8.6	9.7	10.1	10.4
92.5°	10.4	11.0	11.6	12.2	12.8	13.6	14.2	14.9	15.5	15.8	16.1
95°	24.4	25.1	25.8	26.4	27.0	27.7	28.4	29.2	29.9	30.2	30.6
97.5°	42.8	43.2	43.8	44.2	44.7	45.2	45.7	46.3	46.8	47.2	47.6
100°	55.5	56.0	56.5	57.1	57.6	58.1	58.5	58.9	59.4	59.7	59.9
102.5°	69.8	70.2	70.4	70.8	71.2	71.9	72.4	73.0	73.7	73.9	74.2
105°	91.1	91.3	91.5	91.7	92.1	92.9	93.7	94.5	95.3	95.3	95.3
107.5°	115.9	116.0	116.1	116.3	116.5	116.8	117.1	117.4	117.8	118.1	118.3
110°	131.5	131.7	131.9	132.1	132.2	132.4	132.6	132.8	133.0	133.3	133.7



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	147.6	147.8	147.8	147.9	148.0	148.0	148.1	148.1	148.1	148.6	149.0
115°	172.0	172.3	172.5	172.8	172.9	172.7	172.5	172.4	172.2	172.3	172.4
117.5°	196.4	196.5	196.7	196.9	196.8	196.6	196.4	196.2	195.9	195.9	195.9
120°	211.9	212.4	212.9	213.5	213.6	213.1	212.7	212.2	211.8	211.7	211.6
122.5°	227.6	228.0	228.4	228.7	228.8	228.6	228.4	228.2	227.9	227.7	227.5
125°	251.6	251.9	252.2	252.4	252.4	252.3	252.1	251.9	251.7	251.4	251.0
127.5°	274.2	274.8	275.4	276.0	276.2	276.0	275.7	275.5	275.4	274.8	274.4
130°	289.3	290.0	290.7	291.4	291.6	291.3	291.1	290.8	290.5	290.2	289.8
132.5°	304.1	304.9	305.6	306.3	306.6	306.3	306.1	305.9	305.8	305.3	304.9
135°	326.6	327.2	327.7	328.2	328.5	328.4	328.3	328.2	328.1	327.8	327.4
137.5°	347.6	348.0	348.5	348.9	349.3	349.5	349.7	350.0	350.2	349.8	349.5
140°	362.1	362.6	363.0	363.5	363.7	363.8	363.9	364.0	364.1	364.0	363.9
142.5°	375.4	375.9	376.3	376.7	377.0	377.2	377.4	377.6	377.6	377.6	377.5
145°	395.8	396.0	396.2	396.4	396.5	396.8	397.1	397.3	397.6	397.5	397.4
147.5°	414.0	414.4	414.6	415.0	415.3	415.5	415.8	416.1	416.3	416.3	416.3
150°	426.5	426.7	426.9	427.0	427.2	427.4	427.6	427.8	427.9	427.9	427.9
152.5°	436.9	437.2	437.4	437.7	437.8	437.9	438.1	438.2	438.3	438.5	438.5
155°	453.0	453.0	453.0	453.0	453.1	453.2	453.3	453.3	453.4	453.8	454.1
157.5°	466.8	466.7	466.5	466.5	466.5	466.5	466.6	466.6	466.7	467.1	467.5
160°	475.5	475.3	475.1	474.9	474.8	474.8	474.8	474.8	474.8	475.3	475.7
162.5°	483.1	482.9	482.6	482.4	482.3	482.3	482.4	482.5	482.6	483.0	483.5
165°	493.1	492.8	492.6	492.3	492.2	492.2	492.2	492.2	492.2	492.8	493.3
167.5°	501.1	500.7	500.3	500.0	499.8	499.9	500.0	500.1	500.1	500.7	501.2
170°	505.6	505.2	504.9	504.5	504.4	504.4	504.4	504.4	504.4	505.0	505.6
172.5°	509.2	508.8	508.5	508.0	507.8	507.8	507.8	507.8	507.8	508.5	509.0
175°	512.8	512.5	512.1	511.8	511.6	511.6	511.6	511.6	511.6	512.1	512.6
177.5°	514.4	514.2	513.9	513.6	513.4	513.4	513.4	513.4	513.4	513.9	514.3
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	8.0	8.0	7.6	7.7	7.2	8.2	7.3
90°	10.8	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.4	16.7	16.8	16.7	16.5	16.4	16.3
95°	30.9	31.3	31.5	31.5	31.5	31.5	31.5
97.5°	48.1	48.4	48.6	48.6	48.6	48.5	48.5
100°	60.2	60.5	60.7	60.9	61.1	61.3	61.4
102.5°	74.5	74.7	74.8	74.8	74.7	74.7	74.6
105°	95.3	95.3	95.4	95.7	95.9	96.0	96.2
107.5°	118.6	118.9	119.0	118.9	118.8	118.7	118.6
110°	134.0	134.4	134.5	134.3	134.1	133.9	133.8



TEST NUMBER: P332451-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	149.5	149.9	150.1	150.0	150.0	150.0	149.9
115°	172.5	172.5	172.5	172.5	172.4	172.3	172.2
117.5°	195.8	195.8	195.7	195.5	195.2	194.9	194.7
120°	211.5	211.4	211.2	211.1	210.9	210.7	210.5
122.5°	227.2	226.9	226.8	226.5	226.2	226.0	225.7
125°	250.7	250.3	249.9	249.6	249.2	248.9	248.5
127.5°	273.8	273.3	272.9	272.5	272.1	271.6	271.3
130°	289.4	289.1	288.6	288.0	287.4	286.8	286.1
132.5°	304.4	304.0	303.5	303.1	302.6	302.1	301.6
135°	327.1	326.7	326.5	326.3	326.1	325.9	325.7
137.5°	349.1	348.7	348.3	347.9	347.7	347.3	347.0
140°	363.8	363.7	363.4	362.7	362.1	361.5	360.9
142.5°	377.4	377.3	377.0	376.6	376.0	375.6	375.1
145°	397.3	397.3	397.1	396.7	396.4	396.0	395.7
147.5°	416.3	416.3	416.1	415.5	414.9	414.4	413.8
150°	427.9	427.9	427.7	427.1	426.6	426.1	425.5
152.5°	438.7	438.9	438.7	438.3	437.7	437.3	436.8
155°	454.5	454.9	454.7	454.1	453.4	452.8	452.2
157.5°	467.9	468.2	468.1	467.7	467.2	466.6	466.2
160°	476.2	476.6	476.6	476.3	475.9	475.5	475.2
162.5°	483.9	484.4	484.3	483.8	483.1	482.6	482.0
165°	493.8	494.4	494.3	493.7	493.0	492.4	491.8
167.5°	501.8	502.3	502.3	501.8	501.2	500.7	500.1
170°	506.2	506.8	506.8	506.2	505.6	505.0	504.4
172.5°	509.5	510.1	510.1	509.4	508.8	508.2	507.6
175°	513.2	513.7	513.7	513.1	512.5	511.8	511.2
177.5°	514.8	515.1	515.1	514.6	514.2	513.6	513.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4

(END OF REPORT)