

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332405

Luminaire Tested: **S123RDIW-S340D1320U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332405
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5877.2 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	27	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	0.9
10°-20°	150.1	2.6
20°-30°	216.1	3.7
30°-40°	243.5	4.1
40°-50°	232.9	4.0
50°-60°	190.7	3.2
60°-70°	128.7	2.2
70°-80°	64.7	1.1
80°-90°	22.0	0.4
90°-100°	107.6	1.8
100°-110°	321.9	5.5
110°-120°	547.5	9.3
120°-130°	720.2	12.3
130°-140°	809.5	13.8
140°-150°	795.7	13.5
150°-160°	669.9	11.4
160°-170°	445.9	7.6
170°-180°	156.2	2.7
0°-30°	420.2	7.1
0°-40°	663.7	11.3
0°-60°	1087.3	18.5
0°-90°	1302.8	22.2
90°-120°	977.1	16.6
90°-150°	3302.5	56.2
90°-180°	4574.0	77.8
0°-180°	5877.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	1	14	31	36	39	6
95°	76	86	96	101	101	86
105°	292	295	306	306	309	313
115°	551	555	552	554	552	545
125°	807	810	808	803	798	719
135°	1047	1054	1053	1048	1045	806
145°	1270	1272	1276	1275	1270	793
155°	1454	1454	1455	1460	1451	669
165°	1584	1580	1580	1587	1578	446
175°	1647	1642	1642	1649	1641	156
180°	1651	1651	1651	1651	1651	



TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.2	8.9	8.5	8.2	7.9	8.1	8.8	9.6	10.3	11.1	11.2
90°	1.3	4.2	7.1	9.9	12.8	16.1	19.9	23.6	27.4	31.1	32.3
92.5°	31.4	33.3	35.3	37.3	39.2	41.3	43.4	45.5	47.7	49.8	50.7
95°	76.5	78.5	80.6	82.6	84.6	86.8	89.1	91.4	93.7	96.0	97.1
97.5°	135.9	137.4	138.9	140.4	141.9	143.5	145.2	146.8	148.5	150.2	151.5
100°	176.4	178.1	179.8	181.6	183.3	184.9	186.3	187.8	189.2	190.7	191.5
102.5°	223.1	224.1	225.2	226.2	227.2	228.7	230.6	232.5	234.4	236.3	237.2
105°	291.8	292.4	293.0	293.5	294.1	295.7	298.3	300.9	303.5	306.1	306.1
107.5°	371.7	372.1	372.4	372.8	373.1	373.8	374.8	375.9	376.9	377.9	378.9
110°	421.5	422.1	422.7	423.2	423.8	424.4	425.0	425.6	426.1	426.7	427.9



TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.4	473.7	474.1	474.4	474.8	475.0	475.1	475.2	475.4	475.5	476.9
115°	551.2	552.1	552.9	553.8	554.7	554.8	554.2	553.7	553.1	552.5	552.8
117.5°	629.6	630.1	630.7	631.3	631.9	631.8	631.0	630.3	629.5	628.8	628.7
120°	678.3	680.0	681.8	683.5	685.2	685.4	683.9	682.5	681.1	679.6	679.3
122.5°	729.2	730.4	731.7	733.0	734.2	734.5	733.7	733.0	732.2	731.5	730.7
125°	806.7	807.6	808.4	809.3	810.2	810.3	809.7	809.2	808.6	808.0	806.9
127.5°	878.3	880.2	882.0	883.8	885.7	886.3	885.7	885.0	884.4	883.8	882.1
130°	926.0	928.3	930.7	933.0	935.3	936.0	935.1	934.3	933.4	932.5	931.4
132.5°	973.8	976.1	978.4	980.7	983.0	983.8	983.2	982.6	981.9	981.3	979.9
135°	1046.7	1048.4	1050.1	1051.8	1053.6	1054.3	1054.0	1053.7	1053.4	1053.1	1052.0
137.5°	1114.1	1115.5	1117.0	1118.4	1119.9	1121.0	1121.7	1122.5	1123.2	1124.0	1122.7
140°	1160.8	1162.2	1163.7	1165.1	1166.6	1167.4	1167.7	1168.0	1168.3	1168.6	1168.3
142.5°	1203.3	1204.8	1206.2	1207.7	1209.1	1210.1	1210.6	1211.1	1211.6	1212.2	1211.9
145°	1269.7	1270.3	1270.9	1271.5	1272.0	1272.8	1273.6	1274.5	1275.4	1276.2	1275.9
147.5°	1327.8	1328.9	1329.9	1331.0	1332.0	1332.9	1333.7	1334.5	1335.3	1336.1	1336.1
150°	1368.3	1368.9	1369.5	1370.0	1370.6	1371.2	1371.8	1372.3	1372.9	1373.5	1373.5
152.5°	1401.5	1402.3	1403.1	1403.9	1404.7	1405.3	1405.7	1406.0	1406.4	1406.7	1407.2
155°	1453.9	1453.9	1453.9	1453.9	1453.9	1454.1	1454.3	1454.6	1454.9	1455.2	1456.4
157.5°	1498.5	1498.2	1497.8	1497.5	1497.1	1497.1	1497.3	1497.5	1497.8	1498.0	1499.2
160°	1526.5	1526.0	1525.4	1524.8	1524.2	1523.9	1523.9	1523.9	1523.9	1523.9	1525.4
162.5°	1551.4	1550.6	1549.8	1549.0	1548.2	1547.9	1548.2	1548.4	1548.6	1548.8	1550.3
165°	1583.6	1582.7	1581.9	1581.0	1580.2	1579.7	1579.7	1579.7	1579.7	1579.7	1581.4
167.5°	1609.3	1608.1	1607.0	1605.8	1604.7	1604.2	1604.4	1604.7	1604.9	1605.1	1606.9
170°	1623.8	1622.7	1621.5	1620.4	1619.2	1618.6	1618.6	1618.6	1618.6	1618.6	1620.6
172.5°	1635.2	1634.1	1632.9	1631.8	1630.6	1630.0	1630.0	1630.0	1630.0	1630.0	1631.8
175°	1647.2	1646.0	1644.9	1643.7	1642.5	1642.0	1642.0	1642.0	1642.0	1642.0	1643.7
177.5°	1652.1	1651.2	1650.2	1649.3	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.3
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	11.4	11.5	11.7	11.8	11.8	11.8	11.8	11.9
90°	33.4	34.6	35.7	36.6	37.2	37.8	38.3	38.9
92.5°	51.6	52.6	53.5	53.8	53.4	53.1	52.7	52.4
95°	98.3	99.4	100.6	101.2	101.2	101.2	101.2	101.2
97.5°	152.8	154.2	155.5	156.1	156.0	155.9	155.8	155.6
100°	192.4	193.2	194.1	194.8	195.4	196.0	196.6	197.1
102.5°	238.0	238.9	239.8	240.1	240.0	239.9	239.8	239.7
105°	306.1	306.1	306.1	306.4	307.0	307.5	308.1	308.7
107.5°	379.8	380.7	381.6	381.9	381.6	381.2	380.9	380.5
110°	429.0	430.2	431.3	431.6	431.0	430.5	429.9	429.3



TEST NUMBER: P332405

CATALOG NUMBER: S123RDIW-S340D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.2	479.6	481.0	481.6	481.5	481.4	481.3	481.2
115°	553.1	553.4	553.7	553.7	553.4	553.1	552.8	552.5
117.5°	628.7	628.6	628.5	628.1	627.3	626.5	625.7	624.9
120°	679.0	678.8	678.5	678.0	677.5	676.9	676.3	675.7
122.5°	730.0	729.2	728.5	727.7	726.9	726.1	725.3	724.5
125°	805.7	804.6	803.4	802.3	801.1	799.9	798.8	797.6
127.5°	880.5	878.9	877.3	875.8	874.5	873.2	871.9	870.5
130°	930.2	929.1	927.9	926.3	924.3	922.3	920.3	918.3
132.5°	978.5	977.1	975.8	974.3	972.7	971.2	969.6	968.1
135°	1050.8	1049.7	1048.5	1047.7	1047.1	1046.5	1045.9	1045.4
137.5°	1121.5	1120.3	1119.1	1118.0	1116.9	1115.8	1114.7	1113.6
140°	1168.0	1167.7	1167.4	1166.3	1164.3	1162.2	1160.2	1158.2
142.5°	1211.6	1211.3	1211.0	1210.1	1208.5	1207.0	1205.4	1203.9
145°	1275.6	1275.4	1275.1	1274.4	1273.2	1272.0	1270.9	1269.7
147.5°	1336.1	1336.1	1336.1	1335.3	1333.6	1331.8	1330.1	1328.4
150°	1373.5	1373.5	1373.5	1372.6	1370.9	1369.2	1367.4	1365.7
152.5°	1407.6	1408.1	1408.5	1408.0	1406.5	1405.0	1403.5	1402.0
155°	1457.5	1458.7	1459.8	1459.4	1457.4	1455.4	1453.3	1451.3
157.5°	1500.4	1501.6	1502.9	1502.6	1501.0	1499.4	1497.8	1496.2
160°	1526.8	1528.3	1529.7	1529.9	1528.7	1527.6	1526.4	1525.2
162.5°	1551.7	1553.2	1554.6	1554.4	1552.6	1550.7	1548.9	1547.0
165°	1583.2	1584.9	1586.6	1586.5	1584.5	1582.5	1580.4	1578.4
167.5°	1608.7	1610.5	1612.3	1612.3	1610.5	1608.7	1606.9	1605.1
170°	1622.7	1624.7	1626.7	1626.7	1624.7	1622.7	1620.6	1618.6
172.5°	1633.6	1635.4	1637.2	1637.1	1635.1	1633.0	1631.0	1629.0
175°	1645.4	1647.2	1648.9	1648.7	1646.7	1644.7	1642.7	1640.7
177.5°	1650.7	1652.1	1653.5	1653.4	1651.7	1650.1	1648.5	1646.9
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1

(END OF REPORT)