

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332453-940

Luminaire Tested: **S123RDIW-S1000D460U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332453-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4807.4 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.9
10°-20°	391.0	8.1
20°-30°	563.0	11.7
30°-40°	634.1	13.2
40°-50°	606.7	12.6
50°-60°	496.8	10.3
60°-70°	335.2	7.0
70°-80°	168.6	3.5
80°-90°	46.1	1.0
90°-100°	33.5	0.7
100°-110°	100.3	2.1
110°-120°	170.6	3.5
120°-130°	224.4	4.7
130°-140°	252.2	5.2
140°-150°	247.9	5.2
150°-160°	208.7	4.3
160°-170°	138.9	2.9
170°-180°	48.7	1.0
0°-30°	1094.5	22.8
0°-40°	1728.6	36.0
0°-60°	2832.1	58.9
0°-90°	3382.1	70.4
90°-120°	304.4	6.3
90°-150°	1029.0	21.4
90°-180°	1425.0	29.6
0°-180°	4807.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	0	4	10	11	12	5
95°	24	27	30	31	32	27
105°	91	92	95	95	96	97
115°	172	173	172	172	172	170
125°	251	252	252	250	248	224
135°	326	328	328	327	326	251
145°	396	396	398	397	396	247
155°	453	453	453	455	452	208
165°	493	492	492	494	492	139
175°	513	512	512	514	511	49
180°	514	514	514	514	514	



TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.4	21.2	19.0	16.8	14.6	13.6	13.8	14.1	14.4	14.5	14.4
90°	0.4	1.3	2.2	3.1	4.0	5.0	6.2	7.4	8.6	9.7	10.1
92.5°	9.8	10.4	11.0	11.6	12.2	12.8	13.6	14.2	14.9	15.5	15.8
95°	23.8	24.4	25.1	25.8	26.4	27.0	27.7	28.4	29.2	29.9	30.2
97.5°	42.4	42.8	43.2	43.8	44.2	44.7	45.2	45.7	46.3	46.8	47.2
100°	54.9	55.5	56.0	56.5	57.1	57.6	58.1	58.5	58.9	59.4	59.7
102.5°	69.5	69.8	70.2	70.4	70.8	71.2	71.9	72.4	73.0	73.7	73.9
105°	91.0	91.1	91.3	91.5	91.7	92.1	92.9	93.7	94.5	95.3	95.3
107.5°	115.8	115.9	116.0	116.1	116.3	116.5	116.8	117.1	117.4	117.8	118.1
110°	131.3	131.5	131.7	131.9	132.1	132.2	132.4	132.6	132.8	133.0	133.3



TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.5	147.6	147.8	147.8	147.9	148.0	148.0	148.1	148.1	148.1	148.6
115°	171.7	172.0	172.3	172.5	172.8	172.9	172.7	172.5	172.4	172.2	172.3
117.5°	196.2	196.4	196.5	196.7	196.9	196.8	196.6	196.4	196.2	195.9	195.9
120°	211.3	211.9	212.4	212.9	213.5	213.6	213.1	212.7	212.2	211.8	211.7
122.5°	227.2	227.6	228.0	228.4	228.7	228.8	228.6	228.4	228.2	227.9	227.7
125°	251.4	251.6	251.9	252.2	252.4	252.4	252.3	252.1	251.9	251.7	251.4
127.5°	273.7	274.2	274.8	275.4	276.0	276.2	276.0	275.7	275.5	275.4	274.8
130°	288.6	289.3	290.0	290.7	291.4	291.6	291.3	291.1	290.8	290.5	290.2
132.5°	303.4	304.1	304.9	305.6	306.3	306.6	306.3	306.1	305.9	305.8	305.3
135°	326.1	326.6	327.2	327.7	328.2	328.5	328.4	328.3	328.2	328.1	327.8
137.5°	347.1	347.6	348.0	348.5	348.9	349.3	349.5	349.7	350.0	350.2	349.8
140°	361.7	362.1	362.6	363.0	363.5	363.7	363.8	363.9	364.0	364.1	364.0
142.5°	375.0	375.4	375.9	376.3	376.7	377.0	377.2	377.4	377.6	377.6	377.6
145°	395.7	395.8	396.0	396.2	396.4	396.5	396.8	397.1	397.3	397.6	397.5
147.5°	413.8	414.0	414.4	414.6	415.0	415.3	415.5	415.8	416.1	416.3	416.3
150°	426.3	426.5	426.7	426.9	427.0	427.2	427.4	427.6	427.8	427.9	427.9
152.5°	436.7	436.9	437.2	437.4	437.7	437.8	437.9	438.1	438.2	438.3	438.5
155°	453.0	453.0	453.0	453.0	453.0	453.1	453.2	453.3	453.3	453.4	453.8
157.5°	466.9	466.8	466.7	466.5	466.5	466.5	466.5	466.6	466.6	466.7	467.1
160°	475.6	475.5	475.3	475.1	474.9	474.8	474.8	474.8	474.8	474.8	475.3
162.5°	483.4	483.1	482.9	482.6	482.4	482.3	482.3	482.4	482.5	482.6	483.0
165°	493.4	493.1	492.8	492.6	492.3	492.2	492.2	492.2	492.2	492.2	492.8
167.5°	501.4	501.1	500.7	500.3	500.0	499.8	499.9	500.0	500.1	500.1	500.7
170°	506.0	505.6	505.2	504.9	504.5	504.4	504.4	504.4	504.4	504.4	505.0
172.5°	509.5	509.2	508.8	508.5	508.0	507.8	507.8	507.8	507.8	507.8	508.5
175°	513.2	512.8	512.5	512.1	511.8	511.6	511.6	511.6	511.6	511.6	512.1
177.5°	514.8	514.4	514.2	513.9	513.6	513.4	513.4	513.4	513.4	513.4	513.9
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	14.3	14.1	14.0	13.8	13.6	13.5	13.3	13.1
90°	10.4	10.8	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.1	16.4	16.7	16.8	16.7	16.5	16.4	16.3
95°	30.6	30.9	31.3	31.5	31.5	31.5	31.5	31.5
97.5°	47.6	48.1	48.4	48.6	48.6	48.6	48.5	48.5
100°	59.9	60.2	60.5	60.7	60.9	61.1	61.3	61.4
102.5°	74.2	74.5	74.7	74.8	74.8	74.7	74.7	74.6
105°	95.3	95.3	95.3	95.4	95.7	95.9	96.0	96.2
107.5°	118.3	118.6	118.9	119.0	118.9	118.8	118.7	118.6
110°	133.7	134.0	134.4	134.5	134.3	134.1	133.9	133.8



TEST NUMBER: P332453-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.0	149.5	149.9	150.1	150.0	150.0	150.0	149.9
115°	172.4	172.5	172.5	172.5	172.5	172.4	172.3	172.2
117.5°	195.9	195.8	195.8	195.7	195.5	195.2	194.9	194.7
120°	211.6	211.5	211.4	211.2	211.1	210.9	210.7	210.5
122.5°	227.5	227.2	226.9	226.8	226.5	226.2	226.0	225.7
125°	251.0	250.7	250.3	249.9	249.6	249.2	248.9	248.5
127.5°	274.4	273.8	273.3	272.9	272.5	272.1	271.6	271.3
130°	289.8	289.4	289.1	288.6	288.0	287.4	286.8	286.1
132.5°	304.9	304.4	304.0	303.5	303.1	302.6	302.1	301.6
135°	327.4	327.1	326.7	326.5	326.3	326.1	325.9	325.7
137.5°	349.5	349.1	348.7	348.3	347.9	347.7	347.3	347.0
140°	363.9	363.8	363.7	363.4	362.7	362.1	361.5	360.9
142.5°	377.5	377.4	377.3	377.0	376.6	376.0	375.6	375.1
145°	397.4	397.3	397.3	397.1	396.7	396.4	396.0	395.7
147.5°	416.3	416.3	416.3	416.1	415.5	414.9	414.4	413.8
150°	427.9	427.9	427.9	427.7	427.1	426.6	426.1	425.5
152.5°	438.5	438.7	438.9	438.7	438.3	437.7	437.3	436.8
155°	454.1	454.5	454.9	454.7	454.1	453.4	452.8	452.2
157.5°	467.5	467.9	468.2	468.1	467.7	467.2	466.6	466.2
160°	475.7	476.2	476.6	476.6	476.3	475.9	475.5	475.2
162.5°	483.5	483.9	484.4	484.3	483.8	483.1	482.6	482.0
165°	493.3	493.8	494.4	494.3	493.7	493.0	492.4	491.8
167.5°	501.2	501.8	502.3	502.3	501.8	501.2	500.7	500.1
170°	505.6	506.2	506.8	506.8	506.2	505.6	505.0	504.4
172.5°	509.0	509.5	510.1	510.1	509.4	508.8	508.2	507.6
175°	512.6	513.2	513.7	513.7	513.1	512.5	511.8	511.2
177.5°	514.3	514.8	515.1	515.1	514.6	514.2	513.6	513.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4

(END OF REPORT)