

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332454-940

Luminaire Tested: **S123RDIW-S1000D755U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332454-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D755U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6225.4 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	92	84	79	74	85	79	74	70	69	65	61	59	56	54	50	48	46	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	37
4	77	67	59	53	72	63	56	51	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	30	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	45	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	26	23	20	18
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.4	2.2
10°-20°	435.5	7.0
20°-30°	684.2	11.0
30°-40°	713.8	11.5
40°-50°	610.9	9.8
50°-60°	465.6	7.5
60°-70°	298.4	4.8
70°-80°	143.6	2.3
80°-90°	40.5	0.7
90°-100°	32.1	0.5
100°-110°	153.0	2.5
110°-120°	367.6	5.9
120°-130°	468.1	7.5
130°-140°	500.2	8.0
140°-150°	467.7	7.5
150°-160°	377.3	6.1
160°-170°	243.5	3.9
170°-180°	83.9	1.3
0°-30°	1259.1	20.2
0°-40°	1973.0	31.7
0°-60°	3049.5	49.0
0°-90°	3532.0	56.7
90°-120°	552.8	8.9
90°-150°	1988.7	31.9
90°-180°	2693.0	43.3
0°-180°	6225.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	20	1	20	1	20	10
95°	25	40	25	40	25	21
105°	29	196	29	196	29	66
115°	386	367	386	367	386	357
125°	528	517	528	517	528	471
135°	650	644	650	644	650	501
145°	750	743	750	743	750	468
155°	817	818	817	818	817	377
165°	861	863	861	863	861	243
175°	880	883	880	883	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	8.8	9.7	8.6	9.1	9.0	9.5	9.4	9.2	10.1	9.5	9.5
90°	19.7	19.4	19.1	18.8	18.5	18.1	17.5	16.9	16.3	15.8	13.8
92.5°	21.8	21.6	21.4	21.2	21.0	20.5	19.6	18.6	17.7	16.8	15.3
95°	25.0	25.0	25.0	25.0	25.0	24.4	23.4	22.4	21.4	20.3	18.7
97.5°	27.0	26.9	26.8	26.6	26.5	25.8	24.6	23.5	22.3	21.1	31.7
100°	27.6	27.4	27.3	27.1	27.0	26.3	25.1	24.0	22.8	21.7	44.4
102.5°	28.1	27.8	27.6	27.3	27.0	28.7	32.4	35.9	39.6	43.2	68.0
105°	28.9	28.6	28.3	28.0	27.7	40.5	66.3	92.1	117.9	143.7	156.9
107.5°	90.7	110.1	129.6	149.0	168.5	187.7	206.6	225.5	244.4	263.4	261.4
110°	180.5	201.3	222.1	243.0	263.9	276.7	281.5	286.3	291.1	296.0	294.4



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	309.6	314.0	318.4	322.8	327.2	329.4	329.3	329.2	329.1	329.0	327.4
115°	385.8	385.2	384.7	384.1	383.5	382.5	381.0	379.6	378.1	376.7	375.3
117.5°	428.6	428.5	428.4	428.3	428.1	427.5	426.3	425.2	424.0	422.8	422.1
120°	458.0	458.0	458.0	458.0	458.0	457.4	456.3	455.1	454.0	452.7	452.4
122.5°	486.9	486.8	486.6	486.5	486.4	486.0	485.1	484.3	483.5	482.7	482.1
125°	527.5	527.3	527.0	526.7	526.4	526.1	525.8	525.5	525.2	525.0	524.3
127.5°	566.7	566.9	567.2	567.6	567.8	567.8	567.3	566.9	566.3	565.9	565.2
130°	591.8	592.2	592.5	592.7	593.1	592.9	592.3	591.7	591.1	590.6	590.0
132.5°	614.9	615.4	615.8	616.2	616.6	616.5	615.9	615.4	614.7	614.2	613.7
135°	650.2	650.7	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2	649.7
137.5°	683.5	683.8	684.0	684.4	684.7	684.5	683.8	683.1	682.3	681.6	681.4
140°	703.4	703.7	704.0	704.3	704.6	704.5	703.8	703.3	702.7	702.1	701.7
142.5°	721.8	722.2	722.6	723.0	723.4	723.4	722.9	722.5	722.0	721.6	721.1
145°	750.0	750.0	750.0	750.0	750.0	749.8	749.6	749.3	748.9	748.7	748.4
147.5°	771.0	771.7	772.3	773.0	773.6	773.9	773.6	773.3	773.0	772.7	772.4
150°	786.8	787.2	787.6	788.1	788.5	788.5	788.3	788.0	787.7	787.4	787.1
152.5°	799.3	800.0	800.7	801.4	802.0	802.1	801.6	801.0	800.5	800.0	799.9
155°	816.9	817.8	818.7	819.6	820.5	820.6	819.7	819.0	818.3	817.6	817.4
157.5°	831.8	832.9	834.0	835.2	836.3	836.4	835.5	834.7	833.8	832.9	833.1
160°	841.2	842.2	843.3	844.3	845.3	845.3	844.5	843.6	842.8	841.9	842.0
162.5°	850.2	851.0	851.9	852.8	853.7	853.7	852.7	851.8	850.8	849.7	849.9
165°	860.9	861.9	862.9	864.0	865.0	864.9	863.7	862.6	861.4	860.2	860.4
167.5°	868.6	869.8	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6	868.6
170°	873.3	874.5	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3	873.3
172.5°	876.0	877.3	878.6	879.9	881.1	881.2	880.0	878.9	877.7	876.6	876.4
175°	879.9	881.1	882.3	883.4	884.6	884.7	883.7	882.6	881.6	880.6	880.5
177.5°	881.1	882.3	883.4	884.6	885.7	885.9	884.9	884.0	883.1	882.2	882.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	10.2	9.3	9.9	9.5	10.7	10.9	13.6	15.7	16.4	14.8	15.1
90°	11.9	10.1	8.2	6.5	5.0	3.6	2.1	0.6	2.1	3.6	5.0
92.5°	13.9	12.5	11.1	10.6	11.0	11.4	11.8	12.2	11.8	11.4	11.0
95°	17.1	15.5	13.9	16.1	22.1	28.1	34.1	40.0	34.1	28.1	22.1
97.5°	42.1	52.6	63.1	69.7	72.4	75.1	77.8	80.4	77.8	75.1	72.4
100°	67.1	89.9	112.6	122.5	119.7	116.7	113.8	110.9	113.8	116.7	119.7
102.5°	92.8	117.7	142.6	153.9	151.9	149.7	147.7	145.5	147.7	149.7	151.9
105°	170.0	183.1	196.2	202.0	200.4	198.8	197.2	195.6	197.2	198.8	200.4
107.5°	259.2	257.2	255.1	253.4	252.2	250.8	249.6	248.3	249.6	250.8	252.2
110°	292.7	291.1	289.5	288.1	287.0	285.8	284.6	283.5	284.6	285.8	287.0





TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.8	324.2	322.6	321.3	320.2	319.1	318.1	317.1	318.1	319.1	320.2
115°	374.0	372.7	371.4	370.3	369.4	368.5	367.7	366.8	367.7	368.5	369.4
117.5°	421.5	420.8	420.2	419.3	418.2	417.1	416.1	415.0	416.1	417.1	418.2
120°	451.9	451.5	451.0	450.1	448.8	447.5	446.2	444.9	446.2	447.5	448.8
122.5°	481.6	481.0	480.5	479.7	478.6	477.5	476.4	475.4	476.4	477.5	478.6
125°	523.8	523.2	522.6	521.7	520.6	519.4	518.3	517.1	518.3	519.4	520.6
127.5°	564.5	563.8	563.1	562.1	561.0	559.8	558.7	557.5	558.7	559.8	561.0
130°	589.4	588.8	588.3	587.4	586.2	585.1	583.9	582.6	583.9	585.1	586.2
132.5°	613.2	612.8	612.3	611.5	610.3	609.1	608.0	606.8	608.0	609.1	610.3
135°	649.1	648.5	647.9	647.2	646.3	645.4	644.6	643.7	644.6	645.4	646.3
137.5°	681.0	680.6	680.4	679.7	678.5	677.4	676.3	675.2	676.3	677.4	678.5
140°	701.2	700.8	700.3	699.7	698.8	697.9	697.1	696.2	697.1	697.9	698.8
142.5°	720.7	720.2	719.8	719.2	718.3	717.4	716.5	715.6	716.5	717.4	718.3
145°	748.1	747.8	747.5	746.9	745.8	744.8	743.8	742.8	743.8	744.8	745.8
147.5°	772.1	771.9	771.5	771.1	770.3	769.7	769.0	768.4	769.0	769.7	770.3
150°	786.8	786.6	786.2	785.9	785.4	785.0	784.5	784.2	784.5	785.0	785.4
152.5°	799.7	799.5	799.3	799.2	798.9	798.7	798.5	798.3	798.5	798.7	798.9
155°	817.3	817.2	817.0	817.1	817.3	817.7	818.0	818.2	818.0	817.7	817.3
157.5°	833.2	833.4	833.6	833.7	833.7	833.7	833.7	833.7	833.7	833.7	833.7
160°	842.1	842.3	842.5	842.6	842.8	842.9	843.0	843.2	843.0	842.9	842.8
162.5°	850.1	850.2	850.3	850.6	851.0	851.3	851.8	852.1	851.8	851.3	851.0
165°	860.5	860.7	860.9	861.1	861.6	862.0	862.5	862.9	862.5	862.0	861.6
167.5°	868.6	868.6	868.6	869.0	869.5	870.1	870.7	871.3	870.7	870.1	869.5
170°	873.3	873.3	873.3	873.7	874.2	874.9	875.4	876.0	875.4	874.9	874.2
172.5°	876.3	876.2	876.0	876.4	877.1	877.7	878.4	879.1	878.4	877.7	877.1
175°	880.3	880.1	880.0	880.3	881.0	881.7	882.4	883.2	882.4	881.7	881.0
177.5°	881.9	881.8	881.7	881.9	882.5	883.1	883.7	884.2	883.7	883.1	882.5
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	14.9	16.7	17.6	18.4	19.3	19.2	19.8	19.9	20.5	20.6	20.7
90°	6.5	8.2	10.1	11.9	13.8	15.8	16.3	16.9	17.5	18.1	18.5
92.5°	10.6	11.1	12.5	13.9	15.3	16.8	17.7	18.6	19.6	20.5	21.0
95°	16.1	13.9	15.5	17.1	18.7	20.3	21.4	22.4	23.4	24.4	25.0
97.5°	69.7	63.1	52.6	42.1	31.7	21.1	22.3	23.5	24.6	25.8	26.5
100°	122.5	112.6	89.9	67.1	44.4	21.7	22.8	24.0	25.1	26.3	27.0
102.5°	153.9	142.6	117.7	92.8	68.0	43.2	39.6	35.9	32.4	28.7	27.0
105°	202.0	196.2	183.1	170.0	156.9	143.7	117.9	92.1	66.3	40.5	27.7
107.5°	253.4	255.1	257.2	259.2	261.4	263.4	244.4	225.5	206.6	187.7	168.5
110°	288.1	289.5	291.1	292.7	294.4	296.0	291.1	286.3	281.5	276.7	263.9



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	321.3	322.6	324.2	325.8	327.4	329.0	329.1	329.2	329.3	329.4	327.2
115°	370.3	371.4	372.7	374.0	375.3	376.7	378.1	379.6	381.0	382.5	383.5
117.5°	419.3	420.2	420.8	421.5	422.1	422.8	424.0	425.2	426.3	427.5	428.1
120°	450.1	451.0	451.5	451.9	452.4	452.7	454.0	455.1	456.3	457.4	458.0
122.5°	479.7	480.5	481.0	481.6	482.1	482.7	483.5	484.3	485.1	486.0	486.4
125°	521.7	522.6	523.2	523.8	524.3	525.0	525.2	525.5	525.8	526.1	526.4
127.5°	562.1	563.1	563.8	564.5	565.2	565.9	566.3	566.9	567.3	567.8	567.8
130°	587.4	588.3	588.8	589.4	590.0	590.6	591.1	591.7	592.3	592.9	593.1
132.5°	611.5	612.3	612.8	613.2	613.7	614.2	614.7	615.4	615.9	616.5	616.6
135°	647.2	647.9	648.5	649.1	649.7	650.2	650.7	651.1	651.6	652.0	652.0
137.5°	679.7	680.4	680.6	681.0	681.4	681.6	682.3	683.1	683.8	684.5	684.7
140°	699.7	700.3	700.8	701.2	701.7	702.1	702.7	703.3	703.8	704.5	704.6
142.5°	719.2	719.8	720.2	720.7	721.1	721.6	722.0	722.5	722.9	723.4	723.4
145°	746.9	747.5	747.8	748.1	748.4	748.7	748.9	749.3	749.6	749.8	750.0
147.5°	771.1	771.5	771.9	772.1	772.4	772.7	773.0	773.3	773.6	773.9	773.6
150°	785.9	786.2	786.6	786.8	787.1	787.4	787.7	788.0	788.3	788.5	788.5
152.5°	799.2	799.3	799.5	799.7	799.9	800.0	800.5	801.0	801.6	802.1	802.0
155°	817.1	817.0	817.2	817.3	817.4	817.6	818.3	819.0	819.7	820.6	820.5
157.5°	833.7	833.6	833.4	833.2	833.1	832.9	833.8	834.7	835.5	836.4	836.3
160°	842.6	842.5	842.3	842.1	842.0	841.9	842.8	843.6	844.5	845.3	845.3
162.5°	850.6	850.3	850.2	850.1	849.9	849.7	850.8	851.8	852.7	853.7	853.7
165°	861.1	860.9	860.7	860.5	860.4	860.2	861.4	862.6	863.7	864.9	865.0
167.5°	869.0	868.6	868.6	868.6	868.6	868.6	869.8	870.9	872.2	873.3	873.3
170°	873.7	873.3	873.3	873.3	873.3	873.3	874.5	875.7	876.9	878.1	878.1
172.5°	876.4	876.0	876.2	876.3	876.4	876.6	877.7	878.9	880.0	881.2	881.1
175°	880.3	880.0	880.1	880.3	880.5	880.6	881.6	882.6	883.7	884.7	884.6
177.5°	881.9	881.7	881.8	881.9	882.1	882.2	883.1	884.0	884.9	885.9	885.7
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	21.8	20.8	20.9	21.4	20.9	20.8	21.8	20.7	20.6	20.5	19.9
90°	18.8	19.1	19.4	19.7	19.4	19.1	18.8	18.5	18.1	17.5	16.9
92.5°	21.2	21.4	21.6	21.8	21.6	21.4	21.2	21.0	20.5	19.6	18.6
95°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	24.4	23.4	22.4
97.5°	26.6	26.8	26.9	27.0	26.9	26.8	26.6	26.5	25.8	24.6	23.5
100°	27.1	27.3	27.4	27.6	27.4	27.3	27.1	27.0	26.3	25.1	24.0
102.5°	27.3	27.6	27.8	28.1	27.8	27.6	27.3	27.0	28.7	32.4	35.9
105°	28.0	28.3	28.6	28.9	28.6	28.3	28.0	27.7	40.5	66.3	92.1
107.5°	149.0	129.6	110.1	90.7	110.1	129.6	149.0	168.5	187.7	206.6	225.5
110°	243.0	222.1	201.3	180.5	201.3	222.1	243.0	263.9	276.7	281.5	286.3



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	322.8	318.4	314.0	309.6	314.0	318.4	322.8	327.2	329.4	329.3	329.2
115°	384.1	384.7	385.2	385.8	385.2	384.7	384.1	383.5	382.5	381.0	379.6
117.5°	428.3	428.4	428.5	428.6	428.5	428.4	428.3	428.1	427.5	426.3	425.2
120°	458.0	458.0	458.0	458.0	458.0	458.0	458.0	458.0	457.4	456.3	455.1
122.5°	486.5	486.6	486.8	486.9	486.8	486.6	486.5	486.4	486.0	485.1	484.3
125°	526.7	527.0	527.3	527.5	527.3	527.0	526.7	526.4	526.1	525.8	525.5
127.5°	567.6	567.2	566.9	566.7	566.9	567.2	567.6	567.8	567.8	567.3	566.9
130°	592.7	592.5	592.2	591.8	592.2	592.5	592.7	593.1	592.9	592.3	591.7
132.5°	616.2	615.8	615.4	614.9	615.4	615.8	616.2	616.6	616.5	615.9	615.4
135°	651.6	651.1	650.7	650.2	650.7	651.1	651.6	652.0	652.0	651.6	651.1
137.5°	684.4	684.0	683.8	683.5	683.8	684.0	684.4	684.7	684.5	683.8	683.1
140°	704.3	704.0	703.7	703.4	703.7	704.0	704.3	704.6	704.5	703.8	703.3
142.5°	723.0	722.6	722.2	721.8	722.2	722.6	723.0	723.4	723.4	722.9	722.5
145°	750.0	750.0	750.0	750.0	750.0	750.0	750.0	750.0	749.8	749.6	749.3
147.5°	773.0	772.3	771.7	771.0	771.7	772.3	773.0	773.6	773.9	773.6	773.3
150°	788.1	787.6	787.2	786.8	787.2	787.6	788.1	788.5	788.5	788.3	788.0
152.5°	801.4	800.7	800.0	799.3	800.0	800.7	801.4	802.0	802.1	801.6	801.0
155°	819.6	818.7	817.8	816.9	817.8	818.7	819.6	820.5	820.6	819.7	819.0
157.5°	835.2	834.0	832.9	831.8	832.9	834.0	835.2	836.3	836.4	835.5	834.7
160°	844.3	843.3	842.2	841.2	842.2	843.3	844.3	845.3	845.3	844.5	843.6
162.5°	852.8	851.9	851.0	850.2	851.0	851.9	852.8	853.7	853.7	852.7	851.8
165°	864.0	862.9	861.9	860.9	861.9	862.9	864.0	865.0	864.9	863.7	862.6
167.5°	872.2	870.9	869.8	868.6	869.8	870.9	872.2	873.3	873.3	872.2	870.9
170°	876.9	875.7	874.5	873.3	874.5	875.7	876.9	878.1	878.1	876.9	875.7
172.5°	879.9	878.6	877.3	876.0	877.3	878.6	879.9	881.1	881.2	880.0	878.9
175°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	884.7	883.7	882.6
177.5°	884.6	883.4	882.3	881.1	882.3	883.4	884.6	885.7	885.9	884.9	884.0
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	19.8	19.2	19.3	18.4	17.6	16.7	14.9	15.1	14.8	16.4	15.7
90°	16.3	15.8	13.8	11.9	10.1	8.2	6.5	5.0	3.6	2.1	0.6
92.5°	17.7	16.8	15.3	13.9	12.5	11.1	10.6	11.0	11.4	11.8	12.2
95°	21.4	20.3	18.7	17.1	15.5	13.9	16.1	22.1	28.1	34.1	40.0
97.5°	22.3	21.1	31.7	42.1	52.6	63.1	69.7	72.4	75.1	77.8	80.4
100°	22.8	21.7	44.4	67.1	89.9	112.6	122.5	119.7	116.7	113.8	110.9
102.5°	39.6	43.2	68.0	92.8	117.7	142.6	153.9	151.9	149.7	147.7	145.5
105°	117.9	143.7	156.9	170.0	183.1	196.2	202.0	200.4	198.8	197.2	195.6
107.5°	244.4	263.4	261.4	259.2	257.2	255.1	253.4	252.2	250.8	249.6	248.3
110°	291.1	296.0	294.4	292.7	291.1	289.5	288.1	287.0	285.8	284.6	283.5



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	329.0	327.4	325.8	324.2	322.6	321.3	320.2	319.1	318.1	317.1
115°	378.1	376.7	375.3	374.0	372.7	371.4	370.3	369.4	368.5	367.7	366.8
117.5°	424.0	422.8	422.1	421.5	420.8	420.2	419.3	418.2	417.1	416.1	415.0
120°	454.0	452.7	452.4	451.9	451.5	451.0	450.1	448.8	447.5	446.2	444.9
122.5°	483.5	482.7	482.1	481.6	481.0	480.5	479.7	478.6	477.5	476.4	475.4
125°	525.2	525.0	524.3	523.8	523.2	522.6	521.7	520.6	519.4	518.3	517.1
127.5°	566.3	565.9	565.2	564.5	563.8	563.1	562.1	561.0	559.8	558.7	557.5
130°	591.1	590.6	590.0	589.4	588.8	588.3	587.4	586.2	585.1	583.9	582.6
132.5°	614.7	614.2	613.7	613.2	612.8	612.3	611.5	610.3	609.1	608.0	606.8
135°	650.7	650.2	649.7	649.1	648.5	647.9	647.2	646.3	645.4	644.6	643.7
137.5°	682.3	681.6	681.4	681.0	680.6	680.4	679.7	678.5	677.4	676.3	675.2
140°	702.7	702.1	701.7	701.2	700.8	700.3	699.7	698.8	697.9	697.1	696.2
142.5°	722.0	721.6	721.1	720.7	720.2	719.8	719.2	718.3	717.4	716.5	715.6
145°	748.9	748.7	748.4	748.1	747.8	747.5	746.9	745.8	744.8	743.8	742.8
147.5°	773.0	772.7	772.4	772.1	771.9	771.5	771.1	770.3	769.7	769.0	768.4
150°	787.7	787.4	787.1	786.8	786.6	786.2	785.9	785.4	785.0	784.5	784.2
152.5°	800.5	800.0	799.9	799.7	799.5	799.3	799.2	798.9	798.7	798.5	798.3
155°	818.3	817.6	817.4	817.3	817.2	817.0	817.1	817.3	817.7	818.0	818.2
157.5°	833.8	832.9	833.1	833.2	833.4	833.6	833.7	833.7	833.7	833.7	833.7
160°	842.8	841.9	842.0	842.1	842.3	842.5	842.6	842.8	842.9	843.0	843.2
162.5°	850.8	849.7	849.9	850.1	850.2	850.3	850.6	851.0	851.3	851.8	852.1
165°	861.4	860.2	860.4	860.5	860.7	860.9	861.1	861.6	862.0	862.5	862.9
167.5°	869.8	868.6	868.6	868.6	868.6	868.6	869.0	869.5	870.1	870.7	871.3
170°	874.5	873.3	873.3	873.3	873.3	873.3	873.7	874.2	874.9	875.4	876.0
172.5°	877.7	876.6	876.4	876.3	876.2	876.0	876.4	877.1	877.7	878.4	879.1
175°	881.6	880.6	880.5	880.3	880.1	880.0	880.3	881.0	881.7	882.4	883.2
177.5°	883.1	882.2	882.1	881.9	881.8	881.7	881.9	882.5	883.1	883.7	884.2
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.6	10.9	10.7	9.5	9.9	9.3	10.2	9.5	9.5	10.1	9.2
90°	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3	16.9
92.5°	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7	18.6
95°	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4	22.4
97.5°	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3	23.5
100°	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8	24.0
102.5°	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6	35.9
105°	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9	92.1
107.5°	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4	225.5
110°	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1	286.3





TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1	329.2
115°	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1	379.6
117.5°	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0	425.2
120°	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0	455.1
122.5°	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5	484.3
125°	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2	525.5
127.5°	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3	566.9
130°	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1	591.7
132.5°	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7	615.4
135°	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7	651.1
137.5°	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3	683.1
140°	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7	703.3
142.5°	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0	722.5
145°	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9	749.3
147.5°	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0	773.3
150°	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7	788.0
152.5°	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5	801.0
155°	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3	819.0
157.5°	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8	834.7
160°	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8	843.6
162.5°	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8	851.8
165°	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4	862.6
167.5°	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8	870.9
170°	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5	875.7
172.5°	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7	878.9
175°	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6	882.6
177.5°	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1	884.0
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	9.4	9.5	9.0	9.1	8.6	9.7	8.8
90°	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	281.5	276.7	263.9	243.0	222.1	201.3	180.5



TEST NUMBER: P332454-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)