

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332456-940

Luminaire Tested: **S123RDIW-S1000D755U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332456-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D755U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6076.5 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	84	78	72	84	78	73	68	67	63	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	57	60	55	51	51	48	45	43	41	38	35
4	76	66	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	22	19	17
10	49	37	29	25	45	34	28	23	31	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.3
10°-20°	391.0	6.4
20°-30°	563.0	9.3
30°-40°	634.1	10.4
40°-50°	606.7	10.0
50°-60°	496.8	8.2
60°-70°	335.2	5.5
70°-80°	168.6	2.8
80°-90°	47.1	0.8
90°-100°	32.1	0.5
100°-110°	153.0	2.5
110°-120°	367.6	6.0
120°-130°	468.1	7.7
130°-140°	500.2	8.2
140°-150°	467.7	7.7
150°-160°	377.3	6.2
160°-170°	243.5	4.0
170°-180°	83.9	1.4
0°-30°	1094.5	18.0
0°-40°	1728.6	28.4
0°-60°	2832.1	46.6
0°-90°	3383.1	55.7
90°-120°	552.8	9.1
90°-150°	1988.7	32.7
90°-180°	2693.0	44.3
0°-180°	6076.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	7	16	18	20	5
95°	40	15	20	25	25	49
105°	196	199	144	34	29	207
115°	367	371	377	383	386	362
125°	517	522	525	526	528	462
135°	644	648	650	652	650	495
145°	743	747	749	750	750	465
155°	818	817	818	821	817	377
165°	863	861	860	865	861	244
175°	883	880	881	885	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.3	19.3	17.2	15.1	14.3	14.6	15.0	15.4	15.8	15.7
90°	0.6	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3
92.5°	12.2	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7
95°	40.0	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4
97.5°	80.4	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3
100°	110.9	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8
102.5°	145.5	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6
105°	195.6	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9
107.5°	248.3	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4
110°	283.5	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1



TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.1	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1
115°	366.8	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1
117.5°	415.0	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0
120°	444.9	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0
122.5°	475.4	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5
125°	517.1	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2
127.5°	557.5	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3
130°	582.6	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1
132.5°	606.8	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7
135°	643.7	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7
137.5°	675.2	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3
140°	696.2	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7
142.5°	715.6	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0
145°	742.8	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9
147.5°	768.4	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0
150°	784.2	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7
152.5°	798.3	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5
155°	818.2	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3
157.5°	833.7	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8
160°	843.2	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8
162.5°	852.1	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8
165°	862.9	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4
167.5°	871.3	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8
170°	876.0	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5
172.5°	879.1	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7
175°	883.2	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6
177.5°	884.2	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	15.6	15.5	15.3	15.2	15.1	14.9	14.8	14.6
90°	16.9	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	18.6	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	22.4	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	23.5	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	24.0	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	35.9	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	92.1	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	225.5	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	286.3	281.5	276.7	263.9	243.0	222.1	201.3	180.5



TEST NUMBER: P332456-940

CATALOG NUMBER: S123RDIW-S1000D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.2	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	379.6	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	425.2	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	455.1	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	484.3	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.5	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	566.9	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	591.7	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.4	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.1	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.3	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.5	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.3	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.3	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.0	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.0	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.0	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	834.7	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	843.6	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	851.8	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	862.6	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	878.9	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	882.6	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.0	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)