

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332480-940

Luminaire Tested: **S123RDIW-S1165D1030U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332480-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1030U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7584.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31
5	69	58	50	44	64	54	47	42	46	41	37	40	35	32	33	30	27
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.1
10°-20°	451.6	6.0
20°-30°	650.2	8.6
30°-40°	732.4	9.7
40°-50°	700.7	9.2
50°-60°	573.8	7.6
60°-70°	387.1	5.1
70°-80°	194.8	2.6
80°-90°	54.9	0.7
90°-100°	43.8	0.6
100°-110°	208.9	2.8
110°-120°	501.7	6.6
120°-130°	638.9	8.4
130°-140°	682.7	9.0
140°-150°	638.4	8.4
150°-160°	514.9	6.8
160°-170°	332.3	4.4
170°-180°	114.5	1.5
0°-30°	1264.1	16.7
0°-40°	1996.5	26.3
0°-60°	3270.9	43.1
0°-90°	3907.7	51.5
90°-120°	754.5	9.9
90°-150°	2714.5	35.8
90°-180°	3676.0	48.5
0°-180°	7584.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	1	10	22	25	27	6
95°	55	20	28	34	34	68
105°	267	272	196	46	39	283
115°	501	506	514	523	527	494
125°	706	713	716	718	720	630
135°	879	884	888	890	888	676
145°	1014	1020	1022	1024	1024	634
155°	1117	1115	1116	1120	1115	514
165°	1178	1175	1174	1181	1175	333
175°	1206	1201	1202	1208	1201	115
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.1	24.8	22.4	20.1	17.7	16.8	17.3	17.8	18.4	18.9	18.8
90°	0.9	2.9	4.9	6.9	8.8	11.1	13.7	16.3	18.9	21.5	22.3
92.5°	16.7	16.1	15.5	15.0	14.4	15.2	17.1	19.0	21.0	22.9	24.2
95°	54.7	46.5	38.3	30.1	22.0	19.0	21.2	23.4	25.6	27.7	29.2
97.5°	109.8	106.1	102.5	98.8	95.1	86.1	71.9	57.5	43.2	28.8	30.4
100°	151.3	155.3	159.3	163.3	167.3	153.7	122.7	91.7	60.6	29.5	31.1
102.5°	198.7	201.5	204.4	207.2	210.1	194.6	160.7	126.8	92.8	58.9	54.0
105°	266.9	269.1	271.3	273.5	275.6	267.8	249.9	231.9	214.1	196.2	161.0
107.5°	338.9	340.6	342.4	344.2	345.9	348.2	351.1	353.8	356.7	359.5	333.7
110°	386.9	388.5	390.1	391.7	393.2	395.2	397.3	399.6	401.7	403.9	397.3



TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	434.2	435.6	437.1	438.5	440.3	442.5	444.7	446.9	449.1	449.2
115°	500.7	501.9	503.0	504.3	505.4	506.9	508.7	510.5	512.3	514.1	516.1
117.5°	566.4	567.8	569.4	570.8	572.3	573.5	574.4	575.3	576.2	577.1	578.7
120°	607.3	609.0	610.8	612.6	614.4	615.6	616.2	616.8	617.4	618.0	619.6
122.5°	648.8	650.2	651.8	653.2	654.7	655.8	656.6	657.3	658.1	658.8	660.0
125°	705.8	707.4	708.9	710.5	712.1	713.4	714.1	714.9	715.7	716.5	716.9
127.5°	760.9	762.5	764.1	765.7	767.3	768.6	769.5	770.5	771.4	772.4	773.0
130°	795.3	796.9	798.5	800.1	801.7	802.9	803.7	804.5	805.3	806.1	806.9
132.5°	828.3	829.9	831.4	833.0	834.6	835.8	836.4	837.0	837.7	838.3	839.1
135°	878.6	879.9	881.0	882.2	883.4	884.4	885.2	886.0	886.8	887.6	888.1
137.5°	921.6	923.1	924.6	926.1	927.6	928.6	929.1	929.5	930.0	930.4	931.3
140°	950.3	951.5	952.7	953.9	955.0	955.9	956.5	957.2	957.7	958.3	959.1
142.5°	976.8	977.9	979.2	980.3	981.6	982.5	983.0	983.6	984.3	984.8	985.5
145°	1013.9	1015.2	1016.6	1018.1	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3
147.5°	1048.8	1049.7	1050.6	1051.5	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1
150°	1070.3	1070.9	1071.5	1072.1	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1
152.5°	1089.7	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7
155°	1116.9	1116.4	1116.1	1115.7	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0
157.5°	1138.0	1138.0	1137.9	1137.9	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1
160°	1150.9	1150.7	1150.5	1150.3	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3
162.5°	1163.1	1162.5	1162.1	1161.5	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2
165°	1177.8	1177.1	1176.6	1176.0	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8
167.5°	1189.2	1188.5	1187.7	1186.9	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2
170°	1195.7	1194.9	1194.1	1193.3	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6
172.5°	1200.0	1199.0	1198.1	1197.1	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0
175°	1205.5	1204.5	1203.5	1202.6	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4
177.5°	1206.9	1206.1	1205.4	1204.6	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	18.7	18.6	18.5	18.4	18.2	18.0	17.8	17.7
90°	23.1	23.9	24.7	25.2	25.7	26.0	26.5	26.8
92.5°	25.5	26.8	28.0	28.8	29.0	29.2	29.5	29.7
95°	30.6	31.9	33.3	34.1	34.1	34.1	34.1	34.1
97.5°	32.0	33.6	35.2	36.1	36.3	36.5	36.7	36.9
100°	32.7	34.3	35.9	36.8	37.0	37.2	37.5	37.6
102.5°	49.0	44.1	39.1	36.9	37.3	37.6	38.0	38.3
105°	125.7	90.4	55.2	37.8	38.3	38.6	39.0	39.4
107.5°	307.8	282.0	256.2	230.0	203.4	176.9	150.3	123.8
110°	390.8	384.2	377.6	360.2	331.7	303.2	274.7	246.3



TEST NUMBER: P332480-940

CATALOG NUMBER: S123RDIW-S1165D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	449.3	449.4	449.5	446.6	440.6	434.6	428.6	422.6
115°	518.1	520.0	522.1	523.4	524.2	525.0	525.8	526.6
117.5°	580.3	581.9	583.5	584.4	584.5	584.7	584.9	585.1
120°	621.2	622.8	624.4	625.2	625.2	625.2	625.2	625.2
122.5°	661.0	662.2	663.3	664.0	664.1	664.2	664.4	664.6
125°	717.3	717.7	718.1	718.5	718.9	719.3	719.7	720.1
127.5°	773.6	774.3	775.0	775.1	774.6	774.3	773.9	773.5
130°	807.7	808.4	809.2	809.5	809.0	808.7	808.2	807.9
132.5°	839.9	840.7	841.5	841.6	841.1	840.5	840.0	839.4
135°	888.8	889.4	889.9	889.9	889.4	888.8	888.1	887.6
137.5°	932.3	933.3	934.2	934.5	934.1	933.7	933.3	932.9
140°	959.9	960.7	961.5	961.7	961.4	960.9	960.6	960.1
142.5°	986.1	986.8	987.4	987.4	986.9	986.3	985.8	985.2
145°	1022.7	1023.1	1023.5	1023.7	1023.7	1023.7	1023.7	1023.7
147.5°	1055.5	1055.9	1056.3	1056.1	1055.2	1054.2	1053.3	1052.4
150°	1075.6	1075.9	1076.4	1076.3	1075.7	1075.0	1074.5	1073.9
152.5°	1093.4	1094.1	1094.8	1094.8	1093.8	1092.9	1092.0	1091.1
155°	1117.9	1118.9	1120.0	1119.8	1118.7	1117.5	1116.2	1115.1
157.5°	1139.3	1140.5	1141.7	1141.5	1140.0	1138.4	1136.8	1135.3
160°	1151.5	1152.7	1153.9	1153.8	1152.4	1151.0	1149.6	1148.2
162.5°	1162.5	1164.0	1165.3	1165.3	1164.1	1162.9	1161.6	1160.4
165°	1177.3	1178.9	1180.5	1180.6	1179.3	1177.9	1176.4	1175.1
167.5°	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6
170°	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1
172.5°	1199.6	1201.1	1202.7	1202.7	1201.0	1199.2	1197.4	1195.7
175°	1204.7	1206.1	1207.6	1207.5	1205.9	1204.3	1202.7	1201.0
177.5°	1206.7	1207.9	1209.2	1209.1	1207.5	1205.9	1204.3	1202.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5

(END OF REPORT)