

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332473-940

Luminaire Tested: **S123RDIW-S1165D460U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332473-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D460U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5331.1 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	99	95	92	98	94	91	88	85	83	80	77	75	73	69	68	66	63
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	62	59	57	53
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	52	49	46
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	46	42	40
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37	35
6	68	55	47	41	64	53	46	40	49	42	38	45	39	35	41	36	33	31
7	63	50	42	37	60	48	41	36	44	38	34	41	35	32	37	33	30	27
8	59	46	38	33	56	44	37	32	41	34	30	37	32	28	34	30	27	25
9	55	42	35	29	52	41	33	29	38	31	27	35	29	26	32	27	24	22
10	51	39	32	27	49	37	31	26	35	29	25	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.3	3.0
10°-20°	451.6	8.5
20°-30°	650.2	12.2
30°-40°	732.4	13.7
40°-50°	700.7	13.1
50°-60°	573.8	10.8
60°-70°	387.1	7.3
70°-80°	194.8	3.7
80°-90°	53.1	1.0
90°-100°	33.5	0.6
100°-110°	100.3	1.9
110°-120°	170.6	3.2
120°-130°	224.4	4.2
130°-140°	252.2	4.7
140°-150°	247.9	4.7
150°-160°	208.7	3.9
160°-170°	138.9	2.6
170°-180°	48.7	0.9
0°-30°	1264.1	23.7
0°-40°	1996.5	37.4
0°-60°	3270.9	61.4
0°-90°	3905.9	73.3
90°-120°	304.4	5.7
90°-150°	1029.0	19.3
90°-180°	1425.0	26.7
0°-180°	5331.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	0	4	10	11	12	5
95°	24	27	30	31	32	27
105°	91	92	95	95	96	97
115°	172	173	172	172	172	170
125°	251	252	252	250	248	224
135°	326	328	328	327	326	251
145°	396	396	398	397	396	247
155°	453	453	453	455	452	208
165°	493	492	492	494	492	139
175°	513	512	512	514	511	49
180°	514	514	514	514	514	



TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.0	24.4	21.8	19.4	16.8	15.6	15.8	16.1	16.3	16.5	16.3
90°	0.4	1.3	2.2	3.1	4.0	5.0	6.2	7.4	8.6	9.7	10.1
92.5°	9.8	10.4	11.0	11.6	12.2	12.8	13.6	14.2	14.9	15.5	15.8
95°	23.8	24.4	25.1	25.8	26.4	27.0	27.7	28.4	29.2	29.9	30.2
97.5°	42.4	42.8	43.2	43.8	44.2	44.7	45.2	45.7	46.3	46.8	47.2
100°	54.9	55.5	56.0	56.5	57.1	57.6	58.1	58.5	58.9	59.4	59.7
102.5°	69.5	69.8	70.2	70.4	70.8	71.2	71.9	72.4	73.0	73.7	73.9
105°	91.0	91.1	91.3	91.5	91.7	92.1	92.9	93.7	94.5	95.3	95.3
107.5°	115.8	115.9	116.0	116.1	116.3	116.5	116.8	117.1	117.4	117.8	118.1
110°	131.3	131.5	131.7	131.9	132.1	132.2	132.4	132.6	132.8	133.0	133.3



TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.5	147.6	147.8	147.8	147.9	148.0	148.0	148.1	148.1	148.1	148.6
115°	171.7	172.0	172.3	172.5	172.8	172.9	172.7	172.5	172.4	172.2	172.3
117.5°	196.2	196.4	196.5	196.7	196.9	196.8	196.6	196.4	196.2	195.9	195.9
120°	211.3	211.9	212.4	212.9	213.5	213.6	213.1	212.7	212.2	211.8	211.7
122.5°	227.2	227.6	228.0	228.4	228.7	228.8	228.6	228.4	228.2	227.9	227.7
125°	251.4	251.6	251.9	252.2	252.4	252.4	252.3	252.1	251.9	251.7	251.4
127.5°	273.7	274.2	274.8	275.4	276.0	276.2	276.0	275.7	275.5	275.4	274.8
130°	288.6	289.3	290.0	290.7	291.4	291.6	291.3	291.1	290.8	290.5	290.2
132.5°	303.4	304.1	304.9	305.6	306.3	306.6	306.3	306.1	305.9	305.8	305.3
135°	326.1	326.6	327.2	327.7	328.2	328.5	328.4	328.3	328.2	328.1	327.8
137.5°	347.1	347.6	348.0	348.5	348.9	349.3	349.5	349.7	350.0	350.2	349.8
140°	361.7	362.1	362.6	363.0	363.5	363.7	363.8	363.9	364.0	364.1	364.0
142.5°	375.0	375.4	375.9	376.3	376.7	377.0	377.2	377.4	377.6	377.6	377.6
145°	395.7	395.8	396.0	396.2	396.4	396.5	396.8	397.1	397.3	397.6	397.5
147.5°	413.8	414.0	414.4	414.6	415.0	415.3	415.5	415.8	416.1	416.3	416.3
150°	426.3	426.5	426.7	426.9	427.0	427.2	427.4	427.6	427.8	427.9	427.9
152.5°	436.7	436.9	437.2	437.4	437.7	437.8	437.9	438.1	438.2	438.3	438.5
155°	453.0	453.0	453.0	453.0	453.0	453.1	453.2	453.3	453.3	453.4	453.8
157.5°	466.9	466.8	466.7	466.5	466.5	466.5	466.5	466.6	466.6	466.7	467.1
160°	475.6	475.5	475.3	475.1	474.9	474.8	474.8	474.8	474.8	474.8	475.3
162.5°	483.4	483.1	482.9	482.6	482.4	482.3	482.3	482.4	482.5	482.6	483.0
165°	493.4	493.1	492.8	492.6	492.3	492.2	492.2	492.2	492.2	492.2	492.8
167.5°	501.4	501.1	500.7	500.3	500.0	499.8	499.9	500.0	500.1	500.1	500.7
170°	506.0	505.6	505.2	504.9	504.5	504.4	504.4	504.4	504.4	504.4	505.0
172.5°	509.5	509.2	508.8	508.5	508.0	507.8	507.8	507.8	507.8	507.8	508.5
175°	513.2	512.8	512.5	512.1	511.8	511.6	511.6	511.6	511.6	511.6	512.1
177.5°	514.8	514.4	514.2	513.9	513.6	513.4	513.4	513.4	513.4	513.4	513.9
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	16.1	16.0	15.8	15.6	15.4	15.2	15.0	14.8
90°	10.4	10.8	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.1	16.4	16.7	16.8	16.7	16.5	16.4	16.3
95°	30.6	30.9	31.3	31.5	31.5	31.5	31.5	31.5
97.5°	47.6	48.1	48.4	48.6	48.6	48.6	48.5	48.5
100°	59.9	60.2	60.5	60.7	60.9	61.1	61.3	61.4
102.5°	74.2	74.5	74.7	74.8	74.8	74.7	74.7	74.6
105°	95.3	95.3	95.3	95.4	95.7	95.9	96.0	96.2
107.5°	118.3	118.6	118.9	119.0	118.9	118.8	118.7	118.6
110°	133.7	134.0	134.4	134.5	134.3	134.1	133.9	133.8





TEST NUMBER: P332473-940

CATALOG NUMBER: S123RDIW-S1165D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.0	149.5	149.9	150.1	150.0	150.0	150.0	149.9
115°	172.4	172.5	172.5	172.5	172.5	172.4	172.3	172.2
117.5°	195.9	195.8	195.8	195.7	195.5	195.2	194.9	194.7
120°	211.6	211.5	211.4	211.2	211.1	210.9	210.7	210.5
122.5°	227.5	227.2	226.9	226.8	226.5	226.2	226.0	225.7
125°	251.0	250.7	250.3	249.9	249.6	249.2	248.9	248.5
127.5°	274.4	273.8	273.3	272.9	272.5	272.1	271.6	271.3
130°	289.8	289.4	289.1	288.6	288.0	287.4	286.8	286.1
132.5°	304.9	304.4	304.0	303.5	303.1	302.6	302.1	301.6
135°	327.4	327.1	326.7	326.5	326.3	326.1	325.9	325.7
137.5°	349.5	349.1	348.7	348.3	347.9	347.7	347.3	347.0
140°	363.9	363.8	363.7	363.4	362.7	362.1	361.5	360.9
142.5°	377.5	377.4	377.3	377.0	376.6	376.0	375.6	375.1
145°	397.4	397.3	397.3	397.1	396.7	396.4	396.0	395.7
147.5°	416.3	416.3	416.3	416.1	415.5	414.9	414.4	413.8
150°	427.9	427.9	427.9	427.7	427.1	426.6	426.1	425.5
152.5°	438.5	438.7	438.9	438.7	438.3	437.7	437.3	436.8
155°	454.1	454.5	454.9	454.7	454.1	453.4	452.8	452.2
157.5°	467.5	467.9	468.2	468.1	467.7	467.2	466.6	466.2
160°	475.7	476.2	476.6	476.6	476.3	475.9	475.5	475.2
162.5°	483.5	483.9	484.4	484.3	483.8	483.1	482.6	482.0
165°	493.3	493.8	494.4	494.3	493.7	493.0	492.4	491.8
167.5°	501.2	501.8	502.3	502.3	501.8	501.2	500.7	500.1
170°	505.6	506.2	506.8	506.8	506.2	505.6	505.0	504.4
172.5°	509.0	509.5	510.1	510.1	509.4	508.8	508.2	507.6
175°	512.6	513.2	513.7	513.7	513.1	512.5	511.8	511.2
177.5°	514.3	514.8	515.1	515.1	514.6	514.2	513.6	513.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4

(END OF REPORT)