

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332475-940

Luminaire Tested: **S123RDIW-S1165D755U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332475-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D755U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6413.3 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	102	97	94	90	95	92	88	86	81	78	76	71	69	68	62	61	59	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	55	53	51	47
3	85	76	69	64	80	72	66	61	64	59	55	57	53	50	50	47	44	41
4	79	68	60	54	74	64	57	52	57	52	48	51	47	43	45	42	39	36
5	72	61	53	47	68	58	51	45	52	46	42	46	42	38	41	37	34	32
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31	28
7	62	50	42	37	58	48	40	35	43	37	33	38	34	30	34	30	27	25
8	58	46	38	33	54	43	36	32	39	33	29	35	30	27	32	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23	21
10	51	39	31	27	48	37	30	26	33	28	24	30	26	22	27	23	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17623	17623	17623	17623
5°	21007	17698	15584	17698
10°	26230	17596	14080	17596
15°	30788	17416	12840	17416
20°	34360	17148	11786	17148
25°	33812	16865	11137	16865
30°	24304	16604	10470	16604
35°	16227	16264	10038	16264
40°	11956	15855	9591	15855
45°	10029	15139	9155	15139
50°	8848	14200	8544	14200
55°	7760	13127	7707	13127
60°	6910	12099	7061	12099
65°	6069	10998	6569	10998
70°	4765	10014	5998	10014
75°	4196	8746	5481	8746
80°	3651	7426	5387	7426
85°	2939	5965	5718	5965



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.0	2.5
10°-20°	503.0	7.8
20°-30°	790.2	12.3
30°-40°	824.4	12.9
40°-50°	705.6	11.0
50°-60°	537.8	8.4
60°-70°	344.7	5.4
70°-80°	165.8	2.6
80°-90°	46.4	0.7
90°-100°	54.9	0.9
100°-110°	164.3	2.6
110°-120°	279.4	4.4
120°-130°	367.5	5.7
130°-140°	413.1	6.4
140°-150°	406.1	6.3
150°-160°	341.9	5.3
160°-170°	227.6	3.5
170°-180°	79.7	1.2
0°-30°	1454.2	22.7
0°-40°	2278.7	35.5
0°-60°	3522.0	54.9
0°-90°	4078.8	63.6
90°-120°	498.6	7.8
90°-150°	1685.3	26.3
90°-180°	2334.0	36.4
0°-180°	6413.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1637	1637	1637	1637	1637	
5°	1944	1638	1442	1638	1944	201
15°	2763	1563	1152	1563	2763	783
25°	2847	1420	938	1420	2847	1224
35°	1235	1238	764	1238	1235	810
45°	659	994	601	994	659	518
55°	414	700	411	700	414	374
65°	238	432	258	432	238	234
75°	101	210	132	210	101	108
85°	24	48	46	48	24	28
90°	20	1	20	1	20	10
95°	52	39	52	39	52	53
105°	158	149	158	149	158	167
115°	282	281	282	281	282	279
125°	407	412	407	412	407	364
135°	533	534	533	534	533	410
145°	648	648	648	648	648	404
155°	741	742	741	742	741	341
165°	806	808	806	808	806	227
175°	837	840	837	840	837	80
180°	843	843	843	843	843	



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1743.7	1746.0	1738.7	1737.6	1729.1	1726.9	1726.9	1715.1	1707.8	1698.4	1692.7
5°	1944.2	1955.4	1949.8	1937.2	1916.1	1911.2	1897.9	1876.9	1853.1	1823.6	1809.6
7.5°	2194.5	2209.8	2204.0	2184.4	2162.4	2144.7	2107.0	2072.2	2023.2	1980.3	1943.6
10°	2399.8	2383.6	2371.0	2352.1	2331.7	2298.8	2259.6	2205.6	2143.2	2094.2	2039.5
12.5°	2553.3	2550.7	2534.7	2515.2	2486.5	2455.2	2407.0	2341.3	2268.8	2197.9	2135.4
15°	2762.8	2767.0	2756.5	2736.1	2695.5	2640.1	2567.2	2539.9	2436.2	2359.1	2282.0
17.5°	2907.7	2906.9	2905.5	2877.3	2835.8	2796.4	2728.8	2656.9	2563.0	2454.4	2350.5
20°	2999.6	2992.7	2994.1	2962.5	2931.7	2886.1	2820.2	2715.8	2638.8	2513.3	2406.0
22.5°	2997.4	2996.1	3001.3	2990.5	2968.1	2933.2	2881.4	2793.2	2694.8	2568.2	2447.6
25°	2846.9	2841.3	2874.3	2883.3	2919.1	2925.3	2909.9	2861.6	2768.4	2638.0	2488.8
27.5°	2382.7	2379.5	2440.7	2517.2	2614.2	2689.6	2762.5	2797.7	2768.4	2675.0	2525.5
30°	1955.4	2021.2	2052.1	2162.8	2286.2	2433.4	2562.3	2684.9	2715.1	2674.5	2551.8
32.5°	1623.4	1681.0	1706.7	1801.8	1916.7	2089.1	2282.5	2456.2	2578.9	2609.9	2536.1
35°	1234.9	1235.6	1294.5	1336.5	1443.1	1620.4	1808.2	2040.9	2272.2	2447.4	2465.6
37.5°	985.4	988.9	1024.5	1066.4	1146.3	1240.1	1405.5	1598.9	1866.1	2135.1	2292.8
40°	850.9	857.1	883.8	925.1	982.6	1053.4	1182.3	1364.6	1587.4	1886.7	2131.3
42.5°	764.5	774.7	788.5	820.3	855.9	922.2	1026.4	1167.2	1369.9	1652.9	1935.1
45°	658.8	664.4	674.9	689.6	721.8	768.1	838.2	932.8	1101.1	1328.8	1611.2
47.5°	581.1	578.2	589.2	601.2	622.7	654.2	701.2	778.4	898.4	1081.1	1320.7
50°	528.4	527.7	535.5	544.6	564.9	588.0	626.6	684.7	780.1	931.5	1150.8
52.5°	479.1	481.8	487.2	498.6	513.3	532.0	566.6	608.5	690.4	821.0	1003.9
55°	413.5	415.6	423.3	429.6	440.1	459.1	480.8	515.9	571.9	663.0	813.7
57.5°	358.0	357.0	364.4	366.0	377.9	393.3	410.1	437.3	478.0	545.7	647.2
60°	321.0	318.9	325.2	330.1	336.4	349.0	363.0	389.7	422.0	471.7	558.6
62.5°	287.3	286.3	291.0	295.9	301.1	312.5	324.3	344.8	370.3	412.2	481.2
65°	238.3	240.4	242.5	244.6	247.4	254.4	265.6	279.6	297.2	326.6	376.4
67.5°	187.3	189.4	190.1	194.4	200.5	204.8	211.7	224.2	236.3	261.2	289.4
70°	151.4	150.7	151.4	153.5	161.2	168.9	178.0	187.2	194.8	212.3	236.2
72.5°	130.1	128.9	130.6	131.1	134.8	137.0	142.7	151.2	161.2	173.1	190.2
75°	100.9	100.9	100.9	100.9	103.7	105.1	107.3	109.3	112.8	118.4	131.1
77.5°	74.5	74.7	75.7	76.4	77.0	77.8	79.1	81.1	82.4	85.3	90.9
80°	58.9	59.6	58.9	59.6	59.6	61.0	61.7	63.8	64.5	67.9	70.1
82.5°	44.3	43.9	44.3	45.0	45.0	46.4	46.5	48.1	48.2	50.0	52.2
85°	23.8	22.5	23.8	23.1	24.5	23.1	23.8	25.2	25.2	25.9	28.7
87.5°	9.5	10.6	9.5	10.0	9.9	10.3	10.3	10.2	11.1	10.4	10.6
90°	19.9	19.5	19.3	19.0	18.6	18.3	17.7	17.0	16.5	15.9	14.0
92.5°	26.8	26.9	27.1	27.3	27.5	27.3	26.8	26.4	25.9	25.4	24.3
95°	51.6	51.6	51.6	51.6	51.6	51.4	50.7	50.1	49.6	49.0	47.8
97.5°	79.5	79.5	79.5	79.6	79.6	79.4	78.6	78.0	77.3	76.7	75.8
100°	100.6	100.3	100.0	99.7	99.4	99.1	98.6	98.2	97.7	97.3	96.6
102.5°	122.3	122.3	122.4	122.5	122.5	122.3	121.9	121.5	121.0	120.6	119.6
105°	157.6	157.2	156.9	156.7	156.3	156.2	156.2	156.2	156.2	156.2	154.9
107.5°	194.2	194.4	194.6	194.7	194.9	194.7	194.3	193.8	193.3	192.9	192.3
110°	219.1	219.4	219.6	220.0	220.3	220.1	219.5	218.9	218.4	217.8	217.5



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.6	245.6	245.7	245.8	245.8	245.5	244.8	244.1	243.3	242.6	242.5
115°	282.0	282.1	282.2	282.4	282.6	282.6	282.4	282.2	282.1	282.0	282.2
117.5°	318.9	319.3	319.7	320.1	320.6	320.7	320.7	320.8	320.8	320.8	321.3
120°	344.8	345.1	345.4	345.7	346.0	346.3	346.3	346.5	346.7	346.8	347.6
122.5°	369.7	370.1	370.5	371.0	371.4	371.8	372.1	372.6	372.9	373.3	373.7
125°	407.1	407.6	408.2	408.8	409.4	410.0	410.5	411.2	411.8	412.3	412.6
127.5°	444.3	445.0	445.6	446.3	446.9	447.7	448.5	449.3	450.1	451.0	451.3
130°	468.6	469.7	470.6	471.7	472.7	473.5	474.1	474.7	475.3	475.9	476.4
132.5°	494.0	494.8	495.6	496.4	497.2	497.9	498.6	499.4	500.1	500.8	501.1
135°	533.4	533.8	534.0	534.3	534.7	535.1	535.7	536.3	536.8	537.4	537.6
137.5°	568.3	568.8	569.4	570.0	570.5	571.1	571.7	572.3	572.9	573.5	573.2
140°	591.0	592.1	593.1	594.1	595.1	595.8	595.9	596.0	596.2	596.4	596.2
142.5°	614.3	615.1	615.9	616.7	617.5	618.0	618.1	618.3	618.4	618.6	618.3
145°	648.0	648.5	649.2	649.7	650.3	650.7	650.9	650.9	651.1	651.3	650.9
147.5°	677.9	678.8	679.7	680.6	681.4	681.9	681.9	681.9	681.9	681.9	681.4
150°	697.0	697.9	698.7	699.5	700.4	700.9	700.9	700.9	700.9	700.9	700.6
152.5°	715.5	716.2	717.0	717.7	718.5	718.8	718.5	718.4	718.1	717.8	717.6
155°	740.7	741.6	742.7	743.7	744.8	744.9	744.4	743.8	743.2	742.6	742.4
157.5°	763.5	764.4	765.2	766.0	766.8	767.0	766.3	765.7	765.1	764.5	764.4
160°	778.4	778.9	779.5	780.2	780.7	780.6	779.9	779.2	778.5	777.7	777.7
162.5°	789.4	790.4	791.4	792.3	793.3	793.4	792.6	791.8	791.1	790.4	790.3
165°	805.5	806.6	807.5	808.6	809.6	809.7	808.8	807.9	807.0	806.1	806.1
167.5°	819.1	820.0	820.9	821.9	822.8	822.8	821.9	820.9	820.0	819.1	819.0
170°	826.0	827.1	828.0	829.1	830.1	830.1	829.1	828.0	827.1	826.0	826.0
172.5°	831.3	832.3	833.4	834.4	835.4	835.4	834.6	833.7	832.8	831.8	831.8
175°	837.2	838.3	839.3	840.3	841.4	841.4	840.5	839.7	838.8	837.9	837.9
177.5°	840.4	841.2	842.0	842.9	843.7	843.8	843.1	842.4	841.7	841.0	841.0
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1690.5	1688.8	1681.0	1672.0	1660.2	1652.3	1646.2	1642.8	1632.7	1620.4	1611.9
5°	1794.9	1773.9	1751.4	1724.1	1698.9	1672.9	1656.8	1637.9	1614.8	1588.9	1570.7
7.5°	1906.7	1865.5	1821.1	1775.3	1730.0	1689.3	1653.5	1622.7	1585.9	1548.7	1522.7
10°	1992.5	1932.2	1869.9	1806.1	1747.9	1693.3	1651.2	1609.9	1565.8	1523.0	1490.8
12.5°	2070.5	1991.1	1919.2	1840.8	1766.5	1701.1	1640.6	1591.9	1538.8	1493.3	1456.5
15°	2169.2	2087.9	2000.9	1881.8	1783.0	1700.3	1626.7	1562.9	1498.4	1442.3	1406.6
17.5°	2261.4	2139.0	2022.2	1922.9	1794.5	1691.1	1601.3	1525.1	1454.3	1394.8	1350.9
20°	2299.5	2181.0	2054.2	1927.3	1801.2	1685.6	1581.1	1497.0	1423.4	1356.1	1315.5
22.5°	2322.5	2188.3	2054.8	1918.4	1784.4	1664.3	1560.9	1468.5	1388.7	1324.7	1274.6
25°	2349.3	2189.5	2042.3	1907.7	1771.0	1640.7	1518.0	1420.0	1333.7	1265.8	1212.5
27.5°	2367.0	2179.0	2005.0	1855.5	1716.8	1587.0	1474.6	1370.6	1283.2	1211.2	1154.1
30°	2370.3	2170.5	1976.4	1814.5	1673.7	1554.5	1435.4	1335.9	1243.3	1166.9	1113.7
32.5°	2374.8	2149.8	1937.7	1765.8	1621.5	1503.5	1395.5	1300.5	1205.8	1130.5	1076.1
35°	2356.3	2138.3	1879.0	1681.3	1537.0	1422.7	1325.3	1237.7	1144.5	1071.6	1016.3
37.5°	2276.6	2092.8	1818.2	1586.4	1435.4	1329.5	1250.2	1173.8	1088.3	1009.7	957.5
40°	2196.5	2047.9	1771.0	1528.6	1370.9	1262.2	1190.8	1128.4	1045.7	972.1	916.1
42.5°	2077.1	1986.8	1726.2	1468.0	1298.0	1193.3	1133.0	1074.5	1001.9	927.2	874.5
45°	1858.0	1869.9	1634.4	1371.5	1197.0	1091.9	1035.2	994.5	930.1	868.3	814.4
47.5°	1583.2	1694.7	1526.6	1268.8	1090.7	992.0	942.4	906.9	863.4	802.9	753.7
50°	1403.8	1562.9	1440.3	1199.9	1024.0	925.9	876.7	848.0	810.2	762.5	715.6
52.5°	1238.4	1409.3	1336.0	1123.0	951.6	861.9	814.0	790.3	760.3	715.4	673.0
55°	1010.0	1183.0	1166.3	1007.1	843.1	762.5	726.1	699.5	679.1	645.5	611.9
57.5°	816.9	981.1	989.7	878.2	747.5	667.9	636.5	616.4	603.2	577.8	546.7
60°	695.3	846.0	875.4	791.3	679.1	609.0	578.2	562.0	551.6	531.3	507.4
62.5°	594.3	722.6	755.9	695.4	613.5	548.0	523.8	508.3	501.1	483.6	462.5
65°	454.9	561.4	593.6	560.0	517.2	464.7	445.1	431.8	425.4	415.6	400.2
67.5°	342.1	419.6	455.0	431.3	415.9	382.6	370.1	363.0	357.4	350.7	337.8
70°	274.7	332.2	368.6	362.3	349.7	332.2	323.1	318.2	312.5	307.0	295.8
72.5°	220.9	260.5	294.6	297.8	287.5	284.0	276.0	273.9	270.5	263.8	257.6
75°	146.5	173.8	197.6	206.8	211.0	214.5	211.0	210.3	209.6	203.9	200.5
77.5°	96.0	110.8	125.7	141.3	147.8	152.7	153.7	156.3	154.4	151.5	149.8
80°	73.6	77.1	87.6	100.9	111.5	115.7	118.4	119.8	119.1	118.4	115.7
82.5°	53.4	56.4	61.3	70.6	79.5	86.5	88.2	87.9	89.4	89.9	87.6
85°	28.7	29.4	30.9	32.3	37.2	44.9	47.0	48.3	49.8	49.8	45.6
87.5°	11.4	10.4	11.1	10.9	12.2	12.5	15.6	18.1	18.9	16.9	17.3
90°	12.0	10.2	8.2	6.5	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	23.3	22.1	21.0	20.0	19.0	18.0	17.0	16.1	17.0	18.0	19.0
95°	46.6	45.5	44.2	43.2	42.2	41.1	40.0	39.1	40.0	41.1	42.2
97.5°	74.9	74.1	73.2	72.4	71.7	70.9	70.1	69.4	70.1	70.9	71.7
100°	95.9	95.1	94.3	93.5	92.6	91.8	90.9	90.0	90.9	91.8	92.6
102.5°	118.7	117.7	116.7	115.9	115.4	114.9	114.4	113.9	114.4	114.9	115.4
105°	153.6	152.2	150.9	150.1	149.8	149.5	149.2	148.9	149.2	149.5	149.8
107.5°	191.8	191.3	190.7	190.4	190.2	190.0	189.8	189.7	189.8	190.0	190.2
110°	217.1	216.9	216.6	216.2	216.0	215.7	215.4	215.1	215.4	215.7	216.0



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	242.5	242.5	242.4	242.3	242.1	241.9	241.7	241.6	241.7	241.9	242.1
115°	282.6	282.9	283.1	283.0	282.6	282.1	281.7	281.3	281.7	282.1	282.6
117.5°	321.6	322.0	322.4	322.4	322.2	321.8	321.6	321.3	321.6	321.8	322.2
120°	348.3	349.0	349.7	349.7	348.8	347.9	347.1	346.2	347.1	347.9	348.8
122.5°	374.1	374.4	374.8	374.7	374.1	373.4	372.7	372.1	372.7	373.4	374.1
125°	413.0	413.2	413.5	413.5	413.0	412.6	412.1	411.7	412.1	412.6	413.0
127.5°	451.7	452.0	452.3	452.0	451.0	450.1	449.2	448.2	449.2	450.1	451.0
130°	476.8	477.2	477.7	477.2	476.1	474.9	473.8	472.6	473.8	474.9	476.1
132.5°	501.4	501.8	502.0	501.7	500.4	499.3	498.1	497.0	498.1	499.3	500.4
135°	537.7	537.9	538.1	537.6	536.8	535.9	535.0	534.1	535.0	535.9	536.8
137.5°	572.8	572.4	572.0	571.5	570.8	570.0	569.3	568.6	569.3	570.0	570.8
140°	596.0	595.9	595.8	595.3	594.6	593.9	593.1	592.4	593.1	593.9	594.6
142.5°	618.0	617.8	617.5	617.0	616.3	615.5	614.8	614.1	614.8	615.5	616.3
145°	650.4	650.0	649.5	649.2	648.8	648.5	648.3	648.0	648.3	648.5	648.8
147.5°	681.0	680.6	680.2	679.8	679.2	678.7	678.1	677.6	678.1	678.7	679.2
150°	700.3	700.0	699.7	699.5	699.2	698.8	698.6	698.3	698.6	698.8	699.2
152.5°	717.5	717.3	717.1	716.8	716.5	716.0	715.6	715.2	715.6	716.0	716.5
155°	742.3	742.2	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0
157.5°	764.2	764.1	764.0	764.0	764.2	764.4	764.6	764.7	764.6	764.4	764.2
160°	777.7	777.7	777.7	777.8	778.1	778.5	778.7	779.0	778.7	778.5	778.1
162.5°	790.1	790.1	790.0	790.1	790.5	790.9	791.3	791.8	791.3	790.9	790.5
165°	806.1	806.1	806.1	806.4	806.8	807.3	807.7	808.2	807.7	807.3	806.8
167.5°	818.9	818.8	818.7	818.9	819.5	820.1	820.6	821.3	820.6	820.1	819.5
170°	826.0	826.0	826.0	826.3	826.9	827.5	828.0	828.7	828.0	827.5	826.9
172.5°	831.8	831.8	831.8	832.1	832.7	833.3	833.9	834.5	833.9	833.3	832.7
175°	837.9	837.9	837.9	838.2	838.8	839.4	840.0	840.5	840.0	839.4	838.8
177.5°	841.0	841.0	841.0	841.2	841.7	842.1	842.6	843.1	842.6	842.1	841.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1609.2	1601.9	1596.9	1585.6	1578.3	1570.5	1562.6	1567.7	1567.1	1566.6	1566.6
5°	1555.2	1539.1	1524.4	1505.5	1493.5	1478.8	1467.6	1466.2	1469.0	1459.2	1453.6
7.5°	1501.6	1479.6	1458.7	1437.9	1415.8	1398.1	1387.0	1381.8	1374.7	1368.6	1362.4
10°	1464.1	1438.2	1417.8	1391.9	1368.1	1347.0	1333.7	1324.6	1319.7	1314.8	1305.7
12.5°	1425.4	1400.1	1374.1	1344.8	1322.1	1297.7	1287.7	1277.6	1268.1	1262.7	1250.2
15°	1368.8	1335.9	1308.5	1277.6	1252.4	1228.6	1214.6	1194.3	1191.4	1184.5	1171.8
17.5°	1312.0	1276.2	1238.6	1215.7	1187.2	1162.4	1141.1	1134.3	1114.2	1106.6	1095.7
20°	1267.1	1234.2	1205.5	1175.4	1134.0	1110.9	1094.0	1084.9	1068.8	1059.0	1052.0
22.5°	1228.4	1195.0	1161.7	1126.6	1092.5	1066.6	1054.3	1040.1	1031.3	1017.5	1010.0
25°	1173.2	1136.8	1096.8	1059.0	1034.5	1014.9	995.2	982.6	970.0	963.7	949.7
27.5°	1109.0	1070.9	1033.6	1004.9	974.7	955.4	937.6	926.4	911.2	900.6	892.9
30°	1073.7	1028.9	996.6	970.7	932.1	913.9	900.6	886.6	875.4	864.2	856.5
32.5°	1032.8	991.8	961.3	929.2	899.6	879.7	862.5	850.2	840.6	829.9	822.2
35°	968.6	934.2	902.7	870.5	848.7	828.4	808.1	797.5	788.5	778.6	771.7
37.5°	910.5	878.4	848.5	817.9	790.9	774.5	758.0	750.0	737.7	731.1	724.0
40°	874.7	843.1	810.9	781.5	753.4	740.8	726.1	714.2	702.9	698.0	690.4
42.5°	835.4	803.9	776.7	745.0	722.0	704.9	691.3	678.3	669.9	662.7	658.4
45°	777.2	749.2	722.6	691.1	669.3	654.6	639.2	627.2	619.6	614.7	606.9
47.5°	720.8	692.8	665.7	638.2	617.2	600.4	585.0	576.7	566.4	560.4	555.2
50°	679.8	654.6	625.9	600.7	579.6	562.8	550.2	539.7	530.6	522.8	519.3
52.5°	642.3	615.4	590.6	566.9	544.8	525.8	514.2	503.2	496.3	487.5	483.5
55°	580.3	554.4	533.3	510.2	488.5	472.3	458.3	448.5	441.6	431.8	426.1
57.5°	522.1	498.9	473.8	453.7	431.3	417.7	406.1	392.8	384.2	376.5	371.0
60°	482.9	456.3	434.5	415.6	396.0	378.4	367.9	357.4	348.3	340.6	335.7
62.5°	441.9	418.7	398.1	377.5	359.5	344.3	332.1	323.2	315.2	310.3	305.4
65°	379.2	361.0	339.9	323.1	306.3	295.1	285.3	277.5	272.0	268.4	264.2
67.5°	321.4	303.7	285.3	268.9	257.6	249.1	242.6	236.0	233.3	228.7	226.0
70°	283.8	265.6	249.5	236.9	225.7	219.4	215.2	210.3	207.4	201.9	199.0
72.5°	242.9	229.7	218.1	207.8	198.8	193.1	187.7	181.6	177.2	171.0	168.2
75°	191.4	179.4	170.3	163.3	157.7	150.0	142.3	136.0	133.8	131.8	131.1
77.5°	141.7	134.1	127.5	121.6	114.7	109.1	107.4	105.9	105.6	104.4	104.4
80°	111.5	104.4	99.5	92.5	88.3	88.3	88.3	86.9	87.6	87.6	87.6
82.5°	82.8	76.4	73.7	71.2	70.4	70.9	70.9	71.2	70.8	71.9	71.3
85°	42.7	43.4	44.9	44.1	44.9	44.9	46.3	45.6	46.3	44.9	46.3
87.5°	17.0	19.0	20.0	21.0	21.8	21.7	22.4	22.5	23.2	23.3	23.4
90°	6.5	8.2	10.2	12.0	14.0	15.9	16.5	17.0	17.7	18.3	18.6
92.5°	20.0	21.0	22.1	23.3	24.3	25.4	25.9	26.4	26.8	27.3	27.5
95°	43.2	44.2	45.5	46.6	47.8	49.0	49.6	50.1	50.7	51.4	51.6
97.5°	72.4	73.2	74.1	74.9	75.8	76.7	77.3	78.0	78.6	79.4	79.6
100°	93.5	94.3	95.1	95.9	96.6	97.3	97.7	98.2	98.6	99.1	99.4
102.5°	115.9	116.7	117.7	118.7	119.6	120.6	121.0	121.5	121.9	122.3	122.5
105°	150.1	150.9	152.2	153.6	154.9	156.2	156.2	156.2	156.2	156.2	156.3
107.5°	190.4	190.7	191.3	191.8	192.3	192.9	193.3	193.8	194.3	194.7	194.9
110°	216.2	216.6	216.9	217.1	217.5	217.8	218.4	218.9	219.5	220.1	220.3



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	242.3	242.4	242.5	242.5	242.5	242.6	243.3	244.1	244.8	245.5	245.8
115°	283.0	283.1	282.9	282.6	282.2	282.0	282.1	282.2	282.4	282.6	282.6
117.5°	322.4	322.4	322.0	321.6	321.3	320.8	320.8	320.8	320.7	320.7	320.6
120°	349.7	349.7	349.0	348.3	347.6	346.8	346.7	346.5	346.3	346.3	346.0
122.5°	374.7	374.8	374.4	374.1	373.7	373.3	372.9	372.6	372.1	371.8	371.4
125°	413.5	413.5	413.2	413.0	412.6	412.3	411.8	411.2	410.5	410.0	409.4
127.5°	452.0	452.3	452.0	451.7	451.3	451.0	450.1	449.3	448.5	447.7	446.9
130°	477.2	477.7	477.2	476.8	476.4	475.9	475.3	474.7	474.1	473.5	472.7
132.5°	501.7	502.0	501.8	501.4	501.1	500.8	500.1	499.4	498.6	497.9	497.2
135°	537.6	538.1	537.9	537.7	537.6	537.4	536.8	536.3	535.7	535.1	534.7
137.5°	571.5	572.0	572.4	572.8	573.2	573.5	572.9	572.3	571.7	571.1	570.5
140°	595.3	595.8	595.9	596.0	596.2	596.4	596.2	596.0	595.9	595.8	595.1
142.5°	617.0	617.5	617.8	618.0	618.3	618.6	618.4	618.3	618.1	618.0	617.5
145°	649.2	649.5	650.0	650.4	650.9	651.3	651.1	650.9	650.9	650.7	650.3
147.5°	679.8	680.2	680.6	681.0	681.4	681.9	681.9	681.9	681.9	681.9	681.4
150°	699.5	699.7	700.0	700.3	700.6	700.9	700.9	700.9	700.9	700.9	700.4
152.5°	716.8	717.1	717.3	717.5	717.6	717.8	718.1	718.4	718.5	718.8	718.5
155°	742.0	742.0	742.2	742.3	742.4	742.6	743.2	743.8	744.4	744.9	744.8
157.5°	764.0	764.0	764.1	764.2	764.4	764.5	765.1	765.7	766.3	767.0	766.8
160°	777.8	777.7	777.7	777.7	777.7	777.7	778.5	779.2	779.9	780.6	780.7
162.5°	790.1	790.0	790.1	790.1	790.3	790.4	791.1	791.8	792.6	793.4	793.3
165°	806.4	806.1	806.1	806.1	806.1	806.1	807.0	807.9	808.8	809.7	809.6
167.5°	818.9	818.7	818.8	818.9	819.0	819.1	820.0	820.9	821.9	822.8	822.8
170°	826.3	826.0	826.0	826.0	826.0	826.0	827.1	828.0	829.1	830.1	830.1
172.5°	832.1	831.8	831.8	831.8	831.8	831.8	832.8	833.7	834.6	835.4	835.4
175°	838.2	837.9	837.9	837.9	837.9	837.9	838.8	839.7	840.5	841.4	841.4
177.5°	841.2	841.0	841.0	841.0	841.0	841.0	841.7	842.4	843.1	843.8	843.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1559.9	1559.2	1559.9	1557.6	1559.9	1559.2	1559.9	1566.6	1566.6	1567.1	1567.7
5°	1451.4	1450.8	1448.7	1442.3	1448.7	1450.8	1451.4	1453.6	1459.2	1469.0	1466.2
7.5°	1356.8	1355.8	1349.7	1349.9	1349.7	1355.8	1356.8	1362.4	1368.6	1374.7	1381.8
10°	1300.8	1301.5	1293.1	1288.2	1293.1	1301.5	1300.8	1305.7	1314.8	1319.7	1324.6
12.5°	1246.4	1243.2	1236.4	1231.0	1236.4	1243.2	1246.4	1250.2	1262.7	1268.1	1277.6
15°	1174.7	1167.6	1150.8	1152.2	1150.8	1167.6	1174.7	1171.8	1184.5	1191.4	1194.3
17.5°	1090.1	1084.9	1084.7	1074.9	1084.7	1084.9	1090.1	1095.7	1106.6	1114.2	1134.3
20°	1040.8	1037.2	1038.7	1028.9	1038.7	1037.2	1040.8	1052.0	1059.0	1068.8	1084.9
22.5°	1002.1	998.5	992.7	989.6	992.7	998.5	1002.1	1010.0	1017.5	1031.3	1040.1
25°	945.5	939.9	934.2	937.7	934.2	939.9	945.5	949.7	963.7	970.0	982.6
27.5°	888.9	884.7	879.0	878.3	879.0	884.7	888.9	892.9	900.6	911.2	926.4
30°	852.9	848.7	846.0	842.4	846.0	848.7	852.9	856.5	864.2	875.4	886.6
32.5°	816.5	815.6	810.7	809.9	810.7	815.6	816.5	822.2	829.9	840.6	850.2
35°	768.8	764.6	763.2	763.9	763.2	764.6	768.8	771.7	778.6	788.5	797.5
37.5°	723.5	717.9	715.4	712.9	715.4	717.9	723.5	724.0	731.1	737.7	750.0
40°	691.1	685.5	684.0	682.6	684.0	685.5	691.1	690.4	698.0	702.9	714.2
42.5°	654.6	652.4	651.5	649.0	651.5	652.4	654.6	658.4	662.7	669.9	678.3
45°	604.8	604.1	599.9	601.4	599.9	604.1	604.8	606.9	614.7	619.6	627.2
47.5°	552.4	549.3	546.4	548.3	546.4	549.3	552.4	555.2	560.4	566.4	576.7
50°	516.6	515.1	508.8	510.2	508.8	515.1	516.6	519.3	522.8	530.6	539.7
52.5°	480.6	475.3	473.0	472.1	473.0	475.3	480.6	483.5	487.5	496.3	503.2
55°	421.2	414.9	412.1	410.7	412.1	414.9	421.2	426.1	431.8	441.6	448.5
57.5°	362.9	361.2	359.0	360.5	359.0	361.2	362.9	371.0	376.5	384.2	392.8
60°	328.7	328.7	328.7	328.0	328.7	328.7	328.7	335.7	340.6	348.3	357.4
62.5°	302.4	300.7	300.1	301.1	300.1	300.7	302.4	305.4	310.3	315.2	323.2
65°	262.2	261.4	258.6	257.9	258.6	261.4	262.2	264.2	268.4	272.0	277.5
67.5°	224.2	221.6	220.8	219.8	220.8	221.6	224.2	226.0	228.7	233.3	236.0
70°	195.6	194.1	189.9	190.6	189.9	194.1	195.6	199.0	201.9	207.4	210.3
72.5°	164.7	163.3	162.5	161.5	162.5	163.3	164.7	168.2	171.0	177.2	181.6
75°	130.4	129.7	128.9	131.8	128.9	129.7	130.4	131.1	131.8	133.8	136.0
77.5°	104.4	104.4	104.9	103.7	104.9	104.4	104.4	104.4	104.4	105.6	105.9
80°	87.6	87.6	86.9	86.9	86.9	87.6	87.6	87.6	87.6	87.6	86.9
82.5°	70.3	70.8	71.2	70.1	71.2	70.8	70.3	71.3	71.9	70.8	71.2
85°	46.3	45.6	47.0	46.3	47.0	45.6	46.3	46.3	44.9	46.3	45.6
87.5°	24.5	23.5	23.5	24.2	23.5	23.5	24.5	23.4	23.3	23.2	22.5
90°	19.0	19.3	19.5	19.9	19.5	19.3	19.0	18.6	18.3	17.7	17.0
92.5°	27.3	27.1	26.9	26.8	26.9	27.1	27.3	27.5	27.3	26.8	26.4
95°	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.4	50.7	50.1
97.5°	79.6	79.5	79.5	79.5	79.5	79.5	79.6	79.6	79.4	78.6	78.0
100°	99.7	100.0	100.3	100.6	100.3	100.0	99.7	99.4	99.1	98.6	98.2
102.5°	122.5	122.4	122.3	122.3	122.3	122.4	122.5	122.5	122.3	121.9	121.5
105°	156.7	156.9	157.2	157.6	157.2	156.9	156.7	156.3	156.2	156.2	156.2
107.5°	194.7	194.6	194.4	194.2	194.4	194.6	194.7	194.9	194.7	194.3	193.8
110°	220.0	219.6	219.4	219.1	219.4	219.6	220.0	220.3	220.1	219.5	218.9



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	245.8	245.7	245.6	245.6	245.6	245.7	245.8	245.8	245.5	244.8	244.1
115°	282.4	282.2	282.1	282.0	282.1	282.2	282.4	282.6	282.6	282.4	282.2
117.5°	320.1	319.7	319.3	318.9	319.3	319.7	320.1	320.6	320.7	320.7	320.8
120°	345.7	345.4	345.1	344.8	345.1	345.4	345.7	346.0	346.3	346.3	346.5
122.5°	371.0	370.5	370.1	369.7	370.1	370.5	371.0	371.4	371.8	372.1	372.6
125°	408.8	408.2	407.6	407.1	407.6	408.2	408.8	409.4	410.0	410.5	411.2
127.5°	446.3	445.6	445.0	444.3	445.0	445.6	446.3	446.9	447.7	448.5	449.3
130°	471.7	470.6	469.7	468.6	469.7	470.6	471.7	472.7	473.5	474.1	474.7
132.5°	496.4	495.6	494.8	494.0	494.8	495.6	496.4	497.2	497.9	498.6	499.4
135°	534.3	534.0	533.8	533.4	533.8	534.0	534.3	534.7	535.1	535.7	536.3
137.5°	570.0	569.4	568.8	568.3	568.8	569.4	570.0	570.5	571.1	571.7	572.3
140°	594.1	593.1	592.1	591.0	592.1	593.1	594.1	595.1	595.8	595.9	596.0
142.5°	616.7	615.9	615.1	614.3	615.1	615.9	616.7	617.5	618.0	618.1	618.3
145°	649.7	649.2	648.5	648.0	648.5	649.2	649.7	650.3	650.7	650.9	650.9
147.5°	680.6	679.7	678.8	677.9	678.8	679.7	680.6	681.4	681.9	681.9	681.9
150°	699.5	698.7	697.9	697.0	697.9	698.7	699.5	700.4	700.9	700.9	700.9
152.5°	717.7	717.0	716.2	715.5	716.2	717.0	717.7	718.5	718.8	718.5	718.4
155°	743.7	742.7	741.6	740.7	741.6	742.7	743.7	744.8	744.9	744.4	743.8
157.5°	766.0	765.2	764.4	763.5	764.4	765.2	766.0	766.8	767.0	766.3	765.7
160°	780.2	779.5	778.9	778.4	778.9	779.5	780.2	780.7	780.6	779.9	779.2
162.5°	792.3	791.4	790.4	789.4	790.4	791.4	792.3	793.3	793.4	792.6	791.8
165°	808.6	807.5	806.6	805.5	806.6	807.5	808.6	809.6	809.7	808.8	807.9
167.5°	821.9	820.9	820.0	819.1	820.0	820.9	821.9	822.8	822.8	821.9	820.9
170°	829.1	828.0	827.1	826.0	827.1	828.0	829.1	830.1	830.1	829.1	828.0
172.5°	834.4	833.4	832.3	831.3	832.3	833.4	834.4	835.4	835.4	834.6	833.7
175°	840.3	839.3	838.3	837.2	838.3	839.3	840.3	841.4	841.4	840.5	839.7
177.5°	842.9	842.0	841.2	840.4	841.2	842.0	842.9	843.7	843.8	843.1	842.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1562.6	1570.5	1578.3	1585.6	1596.9	1601.9	1609.2	1611.9	1620.4	1632.7	1642.8
5°	1467.6	1478.8	1493.5	1505.5	1524.4	1539.1	1555.2	1570.7	1588.9	1614.8	1637.9
7.5°	1387.0	1398.1	1415.8	1437.9	1458.7	1479.6	1501.6	1522.7	1548.7	1585.9	1622.7
10°	1333.7	1347.0	1368.1	1391.9	1417.8	1438.2	1464.1	1490.8	1523.0	1565.8	1609.9
12.5°	1287.7	1297.7	1322.1	1344.8	1374.1	1400.1	1425.4	1456.5	1493.3	1538.8	1591.9
15°	1214.6	1228.6	1252.4	1277.6	1308.5	1335.9	1368.8	1406.6	1442.3	1498.4	1562.9
17.5°	1141.1	1162.4	1187.2	1215.7	1238.6	1276.2	1312.0	1350.9	1394.8	1454.3	1525.1
20°	1094.0	1110.9	1134.0	1175.4	1205.5	1234.2	1267.1	1315.5	1356.1	1423.4	1497.0
22.5°	1054.3	1066.6	1092.5	1126.6	1161.7	1195.0	1228.4	1274.6	1324.7	1388.7	1468.5
25°	995.2	1014.9	1034.5	1059.0	1096.8	1136.8	1173.2	1212.5	1265.8	1333.7	1420.0
27.5°	937.6	955.4	974.7	1004.9	1033.6	1070.9	1109.0	1154.1	1211.2	1283.2	1370.6
30°	900.6	913.9	932.1	970.7	996.6	1028.9	1073.7	1113.7	1166.9	1243.3	1335.9
32.5°	862.5	879.7	899.6	929.2	961.3	991.8	1032.8	1076.1	1130.5	1205.8	1300.5
35°	808.1	828.4	848.7	870.5	902.7	934.2	968.6	1016.3	1071.6	1144.5	1237.7
37.5°	758.0	774.5	790.9	817.9	848.5	878.4	910.5	957.5	1009.7	1088.3	1173.8
40°	726.1	740.8	753.4	781.5	810.9	843.1	874.7	916.1	972.1	1045.7	1128.4
42.5°	691.3	704.9	722.0	745.0	776.7	803.9	835.4	874.5	927.2	1001.9	1074.5
45°	639.2	654.6	669.3	691.1	722.6	749.2	777.2	814.4	868.3	930.1	994.5
47.5°	585.0	600.4	617.2	638.2	665.7	692.8	720.8	753.7	802.9	863.4	906.9
50°	550.2	562.8	579.6	600.7	625.9	654.6	679.8	715.6	762.5	810.2	848.0
52.5°	514.2	525.8	544.8	566.9	590.6	615.4	642.3	673.0	715.4	760.3	790.3
55°	458.3	472.3	488.5	510.2	533.3	554.4	580.3	611.9	645.5	679.1	699.5
57.5°	406.1	417.7	431.3	453.7	473.8	498.9	522.1	546.7	577.8	603.2	616.4
60°	367.9	378.4	396.0	415.6	434.5	456.3	482.9	507.4	531.3	551.6	562.0
62.5°	332.1	344.3	359.5	377.5	398.1	418.7	441.9	462.5	483.6	501.1	508.3
65°	285.3	295.1	306.3	323.1	339.9	361.0	379.2	400.2	415.6	425.4	431.8
67.5°	242.6	249.1	257.6	268.9	285.3	303.7	321.4	337.8	350.7	357.4	363.0
70°	215.2	219.4	225.7	236.9	249.5	265.6	283.8	295.8	307.0	312.5	318.2
72.5°	187.7	193.1	198.8	207.8	218.1	229.7	242.9	257.6	263.8	270.5	273.9
75°	142.3	150.0	157.7	163.3	170.3	179.4	191.4	200.5	203.9	209.6	210.3
77.5°	107.4	109.1	114.7	121.6	127.5	134.1	141.7	149.8	151.5	154.4	156.3
80°	88.3	88.3	88.3	92.5	99.5	104.4	111.5	115.7	118.4	119.1	119.8
82.5°	70.9	70.9	70.4	71.2	73.7	76.4	82.8	87.6	89.9	89.4	87.9
85°	46.3	44.9	44.9	44.1	44.9	43.4	42.7	45.6	49.8	49.8	48.3
87.5°	22.4	21.7	21.8	21.0	20.0	19.0	17.0	17.3	16.9	18.9	18.1
90°	16.5	15.9	14.0	12.0	10.2	8.2	6.5	5.1	3.6	2.1	0.6
92.5°	25.9	25.4	24.3	23.3	22.1	21.0	20.0	19.0	18.0	17.0	16.1
95°	49.6	49.0	47.8	46.6	45.5	44.2	43.2	42.2	41.1	40.0	39.1
97.5°	77.3	76.7	75.8	74.9	74.1	73.2	72.4	71.7	70.9	70.1	69.4
100°	97.7	97.3	96.6	95.9	95.1	94.3	93.5	92.6	91.8	90.9	90.0
102.5°	121.0	120.6	119.6	118.7	117.7	116.7	115.9	115.4	114.9	114.4	113.9
105°	156.2	156.2	154.9	153.6	152.2	150.9	150.1	149.8	149.5	149.2	148.9
107.5°	193.3	192.9	192.3	191.8	191.3	190.7	190.4	190.2	190.0	189.8	189.7
110°	218.4	217.8	217.5	217.1	216.9	216.6	216.2	216.0	215.7	215.4	215.1



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	243.3	242.6	242.5	242.5	242.5	242.4	242.3	242.1	241.9	241.7	241.6
115°	282.1	282.0	282.2	282.6	282.9	283.1	283.0	282.6	282.1	281.7	281.3
117.5°	320.8	320.8	321.3	321.6	322.0	322.4	322.4	322.2	321.8	321.6	321.3
120°	346.7	346.8	347.6	348.3	349.0	349.7	349.7	348.8	347.9	347.1	346.2
122.5°	372.9	373.3	373.7	374.1	374.4	374.8	374.7	374.1	373.4	372.7	372.1
125°	411.8	412.3	412.6	413.0	413.2	413.5	413.5	413.0	412.6	412.1	411.7
127.5°	450.1	451.0	451.3	451.7	452.0	452.3	452.0	451.0	450.1	449.2	448.2
130°	475.3	475.9	476.4	476.8	477.2	477.7	477.2	476.1	474.9	473.8	472.6
132.5°	500.1	500.8	501.1	501.4	501.8	502.0	501.7	500.4	499.3	498.1	497.0
135°	536.8	537.4	537.6	537.7	537.9	538.1	537.6	536.8	535.9	535.0	534.1
137.5°	572.9	573.5	573.2	572.8	572.4	572.0	571.5	570.8	570.0	569.3	568.6
140°	596.2	596.4	596.2	596.0	595.9	595.8	595.3	594.6	593.9	593.1	592.4
142.5°	618.4	618.6	618.3	618.0	617.8	617.5	617.0	616.3	615.5	614.8	614.1
145°	651.1	651.3	650.9	650.4	650.0	649.5	649.2	648.8	648.5	648.3	648.0
147.5°	681.9	681.9	681.4	681.0	680.6	680.2	679.8	679.2	678.7	678.1	677.6
150°	700.9	700.9	700.6	700.3	700.0	699.7	699.5	699.2	698.8	698.6	698.3
152.5°	718.1	717.8	717.6	717.5	717.3	717.1	716.8	716.5	716.0	715.6	715.2
155°	743.2	742.6	742.4	742.3	742.2	742.0	742.0	742.0	742.0	742.0	742.0
157.5°	765.1	764.5	764.4	764.2	764.1	764.0	764.0	764.2	764.4	764.6	764.7
160°	778.5	777.7	777.7	777.7	777.7	777.7	777.8	778.1	778.5	778.7	779.0
162.5°	791.1	790.4	790.3	790.1	790.1	790.0	790.1	790.5	790.9	791.3	791.8
165°	807.0	806.1	806.1	806.1	806.1	806.1	806.4	806.8	807.3	807.7	808.2
167.5°	820.0	819.1	819.0	818.9	818.8	818.7	818.9	819.5	820.1	820.6	821.3
170°	827.1	826.0	826.0	826.0	826.0	826.0	826.3	826.9	827.5	828.0	828.7
172.5°	832.8	831.8	831.8	831.8	831.8	831.8	832.1	832.7	833.3	833.9	834.5
175°	838.8	837.9	837.9	837.9	837.9	837.9	838.2	838.8	839.4	840.0	840.5
177.5°	841.7	841.0	841.0	841.0	841.0	841.0	841.2	841.7	842.1	842.6	843.1
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1646.2	1652.3	1660.2	1672.0	1681.0	1688.8	1690.5	1692.7	1698.4	1707.8	1715.1
5°	1656.8	1672.9	1698.9	1724.1	1751.4	1773.9	1794.9	1809.6	1823.6	1853.1	1876.9
7.5°	1653.5	1689.3	1730.0	1775.3	1821.1	1865.5	1906.7	1943.6	1980.3	2023.2	2072.2
10°	1651.2	1693.3	1747.9	1806.1	1869.9	1932.2	1992.5	2039.5	2094.2	2143.2	2205.6
12.5°	1640.6	1701.1	1766.5	1840.8	1919.2	1991.1	2070.5	2135.4	2197.9	2268.8	2341.3
15°	1626.7	1700.3	1783.0	1881.8	2000.9	2087.9	2169.2	2282.0	2359.1	2436.2	2539.9
17.5°	1601.3	1691.1	1794.5	1922.9	2022.2	2139.0	2261.4	2350.5	2454.4	2563.0	2656.9
20°	1581.1	1685.6	1801.2	1927.3	2054.2	2181.0	2299.5	2406.0	2513.3	2638.8	2715.8
22.5°	1560.9	1664.3	1784.4	1918.4	2054.8	2188.3	2322.5	2447.6	2568.2	2694.8	2793.2
25°	1518.0	1640.7	1771.0	1907.7	2042.3	2189.5	2349.3	2488.8	2638.0	2768.4	2861.6
27.5°	1474.6	1587.0	1716.8	1855.5	2005.0	2179.0	2367.0	2525.5	2675.0	2768.4	2797.7
30°	1435.4	1554.5	1673.7	1814.5	1976.4	2170.5	2370.3	2551.8	2674.5	2715.1	2684.9
32.5°	1395.5	1503.5	1621.5	1765.8	1937.7	2149.8	2374.8	2536.1	2609.9	2578.9	2456.2
35°	1325.3	1422.7	1537.0	1681.3	1879.0	2138.3	2356.3	2465.6	2447.4	2272.2	2040.9
37.5°	1250.2	1329.5	1435.4	1586.4	1818.2	2092.8	2276.6	2292.8	2135.1	1866.1	1598.9
40°	1190.8	1262.2	1370.9	1528.6	1771.0	2047.9	2196.5	2131.3	1886.7	1587.4	1364.6
42.5°	1133.0	1193.3	1298.0	1468.0	1726.2	1986.8	2077.1	1935.1	1652.9	1369.9	1167.2
45°	1035.2	1091.9	1197.0	1371.5	1634.4	1869.9	1858.0	1611.2	1328.8	1101.1	932.8
47.5°	942.4	992.0	1090.7	1268.8	1526.6	1694.7	1583.2	1320.7	1081.1	898.4	778.4
50°	876.7	925.9	1024.0	1199.9	1440.3	1562.9	1403.8	1150.8	931.5	780.1	684.7
52.5°	814.0	861.9	951.6	1123.0	1336.0	1409.3	1238.4	1003.9	821.0	690.4	608.5
55°	726.1	762.5	843.1	1007.1	1166.3	1183.0	1010.0	813.7	663.0	571.9	515.9
57.5°	636.5	667.9	747.5	878.2	989.7	981.1	816.9	647.2	545.7	478.0	437.3
60°	578.2	609.0	679.1	791.3	875.4	846.0	695.3	558.6	471.7	422.0	389.7
62.5°	523.8	548.0	613.5	695.4	755.9	722.6	594.3	481.2	412.2	370.3	344.8
65°	445.1	464.7	517.2	560.0	593.6	561.4	454.9	376.4	326.6	297.2	279.6
67.5°	370.1	382.6	415.9	431.3	455.0	419.6	342.1	289.4	261.2	236.3	224.2
70°	323.1	332.2	349.7	362.3	368.6	332.2	274.7	236.2	212.3	194.8	187.2
72.5°	276.0	284.0	287.5	297.8	294.6	260.5	220.9	190.2	173.1	161.2	151.2
75°	211.0	214.5	211.0	206.8	197.6	173.8	146.5	131.1	118.4	112.8	109.3
77.5°	153.7	152.7	147.8	141.3	125.7	110.8	96.0	90.9	85.3	82.4	81.1
80°	118.4	115.7	111.5	100.9	87.6	77.1	73.6	70.1	67.9	64.5	63.8
82.5°	88.2	86.5	79.5	70.6	61.3	56.4	53.4	52.2	50.0	48.2	48.1
85°	47.0	44.9	37.2	32.3	30.9	29.4	28.7	28.7	25.9	25.2	25.2
87.5°	15.6	12.5	12.2	10.9	11.1	10.4	11.4	10.6	10.4	11.1	10.2
90°	2.1	3.6	5.1	6.5	8.2	10.2	12.0	14.0	15.9	16.5	17.0
92.5°	17.0	18.0	19.0	20.0	21.0	22.1	23.3	24.3	25.4	25.9	26.4
95°	40.0	41.1	42.2	43.2	44.2	45.5	46.6	47.8	49.0	49.6	50.1
97.5°	70.1	70.9	71.7	72.4	73.2	74.1	74.9	75.8	76.7	77.3	78.0
100°	90.9	91.8	92.6	93.5	94.3	95.1	95.9	96.6	97.3	97.7	98.2
102.5°	114.4	114.9	115.4	115.9	116.7	117.7	118.7	119.6	120.6	121.0	121.5
105°	149.2	149.5	149.8	150.1	150.9	152.2	153.6	154.9	156.2	156.2	156.2
107.5°	189.8	190.0	190.2	190.4	190.7	191.3	191.8	192.3	192.9	193.3	193.8
110°	215.4	215.7	216.0	216.2	216.6	216.9	217.1	217.5	217.8	218.4	218.9



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	241.7	241.9	242.1	242.3	242.4	242.5	242.5	242.5	242.6	243.3	244.1
115°	281.7	282.1	282.6	283.0	283.1	282.9	282.6	282.2	282.0	282.1	282.2
117.5°	321.6	321.8	322.2	322.4	322.4	322.0	321.6	321.3	320.8	320.8	320.8
120°	347.1	347.9	348.8	349.7	349.7	349.0	348.3	347.6	346.8	346.7	346.5
122.5°	372.7	373.4	374.1	374.7	374.8	374.4	374.1	373.7	373.3	372.9	372.6
125°	412.1	412.6	413.0	413.5	413.5	413.2	413.0	412.6	412.3	411.8	411.2
127.5°	449.2	450.1	451.0	452.0	452.3	452.0	451.7	451.3	451.0	450.1	449.3
130°	473.8	474.9	476.1	477.2	477.7	477.2	476.8	476.4	475.9	475.3	474.7
132.5°	498.1	499.3	500.4	501.7	502.0	501.8	501.4	501.1	500.8	500.1	499.4
135°	535.0	535.9	536.8	537.6	538.1	537.9	537.7	537.6	537.4	536.8	536.3
137.5°	569.3	570.0	570.8	571.5	572.0	572.4	572.8	573.2	573.5	572.9	572.3
140°	593.1	593.9	594.6	595.3	595.8	595.9	596.0	596.2	596.4	596.2	596.0
142.5°	614.8	615.5	616.3	617.0	617.5	617.8	618.0	618.3	618.6	618.4	618.3
145°	648.3	648.5	648.8	649.2	649.5	650.0	650.4	650.9	651.3	651.1	650.9
147.5°	678.1	678.7	679.2	679.8	680.2	680.6	681.0	681.4	681.9	681.9	681.9
150°	698.6	698.8	699.2	699.5	699.7	700.0	700.3	700.6	700.9	700.9	700.9
152.5°	715.6	716.0	716.5	716.8	717.1	717.3	717.5	717.6	717.8	718.1	718.4
155°	742.0	742.0	742.0	742.0	742.0	742.2	742.3	742.4	742.6	743.2	743.8
157.5°	764.6	764.4	764.2	764.0	764.0	764.1	764.2	764.4	764.5	765.1	765.7
160°	778.7	778.5	778.1	777.8	777.7	777.7	777.7	777.7	777.7	778.5	779.2
162.5°	791.3	790.9	790.5	790.1	790.0	790.1	790.1	790.3	790.4	791.1	791.8
165°	807.7	807.3	806.8	806.4	806.1	806.1	806.1	806.1	806.1	807.0	807.9
167.5°	820.6	820.1	819.5	818.9	818.7	818.8	818.9	819.0	819.1	820.0	820.9
170°	828.0	827.5	826.9	826.3	826.0	826.0	826.0	826.0	826.0	827.1	828.0
172.5°	833.9	833.3	832.7	832.1	831.8	831.8	831.8	831.8	831.8	832.8	833.7
175°	840.0	839.4	838.8	838.2	837.9	837.9	837.9	837.9	837.9	838.8	839.7
177.5°	842.6	842.1	841.7	841.2	841.0	841.0	841.0	841.0	841.0	841.7	842.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1726.9	1726.9	1729.1	1737.6	1738.7	1746.0	1743.7
5°	1897.9	1911.2	1916.1	1937.2	1949.8	1955.4	1944.2
7.5°	2107.0	2144.7	2162.4	2184.4	2204.0	2209.8	2194.5
10°	2259.6	2298.8	2331.7	2352.1	2371.0	2383.6	2399.8
12.5°	2407.0	2455.2	2486.5	2515.2	2534.7	2550.7	2553.3
15°	2567.2	2640.1	2695.5	2736.1	2756.5	2767.0	2762.8
17.5°	2728.8	2796.4	2835.8	2877.3	2905.5	2906.9	2907.7
20°	2820.2	2886.1	2931.7	2962.5	2994.1	2992.7	2999.6
22.5°	2881.4	2933.2	2968.1	2990.5	3001.3	2996.1	2997.4
25°	2909.9	2925.3	2919.1	2883.3	2874.3	2841.3	2846.9
27.5°	2762.5	2689.6	2614.2	2517.2	2440.7	2379.5	2382.7
30°	2562.3	2433.4	2286.2	2162.8	2052.1	2021.2	1955.4
32.5°	2282.5	2089.1	1916.7	1801.8	1706.7	1681.0	1623.4
35°	1808.2	1620.4	1443.1	1336.5	1294.5	1235.6	1234.9
37.5°	1405.5	1240.1	1146.3	1066.4	1024.5	988.9	985.4
40°	1182.3	1053.4	982.6	925.1	883.8	857.1	850.9
42.5°	1026.4	922.2	855.9	820.3	788.5	774.7	764.5
45°	838.2	768.1	721.8	689.6	674.9	664.4	658.8
47.5°	701.2	654.2	622.7	601.2	589.2	578.2	581.1
50°	626.6	588.0	564.9	544.6	535.5	527.7	528.4
52.5°	566.6	532.0	513.3	498.6	487.2	481.8	479.1
55°	480.8	459.1	440.1	429.6	423.3	415.6	413.5
57.5°	410.1	393.3	377.9	366.0	364.4	357.0	358.0
60°	363.0	349.0	336.4	330.1	325.2	318.9	321.0
62.5°	324.3	312.5	301.1	295.9	291.0	286.3	287.3
65°	265.6	254.4	247.4	244.6	242.5	240.4	238.3
67.5°	211.7	204.8	200.5	194.4	190.1	189.4	187.3
70°	178.0	168.9	161.2	153.5	151.4	150.7	151.4
72.5°	142.7	137.0	134.8	131.1	130.6	128.9	130.1
75°	107.3	105.1	103.7	100.9	100.9	100.9	100.9
77.5°	79.1	77.8	77.0	76.4	75.7	74.7	74.5
80°	61.7	61.0	59.6	59.6	58.9	59.6	58.9
82.5°	46.5	46.4	45.0	45.0	44.3	43.9	44.3
85°	23.8	23.1	24.5	23.1	23.8	22.5	23.8
87.5°	10.3	10.3	9.9	10.0	9.5	10.6	9.5
90°	17.7	18.3	18.6	19.0	19.3	19.5	19.9
92.5°	26.8	27.3	27.5	27.3	27.1	26.9	26.8
95°	50.7	51.4	51.6	51.6	51.6	51.6	51.6
97.5°	78.6	79.4	79.6	79.6	79.5	79.5	79.5
100°	98.6	99.1	99.4	99.7	100.0	100.3	100.6
102.5°	121.9	122.3	122.5	122.5	122.4	122.3	122.3
105°	156.2	156.2	156.3	156.7	156.9	157.2	157.6
107.5°	194.3	194.7	194.9	194.7	194.6	194.4	194.2
110°	219.5	220.1	220.3	220.0	219.6	219.4	219.1



TEST NUMBER: P332475-940

CATALOG NUMBER: S123RDIW-S1165D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	244.8	245.5	245.8	245.8	245.7	245.6	245.6
115°	282.4	282.6	282.6	282.4	282.2	282.1	282.0
117.5°	320.7	320.7	320.6	320.1	319.7	319.3	318.9
120°	346.3	346.3	346.0	345.7	345.4	345.1	344.8
122.5°	372.1	371.8	371.4	371.0	370.5	370.1	369.7
125°	410.5	410.0	409.4	408.8	408.2	407.6	407.1
127.5°	448.5	447.7	446.9	446.3	445.6	445.0	444.3
130°	474.1	473.5	472.7	471.7	470.6	469.7	468.6
132.5°	498.6	497.9	497.2	496.4	495.6	494.8	494.0
135°	535.7	535.1	534.7	534.3	534.0	533.8	533.4
137.5°	571.7	571.1	570.5	570.0	569.4	568.8	568.3
140°	595.9	595.8	595.1	594.1	593.1	592.1	591.0
142.5°	618.1	618.0	617.5	616.7	615.9	615.1	614.3
145°	650.9	650.7	650.3	649.7	649.2	648.5	648.0
147.5°	681.9	681.9	681.4	680.6	679.7	678.8	677.9
150°	700.9	700.9	700.4	699.5	698.7	697.9	697.0
152.5°	718.5	718.8	718.5	717.7	717.0	716.2	715.5
155°	744.4	744.9	744.8	743.7	742.7	741.6	740.7
157.5°	766.3	767.0	766.8	766.0	765.2	764.4	763.5
160°	779.9	780.6	780.7	780.2	779.5	778.9	778.4
162.5°	792.6	793.4	793.3	792.3	791.4	790.4	789.4
165°	808.8	809.7	809.6	808.6	807.5	806.6	805.5
167.5°	821.9	822.8	822.8	821.9	820.9	820.0	819.1
170°	829.1	830.1	830.1	829.1	828.0	827.1	826.0
172.5°	834.6	835.4	835.4	834.4	833.4	832.3	831.3
175°	840.5	841.4	841.4	840.3	839.3	838.3	837.2
177.5°	843.1	843.8	843.7	842.9	842.0	841.2	840.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6

(END OF REPORT)