

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332441

Luminaire Tested: **S123RDIW-S775D1030U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332441
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1030U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6493.7 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33				
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	1.9
10°-20°	337.3	5.2
20°-30°	485.7	7.5
30°-40°	547.1	8.4
40°-50°	523.4	8.1
50°-60°	428.6	6.6
60°-70°	289.2	4.5
70°-80°	145.5	2.2
80°-90°	42.3	0.7
90°-100°	84.0	1.3
100°-110°	251.5	3.9
110°-120°	427.7	6.6
120°-130°	562.6	8.7
130°-140°	632.3	9.7
140°-150°	621.6	9.6
150°-160°	523.3	8.1
160°-170°	348.3	5.4
170°-180°	122.0	1.9
0°-30°	944.3	14.5
0°-40°	1491.4	23.0
0°-60°	2443.4	37.6
0°-90°	2920.4	45.0
90°-120°	763.2	11.8
90°-150°	2579.7	39.7
90°-180°	3573.0	55.0
0°-180°	6493.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	11	24	28	30	6
95°	60	67	75	79	79	67
105°	228	230	239	239	241	244
115°	431	433	432	432	432	426
125°	630	633	631	627	623	562
135°	818	823	823	819	817	630
145°	992	994	997	996	992	619
155°	1136	1136	1137	1140	1134	523
165°	1237	1234	1234	1239	1233	349
175°	1287	1283	1283	1288	1282	122
180°	1290	1290	1290	1290	1290	



TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.3	18.7	17.1	15.5	13.9	13.4	14.0	14.6	15.2	15.8	15.7
90°	1.0	3.3	5.5	7.8	10.0	12.6	15.5	18.5	21.4	24.3	25.2
92.5°	24.5	26.0	27.6	29.1	30.6	32.2	33.9	35.6	37.2	38.9	39.6
95°	59.8	61.3	62.9	64.5	66.1	67.8	69.6	71.4	73.2	75.0	75.9
97.5°	106.2	107.3	108.5	109.7	110.9	112.1	113.4	114.7	116.0	117.3	118.4
100°	137.8	139.1	140.5	141.8	143.2	144.4	145.6	146.7	147.8	148.9	149.6
102.5°	174.3	175.1	175.9	176.7	177.5	178.6	180.1	181.6	183.1	184.6	185.3
105°	228.0	228.4	228.9	229.3	229.8	231.0	233.0	235.0	237.1	239.1	239.1
107.5°	290.4	290.6	290.9	291.2	291.4	292.0	292.8	293.6	294.4	295.2	295.9
110°	329.3	329.7	330.2	330.6	331.1	331.5	332.0	332.4	332.9	333.3	334.2



TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	369.8	370.1	370.3	370.6	370.9	371.0	371.1	371.2	371.3	371.4	372.5
115°	430.6	431.2	431.9	432.6	433.3	433.4	432.9	432.5	432.0	431.6	431.8
117.5°	491.8	492.2	492.7	493.1	493.6	493.5	492.9	492.3	491.7	491.2	491.1
120°	529.9	531.2	532.6	533.9	535.3	535.4	534.2	533.1	532.0	530.9	530.6
122.5°	569.6	570.6	571.6	572.5	573.5	573.7	573.2	572.6	572.0	571.4	570.8
125°	630.2	630.8	631.5	632.2	632.9	633.0	632.5	632.1	631.6	631.2	630.3
127.5°	686.1	687.5	689.0	690.4	691.8	692.3	691.8	691.3	690.8	690.3	689.1
130°	723.4	725.2	727.0	728.8	730.6	731.1	730.5	729.8	729.1	728.4	727.5
132.5°	760.6	762.4	764.2	766.1	767.9	768.5	768.0	767.5	767.0	766.5	765.4
135°	817.6	818.9	820.3	821.6	823.0	823.5	823.3	823.1	822.9	822.6	821.7
137.5°	870.3	871.4	872.5	873.6	874.8	875.6	876.2	876.8	877.4	878.0	877.0
140°	906.7	907.9	909.0	910.1	911.2	911.9	912.1	912.4	912.6	912.8	912.6
142.5°	940.0	941.1	942.2	943.3	944.5	945.2	945.6	946.0	946.5	946.9	946.6
145°	991.8	992.3	992.7	993.2	993.6	994.2	994.9	995.6	996.2	996.9	996.7
147.5°	1037.2	1038.0	1038.8	1039.7	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7
150°	1068.8	1069.3	1069.7	1070.2	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9
152.5°	1094.8	1095.4	1096.0	1096.7	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2
155°	1135.7	1135.7	1135.7	1135.7	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6
157.5°	1170.6	1170.3	1170.0	1169.7	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1
160°	1192.4	1192.0	1191.5	1191.1	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5
162.5°	1211.9	1211.3	1210.6	1210.0	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0
165°	1237.0	1236.3	1235.7	1235.0	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3
167.5°	1257.1	1256.2	1255.3	1254.4	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2
170°	1268.4	1267.5	1266.6	1265.7	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9
172.5°	1277.3	1276.4	1275.5	1274.6	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7
175°	1286.7	1285.8	1284.9	1284.0	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0
177.5°	1290.5	1289.8	1289.1	1288.3	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	15.7	15.7	15.7	15.7	15.6	15.5	15.4	15.3
90°	26.1	27.0	27.9	28.6	29.0	29.5	29.9	30.4
92.5°	40.3	41.1	41.8	42.0	41.7	41.5	41.2	40.9
95°	76.8	77.7	78.6	79.0	79.0	79.0	79.0	79.0
97.5°	119.4	120.4	121.5	121.9	121.8	121.8	121.7	121.6
100°	150.3	151.0	151.6	152.2	152.6	153.1	153.5	154.0
102.5°	185.9	186.6	187.3	187.6	187.5	187.4	187.3	187.2
105°	239.1	239.1	239.1	239.3	239.8	240.2	240.7	241.1
107.5°	296.7	297.4	298.1	298.3	298.1	297.8	297.5	297.2
110°	335.1	336.0	336.9	337.1	336.7	336.2	335.8	335.3



TEST NUMBER: P332441

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	373.6	374.6	375.7	376.2	376.1	376.0	376.0	375.9
115°	432.0	432.3	432.5	432.5	432.3	432.0	431.8	431.6
117.5°	491.1	491.0	491.0	490.6	490.0	489.4	488.7	488.1
120°	530.4	530.2	530.0	529.6	529.2	528.7	528.3	527.8
122.5°	570.2	569.6	569.1	568.4	567.8	567.2	566.6	565.9
125°	629.4	628.5	627.6	626.7	625.8	624.9	624.0	623.1
127.5°	687.8	686.6	685.3	684.1	683.1	682.1	681.0	680.0
130°	726.6	725.7	724.8	723.6	722.0	720.4	718.9	717.3
132.5°	764.4	763.3	762.2	761.1	759.8	758.6	757.4	756.2
135°	820.8	819.9	819.0	818.4	817.9	817.5	817.0	816.6
137.5°	876.1	875.1	874.2	873.3	872.4	871.6	870.7	869.9
140°	912.4	912.1	911.9	911.0	909.4	907.9	906.3	904.7
142.5°	946.4	946.2	946.0	945.2	944.0	942.8	941.6	940.4
145°	996.5	996.2	996.0	995.4	994.5	993.6	992.7	991.8
147.5°	1043.7	1043.7	1043.7	1043.0	1041.7	1040.3	1039.0	1037.6
150°	1072.9	1072.9	1072.9	1072.2	1070.9	1069.5	1068.2	1066.8
152.5°	1099.5	1099.9	1100.3	1099.9	1098.7	1097.5	1096.3	1095.2
155°	1138.5	1139.4	1140.3	1140.0	1138.4	1136.8	1135.3	1133.7
157.5°	1172.0	1173.0	1173.9	1173.8	1172.5	1171.3	1170.0	1168.7
160°	1192.7	1193.8	1194.9	1195.0	1194.1	1193.2	1192.3	1191.4
162.5°	1212.1	1213.2	1214.4	1214.2	1212.8	1211.3	1209.9	1208.4
165°	1236.7	1238.0	1239.4	1239.3	1237.7	1236.1	1234.5	1233.0
167.5°	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8
170°	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4
172.5°	1276.1	1277.5	1278.9	1278.8	1277.2	1275.6	1274.0	1272.5
175°	1285.3	1286.7	1288.0	1287.9	1286.3	1284.7	1283.2	1281.6
177.5°	1289.4	1290.5	1291.6	1291.5	1290.2	1289.0	1287.7	1286.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7

(END OF REPORT)