

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332449

Luminaire Tested: **S123RDIW-S775D1535U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332449
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1535U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8240.9 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	57	71	64	58	53	52	47	44	40	37	35	30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	1.5
10°-20°	337.3	4.1
20°-30°	485.7	5.9
30°-40°	547.1	6.6
40°-50°	523.4	6.4
50°-60°	428.6	5.2
60°-70°	289.2	3.5
70°-80°	145.5	1.8
80°-90°	44.2	0.5
90°-100°	125.1	1.5
100°-110°	374.3	4.5
110°-120°	636.6	7.7
120°-130°	837.4	10.2
130°-140°	941.2	11.4
140°-150°	925.2	11.2
150°-160°	778.9	9.5
160°-170°	518.5	6.3
170°-180°	181.6	2.2
0°-30°	944.3	11.5
0°-40°	1491.4	18.1
0°-60°	2443.4	29.7
0°-90°	2922.3	35.5
90°-120°	1136.0	13.8
90°-150°	3839.7	46.6
90°-180°	5319.0	64.5
0°-180°	8240.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	2	17	36	42	45	8
95°	89	100	112	117	118	100
105°	339	343	356	356	359	363
115°	641	645	642	644	642	634
125°	938	942	940	933	927	836
135°	1217	1225	1224	1219	1215	937
145°	1476	1479	1484	1482	1476	922
155°	1690	1690	1692	1697	1687	778
165°	1841	1837	1837	1845	1835	519
175°	1915	1909	1909	1917	1908	182
180°	1920	1920	1920	1920	1920	



TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.4	19.0	17.7	16.3	14.9	14.6	15.5	16.4	17.3	18.1	18.2
90°	1.5	4.9	8.2	11.6	14.9	18.8	23.1	27.5	31.8	36.2	37.5
92.5°	36.5	38.8	41.0	43.3	45.6	48.0	50.5	52.9	55.4	57.9	59.0
95°	89.0	91.3	93.7	96.0	98.4	100.9	103.5	106.2	108.9	111.6	112.9
97.5°	158.0	159.8	161.5	163.3	165.0	166.8	168.8	170.7	172.7	174.6	176.2
100°	205.1	207.1	209.1	211.1	213.1	215.0	216.6	218.3	220.0	221.7	222.7
102.5°	259.4	260.6	261.8	263.0	264.2	265.9	268.1	270.3	272.5	274.7	275.8
105°	339.3	340.0	340.6	341.3	342.0	343.8	346.8	349.8	352.9	355.9	355.9
107.5°	432.2	432.6	433.0	433.4	433.8	434.6	435.8	437.0	438.2	439.4	440.5
110°	490.1	490.8	491.4	492.1	492.8	493.4	494.1	494.8	495.4	496.1	497.5



TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	550.4	550.8	551.2	551.6	552.0	552.3	552.4	552.5	552.7	552.8	554.4
115°	640.9	641.9	642.9	643.9	644.9	645.1	644.4	643.7	643.1	642.4	642.7
117.5°	732.0	732.6	733.3	734.0	734.6	734.5	733.7	732.8	731.9	731.1	731.0
120°	788.7	790.7	792.7	794.7	796.7	796.9	795.2	793.5	791.8	790.2	789.8
122.5°	847.8	849.2	850.7	852.2	853.7	854.0	853.1	852.2	851.4	850.5	849.6
125°	937.9	938.9	940.0	941.0	942.0	942.1	941.5	940.8	940.1	939.5	938.1
127.5°	1021.2	1023.3	1025.5	1027.6	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6
130°	1076.7	1079.4	1082.0	1084.7	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9
132.5°	1132.2	1134.8	1137.5	1140.2	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3
135°	1216.9	1218.9	1220.9	1222.9	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1
137.5°	1295.3	1297.0	1298.7	1300.4	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4
140°	1349.6	1351.3	1353.0	1354.6	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3
142.5°	1399.1	1400.7	1402.4	1404.1	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0
145°	1476.3	1477.0	1477.6	1478.3	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5
147.5°	1543.8	1545.0	1546.2	1547.5	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5
150°	1590.9	1591.6	1592.2	1592.9	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9
152.5°	1629.5	1630.4	1631.4	1632.3	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1
155°	1690.4	1690.4	1690.4	1690.4	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3
157.5°	1742.3	1741.9	1741.5	1741.1	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1
160°	1774.9	1774.2	1773.5	1772.8	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5
162.5°	1803.8	1802.9	1801.9	1801.0	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5
165°	1841.2	1840.2	1839.2	1838.2	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7
167.5°	1871.1	1869.7	1868.4	1867.0	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3
170°	1887.9	1886.6	1885.3	1883.9	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3
172.5°	1901.2	1899.9	1898.5	1897.2	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3
175°	1915.1	1913.8	1912.4	1911.1	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1
177.5°	1920.8	1919.8	1918.7	1917.6	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	18.3	18.4	18.5	18.5	18.4	18.4	18.3	18.3
90°	38.9	40.2	41.6	42.6	43.2	43.9	44.6	45.2
92.5°	60.0	61.1	62.2	62.5	62.1	61.7	61.3	60.9
95°	114.3	115.6	116.9	117.6	117.6	117.6	117.6	117.6
97.5°	177.7	179.2	180.8	181.5	181.4	181.2	181.1	181.0
100°	223.7	224.7	225.7	226.5	227.2	227.9	228.5	229.2
102.5°	276.8	277.8	278.8	279.2	279.1	278.9	278.8	278.7
105°	355.9	355.9	355.9	356.2	356.9	357.6	358.2	358.9
107.5°	441.6	442.6	443.7	444.0	443.6	443.2	442.8	442.4
110°	498.8	500.1	501.5	501.8	501.1	500.5	499.8	499.1



TEST NUMBER: P332449

CATALOG NUMBER: S123RDIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	556.0	557.6	559.2	560.0	559.9	559.7	559.6	559.4
115°	643.1	643.4	643.7	643.7	643.4	643.1	642.7	642.4
117.5°	730.9	730.9	730.8	730.3	729.3	728.4	727.5	726.5
120°	789.5	789.2	788.8	788.3	787.7	787.0	786.3	785.6
122.5°	848.7	847.9	847.0	846.1	845.2	844.2	843.3	842.3
125°	936.8	935.4	934.1	932.7	931.4	930.1	928.7	927.4
127.5°	1023.8	1021.9	1020.0	1018.3	1016.8	1015.2	1013.7	1012.1
130°	1081.5	1080.2	1078.9	1077.0	1074.7	1072.3	1070.0	1067.6
132.5°	1137.7	1136.1	1134.5	1132.8	1131.0	1129.2	1127.3	1125.5
135°	1221.8	1220.4	1219.1	1218.1	1217.4	1216.7	1216.1	1215.4
137.5°	1304.0	1302.6	1301.2	1299.8	1298.5	1297.3	1296.0	1294.7
140°	1358.0	1357.7	1357.3	1356.0	1353.6	1351.3	1348.9	1346.6
142.5°	1408.7	1408.3	1408.0	1406.9	1405.1	1403.3	1401.5	1399.7
145°	1483.1	1482.8	1482.5	1481.6	1480.3	1479.0	1477.6	1476.3
147.5°	1553.5	1553.5	1553.5	1552.5	1550.5	1548.5	1546.4	1544.4
150°	1596.9	1596.9	1596.9	1595.9	1593.9	1591.9	1589.9	1587.9
152.5°	1636.6	1637.1	1637.7	1637.1	1635.3	1633.6	1631.8	1630.1
155°	1694.6	1695.9	1697.3	1696.8	1694.4	1692.1	1689.7	1687.4
157.5°	1744.5	1745.9	1747.3	1747.1	1745.2	1743.3	1741.4	1739.6
160°	1775.2	1776.9	1778.5	1778.7	1777.4	1776.0	1774.7	1773.3
162.5°	1804.1	1805.8	1807.5	1807.3	1805.1	1803.0	1800.8	1798.7
165°	1840.7	1842.7	1844.7	1844.6	1842.2	1839.9	1837.5	1835.2
167.5°	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2
170°	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9
172.5°	1899.3	1901.4	1903.5	1903.4	1901.0	1898.7	1896.3	1894.0
175°	1913.1	1915.1	1917.1	1916.9	1914.6	1912.2	1909.9	1907.6
177.5°	1919.2	1920.8	1922.4	1922.3	1920.4	1918.5	1916.7	1914.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6

(END OF REPORT)