

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332433

Luminaire Tested: **S123RDIW-S775D460U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332433
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D460U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4516.7 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65																				
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55																				
2	93	85	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47																				
3	85	75	68	62	80	71	65	60	63	58	54	56	52	49	49	46	44	40																				
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	44	41	38	35																				
5	72	60	52	46	67	57	50	44	51	45	40	45	41	37	40	36	33	31																				
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27																				
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	33	29	26	24																				
8	57	45	37	32	54	43	35	30	38	32	28	34	30	26	31	27	24	22																				
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20																				
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	27	23	20	18																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	2.7
10°-20°	337.3	7.5
20°-30°	485.7	10.8
30°-40°	547.1	12.1
40°-50°	523.4	11.6
50°-60°	428.6	9.5
60°-70°	289.2	6.4
70°-80°	145.5	3.2
80°-90°	40.2	0.9
90°-100°	37.6	0.8
100°-110°	112.5	2.5
110°-120°	191.3	4.2
120°-130°	251.7	5.6
130°-140°	282.9	6.3
140°-150°	278.0	6.2
150°-160°	234.1	5.2
160°-170°	155.8	3.4
170°-180°	54.6	1.2
0°-30°	944.3	20.9
0°-40°	1491.4	33.0
0°-60°	2443.4	54.1
0°-90°	2918.3	64.6
90°-120°	341.4	7.6
90°-150°	1153.9	25.5
90°-180°	1598.0	35.4
0°-180°	4516.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	0	5	11	13	14	4
95°	27	30	34	35	35	30
105°	102	103	107	107	108	109
115°	193	194	193	194	193	191
125°	282	283	282	280	279	251
135°	366	368	368	366	365	282
145°	444	445	446	445	444	277
155°	508	508	508	510	507	234
165°	553	552	552	554	552	156
175°	576	574	574	576	573	55
180°	577	577	577	577	577	



TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.2	18.3	16.5	14.7	12.8	12.0	12.3	12.5	12.8	13.1	13.0
90°	0.5	1.5	2.5	3.5	4.5	5.6	6.9	8.3	9.6	10.9	11.3
92.5°	11.0	11.7	12.3	13.0	13.7	14.4	15.2	15.9	16.7	17.4	17.7
95°	26.7	27.4	28.1	28.9	29.6	30.3	31.1	31.9	32.7	33.5	33.9
97.5°	47.5	48.0	48.5	49.1	49.6	50.1	50.7	51.3	51.9	52.5	52.9
100°	61.6	62.2	62.8	63.4	64.0	64.6	65.1	65.6	66.1	66.6	66.9
102.5°	77.9	78.3	78.7	79.0	79.4	79.9	80.6	81.2	81.9	82.6	82.9
105°	102.0	102.2	102.4	102.6	102.8	103.3	104.2	105.1	106.0	106.9	106.9
107.5°	129.9	130.0	130.1	130.2	130.4	130.6	131.0	131.3	131.7	132.1	132.4
110°	147.3	147.5	147.7	147.9	148.1	148.3	148.5	148.7	148.9	149.1	149.5



TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.4	165.5	165.7	165.8	165.9	166.0	166.0	166.1	166.1	166.1	166.6
115°	192.6	192.9	193.2	193.5	193.8	193.9	193.7	193.5	193.3	193.1	193.2
117.5°	220.0	220.2	220.4	220.6	220.8	220.7	220.5	220.2	220.0	219.7	219.7
120°	237.0	237.6	238.2	238.8	239.4	239.5	239.0	238.5	238.0	237.5	237.4
122.5°	254.8	255.2	255.7	256.1	256.5	256.6	256.4	256.1	255.9	255.6	255.3
125°	281.9	282.2	282.5	282.8	283.1	283.1	282.9	282.7	282.5	282.3	281.9
127.5°	306.9	307.5	308.2	308.8	309.5	309.7	309.5	309.2	309.0	308.8	308.2
130°	323.6	324.4	325.2	326.0	326.8	327.0	326.7	326.4	326.1	325.8	325.4
132.5°	340.2	341.0	341.9	342.7	343.5	343.8	343.5	343.3	343.1	342.9	342.4
135°	365.7	366.3	366.9	367.5	368.1	368.4	368.3	368.2	368.1	368.0	367.6
137.5°	389.3	389.8	390.3	390.8	391.3	391.7	391.9	392.2	392.5	392.7	392.3
140°	405.6	406.1	406.6	407.1	407.6	407.9	408.0	408.1	408.2	408.3	408.2
142.5°	420.5	421.0	421.5	422.0	422.5	422.8	423.0	423.2	423.4	423.5	423.4
145°	443.7	443.9	444.1	444.3	444.5	444.7	445.0	445.3	445.6	445.9	445.8
147.5°	464.0	464.3	464.7	465.0	465.4	465.7	466.0	466.3	466.6	466.9	466.9
150°	478.1	478.3	478.5	478.7	478.9	479.1	479.3	479.5	479.7	479.9	479.9
152.5°	489.7	490.0	490.3	490.5	490.8	491.0	491.1	491.3	491.4	491.5	491.7
155°	508.0	508.0	508.0	508.0	508.0	508.1	508.2	508.3	508.4	508.5	508.9
157.5°	523.6	523.5	523.4	523.2	523.1	523.1	523.2	523.3	523.3	523.4	523.8
160°	533.4	533.2	533.0	532.8	532.6	532.5	532.5	532.5	532.5	532.5	533.0
162.5°	542.1	541.8	541.5	541.2	541.0	540.9	540.9	541.0	541.1	541.2	541.7
165°	553.3	553.0	552.7	552.4	552.1	552.0	552.0	552.0	552.0	552.0	552.6
167.5°	562.3	561.9	561.5	561.1	560.7	560.5	560.6	560.7	560.8	560.8	561.5
170°	567.4	567.0	566.6	566.2	565.8	565.6	565.6	565.6	565.6	565.6	566.3
172.5°	571.4	571.0	570.6	570.2	569.7	569.5	569.5	569.5	569.5	569.5	570.2
175°	575.5	575.1	574.7	574.3	573.9	573.7	573.7	573.7	573.7	573.7	574.3
177.5°	577.3	576.9	576.6	576.3	576.0	575.8	575.8	575.8	575.8	575.8	576.3
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9



TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	12.9	12.7	12.6	12.5	12.4	12.2	12.1	11.9
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	18.0	18.4	18.7	18.8	18.7	18.5	18.4	18.3
95°	34.3	34.7	35.1	35.3	35.3	35.3	35.3	35.3
97.5°	53.4	53.9	54.3	54.5	54.5	54.5	54.4	54.4
100°	67.2	67.5	67.8	68.1	68.3	68.5	68.7	68.9
102.5°	83.2	83.5	83.8	83.9	83.9	83.8	83.8	83.7
105°	106.9	106.9	106.9	107.0	107.3	107.5	107.7	107.9
107.5°	132.7	133.0	133.3	133.4	133.3	133.2	133.1	133.0
110°	149.9	150.3	150.7	150.8	150.6	150.4	150.2	150.0



TEST NUMBER: P332433

CATALOG NUMBER: S123RDIW-S775D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.6	168.1	168.3	168.2	168.2	168.2	168.1
115°	193.3	193.4	193.5	193.5	193.4	193.3	193.2	193.1
117.5°	219.7	219.6	219.6	219.5	219.2	218.9	218.6	218.3
120°	237.3	237.2	237.1	236.9	236.7	236.5	236.3	236.1
122.5°	255.1	254.8	254.5	254.3	254.0	253.7	253.4	253.1
125°	281.5	281.1	280.7	280.3	279.9	279.5	279.1	278.7
127.5°	307.7	307.1	306.5	306.0	305.6	305.1	304.6	304.2
130°	325.0	324.6	324.2	323.7	323.0	322.3	321.6	320.8
132.5°	341.9	341.4	340.9	340.4	339.9	339.3	338.8	338.2
135°	367.2	366.8	366.4	366.1	365.9	365.7	365.5	365.3
137.5°	391.9	391.5	391.0	390.6	390.2	389.9	389.5	389.1
140°	408.1	408.0	407.9	407.5	406.8	406.1	405.4	404.7
142.5°	423.3	423.2	423.1	422.8	422.3	421.7	421.2	420.6
145°	445.7	445.6	445.5	445.3	444.9	444.5	444.1	443.7
147.5°	466.9	466.9	466.9	466.6	466.0	465.3	464.7	464.1
150°	479.9	479.9	479.9	479.6	479.0	478.4	477.8	477.2
152.5°	491.8	492.0	492.2	492.0	491.5	490.9	490.4	489.9
155°	509.3	509.7	510.1	509.9	509.2	508.5	507.8	507.1
157.5°	524.3	524.7	525.1	525.0	524.5	523.9	523.3	522.8
160°	533.5	534.0	534.5	534.5	534.1	533.7	533.3	532.9
162.5°	542.2	542.7	543.2	543.1	542.5	541.8	541.2	540.5
165°	553.2	553.8	554.4	554.3	553.6	552.9	552.2	551.5
167.5°	562.1	562.7	563.3	563.3	562.7	562.1	561.5	560.8
170°	567.0	567.7	568.4	568.4	567.7	567.0	566.3	565.6
172.5°	570.8	571.4	572.0	572.0	571.3	570.6	569.9	569.2
175°	574.9	575.5	576.1	576.1	575.4	574.7	574.0	573.3
177.5°	576.8	577.3	577.7	577.7	577.1	576.6	576.0	575.4
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9

(END OF REPORT)