

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332406-940

Luminaire Tested: **S123RDIW-S340D1535U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332406-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1535U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6685.3 lumens  
Efficiency: N/A  
Efficacy: 125.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - 90°-270°    - · - 135°-315°



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	45	45	45	27	27	27	18
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	23	23	16
2	83	76	70	66	73	67	62	58	51	48	45	35	34	32	21	20	20	13
3	76	67	60	55	66	59	54	49	45	41	38	31	29	27	19	18	17	12
4	69	59	52	46	61	52	46	42	40	36	32	28	25	23	17	16	15	10
5	63	53	45	39	56	47	40	36	36	31	28	25	22	20	15	14	13	9
6	58	47	39	34	51	42	35	31	32	27	24	23	20	18	14	13	11	8
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	11	10	7
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	10	9	6
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	9	8	6
10	43	32	25	20	38	28	22	19	22	18	15	16	13	11	10	9	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.7	0.7
10°-20°	149.1	2.2
20°-30°	234.2	3.5
30°-40°	244.4	3.7
40°-50°	209.1	3.1
50°-60°	159.4	2.4
60°-70°	102.2	1.5
70°-80°	49.1	0.7
80°-90°	18.0	0.3
90°-100°	65.2	1.0
100°-110°	310.9	4.7
110°-120°	746.8	11.2
120°-130°	951.0	14.2
130°-140°	1016.1	15.2
140°-150°	950.2	14.2
150°-160°	766.5	11.5
160°-170°	494.7	7.4
170°-180°	170.5	2.6
0°-30°	431.1	6.4
0°-40°	675.4	10.1
0°-60°	1044.0	15.6
0°-90°	1213.3	18.1
90°-120°	1123.0	16.8
90°-150°	4040.3	60.4
90°-180°	5472.0	81.9
0°-180°	6685.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	9
90°	40	1	40	1	40	18
95°	51	81	51	81	51	42
105°	59	397	59	397	59	134
115°	784	745	784	745	784	724
125°	1072	1050	1072	1050	1072	957
135°	1321	1308	1321	1308	1321	1019
145°	1524	1509	1524	1509	1524	951
155°	1660	1662	1660	1662	1660	765
165°	1749	1753	1749	1753	1749	494
175°	1788	1794	1788	1794	1788	170
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	9.6	9.9	9.5	9.5	9.4	9.4	9.1	8.8	9.0	8.6	7.9
90°	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3	33.2	32.0	28.2
92.5°	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9	36.0	34.2	31.2
95°	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5	43.4	41.3	38.1
97.5°	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7	45.3	42.9	64.3
100°	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7	46.4	44.0	90.2
102.5°	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0	80.3	87.7	138.2
105°	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1	239.5	291.9	318.6
107.5°	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2	496.7	535.1	530.9
110°	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7	591.5	601.2	598.0



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8	668.6	668.4	665.1
115°	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2	768.1	765.2	762.5
117.5°	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8	861.4	859.1	857.6
120°	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6	922.2	919.8	918.9
122.5°	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9	982.3	980.6	979.5
125°	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6	1067.1	1066.5	1065.3
127.5°	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6	1150.6	1149.7	1148.3
130°	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1	1201.0	1199.8	1198.6
132.5°	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2	1248.9	1247.8	1246.8
135°	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1	1319.9
137.5°	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7	1386.3	1384.8	1384.2
140°	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8	1427.6	1426.4	1425.5
142.5°	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8	1466.8	1465.9	1465.0
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2	1521.6	1521.1	1520.5
147.5°	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0	1570.5	1569.9	1569.2
150°	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9	1600.3	1599.7	1599.1
152.5°	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5	1626.4	1625.3	1625.0
155°	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0	1662.5	1661.0	1660.7
157.5°	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8	1694.0	1692.2	1692.6
160°	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0	1712.2	1710.4	1710.7
162.5°	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4	1728.4	1726.4	1726.6
165°	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4	1750.1	1747.7	1748.0
167.5°	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8	1764.8
170°	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3	1774.3
172.5°	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5	1783.2	1780.7	1780.5
175°	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1	1791.1	1789.0	1788.7
177.5°	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0	1794.1	1792.2	1792.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	7.5	6.6	6.2	5.4	5.4	4.9	5.4	5.6	6.3	6.2	6.9
90°	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3	4.3	7.2	10.3
92.5°	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8	24.0	23.1	22.3
95°	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3	69.2	57.1	44.9
97.5°	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5	158.0	152.6	147.0
100°	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3	231.2	237.1	243.1
102.5°	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7	300.0	304.3	308.4
105°	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3	400.6	403.8	407.1
107.5°	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4	507.0	509.6	512.3
110°	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9	578.3	580.6	583.0





TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2	646.3	648.5	650.6
115°	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2	747.0	748.8	750.6
117.5°	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0	845.3	847.4	849.6
120°	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8	906.5	909.2	911.9
122.5°	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7	967.9	970.1	972.2
125°	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4	1052.8	1055.3	1057.6
127.5°	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6	1135.0	1137.4	1139.7
130°	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7	1186.2	1188.6	1190.9
132.5°	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9	1235.2	1237.6	1239.9
135°	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8	1309.6	1311.3	1313.1
137.5°	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7	1374.0	1376.3	1378.5
140°	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4	1416.2	1418.0	1419.8
142.5°	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8	1455.6	1457.4	1459.2
145°	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0	1511.1	1513.2	1515.3
147.5°	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0	1562.5	1563.8	1565.1
150°	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0	1593.9	1594.8	1595.7
152.5°	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8	1622.3	1622.6	1623.1
155°	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3	1661.8	1661.2	1660.6
157.5°	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8	1693.8	1693.7	1693.6
160°	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1	1712.7	1712.4	1712.2
162.5°	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2	1730.4	1729.7	1728.8
165°	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0	1752.1	1751.2	1750.3
167.5°	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0	1768.9	1767.7	1766.6
170°	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7	1778.5	1777.3	1776.1
172.5°	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1	1784.7	1783.2	1781.8
175°	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3	1792.9	1791.4	1789.9
177.5°	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4	1795.3	1794.1	1793.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	7.3	8.5	9.4	10.3	11.2	11.9	12.3	12.5	12.9	13.2	13.4
90°	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3	35.6	36.7	37.6
92.5°	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9	39.9	41.7	42.8
95°	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5	47.5	49.6	50.6
97.5°	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7	50.0	52.4	53.8
100°	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7	51.1	53.5	54.8
102.5°	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0	65.7	58.3	54.9
105°	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1	134.6	82.2	56.3
107.5°	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2	419.7	381.3	342.3
110°	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7	571.9	562.1	536.0



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8	669.0	669.1	664.8
115°	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2	774.1	777.0	779.1
117.5°	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8	866.1	868.5	869.9
120°	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6	926.9	929.3	930.5
122.5°	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9	985.6	987.3	988.2
125°	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6	1068.3	1068.8	1069.4
127.5°	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6	1152.5	1153.4	1153.6
130°	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1	1203.4	1204.5	1204.8
132.5°	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2	1251.3	1252.5	1252.7
135°	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6
137.5°	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7	1389.1	1390.5	1390.9
140°	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8	1429.9	1431.1	1431.5
142.5°	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8	1468.7	1469.6	1469.7
145°	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2	1522.9	1523.4	1523.8
147.5°	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0	1571.6	1572.3	1571.8
150°	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9	1601.5	1602.0	1602.0
152.5°	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5	1628.5	1629.6	1629.4
155°	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0	1665.4	1667.0	1666.8
157.5°	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8	1697.5	1699.3	1699.1
160°	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0	1715.7	1717.4	1717.3
162.5°	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4	1732.4	1734.4	1734.5
165°	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4	1754.8	1757.2	1757.3
167.5°	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2
170°	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9
172.5°	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5	1787.9	1790.2	1790.1
175°	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1	1795.2	1797.3	1797.2
177.5°	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0	1797.9	1799.8	1799.6
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	13.8	13.6	13.7	14.0	13.7	13.6	13.8	13.4	13.2	12.9	12.5
90°	38.3	38.8	39.4	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3
92.5°	43.2	43.5	43.9	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9
95°	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5
97.5°	54.0	54.3	54.7	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7
100°	55.1	55.4	55.7	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7
102.5°	55.5	56.0	56.5	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0
105°	56.9	57.5	58.1	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1
107.5°	302.8	263.2	223.7	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2
110°	493.7	451.3	408.9	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	655.8	646.8	637.9	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8
115°	780.3	781.5	782.7	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2
117.5°	870.0	870.3	870.6	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8
120°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6
122.5°	988.5	988.6	988.9	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9
125°	1070.1	1070.6	1071.2	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6
127.5°	1153.1	1152.4	1151.8	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6
130°	1204.3	1203.6	1203.0	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1
132.5°	1251.9	1251.1	1250.2	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2
135°	1323.7	1322.9	1322.0	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9
137.5°	1390.4	1389.7	1389.1	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7
140°	1430.8	1430.3	1429.7	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8
142.5°	1468.9	1468.0	1467.2	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2
147.5°	1570.5	1569.1	1567.7	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0
150°	1601.1	1600.2	1599.3	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9
152.5°	1628.1	1626.7	1625.3	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5
155°	1665.0	1663.2	1661.4	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0
157.5°	1696.7	1694.4	1692.1	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8
160°	1715.2	1713.2	1711.1	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0
162.5°	1732.7	1730.8	1729.0	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4
165°	1755.2	1753.2	1751.1	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4
167.5°	1771.8	1769.5	1767.1	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5
170°	1781.5	1779.1	1776.7	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1
172.5°	1787.5	1784.9	1782.3	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5
175°	1794.7	1792.4	1790.0	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1
177.5°	1797.2	1794.8	1792.4	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	12.3	11.9	11.2	10.3	9.4	8.5	7.3	6.9	6.2	6.3	5.6
90°	33.2	32.0	28.2	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3
92.5°	36.0	34.2	31.2	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8
95°	43.4	41.3	38.1	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3
97.5°	45.3	42.9	64.3	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5
100°	46.4	44.0	90.2	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3
102.5°	80.3	87.7	138.2	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7
105°	239.5	291.9	318.6	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3
107.5°	496.7	535.1	530.9	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4
110°	591.5	601.2	598.0	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	668.6	668.4	665.1	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2
115°	768.1	765.2	762.5	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2
117.5°	861.4	859.1	857.6	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0
120°	922.2	919.8	918.9	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8
122.5°	982.3	980.6	979.5	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7
125°	1067.1	1066.5	1065.3	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4
127.5°	1150.6	1149.7	1148.3	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6
130°	1201.0	1199.8	1198.6	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7
132.5°	1248.9	1247.8	1246.8	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9
135°	1322.0	1321.1	1319.9	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8
137.5°	1386.3	1384.8	1384.2	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7
140°	1427.6	1426.4	1425.5	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4
142.5°	1466.8	1465.9	1465.0	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8
145°	1521.6	1521.1	1520.5	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0
147.5°	1570.5	1569.9	1569.2	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0
150°	1600.3	1599.7	1599.1	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0
152.5°	1626.4	1625.3	1625.0	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8
155°	1662.5	1661.0	1660.7	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3
157.5°	1694.0	1692.2	1692.6	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8
160°	1712.2	1710.4	1710.7	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1
162.5°	1728.4	1726.4	1726.6	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2
165°	1750.1	1747.7	1748.0	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0
167.5°	1767.1	1764.8	1764.8	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0
170°	1776.7	1774.3	1774.3	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7
172.5°	1783.2	1780.7	1780.5	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1
175°	1791.1	1789.0	1788.7	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3
177.5°	1794.1	1792.2	1792.0	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	5.4	4.9	5.4	5.4	6.2	6.6	7.5	7.9	8.6	9.0	8.8
90°	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3
92.5°	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9
95°	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5
97.5°	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7
100°	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7
102.5°	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0
105°	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1
107.5°	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2
110°	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7





TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8
115°	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2
117.5°	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8
120°	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6
122.5°	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9
125°	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6
127.5°	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6
130°	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1
132.5°	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2
135°	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9
137.5°	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7
140°	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8
142.5°	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8
145°	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2
147.5°	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0
150°	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9
152.5°	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5
155°	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0
157.5°	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8
160°	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0
162.5°	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4
165°	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4
167.5°	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5
170°	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1
172.5°	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5
175°	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1
177.5°	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	9.1	9.4	9.4	9.5	9.5	9.9	9.6
90°	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	571.9	562.1	536.0	493.7	451.3	408.9	366.6



TEST NUMBER: P332406-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)