

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332409-940

Luminaire Tested: **S123RDIW-S340D1535U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332409-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1535U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5905.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17
2	83	76	70	65	73	67	63	59	51	48	45	36	34	33	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	17	12
4	69	59	52	46	61	52	46	41	40	36	32	28	26	24	18	16	15	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	7
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	0.8
10°-20°	133.9	2.3
20°-30°	192.7	3.3
30°-40°	217.1	3.7
40°-50°	207.7	3.5
50°-60°	170.1	2.9
60°-70°	114.8	1.9
70°-80°	57.7	1.0
80°-90°	20.3	0.3
90°-100°	111.5	1.9
100°-110°	333.8	5.7
110°-120°	567.7	9.6
120°-130°	746.7	12.6
130°-140°	839.3	14.2
140°-150°	825.0	14.0
150°-160°	694.5	11.8
160°-170°	462.3	7.8
170°-180°	161.9	2.7
0°-30°	374.7	6.3
0°-40°	591.8	10.0
0°-60°	969.6	16.4
0°-90°	1162.4	19.7
90°-120°	1013.0	17.2
90°-150°	3423.9	58.0
90°-180°	4743.0	80.3
0°-180°	5905.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	1	15	32	38	40	6
95°	79	89	100	105	105	89
105°	303	306	317	318	320	324
115°	572	575	573	574	573	565
125°	836	840	838	832	827	746
135°	1085	1093	1092	1087	1084	836
145°	1316	1319	1323	1322	1316	822
155°	1507	1507	1509	1513	1505	694
165°	1642	1638	1638	1645	1636	463
175°	1708	1703	1702	1709	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.2	8.0	7.8	7.6	7.4	7.7	8.5	9.2	10.0	10.8	11.0
90°	1.3	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4
92.5°	32.5	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6
95°	79.4	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7
97.5°	140.9	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1
100°	182.9	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6
102.5°	231.3	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9
105°	302.6	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4
107.5°	385.4	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8
110°	437.0	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6



TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.8	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4
115°	571.5	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1
117.5°	652.7	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8
120°	703.3	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3
122.5°	756.0	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6
125°	836.3	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5
127.5°	910.6	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5
130°	960.1	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6
132.5°	1009.6	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9
135°	1085.1	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7
137.5°	1155.0	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0
140°	1203.5	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1247.6	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4
145°	1316.4	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9
147.5°	1376.6	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3
150°	1418.6	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0
152.5°	1453.0	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9
155°	1507.3	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9
157.5°	1553.6	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3
160°	1582.7	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4
162.5°	1608.5	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3
165°	1641.8	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6
167.5°	1668.5	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0
170°	1683.5	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3
172.5°	1695.3	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8
175°	1707.7	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1
177.5°	1712.8	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	11.1	11.2	11.4	11.5	11.6	11.6	11.7	11.7
90°	34.7	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	53.5	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	101.9	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	158.5	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	199.5	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	246.8	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	393.8	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	444.8	445.9	447.2	447.5	446.8	446.3	445.7	445.1



TEST NUMBER: P332409-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.8	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	704.0	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.8	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	835.4	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	912.9	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	964.4	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1014.5	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1089.5	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1162.8	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.9	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1256.2	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.5	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.4	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1511.1	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1555.6	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1583.0	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1608.7	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1641.4	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1693.6	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1705.9	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1711.4	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)