

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332208-935

Luminaire Tested: **S123DIW-S1000D1535U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332208-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1535U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8834.6 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	34
2	87	80	74	68	79	73	67	63	60	56	53	48	45	43	37	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	24	21	19	16
7	56	44	37	31	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.5
10°-20°	362.5	4.1
20°-30°	535.5	6.1
30°-40°	625.5	7.1
40°-50°	628.8	7.1
50°-60°	552.4	6.3
60°-70°	411.5	4.7
70°-80°	234.5	2.7
80°-90°	72.1	0.8
90°-100°	63.0	0.7
100°-110°	300.2	3.4
110°-120°	721.1	8.2
120°-130°	918.3	10.4
130°-140°	981.1	11.1
140°-150°	917.5	10.4
150°-160°	740.1	8.4
160°-170°	477.6	5.4
170°-180°	164.6	1.9
0°-30°	1026.3	11.6
0°-40°	1651.8	18.7
0°-60°	2833.0	32.1
0°-90°	3551.1	40.2
90°-120°	1084.3	12.3
90°-150°	3901.2	44.2
90°-180°	5283.0	59.8
0°-180°	8834.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	1	14	31	36	39	7
95°	78	29	40	48	49	97
105°	384	390	282	67	57	407
115°	720	728	739	751	757	710
125°	1014	1024	1030	1032	1035	905
135°	1263	1270	1276	1279	1276	972
145°	1457	1466	1469	1471	1471	912
155°	1605	1603	1604	1610	1603	739
165°	1693	1689	1688	1697	1689	478
175°	1732	1726	1727	1735	1726	165
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.6	24.5	24.5	24.5	24.5	24.6	25.2	25.7	26.3	26.8	26.9
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0
92.5°	23.9	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8
95°	78.5	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9
97.5°	157.8	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7
100°	217.6	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8
102.5°	285.5	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6
105°	383.6	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3
107.5°	487.1	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6
110°	556.0	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1



TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	622.0	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6
115°	719.5	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7
117.5°	814.0	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7
120°	872.7	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4
122.5°	932.5	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5
125°	1014.3	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4
127.5°	1093.6	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9
130°	1143.0	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6
132.5°	1190.4	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9
135°	1262.7	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4
137.5°	1324.5	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5
140°	1365.7	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5
142.5°	1403.8	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3
145°	1457.1	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2
147.5°	1507.3	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4
150°	1538.2	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2
152.5°	1566.0	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4
155°	1605.1	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2
157.5°	1635.5	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6
160°	1654.1	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2
162.5°	1671.5	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9
165°	1692.6	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8
167.5°	1709.1	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2
170°	1718.4	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5
172.5°	1724.6	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7
175°	1732.5	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4
177.5°	1734.6	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	26.9	26.9	26.9	26.9	27.0	27.2	27.3	27.4
90°	33.1	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	36.6	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.1	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	47.0	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	70.5	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	180.6	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	442.4	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	561.6	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332208-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.8	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	744.6	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	834.1	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	892.8	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	950.0	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1030.9	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1111.9	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1160.7	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1207.1	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1339.9	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1379.6	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1417.2	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1469.8	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1516.9	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1545.8	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1571.4	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1606.7	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1637.4	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1654.9	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1670.8	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1692.0	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1724.0	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1731.4	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1734.1	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)