

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332393-940

Luminaire Tested: **S123RDIW-S340D460U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332393-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D460U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2584.1 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.9
10°-20°	133.9	5.2
20°-30°	192.7	7.5
30°-40°	217.1	8.4
40°-50°	207.7	8.0
50°-60°	170.1	6.6
60°-70°	114.8	4.4
70°-80°	57.7	2.2
80°-90°	16.8	0.6
90°-100°	33.5	1.3
100°-110°	100.3	3.9
110°-120°	170.6	6.6
120°-130°	224.4	8.7
130°-140°	252.2	9.8
140°-150°	247.9	9.6
150°-160°	208.7	8.1
160°-170°	138.9	5.4
170°-180°	48.7	1.9
0°-30°	374.7	14.5
0°-40°	591.8	22.9
0°-60°	969.6	37.5
0°-90°	1158.9	44.8
90°-120°	304.4	11.8
90°-150°	1029.0	39.8
90°-180°	1425.0	55.1
0°-180°	2584.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	0	4	10	11	12	3
95°	24	27	30	31	32	27
105°	91	92	95	95	96	97
115°	172	173	172	172	172	170
125°	251	252	252	250	248	224
135°	326	328	328	327	326	251
145°	396	396	398	397	396	247
155°	453	453	453	455	452	208
165°	493	492	492	494	492	139
175°	513	512	512	514	511	49
180°	514	514	514	514	514	



TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.0	7.4	6.8	6.2	5.5	5.4	5.5	5.8	6.1	6.2	6.2
90°	0.4	1.3	2.2	3.1	4.0	5.0	6.2	7.4	8.6	9.7	10.1
92.5°	9.8	10.4	11.0	11.6	12.2	12.8	13.6	14.2	14.9	15.5	15.8
95°	23.8	24.4	25.1	25.8	26.4	27.0	27.7	28.4	29.2	29.9	30.2
97.5°	42.4	42.8	43.2	43.8	44.2	44.7	45.2	45.7	46.3	46.8	47.2
100°	54.9	55.5	56.0	56.5	57.1	57.6	58.1	58.5	58.9	59.4	59.7
102.5°	69.5	69.8	70.2	70.4	70.8	71.2	71.9	72.4	73.0	73.7	73.9
105°	91.0	91.1	91.3	91.5	91.7	92.1	92.9	93.7	94.5	95.3	95.3
107.5°	115.8	115.9	116.0	116.1	116.3	116.5	116.8	117.1	117.4	117.8	118.1
110°	131.3	131.5	131.7	131.9	132.1	132.2	132.4	132.6	132.8	133.0	133.3



TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.5	147.6	147.8	147.8	147.9	148.0	148.0	148.1	148.1	148.1	148.6
115°	171.7	172.0	172.3	172.5	172.8	172.9	172.7	172.5	172.4	172.2	172.3
117.5°	196.2	196.4	196.5	196.7	196.9	196.8	196.6	196.4	196.2	195.9	195.9
120°	211.3	211.9	212.4	212.9	213.5	213.6	213.1	212.7	212.2	211.8	211.7
122.5°	227.2	227.6	228.0	228.4	228.7	228.8	228.6	228.4	228.2	227.9	227.7
125°	251.4	251.6	251.9	252.2	252.4	252.4	252.3	252.1	251.9	251.7	251.4
127.5°	273.7	274.2	274.8	275.4	276.0	276.2	276.0	275.7	275.5	275.4	274.8
130°	288.6	289.3	290.0	290.7	291.4	291.6	291.3	291.1	290.8	290.5	290.2
132.5°	303.4	304.1	304.9	305.6	306.3	306.6	306.3	306.1	305.9	305.8	305.3
135°	326.1	326.6	327.2	327.7	328.2	328.5	328.4	328.3	328.2	328.1	327.8
137.5°	347.1	347.6	348.0	348.5	348.9	349.3	349.5	349.7	350.0	350.2	349.8
140°	361.7	362.1	362.6	363.0	363.5	363.7	363.8	363.9	364.0	364.1	364.0
142.5°	375.0	375.4	375.9	376.3	376.7	377.0	377.2	377.4	377.6	377.6	377.6
145°	395.7	395.8	396.0	396.2	396.4	396.5	396.8	397.1	397.3	397.6	397.5
147.5°	413.8	414.0	414.4	414.6	415.0	415.3	415.5	415.8	416.1	416.3	416.3
150°	426.3	426.5	426.7	426.9	427.0	427.2	427.4	427.6	427.8	427.9	427.9
152.5°	436.7	436.9	437.2	437.4	437.7	437.8	437.9	438.1	438.2	438.3	438.5
155°	453.0	453.0	453.0	453.0	453.0	453.1	453.2	453.3	453.3	453.4	453.8
157.5°	466.9	466.8	466.7	466.5	466.5	466.5	466.5	466.6	466.6	466.7	467.1
160°	475.6	475.5	475.3	475.1	474.9	474.8	474.8	474.8	474.8	474.8	475.3
162.5°	483.4	483.1	482.9	482.6	482.4	482.3	482.3	482.4	482.5	482.6	483.0
165°	493.4	493.1	492.8	492.6	492.3	492.2	492.2	492.2	492.2	492.2	492.8
167.5°	501.4	501.1	500.7	500.3	500.0	499.8	499.9	500.0	500.1	500.1	500.7
170°	506.0	505.6	505.2	504.9	504.5	504.4	504.4	504.4	504.4	504.4	505.0
172.5°	509.5	509.2	508.8	508.5	508.0	507.8	507.8	507.8	507.8	507.8	508.5
175°	513.2	512.8	512.5	512.1	511.8	511.6	511.6	511.6	511.6	511.6	512.1
177.5°	514.8	514.4	514.2	513.9	513.6	513.4	513.4	513.4	513.4	513.4	513.9
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.1
90°	10.4	10.8	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.1	16.4	16.7	16.8	16.7	16.5	16.4	16.3
95°	30.6	30.9	31.3	31.5	31.5	31.5	31.5	31.5
97.5°	47.6	48.1	48.4	48.6	48.6	48.6	48.5	48.5
100°	59.9	60.2	60.5	60.7	60.9	61.1	61.3	61.4
102.5°	74.2	74.5	74.7	74.8	74.8	74.7	74.7	74.6
105°	95.3	95.3	95.3	95.4	95.7	95.9	96.0	96.2
107.5°	118.3	118.6	118.9	119.0	118.9	118.8	118.7	118.6
110°	133.7	134.0	134.4	134.5	134.3	134.1	133.9	133.8





TEST NUMBER: P332393-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.0	149.5	149.9	150.1	150.0	150.0	150.0	149.9
115°	172.4	172.5	172.5	172.5	172.5	172.4	172.3	172.2
117.5°	195.9	195.8	195.8	195.7	195.5	195.2	194.9	194.7
120°	211.6	211.5	211.4	211.2	211.1	210.9	210.7	210.5
122.5°	227.5	227.2	226.9	226.8	226.5	226.2	226.0	225.7
125°	251.0	250.7	250.3	249.9	249.6	249.2	248.9	248.5
127.5°	274.4	273.8	273.3	272.9	272.5	272.1	271.6	271.3
130°	289.8	289.4	289.1	288.6	288.0	287.4	286.8	286.1
132.5°	304.9	304.4	304.0	303.5	303.1	302.6	302.1	301.6
135°	327.4	327.1	326.7	326.5	326.3	326.1	325.9	325.7
137.5°	349.5	349.1	348.7	348.3	347.9	347.7	347.3	347.0
140°	363.9	363.8	363.7	363.4	362.7	362.1	361.5	360.9
142.5°	377.5	377.4	377.3	377.0	376.6	376.0	375.6	375.1
145°	397.4	397.3	397.3	397.1	396.7	396.4	396.0	395.7
147.5°	416.3	416.3	416.3	416.1	415.5	414.9	414.4	413.8
150°	427.9	427.9	427.9	427.7	427.1	426.6	426.1	425.5
152.5°	438.5	438.7	438.9	438.7	438.3	437.7	437.3	436.8
155°	454.1	454.5	454.9	454.7	454.1	453.4	452.8	452.2
157.5°	467.5	467.9	468.2	468.1	467.7	467.2	466.6	466.2
160°	475.7	476.2	476.6	476.6	476.3	475.9	475.5	475.2
162.5°	483.5	483.9	484.4	484.3	483.8	483.1	482.6	482.0
165°	493.3	493.8	494.4	494.3	493.7	493.0	492.4	491.8
167.5°	501.2	501.8	502.3	502.3	501.8	501.2	500.7	500.1
170°	505.6	506.2	506.8	506.8	506.2	505.6	505.0	504.4
172.5°	509.0	509.5	510.1	510.1	509.4	508.8	508.2	507.6
175°	512.6	513.2	513.7	513.7	513.1	512.5	511.8	511.2
177.5°	514.3	514.8	515.1	515.1	514.6	514.2	513.6	513.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4

(END OF REPORT)