

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332397-940

Luminaire Tested: **S123RDIW-S340D755U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332397-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3494.2 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	21	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.4
10°-20°	133.9	3.8
20°-30°	192.7	5.5
30°-40°	217.1	6.2
40°-50°	207.7	5.9
50°-60°	170.1	4.9
60°-70°	114.8	3.3
70°-80°	57.7	1.7
80°-90°	17.8	0.5
90°-100°	54.9	1.6
100°-110°	164.3	4.7
110°-120°	279.4	8.0
120°-130°	367.5	10.5
130°-140°	413.1	11.8
140°-150°	406.1	11.6
150°-160°	341.9	9.8
160°-170°	227.6	6.5
170°-180°	79.7	2.3
0°-30°	374.7	10.7
0°-40°	591.8	16.9
0°-60°	969.6	27.7
0°-90°	1159.8	33.2
90°-120°	498.6	14.3
90°-150°	1685.3	48.2
90°-180°	2334.0	66.8
0°-180°	3494.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	1	7	16	18	20	3
95°	39	44	49	52	52	44
105°	149	150	156	156	158	159
115°	281	283	282	283	282	278
125°	412	414	412	410	407	367
135°	534	538	537	535	533	411
145°	648	649	651	650	648	405
155°	742	742	743	745	741	341
165°	808	806	806	810	806	228
175°	840	838	838	841	837	80
180°	843	843	843	843	843	



TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.1	7.6	7.0	6.6	6.1	6.0	6.3	6.8	7.1	7.5	7.6
90°	0.6	2.1	3.6	5.1	6.5	8.2	10.2	12.0	14.0	15.9	16.5
92.5°	16.1	17.0	18.0	19.0	20.0	21.0	22.1	23.3	24.3	25.4	25.9
95°	39.1	40.0	41.1	42.2	43.2	44.2	45.5	46.6	47.8	49.0	49.6
97.5°	69.4	70.1	70.9	71.7	72.4	73.2	74.1	74.9	75.8	76.7	77.3
100°	90.0	90.9	91.8	92.6	93.5	94.3	95.1	95.9	96.6	97.3	97.7
102.5°	113.9	114.4	114.9	115.4	115.9	116.7	117.7	118.7	119.6	120.6	121.0
105°	148.9	149.2	149.5	149.8	150.1	150.9	152.2	153.6	154.9	156.2	156.2
107.5°	189.7	189.8	190.0	190.2	190.4	190.7	191.3	191.8	192.3	192.9	193.3
110°	215.1	215.4	215.7	216.0	216.2	216.6	216.9	217.1	217.5	217.8	218.4



TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	241.6	241.7	241.9	242.1	242.3	242.4	242.5	242.5	242.5	242.6	243.3
115°	281.3	281.7	282.1	282.6	283.0	283.1	282.9	282.6	282.2	282.0	282.1
117.5°	321.3	321.6	321.8	322.2	322.4	322.4	322.0	321.6	321.3	320.8	320.8
120°	346.2	347.1	347.9	348.8	349.7	349.7	349.0	348.3	347.6	346.8	346.7
122.5°	372.1	372.7	373.4	374.1	374.7	374.8	374.4	374.1	373.7	373.3	372.9
125°	411.7	412.1	412.6	413.0	413.5	413.5	413.2	413.0	412.6	412.3	411.8
127.5°	448.2	449.2	450.1	451.0	452.0	452.3	452.0	451.7	451.3	451.0	450.1
130°	472.6	473.8	474.9	476.1	477.2	477.7	477.2	476.8	476.4	475.9	475.3
132.5°	497.0	498.1	499.3	500.4	501.7	502.0	501.8	501.4	501.1	500.8	500.1
135°	534.1	535.0	535.9	536.8	537.6	538.1	537.9	537.7	537.6	537.4	536.8
137.5°	568.6	569.3	570.0	570.8	571.5	572.0	572.4	572.8	573.2	573.5	572.9
140°	592.4	593.1	593.9	594.6	595.3	595.8	595.9	596.0	596.2	596.4	596.2
142.5°	614.1	614.8	615.5	616.3	617.0	617.5	617.8	618.0	618.3	618.6	618.4
145°	648.0	648.3	648.5	648.8	649.2	649.5	650.0	650.4	650.9	651.3	651.1
147.5°	677.6	678.1	678.7	679.2	679.8	680.2	680.6	681.0	681.4	681.9	681.9
150°	698.3	698.6	698.8	699.2	699.5	699.7	700.0	700.3	700.6	700.9	700.9
152.5°	715.2	715.6	716.0	716.5	716.8	717.1	717.3	717.5	717.6	717.8	718.1
155°	742.0	742.0	742.0	742.0	742.0	742.0	742.2	742.3	742.4	742.6	743.2
157.5°	764.7	764.6	764.4	764.2	764.0	764.0	764.1	764.2	764.4	764.5	765.1
160°	779.0	778.7	778.5	778.1	777.8	777.7	777.7	777.7	777.7	777.7	778.5
162.5°	791.8	791.3	790.9	790.5	790.1	790.0	790.1	790.1	790.3	790.4	791.1
165°	808.2	807.7	807.3	806.8	806.4	806.1	806.1	806.1	806.1	806.1	807.0
167.5°	821.3	820.6	820.1	819.5	818.9	818.7	818.8	818.9	819.0	819.1	820.0
170°	828.7	828.0	827.5	826.9	826.3	826.0	826.0	826.0	826.0	826.0	827.1
172.5°	834.5	833.9	833.3	832.7	832.1	831.8	831.8	831.8	831.8	831.8	832.8
175°	840.5	840.0	839.4	838.8	838.2	837.9	837.9	837.9	837.9	837.9	838.8
177.5°	843.1	842.6	842.1	841.7	841.2	841.0	841.0	841.0	841.0	841.0	841.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	7.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7
90°	17.0	17.7	18.3	18.6	19.0	19.3	19.5	19.9
92.5°	26.4	26.8	27.3	27.5	27.3	27.1	26.9	26.8
95°	50.1	50.7	51.4	51.6	51.6	51.6	51.6	51.6
97.5°	78.0	78.6	79.4	79.6	79.6	79.5	79.5	79.5
100°	98.2	98.6	99.1	99.4	99.7	100.0	100.3	100.6
102.5°	121.5	121.9	122.3	122.5	122.5	122.4	122.3	122.3
105°	156.2	156.2	156.2	156.3	156.7	156.9	157.2	157.6
107.5°	193.8	194.3	194.7	194.9	194.7	194.6	194.4	194.2
110°	218.9	219.5	220.1	220.3	220.0	219.6	219.4	219.1



TEST NUMBER: P332397-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.1	244.8	245.5	245.8	245.8	245.7	245.6	245.6
115°	282.2	282.4	282.6	282.6	282.4	282.2	282.1	282.0
117.5°	320.8	320.7	320.7	320.6	320.1	319.7	319.3	318.9
120°	346.5	346.3	346.3	346.0	345.7	345.4	345.1	344.8
122.5°	372.6	372.1	371.8	371.4	371.0	370.5	370.1	369.7
125°	411.2	410.5	410.0	409.4	408.8	408.2	407.6	407.1
127.5°	449.3	448.5	447.7	446.9	446.3	445.6	445.0	444.3
130°	474.7	474.1	473.5	472.7	471.7	470.6	469.7	468.6
132.5°	499.4	498.6	497.9	497.2	496.4	495.6	494.8	494.0
135°	536.3	535.7	535.1	534.7	534.3	534.0	533.8	533.4
137.5°	572.3	571.7	571.1	570.5	570.0	569.4	568.8	568.3
140°	596.0	595.9	595.8	595.1	594.1	593.1	592.1	591.0
142.5°	618.3	618.1	618.0	617.5	616.7	615.9	615.1	614.3
145°	650.9	650.9	650.7	650.3	649.7	649.2	648.5	648.0
147.5°	681.9	681.9	681.9	681.4	680.6	679.7	678.8	677.9
150°	700.9	700.9	700.9	700.4	699.5	698.7	697.9	697.0
152.5°	718.4	718.5	718.8	718.5	717.7	717.0	716.2	715.5
155°	743.8	744.4	744.9	744.8	743.7	742.7	741.6	740.7
157.5°	765.7	766.3	767.0	766.8	766.0	765.2	764.4	763.5
160°	779.2	779.9	780.6	780.7	780.2	779.5	778.9	778.4
162.5°	791.8	792.6	793.4	793.3	792.3	791.4	790.4	789.4
165°	807.9	808.8	809.7	809.6	808.6	807.5	806.6	805.5
167.5°	820.9	821.9	822.8	822.8	821.9	820.9	820.0	819.1
170°	828.0	829.1	830.1	830.1	829.1	828.0	827.1	826.0
172.5°	833.7	834.6	835.4	835.4	834.4	833.4	832.3	831.3
175°	839.7	840.5	841.4	841.4	840.3	839.3	838.3	837.2
177.5°	842.4	843.1	843.8	843.7	842.9	842.0	841.2	840.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6

(END OF REPORT)