

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332185-935

Luminaire Tested: **S123DIW-S1000D460U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332185-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D460U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4924.0 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	67	66	64	61
2	93	86	79	74	88	81	76	71	73	69	65	66	63	59	59	57	54	51
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	53	49	46	43
4	78	67	58	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	37	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.4	2.6
10°-20°	362.5	7.4
20°-30°	535.5	10.9
30°-40°	625.5	12.7
40°-50°	628.8	12.8
50°-60°	552.4	11.2
60°-70°	411.5	8.4
70°-80°	234.5	4.8
80°-90°	68.8	1.4
90°-100°	32.4	0.7
100°-110°	96.8	2.0
110°-120°	164.7	3.3
120°-130°	216.7	4.4
130°-140°	243.5	4.9
140°-150°	239.4	4.9
150°-160°	201.5	4.1
160°-170°	134.2	2.7
170°-180°	47.0	1.0
0°-30°	1026.3	20.8
0°-40°	1651.8	33.5
0°-60°	2833.0	57.5
0°-90°	3547.8	72.1
90°-120°	293.9	6.0
90°-150°	993.5	20.2
90°-180°	1376.0	27.9
0°-180°	4924.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	0	4	9	11	12	5
95°	23	26	29	30	30	26
105°	88	89	92	92	93	94
115°	166	167	166	167	166	164
125°	243	244	243	242	240	216
135°	315	317	317	315	314	243
145°	382	383	384	384	382	239
155°	437	437	438	439	437	201
165°	476	475	475	477	475	134
175°	496	494	494	496	494	47
180°	497	497	497	497	497	



TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.5	24.0	23.6	23.1	22.6	22.4	22.5	22.5	22.5	22.5	22.4
90°	0.4	1.3	2.2	3.0	3.9	4.8	5.9	7.1	8.3	9.4	9.7
92.5°	9.5	10.1	10.6	11.2	11.8	12.4	13.1	13.7	14.4	15.0	15.2
95°	23.0	23.6	24.2	24.9	25.5	26.1	26.8	27.5	28.2	28.8	29.2
97.5°	40.9	41.3	41.8	42.3	42.7	43.1	43.7	44.2	44.7	45.2	45.5
100°	53.0	53.6	54.1	54.6	55.1	55.6	56.1	56.5	56.9	57.3	57.6
102.5°	67.1	67.4	67.8	68.0	68.4	68.8	69.4	69.9	70.5	71.1	71.4
105°	87.8	88.0	88.2	88.3	88.5	88.9	89.7	90.5	91.3	92.0	92.0
107.5°	111.8	111.9	112.0	112.1	112.3	112.4	112.8	113.0	113.4	113.7	114.0
110°	126.8	127.0	127.2	127.3	127.5	127.7	127.9	128.0	128.2	128.4	128.7



TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.4	142.5	142.7	142.8	142.8	142.9	142.9	143.0	143.0	143.0	143.4
115°	165.8	166.1	166.3	166.6	166.9	166.9	166.8	166.6	166.4	166.3	166.3
117.5°	189.4	189.6	189.8	189.9	190.1	190.0	189.9	189.6	189.4	189.2	189.2
120°	204.1	204.6	205.1	205.6	206.1	206.2	205.8	205.3	204.9	204.5	204.4
122.5°	219.4	219.7	220.2	220.5	220.8	220.9	220.8	220.5	220.3	220.1	219.8
125°	242.7	243.0	243.2	243.5	243.7	243.7	243.6	243.4	243.2	243.1	242.7
127.5°	264.2	264.8	265.4	265.9	266.5	266.7	266.5	266.2	266.0	265.9	265.4
130°	278.6	279.3	280.0	280.7	281.4	281.5	281.3	281.0	280.8	280.5	280.2
132.5°	292.9	293.6	294.4	295.1	295.8	296.0	295.8	295.6	295.4	295.2	294.8
135°	314.9	315.4	315.9	316.4	316.9	317.2	317.1	317.0	316.9	316.8	316.5
137.5°	335.2	335.6	336.0	336.5	336.9	337.3	337.4	337.7	337.9	338.1	337.8
140°	349.2	349.7	350.1	350.5	350.9	351.2	351.3	351.4	351.5	351.5	351.5
142.5°	362.1	362.5	362.9	363.3	363.8	364.0	364.2	364.4	364.5	364.6	364.5
145°	382.0	382.2	382.4	382.5	382.7	382.9	383.1	383.4	383.7	383.9	383.8
147.5°	399.5	399.8	400.1	400.4	400.7	401.0	401.2	401.5	401.7	402.0	402.0
150°	411.6	411.8	412.0	412.2	412.3	412.5	412.7	412.8	413.0	413.2	413.2
152.5°	421.6	421.9	422.1	422.3	422.6	422.8	422.8	423.0	423.1	423.2	423.4
155°	437.4	437.4	437.4	437.4	437.4	437.5	437.6	437.6	437.7	437.8	438.2
157.5°	450.8	450.7	450.6	450.5	450.4	450.4	450.5	450.6	450.6	450.6	451.0
160°	459.3	459.1	458.9	458.7	458.6	458.5	458.5	458.5	458.5	458.5	458.9
162.5°	466.7	466.5	466.2	466.0	465.8	465.7	465.7	465.8	465.9	466.0	466.4
165°	476.4	476.1	475.9	475.6	475.4	475.3	475.3	475.3	475.3	475.3	475.8
167.5°	484.1	483.8	483.5	483.1	482.8	482.6	482.7	482.8	482.8	482.8	483.5
170°	488.5	488.2	487.8	487.5	487.2	487.0	487.0	487.0	487.0	487.0	487.6
172.5°	492.0	491.6	491.3	490.9	490.5	490.3	490.3	490.3	490.3	490.3	490.9
175°	495.5	495.2	494.8	494.5	494.1	494.0	494.0	494.0	494.0	494.0	494.5
177.5°	497.1	496.7	496.5	496.2	495.9	495.8	495.8	495.8	495.8	495.8	496.2
180°	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7



TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	22.2	22.0	22.0	21.9	22.0	22.0	22.0	22.0
90°	10.1	10.4	10.8	11.0	11.2	11.4	11.5	11.7
92.5°	15.5	15.8	16.1	16.2	16.1	15.9	15.8	15.8
95°	29.5	29.9	30.2	30.4	30.4	30.4	30.4	30.4
97.5°	46.0	46.4	46.8	46.9	46.9	46.9	46.8	46.8
100°	57.9	58.1	58.4	58.6	58.8	59.0	59.2	59.3
102.5°	71.6	71.9	72.2	72.2	72.2	72.2	72.2	72.1
105°	92.0	92.0	92.0	92.1	92.4	92.6	92.7	92.9
107.5°	114.3	114.5	114.8	114.9	114.8	114.7	114.6	114.5
110°	129.1	129.4	129.8	129.8	129.7	129.5	129.3	129.2





TEST NUMBER: P332185-935

CATALOG NUMBER: S123DIW-S1000D460U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	143.9	144.3	144.7	144.9	144.8	144.8	144.8	144.7
115°	166.4	166.5	166.6	166.6	166.5	166.4	166.3	166.3
117.5°	189.2	189.1	189.1	189.0	188.7	188.5	188.2	188.0
120°	204.3	204.2	204.1	204.0	203.8	203.6	203.5	203.3
122.5°	219.6	219.4	219.1	219.0	218.7	218.4	218.2	217.9
125°	242.4	242.0	241.7	241.3	241.0	240.6	240.3	240.0
127.5°	264.9	264.4	263.9	263.5	263.1	262.7	262.3	261.9
130°	279.8	279.5	279.1	278.7	278.1	277.5	276.9	276.2
132.5°	294.4	293.9	293.5	293.1	292.7	292.1	291.7	291.2
135°	316.2	315.8	315.5	315.2	315.0	314.9	314.7	314.5
137.5°	337.4	337.1	336.7	336.3	336.0	335.7	335.4	335.0
140°	351.4	351.3	351.2	350.9	350.3	349.7	349.0	348.4
142.5°	364.5	364.4	364.3	364.0	363.6	363.1	362.7	362.1
145°	383.7	383.7	383.6	383.4	383.1	382.7	382.4	382.0
147.5°	402.0	402.0	402.0	401.7	401.2	400.6	400.1	399.6
150°	413.2	413.2	413.2	412.9	412.4	411.9	411.4	410.9
152.5°	423.4	423.6	423.8	423.6	423.2	422.7	422.2	421.8
155°	438.5	438.9	439.2	439.0	438.4	437.8	437.2	436.6
157.5°	451.4	451.8	452.1	452.0	451.6	451.1	450.6	450.1
160°	459.3	459.8	460.2	460.2	459.9	459.5	459.2	458.8
162.5°	466.8	467.3	467.7	467.6	467.1	466.5	466.0	465.4
165°	476.3	476.8	477.3	477.3	476.6	476.0	475.4	474.8
167.5°	484.0	484.5	485.0	485.0	484.5	484.0	483.5	482.8
170°	488.2	488.8	489.4	489.4	488.8	488.2	487.6	487.0
172.5°	491.5	492.0	492.5	492.5	491.9	491.3	490.7	490.1
175°	495.0	495.5	496.0	496.0	495.4	494.8	494.2	493.6
177.5°	496.6	497.1	497.4	497.4	496.9	496.5	495.9	495.4
180°	496.7	496.7	496.7	496.7	496.7	496.7	496.7	496.7

(END OF REPORT)