

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332420-940

Luminaire Tested: **S123RDIW-S560D1030U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332420-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1030U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5582.3 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34			34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	35	29			29
2	86	79	73	68	78	72	67	62	58	54	51	45	42	40	33	31	30	25			25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21			21
4	72	62	54	48	65	56	50	44	45	41	37	35	32	30	26	24	22	18			18
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	21	20	16			16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14			14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	15	13			13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11			11
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10			10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.4
10°-20°	220.1	3.9
20°-30°	316.9	5.7
30°-40°	356.9	6.4
40°-50°	341.4	6.1
50°-60°	279.6	5.0
60°-70°	188.7	3.4
70°-80°	94.9	1.7
80°-90°	28.5	0.5
90°-100°	43.8	0.8
100°-110°	208.9	3.7
110°-120°	501.7	9.0
120°-130°	638.9	11.4
130°-140°	682.7	12.2
140°-150°	638.4	11.4
150°-160°	514.9	9.2
160°-170°	332.3	6.0
170°-180°	114.5	2.1
0°-30°	616.0	11.0
0°-40°	972.9	17.4
0°-60°	1594.0	28.6
0°-90°	1906.0	34.1
90°-120°	754.5	13.5
90°-150°	2714.5	48.6
90°-180°	3676.0	65.9
0°-180°	5582.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	10	22	25	27	4
95°	55	20	28	34	34	68
105°	267	272	196	46	39	283
115°	501	506	514	523	527	494
125°	706	713	716	718	720	630
135°	879	884	888	890	888	676
145°	1014	1020	1022	1024	1024	634
155°	1117	1115	1116	1120	1115	514
165°	1178	1175	1174	1181	1175	333
175°	1206	1201	1202	1208	1201	115
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.3	12.4	11.4	10.5	9.5	9.4	9.8	10.3	10.9	11.4	11.4
90°	0.9	2.9	4.9	6.9	8.8	11.1	13.7	16.3	18.9	21.5	22.3
92.5°	16.7	16.1	15.5	15.0	14.4	15.2	17.1	19.0	21.0	22.9	24.2
95°	54.7	46.5	38.3	30.1	22.0	19.0	21.2	23.4	25.6	27.7	29.2
97.5°	109.8	106.1	102.5	98.8	95.1	86.1	71.9	57.5	43.2	28.8	30.4
100°	151.3	155.3	159.3	163.3	167.3	153.7	122.7	91.7	60.6	29.5	31.1
102.5°	198.7	201.5	204.4	207.2	210.1	194.6	160.7	126.8	92.8	58.9	54.0
105°	266.9	269.1	271.3	273.5	275.6	267.8	249.9	231.9	214.1	196.2	161.0
107.5°	338.9	340.6	342.4	344.2	345.9	348.2	351.1	353.8	356.7	359.5	333.7
110°	386.9	388.5	390.1	391.7	393.2	395.2	397.3	399.6	401.7	403.9	397.3



TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	434.2	435.6	437.1	438.5	440.3	442.5	444.7	446.9	449.1	449.2
115°	500.7	501.9	503.0	504.3	505.4	506.9	508.7	510.5	512.3	514.1	516.1
117.5°	566.4	567.8	569.4	570.8	572.3	573.5	574.4	575.3	576.2	577.1	578.7
120°	607.3	609.0	610.8	612.6	614.4	615.6	616.2	616.8	617.4	618.0	619.6
122.5°	648.8	650.2	651.8	653.2	654.7	655.8	656.6	657.3	658.1	658.8	660.0
125°	705.8	707.4	708.9	710.5	712.1	713.4	714.1	714.9	715.7	716.5	716.9
127.5°	760.9	762.5	764.1	765.7	767.3	768.6	769.5	770.5	771.4	772.4	773.0
130°	795.3	796.9	798.5	800.1	801.7	802.9	803.7	804.5	805.3	806.1	806.9
132.5°	828.3	829.9	831.4	833.0	834.6	835.8	836.4	837.0	837.7	838.3	839.1
135°	878.6	879.9	881.0	882.2	883.4	884.4	885.2	886.0	886.8	887.6	888.1
137.5°	921.6	923.1	924.6	926.1	927.6	928.6	929.1	929.5	930.0	930.4	931.3
140°	950.3	951.5	952.7	953.9	955.0	955.9	956.5	957.2	957.7	958.3	959.1
142.5°	976.8	977.9	979.2	980.3	981.6	982.5	983.0	983.6	984.3	984.8	985.5
145°	1013.9	1015.2	1016.6	1018.1	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3
147.5°	1048.8	1049.7	1050.6	1051.5	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1
150°	1070.3	1070.9	1071.5	1072.1	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1
152.5°	1089.7	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7
155°	1116.9	1116.4	1116.1	1115.7	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0
157.5°	1138.0	1138.0	1137.9	1137.9	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1
160°	1150.9	1150.7	1150.5	1150.3	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3
162.5°	1163.1	1162.5	1162.1	1161.5	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2
165°	1177.8	1177.1	1176.6	1176.0	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8
167.5°	1189.2	1188.5	1187.7	1186.9	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2
170°	1195.7	1194.9	1194.1	1193.3	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6
172.5°	1200.0	1199.0	1198.1	1197.1	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0
175°	1205.5	1204.5	1203.5	1202.6	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4
177.5°	1206.9	1206.1	1205.4	1204.6	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	11.5	11.5	11.6	11.6	11.5	11.5	11.4	11.4
90°	23.1	23.9	24.7	25.2	25.7	26.0	26.5	26.8
92.5°	25.5	26.8	28.0	28.8	29.0	29.2	29.5	29.7
95°	30.6	31.9	33.3	34.1	34.1	34.1	34.1	34.1
97.5°	32.0	33.6	35.2	36.1	36.3	36.5	36.7	36.9
100°	32.7	34.3	35.9	36.8	37.0	37.2	37.5	37.6
102.5°	49.0	44.1	39.1	36.9	37.3	37.6	38.0	38.3
105°	125.7	90.4	55.2	37.8	38.3	38.6	39.0	39.4
107.5°	307.8	282.0	256.2	230.0	203.4	176.9	150.3	123.8
110°	390.8	384.2	377.6	360.2	331.7	303.2	274.7	246.3



TEST NUMBER: P332420-940

CATALOG NUMBER: S123RDIW-S560D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	449.3	449.4	449.5	446.6	440.6	434.6	428.6	422.6
115°	518.1	520.0	522.1	523.4	524.2	525.0	525.8	526.6
117.5°	580.3	581.9	583.5	584.4	584.5	584.7	584.9	585.1
120°	621.2	622.8	624.4	625.2	625.2	625.2	625.2	625.2
122.5°	661.0	662.2	663.3	664.0	664.1	664.2	664.4	664.6
125°	717.3	717.7	718.1	718.5	718.9	719.3	719.7	720.1
127.5°	773.6	774.3	775.0	775.1	774.6	774.3	773.9	773.5
130°	807.7	808.4	809.2	809.5	809.0	808.7	808.2	807.9
132.5°	839.9	840.7	841.5	841.6	841.1	840.5	840.0	839.4
135°	888.8	889.4	889.9	889.9	889.4	888.8	888.1	887.6
137.5°	932.3	933.3	934.2	934.5	934.1	933.7	933.3	932.9
140°	959.9	960.7	961.5	961.7	961.4	960.9	960.6	960.1
142.5°	986.1	986.8	987.4	987.4	986.9	986.3	985.8	985.2
145°	1022.7	1023.1	1023.5	1023.7	1023.7	1023.7	1023.7	1023.7
147.5°	1055.5	1055.9	1056.3	1056.1	1055.2	1054.2	1053.3	1052.4
150°	1075.6	1075.9	1076.4	1076.3	1075.7	1075.0	1074.5	1073.9
152.5°	1093.4	1094.1	1094.8	1094.8	1093.8	1092.9	1092.0	1091.1
155°	1117.9	1118.9	1120.0	1119.8	1118.7	1117.5	1116.2	1115.1
157.5°	1139.3	1140.5	1141.7	1141.5	1140.0	1138.4	1136.8	1135.3
160°	1151.5	1152.7	1153.9	1153.8	1152.4	1151.0	1149.6	1148.2
162.5°	1162.5	1164.0	1165.3	1165.3	1164.1	1162.9	1161.6	1160.4
165°	1177.3	1178.9	1180.5	1180.6	1179.3	1177.9	1176.4	1175.1
167.5°	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6
170°	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1
172.5°	1199.6	1201.1	1202.7	1202.7	1201.0	1199.2	1197.4	1195.7
175°	1204.7	1206.1	1207.6	1207.5	1205.9	1204.3	1202.7	1201.0
177.5°	1206.7	1207.9	1209.2	1209.1	1207.5	1205.9	1204.3	1202.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5

(END OF REPORT)