

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332190-935

Luminaire Tested: **S123DIW-S1000D755U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332190-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6149.3 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	91	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45	41
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	36	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26
6	64	52	43	37	59	48	41	36	43	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.1
10°-20°	362.5	5.9
20°-30°	535.5	8.7
30°-40°	625.5	10.2
40°-50°	628.8	10.2
50°-60°	552.4	9.0
60°-70°	411.5	6.7
70°-80°	234.5	3.8
80°-90°	69.7	1.1
90°-100°	31.0	0.5
100°-110°	147.8	2.4
110°-120°	355.0	5.8
120°-130°	452.0	7.4
130°-140°	482.9	7.9
140°-150°	451.6	7.3
150°-160°	364.3	5.9
160°-170°	235.1	3.8
170°-180°	81.0	1.3
0°-30°	1026.3	16.7
0°-40°	1651.8	26.9
0°-60°	2833.0	46.1
0°-90°	3548.7	57.7
90°-120°	533.7	8.7
90°-150°	1920.2	31.2
90°-180°	2601.0	42.3
0°-180°	6149.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	1	7	15	18	19	5
95°	39	14	20	24	24	48
105°	189	192	139	33	28	200
115°	354	358	364	370	373	349
125°	499	504	507	508	509	446
135°	622	625	628	630	628	478
145°	717	722	723	724	724	449
155°	790	789	790	792	789	364
165°	833	831	831	835	831	235
175°	853	850	850	854	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.5	24.2	23.8	23.5	23.2	23.1	23.2	23.3	23.5	23.7	23.6
90°	0.6	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8
92.5°	11.8	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1
95°	38.7	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7
97.5°	77.7	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5
100°	107.1	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0
102.5°	140.5	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2
105°	188.8	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8
107.5°	239.7	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0
110°	273.7	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1



TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.2	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8
115°	354.1	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1
117.5°	400.7	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4
120°	429.6	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3
122.5°	459.0	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8
125°	499.3	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1
127.5°	538.3	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8
130°	562.6	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8
132.5°	585.9	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6
135°	621.6	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3
137.5°	651.9	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8
140°	672.2	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5
142.5°	691.0	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2
145°	717.2	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2
147.5°	741.9	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4
150°	757.2	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6
152.5°	770.8	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9
155°	790.1	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1
157.5°	805.0	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1
160°	814.2	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7
162.5°	822.8	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5
165°	833.2	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7
167.5°	841.3	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8
170°	845.8	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4
172.5°	848.9	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5
175°	852.8	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3
177.5°	853.8	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	23.5	23.4	23.2	23.2	23.3	23.3	23.4	23.5
90°	16.4	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.0	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	21.6	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	22.6	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	23.2	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	34.7	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	88.9	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	217.7	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	276.5	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332190-935

CATALOG NUMBER: S123DIW-S1000D755U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	317.9	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	366.5	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	410.5	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	439.5	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	467.6	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.4	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.3	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.4	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.2	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	659.5	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.1	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	697.6	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.5	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.7	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	760.9	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	773.4	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	790.8	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.0	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	814.6	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	822.4	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	832.8	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	848.6	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	852.2	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	853.6	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)