

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332426-940

Luminaire Tested: **S123RDIW-S560D1535U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332426-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1535U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7463.4 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	30	30	23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22	17
4	71	61	53	48	63	55	48	44	43	39	35	32	29	27	22	21	19	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13
6	60	49	41	35	53	44	37	32	35	30	26	26	23	21	18	17	15	12
7	55	44	36	31	49	40	33	28	31	27	23	24	21	18	17	15	13	10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8587	8587	8587	8587
5°	10237	8625	7595	8625
10°	12783	8575	6862	8575
15°	15004	8487	6257	8487
20°	16745	8356	5743	8356
25°	16476	8219	5428	8219
30°	11844	8090	5102	8090
35°	7908	7926	4892	7926
40°	5826	7727	4675	7727
45°	4886	7377	4460	7377
50°	4312	6921	4163	6921
55°	3781	6397	3755	6397
60°	3367	5896	3442	5896
65°	2957	5359	3202	5359
70°	2319	4881	2924	4881
75°	2046	4263	2670	4263
80°	1779	3620	2628	3620
85°	1433	2902	2791	2902



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.5	1.1
10°-20°	245.1	3.3
20°-30°	385.1	5.2
30°-40°	401.8	5.4
40°-50°	343.8	4.6
50°-60°	262.1	3.5
60°-70°	168.0	2.3
70°-80°	80.8	1.1
80°-90°	26.4	0.4
90°-100°	65.2	0.9
100°-110°	310.9	4.2
110°-120°	746.8	10.0
120°-130°	951.0	12.7
130°-140°	1016.1	13.6
140°-150°	950.2	12.7
150°-160°	766.5	10.3
160°-170°	494.7	6.6
170°-180°	170.5	2.3
0°-30°	708.7	9.5
0°-40°	1110.4	14.9
0°-60°	1716.3	23.0
0°-90°	1991.5	26.7
90°-120°	1123.0	15.0
90°-150°	4040.3	54.1
90°-180°	5472.0	73.3
0°-180°	7463.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	947	798	703	798	947	98
15°	1346	762	562	762	1346	382
25°	1387	692	457	692	1387	596
35°	602	603	372	603	602	395
45°	321	485	293	485	321	252
55°	202	341	200	341	202	182
65°	116	210	126	210	116	114
75°	49	102	64	102	49	53
85°	12	24	23	24	12	14
90°	40	1	40	1	40	18
95°	51	81	51	81	51	42
105°	59	397	59	397	59	134
115°	784	745	784	745	784	724
125°	1072	1050	1072	1050	1072	957
135°	1321	1308	1321	1308	1321	1019
145°	1524	1509	1524	1509	1524	951
155°	1660	1662	1660	1662	1660	765
165°	1749	1753	1749	1753	1749	494
175°	1788	1794	1788	1794	1788	170
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	849.7	850.9	847.3	846.8	842.7	841.6	841.6	835.8	832.2	827.6	824.9
5°	947.4	952.9	950.2	944.1	933.8	931.4	924.9	914.6	903.0	888.7	881.9
7.5°	1069.4	1076.9	1074.0	1064.5	1053.8	1045.1	1026.8	1009.8	986.0	965.1	947.2
10°	1169.5	1161.5	1155.5	1146.2	1136.3	1120.3	1101.2	1074.9	1044.5	1020.6	993.9
12.5°	1244.3	1243.0	1235.2	1225.7	1211.7	1196.5	1173.0	1140.9	1105.6	1071.0	1040.6
15°	1346.4	1348.4	1343.3	1333.4	1313.6	1286.6	1251.1	1237.8	1187.2	1149.6	1112.1
17.5°	1417.0	1416.6	1415.9	1402.1	1382.0	1362.7	1329.8	1294.8	1249.0	1196.1	1145.5
20°	1461.8	1458.4	1459.1	1443.7	1428.7	1406.5	1374.4	1323.5	1285.9	1224.8	1172.5
22.5°	1460.7	1460.0	1462.6	1457.3	1446.4	1429.4	1404.2	1361.2	1313.2	1251.5	1192.8
25°	1387.3	1384.6	1400.7	1405.1	1422.5	1425.6	1418.1	1394.5	1349.1	1285.6	1212.8
27.5°	1161.1	1159.6	1189.4	1226.6	1274.0	1310.7	1346.2	1363.3	1349.1	1303.6	1230.7
30°	952.9	985.0	1000.1	1054.0	1114.1	1185.8	1248.7	1308.4	1323.1	1303.3	1243.6
32.5°	791.1	819.1	831.7	878.1	934.1	1018.1	1112.3	1196.9	1256.8	1271.9	1235.9
35°	601.8	602.2	630.8	651.3	703.2	789.6	881.2	994.5	1107.2	1192.7	1201.6
37.5°	480.2	481.9	499.3	519.7	558.7	604.3	684.9	779.2	909.4	1040.4	1117.3
40°	414.6	417.7	430.7	450.8	478.8	513.4	576.2	664.9	773.6	919.4	1038.7
42.5°	372.6	377.6	384.2	399.8	417.1	449.4	500.2	568.8	667.5	805.5	943.0
45°	321.0	323.8	328.9	336.1	351.8	374.3	408.5	454.6	536.5	647.6	785.2
47.5°	283.2	281.8	287.1	293.0	303.4	318.8	341.7	379.3	437.8	526.8	643.6
50°	257.5	257.2	260.9	265.4	275.3	286.6	305.3	333.7	380.1	453.9	560.8
52.5°	233.4	234.8	237.5	243.0	250.1	259.2	276.1	296.5	336.4	400.1	489.2
55°	201.5	202.5	206.3	209.4	214.5	223.7	234.3	251.4	278.7	323.1	396.5
57.5°	174.4	174.0	177.6	178.3	184.1	191.6	199.8	213.1	232.9	265.9	315.4
60°	156.4	155.4	158.5	160.9	163.9	170.0	176.9	189.9	205.6	229.9	272.2
62.5°	140.0	139.6	141.8	144.2	146.7	152.3	158.1	168.0	180.5	200.9	234.5
65°	116.1	117.2	118.2	119.2	120.6	123.9	129.5	136.3	144.8	159.2	183.4
67.5°	91.2	92.3	92.6	94.7	97.6	99.8	103.2	109.2	115.2	127.2	141.1
70°	73.7	73.4	73.7	74.8	78.6	82.3	86.8	91.2	95.0	103.5	115.1
72.5°	63.4	62.8	63.7	63.8	65.7	66.7	69.6	73.7	78.6	84.4	92.7
75°	49.2	49.2	49.2	49.2	50.6	51.3	52.3	53.3	55.0	57.7	63.8
77.5°	36.4	36.4	36.9	37.2	37.5	37.9	38.5	39.6	40.1	41.6	44.2
80°	28.7	29.1	28.7	29.1	29.1	29.7	30.1	31.1	31.4	33.2	34.2
82.5°	21.6	21.4	21.6	21.9	21.9	22.6	22.6	23.5	23.5	24.3	25.4
85°	11.6	11.0	11.6	11.2	11.9	11.2	11.6	12.3	12.3	12.7	14.0
87.5°	10.7	11.1	10.5	10.6	10.5	10.6	10.4	10.2	10.4	10.0	9.5
90°	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3	33.2	32.0	28.2
92.5°	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9	36.0	34.2	31.2
95°	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5	43.4	41.3	38.1
97.5°	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7	45.3	42.9	64.3
100°	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7	46.4	44.0	90.2
102.5°	57.1	56.5	56.0	55.5	54.9	53.3	65.7	73.0	80.3	87.7	138.2
105°	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1	239.5	291.9	318.6
107.5°	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2	496.7	535.1	530.9
110°	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7	591.5	601.2	598.0



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8	668.6	668.4	665.1
115°	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2	768.1	765.2	762.5
117.5°	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8	861.4	859.1	857.6
120°	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6	922.2	919.8	918.9
122.5°	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9	982.3	980.6	979.5
125°	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6	1067.1	1066.5	1065.3
127.5°	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6	1150.6	1149.7	1148.3
130°	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1	1201.0	1199.8	1198.6
132.5°	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2	1248.9	1247.8	1246.8
135°	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1	1319.9
137.5°	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7	1386.3	1384.8	1384.2
140°	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8	1427.6	1426.4	1425.5
142.5°	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8	1466.8	1465.9	1465.0
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2	1521.6	1521.1	1520.5
147.5°	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0	1570.5	1569.9	1569.2
150°	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9	1600.3	1599.7	1599.1
152.5°	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5	1626.4	1625.3	1625.0
155°	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0	1662.5	1661.0	1660.7
157.5°	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8	1694.0	1692.2	1692.6
160°	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0	1712.2	1710.4	1710.7
162.5°	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4	1728.4	1726.4	1726.6
165°	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4	1750.1	1747.7	1748.0
167.5°	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8	1764.8
170°	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3	1774.3
172.5°	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5	1783.2	1780.7	1780.5
175°	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1	1791.1	1789.0	1788.7
177.5°	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0	1794.1	1792.2	1792.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	823.8	823.0	819.1	814.8	809.0	805.2	802.2	800.6	795.7	789.6	785.5
5°	874.7	864.4	853.5	840.2	827.9	815.3	807.4	798.2	786.9	774.3	765.4
7.5°	929.2	909.1	887.4	865.1	843.0	823.2	805.7	790.8	772.8	754.7	742.0
10°	971.0	941.6	911.2	880.1	851.8	825.2	804.7	784.5	763.0	742.2	726.5
12.5°	1009.0	970.4	935.3	897.1	860.9	829.0	799.5	775.8	749.9	727.7	709.8
15°	1057.0	1017.4	975.1	917.0	868.9	828.6	792.7	761.6	730.2	702.9	685.5
17.5°	1102.0	1042.4	985.5	937.0	874.5	824.1	780.3	743.2	708.7	679.8	658.3
20°	1120.6	1062.9	1001.0	939.2	877.8	821.4	770.5	729.5	693.7	660.8	641.1
22.5°	1131.8	1066.4	1001.3	934.9	869.6	811.0	760.7	715.6	676.7	645.6	621.2
25°	1144.9	1066.9	995.2	929.7	863.1	799.5	739.8	692.0	650.0	616.8	590.8
27.5°	1153.4	1061.8	977.0	904.2	836.6	773.4	718.6	667.9	625.3	590.2	562.4
30°	1155.1	1057.7	963.1	884.2	815.6	757.5	699.5	650.9	605.9	568.6	542.7
32.5°	1157.3	1047.7	944.3	860.5	790.2	732.7	680.1	633.7	587.5	550.9	524.4
35°	1148.3	1042.1	915.7	819.4	749.0	693.3	645.9	603.2	557.8	522.2	495.3
37.5°	1109.5	1019.8	886.0	773.0	699.5	647.9	609.2	572.0	530.4	492.0	466.6
40°	1070.4	998.0	863.1	744.9	668.1	615.1	580.2	549.9	509.6	473.7	446.4
42.5°	1012.2	968.2	841.2	715.4	632.5	581.5	552.1	523.6	488.3	451.8	426.1
45°	905.4	911.2	796.5	668.4	583.4	532.1	504.4	484.6	453.3	423.2	396.9
47.5°	771.5	825.8	744.0	618.3	531.5	483.4	459.2	441.9	420.8	391.3	367.3
50°	684.1	761.6	701.9	584.7	499.0	451.2	427.3	413.3	394.8	371.6	348.7
52.5°	603.5	686.8	651.0	547.2	463.8	420.0	396.6	385.1	370.5	348.7	328.0
55°	492.1	576.5	568.3	490.8	410.9	371.6	353.8	340.9	330.9	314.6	298.2
57.5°	398.1	478.0	482.3	427.9	364.3	325.5	310.2	300.4	293.9	281.6	266.4
60°	338.9	412.2	426.6	385.6	330.9	296.8	281.8	273.9	268.8	258.9	247.3
62.5°	289.6	352.1	368.4	338.9	299.0	267.0	255.3	247.7	244.2	235.7	225.4
65°	221.7	273.6	289.3	272.9	252.1	226.4	216.9	210.4	207.3	202.5	195.0
67.5°	166.7	204.6	221.8	210.2	202.7	186.5	180.4	176.9	174.2	170.9	164.6
70°	133.8	161.9	179.7	176.6	170.4	161.9	157.5	155.1	152.3	149.6	144.1
72.5°	107.6	126.9	143.6	145.2	140.1	138.4	134.5	133.5	131.8	128.6	125.6
75°	71.4	84.7	96.3	100.8	102.8	104.5	102.8	102.5	102.1	99.4	97.6
77.5°	46.8	53.9	61.3	68.8	72.1	74.4	74.9	76.2	75.3	73.8	73.0
80°	35.8	37.5	42.7	49.2	54.3	56.4	57.7	58.4	58.1	57.7	56.4
82.5°	26.0	27.5	29.9	34.4	38.7	42.2	43.0	42.8	43.6	43.8	42.7
85°	14.0	14.4	15.1	15.7	18.1	21.8	22.9	23.5	24.3	24.3	22.2
87.5°	9.3	8.2	7.9	7.3	7.5	7.2	8.2	9.0	9.9	9.4	10.0
90°	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3	4.3	7.2	10.3
92.5°	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8	24.0	23.1	22.3
95°	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3	69.2	57.1	44.9
97.5°	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5	158.0	152.6	147.0
100°	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3	231.2	237.1	243.1
102.5°	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7	300.0	304.3	308.4
105°	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3	400.6	403.8	407.1
107.5°	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4	507.0	509.6	512.3
110°	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9	578.3	580.6	583.0





TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2	646.3	648.5	650.6
115°	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2	747.0	748.8	750.6
117.5°	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0	845.3	847.4	849.6
120°	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8	906.5	909.2	911.9
122.5°	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7	967.9	970.1	972.2
125°	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4	1052.8	1055.3	1057.6
127.5°	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6	1135.0	1137.4	1139.7
130°	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7	1186.2	1188.6	1190.9
132.5°	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9	1235.2	1237.6	1239.9
135°	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8	1309.6	1311.3	1313.1
137.5°	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7	1374.0	1376.3	1378.5
140°	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4	1416.2	1418.0	1419.8
142.5°	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8	1455.6	1457.4	1459.2
145°	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0	1511.1	1513.2	1515.3
147.5°	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0	1562.5	1563.8	1565.1
150°	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0	1593.9	1594.8	1595.7
152.5°	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8	1622.3	1622.6	1623.1
155°	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3	1661.8	1661.2	1660.6
157.5°	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8	1693.8	1693.7	1693.6
160°	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1	1712.7	1712.4	1712.2
162.5°	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2	1730.4	1729.7	1728.8
165°	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0	1752.1	1751.2	1750.3
167.5°	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0	1768.9	1767.7	1766.6
170°	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7	1778.5	1777.3	1776.1
172.5°	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1	1784.7	1783.2	1781.8
175°	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3	1792.9	1791.4	1789.9
177.5°	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4	1795.3	1794.1	1793.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	784.2	780.6	778.2	772.7	769.2	765.4	761.5	763.9	763.7	763.4	763.4
5°	757.9	750.0	742.9	733.6	727.8	720.7	715.2	714.5	715.9	711.1	708.4
7.5°	731.8	721.0	710.9	700.7	689.9	681.3	675.9	673.4	669.9	667.0	663.9
10°	713.5	700.9	690.9	678.3	666.7	656.5	650.0	645.5	643.1	640.7	636.3
12.5°	694.6	682.2	669.6	655.3	644.3	632.4	627.6	622.6	618.0	615.3	609.2
15°	667.0	650.9	637.7	622.6	610.4	598.7	591.9	582.0	580.6	577.2	571.1
17.5°	639.4	622.0	603.6	592.5	578.5	566.5	556.1	552.8	543.0	539.3	534.0
20°	617.5	601.5	587.5	572.7	552.6	541.4	533.2	528.7	520.8	516.0	512.6
22.5°	598.7	582.3	566.1	549.0	532.4	519.8	513.7	506.8	502.6	495.9	492.1
25°	571.8	554.0	534.5	516.0	504.1	494.5	485.0	478.8	472.7	469.6	462.8
27.5°	540.5	521.9	503.7	489.7	475.0	465.6	456.9	451.5	444.1	438.9	435.2
30°	523.3	501.4	485.7	473.1	454.2	445.4	438.9	432.0	426.6	421.2	417.3
32.5°	503.3	483.3	468.4	452.8	438.4	428.7	420.3	414.3	409.7	404.5	400.7
35°	472.0	455.3	439.9	424.2	413.6	403.7	393.8	388.7	384.2	379.4	376.0
37.5°	443.7	428.1	413.5	398.6	385.5	377.4	369.4	365.5	359.5	356.3	352.8
40°	426.2	410.9	395.2	380.8	367.1	361.1	353.8	348.0	342.6	340.2	336.4
42.5°	407.2	391.7	378.5	363.0	351.9	343.5	336.9	330.6	326.5	323.0	320.8
45°	378.8	365.1	352.1	336.8	326.2	319.0	311.5	305.7	301.9	299.5	295.8
47.5°	351.2	337.6	324.4	311.0	300.8	292.6	285.1	281.0	276.1	273.1	270.5
50°	331.3	319.0	305.0	292.7	282.5	274.3	268.1	263.0	258.5	254.8	253.1
52.5°	313.0	299.9	287.8	276.3	265.6	256.2	250.7	245.2	241.9	237.6	235.6
55°	282.8	270.2	259.9	248.6	238.1	230.2	223.4	218.6	215.2	210.4	207.7
57.5°	254.4	243.1	230.9	221.1	210.2	203.6	197.9	191.4	187.3	183.5	180.8
60°	235.3	222.3	211.8	202.5	193.0	184.4	179.3	174.2	169.8	165.9	163.6
62.5°	215.3	204.0	194.0	184.0	175.2	167.7	161.8	157.5	153.6	151.2	148.8
65°	184.8	175.9	165.7	157.5	149.3	143.8	139.0	135.3	132.5	130.8	128.8
67.5°	156.7	148.0	139.1	131.0	125.6	121.4	118.2	115.0	113.7	111.5	110.1
70°	138.3	129.5	121.6	115.5	109.9	106.9	104.9	102.5	101.1	98.4	97.0
72.5°	118.4	112.0	106.3	101.2	96.8	94.1	91.5	88.5	86.3	83.4	81.9
75°	93.3	87.5	83.0	79.5	76.9	73.1	69.4	66.3	65.3	64.2	63.8
77.5°	69.0	65.4	62.2	59.3	55.9	53.1	52.3	51.6	51.5	50.9	50.9
80°	54.3	50.9	48.5	45.1	43.1	43.1	43.1	42.4	42.7	42.7	42.7
82.5°	40.4	37.2	35.9	34.7	34.3	34.6	34.6	34.7	34.5	35.0	34.8
85°	20.9	21.1	21.8	21.5	21.8	21.8	22.6	22.2	22.6	21.8	22.6
87.5°	10.3	11.8	12.8	13.9	14.9	15.4	16.0	16.1	16.7	16.9	17.1
90°	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3	35.6	36.7	37.6
92.5°	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9	39.9	41.7	42.8
95°	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5	47.5	49.6	50.6
97.5°	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7	50.0	52.4	53.8
100°	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7	51.1	53.5	54.8
102.5°	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0	65.7	58.3	54.9
105°	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1	134.6	82.2	56.3
107.5°	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2	419.7	381.3	342.3
110°	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7	571.9	562.1	536.0



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8	669.0	669.1	664.8
115°	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2	774.1	777.0	779.1
117.5°	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8	866.1	868.5	869.9
120°	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6	926.9	929.3	930.5
122.5°	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9	985.6	987.3	988.2
125°	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6	1068.3	1068.8	1069.4
127.5°	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6	1152.5	1153.4	1153.6
130°	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1	1203.4	1204.5	1204.8
132.5°	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2	1251.3	1252.5	1252.7
135°	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6
137.5°	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7	1389.1	1390.5	1390.9
140°	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8	1429.9	1431.1	1431.5
142.5°	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8	1468.7	1469.6	1469.7
145°	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2	1522.9	1523.4	1523.8
147.5°	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0	1571.6	1572.3	1571.8
150°	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9	1601.5	1602.0	1602.0
152.5°	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5	1628.5	1629.6	1629.4
155°	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0	1665.4	1667.0	1666.8
157.5°	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8	1697.5	1699.3	1699.1
160°	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0	1715.7	1717.4	1717.3
162.5°	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4	1732.4	1734.4	1734.5
165°	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4	1754.8	1757.2	1757.3
167.5°	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2
170°	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9
172.5°	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5	1787.9	1790.2	1790.1
175°	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1	1795.2	1797.3	1797.2
177.5°	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0	1797.9	1799.8	1799.6
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	760.1	759.8	760.1	759.0	760.1	759.8	760.1	763.4	763.4	763.7	763.9
5°	707.3	706.9	706.0	702.9	706.0	706.9	707.3	708.4	711.1	715.9	714.5
7.5°	661.2	660.8	657.7	657.8	657.7	660.8	661.2	663.9	667.0	669.9	673.4
10°	633.9	634.3	630.2	627.8	630.2	634.3	633.9	636.3	640.7	643.1	645.5
12.5°	607.4	605.8	602.5	599.9	602.5	605.8	607.4	609.2	615.3	618.0	622.6
15°	572.4	569.0	560.8	561.5	560.8	569.0	572.4	571.1	577.2	580.6	582.0
17.5°	531.2	528.7	528.6	523.8	528.6	528.7	531.2	534.0	539.3	543.0	552.8
20°	507.2	505.5	506.1	501.4	506.1	505.5	507.2	512.6	516.0	520.8	528.7
22.5°	488.3	486.6	483.8	482.2	483.8	486.6	488.3	492.1	495.9	502.6	506.8
25°	460.7	458.0	455.3	457.0	455.3	458.0	460.7	462.8	469.6	472.7	478.8
27.5°	433.1	431.1	428.4	428.0	428.4	431.1	433.1	435.2	438.9	444.1	451.5
30°	415.6	413.6	412.2	410.5	412.2	413.6	415.6	417.3	421.2	426.6	432.0
32.5°	397.9	397.5	395.0	394.7	395.0	397.5	397.9	400.7	404.5	409.7	414.3
35°	374.7	372.6	371.9	372.3	371.9	372.6	374.7	376.0	379.4	384.2	388.7
37.5°	352.6	349.9	348.7	347.4	348.7	349.9	352.6	352.8	356.3	359.5	365.5
40°	336.8	334.0	333.3	332.7	333.3	334.0	336.8	336.4	340.2	342.6	348.0
42.5°	319.0	317.9	317.5	316.3	317.5	317.9	319.0	320.8	323.0	326.5	330.6
45°	294.7	294.4	292.4	293.0	292.4	294.4	294.7	295.8	299.5	301.9	305.7
47.5°	269.2	267.7	266.3	267.2	266.3	267.7	269.2	270.5	273.1	276.1	281.0
50°	251.7	251.0	248.0	248.6	248.0	251.0	251.7	253.1	254.8	258.5	263.0
52.5°	234.3	231.7	230.5	230.1	230.5	231.7	234.3	235.6	237.6	241.9	245.2
55°	205.3	202.2	200.8	200.1	200.8	202.2	205.3	207.7	210.4	215.2	218.6
57.5°	176.8	176.0	175.0	175.7	175.0	176.0	176.8	180.8	183.5	187.3	191.4
60°	160.2	160.2	160.2	159.9	160.2	160.2	160.2	163.6	165.9	169.8	174.2
62.5°	147.3	146.5	146.2	146.7	146.2	146.5	147.3	148.8	151.2	153.6	157.5
65°	127.7	127.4	126.0	125.7	126.0	127.4	127.7	128.8	130.8	132.5	135.3
67.5°	109.2	108.0	107.6	107.1	107.6	108.0	109.2	110.1	111.5	113.7	115.0
70°	95.3	94.6	92.6	92.9	92.6	94.6	95.3	97.0	98.4	101.1	102.5
72.5°	80.3	79.5	79.2	78.6	79.2	79.5	80.3	81.9	83.4	86.3	88.5
75°	63.5	63.2	62.9	64.2	62.9	63.2	63.5	63.8	64.2	65.3	66.3
77.5°	50.9	50.9	51.1	50.6	51.1	50.9	50.9	50.9	50.9	51.5	51.6
80°	42.7	42.7	42.4	42.4	42.4	42.7	42.7	42.7	42.7	42.7	42.4
82.5°	34.2	34.5	34.7	34.2	34.7	34.5	34.2	34.8	35.0	34.5	34.7
85°	22.6	22.2	22.9	22.6	22.9	22.2	22.6	22.6	21.8	22.6	22.2
87.5°	17.7	17.3	17.5	17.8	17.5	17.3	17.7	17.1	16.9	16.7	16.1
90°	38.3	38.8	39.4	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3
92.5°	43.2	43.5	43.9	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9
95°	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5
97.5°	54.0	54.3	54.7	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7
100°	55.1	55.4	55.7	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7
102.5°	55.5	56.0	56.5	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0
105°	56.9	57.5	58.1	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1
107.5°	302.8	263.2	223.7	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2
110°	493.7	451.3	408.9	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	655.8	646.8	637.9	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8
115°	780.3	781.5	782.7	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2
117.5°	870.0	870.3	870.6	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8
120°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6
122.5°	988.5	988.6	988.9	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9
125°	1070.1	1070.6	1071.2	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6
127.5°	1153.1	1152.4	1151.8	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6
130°	1204.3	1203.6	1203.0	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1
132.5°	1251.9	1251.1	1250.2	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2
135°	1323.7	1322.9	1322.0	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9
137.5°	1390.4	1389.7	1389.1	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7
140°	1430.8	1430.3	1429.7	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8
142.5°	1468.9	1468.0	1467.2	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2
147.5°	1570.5	1569.1	1567.7	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0
150°	1601.1	1600.2	1599.3	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9
152.5°	1628.1	1626.7	1625.3	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5
155°	1665.0	1663.2	1661.4	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0
157.5°	1696.7	1694.4	1692.1	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8
160°	1715.2	1713.2	1711.1	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0
162.5°	1732.7	1730.8	1729.0	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4
165°	1755.2	1753.2	1751.1	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4
167.5°	1771.8	1769.5	1767.1	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5
170°	1781.5	1779.1	1776.7	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1
172.5°	1787.5	1784.9	1782.3	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5
175°	1794.7	1792.4	1790.0	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1
177.5°	1797.2	1794.8	1792.4	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	761.5	765.4	769.2	772.7	778.2	780.6	784.2	785.5	789.6	795.7	800.6
5°	715.2	720.7	727.8	733.6	742.9	750.0	757.9	765.4	774.3	786.9	798.2
7.5°	675.9	681.3	689.9	700.7	710.9	721.0	731.8	742.0	754.7	772.8	790.8
10°	650.0	656.5	666.7	678.3	690.9	700.9	713.5	726.5	742.2	763.0	784.5
12.5°	627.6	632.4	644.3	655.3	669.6	682.2	694.6	709.8	727.7	749.9	775.8
15°	591.9	598.7	610.4	622.6	637.7	650.9	667.0	685.5	702.9	730.2	761.6
17.5°	556.1	566.5	578.5	592.5	603.6	622.0	639.4	658.3	679.8	708.7	743.2
20°	533.2	541.4	552.6	572.7	587.5	601.5	617.5	641.1	660.8	693.7	729.5
22.5°	513.7	519.8	532.4	549.0	566.1	582.3	598.7	621.2	645.6	676.7	715.6
25°	485.0	494.5	504.1	516.0	534.5	554.0	571.8	590.8	616.8	650.0	692.0
27.5°	456.9	465.6	475.0	489.7	503.7	521.9	540.5	562.4	590.2	625.3	667.9
30°	438.9	445.4	454.2	473.1	485.7	501.4	523.3	542.7	568.6	605.9	650.9
32.5°	420.3	428.7	438.4	452.8	468.4	483.3	503.3	524.4	550.9	587.5	633.7
35°	393.8	403.7	413.6	424.2	439.9	455.3	472.0	495.3	522.2	557.8	603.2
37.5°	369.4	377.4	385.5	398.6	413.5	428.1	443.7	466.6	492.0	530.4	572.0
40°	353.8	361.1	367.1	380.8	395.2	410.9	426.2	446.4	473.7	509.6	549.9
42.5°	336.9	343.5	351.9	363.0	378.5	391.7	407.2	426.1	451.8	488.3	523.6
45°	311.5	319.0	326.2	336.8	352.1	365.1	378.8	396.9	423.2	453.3	484.6
47.5°	285.1	292.6	300.8	311.0	324.4	337.6	351.2	367.3	391.3	420.8	441.9
50°	268.1	274.3	282.5	292.7	305.0	319.0	331.3	348.7	371.6	394.8	413.3
52.5°	250.7	256.2	265.6	276.3	287.8	299.9	313.0	328.0	348.7	370.5	385.1
55°	223.4	230.2	238.1	248.6	259.9	270.2	282.8	298.2	314.6	330.9	340.9
57.5°	197.9	203.6	210.2	221.1	230.9	243.1	254.4	266.4	281.6	293.9	300.4
60°	179.3	184.4	193.0	202.5	211.8	222.3	235.3	247.3	258.9	268.8	273.9
62.5°	161.8	167.7	175.2	184.0	194.0	204.0	215.3	225.4	235.7	244.2	247.7
65°	139.0	143.8	149.3	157.5	165.7	175.9	184.8	195.0	202.5	207.3	210.4
67.5°	118.2	121.4	125.6	131.0	139.1	148.0	156.7	164.6	170.9	174.2	176.9
70°	104.9	106.9	109.9	115.5	121.6	129.5	138.3	144.1	149.6	152.3	155.1
72.5°	91.5	94.1	96.8	101.2	106.3	112.0	118.4	125.6	128.6	131.8	133.5
75°	69.4	73.1	76.9	79.5	83.0	87.5	93.3	97.6	99.4	102.1	102.5
77.5°	52.3	53.1	55.9	59.3	62.2	65.4	69.0	73.0	73.8	75.3	76.2
80°	43.1	43.1	43.1	45.1	48.5	50.9	54.3	56.4	57.7	58.1	58.4
82.5°	34.6	34.6	34.3	34.7	35.9	37.2	40.4	42.7	43.8	43.6	42.8
85°	22.6	21.8	21.8	21.5	21.8	21.1	20.9	22.2	24.3	24.3	23.5
87.5°	16.0	15.4	14.9	13.9	12.8	11.8	10.3	10.0	9.4	9.9	9.0
90°	33.2	32.0	28.2	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3
92.5°	36.0	34.2	31.2	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8
95°	43.4	41.3	38.1	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3
97.5°	45.3	42.9	64.3	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5
100°	46.4	44.0	90.2	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3
102.5°	80.3	87.7	138.2	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7
105°	239.5	291.9	318.6	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3
107.5°	496.7	535.1	530.9	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4
110°	591.5	601.2	598.0	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	668.6	668.4	665.1	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2
115°	768.1	765.2	762.5	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2
117.5°	861.4	859.1	857.6	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0
120°	922.2	919.8	918.9	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8
122.5°	982.3	980.6	979.5	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7
125°	1067.1	1066.5	1065.3	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4
127.5°	1150.6	1149.7	1148.3	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6
130°	1201.0	1199.8	1198.6	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7
132.5°	1248.9	1247.8	1246.8	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9
135°	1322.0	1321.1	1319.9	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8
137.5°	1386.3	1384.8	1384.2	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7
140°	1427.6	1426.4	1425.5	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4
142.5°	1466.8	1465.9	1465.0	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8
145°	1521.6	1521.1	1520.5	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0
147.5°	1570.5	1569.9	1569.2	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0
150°	1600.3	1599.7	1599.1	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0
152.5°	1626.4	1625.3	1625.0	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8
155°	1662.5	1661.0	1660.7	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3
157.5°	1694.0	1692.2	1692.6	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8
160°	1712.2	1710.4	1710.7	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1
162.5°	1728.4	1726.4	1726.6	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2
165°	1750.1	1747.7	1748.0	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0
167.5°	1767.1	1764.8	1764.8	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0
170°	1776.7	1774.3	1774.3	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7
172.5°	1783.2	1780.7	1780.5	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1
175°	1791.1	1789.0	1788.7	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3
177.5°	1794.1	1792.2	1792.0	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	802.2	805.2	809.0	814.8	819.1	823.0	823.8	824.9	827.6	832.2	835.8
5°	807.4	815.3	827.9	840.2	853.5	864.4	874.7	881.9	888.7	903.0	914.6
7.5°	805.7	823.2	843.0	865.1	887.4	909.1	929.2	947.2	965.1	986.0	1009.8
10°	804.7	825.2	851.8	880.1	911.2	941.6	971.0	993.9	1020.6	1044.5	1074.9
12.5°	799.5	829.0	860.9	897.1	935.3	970.4	1009.0	1040.6	1071.0	1105.6	1140.9
15°	792.7	828.6	868.9	917.0	975.1	1017.4	1057.0	1112.1	1149.6	1187.2	1237.8
17.5°	780.3	824.1	874.5	937.0	985.5	1042.4	1102.0	1145.5	1196.1	1249.0	1294.8
20°	770.5	821.4	877.8	939.2	1001.0	1062.9	1120.6	1172.5	1224.8	1285.9	1323.5
22.5°	760.7	811.0	869.6	934.9	1001.3	1066.4	1131.8	1192.8	1251.5	1313.2	1361.2
25°	739.8	799.5	863.1	929.7	995.2	1066.9	1144.9	1212.8	1285.6	1349.1	1394.5
27.5°	718.6	773.4	836.6	904.2	977.0	1061.8	1153.4	1230.7	1303.6	1349.1	1363.3
30°	699.5	757.5	815.6	884.2	963.1	1057.7	1155.1	1243.6	1303.3	1323.1	1308.4
32.5°	680.1	732.7	790.2	860.5	944.3	1047.7	1157.3	1235.9	1271.9	1256.8	1196.9
35°	645.9	693.3	749.0	819.4	915.7	1042.1	1148.3	1201.6	1192.7	1107.2	994.5
37.5°	609.2	647.9	699.5	773.0	886.0	1019.8	1109.5	1117.3	1040.4	909.4	779.2
40°	580.2	615.1	668.1	744.9	863.1	998.0	1070.4	1038.7	919.4	773.6	664.9
42.5°	552.1	581.5	632.5	715.4	841.2	968.2	1012.2	943.0	805.5	667.5	568.8
45°	504.4	532.1	583.4	668.4	796.5	911.2	905.4	785.2	647.6	536.5	454.6
47.5°	459.2	483.4	531.5	618.3	744.0	825.8	771.5	643.6	526.8	437.8	379.3
50°	427.3	451.2	499.0	584.7	701.9	761.6	684.1	560.8	453.9	380.1	333.7
52.5°	396.6	420.0	463.8	547.2	651.0	686.8	603.5	489.2	400.1	336.4	296.5
55°	353.8	371.6	410.9	490.8	568.3	576.5	492.1	396.5	323.1	278.7	251.4
57.5°	310.2	325.5	364.3	427.9	482.3	478.0	398.1	315.4	265.9	232.9	213.1
60°	281.8	296.8	330.9	385.6	426.6	412.2	338.9	272.2	229.9	205.6	189.9
62.5°	255.3	267.0	299.0	338.9	368.4	352.1	289.6	234.5	200.9	180.5	168.0
65°	216.9	226.4	252.1	272.9	289.3	273.6	221.7	183.4	159.2	144.8	136.3
67.5°	180.4	186.5	202.7	210.2	221.8	204.6	166.7	141.1	127.2	115.2	109.2
70°	157.5	161.9	170.4	176.6	179.7	161.9	133.8	115.1	103.5	95.0	91.2
72.5°	134.5	138.4	140.1	145.2	143.6	126.9	107.6	92.7	84.4	78.6	73.7
75°	102.8	104.5	102.8	100.8	96.3	84.7	71.4	63.8	57.7	55.0	53.3
77.5°	74.9	74.4	72.1	68.8	61.3	53.9	46.8	44.2	41.6	40.1	39.6
80°	57.7	56.4	54.3	49.2	42.7	37.5	35.8	34.2	33.2	31.4	31.1
82.5°	43.0	42.2	38.7	34.4	29.9	27.5	26.0	25.4	24.3	23.5	23.5
85°	22.9	21.8	18.1	15.7	15.1	14.4	14.0	14.0	12.7	12.3	12.3
87.5°	8.2	7.2	7.5	7.3	7.9	8.2	9.3	9.5	10.0	10.4	10.2
90°	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3
92.5°	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9
95°	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5
97.5°	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7
100°	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7
102.5°	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0
105°	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1
107.5°	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2
110°	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7





TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8
115°	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2
117.5°	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8
120°	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6
122.5°	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9
125°	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6
127.5°	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6
130°	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1
132.5°	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2
135°	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9
137.5°	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7
140°	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8
142.5°	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8
145°	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2
147.5°	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0
150°	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9
152.5°	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5
155°	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0
157.5°	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8
160°	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0
162.5°	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4
165°	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4
167.5°	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5
170°	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1
172.5°	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5
175°	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1
177.5°	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	841.6	841.6	842.7	846.8	847.3	850.9	849.7
5°	924.9	931.4	933.8	944.1	950.2	952.9	947.4
7.5°	1026.8	1045.1	1053.8	1064.5	1074.0	1076.9	1069.4
10°	1101.2	1120.3	1136.3	1146.2	1155.5	1161.5	1169.5
12.5°	1173.0	1196.5	1211.7	1225.7	1235.2	1243.0	1244.3
15°	1251.1	1286.6	1313.6	1333.4	1343.3	1348.4	1346.4
17.5°	1329.8	1362.7	1382.0	1402.1	1415.9	1416.6	1417.0
20°	1374.4	1406.5	1428.7	1443.7	1459.1	1458.4	1461.8
22.5°	1404.2	1429.4	1446.4	1457.3	1462.6	1460.0	1460.7
25°	1418.1	1425.6	1422.5	1405.1	1400.7	1384.6	1387.3
27.5°	1346.2	1310.7	1274.0	1226.6	1189.4	1159.6	1161.1
30°	1248.7	1185.8	1114.1	1054.0	1000.1	985.0	952.9
32.5°	1112.3	1018.1	934.1	878.1	831.7	819.1	791.1
35°	881.2	789.6	703.2	651.3	630.8	602.2	601.8
37.5°	684.9	604.3	558.7	519.7	499.3	481.9	480.2
40°	576.2	513.4	478.8	450.8	430.7	417.7	414.6
42.5°	500.2	449.4	417.1	399.8	384.2	377.6	372.6
45°	408.5	374.3	351.8	336.1	328.9	323.8	321.0
47.5°	341.7	318.8	303.4	293.0	287.1	281.8	283.2
50°	305.3	286.6	275.3	265.4	260.9	257.2	257.5
52.5°	276.1	259.2	250.1	243.0	237.5	234.8	233.4
55°	234.3	223.7	214.5	209.4	206.3	202.5	201.5
57.5°	199.8	191.6	184.1	178.3	177.6	174.0	174.4
60°	176.9	170.0	163.9	160.9	158.5	155.4	156.4
62.5°	158.1	152.3	146.7	144.2	141.8	139.6	140.0
65°	129.5	123.9	120.6	119.2	118.2	117.2	116.1
67.5°	103.2	99.8	97.6	94.7	92.6	92.3	91.2
70°	86.8	82.3	78.6	74.8	73.7	73.4	73.7
72.5°	69.6	66.7	65.7	63.8	63.7	62.8	63.4
75°	52.3	51.3	50.6	49.2	49.2	49.2	49.2
77.5°	38.5	37.9	37.5	37.2	36.9	36.4	36.4
80°	30.1	29.7	29.1	29.1	28.7	29.1	28.7
82.5°	22.6	22.6	21.9	21.9	21.6	21.4	21.6
85°	11.6	11.2	11.9	11.2	11.6	11.0	11.6
87.5°	10.4	10.6	10.5	10.6	10.5	11.1	10.7
90°	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	571.9	562.1	536.0	493.7	451.3	408.9	366.6



TEST NUMBER: P332426-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)