

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332238-935

Luminaire Tested: **S123DIW-S1165D1535U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332238-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9384.1 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	65		57	55	54		44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45		44	41	38		35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39		39	35	32		31	28	26	22
5	67	56	47	41	61	51	44	39	43	37	33		35	31	28		28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29		32	28	24		25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18		22	18	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	1.6
10°-20°	418.7	4.5
20°-30°	618.4	6.6
30°-40°	722.4	7.7
40°-50°	726.3	7.7
50°-60°	638.0	6.8
60°-70°	475.3	5.1
70°-80°	270.8	2.9
80°-90°	82.6	0.9
90°-100°	63.0	0.7
100°-110°	300.2	3.2
110°-120°	721.1	7.7
120°-130°	918.3	9.8
130°-140°	981.1	10.5
140°-150°	917.5	9.8
150°-160°	740.1	7.9
160°-170°	477.6	5.1
170°-180°	164.6	1.8
0°-30°	1185.3	12.6
0°-40°	1907.7	20.3
0°-60°	3272.0	34.9
0°-90°	4100.6	43.7
90°-120°	1084.3	11.6
90°-150°	3901.2	41.6
90°-180°	5283.0	56.3
0°-180°	9384.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	14	31	36	39	8
95°	78	29	40	48	49	97
105°	384	390	282	67	57	407
115°	720	728	739	751	757	710
125°	1014	1024	1030	1032	1035	905
135°	1263	1270	1276	1279	1276	972
145°	1457	1466	1469	1471	1471	912
155°	1605	1603	1604	1610	1603	739
165°	1693	1689	1688	1697	1689	478
175°	1732	1726	1727	1735	1726	165
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.4	28.2	28.1	28.0	27.8	28.0	28.5	29.0	29.5	30.0	30.0
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0
92.5°	23.9	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8
95°	78.5	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9
97.5°	157.8	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7
100°	217.6	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8
102.5°	285.5	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6
105°	383.6	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3
107.5°	487.1	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6
110°	556.0	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1



TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	622.0	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6
115°	719.5	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7
117.5°	814.0	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7
120°	872.7	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4
122.5°	932.5	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5
125°	1014.3	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4
127.5°	1093.6	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9
130°	1143.0	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6
132.5°	1190.4	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9
135°	1262.7	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4
137.5°	1324.5	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5
140°	1365.7	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5
142.5°	1403.8	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3
145°	1457.1	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2
147.5°	1507.3	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4
150°	1538.2	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2
152.5°	1566.0	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4
155°	1605.1	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2
157.5°	1635.5	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6
160°	1654.1	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2
162.5°	1671.5	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9
165°	1692.6	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8
167.5°	1709.1	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2
170°	1718.4	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5
172.5°	1724.6	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7
175°	1732.5	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4
177.5°	1734.6	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	30.0	30.0	30.0	30.0	30.1	30.2	30.3	30.5
90°	33.1	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	36.6	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.1	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	47.0	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	70.5	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	180.6	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	442.4	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	561.6	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332238-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.8	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	744.6	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	834.1	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	892.8	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	950.0	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1030.9	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1111.9	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1160.7	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1207.1	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1339.9	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1379.6	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1417.2	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1469.8	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1516.9	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1545.8	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1571.4	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1606.7	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1637.4	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1654.9	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1670.8	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1692.0	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1724.0	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1731.4	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1734.1	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)