

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332210-935

Luminaire Tested: **S123DIW-S1165D460U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332210-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D460U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5804.7 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73	
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	69	67	66	66	66	66	62	
2	94	87	81	75	89	83	77	73	75	71	67	68	64	61	61	58	56	56	56	56	53	
3	86	77	69	63	82	73	66	61	66	61	57	60	56	52	54	51	48	48	48	48	45	
4	79	68	60	54	75	65	58	52	59	53	49	54	49	45	49	45	42	42	42	42	39	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	37	37	37	37	34	
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	40	36	32	32	32	32	30	
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	37	32	29	29	29	29	26	
8	58	45	37	32	55	44	36	31	40	34	29	37	31	28	34	29	26	26	26	26	24	
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	21	21	21	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	2.4
10°-20°	441.2	7.6
20°-30°	740.4	12.8
30°-40°	838.4	14.4
40°-50°	751.8	13.0
50°-60°	606.7	10.5
60°-70°	422.8	7.3
70°-80°	222.2	3.8
80°-90°	55.8	1.0
90°-100°	18.9	0.3
100°-110°	90.2	1.6
110°-120°	216.7	3.7
120°-130°	276.0	4.8
130°-140°	294.8	5.1
140°-150°	275.7	4.7
150°-160°	222.4	3.8
160°-170°	143.5	2.5
170°-180°	49.5	0.9
0°-30°	1319.2	22.7
0°-40°	2157.5	37.2
0°-60°	3516.1	60.6
0°-90°	4216.9	72.6
90°-120°	325.9	5.6
90°-150°	1172.4	20.2
90°-180°	1588.0	27.4
0°-180°	5804.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	53
90°	12	0	12	0	12	7
95°	15	24	15	24	15	12
105°	17	115	17	115	17	39
115°	228	216	228	216	228	210
125°	311	305	311	305	311	278
135°	383	379	383	379	383	296
145°	442	438	442	438	442	276
155°	482	482	482	482	482	222
165°	508	509	508	509	508	143
175°	519	521	519	521	519	49
180°	521	521	521	521	521	



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	18.6	17.5	17.9	18.4	17.9	18.3	18.9	19.3	19.8	20.2	20.6
90°	11.6	11.5	11.3	11.1	10.9	10.7	10.3	10.0	9.6	9.3	8.2
92.5°	12.8	12.7	12.7	12.6	12.4	12.1	11.5	11.0	10.4	9.9	9.0
95°	14.7	14.7	14.7	14.7	14.7	14.4	13.8	13.2	12.6	12.0	11.0
97.5°	15.9	15.8	15.8	15.7	15.6	15.2	14.6	13.9	13.2	12.5	18.7
100°	16.3	16.2	16.1	16.0	15.9	15.5	14.8	14.1	13.4	12.7	26.2
102.5°	16.5	16.4	16.3	16.1	15.9	17.0	19.0	21.2	23.3	25.5	40.1
105°	17.0	16.9	16.7	16.5	16.4	23.8	39.1	54.2	69.5	84.7	92.5
107.5°	53.5	64.9	76.4	87.8	99.4	110.6	121.8	132.9	144.1	155.2	154.0
110°	106.4	118.6	131.0	143.3	155.6	163.1	165.9	168.8	171.6	174.4	173.5



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	182.5	185.1	187.7	190.3	192.9	194.2	194.1	194.1	194.0	194.0	193.0
115°	227.5	227.1	226.8	226.4	226.1	225.5	224.6	223.8	222.9	222.1	221.3
117.5°	252.7	252.6	252.5	252.4	252.4	252.0	251.3	250.6	249.9	249.3	248.9
120°	270.0	270.0	270.0	270.0	270.0	269.7	269.0	268.3	267.6	266.9	266.7
122.5°	287.1	287.0	286.9	286.8	286.7	286.5	286.0	285.5	285.0	284.6	284.2
125°	311.0	310.8	310.6	310.5	310.3	310.1	310.0	309.8	309.6	309.4	309.1
127.5°	334.1	334.2	334.4	334.6	334.8	334.7	334.4	334.2	333.9	333.6	333.2
130°	348.9	349.0	349.2	349.4	349.6	349.5	349.1	348.8	348.4	348.1	347.8
132.5°	362.6	362.7	363.0	363.3	363.5	363.4	363.1	362.7	362.4	362.1	361.8
135°	383.3	383.6	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3	383.0
137.5°	402.9	403.1	403.3	403.5	403.6	403.5	403.0	402.7	402.3	401.8	401.7
140°	414.7	414.8	415.0	415.2	415.3	415.3	414.9	414.6	414.2	413.9	413.6
142.5°	425.5	425.8	426.0	426.2	426.5	426.5	426.2	425.9	425.6	425.3	425.1
145°	442.1	442.1	442.1	442.1	442.1	442.0	441.9	441.7	441.5	441.3	441.2
147.5°	454.5	455.0	455.3	455.7	456.1	456.2	456.1	455.9	455.7	455.6	455.4
150°	463.8	464.1	464.3	464.6	464.9	464.9	464.7	464.5	464.3	464.2	464.0
152.5°	471.2	471.7	472.0	472.4	472.8	472.9	472.5	472.3	471.9	471.7	471.5
155°	481.6	482.1	482.6	483.1	483.6	483.7	483.3	482.8	482.4	482.0	481.9
157.5°	490.3	491.0	491.7	492.3	493.0	493.1	492.6	492.1	491.5	491.0	491.1
160°	495.9	496.5	497.1	497.7	498.3	498.3	497.8	497.3	496.8	496.3	496.4
162.5°	501.2	501.7	502.2	502.7	503.3	503.3	502.7	502.1	501.5	500.9	501.0
165°	507.6	508.2	508.8	509.3	509.9	509.9	509.2	508.5	507.8	507.1	507.2
167.5°	512.1	512.8	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1	512.1
170°	514.9	515.6	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9	514.9
172.5°	516.4	517.2	517.9	518.7	519.4	519.4	518.8	518.1	517.4	516.7	516.7
175°	518.8	519.4	520.1	520.8	521.5	521.5	520.9	520.3	519.7	519.1	519.0
177.5°	519.4	520.1	520.8	521.5	522.2	522.3	521.7	521.2	520.6	520.0	520.0
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	21.4	21.8	19.9	17.6	16.3	14.5	14.3	13.1	12.1	12.3	12.0
90°	7.1	5.9	4.8	3.8	2.9	2.1	1.2	0.3	1.2	2.1	2.9
92.5°	8.2	7.4	6.5	6.2	6.5	6.7	7.0	7.2	7.0	6.7	6.5
95°	10.1	9.1	8.2	9.5	13.0	16.5	20.1	23.6	20.1	16.5	13.0
97.5°	24.8	31.0	37.2	41.1	42.7	44.3	45.8	47.4	45.8	44.3	42.7
100°	39.6	53.0	66.4	72.2	70.5	68.8	67.1	65.3	67.1	68.8	70.5
102.5°	54.8	69.4	84.0	90.7	89.5	88.3	87.0	85.8	87.0	88.3	89.5
105°	100.2	107.9	115.6	119.1	118.1	117.2	116.2	115.3	116.2	117.2	118.1
107.5°	152.8	151.6	150.4	149.4	148.6	147.9	147.1	146.4	147.1	147.9	148.6
110°	172.5	171.6	170.7	169.9	169.2	168.5	167.8	167.1	167.8	168.5	169.2



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	192.1	191.1	190.2	189.4	188.7	188.1	187.5	186.9	187.5	188.1	188.7
115°	220.5	219.7	219.0	218.3	217.7	217.2	216.7	216.2	216.7	217.2	217.7
117.5°	248.5	248.1	247.7	247.2	246.5	245.9	245.3	244.6	245.3	245.9	246.5
120°	266.4	266.1	265.9	265.4	264.6	263.8	263.0	262.3	263.0	263.8	264.6
122.5°	283.9	283.6	283.3	282.8	282.1	281.5	280.9	280.3	280.9	281.5	282.1
125°	308.8	308.4	308.1	307.5	306.9	306.2	305.5	304.8	305.5	306.2	306.9
127.5°	332.8	332.3	331.9	331.4	330.7	330.0	329.3	328.6	329.3	330.0	330.7
130°	347.5	347.2	346.8	346.3	345.6	344.9	344.2	343.5	344.2	344.9	345.6
132.5°	361.5	361.3	360.9	360.5	359.8	359.1	358.4	357.7	358.4	359.1	359.8
135°	382.6	382.3	381.9	381.5	381.0	380.5	380.0	379.4	380.0	380.5	381.0
137.5°	401.5	401.3	401.1	400.6	400.0	399.3	398.7	398.0	398.7	399.3	400.0
140°	413.4	413.1	412.8	412.5	412.0	411.5	411.0	410.4	411.0	411.5	412.0
142.5°	424.8	424.6	424.3	424.0	423.4	422.9	422.4	421.9	422.4	422.9	423.4
145°	441.0	440.8	440.7	440.3	439.7	439.1	438.5	437.9	438.5	439.1	439.7
147.5°	455.2	455.0	454.9	454.5	454.2	453.7	453.4	453.0	453.4	453.7	454.2
150°	463.8	463.6	463.5	463.3	463.0	462.8	462.5	462.3	462.5	462.8	463.0
152.5°	471.4	471.3	471.2	471.1	471.0	470.9	470.7	470.6	470.7	470.9	471.0
155°	481.8	481.7	481.6	481.7	481.9	482.0	482.2	482.3	482.2	482.0	481.9
157.5°	491.2	491.3	491.4	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5
160°	496.5	496.5	496.6	496.7	496.8	496.9	497.0	497.1	497.0	496.9	496.8
162.5°	501.1	501.2	501.3	501.4	501.7	501.9	502.1	502.3	502.1	501.9	501.7
165°	507.3	507.4	507.5	507.6	507.9	508.2	508.4	508.7	508.4	508.2	507.9
167.5°	512.1	512.1	512.1	512.3	512.6	513.0	513.3	513.7	513.3	513.0	512.6
170°	514.9	514.9	514.9	515.1	515.4	515.7	516.1	516.4	516.1	515.7	515.4
172.5°	516.6	516.5	516.4	516.6	517.0	517.5	517.9	518.2	517.9	517.5	517.0
175°	518.9	518.8	518.8	518.9	519.4	519.8	520.2	520.6	520.2	519.8	519.4
177.5°	519.9	519.9	519.8	519.9	520.2	520.6	520.9	521.2	520.9	520.6	520.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	11.6	12.3	12.1	12.7	12.5	13.3	13.3	12.3	12.3	14.0	12.0
90°	3.8	4.8	5.9	7.1	8.2	9.3	9.6	10.0	10.3	10.7	10.9
92.5°	6.2	6.5	7.4	8.2	9.0	9.9	10.4	11.0	11.5	12.1	12.4
95°	9.5	8.2	9.1	10.1	11.0	12.0	12.6	13.2	13.8	14.4	14.7
97.5°	41.1	37.2	31.0	24.8	18.7	12.5	13.2	13.9	14.6	15.2	15.6
100°	72.2	66.4	53.0	39.6	26.2	12.7	13.4	14.1	14.8	15.5	15.9
102.5°	90.7	84.0	69.4	54.8	40.1	25.5	23.3	21.2	19.0	17.0	15.9
105°	119.1	115.6	107.9	100.2	92.5	84.7	69.5	54.2	39.1	23.8	16.4
107.5°	149.4	150.4	151.6	152.8	154.0	155.2	144.1	132.9	121.8	110.6	99.4
110°	169.9	170.7	171.6	172.5	173.5	174.4	171.6	168.8	165.9	163.1	155.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	189.4	190.2	191.1	192.1	193.0	194.0	194.0	194.1	194.1	194.2	192.9
115°	218.3	219.0	219.7	220.5	221.3	222.1	222.9	223.8	224.6	225.5	226.1
117.5°	247.2	247.7	248.1	248.5	248.9	249.3	249.9	250.6	251.3	252.0	252.4
120°	265.4	265.9	266.1	266.4	266.7	266.9	267.6	268.3	269.0	269.7	270.0
122.5°	282.8	283.3	283.6	283.9	284.2	284.6	285.0	285.5	286.0	286.5	286.7
125°	307.5	308.1	308.4	308.8	309.1	309.4	309.6	309.8	310.0	310.1	310.3
127.5°	331.4	331.9	332.3	332.8	333.2	333.6	333.9	334.2	334.4	334.7	334.8
130°	346.3	346.8	347.2	347.5	347.8	348.1	348.4	348.8	349.1	349.5	349.6
132.5°	360.5	360.9	361.3	361.5	361.8	362.1	362.4	362.7	363.1	363.4	363.5
135°	381.5	381.9	382.3	382.6	383.0	383.3	383.6	383.8	384.1	384.4	384.4
137.5°	400.6	401.1	401.3	401.5	401.7	401.8	402.3	402.7	403.0	403.5	403.6
140°	412.5	412.8	413.1	413.4	413.6	413.9	414.2	414.6	414.9	415.3	415.3
142.5°	424.0	424.3	424.6	424.8	425.1	425.3	425.6	425.9	426.2	426.5	426.5
145°	440.3	440.7	440.8	441.0	441.2	441.3	441.5	441.7	441.9	442.0	442.1
147.5°	454.5	454.9	455.0	455.2	455.4	455.6	455.7	455.9	456.1	456.2	456.1
150°	463.3	463.5	463.6	463.8	464.0	464.2	464.3	464.5	464.7	464.9	464.9
152.5°	471.1	471.2	471.3	471.4	471.5	471.7	471.9	472.3	472.5	472.9	472.8
155°	481.7	481.6	481.7	481.8	481.9	482.0	482.4	482.8	483.3	483.7	483.6
157.5°	491.5	491.4	491.3	491.2	491.1	491.0	491.5	492.1	492.6	493.1	493.0
160°	496.7	496.6	496.5	496.5	496.4	496.3	496.8	497.3	497.8	498.3	498.3
162.5°	501.4	501.3	501.2	501.1	501.0	500.9	501.5	502.1	502.7	503.3	503.3
165°	507.6	507.5	507.4	507.3	507.2	507.1	507.8	508.5	509.2	509.9	509.9
167.5°	512.3	512.1	512.1	512.1	512.1	512.1	512.8	513.5	514.1	514.8	514.8
170°	515.1	514.9	514.9	514.9	514.9	514.9	515.6	516.3	516.9	517.6	517.6
172.5°	516.6	516.4	516.5	516.6	516.7	516.7	517.4	518.1	518.8	519.4	519.4
175°	518.9	518.8	518.8	518.9	519.0	519.1	519.7	520.3	520.9	521.5	521.5
177.5°	519.9	519.8	519.9	519.9	520.0	520.0	520.6	521.2	521.7	522.3	522.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	12.0	12.0	11.5	11.0	11.5	12.0	12.0	12.0	14.0	12.3	12.3
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.7	10.3	10.0
92.5°	12.6	12.7	12.7	12.8	12.7	12.7	12.6	12.4	12.1	11.5	11.0
95°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.4	13.8	13.2
97.5°	15.7	15.8	15.8	15.9	15.8	15.8	15.7	15.6	15.2	14.6	13.9
100°	16.0	16.1	16.2	16.3	16.2	16.1	16.0	15.9	15.5	14.8	14.1
102.5°	16.1	16.3	16.4	16.5	16.4	16.3	16.1	15.9	17.0	19.0	21.2
105°	16.5	16.7	16.9	17.0	16.9	16.7	16.5	16.4	23.8	39.1	54.2
107.5°	87.8	76.4	64.9	53.5	64.9	76.4	87.8	99.4	110.6	121.8	132.9
110°	143.3	131.0	118.6	106.4	118.6	131.0	143.3	155.6	163.1	165.9	168.8



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	190.3	187.7	185.1	182.5	185.1	187.7	190.3	192.9	194.2	194.1	194.1
115°	226.4	226.8	227.1	227.5	227.1	226.8	226.4	226.1	225.5	224.6	223.8
117.5°	252.4	252.5	252.6	252.7	252.6	252.5	252.4	252.4	252.0	251.3	250.6
120°	270.0	270.0	270.0	270.0	270.0	270.0	270.0	270.0	269.7	269.0	268.3
122.5°	286.8	286.9	287.0	287.1	287.0	286.9	286.8	286.7	286.5	286.0	285.5
125°	310.5	310.6	310.8	311.0	310.8	310.6	310.5	310.3	310.1	310.0	309.8
127.5°	334.6	334.4	334.2	334.1	334.2	334.4	334.6	334.8	334.7	334.4	334.2
130°	349.4	349.2	349.0	348.9	349.0	349.2	349.4	349.6	349.5	349.1	348.8
132.5°	363.3	363.0	362.7	362.6	362.7	363.0	363.3	363.5	363.4	363.1	362.7
135°	384.1	383.8	383.6	383.3	383.6	383.8	384.1	384.4	384.4	384.1	383.8
137.5°	403.5	403.3	403.1	402.9	403.1	403.3	403.5	403.6	403.5	403.0	402.7
140°	415.2	415.0	414.8	414.7	414.8	415.0	415.2	415.3	415.3	414.9	414.6
142.5°	426.2	426.0	425.8	425.5	425.8	426.0	426.2	426.5	426.5	426.2	425.9
145°	442.1	442.1	442.1	442.1	442.1	442.1	442.1	442.1	442.0	441.9	441.7
147.5°	455.7	455.3	455.0	454.5	455.0	455.3	455.7	456.1	456.2	456.1	455.9
150°	464.6	464.3	464.1	463.8	464.1	464.3	464.6	464.9	464.9	464.7	464.5
152.5°	472.4	472.0	471.7	471.2	471.7	472.0	472.4	472.8	472.9	472.5	472.3
155°	483.1	482.6	482.1	481.6	482.1	482.6	483.1	483.6	483.7	483.3	482.8
157.5°	492.3	491.7	491.0	490.3	491.0	491.7	492.3	493.0	493.1	492.6	492.1
160°	497.7	497.1	496.5	495.9	496.5	497.1	497.7	498.3	498.3	497.8	497.3
162.5°	502.7	502.2	501.7	501.2	501.7	502.2	502.7	503.3	503.3	502.7	502.1
165°	509.3	508.8	508.2	507.6	508.2	508.8	509.3	509.9	509.9	509.2	508.5
167.5°	514.1	513.5	512.8	512.1	512.8	513.5	514.1	514.8	514.8	514.1	513.5
170°	516.9	516.3	515.6	514.9	515.6	516.3	516.9	517.6	517.6	516.9	516.3
172.5°	518.7	517.9	517.2	516.4	517.2	517.9	518.7	519.4	519.4	518.8	518.1
175°	520.8	520.1	519.4	518.8	519.4	520.1	520.8	521.5	521.5	520.9	520.3
177.5°	521.5	520.8	520.1	519.4	520.1	520.8	521.5	522.2	522.3	521.7	521.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	13.3	13.3	12.5	12.7	12.1	12.3	11.6	12.0	12.3	12.1	13.1
90°	9.6	9.3	8.2	7.1	5.9	4.8	3.8	2.9	2.1	1.2	0.3
92.5°	10.4	9.9	9.0	8.2	7.4	6.5	6.2	6.5	6.7	7.0	7.2
95°	12.6	12.0	11.0	10.1	9.1	8.2	9.5	13.0	16.5	20.1	23.6
97.5°	13.2	12.5	18.7	24.8	31.0	37.2	41.1	42.7	44.3	45.8	47.4
100°	13.4	12.7	26.2	39.6	53.0	66.4	72.2	70.5	68.8	67.1	65.3
102.5°	23.3	25.5	40.1	54.8	69.4	84.0	90.7	89.5	88.3	87.0	85.8
105°	69.5	84.7	92.5	100.2	107.9	115.6	119.1	118.1	117.2	116.2	115.3
107.5°	144.1	155.2	154.0	152.8	151.6	150.4	149.4	148.6	147.9	147.1	146.4
110°	171.6	174.4	173.5	172.5	171.6	170.7	169.9	169.2	168.5	167.8	167.1



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	194.0	194.0	193.0	192.1	191.1	190.2	189.4	188.7	188.1	187.5	186.9
115°	222.9	222.1	221.3	220.5	219.7	219.0	218.3	217.7	217.2	216.7	216.2
117.5°	249.9	249.3	248.9	248.5	248.1	247.7	247.2	246.5	245.9	245.3	244.6
120°	267.6	266.9	266.7	266.4	266.1	265.9	265.4	264.6	263.8	263.0	262.3
122.5°	285.0	284.6	284.2	283.9	283.6	283.3	282.8	282.1	281.5	280.9	280.3
125°	309.6	309.4	309.1	308.8	308.4	308.1	307.5	306.9	306.2	305.5	304.8
127.5°	333.9	333.6	333.2	332.8	332.3	331.9	331.4	330.7	330.0	329.3	328.6
130°	348.4	348.1	347.8	347.5	347.2	346.8	346.3	345.6	344.9	344.2	343.5
132.5°	362.4	362.1	361.8	361.5	361.3	360.9	360.5	359.8	359.1	358.4	357.7
135°	383.6	383.3	383.0	382.6	382.3	381.9	381.5	381.0	380.5	380.0	379.4
137.5°	402.3	401.8	401.7	401.5	401.3	401.1	400.6	400.0	399.3	398.7	398.0
140°	414.2	413.9	413.6	413.4	413.1	412.8	412.5	412.0	411.5	411.0	410.4
142.5°	425.6	425.3	425.1	424.8	424.6	424.3	424.0	423.4	422.9	422.4	421.9
145°	441.5	441.3	441.2	441.0	440.8	440.7	440.3	439.7	439.1	438.5	437.9
147.5°	455.7	455.6	455.4	455.2	455.0	454.9	454.5	454.2	453.7	453.4	453.0
150°	464.3	464.2	464.0	463.8	463.6	463.5	463.3	463.0	462.8	462.5	462.3
152.5°	471.9	471.7	471.5	471.4	471.3	471.2	471.1	471.0	470.9	470.7	470.6
155°	482.4	482.0	481.9	481.8	481.7	481.6	481.7	481.9	482.0	482.2	482.3
157.5°	491.5	491.0	491.1	491.2	491.3	491.4	491.5	491.5	491.5	491.5	491.5
160°	496.8	496.3	496.4	496.5	496.5	496.6	496.7	496.8	496.9	497.0	497.1
162.5°	501.5	500.9	501.0	501.1	501.2	501.3	501.4	501.7	501.9	502.1	502.3
165°	507.8	507.1	507.2	507.3	507.4	507.5	507.6	507.9	508.2	508.4	508.7
167.5°	512.8	512.1	512.1	512.1	512.1	512.1	512.3	512.6	513.0	513.3	513.7
170°	515.6	514.9	514.9	514.9	514.9	514.9	515.1	515.4	515.7	516.1	516.4
172.5°	517.4	516.7	516.7	516.6	516.5	516.4	516.6	517.0	517.5	517.9	518.2
175°	519.7	519.1	519.0	518.9	518.8	518.8	518.9	519.4	519.8	520.2	520.6
177.5°	520.6	520.0	520.0	519.9	519.9	519.8	519.9	520.2	520.6	520.9	521.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.3	14.5	16.3	17.6	19.9	21.8	21.4	20.6	20.2	19.8	19.3
90°	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6	10.0
92.5°	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4	11.0
95°	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6	13.2
97.5°	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2	13.9
100°	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4	14.1
102.5°	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3	21.2
105°	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5	54.2
107.5°	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1	132.9
110°	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6	168.8



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0	194.1
115°	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9	223.8
117.5°	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9	250.6
120°	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6	268.3
122.5°	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0	285.5
125°	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6	309.8
127.5°	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9	334.2
130°	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4	348.8
132.5°	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4	362.7
135°	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6	383.8
137.5°	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3	402.7
140°	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2	414.6
142.5°	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6	425.9
145°	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5	441.7
147.5°	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7	455.9
150°	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3	464.5
152.5°	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9	472.3
155°	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4	482.8
157.5°	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5	492.1
160°	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8	497.3
162.5°	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5	502.1
165°	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8	508.5
167.5°	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8	513.5
170°	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6	516.3
172.5°	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4	518.1
175°	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7	520.3
177.5°	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6	521.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	18.9	18.3	17.9	18.4	17.9	17.5	18.6
90°	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332210-935

CATALOG NUMBER: S123DIW-S1165D460U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)