

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332446-940

Luminaire Tested: **S123RDIW-S775D1535U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332446-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1535U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8192.3 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29
2	86	79	74	69	78	72	67	63	58	54	51	45	42	40	33	31	30	25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	28	26	21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	33	29	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11739	11739	11739	11739
5°	13993	11788	10381	11788
10°	17472	11721	9379	11721
15°	20508	11602	8553	11602
20°	22888	11423	7851	11423
25°	22523	11233	7418	11233
30°	16189	11059	6975	11059
35°	10809	10834	6687	10834
40°	7964	10561	6389	10561
45°	6680	10085	6098	10085
50°	5894	9460	5690	9460
55°	5168	8743	5134	8743
60°	4603	8060	4704	8060
65°	4042	7325	4376	7325
70°	3175	6672	3997	6672
75°	2795	5827	3647	5827
80°	2430	4947	3589	4947
85°	1964	3977	3816	3977



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	1.3
10°-20°	335.1	4.1
20°-30°	526.4	6.4
30°-40°	549.2	6.7
40°-50°	470.0	5.7
50°-60°	358.2	4.4
60°-70°	229.6	2.8
70°-80°	110.5	1.3
80°-90°	34.3	0.4
90°-100°	65.2	0.8
100°-110°	310.9	3.8
110°-120°	746.8	9.1
120°-130°	951.0	11.6
130°-140°	1016.1	12.4
140°-150°	950.2	11.6
150°-160°	766.5	9.4
160°-170°	494.7	6.0
170°-180°	170.5	2.1
0°-30°	968.7	11.8
0°-40°	1517.9	18.5
0°-60°	2346.1	28.6
0°-90°	2720.4	33.2
90°-120°	1123.0	13.7
90°-150°	4040.3	49.3
90°-180°	5472.0	66.8
0°-180°	8192.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1295	1091	961	1091	1295	134
15°	1840	1041	768	1041	1840	522
25°	1896	946	625	946	1896	815
35°	823	824	509	824	823	539
45°	439	662	401	662	439	345
55°	275	466	274	466	275	249
65°	159	288	172	288	159	156
75°	67	140	88	140	67	72
85°	16	32	31	32	16	19
90°	40	1	40	1	40	19
95°	51	81	51	81	51	42
105°	59	397	59	397	59	134
115°	784	745	784	745	784	724
125°	1072	1050	1072	1050	1072	957
135°	1321	1308	1321	1308	1321	1019
145°	1524	1509	1524	1509	1524	951
155°	1660	1662	1660	1662	1660	765
165°	1749	1753	1749	1753	1749	494
175°	1788	1794	1788	1794	1788	170
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1161.5	1163.1	1158.2	1157.4	1151.8	1150.3	1150.3	1142.5	1137.6	1131.3	1127.6
5°	1295.0	1302.5	1298.8	1290.4	1276.4	1273.1	1264.3	1250.3	1234.4	1214.8	1205.4
7.5°	1461.8	1472.0	1468.1	1455.1	1440.5	1428.6	1403.6	1380.3	1347.7	1319.1	1294.7
10°	1598.5	1587.8	1579.4	1566.7	1553.3	1531.2	1505.1	1469.2	1427.6	1395.0	1358.5
12.5°	1700.8	1699.1	1688.5	1675.4	1656.4	1635.5	1603.4	1559.6	1511.3	1464.1	1422.5
15°	1840.3	1843.2	1836.1	1822.6	1795.5	1758.6	1710.1	1691.8	1622.8	1571.5	1520.1
17.5°	1936.9	1936.4	1935.4	1916.6	1889.0	1862.8	1817.8	1769.9	1707.3	1635.0	1565.8
20°	1998.1	1993.5	1994.4	1973.4	1952.8	1922.5	1878.7	1809.1	1757.7	1674.2	1602.7
22.5°	1996.6	1995.7	1999.3	1992.1	1977.1	1953.9	1919.3	1860.6	1795.1	1710.7	1630.3
25°	1896.4	1892.7	1914.6	1920.7	1944.5	1948.7	1938.4	1906.2	1844.1	1757.2	1657.8
27.5°	1587.2	1585.1	1625.8	1676.8	1741.3	1791.6	1840.1	1863.6	1844.1	1781.9	1682.3
30°	1302.5	1346.4	1367.0	1440.7	1522.9	1621.0	1706.8	1788.5	1808.6	1781.5	1699.8
32.5°	1081.5	1119.7	1136.8	1200.2	1276.8	1391.6	1520.5	1636.1	1717.9	1738.6	1689.3
35°	822.6	823.0	862.3	890.3	961.3	1079.3	1204.5	1359.5	1513.5	1630.2	1642.4
37.5°	656.4	658.7	682.4	710.3	763.6	826.1	936.2	1065.1	1243.0	1422.2	1527.2
40°	566.8	571.0	588.7	616.3	654.5	701.7	787.6	909.0	1057.4	1256.8	1419.7
42.5°	509.3	516.0	525.2	546.4	570.2	614.3	683.8	777.5	912.5	1101.0	1289.0
45°	438.8	442.6	449.6	459.4	480.9	511.7	558.4	621.3	733.4	885.2	1073.3
47.5°	387.1	385.1	392.5	400.5	414.7	435.8	467.1	518.5	598.4	720.1	879.8
50°	352.0	351.5	356.7	362.7	376.3	391.7	417.4	456.1	519.6	620.5	766.6
52.5°	319.1	320.9	324.6	332.2	341.9	354.4	377.4	405.3	459.9	546.9	668.7
55°	275.4	276.9	282.0	286.1	293.2	305.8	320.3	343.6	380.9	441.7	542.0
57.5°	238.4	237.8	242.7	243.8	251.7	262.0	273.2	291.3	318.4	363.5	431.1
60°	213.8	212.4	216.6	219.9	224.1	232.5	241.8	259.6	281.1	314.1	372.1
62.5°	191.5	190.7	193.9	197.1	200.5	208.2	216.1	229.7	246.6	274.6	320.6
65°	158.7	160.2	161.5	162.9	164.8	169.4	176.9	186.3	198.0	217.6	250.7
67.5°	124.8	126.2	126.6	129.5	133.5	136.4	141.0	149.3	157.4	174.0	192.8
70°	100.9	100.4	100.9	102.3	107.4	112.5	118.6	124.7	129.7	141.4	157.3
72.5°	86.7	85.8	87.0	87.3	89.8	91.2	95.1	100.8	107.4	115.3	126.7
75°	67.2	67.2	67.2	67.2	69.1	70.0	71.4	72.9	75.2	78.9	87.3
77.5°	49.7	49.8	50.4	50.9	51.3	51.8	52.7	54.0	54.9	56.9	60.5
80°	39.2	39.7	39.2	39.7	39.7	40.6	41.1	42.4	43.0	45.3	46.7
82.5°	29.5	29.2	29.5	30.0	30.0	30.9	31.0	32.0	32.1	33.3	34.8
85°	15.9	15.0	15.9	15.4	16.3	15.4	15.9	16.8	16.8	17.3	19.2
87.5°	11.8	12.4	11.5	11.8	11.6	11.9	11.6	11.3	11.9	11.2	10.9
90°	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3	33.2	32.0	28.2
92.5°	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9	36.0	34.2	31.2
95°	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5	43.4	41.3	38.1
97.5°	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7	45.3	42.9	64.3
100°	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7	46.4	44.0	90.2
102.5°	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0	80.3	87.7	138.2
105°	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1	239.5	291.9	318.6
107.5°	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2	496.7	535.1	530.9
110°	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7	591.5	601.2	598.0



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8	668.6	668.4	665.1
115°	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2	768.1	765.2	762.5
117.5°	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8	861.4	859.1	857.6
120°	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6	922.2	919.8	918.9
122.5°	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9	982.3	980.6	979.5
125°	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6	1067.1	1066.5	1065.3
127.5°	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6	1150.6	1149.7	1148.3
130°	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1	1201.0	1199.8	1198.6
132.5°	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2	1248.9	1247.8	1246.8
135°	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1	1319.9
137.5°	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7	1386.3	1384.8	1384.2
140°	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8	1427.6	1426.4	1425.5
142.5°	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8	1466.8	1465.9	1465.0
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2	1521.6	1521.1	1520.5
147.5°	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0	1570.5	1569.9	1569.2
150°	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9	1600.3	1599.7	1599.1
152.5°	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5	1626.4	1625.3	1625.0
155°	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0	1662.5	1661.0	1660.7
157.5°	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8	1694.0	1692.2	1692.6
160°	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0	1712.2	1710.4	1710.7
162.5°	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4	1728.4	1726.4	1726.6
165°	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4	1750.1	1747.7	1748.0
167.5°	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8	1764.8
170°	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3	1774.3
172.5°	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5	1783.2	1780.7	1780.5
175°	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1	1791.1	1789.0	1788.7
177.5°	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0	1794.1	1792.2	1792.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1126.1	1124.9	1119.7	1113.7	1105.9	1100.6	1096.5	1094.3	1087.6	1079.3	1073.8
5°	1195.6	1181.6	1166.7	1148.4	1131.7	1114.4	1103.7	1091.0	1075.7	1058.4	1046.2
7.5°	1270.2	1242.7	1213.1	1182.6	1152.4	1125.3	1101.4	1080.9	1056.4	1031.6	1014.3
10°	1327.3	1287.1	1245.5	1203.1	1164.3	1127.9	1099.9	1072.4	1042.9	1014.5	993.0
12.5°	1379.2	1326.3	1278.4	1226.3	1176.7	1133.2	1092.8	1060.4	1025.0	994.7	970.2
15°	1444.9	1390.8	1332.8	1253.5	1187.7	1132.6	1083.6	1041.1	998.2	960.8	937.0
17.5°	1506.4	1424.9	1347.1	1280.9	1195.3	1126.5	1066.7	1015.8	968.8	929.2	899.8
20°	1531.8	1452.9	1368.3	1283.9	1199.8	1122.8	1053.2	997.2	948.2	903.4	876.3
22.5°	1547.0	1457.7	1368.7	1277.9	1188.7	1108.6	1039.8	978.1	925.1	882.4	849.0
25°	1564.9	1458.5	1360.4	1270.8	1179.7	1092.9	1011.2	945.8	888.4	843.1	807.6
27.5°	1576.6	1451.4	1335.6	1235.9	1143.6	1057.1	982.2	913.0	854.7	806.8	768.7
30°	1578.9	1445.8	1316.5	1208.7	1114.8	1035.5	956.1	889.8	828.2	777.3	741.8
32.5°	1581.9	1432.0	1290.8	1176.2	1080.1	1001.5	929.6	866.3	803.2	753.0	716.8
35°	1569.6	1424.4	1251.6	1120.0	1023.8	947.7	882.8	824.5	762.4	713.8	676.9
37.5°	1516.5	1394.0	1211.1	1056.7	956.1	885.6	832.8	781.9	725.0	672.5	637.8
40°	1463.1	1364.1	1179.7	1018.2	913.2	840.8	793.2	751.6	696.5	647.6	610.2
42.5°	1383.6	1323.5	1149.9	977.9	864.6	794.9	754.7	715.8	667.4	617.7	582.6
45°	1237.6	1245.5	1088.7	913.6	797.4	727.4	689.6	662.5	619.6	578.5	542.5
47.5°	1054.6	1128.8	1016.9	845.2	726.5	660.8	627.8	604.1	575.2	534.8	502.0
50°	935.1	1041.1	959.4	799.2	682.1	616.7	584.1	564.9	539.7	507.9	476.6
52.5°	824.9	938.8	889.9	748.1	633.9	574.2	542.2	526.5	506.4	476.5	448.3
55°	672.7	788.1	776.9	670.8	561.6	507.9	483.7	465.9	452.4	430.0	407.6
57.5°	544.2	653.5	659.3	585.0	497.9	444.9	424.0	410.6	401.8	384.9	364.2
60°	463.2	563.5	583.1	527.1	452.4	405.7	385.1	374.4	367.4	353.9	338.0
62.5°	395.9	481.3	503.5	463.2	408.7	365.0	348.9	338.6	333.8	322.1	308.1
65°	303.0	374.0	395.4	373.0	344.6	309.5	296.5	287.6	283.4	276.9	266.5
67.5°	227.8	279.6	303.1	287.3	277.1	254.9	246.6	241.8	238.1	233.6	225.1
70°	183.0	221.3	245.6	241.4	233.0	221.3	215.3	212.0	208.2	204.5	197.0
72.5°	147.1	173.5	196.3	198.4	191.5	189.1	183.9	182.4	180.2	175.8	171.7
75°	97.6	115.7	131.6	137.7	140.5	142.9	140.5	140.1	139.6	135.9	133.5
77.5°	63.9	73.7	83.7	94.1	98.5	101.7	102.5	104.2	102.9	100.9	99.8
80°	49.0	51.4	58.3	67.2	74.2	77.0	78.9	79.8	79.4	78.9	77.0
82.5°	35.6	37.5	40.8	47.1	53.0	57.6	58.8	58.6	59.6	59.8	58.3
85°	19.2	19.6	20.5	21.5	24.7	29.9	31.3	32.2	33.2	33.2	30.3
87.5°	10.8	9.7	9.6	9.0	9.5	9.3	11.0	12.2	13.2	12.3	12.8
90°	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3	4.3	7.2	10.3
92.5°	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8	24.0	23.1	22.3
95°	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3	69.2	57.1	44.9
97.5°	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5	158.0	152.6	147.0
100°	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3	231.2	237.1	243.1
102.5°	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7	300.0	304.3	308.4
105°	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3	400.6	403.8	407.1
107.5°	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4	507.0	509.6	512.3
110°	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9	578.3	580.6	583.0



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2	646.3	648.5	650.6
115°	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2	747.0	748.8	750.6
117.5°	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0	845.3	847.4	849.6
120°	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8	906.5	909.2	911.9
122.5°	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7	967.9	970.1	972.2
125°	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4	1052.8	1055.3	1057.6
127.5°	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6	1135.0	1137.4	1139.7
130°	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7	1186.2	1188.6	1190.9
132.5°	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9	1235.2	1237.6	1239.9
135°	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8	1309.6	1311.3	1313.1
137.5°	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7	1374.0	1376.3	1378.5
140°	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4	1416.2	1418.0	1419.8
142.5°	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8	1455.6	1457.4	1459.2
145°	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0	1511.1	1513.2	1515.3
147.5°	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0	1562.5	1563.8	1565.1
150°	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0	1593.9	1594.8	1595.7
152.5°	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8	1622.3	1622.6	1623.1
155°	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3	1661.8	1661.2	1660.6
157.5°	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8	1693.8	1693.7	1693.6
160°	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1	1712.7	1712.4	1712.2
162.5°	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2	1730.4	1729.7	1728.8
165°	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0	1752.1	1751.2	1750.3
167.5°	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0	1768.9	1767.7	1766.6
170°	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7	1778.5	1777.3	1776.1
172.5°	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1	1784.7	1783.2	1781.8
175°	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3	1792.9	1791.4	1789.9
177.5°	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4	1795.3	1794.1	1793.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1071.9	1067.0	1063.7	1056.2	1051.3	1046.2	1040.9	1044.3	1043.9	1043.5	1043.5
5°	1036.0	1025.2	1015.4	1002.8	994.9	985.1	977.6	976.7	978.6	972.0	968.2
7.5°	1000.3	985.6	971.7	957.8	943.1	931.3	923.9	920.4	915.7	911.7	907.5
10°	975.3	958.0	944.4	927.2	911.3	897.3	888.4	882.3	879.0	875.8	869.8
12.5°	949.5	932.6	915.3	895.8	880.7	864.4	857.8	851.0	844.7	841.1	832.8
15°	911.8	889.8	871.6	851.0	834.3	818.4	809.0	795.5	793.6	789.0	780.6
17.5°	874.0	850.2	825.0	809.9	790.9	774.4	760.1	755.5	742.2	737.2	729.9
20°	844.1	822.2	803.0	782.9	755.4	739.9	728.8	722.7	711.9	705.4	700.7
22.5°	818.3	796.0	773.8	750.5	727.7	710.4	702.2	692.8	687.0	677.8	672.7
25°	781.5	757.2	730.7	705.4	689.1	676.0	662.9	654.5	646.1	641.9	632.6
27.5°	738.8	713.4	688.5	669.4	649.3	636.4	624.6	617.1	607.0	599.9	594.8
30°	715.2	685.4	663.9	646.6	620.9	608.8	599.9	590.6	583.1	575.6	570.5
32.5°	688.0	660.7	640.3	618.9	599.2	586.0	574.5	566.3	559.9	552.9	547.7
35°	645.2	622.3	601.3	579.8	565.3	551.8	538.3	531.3	525.2	518.7	514.0
37.5°	606.5	585.1	565.2	544.8	526.9	515.9	505.0	499.6	491.4	487.1	482.2
40°	582.6	561.6	540.1	520.6	501.9	493.5	483.7	475.7	468.2	465.0	459.9
42.5°	556.5	535.5	517.4	496.2	481.0	469.6	460.5	451.8	446.2	441.5	438.5
45°	517.7	499.1	481.3	460.3	445.9	436.0	425.8	417.9	412.7	409.5	404.3
47.5°	480.1	461.5	443.4	425.1	411.1	399.9	389.7	384.1	377.3	373.3	369.9
50°	452.8	436.0	416.9	400.1	386.1	374.9	366.5	359.4	353.4	348.3	346.0
52.5°	427.8	409.9	393.3	377.7	362.9	350.3	342.6	335.2	330.6	324.8	322.0
55°	386.6	369.3	355.3	339.8	325.4	314.7	305.3	298.8	294.1	287.6	283.8
57.5°	347.8	332.3	315.6	302.2	287.3	278.2	270.5	261.6	255.9	250.8	247.2
60°	321.6	303.9	289.4	276.9	263.8	252.1	245.1	238.1	232.0	226.9	223.6
62.5°	294.4	278.9	265.2	251.5	239.5	229.3	221.2	215.3	210.0	206.7	203.5
65°	252.5	240.4	226.4	215.3	204.0	196.5	190.0	184.9	181.1	178.8	176.0
67.5°	214.1	202.3	190.1	179.1	171.7	165.9	161.7	157.2	155.3	152.4	150.5
70°	189.0	176.9	166.2	157.8	150.3	146.2	143.3	140.1	138.2	134.5	132.6
72.5°	161.8	153.0	145.3	138.4	132.4	128.6	125.0	121.0	118.1	113.9	112.1
75°	127.4	119.5	113.4	108.8	105.0	99.9	94.8	90.6	89.2	87.7	87.3
77.5°	94.4	89.3	85.0	81.1	76.4	72.7	71.5	70.6	70.3	69.6	69.6
80°	74.2	69.6	66.3	61.6	58.9	58.9	58.9	57.9	58.3	58.3	58.3
82.5°	55.2	50.9	49.1	47.4	46.9	47.3	47.3	47.4	47.2	47.9	47.5
85°	28.4	29.0	29.9	29.4	29.9	29.9	30.9	30.3	30.9	29.9	30.9
87.5°	13.1	14.9	16.1	17.2	18.4	18.7	19.4	19.5	20.2	20.4	20.6
90°	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3	35.6	36.7	37.6
92.5°	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9	39.9	41.7	42.8
95°	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5	47.5	49.6	50.6
97.5°	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7	50.0	52.4	53.8
100°	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7	51.1	53.5	54.8
102.5°	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0	65.7	58.3	54.9
105°	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1	134.6	82.2	56.3
107.5°	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2	419.7	381.3	342.3
110°	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7	571.9	562.1	536.0



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8	669.0	669.1	664.8
115°	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2	774.1	777.0	779.1
117.5°	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8	866.1	868.5	869.9
120°	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6	926.9	929.3	930.5
122.5°	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9	985.6	987.3	988.2
125°	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6	1068.3	1068.8	1069.4
127.5°	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6	1152.5	1153.4	1153.6
130°	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1	1203.4	1204.5	1204.8
132.5°	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2	1251.3	1252.5	1252.7
135°	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6
137.5°	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7	1389.1	1390.5	1390.9
140°	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8	1429.9	1431.1	1431.5
142.5°	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8	1468.7	1469.6	1469.7
145°	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2	1522.9	1523.4	1523.8
147.5°	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0	1571.6	1572.3	1571.8
150°	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9	1601.5	1602.0	1602.0
152.5°	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5	1628.5	1629.6	1629.4
155°	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0	1665.4	1667.0	1666.8
157.5°	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8	1697.5	1699.3	1699.1
160°	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0	1715.7	1717.4	1717.3
162.5°	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4	1732.4	1734.4	1734.5
165°	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4	1754.8	1757.2	1757.3
167.5°	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2
170°	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9
172.5°	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5	1787.9	1790.2	1790.1
175°	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1	1795.2	1797.3	1797.2
177.5°	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0	1797.9	1799.8	1799.6
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1039.0	1038.7	1039.0	1037.5	1039.0	1038.7	1039.0	1043.5	1043.5	1043.9	1044.3
5°	966.9	966.3	965.0	960.8	965.0	966.3	966.9	968.2	972.0	978.6	976.7
7.5°	903.8	903.2	899.1	899.2	899.1	903.2	903.8	907.5	911.7	915.7	920.4
10°	866.5	866.9	861.4	858.1	861.4	866.9	866.5	869.8	875.8	879.0	882.3
12.5°	830.3	828.1	823.6	820.0	823.6	828.1	830.3	832.8	841.1	844.7	851.0
15°	782.5	777.8	766.6	767.5	766.6	777.8	782.5	780.6	789.0	793.6	795.5
17.5°	726.1	722.7	722.5	716.0	722.5	722.7	726.1	729.9	737.2	742.2	755.5
20°	693.3	691.0	691.9	685.4	691.9	691.0	693.3	700.7	705.4	711.9	722.7
22.5°	667.5	665.2	661.3	659.2	661.3	665.2	667.5	672.7	677.8	687.0	692.8
25°	629.8	626.1	622.3	624.6	622.3	626.1	629.8	632.6	641.9	646.1	654.5
27.5°	592.1	589.2	585.5	585.1	585.5	589.2	592.1	594.8	599.9	607.0	617.1
30°	568.2	565.3	563.5	561.2	563.5	565.3	568.2	570.5	575.6	583.1	590.6
32.5°	543.9	543.3	539.9	539.5	539.9	543.3	543.9	547.7	552.9	559.9	566.3
35°	512.1	509.3	508.4	508.9	508.4	509.3	512.1	514.0	518.7	525.2	531.3
37.5°	482.0	478.2	476.5	474.9	476.5	478.2	482.0	482.2	487.1	491.4	499.6
40°	460.3	456.6	455.7	454.7	455.7	456.6	460.3	459.9	465.0	468.2	475.7
42.5°	436.0	434.5	434.0	432.3	434.0	434.5	436.0	438.5	441.5	446.2	451.8
45°	402.9	402.4	399.7	400.6	399.7	402.4	402.9	404.3	409.5	412.7	417.9
47.5°	368.0	366.0	364.0	365.2	364.0	366.0	368.0	369.9	373.3	377.3	384.1
50°	344.1	343.1	338.9	339.8	338.9	343.1	344.1	346.0	348.3	353.4	359.4
52.5°	320.2	316.6	315.0	314.5	315.0	316.6	320.2	322.0	324.8	330.6	335.2
55°	280.6	276.3	274.5	273.6	274.5	276.3	280.6	283.8	287.6	294.1	298.8
57.5°	241.7	240.6	239.2	240.1	239.2	240.6	241.7	247.2	250.8	255.9	261.6
60°	218.9	218.9	218.9	218.5	218.9	218.9	218.9	223.6	226.9	232.0	238.1
62.5°	201.4	200.3	199.9	200.5	199.9	200.3	201.4	203.5	206.7	210.0	215.3
65°	174.6	174.2	172.3	171.8	172.3	174.2	174.6	176.0	178.8	181.1	184.9
67.5°	149.3	147.6	147.0	146.4	147.0	147.6	149.3	150.5	152.4	155.3	157.2
70°	130.3	129.3	126.5	127.0	126.5	129.3	130.3	132.6	134.5	138.2	140.1
72.5°	109.7	108.8	108.3	107.5	108.3	108.8	109.7	112.1	113.9	118.1	121.0
75°	86.9	86.4	85.9	87.7	85.9	86.4	86.9	87.3	87.7	89.2	90.6
77.5°	69.6	69.6	69.8	69.1	69.8	69.6	69.6	69.6	69.6	70.3	70.6
80°	58.3	58.3	57.9	57.9	57.9	58.3	58.3	58.3	58.3	58.3	57.9
82.5°	46.8	47.2	47.4	46.7	47.4	47.2	46.8	47.5	47.9	47.2	47.4
85°	30.9	30.3	31.3	30.9	31.3	30.3	30.9	30.9	29.9	30.9	30.3
87.5°	21.5	20.9	21.0	21.4	21.0	20.9	21.5	20.6	20.4	20.2	19.5
90°	38.3	38.8	39.4	39.9	39.4	38.8	38.3	37.6	36.7	35.6	34.3
92.5°	43.2	43.5	43.9	44.2	43.9	43.5	43.2	42.8	41.7	39.9	37.9
95°	50.6	50.6	50.6	50.6	50.6	50.6	50.6	50.6	49.6	47.5	45.5
97.5°	54.0	54.3	54.7	54.9	54.7	54.3	54.0	53.8	52.4	50.0	47.7
100°	55.1	55.4	55.7	56.0	55.7	55.4	55.1	54.8	53.5	51.1	48.7
102.5°	55.5	56.0	56.5	57.1	56.5	56.0	55.5	54.9	58.3	65.7	73.0
105°	56.9	57.5	58.1	58.7	58.1	57.5	56.9	56.3	82.2	134.6	187.1
107.5°	302.8	263.2	223.7	184.2	223.7	263.2	302.8	342.3	381.3	419.7	458.2
110°	493.7	451.3	408.9	366.6	408.9	451.3	493.7	536.0	562.1	571.9	581.7



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	655.8	646.8	637.9	628.9	637.9	646.8	655.8	664.8	669.1	669.0	668.8
115°	780.3	781.5	782.7	783.9	782.7	781.5	780.3	779.1	777.0	774.1	771.2
117.5°	870.0	870.3	870.6	870.8	870.6	870.3	870.0	869.9	868.5	866.1	863.8
120°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	929.3	926.9	924.6
122.5°	988.5	988.6	988.9	989.2	988.9	988.6	988.5	988.2	987.3	985.6	983.9
125°	1070.1	1070.6	1071.2	1071.8	1071.2	1070.6	1070.1	1069.4	1068.8	1068.3	1067.6
127.5°	1153.1	1152.4	1151.8	1151.3	1151.8	1152.4	1153.1	1153.6	1153.4	1152.5	1151.6
130°	1204.3	1203.6	1203.0	1202.5	1203.0	1203.6	1204.3	1204.8	1204.5	1203.4	1202.1
132.5°	1251.9	1251.1	1250.2	1249.4	1250.2	1251.1	1251.9	1252.7	1252.5	1251.3	1250.2
135°	1323.7	1322.9	1322.0	1321.1	1322.0	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9
137.5°	1390.4	1389.7	1389.1	1388.6	1389.1	1389.7	1390.4	1390.9	1390.5	1389.1	1387.7
140°	1430.8	1430.3	1429.7	1429.1	1429.7	1430.3	1430.8	1431.5	1431.1	1429.9	1428.8
142.5°	1468.9	1468.0	1467.2	1466.4	1467.2	1468.0	1468.9	1469.7	1469.6	1468.7	1467.8
145°	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.8	1523.4	1522.9	1522.2
147.5°	1570.5	1569.1	1567.7	1566.4	1567.7	1569.1	1570.5	1571.8	1572.3	1571.6	1571.0
150°	1601.1	1600.2	1599.3	1598.4	1599.3	1600.2	1601.1	1602.0	1602.0	1601.5	1600.9
152.5°	1628.1	1626.7	1625.3	1624.0	1625.3	1626.7	1628.1	1629.4	1629.6	1628.5	1627.5
155°	1665.0	1663.2	1661.4	1659.7	1661.4	1663.2	1665.0	1666.8	1667.0	1665.4	1664.0
157.5°	1696.7	1694.4	1692.1	1689.8	1692.1	1694.4	1696.7	1699.1	1699.3	1697.5	1695.8
160°	1715.2	1713.2	1711.1	1709.1	1711.1	1713.2	1715.2	1717.3	1717.4	1715.7	1714.0
162.5°	1732.7	1730.8	1729.0	1727.2	1729.0	1730.8	1732.7	1734.5	1734.4	1732.4	1730.4
165°	1755.2	1753.2	1751.1	1749.0	1751.1	1753.2	1755.2	1757.3	1757.2	1754.8	1752.4
167.5°	1771.8	1769.5	1767.1	1764.8	1767.1	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5
170°	1781.5	1779.1	1776.7	1774.3	1776.7	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1
172.5°	1787.5	1784.9	1782.3	1779.7	1782.3	1784.9	1787.5	1790.1	1790.2	1787.9	1785.5
175°	1794.7	1792.4	1790.0	1787.7	1790.0	1792.4	1794.7	1797.2	1797.3	1795.2	1793.1
177.5°	1797.2	1794.8	1792.4	1790.1	1792.4	1794.8	1797.2	1799.6	1799.8	1797.9	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1040.9	1046.2	1051.3	1056.2	1063.7	1067.0	1071.9	1073.8	1079.3	1087.6	1094.3
5°	977.6	985.1	994.9	1002.8	1015.4	1025.2	1036.0	1046.2	1058.4	1075.7	1091.0
7.5°	923.9	931.3	943.1	957.8	971.7	985.6	1000.3	1014.3	1031.6	1056.4	1080.9
10°	888.4	897.3	911.3	927.2	944.4	958.0	975.3	993.0	1014.5	1042.9	1072.4
12.5°	857.8	864.4	880.7	895.8	915.3	932.6	949.5	970.2	994.7	1025.0	1060.4
15°	809.0	818.4	834.3	851.0	871.6	889.8	911.8	937.0	960.8	998.2	1041.1
17.5°	760.1	774.4	790.9	809.9	825.0	850.2	874.0	899.8	929.2	968.8	1015.8
20°	728.8	739.9	755.4	782.9	803.0	822.2	844.1	876.3	903.4	948.2	997.2
22.5°	702.2	710.4	727.7	750.5	773.8	796.0	818.3	849.0	882.4	925.1	978.1
25°	662.9	676.0	689.1	705.4	730.7	757.2	781.5	807.6	843.1	888.4	945.8
27.5°	624.6	636.4	649.3	669.4	688.5	713.4	738.8	768.7	806.8	854.7	913.0
30°	599.9	608.8	620.9	646.6	663.9	685.4	715.2	741.8	777.3	828.2	889.8
32.5°	574.5	586.0	599.2	618.9	640.3	660.7	688.0	716.8	753.0	803.2	866.3
35°	538.3	551.8	565.3	579.8	601.3	622.3	645.2	676.9	713.8	762.4	824.5
37.5°	505.0	515.9	526.9	544.8	565.2	585.1	606.5	637.8	672.5	725.0	781.9
40°	483.7	493.5	501.9	520.6	540.1	561.6	582.6	610.2	647.6	696.5	751.6
42.5°	460.5	469.6	481.0	496.2	517.4	535.5	556.5	582.6	617.7	667.4	715.8
45°	425.8	436.0	445.9	460.3	481.3	499.1	517.7	542.5	578.5	619.6	662.5
47.5°	389.7	399.9	411.1	425.1	443.4	461.5	480.1	502.0	534.8	575.2	604.1
50°	366.5	374.9	386.1	400.1	416.9	436.0	452.8	476.6	507.9	539.7	564.9
52.5°	342.6	350.3	362.9	377.7	393.3	409.9	427.8	448.3	476.5	506.4	526.5
55°	305.3	314.7	325.4	339.8	355.3	369.3	386.6	407.6	430.0	452.4	465.9
57.5°	270.5	278.2	287.3	302.2	315.6	332.3	347.8	364.2	384.9	401.8	410.6
60°	245.1	252.1	263.8	276.9	289.4	303.9	321.6	338.0	353.9	367.4	374.4
62.5°	221.2	229.3	239.5	251.5	265.2	278.9	294.4	308.1	322.1	333.8	338.6
65°	190.0	196.5	204.0	215.3	226.4	240.4	252.5	266.5	276.9	283.4	287.6
67.5°	161.7	165.9	171.7	179.1	190.1	202.3	214.1	225.1	233.6	238.1	241.8
70°	143.3	146.2	150.3	157.8	166.2	176.9	189.0	197.0	204.5	208.2	212.0
72.5°	125.0	128.6	132.4	138.4	145.3	153.0	161.8	171.7	175.8	180.2	182.4
75°	94.8	99.9	105.0	108.8	113.4	119.5	127.4	133.5	135.9	139.6	140.1
77.5°	71.5	72.7	76.4	81.1	85.0	89.3	94.4	99.8	100.9	102.9	104.2
80°	58.9	58.9	58.9	61.6	66.3	69.6	74.2	77.0	78.9	79.4	79.8
82.5°	47.3	47.3	46.9	47.4	49.1	50.9	55.2	58.3	59.8	59.6	58.6
85°	30.9	29.9	29.9	29.4	29.9	29.0	28.4	30.3	33.2	33.2	32.2
87.5°	19.4	18.7	18.4	17.2	16.1	14.9	13.1	12.8	12.3	13.2	12.2
90°	33.2	32.0	28.2	24.3	20.4	16.6	13.2	10.3	7.2	4.3	1.3
92.5°	36.0	34.2	31.2	28.4	25.4	22.5	21.5	22.3	23.1	24.0	24.8
95°	43.4	41.3	38.1	34.8	31.6	28.3	32.7	44.9	57.1	69.2	81.3
97.5°	45.3	42.9	64.3	85.6	106.9	128.2	141.6	147.0	152.6	158.0	163.5
100°	46.4	44.0	90.2	136.4	182.6	228.8	249.0	243.1	237.1	231.2	225.3
102.5°	80.3	87.7	138.2	188.7	239.2	289.6	312.7	308.4	304.3	300.0	295.7
105°	239.5	291.9	318.6	345.3	371.9	398.6	410.3	407.1	403.8	400.6	397.3
107.5°	496.7	535.1	530.9	526.7	522.5	518.3	514.9	512.3	509.6	507.0	504.4
110°	591.5	601.2	598.0	594.7	591.5	588.2	585.4	583.0	580.6	578.3	575.9



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	668.6	668.4	665.1	661.9	658.6	655.4	652.6	650.6	648.5	646.3	644.2
115°	768.1	765.2	762.5	759.8	757.2	754.6	752.3	750.6	748.8	747.0	745.2
117.5°	861.4	859.1	857.6	856.3	855.0	853.6	851.9	849.6	847.4	845.3	843.0
120°	922.2	919.8	918.9	918.0	917.1	916.3	914.5	911.9	909.2	906.5	903.8
122.5°	982.3	980.6	979.5	978.4	977.2	976.2	974.5	972.2	970.1	967.9	965.7
125°	1067.1	1066.5	1065.3	1064.1	1062.9	1061.8	1060.0	1057.6	1055.3	1052.8	1050.4
127.5°	1150.6	1149.7	1148.3	1146.8	1145.4	1144.0	1142.1	1139.7	1137.4	1135.0	1132.6
130°	1201.0	1199.8	1198.6	1197.4	1196.2	1195.1	1193.3	1190.9	1188.6	1186.2	1183.7
132.5°	1248.9	1247.8	1246.8	1245.9	1244.9	1244.0	1242.3	1239.9	1237.6	1235.2	1232.9
135°	1322.0	1321.1	1319.9	1318.8	1317.5	1316.3	1314.9	1313.1	1311.3	1309.6	1307.8
137.5°	1386.3	1384.8	1384.2	1383.5	1382.9	1382.2	1380.7	1378.5	1376.3	1374.0	1371.7
140°	1427.6	1426.4	1425.5	1424.6	1423.7	1422.8	1421.6	1419.8	1418.0	1416.2	1414.4
142.5°	1466.8	1465.9	1465.0	1464.1	1463.2	1462.3	1461.0	1459.2	1457.4	1455.6	1453.8
145°	1521.6	1521.1	1520.5	1519.8	1519.3	1518.7	1517.3	1515.3	1513.2	1511.1	1509.0
147.5°	1570.5	1569.9	1569.2	1568.7	1568.1	1567.4	1566.5	1565.1	1563.8	1562.5	1561.0
150°	1600.3	1599.7	1599.1	1598.6	1597.9	1597.3	1596.6	1595.7	1594.8	1593.9	1593.0
152.5°	1626.4	1625.3	1625.0	1624.6	1624.3	1623.9	1623.5	1623.1	1622.6	1622.3	1621.8
155°	1662.5	1661.0	1660.7	1660.5	1660.2	1659.8	1660.0	1660.6	1661.2	1661.8	1662.3
157.5°	1694.0	1692.2	1692.6	1692.8	1693.1	1693.4	1693.6	1693.6	1693.7	1693.8	1693.8
160°	1712.2	1710.4	1710.7	1710.9	1711.3	1711.5	1711.8	1712.2	1712.4	1712.7	1713.1
162.5°	1728.4	1726.4	1726.6	1727.0	1727.2	1727.5	1728.0	1728.8	1729.7	1730.4	1731.2
165°	1750.1	1747.7	1748.0	1748.3	1748.6	1748.9	1749.4	1750.3	1751.2	1752.1	1753.0
167.5°	1767.1	1764.8	1764.8	1764.8	1764.8	1764.8	1765.3	1766.6	1767.7	1768.9	1770.0
170°	1776.7	1774.3	1774.3	1774.3	1774.3	1774.3	1775.0	1776.1	1777.3	1778.5	1779.7
172.5°	1783.2	1780.7	1780.5	1780.3	1780.0	1779.8	1780.4	1781.8	1783.2	1784.7	1786.1
175°	1791.1	1789.0	1788.7	1788.4	1788.1	1787.8	1788.4	1789.9	1791.4	1792.9	1794.3
177.5°	1794.1	1792.2	1792.0	1791.7	1791.5	1791.3	1791.7	1793.0	1794.1	1795.3	1796.4
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1096.5	1100.6	1105.9	1113.7	1119.7	1124.9	1126.1	1127.6	1131.3	1137.6	1142.5
5°	1103.7	1114.4	1131.7	1148.4	1166.7	1181.6	1195.6	1205.4	1214.8	1234.4	1250.3
7.5°	1101.4	1125.3	1152.4	1182.6	1213.1	1242.7	1270.2	1294.7	1319.1	1347.7	1380.3
10°	1099.9	1127.9	1164.3	1203.1	1245.5	1287.1	1327.3	1358.5	1395.0	1427.6	1469.2
12.5°	1092.8	1133.2	1176.7	1226.3	1278.4	1326.3	1379.2	1422.5	1464.1	1511.3	1559.6
15°	1083.6	1132.6	1187.7	1253.5	1332.8	1390.8	1444.9	1520.1	1571.5	1622.8	1691.8
17.5°	1066.7	1126.5	1195.3	1280.9	1347.1	1424.9	1506.4	1565.8	1635.0	1707.3	1769.9
20°	1053.2	1122.8	1199.8	1283.9	1368.3	1452.9	1531.8	1602.7	1674.2	1757.7	1809.1
22.5°	1039.8	1108.6	1188.7	1277.9	1368.7	1457.7	1547.0	1630.3	1710.7	1795.1	1860.6
25°	1011.2	1092.9	1179.7	1270.8	1360.4	1458.5	1564.9	1657.8	1757.2	1844.1	1906.2
27.5°	982.2	1057.1	1143.6	1235.9	1335.6	1451.4	1576.6	1682.3	1781.9	1844.1	1863.6
30°	956.1	1035.5	1114.8	1208.7	1316.5	1445.8	1578.9	1699.8	1781.5	1808.6	1788.5
32.5°	929.6	1001.5	1080.1	1176.2	1290.8	1432.0	1581.9	1689.3	1738.6	1717.9	1636.1
35°	882.8	947.7	1023.8	1120.0	1251.6	1424.4	1569.6	1642.4	1630.2	1513.5	1359.5
37.5°	832.8	885.6	956.1	1056.7	1211.1	1394.0	1516.5	1527.2	1422.2	1243.0	1065.1
40°	793.2	840.8	913.2	1018.2	1179.7	1364.1	1463.1	1419.7	1256.8	1057.4	909.0
42.5°	754.7	794.9	864.6	977.9	1149.9	1323.5	1383.6	1289.0	1101.0	912.5	777.5
45°	689.6	727.4	797.4	913.6	1088.7	1245.5	1237.6	1073.3	885.2	733.4	621.3
47.5°	627.8	660.8	726.5	845.2	1016.9	1128.8	1054.6	879.8	720.1	598.4	518.5
50°	584.1	616.7	682.1	799.2	959.4	1041.1	935.1	766.6	620.5	519.6	456.1
52.5°	542.2	574.2	633.9	748.1	889.9	938.8	824.9	668.7	546.9	459.9	405.3
55°	483.7	507.9	561.6	670.8	776.9	788.1	672.7	542.0	441.7	380.9	343.6
57.5°	424.0	444.9	497.9	585.0	659.3	653.5	544.2	431.1	363.5	318.4	291.3
60°	385.1	405.7	452.4	527.1	583.1	563.5	463.2	372.1	314.1	281.1	259.6
62.5°	348.9	365.0	408.7	463.2	503.5	481.3	395.9	320.6	274.6	246.6	229.7
65°	296.5	309.5	344.6	373.0	395.4	374.0	303.0	250.7	217.6	198.0	186.3
67.5°	246.6	254.9	277.1	287.3	303.1	279.6	227.8	192.8	174.0	157.4	149.3
70°	215.3	221.3	233.0	241.4	245.6	221.3	183.0	157.3	141.4	129.7	124.7
72.5°	183.9	189.1	191.5	198.4	196.3	173.5	147.1	126.7	115.3	107.4	100.8
75°	140.5	142.9	140.5	137.7	131.6	115.7	97.6	87.3	78.9	75.2	72.9
77.5°	102.5	101.7	98.5	94.1	83.7	73.7	63.9	60.5	56.9	54.9	54.0
80°	78.9	77.0	74.2	67.2	58.3	51.4	49.0	46.7	45.3	43.0	42.4
82.5°	58.8	57.6	53.0	47.1	40.8	37.5	35.6	34.8	33.3	32.1	32.0
85°	31.3	29.9	24.7	21.5	20.5	19.6	19.2	19.2	17.3	16.8	16.8
87.5°	11.0	9.3	9.5	9.0	9.6	9.7	10.8	10.9	11.2	11.9	11.3
90°	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2	34.3
92.5°	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0	37.9
95°	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4	45.5
97.5°	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3	47.7
100°	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4	48.7
102.5°	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3	73.0
105°	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5	187.1
107.5°	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7	458.2
110°	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5	581.7



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6	668.8
115°	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1	771.2
117.5°	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4	863.8
120°	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2	924.6
122.5°	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3	983.9
125°	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1	1067.6
127.5°	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6	1151.6
130°	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0	1202.1
132.5°	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9	1250.2
135°	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0	1322.9
137.5°	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3	1387.7
140°	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6	1428.8
142.5°	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8	1467.8
145°	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6	1522.2
147.5°	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5	1571.0
150°	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3	1600.9
152.5°	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4	1627.5
155°	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5	1664.0
157.5°	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0	1695.8
160°	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2	1714.0
162.5°	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4	1730.4
165°	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1	1752.4
167.5°	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1	1769.5
170°	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7	1779.1
172.5°	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2	1785.5
175°	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1	1793.1
177.5°	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1	1796.0
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1150.3	1150.3	1151.8	1157.4	1158.2	1163.1	1161.5
5°	1264.3	1273.1	1276.4	1290.4	1298.8	1302.5	1295.0
7.5°	1403.6	1428.6	1440.5	1455.1	1468.1	1472.0	1461.8
10°	1505.1	1531.2	1553.3	1566.7	1579.4	1587.8	1598.5
12.5°	1603.4	1635.5	1656.4	1675.4	1688.5	1699.1	1700.8
15°	1710.1	1758.6	1795.5	1822.6	1836.1	1843.2	1840.3
17.5°	1817.8	1862.8	1889.0	1916.6	1935.4	1936.4	1936.9
20°	1878.7	1922.5	1952.8	1973.4	1994.4	1993.5	1998.1
22.5°	1919.3	1953.9	1977.1	1992.1	1999.3	1995.7	1996.6
25°	1938.4	1948.7	1944.5	1920.7	1914.6	1892.7	1896.4
27.5°	1840.1	1791.6	1741.3	1676.8	1625.8	1585.1	1587.2
30°	1706.8	1621.0	1522.9	1440.7	1367.0	1346.4	1302.5
32.5°	1520.5	1391.6	1276.8	1200.2	1136.8	1119.7	1081.5
35°	1204.5	1079.3	961.3	890.3	862.3	823.0	822.6
37.5°	936.2	826.1	763.6	710.3	682.4	658.7	656.4
40°	787.6	701.7	654.5	616.3	588.7	571.0	566.8
42.5°	683.8	614.3	570.2	546.4	525.2	516.0	509.3
45°	558.4	511.7	480.9	459.4	449.6	442.6	438.8
47.5°	467.1	435.8	414.7	400.5	392.5	385.1	387.1
50°	417.4	391.7	376.3	362.7	356.7	351.5	352.0
52.5°	377.4	354.4	341.9	332.2	324.6	320.9	319.1
55°	320.3	305.8	293.2	286.1	282.0	276.9	275.4
57.5°	273.2	262.0	251.7	243.8	242.7	237.8	238.4
60°	241.8	232.5	224.1	219.9	216.6	212.4	213.8
62.5°	216.1	208.2	200.5	197.1	193.9	190.7	191.5
65°	176.9	169.4	164.8	162.9	161.5	160.2	158.7
67.5°	141.0	136.4	133.5	129.5	126.6	126.2	124.8
70°	118.6	112.5	107.4	102.3	100.9	100.4	100.9
72.5°	95.1	91.2	89.8	87.3	87.0	85.8	86.7
75°	71.4	70.0	69.1	67.2	67.2	67.2	67.2
77.5°	52.7	51.8	51.3	50.9	50.4	49.8	49.7
80°	41.1	40.6	39.7	39.7	39.2	39.7	39.2
82.5°	31.0	30.9	30.0	30.0	29.5	29.2	29.5
85°	15.9	15.4	16.3	15.4	15.9	15.0	15.9
87.5°	11.6	11.9	11.6	11.8	11.5	12.4	11.8
90°	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	571.9	562.1	536.0	493.7	451.3	408.9	366.6



TEST NUMBER: P332446-940

CATALOG NUMBER: S123RDIW-S775D1535U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)