

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332094-935

Luminaire Tested: **S123DIW-S340D460U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332094-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D460U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2803.3 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35	30				
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26				
4	73	62	54	48	66	57	50	45	48	43	39	39	35	32	31	28	26	22				
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17				
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.6
10°-20°	124.1	4.4
20°-30°	183.3	6.5
30°-40°	214.1	7.6
40°-50°	215.3	7.7
50°-60°	189.1	6.7
60°-70°	140.9	5.0
70°-80°	80.3	2.9
80°-90°	24.5	0.9
90°-100°	18.9	0.7
100°-110°	90.2	3.2
110°-120°	216.7	7.7
120°-130°	276.0	9.8
130°-140°	294.8	10.5
140°-150°	275.7	9.8
150°-160°	222.4	7.9
160°-170°	143.5	5.1
170°-180°	49.5	1.8
0°-30°	351.4	12.5
0°-40°	565.5	20.2
0°-60°	969.9	34.6
0°-90°	1215.5	43.4
90°-120°	325.9	11.6
90°-150°	1172.4	41.8
90°-180°	1588.0	56.6
0°-180°	2803.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	0	4	9	11	12	2
95°	24	9	12	15	15	29
105°	115	117	85	20	17	122
115°	216	219	222	226	228	213
125°	305	308	309	310	311	272
135°	379	382	383	384	383	292
145°	438	440	441	442	442	274
155°	482	482	482	484	482	222
165°	509	508	507	510	508	144
175°	521	519	519	522	519	50
180°	521	521	521	521	521	



TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.4	8.4	8.4	8.3	8.3	8.4	8.4	8.6	8.8	9.0	9.0
90°	0.3	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6
92.5°	7.2	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4
95°	23.6	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6
97.5°	47.4	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2
100°	65.3	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4
102.5°	85.8	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3
105°	115.3	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5
107.5°	146.4	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1
110°	167.1	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6



TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.9	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0
115°	216.2	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9
117.5°	244.6	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9
120°	262.3	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6
122.5°	280.3	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0
125°	304.8	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6
127.5°	328.6	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9
130°	343.5	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4
132.5°	357.7	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4
135°	379.4	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6
137.5°	398.0	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3
140°	410.4	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2
142.5°	421.9	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6
145°	437.9	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5
147.5°	453.0	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7
150°	462.3	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3
152.5°	470.6	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9
155°	482.3	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4
157.5°	491.5	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5
160°	497.1	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8
162.5°	502.3	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5
165°	508.7	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8
167.5°	513.7	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8
170°	516.4	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6
172.5°	518.2	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4
175°	520.6	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7
177.5°	521.2	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	9.0	8.9	8.9	9.0	9.0	9.0	9.0	9.0
90°	10.0	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.0	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.2	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	13.9	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.1	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	21.2	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	54.2	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	132.9	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	168.8	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332094-935

CATALOG NUMBER: S123DIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	194.1	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	223.8	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	250.6	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	268.3	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	285.5	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	309.8	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.2	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	348.8	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	362.7	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	402.7	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.6	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	425.9	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.7	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	455.9	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.5	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.3	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	482.8	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.1	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.3	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.1	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	508.5	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.1	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.3	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.2	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)