

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332096-935

Luminaire Tested: **S123DIW-S340D755U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332096-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3852.6 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	32	30	29	23
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	20
4	72	61	54	48	64	55	49	44	45	40	36	35	31	29	25	23	21	17
5	66	54	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	24	22	21	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	19	16	15	12
8	52	40	32	27	46	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4456	4456	4456	4456
5°	5314	4475	3965	4475
10°	6652	4453	3583	4453
15°	8158	4416	3335	4416
20°	9718	4361	3175	4361
25°	10320	4292	3139	4292
30°	8846	4243	3156	4243
35°	6151	4172	3189	4172
40°	4634	4089	3180	4089
45°	3847	3965	3139	3965
50°	3446	3716	3110	3716
55°	3222	3445	3072	3445
60°	3023	3160	3040	3160
65°	2840	2881	2942	2881
70°	2662	2565	2801	2565
75°	2383	2246	2570	2246
80°	2089	1841	2213	1841
85°	1643	1334	1494	1334



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	1.1
10°-20°	130.8	3.4
20°-30°	219.5	5.7
30°-40°	248.5	6.5
40°-50°	222.9	5.8
50°-60°	179.8	4.7
60°-70°	125.3	3.3
70°-80°	65.9	1.7
80°-90°	18.5	0.5
90°-100°	31.0	0.8
100°-110°	147.8	3.8
110°-120°	355.0	9.2
120°-130°	452.0	11.7
130°-140°	482.9	12.5
140°-150°	451.6	11.7
150°-160°	364.3	9.5
160°-170°	235.1	6.1
170°-180°	81.0	2.1
0°-30°	391.0	10.1
0°-40°	639.5	16.6
0°-60°	1042.2	27.1
0°-90°	1251.9	32.5
90°-120°	533.7	13.9
90°-150°	1920.2	49.8
90°-180°	2601.0	67.5
0°-180°	3852.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	414	414	414	414	414	
5°	492	414	367	414	492	51
15°	732	396	299	396	732	211
25°	869	361	264	361	869	381
35°	468	318	243	318	468	304
45°	253	260	206	260	253	200
55°	172	184	164	184	172	154
65°	112	113	116	113	112	111
75°	57	54	62	54	57	61
85°	13	11	12	11	13	16
90°	19	1	19	1	19	9
95°	24	39	24	39	24	20
105°	28	189	28	189	28	64
115°	373	354	373	354	373	344
125°	509	499	509	499	509	455
135°	628	622	628	622	628	484
145°	724	717	724	717	724	452
155°	789	790	789	790	789	364
165°	831	833	831	833	831	235
175°	850	853	850	853	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	439.4	439.0	438.2	438.9	437.6	435.8	435.7	434.0	429.4	429.1	427.8
5°	491.8	490.3	490.0	489.8	487.0	483.2	476.0	475.4	465.7	461.0	455.1
7.5°	559.8	560.6	557.7	555.2	546.6	540.9	533.1	523.2	511.4	499.4	491.5
10°	608.6	615.2	607.0	601.3	596.2	586.3	574.9	560.6	546.4	529.8	517.1
12.5°	660.9	664.1	662.5	657.2	649.1	634.1	613.9	598.1	585.0	557.3	546.1
15°	732.1	744.3	736.5	718.5	718.8	704.6	678.2	649.1	633.6	609.3	576.3
17.5°	808.0	809.5	806.2	791.2	781.2	761.6	737.1	709.3	678.0	648.6	613.5
20°	848.4	847.2	840.2	832.4	815.2	800.0	773.3	742.2	702.1	673.1	634.8
22.5°	870.9	868.9	865.6	859.0	844.7	828.4	804.3	770.4	732.2	692.4	648.2
25°	868.9	871.5	871.9	870.1	865.1	855.3	836.5	809.3	771.3	720.1	674.0
27.5°	790.3	794.0	804.7	814.2	824.8	835.7	834.2	820.8	792.6	748.4	692.0
30°	711.7	703.6	723.5	748.6	765.6	795.7	812.5	813.6	797.7	759.8	704.8
32.5°	602.5	611.4	620.2	651.0	688.3	722.0	755.6	782.6	785.7	760.4	712.4
35°	468.1	479.2	495.2	511.3	551.4	585.9	644.9	696.2	737.1	742.5	713.1
37.5°	377.3	382.7	392.9	409.0	435.1	476.1	521.7	586.6	645.9	690.0	691.9
40°	329.8	331.4	342.8	355.0	376.3	410.0	451.1	508.5	579.5	641.1	666.8
42.5°	294.1	297.6	302.6	314.3	331.2	356.5	394.8	442.2	507.3	578.2	628.4
45°	252.7	256.8	259.8	267.6	279.7	296.7	323.3	366.7	416.2	489.4	557.0
47.5°	225.4	225.7	227.9	233.8	242.0	254.9	273.7	301.5	347.0	406.4	475.8
50°	205.8	209.0	209.8	214.4	220.8	230.2	245.9	269.6	306.9	359.0	422.8
52.5°	192.0	193.0	195.2	198.5	204.1	211.5	225.1	243.6	272.9	317.4	376.0
55°	171.7	171.7	173.9	176.5	179.7	186.3	195.4	209.0	231.3	265.8	314.4
57.5°	152.9	153.9	155.5	156.3	159.0	163.4	170.9	181.3	197.9	224.5	263.0
60°	140.4	142.2	142.0	143.6	146.0	149.5	155.8	164.3	179.1	200.4	232.9
62.5°	129.5	129.4	129.3	131.3	133.6	136.9	141.1	148.4	161.0	179.9	207.5
65°	111.5	111.2	112.5	113.7	114.5	116.9	120.1	126.6	135.0	149.0	170.5
67.5°	95.6	94.4	95.1	95.6	96.9	98.8	101.9	105.8	112.4	123.7	139.9
70°	84.6	83.6	83.4	83.9	85.1	86.4	88.7	92.5	98.7	107.7	119.5
72.5°	73.4	72.8	72.7	73.6	74.1	75.1	76.6	80.1	85.1	91.9	102.9
75°	57.3	57.3	57.3	57.6	58.2	59.0	60.2	62.0	65.8	70.6	78.0
77.5°	43.0	43.0	42.7	42.7	43.6	43.9	44.2	45.9	48.0	51.2	56.7
80°	33.7	32.7	33.1	33.7	34.1	34.3	34.9	35.3	37.1	38.9	42.7
82.5°	25.1	24.2	24.3	25.2	25.3	25.5	26.1	26.6	27.3	28.9	31.0
85°	13.3	13.3	13.4	13.4	13.6	13.4	14.0	14.2	14.2	15.2	16.4
87.5°	8.6	8.3	8.4	8.4	8.3	8.3	8.4	8.4	8.4	8.5	8.3
90°	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4	15.8	15.2	13.3
92.5°	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0	17.1	16.2	14.8
95°	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6	20.7	19.6	18.1
97.5°	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6	21.5	20.4	30.6
100°	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2	22.0	20.9	42.9
102.5°	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7	38.2	41.7	65.7
105°	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9	113.8	138.8	151.4
107.5°	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7	236.0	254.3	252.4
110°	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5	281.1	285.8	284.2



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9	317.8	317.7	316.2
115°	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5	365.1	363.7	362.4
117.5°	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5	409.4	408.3	407.6
120°	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5	438.3	437.1	436.8
122.5°	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6	466.8	466.1	465.5
125°	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4	507.1	506.9	506.3
127.5°	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3	546.8	546.4	545.7
130°	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4	570.8	570.2	569.6
132.5°	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2	593.6	593.1	592.5
135°	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8	627.3
137.5°	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5	658.8	658.1	657.9
140°	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1	678.5	678.0	677.5
142.5°	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6	697.2	696.7	696.3
145°	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5	723.2	722.9	722.6
147.5°	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7	746.4	746.1	745.8
150°	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9	760.6	760.3	760.0
152.5°	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4	772.9	772.5	772.3
155°	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8	790.1	789.5	789.3
157.5°	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0	805.1	804.3	804.4
160°	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6	813.7	812.9	813.0
162.5°	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4	821.5	820.4	820.6
165°	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8	831.7	830.6	830.8
167.5°	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7	838.7
170°	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3	843.3
172.5°	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6	847.5	846.4	846.2
175°	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2	851.3	850.2	850.2
177.5°	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6	852.6	851.8	851.7
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	426.8	425.6	424.3	422.1	420.1	417.4	416.6	415.6	412.7	410.2	408.2
5°	452.9	448.1	441.1	434.6	429.5	422.4	418.4	414.2	408.2	402.8	398.4
7.5°	480.2	470.7	459.8	448.1	437.0	426.5	417.9	410.3	401.8	393.9	387.6
10°	501.9	488.2	472.9	456.5	442.5	428.9	417.4	407.4	396.6	387.1	379.3
12.5°	526.6	506.4	485.3	465.4	448.8	429.8	415.9	403.2	390.9	379.6	370.8
15°	555.8	530.1	505.2	477.8	452.5	428.9	412.4	396.3	382.1	370.5	359.2
17.5°	582.5	553.4	520.6	487.2	456.7	428.6	405.6	387.4	369.6	355.4	344.2
20°	597.5	564.5	527.4	492.7	458.9	427.7	402.3	380.7	361.4	346.4	333.8
22.5°	610.5	571.8	533.4	496.3	458.7	425.1	396.4	374.1	353.3	338.5	325.1
25°	624.1	577.6	539.2	495.7	453.7	418.8	386.8	361.4	340.6	323.3	309.5
27.5°	635.6	577.3	531.6	484.7	445.7	410.8	376.5	349.4	327.3	308.5	294.5
30°	643.3	578.1	523.7	477.4	438.1	402.0	368.7	341.4	318.1	299.1	285.9
32.5°	648.1	577.6	516.5	467.1	425.9	393.9	360.2	331.9	308.0	289.3	276.6
35°	650.9	574.0	504.0	445.9	406.2	375.1	346.8	317.5	292.5	275.0	260.5
37.5°	645.2	566.6	489.7	425.4	381.9	351.4	327.5	302.6	278.6	259.4	246.9
40°	636.5	561.8	478.4	411.0	365.2	335.8	315.6	291.0	267.3	249.1	237.5
42.5°	619.6	552.1	466.1	394.9	347.9	318.5	299.8	279.3	256.9	239.8	228.2
45°	578.5	530.7	447.5	370.9	322.4	291.9	275.4	260.5	240.3	223.7	213.6
47.5°	521.4	498.7	420.7	345.5	295.6	266.3	249.2	237.3	222.5	209.0	199.4
50°	481.8	472.3	402.6	328.1	277.8	249.1	232.6	221.9	211.2	197.8	189.0
52.5°	436.1	441.9	381.4	310.2	259.7	231.4	216.0	207.4	197.8	186.7	179.0
55°	371.7	392.7	344.8	280.0	232.6	205.8	191.1	183.6	177.9	169.7	163.1
57.5°	311.4	338.2	305.2	248.9	206.1	183.0	168.9	160.7	157.0	152.7	147.5
60°	275.6	302.0	277.0	228.1	188.4	166.3	153.9	146.8	143.2	140.2	135.8
62.5°	243.7	270.4	249.4	206.9	170.8	150.4	139.6	132.7	129.9	128.4	124.6
65°	199.8	222.8	208.8	173.9	145.9	127.8	118.0	113.1	110.6	109.9	107.5
67.5°	162.6	180.1	170.0	144.2	122.2	106.6	98.2	94.1	92.1	91.9	90.1
70°	138.2	154.6	146.8	123.6	104.5	92.3	85.1	81.5	80.2	80.1	79.0
72.5°	119.2	130.7	124.5	105.1	90.4	79.3	74.0	70.2	68.9	69.1	68.4
75°	88.3	96.9	93.2	79.8	68.0	60.8	56.4	54.0	52.8	53.4	52.5
77.5°	63.5	69.0	65.7	56.4	49.1	43.9	40.6	39.2	38.1	38.1	37.7
80°	48.0	51.1	49.3	43.7	37.7	33.3	30.7	29.7	29.1	28.8	28.7
82.5°	34.2	36.9	34.7	30.9	26.8	24.1	22.6	21.4	20.9	21.0	20.8
85°	17.2	18.3	17.5	15.1	13.4	12.2	11.5	10.8	10.4	10.6	10.2
87.5°	8.3	8.0	7.2	6.2	5.6	4.8	4.6	4.0	4.0	4.2	4.3
90°	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6	2.1	3.4	4.8
92.5°	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8	11.4	11.0	10.6
95°	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7	32.9	27.1	21.4
97.5°	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7	75.1	72.5	69.9
100°	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1	109.9	112.7	115.5
102.5°	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5	142.6	144.6	146.6
105°	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8	190.4	191.9	193.5
107.5°	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7	241.0	242.2	243.5
110°	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7	274.8	276.0	277.1



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2	307.1	308.2	309.2
115°	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1	355.0	355.9	356.7
117.5°	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7	401.7	402.8	403.8
120°	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6	430.8	432.1	433.3
122.5°	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0	460.0	461.1	462.1
125°	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3	500.4	501.5	502.7
127.5°	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3	539.4	540.5	541.7
130°	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6	563.8	564.9	566.0
132.5°	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9	587.0	588.1	589.3
135°	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6	622.4	623.2	624.1
137.5°	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9	653.0	654.1	655.1
140°	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2	673.0	673.9	674.8
142.5°	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0	691.8	692.7	693.5
145°	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2	718.2	719.2	720.1
147.5°	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9	742.5	743.2	743.8
150°	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2	757.5	757.9	758.4
152.5°	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8	771.0	771.2	771.4
155°	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1	789.8	789.5	789.2
157.5°	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0	805.0	804.9	804.9
160°	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2	814.0	813.9	813.7
162.5°	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8	822.4	822.0	821.7
165°	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2	832.8	832.3	831.9
167.5°	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3	840.7	840.2	839.6
170°	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8	845.2	844.7	844.1
172.5°	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9	848.2	847.5	846.9
175°	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8	852.0	851.4	850.7
177.5°	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8	853.3	852.6	852.1
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	407.1	406.0	404.4	402.0	400.0	397.0	397.0	397.4	397.4	397.4	397.0
5°	394.8	391.8	388.1	383.9	379.5	375.1	374.3	372.6	371.5	370.7	369.7
7.5°	381.7	376.3	371.1	365.2	359.8	355.4	352.3	349.7	348.1	346.3	345.0
10°	372.9	366.3	360.1	353.9	347.0	341.6	338.2	335.8	334.0	332.3	331.6
12.5°	362.5	354.9	348.0	342.1	334.7	329.1	325.8	324.7	322.6	319.2	317.5
15°	347.2	340.2	332.0	323.0	319.3	312.5	308.7	306.9	305.7	303.1	302.3
17.5°	334.2	325.0	315.7	309.0	302.3	296.8	294.6	292.4	290.8	288.7	288.0
20°	323.7	315.6	307.1	299.9	292.8	286.8	285.0	283.4	281.8	280.9	280.0
22.5°	313.1	305.0	297.9	291.2	283.7	279.7	277.8	276.0	274.9	274.2	273.5
25°	298.3	291.0	283.2	277.2	271.2	268.5	267.3	266.4	265.5	264.6	264.3
27.5°	285.0	277.1	270.8	265.1	260.8	258.6	257.4	257.0	257.2	257.5	257.8
30°	275.0	267.8	262.6	257.8	253.7	251.8	251.5	251.5	252.4	252.5	253.0
32.5°	265.9	259.9	254.7	250.0	247.0	245.6	246.4	246.4	247.0	247.5	248.3
35°	252.5	247.3	243.3	239.3	236.7	237.3	237.7	238.1	239.1	240.3	241.1
37.5°	239.8	235.3	231.1	228.0	226.8	227.8	228.9	229.6	230.8	231.8	232.6
40°	230.7	227.2	223.3	220.4	220.8	221.4	222.2	223.3	224.3	224.9	225.7
42.5°	222.1	218.6	215.5	213.2	213.8	214.6	215.0	215.5	216.7	217.8	218.3
45°	209.2	206.4	203.6	202.2	202.6	203.0	203.4	204.0	205.0	205.8	206.0
47.5°	194.7	192.7	190.8	189.4	190.1	189.9	190.5	191.7	192.0	192.5	193.6
50°	185.4	183.6	181.3	180.9	180.9	180.9	181.2	182.7	182.7	183.6	184.3
52.5°	175.0	173.9	172.5	171.8	171.4	171.4	172.3	173.1	173.4	174.5	175.4
55°	159.9	158.7	157.5	156.9	156.4	156.9	158.4	158.9	159.9	160.5	161.1
57.5°	144.0	143.1	142.2	141.8	141.7	142.2	143.1	144.3	144.6	146.5	147.3
60°	133.6	132.2	131.4	131.4	131.0	132.8	132.4	134.4	134.8	136.0	137.4
62.5°	122.9	121.0	120.6	120.6	121.2	121.7	122.3	123.1	124.2	125.7	126.8
65°	105.5	104.5	105.9	105.7	105.3	106.5	106.5	107.5	108.7	110.1	112.4
67.5°	89.1	88.6	88.7	88.7	89.3	90.0	90.6	91.4	92.9	94.4	95.8
70°	78.0	78.6	77.7	78.4	79.0	79.2	79.6	80.8	82.4	83.4	85.1
72.5°	67.2	67.2	67.3	67.7	68.3	68.6	69.1	70.4	72.2	73.0	74.3
75°	51.7	51.6	52.2	52.2	53.1	53.6	54.0	54.6	56.1	57.3	58.4
77.5°	37.8	38.1	37.9	38.6	38.3	38.4	39.6	40.2	40.4	42.8	43.3
80°	28.5	28.8	29.1	29.3	29.4	29.1	30.5	31.1	31.1	32.5	33.5
82.5°	20.5	20.7	21.2	21.4	21.4	21.9	22.0	22.4	22.9	23.5	24.8
85°	10.2	10.8	11.0	10.8	11.0	10.6	11.2	11.5	11.6	11.6	11.6
87.5°	4.5	4.9	5.2	5.7	5.9	6.4	6.5	6.3	6.5	7.1	6.5
90°	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4	16.9	17.5	17.9
92.5°	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0	18.9	19.8	20.3
95°	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6	22.6	23.6	24.1
97.5°	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6	23.8	24.9	25.6
100°	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2	24.3	25.4	26.1
102.5°	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7	31.3	27.7	26.1
105°	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9	64.0	39.1	26.8
107.5°	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7	199.5	181.2	162.7
110°	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5	271.8	267.2	254.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9	318.0	318.1	315.9
115°	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5	367.9	369.3	370.3
117.5°	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5	411.6	412.8	413.4
120°	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5	440.6	441.7	442.2
122.5°	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6	468.4	469.2	469.7
125°	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4	507.7	508.0	508.2
127.5°	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3	547.8	548.2	548.3
130°	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4	571.9	572.5	572.7
132.5°	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2	594.7	595.3	595.4
135°	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7	629.1	629.6	629.6
137.5°	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5	660.2	660.9	661.1
140°	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1	679.6	680.2	680.4
142.5°	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6	698.0	698.4	698.5
145°	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5	723.8	724.0	724.2
147.5°	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7	746.9	747.3	747.0
150°	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9	761.1	761.4	761.4
152.5°	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4	774.0	774.5	774.4
155°	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8	791.5	792.3	792.2
157.5°	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0	806.8	807.6	807.5
160°	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6	815.5	816.2	816.2
162.5°	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4	823.4	824.3	824.3
165°	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8	834.0	835.1	835.2
167.5°	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9	842.1	843.3	843.3
170°	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5	846.7	847.8	847.8
172.5°	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6	849.7	850.8	850.8
175°	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2	853.3	854.2	854.1
177.5°	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6	854.5	855.4	855.2
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	395.9	395.7	396.8	396.1	396.8	395.7	395.9	397.0	397.4	397.4	397.4
5°	368.5	369.1	367.0	367.0	367.0	369.1	368.5	369.7	370.7	371.5	372.6
7.5°	344.1	343.2	343.3	342.2	343.3	343.2	344.1	345.0	346.3	348.1	349.7
10°	329.2	328.0	327.5	327.8	327.5	328.0	329.2	331.6	332.3	334.0	335.8
12.5°	316.8	316.6	313.9	313.9	313.9	316.6	316.8	317.5	319.2	322.6	324.7
15°	302.3	298.5	298.1	299.3	298.1	298.5	302.3	302.3	303.1	305.7	306.9
17.5°	287.7	285.7	285.9	285.2	285.9	285.7	287.7	288.0	288.7	290.8	292.4
20°	280.0	278.8	278.6	277.2	278.6	278.8	280.0	280.0	280.9	281.8	283.4
22.5°	272.9	272.6	272.7	271.1	272.7	272.6	272.9	273.5	274.2	274.9	276.0
25°	264.2	265.2	264.3	264.3	264.3	265.2	264.2	264.3	264.6	265.5	266.4
27.5°	258.2	258.2	257.8	257.8	257.8	258.2	258.2	257.8	257.5	257.2	257.0
30°	253.7	253.6	253.9	253.9	253.9	253.6	253.7	253.0	252.5	252.4	251.5
32.5°	249.3	249.5	249.6	249.8	249.6	249.5	249.3	248.3	247.5	247.0	246.4
35°	242.3	242.5	243.1	242.7	243.1	242.5	242.3	241.1	240.3	239.1	238.1
37.5°	232.9	233.8	233.7	233.9	233.7	233.8	232.9	232.6	231.8	230.8	229.6
40°	225.8	226.4	226.3	226.3	226.3	226.4	225.8	225.7	224.9	224.3	223.3
42.5°	218.6	219.0	218.5	218.3	218.5	219.0	218.6	218.3	217.8	216.7	215.5
45°	206.8	206.4	207.0	206.2	207.0	206.4	206.8	206.0	205.8	205.0	204.0
47.5°	193.6	194.0	194.2	194.8	194.2	194.0	193.6	193.6	192.5	192.0	191.7
50°	184.8	186.0	186.0	185.7	186.0	186.0	184.8	184.3	183.6	182.7	182.7
52.5°	176.1	176.6	177.5	177.4	177.5	176.6	176.1	175.4	174.5	173.4	173.1
55°	162.6	163.1	163.5	163.7	163.5	163.1	162.6	161.1	160.5	159.9	158.9
57.5°	148.8	148.6	149.6	149.9	149.6	148.6	148.8	147.3	146.5	144.6	144.3
60°	139.0	139.0	140.6	141.2	140.6	139.0	139.0	137.4	136.0	134.8	134.4
62.5°	128.5	129.2	130.8	130.0	130.8	129.2	128.5	126.8	125.7	124.2	123.1
65°	113.3	114.9	114.8	115.5	114.8	114.9	113.3	112.4	110.1	108.7	107.5
67.5°	97.4	98.4	99.9	100.0	99.9	98.4	97.4	95.8	94.4	92.9	91.4
70°	86.6	87.6	88.4	89.0	88.4	87.6	86.6	85.1	83.4	82.4	80.8
72.5°	76.2	76.7	78.7	77.8	78.7	76.7	76.2	74.3	73.0	72.2	70.4
75°	59.8	61.2	62.4	61.8	62.4	61.2	59.8	58.4	57.3	56.1	54.6
77.5°	44.2	45.6	46.1	45.6	46.1	45.6	44.2	43.3	42.8	40.4	40.2
80°	34.9	34.7	35.9	35.7	35.9	34.7	34.9	33.5	32.5	31.1	31.1
82.5°	25.6	25.4	25.9	26.1	25.9	25.4	25.6	24.8	23.5	22.9	22.4
85°	12.4	13.0	12.2	12.1	12.2	13.0	12.4	11.6	11.6	11.6	11.5
87.5°	6.5	6.5	6.5	6.4	6.5	6.5	6.5	6.5	7.1	6.5	6.3
90°	18.2	18.4	18.7	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4
92.5°	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0
95°	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6
97.5°	25.7	25.8	26.0	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6
100°	26.2	26.3	26.4	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2
102.5°	26.3	26.6	26.9	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7
105°	27.0	27.3	27.6	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9
107.5°	143.9	125.1	106.3	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7
110°	234.6	214.5	194.3	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	311.7	307.5	303.2	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9
115°	370.8	371.4	372.0	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5
117.5°	413.5	413.6	413.7	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5
120°	442.2	442.2	442.2	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5
122.5°	469.8	469.8	470.0	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6
125°	508.6	508.9	509.1	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4
127.5°	548.0	547.7	547.4	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3
130°	572.3	572.0	571.8	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4
132.5°	595.0	594.6	594.2	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2
135°	629.1	628.7	628.3	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7
137.5°	660.8	660.5	660.2	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5
140°	680.0	679.8	679.5	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1
142.5°	698.1	697.8	697.3	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6
145°	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5
147.5°	746.4	745.7	745.1	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7
150°	761.0	760.5	760.1	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9
152.5°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4
155°	791.3	790.5	789.6	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8
157.5°	806.4	805.3	804.3	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0
160°	815.2	814.2	813.2	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6
162.5°	823.5	822.6	821.7	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4
165°	834.2	833.2	832.2	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8
167.5°	842.1	840.9	839.8	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9
170°	846.7	845.5	844.4	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5
172.5°	849.5	848.3	847.1	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6
175°	853.0	851.9	850.8	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2
177.5°	854.1	853.0	851.9	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	397.0	397.0	400.0	402.0	404.4	406.0	407.1	408.2	410.2	412.7	415.6
5°	374.3	375.1	379.5	383.9	388.1	391.8	394.8	398.4	402.8	408.2	414.2
7.5°	352.3	355.4	359.8	365.2	371.1	376.3	381.7	387.6	393.9	401.8	410.3
10°	338.2	341.6	347.0	353.9	360.1	366.3	372.9	379.3	387.1	396.6	407.4
12.5°	325.8	329.1	334.7	342.1	348.0	354.9	362.5	370.8	379.6	390.9	403.2
15°	308.7	312.5	319.3	323.0	332.0	340.2	347.2	359.2	370.5	382.1	396.3
17.5°	294.6	296.8	302.3	309.0	315.7	325.0	334.2	344.2	355.4	369.6	387.4
20°	285.0	286.8	292.8	299.9	307.1	315.6	323.7	333.8	346.4	361.4	380.7
22.5°	277.8	279.7	283.7	291.2	297.9	305.0	313.1	325.1	338.5	353.3	374.1
25°	267.3	268.5	271.2	277.2	283.2	291.0	298.3	309.5	323.3	340.6	361.4
27.5°	257.4	258.6	260.8	265.1	270.8	277.1	285.0	294.5	308.5	327.3	349.4
30°	251.5	251.8	253.7	257.8	262.6	267.8	275.0	285.9	299.1	318.1	341.4
32.5°	246.4	245.6	247.0	250.0	254.7	259.9	265.9	276.6	289.3	308.0	331.9
35°	237.7	237.3	236.7	239.3	243.3	247.3	252.5	260.5	275.0	292.5	317.5
37.5°	228.9	227.8	226.8	228.0	231.1	235.3	239.8	246.9	259.4	278.6	302.6
40°	222.2	221.4	220.8	220.4	223.3	227.2	230.7	237.5	249.1	267.3	291.0
42.5°	215.0	214.6	213.8	213.2	215.5	218.6	222.1	228.2	239.8	256.9	279.3
45°	203.4	203.0	202.6	202.2	203.6	206.4	209.2	213.6	223.7	240.3	260.5
47.5°	190.5	189.9	190.1	189.4	190.8	192.7	194.7	199.4	209.0	222.5	237.3
50°	181.2	180.9	180.9	180.9	181.3	183.6	185.4	189.0	197.8	211.2	221.9
52.5°	172.3	171.4	171.4	171.8	172.5	173.9	175.0	179.0	186.7	197.8	207.4
55°	158.4	156.9	156.4	156.9	157.5	158.7	159.9	163.1	169.7	177.9	183.6
57.5°	143.1	142.2	141.7	141.8	142.2	143.1	144.0	147.5	152.7	157.0	160.7
60°	132.4	132.8	131.0	131.4	131.4	132.2	133.6	135.8	140.2	143.2	146.8
62.5°	122.3	121.7	121.2	120.6	120.6	121.0	122.9	124.6	128.4	129.9	132.7
65°	106.5	106.5	105.3	105.7	105.9	104.5	105.5	107.5	109.9	110.6	113.1
67.5°	90.6	90.0	89.3	88.7	88.7	88.6	89.1	90.1	91.9	92.1	94.1
70°	79.6	79.2	79.0	78.4	77.7	78.6	78.0	79.0	80.1	80.2	81.5
72.5°	69.1	68.6	68.3	67.7	67.3	67.2	67.2	68.4	69.1	68.9	70.2
75°	54.0	53.6	53.1	52.2	52.2	51.6	51.7	52.5	53.4	52.8	54.0
77.5°	39.6	38.4	38.3	38.6	37.9	38.1	37.8	37.7	38.1	38.1	39.2
80°	30.5	29.1	29.4	29.3	29.1	28.8	28.5	28.7	28.8	29.1	29.7
82.5°	22.0	21.9	21.4	21.4	21.2	20.7	20.5	20.8	21.0	20.9	21.4
85°	11.2	10.6	11.0	10.8	11.0	10.8	10.2	10.2	10.6	10.4	10.8
87.5°	6.5	6.4	5.9	5.7	5.2	4.9	4.5	4.3	4.2	4.0	4.0
90°	15.8	15.2	13.3	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6
92.5°	17.1	16.2	14.8	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8
95°	20.7	19.6	18.1	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7
97.5°	21.5	20.4	30.6	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7
100°	22.0	20.9	42.9	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1
102.5°	38.2	41.7	65.7	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5
105°	113.8	138.8	151.4	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8
107.5°	236.0	254.3	252.4	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7
110°	281.1	285.8	284.2	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	317.8	317.7	316.2	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2
115°	365.1	363.7	362.4	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1
117.5°	409.4	408.3	407.6	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7
120°	438.3	437.1	436.8	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6
122.5°	466.8	466.1	465.5	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0
125°	507.1	506.9	506.3	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3
127.5°	546.8	546.4	545.7	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3
130°	570.8	570.2	569.6	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6
132.5°	593.6	593.1	592.5	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9
135°	628.3	627.8	627.3	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6
137.5°	658.8	658.1	657.9	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9
140°	678.5	678.0	677.5	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2
142.5°	697.2	696.7	696.3	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0
145°	723.2	722.9	722.6	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2
147.5°	746.4	746.1	745.8	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9
150°	760.6	760.3	760.0	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2
152.5°	772.9	772.5	772.3	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8
155°	790.1	789.5	789.3	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1
157.5°	805.1	804.3	804.4	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0
160°	813.7	812.9	813.0	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2
162.5°	821.5	820.4	820.6	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8
165°	831.7	830.6	830.8	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2
167.5°	839.8	838.7	838.7	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3
170°	844.4	843.3	843.3	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8
172.5°	847.5	846.4	846.2	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9
175°	851.3	850.2	850.2	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8
177.5°	852.6	851.8	851.7	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	416.6	417.4	420.1	422.1	424.3	425.6	426.8	427.8	429.1	429.4	434.0
5°	418.4	422.4	429.5	434.6	441.1	448.1	452.9	455.1	461.0	465.7	475.4
7.5°	417.9	426.5	437.0	448.1	459.8	470.7	480.2	491.5	499.4	511.4	523.2
10°	417.4	428.9	442.5	456.5	472.9	488.2	501.9	517.1	529.8	546.4	560.6
12.5°	415.9	429.8	448.8	465.4	485.3	506.4	526.6	546.1	557.3	585.0	598.1
15°	412.4	428.9	452.5	477.8	505.2	530.1	555.8	576.3	609.3	633.6	649.1
17.5°	405.6	428.6	456.7	487.2	520.6	553.4	582.5	613.5	648.6	678.0	709.3
20°	402.3	427.7	458.9	492.7	527.4	564.5	597.5	634.8	673.1	702.1	742.2
22.5°	396.4	425.1	458.7	496.3	533.4	571.8	610.5	648.2	692.4	732.2	770.4
25°	386.8	418.8	453.7	495.7	539.2	577.6	624.1	674.0	720.1	771.3	809.3
27.5°	376.5	410.8	445.7	484.7	531.6	577.3	635.6	692.0	748.4	792.6	820.8
30°	368.7	402.0	438.1	477.4	523.7	578.1	643.3	704.8	759.8	797.7	813.6
32.5°	360.2	393.9	425.9	467.1	516.5	577.6	648.1	712.4	760.4	785.7	782.6
35°	346.8	375.1	406.2	445.9	504.0	574.0	650.9	713.1	742.5	737.1	696.2
37.5°	327.5	351.4	381.9	425.4	489.7	566.6	645.2	691.9	690.0	645.9	586.6
40°	315.6	335.8	365.2	411.0	478.4	561.8	636.5	666.8	641.1	579.5	508.5
42.5°	299.8	318.5	347.9	394.9	466.1	552.1	619.6	628.4	578.2	507.3	442.2
45°	275.4	291.9	322.4	370.9	447.5	530.7	578.5	557.0	489.4	416.2	366.7
47.5°	249.2	266.3	295.6	345.5	420.7	498.7	521.4	475.8	406.4	347.0	301.5
50°	232.6	249.1	277.8	328.1	402.6	472.3	481.8	422.8	359.0	306.9	269.6
52.5°	216.0	231.4	259.7	310.2	381.4	441.9	436.1	376.0	317.4	272.9	243.6
55°	191.1	205.8	232.6	280.0	344.8	392.7	371.7	314.4	265.8	231.3	209.0
57.5°	168.9	183.0	206.1	248.9	305.2	338.2	311.4	263.0	224.5	197.9	181.3
60°	153.9	166.3	188.4	228.1	277.0	302.0	275.6	232.9	200.4	179.1	164.3
62.5°	139.6	150.4	170.8	206.9	249.4	270.4	243.7	207.5	179.9	161.0	148.4
65°	118.0	127.8	145.9	173.9	208.8	222.8	199.8	170.5	149.0	135.0	126.6
67.5°	98.2	106.6	122.2	144.2	170.0	180.1	162.6	139.9	123.7	112.4	105.8
70°	85.1	92.3	104.5	123.6	146.8	154.6	138.2	119.5	107.7	98.7	92.5
72.5°	74.0	79.3	90.4	105.1	124.5	130.7	119.2	102.9	91.9	85.1	80.1
75°	56.4	60.8	68.0	79.8	93.2	96.9	88.3	78.0	70.6	65.8	62.0
77.5°	40.6	43.9	49.1	56.4	65.7	69.0	63.5	56.7	51.2	48.0	45.9
80°	30.7	33.3	37.7	43.7	49.3	51.1	48.0	42.7	38.9	37.1	35.3
82.5°	22.6	24.1	26.8	30.9	34.7	36.9	34.2	31.0	28.9	27.3	26.6
85°	11.5	12.2	13.4	15.1	17.5	18.3	17.2	16.4	15.2	14.2	14.2
87.5°	4.6	4.8	5.6	6.2	7.2	8.0	8.3	8.3	8.5	8.4	8.4
90°	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4
92.5°	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0
95°	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6
97.5°	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6
100°	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2
102.5°	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7
105°	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9
107.5°	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7
110°	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9
115°	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5
117.5°	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5
120°	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5
122.5°	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6
125°	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4
127.5°	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3
130°	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4
132.5°	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2
135°	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7
137.5°	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5
140°	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1
142.5°	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6
145°	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5
147.5°	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7
150°	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9
152.5°	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4
155°	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8
157.5°	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0
160°	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6
162.5°	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4
165°	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8
167.5°	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9
170°	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5
172.5°	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6
175°	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2
177.5°	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	435.7	435.8	437.6	438.9	438.2	439.0	439.4
5°	476.0	483.2	487.0	489.8	490.0	490.3	491.8
7.5°	533.1	540.9	546.6	555.2	557.7	560.6	559.8
10°	574.9	586.3	596.2	601.3	607.0	615.2	608.6
12.5°	613.9	634.1	649.1	657.2	662.5	664.1	660.9
15°	678.2	704.6	718.8	718.5	736.5	744.3	732.1
17.5°	737.1	761.6	781.2	791.2	806.2	809.5	808.0
20°	773.3	800.0	815.2	832.4	840.2	847.2	848.4
22.5°	804.3	828.4	844.7	859.0	865.6	868.9	870.9
25°	836.5	855.3	865.1	870.1	871.9	871.5	868.9
27.5°	834.2	835.7	824.8	814.2	804.7	794.0	790.3
30°	812.5	795.7	765.6	748.6	723.5	703.6	711.7
32.5°	755.6	722.0	688.3	651.0	620.2	611.4	602.5
35°	644.9	585.9	551.4	511.3	495.2	479.2	468.1
37.5°	521.7	476.1	435.1	409.0	392.9	382.7	377.3
40°	451.1	410.0	376.3	355.0	342.8	331.4	329.8
42.5°	394.8	356.5	331.2	314.3	302.6	297.6	294.1
45°	323.3	296.7	279.7	267.6	259.8	256.8	252.7
47.5°	273.7	254.9	242.0	233.8	227.9	225.7	225.4
50°	245.9	230.2	220.8	214.4	209.8	209.0	205.8
52.5°	225.1	211.5	204.1	198.5	195.2	193.0	192.0
55°	195.4	186.3	179.7	176.5	173.9	171.7	171.7
57.5°	170.9	163.4	159.0	156.3	155.5	153.9	152.9
60°	155.8	149.5	146.0	143.6	142.0	142.2	140.4
62.5°	141.1	136.9	133.6	131.3	129.3	129.4	129.5
65°	120.1	116.9	114.5	113.7	112.5	111.2	111.5
67.5°	101.9	98.8	96.9	95.6	95.1	94.4	95.6
70°	88.7	86.4	85.1	83.9	83.4	83.6	84.6
72.5°	76.6	75.1	74.1	73.6	72.7	72.8	73.4
75°	60.2	59.0	58.2	57.6	57.3	57.3	57.3
77.5°	44.2	43.9	43.6	42.7	42.7	43.0	43.0
80°	34.9	34.3	34.1	33.7	33.1	32.7	33.7
82.5°	26.1	25.5	25.3	25.2	24.3	24.2	25.1
85°	14.0	13.4	13.6	13.4	13.4	13.3	13.3
87.5°	8.4	8.3	8.3	8.4	8.4	8.3	8.6
90°	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332096-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)