

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332100-935

Luminaire Tested: **S123DIW-S340D755U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332100-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D755U935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3817.1 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32								
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27								
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22								
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19								
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16								
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14								
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12								
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11								
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10								
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9								
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.2
10°-20°	124.1	3.3
20°-30°	183.3	4.8
30°-40°	214.1	5.6
40°-50°	215.3	5.6
50°-60°	189.1	5.0
60°-70°	140.9	3.7
70°-80°	80.3	2.1
80°-90°	25.4	0.7
90°-100°	31.0	0.8
100°-110°	147.8	3.9
110°-120°	355.0	9.3
120°-130°	452.0	11.8
130°-140°	482.9	12.7
140°-150°	451.6	11.8
150°-160°	364.3	9.5
160°-170°	235.1	6.2
170°-180°	81.0	2.1
0°-30°	351.4	9.2
0°-40°	565.5	14.8
0°-60°	969.9	25.4
0°-90°	1216.5	31.9
90°-120°	533.7	14.0
90°-150°	1920.2	50.3
90°-180°	2601.0	68.1
0°-180°	3817.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	1	7	15	18	19	3
95°	39	14	20	24	24	48
105°	189	192	139	33	28	200
115°	354	358	364	370	373	349
125°	499	504	507	508	509	446
135°	622	625	628	630	628	478
145°	717	722	723	724	724	449
155°	790	789	790	792	789	364
165°	833	831	831	835	831	235
175°	853	850	850	854	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.4	8.5	8.6	8.7	8.8	9.0	9.2	9.5	9.8	10.1	10.2
90°	0.6	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8
92.5°	11.8	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1
95°	38.7	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7
97.5°	77.7	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5
100°	107.1	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0
102.5°	140.5	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2
105°	188.8	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8
107.5°	239.7	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0
110°	273.7	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1



TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.2	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8
115°	354.1	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1
117.5°	400.7	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4
120°	429.6	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3
122.5°	459.0	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8
125°	499.3	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1
127.5°	538.3	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8
130°	562.6	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8
132.5°	585.9	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6
135°	621.6	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3
137.5°	651.9	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8
140°	672.2	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5
142.5°	691.0	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2
145°	717.2	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2
147.5°	741.9	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4
150°	757.2	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6
152.5°	770.8	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9
155°	790.1	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1
157.5°	805.0	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1
160°	814.2	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7
162.5°	822.8	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5
165°	833.2	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7
167.5°	841.3	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8
170°	845.8	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4
172.5°	848.9	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5
175°	852.8	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3
177.5°	853.8	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	10.2	10.2	10.2	10.3	10.3	10.4	10.5	10.5
90°	16.4	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.0	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	21.6	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	22.6	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	23.2	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	34.7	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	88.9	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	217.7	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	276.5	271.8	267.2	254.8	234.6	214.5	194.3	174.3





TEST NUMBER: P332100-935

CATALOG NUMBER: S123DIW-S340D755U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	317.9	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	366.5	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	410.5	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	439.5	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	467.6	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.4	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.3	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.4	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.2	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	659.5	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.1	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	697.6	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.5	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.7	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	760.9	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	773.4	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	790.8	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.0	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	814.6	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	822.4	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	832.8	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	848.6	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	852.2	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	853.6	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)