

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332132-935

Luminaire Tested: **S123DIW-S560D1030U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332132-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1030U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5607.2 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	57	71	64	58	53	52	48	44	41	38	35	31	29	27	23
4	72	62	54	49	65	56	50	45	46	41	38	37	33	30	28	25	24	20
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.0	1.2
10°-20°	215.0	3.8
20°-30°	360.8	6.4
30°-40°	408.6	7.3
40°-50°	366.4	6.5
50°-60°	295.7	5.3
60°-70°	206.0	3.7
70°-80°	108.3	1.9
80°-90°	29.7	0.5
90°-100°	42.3	0.8
100°-110°	201.7	3.6
110°-120°	484.5	8.6
120°-130°	616.9	11.0
130°-140°	659.2	11.8
140°-150°	616.4	11.0
150°-160°	497.2	8.9
160°-170°	320.9	5.7
170°-180°	110.6	2.0
0°-30°	642.9	11.5
0°-40°	1051.4	18.8
0°-60°	1713.5	30.6
0°-90°	2057.5	36.7
90°-120°	728.5	13.0
90°-150°	2621.0	46.7
90°-180°	3550.0	63.3
0°-180°	5607.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	26
90°	26	1	26	1	26	13
95°	33	53	33	53	33	27
105°	38	258	38	258	38	87
115°	508	484	508	484	508	470
125°	695	682	695	682	695	621
135°	857	848	857	848	857	661
145°	988	979	988	979	988	617
155°	1077	1078	1077	1078	1077	496
165°	1135	1137	1135	1137	1135	320
175°	1160	1164	1160	1164	1160	110
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	13.1	12.5	12.7	12.9	12.6	12.7	12.8	12.9	13.0	13.1	12.9
90°	25.9	25.6	25.1	24.8	24.4	23.8	23.1	22.3	21.5	20.8	18.3
92.5°	28.7	28.5	28.2	28.0	27.8	27.0	25.8	24.6	23.3	22.1	20.2
95°	32.9	32.9	32.9	32.9	32.9	32.2	30.8	29.5	28.2	26.8	24.7
97.5°	35.6	35.5	35.2	35.0	34.9	34.0	32.5	30.9	29.4	27.8	41.7
100°	36.3	36.2	35.9	35.7	35.6	34.7	33.1	31.6	30.0	28.5	58.5
102.5°	37.0	36.7	36.3	36.0	35.6	37.8	42.6	47.4	52.2	56.9	89.6
105°	38.1	37.6	37.3	36.9	36.5	53.3	87.3	121.4	155.4	189.4	206.7
107.5°	119.5	145.2	170.8	196.4	222.1	247.4	272.3	297.2	322.2	347.2	344.4
110°	237.8	265.3	292.7	320.3	347.8	364.6	371.0	377.4	383.7	390.0	387.9



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.0	413.8	419.7	425.4	431.2	434.0	433.9	433.9	433.7	433.6	431.5
115°	508.5	507.7	507.0	506.2	505.4	504.1	502.1	500.2	498.3	496.4	494.6
117.5°	564.9	564.7	564.6	564.4	564.3	563.4	561.9	560.3	558.8	557.2	556.4
120°	603.6	603.6	603.6	603.6	603.6	602.9	601.3	599.8	598.2	596.7	596.2
122.5°	641.7	641.5	641.4	641.2	641.1	640.4	639.4	638.3	637.2	636.1	635.4
125°	695.3	694.9	694.5	694.1	693.8	693.4	693.0	692.6	692.2	691.8	691.0
127.5°	746.8	747.3	747.6	748.0	748.4	748.3	747.6	747.0	746.4	745.8	744.9
130°	780.1	780.4	780.8	781.2	781.6	781.4	780.6	779.9	779.1	778.3	777.6
132.5°	810.5	811.1	811.6	812.1	812.6	812.5	811.8	811.0	810.2	809.4	808.8
135°	857.0	857.6	858.2	858.8	859.3	859.3	858.8	858.2	857.6	857.0	856.3
137.5°	900.8	901.1	901.6	901.9	902.3	902.1	901.1	900.2	899.2	898.4	897.9
140°	927.0	927.5	927.8	928.2	928.6	928.4	927.6	926.9	926.1	925.3	924.7
142.5°	951.2	951.8	952.4	952.9	953.4	953.4	952.8	952.2	951.6	950.9	950.4
145°	988.4	988.4	988.4	988.4	988.4	988.3	987.9	987.5	987.1	986.7	986.4
147.5°	1016.2	1017.0	1017.9	1018.8	1019.7	1019.9	1019.5	1019.2	1018.7	1018.4	1018.0
150°	1036.9	1037.5	1038.0	1038.6	1039.2	1039.3	1038.9	1038.5	1038.1	1037.8	1037.3
152.5°	1053.5	1054.4	1055.2	1056.1	1057.0	1057.1	1056.4	1055.8	1055.1	1054.4	1054.1
155°	1076.7	1077.8	1079.0	1080.1	1081.2	1081.4	1080.4	1079.4	1078.5	1077.5	1077.4
157.5°	1096.2	1097.7	1099.2	1100.7	1102.2	1102.3	1101.2	1100.1	1098.9	1097.8	1097.9
160°	1108.6	1110.0	1111.4	1112.7	1114.0	1114.1	1113.0	1111.8	1110.7	1109.6	1109.7
162.5°	1120.4	1121.6	1122.8	1124.0	1125.2	1125.2	1123.9	1122.5	1121.2	1119.9	1120.1
165°	1134.6	1135.9	1137.3	1138.7	1140.0	1139.9	1138.3	1136.8	1135.3	1133.8	1133.9
167.5°	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8	1144.8
170°	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1	1151.1
172.5°	1154.5	1156.2	1157.9	1159.6	1161.2	1161.3	1159.8	1158.3	1156.8	1155.2	1155.0
175°	1159.7	1161.2	1162.8	1164.3	1165.9	1166.0	1164.6	1163.2	1161.9	1160.5	1160.4
177.5°	1161.2	1162.8	1164.3	1165.9	1167.4	1167.5	1166.3	1165.1	1163.9	1162.6	1162.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	12.9	12.7	11.4	9.9	9.0	7.8	7.4	6.5	6.4	6.7	6.9
90°	15.8	13.3	10.8	8.5	6.6	4.7	2.8	0.9	2.8	4.7	6.6
92.5°	18.3	16.5	14.6	13.9	14.5	15.0	15.6	16.1	15.6	15.0	14.5
95°	22.6	20.5	18.3	21.3	29.1	37.0	44.9	52.8	44.9	37.0	29.1
97.5°	55.5	69.4	83.2	91.9	95.4	98.9	102.5	106.0	102.5	98.9	95.4
100°	88.5	118.5	148.4	161.5	157.6	153.9	150.0	146.1	150.0	153.9	157.6
102.5°	122.4	155.2	187.9	202.9	200.1	197.3	194.6	191.8	194.6	197.3	200.1
105°	223.9	241.3	258.6	266.1	264.1	261.9	259.8	257.7	259.8	261.9	264.1
107.5°	341.6	339.0	336.2	334.0	332.3	330.6	328.9	327.3	328.9	330.6	332.3
110°	385.8	383.7	381.6	379.7	378.2	376.7	375.1	373.6	375.1	376.7	378.2



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	429.4	427.2	425.2	423.4	422.1	420.6	419.2	417.8	419.2	420.6	422.1
115°	492.9	491.2	489.5	488.0	486.9	485.7	484.6	483.5	484.6	485.7	486.9
117.5°	555.5	554.7	553.7	552.6	551.1	549.7	548.3	546.9	548.3	549.7	551.1
120°	595.6	595.0	594.4	593.2	591.5	589.8	588.1	586.3	588.1	589.8	591.5
122.5°	634.6	634.0	633.2	632.1	630.7	629.3	627.8	626.5	627.8	629.3	630.7
125°	690.3	689.5	688.8	687.6	686.0	684.5	683.0	681.5	683.0	684.5	686.0
127.5°	744.0	743.0	742.1	740.9	739.3	737.8	736.2	734.7	736.2	737.8	739.3
130°	776.8	776.0	775.2	774.1	772.6	771.0	769.5	767.9	769.5	771.0	772.6
132.5°	808.2	807.6	807.0	805.9	804.3	802.8	801.3	799.8	801.3	802.8	804.3
135°	855.5	854.7	853.9	853.0	851.8	850.7	849.5	848.3	849.5	850.7	851.8
137.5°	897.5	897.1	896.6	895.7	894.2	892.8	891.3	889.8	891.3	892.8	894.2
140°	924.2	923.6	923.0	922.1	921.0	919.9	918.7	917.6	918.7	919.9	921.0
142.5°	949.8	949.2	948.6	947.8	946.6	945.5	944.3	943.1	944.3	945.5	946.6
145°	985.9	985.6	985.2	984.3	983.0	981.6	980.2	979.0	980.2	981.6	983.0
147.5°	1017.6	1017.2	1016.8	1016.2	1015.3	1014.4	1013.6	1012.7	1013.6	1014.4	1015.3
150°	1037.0	1036.6	1036.2	1035.7	1035.2	1034.6	1034.0	1033.5	1034.0	1034.6	1035.2
152.5°	1053.9	1053.7	1053.4	1053.2	1052.9	1052.7	1052.4	1052.1	1052.4	1052.7	1052.9
155°	1077.1	1076.9	1076.8	1076.9	1077.3	1077.6	1078.0	1078.4	1078.0	1077.6	1077.3
157.5°	1098.1	1098.4	1098.5	1098.6	1098.7	1098.7	1098.8	1098.8	1098.8	1098.7	1098.7
160°	1109.9	1110.1	1110.3	1110.5	1110.7	1110.9	1111.0	1111.3	1111.0	1110.9	1110.7
162.5°	1120.3	1120.5	1120.7	1121.0	1121.5	1122.1	1122.5	1123.0	1122.5	1122.1	1121.5
165°	1134.1	1134.3	1134.5	1134.9	1135.5	1136.1	1136.6	1137.2	1136.6	1136.1	1135.5
167.5°	1144.8	1144.8	1144.8	1145.2	1146.0	1146.8	1147.5	1148.2	1147.5	1146.8	1146.0
170°	1151.1	1151.1	1151.1	1151.4	1152.2	1153.0	1153.7	1154.5	1153.7	1153.0	1152.2
172.5°	1154.9	1154.7	1154.6	1154.9	1155.9	1156.8	1157.7	1158.6	1157.7	1156.8	1155.9
175°	1160.2	1159.9	1159.8	1160.2	1161.1	1162.1	1163.0	1164.0	1163.0	1162.1	1161.1
177.5°	1162.4	1162.2	1162.0	1162.4	1163.1	1163.9	1164.6	1165.4	1164.6	1163.9	1163.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	7.0	7.7	7.9	8.7	9.0	9.7	9.8	9.5	9.6	10.6	9.6
90°	8.5	10.8	13.3	15.8	18.3	20.8	21.5	22.3	23.1	23.8	24.4
92.5°	13.9	14.6	16.5	18.3	20.2	22.1	23.3	24.6	25.8	27.0	27.8
95°	21.3	18.3	20.5	22.6	24.7	26.8	28.2	29.5	30.8	32.2	32.9
97.5°	91.9	83.2	69.4	55.5	41.7	27.8	29.4	30.9	32.5	34.0	34.9
100°	161.5	148.4	118.5	88.5	58.5	28.5	30.0	31.6	33.1	34.7	35.6
102.5°	202.9	187.9	155.2	122.4	89.6	56.9	52.2	47.4	42.6	37.8	35.6
105°	266.1	258.6	241.3	223.9	206.7	189.4	155.4	121.4	87.3	53.3	36.5
107.5°	334.0	336.2	339.0	341.6	344.4	347.2	322.2	297.2	272.3	247.4	222.1
110°	379.7	381.6	383.7	385.8	387.9	390.0	383.7	377.4	371.0	364.6	347.8



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	423.4	425.2	427.2	429.4	431.5	433.6	433.7	433.9	433.9	434.0	431.2
115°	488.0	489.5	491.2	492.9	494.6	496.4	498.3	500.2	502.1	504.1	505.4
117.5°	552.6	553.7	554.7	555.5	556.4	557.2	558.8	560.3	561.9	563.4	564.3
120°	593.2	594.4	595.0	595.6	596.2	596.7	598.2	599.8	601.3	602.9	603.6
122.5°	632.1	633.2	634.0	634.6	635.4	636.1	637.2	638.3	639.4	640.4	641.1
125°	687.6	688.8	689.5	690.3	691.0	691.8	692.2	692.6	693.0	693.4	693.8
127.5°	740.9	742.1	743.0	744.0	744.9	745.8	746.4	747.0	747.6	748.3	748.4
130°	774.1	775.2	776.0	776.8	777.6	778.3	779.1	779.9	780.6	781.4	781.6
132.5°	805.9	807.0	807.6	808.2	808.8	809.4	810.2	811.0	811.8	812.5	812.6
135°	853.0	853.9	854.7	855.5	856.3	857.0	857.6	858.2	858.8	859.3	859.3
137.5°	895.7	896.6	897.1	897.5	897.9	898.4	899.2	900.2	901.1	902.1	902.3
140°	922.1	923.0	923.6	924.2	924.7	925.3	926.1	926.9	927.6	928.4	928.6
142.5°	947.8	948.6	949.2	949.8	950.4	950.9	951.6	952.2	952.8	953.4	953.4
145°	984.3	985.2	985.6	985.9	986.4	986.7	987.1	987.5	987.9	988.3	988.4
147.5°	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7	1019.2	1019.5	1019.9	1019.7
150°	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1	1038.5	1038.9	1039.3	1039.2
152.5°	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1	1055.8	1056.4	1057.1	1057.0
155°	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5	1079.4	1080.4	1081.4	1081.2
157.5°	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9	1100.1	1101.2	1102.3	1102.2
160°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7	1111.8	1113.0	1114.1	1114.0
162.5°	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2	1122.5	1123.9	1125.2	1125.2
165°	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3	1136.8	1138.3	1139.9	1140.0
167.5°	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0
170°	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2
172.5°	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8	1158.3	1159.8	1161.3	1161.2
175°	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9	1163.2	1164.6	1166.0	1165.9
177.5°	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9	1165.1	1166.3	1167.5	1167.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	9.7	9.8	9.6	9.4	9.6	9.8	9.7	9.6	10.6	9.6	9.5
90°	24.8	25.1	25.6	25.9	25.6	25.1	24.8	24.4	23.8	23.1	22.3
92.5°	28.0	28.2	28.5	28.7	28.5	28.2	28.0	27.8	27.0	25.8	24.6
95°	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.2	30.8	29.5
97.5°	35.0	35.2	35.5	35.6	35.5	35.2	35.0	34.9	34.0	32.5	30.9
100°	35.7	35.9	36.2	36.3	36.2	35.9	35.7	35.6	34.7	33.1	31.6
102.5°	36.0	36.3	36.7	37.0	36.7	36.3	36.0	35.6	37.8	42.6	47.4
105°	36.9	37.3	37.6	38.1	37.6	37.3	36.9	36.5	53.3	87.3	121.4
107.5°	196.4	170.8	145.2	119.5	145.2	170.8	196.4	222.1	247.4	272.3	297.2
110°	320.3	292.7	265.3	237.8	265.3	292.7	320.3	347.8	364.6	371.0	377.4



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	425.4	419.7	413.8	408.0	413.8	419.7	425.4	431.2	434.0	433.9	433.9
115°	506.2	507.0	507.7	508.5	507.7	507.0	506.2	505.4	504.1	502.1	500.2
117.5°	564.4	564.6	564.7	564.9	564.7	564.6	564.4	564.3	563.4	561.9	560.3
120°	603.6	603.6	603.6	603.6	603.6	603.6	603.6	603.6	602.9	601.3	599.8
122.5°	641.2	641.4	641.5	641.7	641.5	641.4	641.2	641.1	640.4	639.4	638.3
125°	694.1	694.5	694.9	695.3	694.9	694.5	694.1	693.8	693.4	693.0	692.6
127.5°	748.0	747.6	747.3	746.8	747.3	747.6	748.0	748.4	748.3	747.6	747.0
130°	781.2	780.8	780.4	780.1	780.4	780.8	781.2	781.6	781.4	780.6	779.9
132.5°	812.1	811.6	811.1	810.5	811.1	811.6	812.1	812.6	812.5	811.8	811.0
135°	858.8	858.2	857.6	857.0	857.6	858.2	858.8	859.3	859.3	858.8	858.2
137.5°	901.9	901.6	901.1	900.8	901.1	901.6	901.9	902.3	902.1	901.1	900.2
140°	928.2	927.8	927.5	927.0	927.5	927.8	928.2	928.6	928.4	927.6	926.9
142.5°	952.9	952.4	951.8	951.2	951.8	952.4	952.9	953.4	953.4	952.8	952.2
145°	988.4	988.4	988.4	988.4	988.4	988.4	988.4	988.4	988.3	987.9	987.5
147.5°	1018.8	1017.9	1017.0	1016.2	1017.0	1017.9	1018.8	1019.7	1019.9	1019.5	1019.2
150°	1038.6	1038.0	1037.5	1036.9	1037.5	1038.0	1038.6	1039.2	1039.3	1038.9	1038.5
152.5°	1056.1	1055.2	1054.4	1053.5	1054.4	1055.2	1056.1	1057.0	1057.1	1056.4	1055.8
155°	1080.1	1079.0	1077.8	1076.7	1077.8	1079.0	1080.1	1081.2	1081.4	1080.4	1079.4
157.5°	1100.7	1099.2	1097.7	1096.2	1097.7	1099.2	1100.7	1102.2	1102.3	1101.2	1100.1
160°	1112.7	1111.4	1110.0	1108.6	1110.0	1111.4	1112.7	1114.0	1114.1	1113.0	1111.8
162.5°	1124.0	1122.8	1121.6	1120.4	1121.6	1122.8	1124.0	1125.2	1125.2	1123.9	1122.5
165°	1138.7	1137.3	1135.9	1134.6	1135.9	1137.3	1138.7	1140.0	1139.9	1138.3	1136.8
167.5°	1149.4	1147.9	1146.3	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9
170°	1155.6	1154.1	1152.5	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1
172.5°	1159.6	1157.9	1156.2	1154.5	1156.2	1157.9	1159.6	1161.2	1161.3	1159.8	1158.3
175°	1164.3	1162.8	1161.2	1159.7	1161.2	1162.8	1164.3	1165.9	1166.0	1164.6	1163.2
177.5°	1165.9	1164.3	1162.8	1161.2	1162.8	1164.3	1165.9	1167.4	1167.5	1166.3	1165.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	9.8	9.7	9.0	8.7	7.9	7.7	7.0	6.9	6.7	6.4	6.5
90°	21.5	20.8	18.3	15.8	13.3	10.8	8.5	6.6	4.7	2.8	0.9
92.5°	23.3	22.1	20.2	18.3	16.5	14.6	13.9	14.5	15.0	15.6	16.1
95°	28.2	26.8	24.7	22.6	20.5	18.3	21.3	29.1	37.0	44.9	52.8
97.5°	29.4	27.8	41.7	55.5	69.4	83.2	91.9	95.4	98.9	102.5	106.0
100°	30.0	28.5	58.5	88.5	118.5	148.4	161.5	157.6	153.9	150.0	146.1
102.5°	52.2	56.9	89.6	122.4	155.2	187.9	202.9	200.1	197.3	194.6	191.8
105°	155.4	189.4	206.7	223.9	241.3	258.6	266.1	264.1	261.9	259.8	257.7
107.5°	322.2	347.2	344.4	341.6	339.0	336.2	334.0	332.3	330.6	328.9	327.3
110°	383.7	390.0	387.9	385.8	383.7	381.6	379.7	378.2	376.7	375.1	373.6



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	433.7	433.6	431.5	429.4	427.2	425.2	423.4	422.1	420.6	419.2	417.8
115°	498.3	496.4	494.6	492.9	491.2	489.5	488.0	486.9	485.7	484.6	483.5
117.5°	558.8	557.2	556.4	555.5	554.7	553.7	552.6	551.1	549.7	548.3	546.9
120°	598.2	596.7	596.2	595.6	595.0	594.4	593.2	591.5	589.8	588.1	586.3
122.5°	637.2	636.1	635.4	634.6	634.0	633.2	632.1	630.7	629.3	627.8	626.5
125°	692.2	691.8	691.0	690.3	689.5	688.8	687.6	686.0	684.5	683.0	681.5
127.5°	746.4	745.8	744.9	744.0	743.0	742.1	740.9	739.3	737.8	736.2	734.7
130°	779.1	778.3	777.6	776.8	776.0	775.2	774.1	772.6	771.0	769.5	767.9
132.5°	810.2	809.4	808.8	808.2	807.6	807.0	805.9	804.3	802.8	801.3	799.8
135°	857.6	857.0	856.3	855.5	854.7	853.9	853.0	851.8	850.7	849.5	848.3
137.5°	899.2	898.4	897.9	897.5	897.1	896.6	895.7	894.2	892.8	891.3	889.8
140°	926.1	925.3	924.7	924.2	923.6	923.0	922.1	921.0	919.9	918.7	917.6
142.5°	951.6	950.9	950.4	949.8	949.2	948.6	947.8	946.6	945.5	944.3	943.1
145°	987.1	986.7	986.4	985.9	985.6	985.2	984.3	983.0	981.6	980.2	979.0
147.5°	1018.7	1018.4	1018.0	1017.6	1017.2	1016.8	1016.2	1015.3	1014.4	1013.6	1012.7
150°	1038.1	1037.8	1037.3	1037.0	1036.6	1036.2	1035.7	1035.2	1034.6	1034.0	1033.5
152.5°	1055.1	1054.4	1054.1	1053.9	1053.7	1053.4	1053.2	1052.9	1052.7	1052.4	1052.1
155°	1078.5	1077.5	1077.4	1077.1	1076.9	1076.8	1076.9	1077.3	1077.6	1078.0	1078.4
157.5°	1098.9	1097.8	1097.9	1098.1	1098.4	1098.5	1098.6	1098.7	1098.7	1098.8	1098.8
160°	1110.7	1109.6	1109.7	1109.9	1110.1	1110.3	1110.5	1110.7	1110.9	1111.0	1111.3
162.5°	1121.2	1119.9	1120.1	1120.3	1120.5	1120.7	1121.0	1121.5	1122.1	1122.5	1123.0
165°	1135.3	1133.8	1133.9	1134.1	1134.3	1134.5	1134.9	1135.5	1136.1	1136.6	1137.2
167.5°	1146.3	1144.8	1144.8	1144.8	1144.8	1144.8	1145.2	1146.0	1146.8	1147.5	1148.2
170°	1152.5	1151.1	1151.1	1151.1	1151.1	1151.1	1151.4	1152.2	1153.0	1153.7	1154.5
172.5°	1156.8	1155.2	1155.0	1154.9	1154.7	1154.6	1154.9	1155.9	1156.8	1157.7	1158.6
175°	1161.9	1160.5	1160.4	1160.2	1159.9	1159.8	1160.2	1161.1	1162.1	1163.0	1164.0
177.5°	1163.9	1162.6	1162.4	1162.4	1162.2	1162.0	1162.4	1163.1	1163.9	1164.6	1165.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.4	7.8	9.0	9.9	11.4	12.7	12.9	12.9	13.1	13.0	12.9
90°	2.8	4.7	6.6	8.5	10.8	13.3	15.8	18.3	20.8	21.5	22.3
92.5°	15.6	15.0	14.5	13.9	14.6	16.5	18.3	20.2	22.1	23.3	24.6
95°	44.9	37.0	29.1	21.3	18.3	20.5	22.6	24.7	26.8	28.2	29.5
97.5°	102.5	98.9	95.4	91.9	83.2	69.4	55.5	41.7	27.8	29.4	30.9
100°	150.0	153.9	157.6	161.5	148.4	118.5	88.5	58.5	28.5	30.0	31.6
102.5°	194.6	197.3	200.1	202.9	187.9	155.2	122.4	89.6	56.9	52.2	47.4
105°	259.8	261.9	264.1	266.1	258.6	241.3	223.9	206.7	189.4	155.4	121.4
107.5°	328.9	330.6	332.3	334.0	336.2	339.0	341.6	344.4	347.2	322.2	297.2
110°	375.1	376.7	378.2	379.7	381.6	383.7	385.8	387.9	390.0	383.7	377.4



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	419.2	420.6	422.1	423.4	425.2	427.2	429.4	431.5	433.6	433.7	433.9
115°	484.6	485.7	486.9	488.0	489.5	491.2	492.9	494.6	496.4	498.3	500.2
117.5°	548.3	549.7	551.1	552.6	553.7	554.7	555.5	556.4	557.2	558.8	560.3
120°	588.1	589.8	591.5	593.2	594.4	595.0	595.6	596.2	596.7	598.2	599.8
122.5°	627.8	629.3	630.7	632.1	633.2	634.0	634.6	635.4	636.1	637.2	638.3
125°	683.0	684.5	686.0	687.6	688.8	689.5	690.3	691.0	691.8	692.2	692.6
127.5°	736.2	737.8	739.3	740.9	742.1	743.0	744.0	744.9	745.8	746.4	747.0
130°	769.5	771.0	772.6	774.1	775.2	776.0	776.8	777.6	778.3	779.1	779.9
132.5°	801.3	802.8	804.3	805.9	807.0	807.6	808.2	808.8	809.4	810.2	811.0
135°	849.5	850.7	851.8	853.0	853.9	854.7	855.5	856.3	857.0	857.6	858.2
137.5°	891.3	892.8	894.2	895.7	896.6	897.1	897.5	897.9	898.4	899.2	900.2
140°	918.7	919.9	921.0	922.1	923.0	923.6	924.2	924.7	925.3	926.1	926.9
142.5°	944.3	945.5	946.6	947.8	948.6	949.2	949.8	950.4	950.9	951.6	952.2
145°	980.2	981.6	983.0	984.3	985.2	985.6	985.9	986.4	986.7	987.1	987.5
147.5°	1013.6	1014.4	1015.3	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7	1019.2
150°	1034.0	1034.6	1035.2	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1	1038.5
152.5°	1052.4	1052.7	1052.9	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1	1055.8
155°	1078.0	1077.6	1077.3	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5	1079.4
157.5°	1098.8	1098.7	1098.7	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9	1100.1
160°	1111.0	1110.9	1110.7	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7	1111.8
162.5°	1122.5	1122.1	1121.5	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2	1122.5
165°	1136.6	1136.1	1135.5	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3	1136.8
167.5°	1147.5	1146.8	1146.0	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3	1147.9
170°	1153.7	1153.0	1152.2	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5	1154.1
172.5°	1157.7	1156.8	1155.9	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8	1158.3
175°	1163.0	1162.1	1161.1	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9	1163.2
177.5°	1164.6	1163.9	1163.1	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9	1165.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	12.8	12.7	12.6	12.9	12.7	12.5	13.1
90°	23.1	23.8	24.4	24.8	25.1	25.6	25.9
92.5°	25.8	27.0	27.8	28.0	28.2	28.5	28.7
95°	30.8	32.2	32.9	32.9	32.9	32.9	32.9
97.5°	32.5	34.0	34.9	35.0	35.2	35.5	35.6
100°	33.1	34.7	35.6	35.7	35.9	36.2	36.3
102.5°	42.6	37.8	35.6	36.0	36.3	36.7	37.0
105°	87.3	53.3	36.5	36.9	37.3	37.6	38.1
107.5°	272.3	247.4	222.1	196.4	170.8	145.2	119.5
110°	371.0	364.6	347.8	320.3	292.7	265.3	237.8



TEST NUMBER: P332132-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	433.9	434.0	431.2	425.4	419.7	413.8	408.0
115°	502.1	504.1	505.4	506.2	507.0	507.7	508.5
117.5°	561.9	563.4	564.3	564.4	564.6	564.7	564.9
120°	601.3	602.9	603.6	603.6	603.6	603.6	603.6
122.5°	639.4	640.4	641.1	641.2	641.4	641.5	641.7
125°	693.0	693.4	693.8	694.1	694.5	694.9	695.3
127.5°	747.6	748.3	748.4	748.0	747.6	747.3	746.8
130°	780.6	781.4	781.6	781.2	780.8	780.4	780.1
132.5°	811.8	812.5	812.6	812.1	811.6	811.1	810.5
135°	858.8	859.3	859.3	858.8	858.2	857.6	857.0
137.5°	901.1	902.1	902.3	901.9	901.6	901.1	900.8
140°	927.6	928.4	928.6	928.2	927.8	927.5	927.0
142.5°	952.8	953.4	953.4	952.9	952.4	951.8	951.2
145°	987.9	988.3	988.4	988.4	988.4	988.4	988.4
147.5°	1019.5	1019.9	1019.7	1018.8	1017.9	1017.0	1016.2
150°	1038.9	1039.3	1039.2	1038.6	1038.0	1037.5	1036.9
152.5°	1056.4	1057.1	1057.0	1056.1	1055.2	1054.4	1053.5
155°	1080.4	1081.4	1081.2	1080.1	1079.0	1077.8	1076.7
157.5°	1101.2	1102.3	1102.2	1100.7	1099.2	1097.7	1096.2
160°	1113.0	1114.1	1114.0	1112.7	1111.4	1110.0	1108.6
162.5°	1123.9	1125.2	1125.2	1124.0	1122.8	1121.6	1120.4
165°	1138.3	1139.9	1140.0	1138.7	1137.3	1135.9	1134.6
167.5°	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8
170°	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1
172.5°	1159.8	1161.3	1161.2	1159.6	1157.9	1156.2	1154.5
175°	1164.6	1166.0	1165.9	1164.3	1162.8	1161.2	1159.7
177.5°	1166.3	1167.5	1167.4	1165.9	1164.3	1162.8	1161.2
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0

(END OF REPORT)