

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332138-935

Luminaire Tested: **S123DIW-S560D1320U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332138-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6602.7 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	52	50	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	35	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	31	27	27	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.0	1.0
10°-20°	215.0	3.3
20°-30°	360.8	5.5
30°-40°	408.6	6.2
40°-50°	366.4	5.5
50°-60°	295.7	4.5
60°-70°	206.0	3.1
70°-80°	108.3	1.6
80°-90°	30.7	0.5
90°-100°	54.2	0.8
100°-110°	258.2	3.9
110°-120°	620.2	9.4
120°-130°	789.8	12.0
130°-140°	843.9	12.8
140°-150°	789.1	12.0
150°-160°	636.5	9.6
160°-170°	410.8	6.2
170°-180°	141.6	2.1
0°-30°	642.9	9.7
0°-40°	1051.4	15.9
0°-60°	1713.5	26.0
0°-90°	2058.4	31.2
90°-120°	932.6	14.1
90°-150°	3355.4	50.8
90°-180°	4544.0	68.8
0°-180°	6602.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	27
90°	33	1	33	1	33	16
95°	42	68	42	68	42	35
105°	49	330	49	330	49	111
115°	651	619	651	619	651	602
125°	890	872	890	872	890	795
135°	1097	1086	1097	1086	1097	846
145°	1265	1253	1265	1253	1265	790
155°	1378	1380	1378	1380	1378	636
165°	1452	1456	1452	1456	1452	410
175°	1485	1490	1485	1490	1485	141
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	14.6	13.9	14.1	14.3	13.9	14.0	14.1	14.1	14.2	14.3	13.9
90°	33.2	32.7	32.2	31.8	31.3	30.5	29.5	28.5	27.6	26.6	23.3
92.5°	36.8	36.4	36.2	35.9	35.6	34.6	33.1	31.5	29.9	28.3	25.9
95°	42.1	42.1	42.1	42.1	42.1	41.2	39.5	37.8	36.1	34.4	31.6
97.5°	45.6	45.4	45.1	44.9	44.6	43.5	41.6	39.6	37.6	35.6	53.4
100°	46.5	46.2	46.0	45.7	45.5	44.4	42.4	40.5	38.5	36.5	74.9
102.5°	47.4	46.9	46.5	46.1	45.6	48.5	54.5	60.6	66.7	72.8	114.8
105°	48.7	48.2	47.7	47.3	46.8	68.3	111.8	155.3	198.9	242.5	264.6
107.5°	153.0	185.8	218.6	251.5	284.3	316.7	348.6	380.6	412.4	444.4	440.9
110°	304.4	339.7	374.8	410.0	445.1	466.8	474.9	483.0	491.2	499.3	496.6



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	522.4	529.8	537.2	544.6	552.1	555.7	555.5	555.4	555.3	555.1	552.4
115°	651.0	650.0	649.0	648.0	647.0	645.3	642.8	640.4	637.9	635.5	633.3
117.5°	723.2	723.0	722.7	722.6	722.4	721.3	719.3	717.4	715.4	713.4	712.3
120°	772.7	772.7	772.7	772.7	772.7	771.8	769.8	767.8	765.9	763.9	763.2
122.5°	821.5	821.3	821.0	820.9	820.7	819.9	818.6	817.2	815.8	814.4	813.5
125°	890.1	889.6	889.2	888.6	888.1	887.6	887.2	886.7	886.1	885.7	884.7
127.5°	956.1	956.6	957.1	957.6	958.0	957.9	957.1	956.3	955.5	954.8	953.6
130°	998.6	999.1	999.6	1000.1	1000.6	1000.3	999.4	998.3	997.4	996.3	995.4
132.5°	1037.6	1038.3	1039.0	1039.7	1040.3	1040.2	1039.2	1038.2	1037.2	1036.2	1035.4
135°	1097.2	1097.9	1098.6	1099.3	1100.1	1100.1	1099.3	1098.6	1097.9	1097.2	1096.1
137.5°	1153.1	1153.7	1154.2	1154.6	1155.1	1154.8	1153.6	1152.4	1151.2	1150.0	1149.5
140°	1186.8	1187.3	1187.7	1188.3	1188.8	1188.5	1187.6	1186.5	1185.6	1184.6	1183.9
142.5°	1217.8	1218.5	1219.2	1219.9	1220.6	1220.6	1219.7	1218.9	1218.1	1217.4	1216.6
145°	1265.4	1265.4	1265.4	1265.4	1265.4	1265.2	1264.6	1264.2	1263.7	1263.2	1262.7
147.5°	1300.8	1302.0	1303.1	1304.2	1305.4	1305.7	1305.2	1304.7	1304.2	1303.7	1303.2
150°	1327.4	1328.2	1328.9	1329.6	1330.3	1330.5	1330.0	1329.5	1329.0	1328.5	1328.0
152.5°	1348.7	1349.8	1350.9	1352.0	1353.2	1353.3	1352.5	1351.5	1350.7	1349.8	1349.4
155°	1378.4	1379.8	1381.3	1382.8	1384.2	1384.4	1383.1	1381.9	1380.7	1379.4	1379.2
157.5°	1403.3	1405.2	1407.2	1409.1	1411.0	1411.3	1409.8	1408.3	1406.8	1405.3	1405.6
160°	1419.3	1421.0	1422.7	1424.4	1426.2	1426.3	1424.9	1423.3	1421.9	1420.4	1420.6
162.5°	1434.3	1435.9	1437.4	1438.9	1440.5	1440.4	1438.7	1437.0	1435.4	1433.7	1433.9
165°	1452.5	1454.2	1456.0	1457.7	1459.4	1459.3	1457.3	1455.3	1453.4	1451.4	1451.6
167.5°	1465.6	1467.6	1469.6	1471.4	1473.4	1473.4	1471.4	1469.6	1467.6	1465.6	1465.6
170°	1473.5	1475.5	1477.5	1479.5	1481.4	1481.4	1479.5	1477.5	1475.5	1473.5	1473.5
172.5°	1478.0	1480.1	1482.3	1484.5	1486.6	1486.8	1484.8	1482.8	1480.8	1478.9	1478.7
175°	1484.6	1486.6	1488.6	1490.6	1492.5	1492.6	1490.9	1489.2	1487.5	1485.7	1485.5
177.5°	1486.6	1488.6	1490.6	1492.5	1494.5	1494.7	1493.1	1491.5	1490.0	1488.4	1488.2
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	13.8	13.4	12.0	10.3	9.4	8.1	7.6	6.5	6.5	7.0	7.2
90°	20.1	17.0	13.8	10.9	8.5	6.0	3.5	1.1	3.5	6.0	8.5
92.5°	23.5	21.1	18.7	17.8	18.5	19.2	19.9	20.6	19.9	19.2	18.5
95°	28.9	26.2	23.5	27.2	37.3	47.4	57.4	67.5	57.4	47.4	37.3
97.5°	71.1	88.8	106.5	117.6	122.2	126.7	131.2	135.7	131.2	126.7	122.2
100°	113.3	151.7	190.0	206.8	201.8	196.9	192.0	187.1	192.0	196.9	201.8
102.5°	156.7	198.6	240.6	259.8	256.1	252.6	249.1	245.6	249.1	252.6	256.1
105°	286.7	308.8	331.1	340.7	338.0	335.4	332.6	329.9	332.6	335.4	338.0
107.5°	437.4	433.9	430.4	427.6	425.4	423.3	421.1	419.0	421.1	423.3	425.4
110°	493.9	491.2	488.4	486.1	484.1	482.2	480.3	478.3	480.3	482.2	484.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	549.7	547.0	544.2	542.0	540.3	538.5	536.7	534.9	536.7	538.5	540.3
115°	631.0	628.8	626.6	624.7	623.3	621.8	620.4	618.9	620.4	621.8	623.3
117.5°	711.2	710.0	708.9	707.4	705.6	703.8	702.0	700.2	702.0	703.8	705.6
120°	762.4	761.6	761.0	759.5	757.2	755.0	752.9	750.6	752.9	755.0	757.2
122.5°	812.5	811.6	810.6	809.3	807.4	805.6	803.8	802.0	803.8	805.6	807.4
125°	883.7	882.7	881.8	880.3	878.3	876.3	874.3	872.4	874.3	876.3	878.3
127.5°	952.4	951.2	950.0	948.5	946.5	944.5	942.5	940.6	942.5	944.5	946.5
130°	994.5	993.4	992.5	991.0	989.0	987.1	985.1	983.1	985.1	987.1	989.0
132.5°	1034.7	1033.9	1033.1	1031.7	1029.8	1027.8	1025.8	1023.8	1025.8	1027.8	1029.8
135°	1095.2	1094.2	1093.2	1092.0	1090.5	1089.0	1087.5	1086.1	1087.5	1089.0	1090.5
137.5°	1149.0	1148.4	1147.9	1146.7	1144.8	1143.0	1141.1	1139.2	1141.1	1143.0	1144.8
140°	1183.1	1182.4	1181.6	1180.5	1179.1	1177.6	1176.1	1174.7	1176.1	1177.6	1179.1
142.5°	1215.9	1215.1	1214.4	1213.3	1211.9	1210.4	1208.8	1207.4	1208.8	1210.4	1211.9
145°	1262.2	1261.7	1261.2	1260.2	1258.4	1256.7	1255.0	1253.3	1255.0	1256.7	1258.4
147.5°	1302.7	1302.3	1301.7	1301.0	1299.8	1298.6	1297.5	1296.4	1297.5	1298.6	1299.8
150°	1327.5	1327.1	1326.5	1325.9	1325.2	1324.5	1323.7	1323.0	1323.7	1324.5	1325.2
152.5°	1349.2	1348.9	1348.6	1348.2	1347.9	1347.6	1347.2	1346.9	1347.2	1347.6	1347.9
155°	1379.0	1378.7	1378.5	1378.5	1379.1	1379.6	1380.1	1380.5	1380.1	1379.6	1379.1
157.5°	1405.8	1406.1	1406.4	1406.4	1406.5	1406.6	1406.6	1406.7	1406.6	1406.6	1406.5
160°	1420.9	1421.2	1421.4	1421.6	1421.9	1422.1	1422.4	1422.6	1422.4	1422.1	1421.9
162.5°	1434.2	1434.4	1434.7	1435.1	1435.7	1436.4	1437.0	1437.7	1437.0	1436.4	1435.7
165°	1451.9	1452.2	1452.4	1452.9	1453.6	1454.3	1455.1	1455.9	1455.1	1454.3	1453.6
167.5°	1465.6	1465.6	1465.6	1466.0	1467.1	1468.0	1469.0	1470.0	1469.0	1468.0	1467.1
170°	1473.5	1473.5	1473.5	1474.0	1475.1	1476.0	1477.0	1478.0	1477.0	1476.0	1475.1
172.5°	1478.5	1478.3	1478.1	1478.6	1479.7	1480.9	1482.1	1483.3	1482.1	1480.9	1479.7
175°	1485.2	1485.0	1484.7	1485.2	1486.4	1487.7	1488.9	1490.1	1488.9	1487.7	1486.4
177.5°	1488.0	1487.8	1487.6	1488.0	1489.0	1490.0	1490.9	1491.9	1490.9	1490.0	1489.0
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	7.5	8.3	8.7	9.6	10.0	10.8	11.0	10.8	10.9	11.9	11.0
90°	10.9	13.8	17.0	20.1	23.3	26.6	27.6	28.5	29.5	30.5	31.3
92.5°	17.8	18.7	21.1	23.5	25.9	28.3	29.9	31.5	33.1	34.6	35.6
95°	27.2	23.5	26.2	28.9	31.6	34.4	36.1	37.8	39.5	41.2	42.1
97.5°	117.6	106.5	88.8	71.1	53.4	35.6	37.6	39.6	41.6	43.5	44.6
100°	206.8	190.0	151.7	113.3	74.9	36.5	38.5	40.5	42.4	44.4	45.5
102.5°	259.8	240.6	198.6	156.7	114.8	72.8	66.7	60.6	54.5	48.5	45.6
105°	340.7	331.1	308.8	286.7	264.6	242.5	198.9	155.3	111.8	68.3	46.8
107.5°	427.6	430.4	433.9	437.4	440.9	444.4	412.4	380.6	348.6	316.7	284.3
110°	486.1	488.4	491.2	493.9	496.6	499.3	491.2	483.0	474.9	466.8	445.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	542.0	544.2	547.0	549.7	552.4	555.1	555.3	555.4	555.5	555.7	552.1
115°	624.7	626.6	628.8	631.0	633.3	635.5	637.9	640.4	642.8	645.3	647.0
117.5°	707.4	708.9	710.0	711.2	712.3	713.4	715.4	717.4	719.3	721.3	722.4
120°	759.5	761.0	761.6	762.4	763.2	763.9	765.9	767.8	769.8	771.8	772.7
122.5°	809.3	810.6	811.6	812.5	813.5	814.4	815.8	817.2	818.6	819.9	820.7
125°	880.3	881.8	882.7	883.7	884.7	885.7	886.1	886.7	887.2	887.6	888.1
127.5°	948.5	950.0	951.2	952.4	953.6	954.8	955.5	956.3	957.1	957.9	958.0
130°	991.0	992.5	993.4	994.5	995.4	996.3	997.4	998.3	999.4	1000.3	1000.6
132.5°	1031.7	1033.1	1033.9	1034.7	1035.4	1036.2	1037.2	1038.2	1039.2	1040.2	1040.3
135°	1092.0	1093.2	1094.2	1095.2	1096.1	1097.2	1097.9	1098.6	1099.3	1100.1	1100.1
137.5°	1146.7	1147.9	1148.4	1149.0	1149.5	1150.0	1151.2	1152.4	1153.6	1154.8	1155.1
140°	1180.5	1181.6	1182.4	1183.1	1183.9	1184.6	1185.6	1186.5	1187.6	1188.5	1188.8
142.5°	1213.3	1214.4	1215.1	1215.9	1216.6	1217.4	1218.1	1218.9	1219.7	1220.6	1220.6
145°	1260.2	1261.2	1261.7	1262.2	1262.7	1263.2	1263.7	1264.2	1264.6	1265.2	1265.4
147.5°	1301.0	1301.7	1302.3	1302.7	1303.2	1303.7	1304.2	1304.7	1305.2	1305.7	1305.4
150°	1325.9	1326.5	1327.1	1327.5	1328.0	1328.5	1329.0	1329.5	1330.0	1330.5	1330.3
152.5°	1348.2	1348.6	1348.9	1349.2	1349.4	1349.8	1350.7	1351.5	1352.5	1353.3	1353.2
155°	1378.5	1378.5	1378.7	1379.0	1379.2	1379.4	1380.7	1381.9	1383.1	1384.4	1384.2
157.5°	1406.4	1406.4	1406.1	1405.8	1405.6	1405.3	1406.8	1408.3	1409.8	1411.3	1411.0
160°	1421.6	1421.4	1421.2	1420.9	1420.6	1420.4	1421.9	1423.3	1424.9	1426.3	1426.2
162.5°	1435.1	1434.7	1434.4	1434.2	1433.9	1433.7	1435.4	1437.0	1438.7	1440.4	1440.5
165°	1452.9	1452.4	1452.2	1451.9	1451.6	1451.4	1453.4	1455.3	1457.3	1459.3	1459.4
167.5°	1466.0	1465.6	1465.6	1465.6	1465.6	1465.6	1467.6	1469.6	1471.4	1473.4	1473.4
170°	1474.0	1473.5	1473.5	1473.5	1473.5	1473.5	1475.5	1477.5	1479.5	1481.4	1481.4
172.5°	1478.6	1478.1	1478.3	1478.5	1478.7	1478.9	1480.8	1482.8	1484.8	1486.8	1486.6
175°	1485.2	1484.7	1485.0	1485.2	1485.5	1485.7	1487.5	1489.2	1490.9	1492.6	1492.5
177.5°	1488.0	1487.6	1487.8	1488.0	1488.2	1488.4	1490.0	1491.5	1493.1	1494.7	1494.5
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	11.1	11.2	11.0	10.8	11.0	11.2	11.1	11.0	11.9	10.9	10.8
90°	31.8	32.2	32.7	33.2	32.7	32.2	31.8	31.3	30.5	29.5	28.5
92.5°	35.9	36.2	36.4	36.8	36.4	36.2	35.9	35.6	34.6	33.1	31.5
95°	42.1	42.1	42.1	42.1	42.1	42.1	42.1	42.1	41.2	39.5	37.8
97.5°	44.9	45.1	45.4	45.6	45.4	45.1	44.9	44.6	43.5	41.6	39.6
100°	45.7	46.0	46.2	46.5	46.2	46.0	45.7	45.5	44.4	42.4	40.5
102.5°	46.1	46.5	46.9	47.4	46.9	46.5	46.1	45.6	48.5	54.5	60.6
105°	47.3	47.7	48.2	48.7	48.2	47.7	47.3	46.8	68.3	111.8	155.3
107.5°	251.5	218.6	185.8	153.0	185.8	218.6	251.5	284.3	316.7	348.6	380.6
110°	410.0	374.8	339.7	304.4	339.7	374.8	410.0	445.1	466.8	474.9	483.0



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	544.6	537.2	529.8	522.4	529.8	537.2	544.6	552.1	555.7	555.5	555.4
115°	648.0	649.0	650.0	651.0	650.0	649.0	648.0	647.0	645.3	642.8	640.4
117.5°	722.6	722.7	723.0	723.2	723.0	722.7	722.6	722.4	721.3	719.3	717.4
120°	772.7	772.7	772.7	772.7	772.7	772.7	772.7	772.7	771.8	769.8	767.8
122.5°	820.9	821.0	821.3	821.5	821.3	821.0	820.9	820.7	819.9	818.6	817.2
125°	888.6	889.2	889.6	890.1	889.6	889.2	888.6	888.1	887.6	887.2	886.7
127.5°	957.6	957.1	956.6	956.1	956.6	957.1	957.6	958.0	957.9	957.1	956.3
130°	1000.1	999.6	999.1	998.6	999.1	999.6	1000.1	1000.6	1000.3	999.4	998.3
132.5°	1039.7	1039.0	1038.3	1037.6	1038.3	1039.0	1039.7	1040.3	1040.2	1039.2	1038.2
135°	1099.3	1098.6	1097.9	1097.2	1097.9	1098.6	1099.3	1100.1	1100.1	1099.3	1098.6
137.5°	1154.6	1154.2	1153.7	1153.1	1153.7	1154.2	1154.6	1155.1	1154.8	1153.6	1152.4
140°	1188.3	1187.7	1187.3	1186.8	1187.3	1187.7	1188.3	1188.8	1188.5	1187.6	1186.5
142.5°	1219.9	1219.2	1218.5	1217.8	1218.5	1219.2	1219.9	1220.6	1220.6	1219.7	1218.9
145°	1265.4	1265.4	1265.4	1265.4	1265.4	1265.4	1265.4	1265.4	1265.2	1264.6	1264.2
147.5°	1304.2	1303.1	1302.0	1300.8	1302.0	1303.1	1304.2	1305.4	1305.7	1305.2	1304.7
150°	1329.6	1328.9	1328.2	1327.4	1328.2	1328.9	1329.6	1330.3	1330.5	1330.0	1329.5
152.5°	1352.0	1350.9	1349.8	1348.7	1349.8	1350.9	1352.0	1353.2	1353.3	1352.5	1351.5
155°	1382.8	1381.3	1379.8	1378.4	1379.8	1381.3	1382.8	1384.2	1384.4	1383.1	1381.9
157.5°	1409.1	1407.2	1405.2	1403.3	1405.2	1407.2	1409.1	1411.0	1411.3	1409.8	1408.3
160°	1424.4	1422.7	1421.0	1419.3	1421.0	1422.7	1424.4	1426.2	1426.3	1424.9	1423.3
162.5°	1438.9	1437.4	1435.9	1434.3	1435.9	1437.4	1438.9	1440.5	1440.4	1438.7	1437.0
165°	1457.7	1456.0	1454.2	1452.5	1454.2	1456.0	1457.7	1459.4	1459.3	1457.3	1455.3
167.5°	1471.4	1469.6	1467.6	1465.6	1467.6	1469.6	1471.4	1473.4	1473.4	1471.4	1469.6
170°	1479.5	1477.5	1475.5	1473.5	1475.5	1477.5	1479.5	1481.4	1481.4	1479.5	1477.5
172.5°	1484.5	1482.3	1480.1	1478.0	1480.1	1482.3	1484.5	1486.6	1486.8	1484.8	1482.8
175°	1490.6	1488.6	1486.6	1484.6	1486.6	1488.6	1490.6	1492.5	1492.6	1490.9	1489.2
177.5°	1492.5	1490.6	1488.6	1486.6	1488.6	1490.6	1492.5	1494.5	1494.7	1493.1	1491.5
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	11.0	10.8	10.0	9.6	8.7	8.3	7.5	7.2	7.0	6.5	6.5
90°	27.6	26.6	23.3	20.1	17.0	13.8	10.9	8.5	6.0	3.5	1.1
92.5°	29.9	28.3	25.9	23.5	21.1	18.7	17.8	18.5	19.2	19.9	20.6
95°	36.1	34.4	31.6	28.9	26.2	23.5	27.2	37.3	47.4	57.4	67.5
97.5°	37.6	35.6	53.4	71.1	88.8	106.5	117.6	122.2	126.7	131.2	135.7
100°	38.5	36.5	74.9	113.3	151.7	190.0	206.8	201.8	196.9	192.0	187.1
102.5°	66.7	72.8	114.8	156.7	198.6	240.6	259.8	256.1	252.6	249.1	245.6
105°	198.9	242.5	264.6	286.7	308.8	331.1	340.7	338.0	335.4	332.6	329.9
107.5°	412.4	444.4	440.9	437.4	433.9	430.4	427.6	425.4	423.3	421.1	419.0
110°	491.2	499.3	496.6	493.9	491.2	488.4	486.1	484.1	482.2	480.3	478.3



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	555.3	555.1	552.4	549.7	547.0	544.2	542.0	540.3	538.5	536.7	534.9
115°	637.9	635.5	633.3	631.0	628.8	626.6	624.7	623.3	621.8	620.4	618.9
117.5°	715.4	713.4	712.3	711.2	710.0	708.9	707.4	705.6	703.8	702.0	700.2
120°	765.9	763.9	763.2	762.4	761.6	761.0	759.5	757.2	755.0	752.9	750.6
122.5°	815.8	814.4	813.5	812.5	811.6	810.6	809.3	807.4	805.6	803.8	802.0
125°	886.1	885.7	884.7	883.7	882.7	881.8	880.3	878.3	876.3	874.3	872.4
127.5°	955.5	954.8	953.6	952.4	951.2	950.0	948.5	946.5	944.5	942.5	940.6
130°	997.4	996.3	995.4	994.5	993.4	992.5	991.0	989.0	987.1	985.1	983.1
132.5°	1037.2	1036.2	1035.4	1034.7	1033.9	1033.1	1031.7	1029.8	1027.8	1025.8	1023.8
135°	1097.9	1097.2	1096.1	1095.2	1094.2	1093.2	1092.0	1090.5	1089.0	1087.5	1086.1
137.5°	1151.2	1150.0	1149.5	1149.0	1148.4	1147.9	1146.7	1144.8	1143.0	1141.1	1139.2
140°	1185.6	1184.6	1183.9	1183.1	1182.4	1181.6	1180.5	1179.1	1177.6	1176.1	1174.7
142.5°	1218.1	1217.4	1216.6	1215.9	1215.1	1214.4	1213.3	1211.9	1210.4	1208.8	1207.4
145°	1263.7	1263.2	1262.7	1262.2	1261.7	1261.2	1260.2	1258.4	1256.7	1255.0	1253.3
147.5°	1304.2	1303.7	1303.2	1302.7	1302.3	1301.7	1301.0	1299.8	1298.6	1297.5	1296.4
150°	1329.0	1328.5	1328.0	1327.5	1327.1	1326.5	1325.9	1325.2	1324.5	1323.7	1323.0
152.5°	1350.7	1349.8	1349.4	1349.2	1348.9	1348.6	1348.2	1347.9	1347.6	1347.2	1346.9
155°	1380.7	1379.4	1379.2	1379.0	1378.7	1378.5	1378.5	1379.1	1379.6	1380.1	1380.5
157.5°	1406.8	1405.3	1405.6	1405.8	1406.1	1406.4	1406.4	1406.5	1406.6	1406.6	1406.7
160°	1421.9	1420.4	1420.6	1420.9	1421.2	1421.4	1421.6	1421.9	1422.1	1422.4	1422.6
162.5°	1435.4	1433.7	1433.9	1434.2	1434.4	1434.7	1435.1	1435.7	1436.4	1437.0	1437.7
165°	1453.4	1451.4	1451.6	1451.9	1452.2	1452.4	1452.9	1453.6	1454.3	1455.1	1455.9
167.5°	1467.6	1465.6	1465.6	1465.6	1465.6	1465.6	1466.0	1467.1	1468.0	1469.0	1470.0
170°	1475.5	1473.5	1473.5	1473.5	1473.5	1473.5	1474.0	1475.1	1476.0	1477.0	1478.0
172.5°	1480.8	1478.9	1478.7	1478.5	1478.3	1478.1	1478.6	1479.7	1480.9	1482.1	1483.3
175°	1487.5	1485.7	1485.5	1485.2	1485.0	1484.7	1485.2	1486.4	1487.7	1488.9	1490.1
177.5°	1490.0	1488.4	1488.2	1488.0	1487.8	1487.6	1488.0	1489.0	1490.0	1490.9	1491.9
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.6	8.1	9.4	10.3	12.0	13.4	13.8	13.9	14.3	14.2	14.1
90°	3.5	6.0	8.5	10.9	13.8	17.0	20.1	23.3	26.6	27.6	28.5
92.5°	19.9	19.2	18.5	17.8	18.7	21.1	23.5	25.9	28.3	29.9	31.5
95°	57.4	47.4	37.3	27.2	23.5	26.2	28.9	31.6	34.4	36.1	37.8
97.5°	131.2	126.7	122.2	117.6	106.5	88.8	71.1	53.4	35.6	37.6	39.6
100°	192.0	196.9	201.8	206.8	190.0	151.7	113.3	74.9	36.5	38.5	40.5
102.5°	249.1	252.6	256.1	259.8	240.6	198.6	156.7	114.8	72.8	66.7	60.6
105°	332.6	335.4	338.0	340.7	331.1	308.8	286.7	264.6	242.5	198.9	155.3
107.5°	421.1	423.3	425.4	427.6	430.4	433.9	437.4	440.9	444.4	412.4	380.6
110°	480.3	482.2	484.1	486.1	488.4	491.2	493.9	496.6	499.3	491.2	483.0



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	536.7	538.5	540.3	542.0	544.2	547.0	549.7	552.4	555.1	555.3	555.4
115°	620.4	621.8	623.3	624.7	626.6	628.8	631.0	633.3	635.5	637.9	640.4
117.5°	702.0	703.8	705.6	707.4	708.9	710.0	711.2	712.3	713.4	715.4	717.4
120°	752.9	755.0	757.2	759.5	761.0	761.6	762.4	763.2	763.9	765.9	767.8
122.5°	803.8	805.6	807.4	809.3	810.6	811.6	812.5	813.5	814.4	815.8	817.2
125°	874.3	876.3	878.3	880.3	881.8	882.7	883.7	884.7	885.7	886.1	886.7
127.5°	942.5	944.5	946.5	948.5	950.0	951.2	952.4	953.6	954.8	955.5	956.3
130°	985.1	987.1	989.0	991.0	992.5	993.4	994.5	995.4	996.3	997.4	998.3
132.5°	1025.8	1027.8	1029.8	1031.7	1033.1	1033.9	1034.7	1035.4	1036.2	1037.2	1038.2
135°	1087.5	1089.0	1090.5	1092.0	1093.2	1094.2	1095.2	1096.1	1097.2	1097.9	1098.6
137.5°	1141.1	1143.0	1144.8	1146.7	1147.9	1148.4	1149.0	1149.5	1150.0	1151.2	1152.4
140°	1176.1	1177.6	1179.1	1180.5	1181.6	1182.4	1183.1	1183.9	1184.6	1185.6	1186.5
142.5°	1208.8	1210.4	1211.9	1213.3	1214.4	1215.1	1215.9	1216.6	1217.4	1218.1	1218.9
145°	1255.0	1256.7	1258.4	1260.2	1261.2	1261.7	1262.2	1262.7	1263.2	1263.7	1264.2
147.5°	1297.5	1298.6	1299.8	1301.0	1301.7	1302.3	1302.7	1303.2	1303.7	1304.2	1304.7
150°	1323.7	1324.5	1325.2	1325.9	1326.5	1327.1	1327.5	1328.0	1328.5	1329.0	1329.5
152.5°	1347.2	1347.6	1347.9	1348.2	1348.6	1348.9	1349.2	1349.4	1349.8	1350.7	1351.5
155°	1380.1	1379.6	1379.1	1378.5	1378.5	1378.7	1379.0	1379.2	1379.4	1380.7	1381.9
157.5°	1406.6	1406.6	1406.5	1406.4	1406.4	1406.1	1405.8	1405.6	1405.3	1406.8	1408.3
160°	1422.4	1422.1	1421.9	1421.6	1421.4	1421.2	1420.9	1420.6	1420.4	1421.9	1423.3
162.5°	1437.0	1436.4	1435.7	1435.1	1434.7	1434.4	1434.2	1433.9	1433.7	1435.4	1437.0
165°	1455.1	1454.3	1453.6	1452.9	1452.4	1452.2	1451.9	1451.6	1451.4	1453.4	1455.3
167.5°	1469.0	1468.0	1467.1	1466.0	1465.6	1465.6	1465.6	1465.6	1465.6	1467.6	1469.6
170°	1477.0	1476.0	1475.1	1474.0	1473.5	1473.5	1473.5	1473.5	1473.5	1475.5	1477.5
172.5°	1482.1	1480.9	1479.7	1478.6	1478.1	1478.3	1478.5	1478.7	1478.9	1480.8	1482.8
175°	1488.9	1487.7	1486.4	1485.2	1484.7	1485.0	1485.2	1485.5	1485.7	1487.5	1489.2
177.5°	1490.9	1490.0	1489.0	1488.0	1487.6	1487.8	1488.0	1488.2	1488.4	1490.0	1491.5
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	14.1	14.0	13.9	14.3	14.1	13.9	14.6
90°	29.5	30.5	31.3	31.8	32.2	32.7	33.2
92.5°	33.1	34.6	35.6	35.9	36.2	36.4	36.8
95°	39.5	41.2	42.1	42.1	42.1	42.1	42.1
97.5°	41.6	43.5	44.6	44.9	45.1	45.4	45.6
100°	42.4	44.4	45.5	45.7	46.0	46.2	46.5
102.5°	54.5	48.5	45.6	46.1	46.5	46.9	47.4
105°	111.8	68.3	46.8	47.3	47.7	48.2	48.7
107.5°	348.6	316.7	284.3	251.5	218.6	185.8	153.0
110°	474.9	466.8	445.1	410.0	374.8	339.7	304.4



TEST NUMBER: P332138-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	555.5	555.7	552.1	544.6	537.2	529.8	522.4
115°	642.8	645.3	647.0	648.0	649.0	650.0	651.0
117.5°	719.3	721.3	722.4	722.6	722.7	723.0	723.2
120°	769.8	771.8	772.7	772.7	772.7	772.7	772.7
122.5°	818.6	819.9	820.7	820.9	821.0	821.3	821.5
125°	887.2	887.6	888.1	888.6	889.2	889.6	890.1
127.5°	957.1	957.9	958.0	957.6	957.1	956.6	956.1
130°	999.4	1000.3	1000.6	1000.1	999.6	999.1	998.6
132.5°	1039.2	1040.2	1040.3	1039.7	1039.0	1038.3	1037.6
135°	1099.3	1100.1	1100.1	1099.3	1098.6	1097.9	1097.2
137.5°	1153.6	1154.8	1155.1	1154.6	1154.2	1153.7	1153.1
140°	1187.6	1188.5	1188.8	1188.3	1187.7	1187.3	1186.8
142.5°	1219.7	1220.6	1220.6	1219.9	1219.2	1218.5	1217.8
145°	1264.6	1265.2	1265.4	1265.4	1265.4	1265.4	1265.4
147.5°	1305.2	1305.7	1305.4	1304.2	1303.1	1302.0	1300.8
150°	1330.0	1330.5	1330.3	1329.6	1328.9	1328.2	1327.4
152.5°	1352.5	1353.3	1353.2	1352.0	1350.9	1349.8	1348.7
155°	1383.1	1384.4	1384.2	1382.8	1381.3	1379.8	1378.4
157.5°	1409.8	1411.3	1411.0	1409.1	1407.2	1405.2	1403.3
160°	1424.9	1426.3	1426.2	1424.4	1422.7	1421.0	1419.3
162.5°	1438.7	1440.4	1440.5	1438.9	1437.4	1435.9	1434.3
165°	1457.3	1459.3	1459.4	1457.7	1456.0	1454.2	1452.5
167.5°	1471.4	1473.4	1473.4	1471.4	1469.6	1467.6	1465.6
170°	1479.5	1481.4	1481.4	1479.5	1477.5	1475.5	1473.5
172.5°	1484.8	1486.8	1486.6	1484.5	1482.3	1480.1	1478.0
175°	1490.9	1492.6	1492.5	1490.6	1488.6	1486.6	1484.6
177.5°	1493.1	1494.7	1494.5	1492.5	1490.6	1488.6	1486.6
180°	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1	1490.1

(END OF REPORT)